

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331964-940

Luminaire Tested: **S123DIP-S775D585U940-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331964-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S775D585U940-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 585 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4997.7 lumens
Efficiency: N/A
Efficacy: 124.0 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 40.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331964-940

CATALOG NUMBER: S123DIP-S775D585U940-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331964-940

CATALOG NUMBER: S123DIP-S775D585U940-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	64	64	64	58
1	100	96	92	88	93	89	86	83	78	75	73	67	65	63	57	56	54	50
2	91	84	78	73	85	79	73	69	68	64	61	59	56	53	50	48	46	42
3	83	74	67	61	78	69	63	58	61	56	52	52	49	46	45	42	40	36
4	76	66	58	52	71	62	55	49	54	48	44	47	43	39	40	37	34	31
5	70	59	51	45	65	55	48	42	48	43	38	42	38	34	36	33	30	27
6	65	53	45	39	60	50	42	37	44	38	33	38	34	30	33	29	27	24
7	60	48	40	34	56	45	38	33	40	34	30	35	30	27	30	27	24	21
8	56	43	36	30	52	41	34	29	36	30	26	32	27	24	28	24	21	19
9	52	40	32	27	48	37	31	26	33	28	24	29	25	21	26	22	19	17
10	49	36	29	24	45	34	28	23	31	25	21	27	23	19	24	20	17	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10371	10371	10371	10371
5°	12369	10416	9231	10416
10°	15481	10364	8337	10364
15°	18988	10280	7762	10280
20°	22620	10149	7391	10149
25°	24018	9991	7308	9991
30°	20586	9875	7346	9875
35°	14318	9711	7423	9711
40°	10784	9517	7399	9517
45°	8954	9232	7305	9232
50°	8020	8646	7239	8646
55°	7499	8015	7148	8015
60°	7035	7356	7076	7356
65°	6612	6706	6849	6706
70°	6200	5964	6521	5964
75°	5552	5224	5976	5224
80°	4866	4283	5151	4283
85°	3816	3112	3458	3112



TEST NUMBER: P331964-940

CATALOG NUMBER: S123DIP-S775D585U940-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.9	1.9
10°-20°	304.3	6.1
20°-30°	510.8	10.2
30°-40°	578.4	11.6
40°-50°	518.7	10.4
50°-60°	418.6	8.4
60°-70°	291.7	5.8
70°-80°	153.3	3.1
80°-90°	39.4	0.8
90°-100°	24.9	0.5
100°-110°	118.6	2.4
110°-120°	284.9	5.7
120°-130°	362.8	7.3
130°-140°	387.7	7.8
140°-150°	362.5	7.3
150°-160°	292.4	5.9
160°-170°	188.7	3.8
170°-180°	65.0	1.3
0°-30°	910.1	18.2
0°-40°	1488.4	29.8
0°-60°	2425.7	48.5
0°-90°	2910.1	58.2
90°-120°	428.4	8.6
90°-150°	1541.4	30.8
90°-180°	2088.0	41.8
0°-180°	4997.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	964	964	964	964	964	
5°	1145	964	854	964	1145	119
15°	1704	922	696	922	1704	492
25°	2022	841	615	841	2022	887
35°	1090	739	565	739	1090	708
45°	588	606	480	606	588	465
55°	400	427	381	427	400	359
65°	260	263	269	263	260	259
75°	134	126	144	126	134	143
85°	31	25	28	25	31	37
90°	15	0	15	0	15	8
95°	19	31	19	31	19	16
105°	22	152	22	152	22	51
115°	299	284	299	284	299	276
125°	409	401	409	401	409	365
135°	504	499	504	499	504	389
145°	581	576	581	576	581	363
155°	633	634	633	634	633	292
165°	667	669	667	669	667	188
175°	682	685	682	685	682	65
180°	685	685	685	685	685	



TEST NUMBER: P331964-940

CATALOG NUMBER: S123DIP-S775D585U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5
2.5°	1022.5	1021.8	1019.9	1021.5	1018.4	1014.3	1014.0	1010.2	999.3	998.6	995.7
5°	1144.7	1140.9	1140.5	1140.0	1133.5	1124.6	1107.8	1106.3	1084.0	1072.7	1059.3
7.5°	1302.8	1304.8	1298.0	1292.0	1272.0	1258.8	1240.8	1217.7	1190.3	1162.3	1143.7
10°	1416.4	1431.7	1412.6	1399.5	1387.4	1364.5	1337.9	1304.8	1271.7	1232.9	1203.5
12.5°	1538.1	1545.7	1541.9	1529.6	1510.6	1475.9	1428.7	1392.1	1361.6	1297.1	1271.0
15°	1703.9	1732.4	1714.2	1672.1	1673.1	1639.9	1578.3	1510.6	1474.7	1418.2	1341.2
17.5°	1880.5	1884.1	1876.3	1841.4	1818.0	1772.5	1715.6	1650.7	1577.9	1509.5	1427.8
20°	1974.7	1971.8	1955.5	1937.3	1897.2	1861.7	1799.7	1727.2	1633.9	1566.6	1477.5
22.5°	2026.9	2022.3	2014.6	1999.3	1965.9	1927.8	1872.1	1793.0	1704.1	1611.5	1508.5
25°	2022.3	2028.4	2029.3	2025.1	2013.4	1990.6	1946.7	1883.6	1794.9	1675.9	1568.5
27.5°	1839.3	1847.9	1872.9	1895.0	1919.7	1944.9	1941.5	1910.2	1844.6	1741.9	1610.5
30°	1656.3	1637.6	1683.8	1742.2	1781.9	1851.9	1891.1	1893.5	1856.5	1768.4	1640.4
32.5°	1402.3	1422.9	1443.3	1515.1	1601.9	1680.5	1758.5	1821.4	1828.5	1769.9	1658.0
35°	1089.6	1115.3	1152.6	1189.9	1283.4	1363.6	1500.8	1620.3	1715.6	1728.2	1659.6
37.5°	878.0	890.7	914.4	951.7	1012.8	1108.0	1214.2	1365.3	1503.2	1605.9	1610.3
40°	767.5	771.2	797.8	826.3	875.7	954.2	1049.9	1183.4	1348.6	1492.0	1551.8
42.5°	684.6	692.8	704.1	731.4	770.8	829.8	918.8	1029.1	1180.6	1345.6	1462.5
45°	588.2	597.5	604.6	622.8	650.8	690.5	752.5	853.4	968.7	1139.1	1296.4
47.5°	524.5	525.3	530.5	544.2	563.3	593.1	636.9	701.8	807.6	945.7	1107.3
50°	478.9	486.4	488.3	499.0	514.0	535.9	572.3	627.4	714.3	835.6	984.1
52.5°	446.8	449.1	454.3	462.1	475.1	492.2	523.8	566.9	635.1	738.5	875.0
55°	399.6	399.6	404.7	410.8	418.3	433.6	454.7	486.4	538.2	618.6	731.6
57.5°	355.9	358.2	361.9	363.7	370.1	380.3	397.8	422.0	460.6	522.4	612.2
60°	326.8	331.0	330.6	334.2	339.8	347.8	362.7	382.4	416.9	466.4	542.0
62.5°	301.4	301.1	301.0	305.5	311.1	318.7	328.3	345.4	374.7	418.6	483.0
65°	259.6	258.6	261.9	264.7	266.5	272.2	279.6	294.5	314.1	346.9	396.8
67.5°	222.4	219.7	221.5	222.4	225.6	230.0	236.9	246.2	261.8	288.0	325.7
70°	197.0	194.7	194.2	195.1	198.0	201.2	206.3	215.2	229.7	250.7	278.2
72.5°	170.9	169.2	169.2	171.2	172.5	174.7	178.3	186.5	198.0	213.7	239.4
75°	133.5	133.5	133.5	133.9	135.4	137.2	140.1	144.3	153.1	164.3	181.6
77.5°	100.0	100.0	99.4	99.3	101.4	102.3	102.9	106.8	111.7	119.3	131.9
80°	78.5	76.1	77.0	78.5	79.4	79.8	81.2	82.1	86.4	90.6	99.4
82.5°	58.2	56.3	56.4	58.7	58.9	59.3	60.7	62.0	63.6	67.4	72.1
85°	30.9	30.9	31.3	31.3	31.7	31.3	32.6	33.2	33.2	35.5	38.3
87.5°	14.3	13.5	13.8	14.1	13.7	14.0	14.3	14.5	14.9	15.2	15.2
90°	15.2	15.1	14.8	14.6	14.4	14.0	13.6	13.1	12.7	12.2	10.7
92.5°	16.9	16.8	16.6	16.5	16.3	15.9	15.2	14.4	13.7	13.0	11.9
95°	19.4	19.4	19.4	19.4	19.4	18.9	18.1	17.4	16.6	15.8	14.5
97.5°	21.0	20.9	20.7	20.6	20.5	20.0	19.1	18.2	17.3	16.4	24.5
100°	21.4	21.2	21.1	21.0	20.9	20.4	19.5	18.5	17.7	16.8	34.4
102.5°	21.8	21.6	21.4	21.1	21.0	22.3	25.1	27.8	30.7	33.4	52.7
105°	22.4	22.1	21.9	21.7	21.5	31.4	51.4	71.3	91.4	111.4	121.5
107.5°	70.3	85.3	100.4	115.5	130.6	145.4	160.2	174.8	189.5	204.1	202.5
110°	139.8	156.0	172.2	188.3	204.5	214.5	218.2	221.9	225.6	229.3	228.1



TEST NUMBER: P331964-940

CATALOG NUMBER: S123DIP-S775D585U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	240.0	243.3	246.7	250.2	253.6	255.3	255.2	255.1	255.1	255.0	253.8
115°	299.1	298.6	298.2	297.7	297.2	296.5	295.3	294.2	293.1	291.9	290.9
117.5°	332.3	332.2	332.1	332.0	331.9	331.4	330.5	329.6	328.7	327.7	327.3
120°	355.0	355.0	355.0	355.0	355.0	354.5	353.7	352.8	351.9	350.9	350.6
122.5°	377.4	377.3	377.2	377.1	377.0	376.7	376.0	375.4	374.8	374.2	373.7
125°	408.9	408.7	408.5	408.2	408.0	407.8	407.5	407.3	407.1	406.9	406.4
127.5°	439.3	439.4	439.7	439.9	440.1	440.1	439.7	439.3	439.0	438.6	438.1
130°	458.8	459.0	459.2	459.4	459.7	459.5	459.1	458.6	458.2	457.7	457.3
132.5°	476.6	477.0	477.2	477.6	478.0	477.9	477.4	477.0	476.5	476.1	475.6
135°	504.0	504.4	504.7	505.1	505.3	505.3	505.1	504.7	504.4	504.0	503.5
137.5°	529.8	529.9	530.2	530.4	530.7	530.5	529.9	529.4	528.9	528.3	528.1
140°	545.2	545.5	545.6	545.9	546.1	546.0	545.5	545.1	544.7	544.2	543.9
142.5°	559.5	559.7	560.1	560.4	560.7	560.7	560.4	560.0	559.6	559.3	558.9
145°	581.3	581.3	581.3	581.3	581.3	581.2	580.9	580.8	580.5	580.3	580.1
147.5°	597.6	598.2	598.6	599.1	599.7	599.9	599.6	599.4	599.1	599.0	598.7
150°	609.8	610.1	610.5	610.8	611.2	611.2	611.0	610.7	610.6	610.3	610.1
152.5°	619.6	620.1	620.6	621.2	621.6	621.7	621.3	620.9	620.5	620.1	619.9
155°	633.2	633.9	634.5	635.3	635.9	636.0	635.4	634.8	634.3	633.7	633.6
157.5°	644.7	645.6	646.5	647.3	648.2	648.4	647.6	646.9	646.3	645.6	645.7
160°	652.0	652.8	653.6	654.4	655.1	655.2	654.5	653.9	653.2	652.6	652.6
162.5°	659.0	659.6	660.3	661.0	661.7	661.7	660.9	660.1	659.4	658.6	658.7
165°	667.3	668.1	668.9	669.7	670.5	670.4	669.5	668.6	667.7	666.7	666.9
167.5°	673.2	674.2	675.1	676.0	676.9	676.9	676.0	675.1	674.2	673.2	673.2
170°	676.9	677.9	678.8	679.7	680.6	680.6	679.7	678.8	677.9	676.9	676.9
172.5°	678.9	679.9	681.0	682.0	683.0	683.0	682.1	681.2	680.3	679.4	679.3
175°	682.0	683.0	683.9	684.7	685.6	685.7	684.9	684.1	683.3	682.5	682.4
177.5°	683.0	683.9	684.7	685.6	686.5	686.6	685.9	685.2	684.5	683.8	683.7
180°	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6



TEST NUMBER: P331964-940

CATALOG NUMBER: S123DIP-S775D585U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5
2.5°	993.4	990.4	987.4	982.2	977.8	971.3	969.5	967.2	960.6	954.6	950.1
5°	1054.1	1042.9	1026.5	1011.6	999.5	983.1	973.8	964.0	950.0	937.4	927.1
7.5°	1117.6	1095.6	1070.1	1042.7	1017.1	992.5	972.6	954.8	935.2	916.7	902.2
10°	1168.0	1136.2	1100.8	1062.5	1029.8	998.1	971.4	948.2	922.9	901.0	882.8
12.5°	1225.5	1178.5	1129.5	1083.1	1044.4	1000.3	968.1	938.4	909.8	883.4	863.0
15°	1293.6	1233.9	1175.9	1112.0	1053.2	998.1	959.8	922.5	889.3	862.2	836.1
17.5°	1355.6	1287.9	1211.6	1133.8	1062.8	997.6	944.0	901.7	860.2	827.2	801.1
20°	1390.7	1313.7	1227.3	1146.6	1068.1	995.2	936.5	886.0	841.2	806.2	776.8
22.5°	1420.9	1330.8	1241.4	1155.1	1067.7	989.3	922.7	870.8	822.2	787.9	756.6
25°	1452.3	1344.4	1254.8	1153.5	1056.0	974.7	900.0	841.2	792.6	752.5	720.3
27.5°	1479.2	1343.5	1237.2	1128.2	1037.5	956.1	876.3	813.2	761.7	718.1	685.4
30°	1497.1	1345.4	1218.9	1111.1	1019.6	935.5	858.0	794.5	740.4	696.1	665.2
32.5°	1508.3	1344.3	1202.1	1087.2	991.1	916.9	838.2	772.5	716.8	673.2	643.5
35°	1514.8	1336.1	1173.1	1037.8	945.3	873.0	807.2	739.0	680.6	640.0	606.5
37.5°	1501.8	1318.8	1139.5	990.2	888.9	817.7	762.3	704.3	648.5	603.7	574.8
40°	1481.2	1307.6	1113.4	956.5	850.1	781.5	734.3	677.3	622.2	579.8	552.7
42.5°	1442.0	1284.8	1084.6	919.2	809.8	741.1	697.8	650.1	598.0	558.1	531.1
45°	1346.3	1235.2	1041.5	863.2	750.2	679.2	641.0	606.5	559.3	520.5	497.1
47.5°	1213.5	1160.7	979.1	804.1	688.0	619.7	580.0	552.1	517.7	486.4	464.0
50°	1121.3	1099.4	936.9	763.8	646.6	579.8	541.5	516.3	491.6	460.3	439.8
52.5°	1014.9	1028.4	887.6	721.9	604.3	538.7	502.7	482.7	460.2	434.5	416.6
55°	865.0	914.0	802.5	651.7	541.5	478.9	444.9	427.1	414.1	394.9	379.5
57.5°	724.7	787.1	710.4	579.3	479.8	425.9	393.2	373.8	365.4	355.4	343.3
60°	641.4	703.0	644.7	530.7	438.4	387.0	358.0	341.7	333.3	326.3	316.0
62.5°	567.1	629.5	580.4	481.5	397.6	350.0	324.9	308.9	302.3	298.6	289.9
65°	464.9	518.6	486.0	404.7	339.4	297.4	274.5	263.3	257.3	255.8	250.2
67.5°	378.4	419.3	395.5	335.7	284.3	248.0	228.5	219.0	214.4	213.9	209.7
70°	321.6	359.9	341.7	287.6	243.3	214.7	198.0	189.5	186.7	186.3	184.0
72.5°	277.6	304.3	289.8	244.6	210.4	184.5	172.2	163.4	160.2	160.9	159.3
75°	205.4	225.5	217.0	185.8	158.3	141.4	131.2	125.6	122.8	124.2	122.3
77.5°	147.8	160.5	152.9	131.3	114.3	102.1	94.6	91.1	88.6	88.5	87.7
80°	111.6	119.0	114.9	101.7	87.7	77.5	71.4	69.1	67.7	67.2	66.8
82.5°	79.5	85.8	80.9	71.9	62.3	56.2	52.8	49.7	48.7	49.0	48.4
85°	40.1	42.4	40.6	35.0	31.3	28.4	26.6	25.2	24.3	24.7	23.8
87.5°	15.7	15.8	14.4	12.6	11.6	10.3	10.1	9.1	8.6	8.7	8.6
90°	9.3	7.8	6.3	5.0	3.9	2.8	1.6	0.5	1.6	2.8	3.9
92.5°	10.8	9.7	8.6	8.2	8.5	8.8	9.2	9.5	9.2	8.8	8.5
95°	13.3	12.0	10.8	12.5	17.1	21.8	26.4	31.0	26.4	21.8	17.1
97.5°	32.6	40.8	49.0	54.0	56.1	58.2	60.3	62.3	60.3	58.2	56.1
100°	52.1	69.6	87.3	95.0	92.7	90.5	88.2	86.0	88.2	90.5	92.7
102.5°	72.0	91.2	110.5	119.3	117.7	116.1	114.4	112.8	114.4	116.1	117.7
105°	131.7	141.9	152.0	156.5	155.2	154.1	152.8	151.6	152.8	154.1	155.2
107.5°	200.9	199.3	197.7	196.4	195.5	194.5	193.4	192.4	193.4	194.5	195.5
110°	226.9	225.6	224.4	223.3	222.4	221.5	220.6	219.7	220.6	221.5	222.4



TEST NUMBER: P331964-940

CATALOG NUMBER: S123DIP-S775D585U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	252.5	251.3	250.0	249.0	248.2	247.4	246.6	245.8	246.6	247.4	248.2
115°	289.9	288.9	287.8	287.0	286.3	285.6	285.0	284.3	285.0	285.6	286.3
117.5°	326.7	326.2	325.7	324.9	324.1	323.3	322.4	321.6	322.4	323.3	324.1
120°	350.3	349.9	349.6	348.9	347.9	346.9	345.8	344.8	345.8	346.9	347.9
122.5°	373.3	372.8	372.4	371.8	371.0	370.1	369.3	368.5	369.3	370.1	371.0
125°	406.0	405.6	405.1	404.4	403.5	402.6	401.7	400.7	401.7	402.6	403.5
127.5°	437.6	436.9	436.4	435.7	434.8	433.9	433.0	432.1	433.0	433.9	434.8
130°	456.8	456.4	455.9	455.2	454.3	453.4	452.5	451.7	452.5	453.4	454.3
132.5°	475.3	474.9	474.6	473.9	473.1	472.2	471.3	470.4	471.3	472.2	473.1
135°	503.1	502.7	502.2	501.7	501.0	500.2	499.6	498.9	499.6	500.2	501.0
137.5°	527.8	527.5	527.4	526.7	525.9	525.0	524.2	523.3	524.2	525.0	525.9
140°	543.5	543.1	542.9	542.3	541.6	541.0	540.3	539.6	540.3	541.0	541.6
142.5°	558.6	558.2	557.9	557.4	556.7	556.1	555.4	554.6	555.4	556.1	556.7
145°	579.9	579.6	579.4	578.9	578.1	577.3	576.5	575.7	576.5	577.3	578.1
147.5°	598.4	598.2	598.0	597.6	597.1	596.6	596.1	595.6	596.1	596.6	597.1
150°	609.8	609.7	609.4	609.1	608.8	608.4	608.1	607.8	608.1	608.4	608.8
152.5°	619.8	619.6	619.6	619.4	619.2	619.0	618.9	618.8	618.9	619.0	619.2
155°	633.5	633.4	633.3	633.3	633.6	633.7	634.0	634.2	634.0	633.7	633.6
157.5°	645.9	646.0	646.0	646.1	646.1	646.1	646.2	646.2	646.2	646.1	646.1
160°	652.7	652.8	653.0	653.1	653.2	653.4	653.4	653.5	653.4	653.4	653.2
162.5°	658.9	659.0	659.1	659.2	659.6	659.9	660.1	660.5	660.1	659.9	659.6
165°	667.0	667.1	667.2	667.4	667.8	668.2	668.4	668.8	668.4	668.2	667.8
167.5°	673.2	673.2	673.2	673.5	674.0	674.4	674.8	675.3	674.8	674.4	674.0
170°	676.9	676.9	676.9	677.2	677.6	678.1	678.5	678.9	678.5	678.1	677.6
172.5°	679.2	679.1	679.0	679.2	679.8	680.3	680.9	681.4	680.9	680.3	679.8
175°	682.3	682.2	682.1	682.3	682.9	683.4	684.0	684.6	684.0	683.4	682.9
177.5°	683.6	683.5	683.4	683.6	684.0	684.5	684.9	685.4	684.9	684.5	684.0
180°	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6



TEST NUMBER: P331964-940

CATALOG NUMBER: S123DIP-S775D585U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5
2.5°	947.4	944.9	941.1	935.5	931.0	923.9	923.9	925.1	925.1	924.7	923.9
5°	918.7	911.7	903.3	893.5	883.2	873.0	871.1	867.4	864.6	862.7	860.3
7.5°	888.4	875.9	863.7	850.0	837.5	827.2	819.9	814.0	810.1	806.0	803.1
10°	867.8	852.4	837.9	823.5	807.6	795.0	787.1	781.5	777.3	773.6	771.7
12.5°	843.6	825.9	809.9	796.2	778.8	765.9	758.3	755.7	750.7	742.9	738.8
15°	808.1	791.8	772.6	751.6	743.2	727.3	718.5	714.3	711.4	705.3	703.5
17.5°	777.8	756.3	734.9	719.2	703.6	690.7	685.7	680.6	676.8	671.8	670.4
20°	753.5	734.3	714.7	697.9	681.5	667.5	663.3	659.6	655.9	653.5	651.7
22.5°	728.8	709.7	693.4	677.7	660.3	651.1	646.6	642.5	639.8	638.3	636.4
25°	694.2	677.3	659.2	645.2	631.2	625.1	622.2	619.9	618.0	615.7	615.3
27.5°	663.2	644.9	630.1	617.1	607.0	601.9	599.2	598.1	598.5	599.3	599.9
30°	640.0	623.2	611.1	599.9	590.6	585.9	585.4	585.4	587.3	587.7	588.7
32.5°	618.8	604.9	592.8	581.9	574.9	571.7	573.5	573.5	575.0	576.1	577.8
35°	587.7	575.6	566.2	557.0	550.9	552.2	553.2	554.1	556.4	559.3	561.2
37.5°	558.1	547.6	537.9	530.6	527.8	530.3	532.5	534.5	537.3	539.4	541.3
40°	536.8	528.9	519.6	513.0	514.0	515.4	517.3	519.6	521.9	523.3	525.2
42.5°	517.0	508.7	501.7	496.2	497.6	499.4	500.4	501.7	504.4	506.8	508.0
45°	486.9	480.4	473.9	470.6	471.5	472.4	473.3	474.7	477.1	478.9	479.5
47.5°	453.0	448.4	444.1	440.9	442.4	442.0	443.2	446.2	446.9	448.1	450.7
50°	431.3	427.1	422.0	421.1	421.1	421.1	421.5	425.3	425.3	427.1	429.0
52.5°	407.4	404.7	401.4	399.8	399.0	399.0	401.0	402.9	403.6	406.3	408.1
55°	372.0	369.3	366.5	365.1	364.1	365.1	368.8	369.7	372.0	373.4	374.9
57.5°	335.2	333.1	330.8	330.0	329.8	331.1	333.1	335.9	336.5	340.8	343.0
60°	310.9	307.6	305.8	305.8	304.9	309.1	308.1	312.8	313.7	316.5	319.8
62.5°	285.9	281.5	280.7	280.7	282.0	283.3	284.5	286.6	289.1	292.6	295.2
65°	245.6	243.3	246.5	246.0	245.0	247.9	247.9	250.2	253.0	256.3	261.4
67.5°	207.3	206.2	206.4	206.4	207.9	209.5	210.7	212.8	216.2	219.6	222.9
70°	181.6	183.0	180.7	182.5	184.0	184.4	185.3	188.2	191.9	194.2	198.0
72.5°	156.6	156.5	156.8	157.5	158.9	159.7	160.7	163.9	168.0	170.0	172.9
75°	120.5	119.9	121.4	121.4	123.7	124.7	125.6	127.0	130.7	133.5	135.8
77.5°	87.9	88.5	88.2	89.8	89.2	89.3	92.2	93.6	94.0	99.5	100.8
80°	66.3	67.2	67.7	68.1	68.7	67.7	71.0	72.3	72.3	75.6	77.9
82.5°	47.6	48.2	49.4	49.8	49.9	50.9	51.2	52.2	53.3	54.8	57.8
85°	23.8	25.2	25.7	25.2	25.7	24.7	26.1	26.6	27.1	27.1	27.1
87.5°	8.5	9.1	9.0	9.7	9.6	10.3	10.3	9.7	9.8	11.1	9.6
90°	5.0	6.3	7.8	9.3	10.7	12.2	12.7	13.1	13.6	14.0	14.4
92.5°	8.2	8.6	9.7	10.8	11.9	13.0	13.7	14.4	15.2	15.9	16.3
95°	12.5	10.8	12.0	13.3	14.5	15.8	16.6	17.4	18.1	18.9	19.4
97.5°	54.0	49.0	40.8	32.6	24.5	16.4	17.3	18.2	19.1	20.0	20.5
100°	95.0	87.3	69.6	52.1	34.4	16.8	17.7	18.5	19.5	20.4	20.9
102.5°	119.3	110.5	91.2	72.0	52.7	33.4	30.7	27.8	25.1	22.3	21.0
105°	156.5	152.0	141.9	131.7	121.5	111.4	91.4	71.3	51.4	31.4	21.5
107.5°	196.4	197.7	199.3	200.9	202.5	204.1	189.5	174.8	160.2	145.4	130.6
110°	223.3	224.4	225.6	226.9	228.1	229.3	225.6	221.9	218.2	214.5	204.5



TEST NUMBER: P331964-940

CATALOG NUMBER: S123DIP-S775D585U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	249.0	250.0	251.3	252.5	253.8	255.0	255.1	255.1	255.2	255.3	253.6
115°	287.0	287.8	288.9	289.9	290.9	291.9	293.1	294.2	295.3	296.5	297.2
117.5°	324.9	325.7	326.2	326.7	327.3	327.7	328.7	329.6	330.5	331.4	331.9
120°	348.9	349.6	349.9	350.3	350.6	350.9	351.9	352.8	353.7	354.5	355.0
122.5°	371.8	372.4	372.8	373.3	373.7	374.2	374.8	375.4	376.0	376.7	377.0
125°	404.4	405.1	405.6	406.0	406.4	406.9	407.1	407.3	407.5	407.8	408.0
127.5°	435.7	436.4	436.9	437.6	438.1	438.6	439.0	439.3	439.7	440.1	440.1
130°	455.2	455.9	456.4	456.8	457.3	457.7	458.2	458.6	459.1	459.5	459.7
132.5°	473.9	474.6	474.9	475.3	475.6	476.1	476.5	477.0	477.4	477.9	478.0
135°	501.7	502.2	502.7	503.1	503.5	504.0	504.4	504.7	505.1	505.3	505.3
137.5°	526.7	527.4	527.5	527.8	528.1	528.3	528.9	529.4	529.9	530.5	530.7
140°	542.3	542.9	543.1	543.5	543.9	544.2	544.7	545.1	545.5	546.0	546.1
142.5°	557.4	557.9	558.2	558.6	558.9	559.3	559.6	560.0	560.4	560.7	560.7
145°	578.9	579.4	579.6	579.9	580.1	580.3	580.5	580.8	580.9	581.2	581.3
147.5°	597.6	598.0	598.2	598.4	598.7	599.0	599.1	599.4	599.6	599.9	599.7
150°	609.1	609.4	609.7	609.8	610.1	610.3	610.6	610.7	611.0	611.2	611.2
152.5°	619.4	619.6	619.6	619.8	619.9	620.1	620.5	620.9	621.3	621.7	621.6
155°	633.3	633.3	633.4	633.5	633.6	633.7	634.3	634.8	635.4	636.0	635.9
157.5°	646.1	646.0	646.0	645.9	645.7	645.6	646.3	646.9	647.6	648.4	648.2
160°	653.1	653.0	652.8	652.7	652.6	652.6	653.2	653.9	654.5	655.2	655.1
162.5°	659.2	659.1	659.0	658.9	658.7	658.6	659.4	660.1	660.9	661.7	661.7
165°	667.4	667.2	667.1	667.0	666.9	666.7	667.7	668.6	669.5	670.4	670.5
167.5°	673.5	673.2	673.2	673.2	673.2	673.2	674.2	675.1	676.0	676.9	676.9
170°	677.2	676.9	676.9	676.9	676.9	676.9	677.9	678.8	679.7	680.6	680.6
172.5°	679.2	679.0	679.1	679.2	679.3	679.4	680.3	681.2	682.1	683.0	683.0
175°	682.3	682.1	682.2	682.3	682.4	682.5	683.3	684.1	684.9	685.7	685.6
177.5°	683.6	683.4	683.5	683.6	683.7	683.8	684.5	685.2	685.9	686.6	686.5
180°	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6



TEST NUMBER: P331964-940

CATALOG NUMBER: S123DIP-S775D585U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5
2.5°	921.3	921.0	923.5	921.7	923.5	921.0	921.3	923.9	924.7	925.1	925.1
5°	857.6	859.0	854.3	854.3	854.3	859.0	857.6	860.3	862.7	864.6	867.4
7.5°	800.8	798.7	798.9	796.4	798.9	798.7	800.8	803.1	806.0	810.1	814.0
10°	766.1	763.3	762.3	762.8	762.3	763.3	766.1	771.7	773.6	777.3	781.5
12.5°	737.3	736.7	730.6	730.7	730.6	736.7	737.3	738.8	742.9	750.7	755.7
15°	703.5	694.6	693.7	696.5	693.7	694.6	703.5	703.5	705.3	711.4	714.3
17.5°	669.6	664.9	665.2	663.8	665.2	664.9	669.6	670.4	671.8	676.8	680.6
20°	651.7	648.9	648.5	645.2	648.5	648.9	651.7	651.7	653.5	655.9	659.6
22.5°	635.3	634.4	634.6	631.0	634.6	634.4	635.3	636.4	638.3	639.8	642.5
25°	614.8	617.2	615.3	615.3	615.3	617.2	614.8	615.3	615.7	618.0	619.9
27.5°	601.0	600.9	599.9	599.9	599.9	600.9	601.0	599.9	599.3	598.5	598.1
30°	590.6	590.0	591.0	591.0	591.0	590.0	590.6	588.7	587.7	587.3	585.4
32.5°	580.1	580.8	580.9	581.3	580.9	580.8	580.1	577.8	576.1	575.0	573.5
35°	563.9	564.4	565.8	564.9	565.8	564.4	563.9	561.2	559.3	556.4	554.1
37.5°	542.1	544.2	543.8	544.5	543.8	544.2	542.1	541.3	539.4	537.3	534.5
40°	525.7	527.1	526.6	526.6	526.6	527.1	525.7	525.2	523.3	521.9	519.6
42.5°	508.8	509.9	508.6	507.9	508.6	509.9	508.8	508.0	506.8	504.4	501.7
45°	481.3	480.4	481.8	479.9	481.8	480.4	481.3	479.5	478.9	477.1	474.7
47.5°	450.5	451.4	451.8	453.2	451.8	451.4	450.5	450.7	448.1	446.9	446.2
50°	430.0	432.7	432.7	432.3	432.7	432.7	430.0	429.0	427.1	425.3	425.3
52.5°	409.7	411.1	413.0	412.9	413.0	411.1	409.7	408.1	406.3	403.6	402.9
55°	378.6	379.5	380.5	380.9	380.5	379.5	378.6	374.9	373.4	372.0	369.7
57.5°	346.3	345.9	348.1	348.8	348.1	345.9	346.3	343.0	340.8	336.5	335.9
60°	323.5	323.5	327.3	328.7	327.3	323.5	323.5	319.8	316.5	313.7	312.8
62.5°	299.3	300.8	304.4	302.5	304.4	300.8	299.3	295.2	292.6	289.1	286.6
65°	263.8	267.5	267.1	268.9	267.1	267.5	263.8	261.4	256.3	253.0	250.2
67.5°	226.7	229.0	232.4	232.6	232.4	229.0	226.7	222.9	219.6	216.2	212.8
70°	201.7	204.0	205.9	207.2	205.9	204.0	201.7	198.0	194.2	191.9	188.2
72.5°	177.4	178.6	183.1	181.1	183.1	178.6	177.4	172.9	170.0	168.0	163.9
75°	139.1	142.4	145.2	143.7	145.2	142.4	139.1	135.8	133.5	130.7	127.0
77.5°	102.9	106.1	107.5	106.3	107.5	106.1	102.9	100.8	99.5	94.0	93.6
80°	81.2	80.8	83.6	83.1	83.6	80.8	81.2	77.9	75.6	72.3	72.3
82.5°	59.6	59.1	60.4	60.7	60.4	59.1	59.6	57.8	54.8	53.3	52.2
85°	29.0	30.3	28.4	28.0	28.4	30.3	29.0	27.1	27.1	27.1	26.6
87.5°	9.6	9.7	9.4	9.0	9.4	9.7	9.6	9.6	11.1	9.8	9.7
90°	14.6	14.8	15.1	15.2	15.1	14.8	14.6	14.4	14.0	13.6	13.1
92.5°	16.5	16.6	16.8	16.9	16.8	16.6	16.5	16.3	15.9	15.2	14.4
95°	19.4	19.4	19.4	19.4	19.4	19.4	19.4	19.4	18.9	18.1	17.4
97.5°	20.6	20.7	20.9	21.0	20.9	20.7	20.6	20.5	20.0	19.1	18.2
100°	21.0	21.1	21.2	21.4	21.2	21.1	21.0	20.9	20.4	19.5	18.5
102.5°	21.1	21.4	21.6	21.8	21.6	21.4	21.1	21.0	22.3	25.1	27.8
105°	21.7	21.9	22.1	22.4	22.1	21.9	21.7	21.5	31.4	51.4	71.3
107.5°	115.5	100.4	85.3	70.3	85.3	100.4	115.5	130.6	145.4	160.2	174.8
110°	188.3	172.2	156.0	139.8	156.0	172.2	188.3	204.5	214.5	218.2	221.9



TEST NUMBER: P331964-940

CATALOG NUMBER: S123DIP-S775D585U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	250.2	246.7	243.3	240.0	243.3	246.7	250.2	253.6	255.3	255.2	255.1
115°	297.7	298.2	298.6	299.1	298.6	298.2	297.7	297.2	296.5	295.3	294.2
117.5°	332.0	332.1	332.2	332.3	332.2	332.1	332.0	331.9	331.4	330.5	329.6
120°	355.0	355.0	355.0	355.0	355.0	355.0	355.0	355.0	354.5	353.7	352.8
122.5°	377.1	377.2	377.3	377.4	377.3	377.2	377.1	377.0	376.7	376.0	375.4
125°	408.2	408.5	408.7	408.9	408.7	408.5	408.2	408.0	407.8	407.5	407.3
127.5°	439.9	439.7	439.4	439.3	439.4	439.7	439.9	440.1	440.1	439.7	439.3
130°	459.4	459.2	459.0	458.8	459.0	459.2	459.4	459.7	459.5	459.1	458.6
132.5°	477.6	477.2	477.0	476.6	477.0	477.2	477.6	478.0	477.9	477.4	477.0
135°	505.1	504.7	504.4	504.0	504.4	504.7	505.1	505.3	505.3	505.1	504.7
137.5°	530.4	530.2	529.9	529.8	529.9	530.2	530.4	530.7	530.5	529.9	529.4
140°	545.9	545.6	545.5	545.2	545.5	545.6	545.9	546.1	546.0	545.5	545.1
142.5°	560.4	560.1	559.7	559.5	559.7	560.1	560.4	560.7	560.7	560.4	560.0
145°	581.3	581.3	581.3	581.3	581.3	581.3	581.3	581.3	581.2	580.9	580.8
147.5°	599.1	598.6	598.2	597.6	598.2	598.6	599.1	599.7	599.9	599.6	599.4
150°	610.8	610.5	610.1	609.8	610.1	610.5	610.8	611.2	611.2	611.0	610.7
152.5°	621.2	620.6	620.1	619.6	620.1	620.6	621.2	621.6	621.7	621.3	620.9
155°	635.3	634.5	633.9	633.2	633.9	634.5	635.3	635.9	636.0	635.4	634.8
157.5°	647.3	646.5	645.6	644.7	645.6	646.5	647.3	648.2	648.4	647.6	646.9
160°	654.4	653.6	652.8	652.0	652.8	653.6	654.4	655.1	655.2	654.5	653.9
162.5°	661.0	660.3	659.6	659.0	659.6	660.3	661.0	661.7	661.7	660.9	660.1
165°	669.7	668.9	668.1	667.3	668.1	668.9	669.7	670.5	670.4	669.5	668.6
167.5°	676.0	675.1	674.2	673.2	674.2	675.1	676.0	676.9	676.9	676.0	675.1
170°	679.7	678.8	677.9	676.9	677.9	678.8	679.7	680.6	680.6	679.7	678.8
172.5°	682.0	681.0	679.9	678.9	679.9	681.0	682.0	683.0	683.0	682.1	681.2
175°	684.7	683.9	683.0	682.0	683.0	683.9	684.7	685.6	685.7	684.9	684.1
177.5°	685.6	684.7	683.9	683.0	683.9	684.7	685.6	686.5	686.6	685.9	685.2
180°	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6



TEST NUMBER: P331964-940

CATALOG NUMBER: S123DIP-S775D585U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5
2.5°	923.9	923.9	931.0	935.5	941.1	944.9	947.4	950.1	954.6	960.6	967.2
5°	871.1	873.0	883.2	893.5	903.3	911.7	918.7	927.1	937.4	950.0	964.0
7.5°	819.9	827.2	837.5	850.0	863.7	875.9	888.4	902.2	916.7	935.2	954.8
10°	787.1	795.0	807.6	823.5	837.9	852.4	867.8	882.8	901.0	922.9	948.2
12.5°	758.3	765.9	778.8	796.2	809.9	825.9	843.6	863.0	883.4	909.8	938.4
15°	718.5	727.3	743.2	751.6	772.6	791.8	808.1	836.1	862.2	889.3	922.5
17.5°	685.7	690.7	703.6	719.2	734.9	756.3	777.8	801.1	827.2	860.2	901.7
20°	663.3	667.5	681.5	697.9	714.7	734.3	753.5	776.8	806.2	841.2	886.0
22.5°	646.6	651.1	660.3	677.7	693.4	709.7	728.8	756.6	787.9	822.2	870.8
25°	622.2	625.1	631.2	645.2	659.2	677.3	694.2	720.3	752.5	792.6	841.2
27.5°	599.2	601.9	607.0	617.1	630.1	644.9	663.2	685.4	718.1	761.7	813.2
30°	585.4	585.9	590.6	599.9	611.1	623.2	640.0	665.2	696.1	740.4	794.5
32.5°	573.5	571.7	574.9	581.9	592.8	604.9	618.8	643.5	673.2	716.8	772.5
35°	553.2	552.2	550.9	557.0	566.2	575.6	587.7	606.5	640.0	680.6	739.0
37.5°	532.5	530.3	527.8	530.6	537.9	547.6	558.1	574.8	603.7	648.5	704.3
40°	517.3	515.4	514.0	513.0	519.6	528.9	536.8	552.7	579.8	622.2	677.3
42.5°	500.4	499.4	497.6	496.2	501.7	508.7	517.0	531.1	558.1	598.0	650.1
45°	473.3	472.4	471.5	470.6	473.9	480.4	486.9	497.1	520.5	559.3	606.5
47.5°	443.2	442.0	442.4	440.9	444.1	448.4	453.0	464.0	486.4	517.7	552.1
50°	421.5	421.1	421.1	421.1	422.0	427.1	431.3	439.8	460.3	491.6	516.3
52.5°	401.0	399.0	399.0	399.8	401.4	404.7	407.4	416.6	434.5	460.2	482.7
55°	368.8	365.1	364.1	365.1	366.5	369.3	372.0	379.5	394.9	414.1	427.1
57.5°	333.1	331.1	329.8	330.0	330.8	333.1	335.2	343.3	355.4	365.4	373.8
60°	308.1	309.1	304.9	305.8	305.8	307.6	310.9	316.0	326.3	333.3	341.7
62.5°	284.5	283.3	282.0	280.7	280.7	281.5	285.9	289.9	298.6	302.3	308.9
65°	247.9	247.9	245.0	246.0	246.5	243.3	245.6	250.2	255.8	257.3	263.3
67.5°	210.7	209.5	207.9	206.4	206.4	206.2	207.3	209.7	213.9	214.4	219.0
70°	185.3	184.4	184.0	182.5	180.7	183.0	181.6	184.0	186.3	186.7	189.5
72.5°	160.7	159.7	158.9	157.5	156.8	156.5	156.6	159.3	160.9	160.2	163.4
75°	125.6	124.7	123.7	121.4	121.4	119.9	120.5	122.3	124.2	122.8	125.6
77.5°	92.2	89.3	89.2	89.8	88.2	88.5	87.9	87.7	88.5	88.6	91.1
80°	71.0	67.7	68.7	68.1	67.7	67.2	66.3	66.8	67.2	67.7	69.1
82.5°	51.2	50.9	49.9	49.8	49.4	48.2	47.6	48.4	49.0	48.7	49.7
85°	26.1	24.7	25.7	25.2	25.7	25.2	23.8	23.8	24.7	24.3	25.2
87.5°	10.3	10.3	9.6	9.7	9.0	9.1	8.5	8.6	8.7	8.6	9.1
90°	12.7	12.2	10.7	9.3	7.8	6.3	5.0	3.9	2.8	1.6	0.5
92.5°	13.7	13.0	11.9	10.8	9.7	8.6	8.2	8.5	8.8	9.2	9.5
95°	16.6	15.8	14.5	13.3	12.0	10.8	12.5	17.1	21.8	26.4	31.0
97.5°	17.3	16.4	24.5	32.6	40.8	49.0	54.0	56.1	58.2	60.3	62.3
100°	17.7	16.8	34.4	52.1	69.6	87.3	95.0	92.7	90.5	88.2	86.0
102.5°	30.7	33.4	52.7	72.0	91.2	110.5	119.3	117.7	116.1	114.4	112.8
105°	91.4	111.4	121.5	131.7	141.9	152.0	156.5	155.2	154.1	152.8	151.6
107.5°	189.5	204.1	202.5	200.9	199.3	197.7	196.4	195.5	194.5	193.4	192.4
110°	225.6	229.3	228.1	226.9	225.6	224.4	223.3	222.4	221.5	220.6	219.7



TEST NUMBER: P331964-940

CATALOG NUMBER: S123DIP-S775D585U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	255.1	255.0	253.8	252.5	251.3	250.0	249.0	248.2	247.4	246.6	245.8
115°	293.1	291.9	290.9	289.9	288.9	287.8	287.0	286.3	285.6	285.0	284.3
117.5°	328.7	327.7	327.3	326.7	326.2	325.7	324.9	324.1	323.3	322.4	321.6
120°	351.9	350.9	350.6	350.3	349.9	349.6	348.9	347.9	346.9	345.8	344.8
122.5°	374.8	374.2	373.7	373.3	372.8	372.4	371.8	371.0	370.1	369.3	368.5
125°	407.1	406.9	406.4	406.0	405.6	405.1	404.4	403.5	402.6	401.7	400.7
127.5°	439.0	438.6	438.1	437.6	436.9	436.4	435.7	434.8	433.9	433.0	432.1
130°	458.2	457.7	457.3	456.8	456.4	455.9	455.2	454.3	453.4	452.5	451.7
132.5°	476.5	476.1	475.6	475.3	474.9	474.6	473.9	473.1	472.2	471.3	470.4
135°	504.4	504.0	503.5	503.1	502.7	502.2	501.7	501.0	500.2	499.6	498.9
137.5°	528.9	528.3	528.1	527.8	527.5	527.4	526.7	525.9	525.0	524.2	523.3
140°	544.7	544.2	543.9	543.5	543.1	542.9	542.3	541.6	541.0	540.3	539.6
142.5°	559.6	559.3	558.9	558.6	558.2	557.9	557.4	556.7	556.1	555.4	554.6
145°	580.5	580.3	580.1	579.9	579.6	579.4	578.9	578.1	577.3	576.5	575.7
147.5°	599.1	599.0	598.7	598.4	598.2	598.0	597.6	597.1	596.6	596.1	595.6
150°	610.6	610.3	610.1	609.8	609.7	609.4	609.1	608.8	608.4	608.1	607.8
152.5°	620.5	620.1	619.9	619.8	619.6	619.6	619.4	619.2	619.0	618.9	618.8
155°	634.3	633.7	633.6	633.5	633.4	633.3	633.3	633.6	633.7	634.0	634.2
157.5°	646.3	645.6	645.7	645.9	646.0	646.0	646.1	646.1	646.1	646.2	646.2
160°	653.2	652.6	652.6	652.7	652.8	653.0	653.1	653.2	653.4	653.4	653.5
162.5°	659.4	658.6	658.7	658.9	659.0	659.1	659.2	659.6	659.9	660.1	660.5
165°	667.7	666.7	666.9	667.0	667.1	667.2	667.4	667.8	668.2	668.4	668.8
167.5°	674.2	673.2	673.2	673.2	673.2	673.2	673.5	674.0	674.4	674.8	675.3
170°	677.9	676.9	676.9	676.9	676.9	676.9	677.2	677.6	678.1	678.5	678.9
172.5°	680.3	679.4	679.3	679.2	679.1	679.0	679.2	679.8	680.3	680.9	681.4
175°	683.3	682.5	682.4	682.3	682.2	682.1	682.3	682.9	683.4	684.0	684.6
177.5°	684.5	683.8	683.7	683.6	683.5	683.4	683.6	684.0	684.5	684.9	685.4
180°	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6



TEST NUMBER: P331964-940

CATALOG NUMBER: S123DIP-S775D585U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5
2.5°	969.5	971.3	977.8	982.2	987.4	990.4	993.4	995.7	998.6	999.3	1010.2
5°	973.8	983.1	999.5	1011.6	1026.5	1042.9	1054.1	1059.3	1072.7	1084.0	1106.3
7.5°	972.6	992.5	1017.1	1042.7	1070.1	1095.6	1117.6	1143.7	1162.3	1190.3	1217.7
10°	971.4	998.1	1029.8	1062.5	1100.8	1136.2	1168.0	1203.5	1232.9	1271.7	1304.8
12.5°	968.1	1000.3	1044.4	1083.1	1129.5	1178.5	1225.5	1271.0	1297.1	1361.6	1392.1
15°	959.8	998.1	1053.2	1112.0	1175.9	1233.9	1293.6	1341.2	1418.2	1474.7	1510.6
17.5°	944.0	997.6	1062.8	1133.8	1211.6	1287.9	1355.6	1427.8	1509.5	1577.9	1650.7
20°	936.5	995.2	1068.1	1146.6	1227.3	1313.7	1390.7	1477.5	1566.6	1633.9	1727.2
22.5°	922.7	989.3	1067.7	1155.1	1241.4	1330.8	1420.9	1508.5	1611.5	1704.1	1793.0
25°	900.0	974.7	1056.0	1153.5	1254.8	1344.4	1452.3	1568.5	1675.9	1794.9	1883.6
27.5°	876.3	956.1	1037.5	1128.2	1237.2	1343.5	1479.2	1610.5	1741.9	1844.6	1910.2
30°	858.0	935.5	1019.6	1111.1	1218.9	1345.4	1497.1	1640.4	1768.4	1856.5	1893.5
32.5°	838.2	916.9	991.1	1087.2	1202.1	1344.3	1508.3	1658.0	1769.9	1828.5	1821.4
35°	807.2	873.0	945.3	1037.8	1173.1	1336.1	1514.8	1659.6	1728.2	1715.6	1620.3
37.5°	762.3	817.7	888.9	990.2	1139.5	1318.8	1501.8	1610.3	1605.9	1503.2	1365.3
40°	734.3	781.5	850.1	956.5	1113.4	1307.6	1481.2	1551.8	1492.0	1348.6	1183.4
42.5°	697.8	741.1	809.8	919.2	1084.6	1284.8	1442.0	1462.5	1345.6	1180.6	1029.1
45°	641.0	679.2	750.2	863.2	1041.5	1235.2	1346.3	1296.4	1139.1	968.7	853.4
47.5°	580.0	619.7	688.0	804.1	979.1	1160.7	1213.5	1107.3	945.7	807.6	701.8
50°	541.5	579.8	646.6	763.8	936.9	1099.4	1121.3	984.1	835.6	714.3	627.4
52.5°	502.7	538.7	604.3	721.9	887.6	1028.4	1014.9	875.0	738.5	635.1	566.9
55°	444.9	478.9	541.5	651.7	802.5	914.0	865.0	731.6	618.6	538.2	486.4
57.5°	393.2	425.9	479.8	579.3	710.4	787.1	724.7	612.2	522.4	460.6	422.0
60°	358.0	387.0	438.4	530.7	644.7	703.0	641.4	542.0	466.4	416.9	382.4
62.5°	324.9	350.0	397.6	481.5	580.4	629.5	567.1	483.0	418.6	374.7	345.4
65°	274.5	297.4	339.4	404.7	486.0	518.6	464.9	396.8	346.9	314.1	294.5
67.5°	228.5	248.0	284.3	335.7	395.5	419.3	378.4	325.7	288.0	261.8	246.2
70°	198.0	214.7	243.3	287.6	341.7	359.9	321.6	278.2	250.7	229.7	215.2
72.5°	172.2	184.5	210.4	244.6	289.8	304.3	277.6	239.4	213.7	198.0	186.5
75°	131.2	141.4	158.3	185.8	217.0	225.5	205.4	181.6	164.3	153.1	144.3
77.5°	94.6	102.1	114.3	131.3	152.9	160.5	147.8	131.9	119.3	111.7	106.8
80°	71.4	77.5	87.7	101.7	114.9	119.0	111.6	99.4	90.6	86.4	82.1
82.5°	52.8	56.2	62.3	71.9	80.9	85.8	79.5	72.1	67.4	63.6	62.0
85°	26.6	28.4	31.3	35.0	40.6	42.4	40.1	38.3	35.5	33.2	33.2
87.5°	10.1	10.3	11.6	12.6	14.4	15.8	15.7	15.2	15.2	14.9	14.5
90°	1.6	2.8	3.9	5.0	6.3	7.8	9.3	10.7	12.2	12.7	13.1
92.5°	9.2	8.8	8.5	8.2	8.6	9.7	10.8	11.9	13.0	13.7	14.4
95°	26.4	21.8	17.1	12.5	10.8	12.0	13.3	14.5	15.8	16.6	17.4
97.5°	60.3	58.2	56.1	54.0	49.0	40.8	32.6	24.5	16.4	17.3	18.2
100°	88.2	90.5	92.7	95.0	87.3	69.6	52.1	34.4	16.8	17.7	18.5
102.5°	114.4	116.1	117.7	119.3	110.5	91.2	72.0	52.7	33.4	30.7	27.8
105°	152.8	154.1	155.2	156.5	152.0	141.9	131.7	121.5	111.4	91.4	71.3
107.5°	193.4	194.5	195.5	196.4	197.7	199.3	200.9	202.5	204.1	189.5	174.8
110°	220.6	221.5	222.4	223.3	224.4	225.6	226.9	228.1	229.3	225.6	221.9



TEST NUMBER: P331964-940

CATALOG NUMBER: S123DIP-S775D585U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	246.6	247.4	248.2	249.0	250.0	251.3	252.5	253.8	255.0	255.1	255.1
115°	285.0	285.6	286.3	287.0	287.8	288.9	289.9	290.9	291.9	293.1	294.2
117.5°	322.4	323.3	324.1	324.9	325.7	326.2	326.7	327.3	327.7	328.7	329.6
120°	345.8	346.9	347.9	348.9	349.6	349.9	350.3	350.6	350.9	351.9	352.8
122.5°	369.3	370.1	371.0	371.8	372.4	372.8	373.3	373.7	374.2	374.8	375.4
125°	401.7	402.6	403.5	404.4	405.1	405.6	406.0	406.4	406.9	407.1	407.3
127.5°	433.0	433.9	434.8	435.7	436.4	436.9	437.6	438.1	438.6	439.0	439.3
130°	452.5	453.4	454.3	455.2	455.9	456.4	456.8	457.3	457.7	458.2	458.6
132.5°	471.3	472.2	473.1	473.9	474.6	474.9	475.3	475.6	476.1	476.5	477.0
135°	499.6	500.2	501.0	501.7	502.2	502.7	503.1	503.5	504.0	504.4	504.7
137.5°	524.2	525.0	525.9	526.7	527.4	527.5	527.8	528.1	528.3	528.9	529.4
140°	540.3	541.0	541.6	542.3	542.9	543.1	543.5	543.9	544.2	544.7	545.1
142.5°	555.4	556.1	556.7	557.4	557.9	558.2	558.6	558.9	559.3	559.6	560.0
145°	576.5	577.3	578.1	578.9	579.4	579.6	579.9	580.1	580.3	580.5	580.8
147.5°	596.1	596.6	597.1	597.6	598.0	598.2	598.4	598.7	599.0	599.1	599.4
150°	608.1	608.4	608.8	609.1	609.4	609.7	609.8	610.1	610.3	610.6	610.7
152.5°	618.9	619.0	619.2	619.4	619.6	619.6	619.8	619.9	620.1	620.5	620.9
155°	634.0	633.7	633.6	633.3	633.3	633.4	633.5	633.6	633.7	634.3	634.8
157.5°	646.2	646.1	646.1	646.1	646.0	646.0	645.9	645.7	645.6	646.3	646.9
160°	653.4	653.4	653.2	653.1	653.0	652.8	652.7	652.6	652.6	653.2	653.9
162.5°	660.1	659.9	659.6	659.2	659.1	659.0	658.9	658.7	658.6	659.4	660.1
165°	668.4	668.2	667.8	667.4	667.2	667.1	667.0	666.9	666.7	667.7	668.6
167.5°	674.8	674.4	674.0	673.5	673.2	673.2	673.2	673.2	673.2	674.2	675.1
170°	678.5	678.1	677.6	677.2	676.9	676.9	676.9	676.9	676.9	677.9	678.8
172.5°	680.9	680.3	679.8	679.2	679.0	679.1	679.2	679.3	679.4	680.3	681.2
175°	684.0	683.4	682.9	682.3	682.1	682.2	682.3	682.4	682.5	683.3	684.1
177.5°	684.9	684.5	684.0	683.6	683.4	683.5	683.6	683.7	683.8	684.5	685.2
180°	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6



TEST NUMBER: P331964-940

CATALOG NUMBER: S123DIP-S775D585U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	963.5	963.5	963.5	963.5	963.5	963.5	963.5
2.5°	1014.0	1014.3	1018.4	1021.5	1019.9	1021.8	1022.5
5°	1107.8	1124.6	1133.5	1140.0	1140.5	1140.9	1144.7
7.5°	1240.8	1258.8	1272.0	1292.0	1298.0	1304.8	1302.8
10°	1337.9	1364.5	1387.4	1399.5	1412.6	1431.7	1416.4
12.5°	1428.7	1475.9	1510.6	1529.6	1541.9	1545.7	1538.1
15°	1578.3	1639.9	1673.1	1672.1	1714.2	1732.4	1703.9
17.5°	1715.6	1772.5	1818.0	1841.4	1876.3	1884.1	1880.5
20°	1799.7	1861.7	1897.2	1937.3	1955.5	1971.8	1974.7
22.5°	1872.1	1927.8	1965.9	1999.3	2014.6	2022.3	2026.9
25°	1946.7	1990.6	2013.4	2025.1	2029.3	2028.4	2022.3
27.5°	1941.5	1944.9	1919.7	1895.0	1872.9	1847.9	1839.3
30°	1891.1	1851.9	1781.9	1742.2	1683.8	1637.6	1656.3
32.5°	1758.5	1680.5	1601.9	1515.1	1443.3	1422.9	1402.3
35°	1500.8	1363.6	1283.4	1189.9	1152.6	1115.3	1089.6
37.5°	1214.2	1108.0	1012.8	951.7	914.4	890.7	878.0
40°	1049.9	954.2	875.7	826.3	797.8	771.2	767.5
42.5°	918.8	829.8	770.8	731.4	704.1	692.8	684.6
45°	752.5	690.5	650.8	622.8	604.6	597.5	588.2
47.5°	636.9	593.1	563.3	544.2	530.5	525.3	524.5
50°	572.3	535.9	514.0	499.0	488.3	486.4	478.9
52.5°	523.8	492.2	475.1	462.1	454.3	449.1	446.8
55°	454.7	433.6	418.3	410.8	404.7	399.6	399.6
57.5°	397.8	380.3	370.1	363.7	361.9	358.2	355.9
60°	362.7	347.8	339.8	334.2	330.6	331.0	326.8
62.5°	328.3	318.7	311.1	305.5	301.0	301.1	301.4
65°	279.6	272.2	266.5	264.7	261.9	258.6	259.6
67.5°	236.9	230.0	225.6	222.4	221.5	219.7	222.4
70°	206.3	201.2	198.0	195.1	194.2	194.7	197.0
72.5°	178.3	174.7	172.5	171.2	169.2	169.2	170.9
75°	140.1	137.2	135.4	133.9	133.5	133.5	133.5
77.5°	102.9	102.3	101.4	99.3	99.4	100.0	100.0
80°	81.2	79.8	79.4	78.5	77.0	76.1	78.5
82.5°	60.7	59.3	58.9	58.7	56.4	56.3	58.2
85°	32.6	31.3	31.7	31.3	31.3	30.9	30.9
87.5°	14.3	14.0	13.7	14.1	13.8	13.5	14.3
90°	13.6	14.0	14.4	14.6	14.8	15.1	15.2
92.5°	15.2	15.9	16.3	16.5	16.6	16.8	16.9
95°	18.1	18.9	19.4	19.4	19.4	19.4	19.4
97.5°	19.1	20.0	20.5	20.6	20.7	20.9	21.0
100°	19.5	20.4	20.9	21.0	21.1	21.2	21.4
102.5°	25.1	22.3	21.0	21.1	21.4	21.6	21.8
105°	51.4	31.4	21.5	21.7	21.9	22.1	22.4
107.5°	160.2	145.4	130.6	115.5	100.4	85.3	70.3
110°	218.2	214.5	204.5	188.3	172.2	156.0	139.8



TEST NUMBER: P331964-940

CATALOG NUMBER: S123DIP-S775D585U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	255.2	255.3	253.6	250.2	246.7	243.3	240.0
115°	295.3	296.5	297.2	297.7	298.2	298.6	299.1
117.5°	330.5	331.4	331.9	332.0	332.1	332.2	332.3
120°	353.7	354.5	355.0	355.0	355.0	355.0	355.0
122.5°	376.0	376.7	377.0	377.1	377.2	377.3	377.4
125°	407.5	407.8	408.0	408.2	408.5	408.7	408.9
127.5°	439.7	440.1	440.1	439.9	439.7	439.4	439.3
130°	459.1	459.5	459.7	459.4	459.2	459.0	458.8
132.5°	477.4	477.9	478.0	477.6	477.2	477.0	476.6
135°	505.1	505.3	505.3	505.1	504.7	504.4	504.0
137.5°	529.9	530.5	530.7	530.4	530.2	529.9	529.8
140°	545.5	546.0	546.1	545.9	545.6	545.5	545.2
142.5°	560.4	560.7	560.7	560.4	560.1	559.7	559.5
145°	580.9	581.2	581.3	581.3	581.3	581.3	581.3
147.5°	599.6	599.9	599.7	599.1	598.6	598.2	597.6
150°	611.0	611.2	611.2	610.8	610.5	610.1	609.8
152.5°	621.3	621.7	621.6	621.2	620.6	620.1	619.6
155°	635.4	636.0	635.9	635.3	634.5	633.9	633.2
157.5°	647.6	648.4	648.2	647.3	646.5	645.6	644.7
160°	654.5	655.2	655.1	654.4	653.6	652.8	652.0
162.5°	660.9	661.7	661.7	661.0	660.3	659.6	659.0
165°	669.5	670.4	670.5	669.7	668.9	668.1	667.3
167.5°	676.0	676.9	676.9	676.0	675.1	674.2	673.2
170°	679.7	680.6	680.6	679.7	678.8	677.9	676.9
172.5°	682.1	683.0	683.0	682.0	681.0	679.9	678.9
175°	684.9	685.7	685.6	684.7	683.9	683.0	682.0
177.5°	685.9	686.6	686.5	685.6	684.7	683.9	683.0
180°	684.6	684.6	684.6	684.6	684.6	684.6	684.6

(END OF REPORT)