

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332704-830

Luminaire Tested: **S124DIP-S1195D1035U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332704-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIP-S1195D1035U830-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1035 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 8198.6 lumens  
Efficiency: N/A  
Efficacy: 122.7 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 66.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332704-830

CATALOG NUMBER: S124DIP-S1195D1035U830-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332704-830

CATALOG NUMBER: S124DIP-S1195D1035U830-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59
1	100	95	91	88	93	89	86	82	77	75	72	67	65	63	57	55	54	49
2	91	83	77	72	84	78	72	68	68	64	60	58	55	53	50	48	46	41
3	83	73	66	60	77	69	62	57	60	55	50	52	48	45	44	41	39	35
4	76	65	57	51	70	61	54	48	53	48	43	46	42	38	40	36	33	30
5	70	58	50	43	65	54	47	41	48	42	37	41	37	33	36	32	29	26
6	64	52	44	38	60	49	41	36	43	37	32	37	33	29	32	29	26	23
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	30	26	23	20
8	55	43	35	29	51	40	33	28	36	30	26	31	26	23	27	23	20	18
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	19	16
10	48	36	28	24	45	34	27	23	30	25	21	27	22	19	23	20	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	15163	15163	15163
5°	15209	15027	15135
10°	15114	14905	14978
15°	14931	14692	14730
20°	14689	14430	14442
25°	14412	14130	14091
30°	14072	13778	13651
35°	13720	13409	13232
40°	13354	12991	12752
45°	12973	12578	12337
50°	12552	12210	11833
55°	12096	11736	11354
60°	11641	11202	10863
65°	11127	10695	10264
70°	10551	10017	9626
75°	9669	9201	8968
80°	8605	8257	8047
85°	7521	7243	7104



TEST NUMBER: P332704-830

CATALOG NUMBER: S124DIP-S1195D1035U830-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	176.9	2.2
10°-20°	498.4	6.1
20°-30°	733.6	8.9
30°-40°	852.8	10.4
40°-50°	852.8	10.4
50°-60°	746.0	9.1
60°-70°	554.0	6.8
70°-80°	314.7	3.8
80°-90°	94.5	1.2
90°-100°	80.2	1.0
100°-110°	237.7	2.9
110°-120°	403.4	4.9
120°-130°	531.9	6.5
130°-140°	597.4	7.3
140°-150°	587.0	7.2
150°-160°	493.7	6.0
160°-170°	328.5	4.0
170°-180°	115.0	1.4
0°-30°	1408.8	17.2
0°-40°	2261.6	27.6
0°-60°	3860.5	47.1
0°-90°	4823.7	58.8
90°-120°	721.3	8.8
90°-150°	2437.7	29.7
90°-180°	3375.0	41.2
0°-180°	8198.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1878	1878	1878	1878	1878	
5°	1877	1870	1854	1870	1868	178
15°	1786	1780	1758	1766	1762	503
25°	1618	1607	1586	1587	1582	744
35°	1392	1381	1361	1350	1343	870
45°	1136	1125	1102	1086	1081	876
55°	859	854	834	816	807	769
65°	582	575	560	545	537	577
75°	310	302	295	289	288	329
85°	81	81	78	78	77	89
90°	3	13	21	26	28	8
95°	56	65	72	74	74	63
105°	219	220	224	227	230	233
115°	410	410	408	407	406	404
125°	597	597	596	595	593	532
135°	770	776	776	774	772	596
145°	936	940	941	940	937	586
155°	1072	1072	1072	1075	1072	493
165°	1168	1165	1163	1168	1165	329
175°	1215	1210	1209	1215	1209	115
180°	1216	1216	1216	1216	1216	



TEST NUMBER: P332704-830

CATALOG NUMBER: S124DIP-S1195D1035U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3
2.5°	1883.1	1882.4	1881.5	1880.7	1879.9	1878.0	1875.1	1872.2	1869.3	1866.3	1869.0
5°	1876.8	1875.5	1874.2	1872.8	1871.5	1869.0	1865.3	1861.6	1857.9	1854.3	1857.9
7.5°	1859.4	1858.0	1856.7	1855.3	1854.0	1851.3	1847.2	1843.1	1839.1	1834.9	1838.0
10°	1843.7	1842.4	1841.1	1839.7	1838.3	1835.5	1831.2	1826.8	1822.5	1818.2	1820.8
12.5°	1823.3	1821.9	1820.5	1819.2	1817.9	1814.9	1810.3	1805.7	1801.1	1796.5	1799.4
15°	1786.5	1785.2	1783.9	1782.5	1781.1	1778.0	1772.9	1767.9	1762.9	1757.9	1759.9
17.5°	1742.3	1740.6	1738.9	1737.3	1735.6	1732.4	1727.6	1722.9	1718.2	1713.4	1714.7
20°	1709.8	1708.1	1706.4	1704.8	1703.1	1699.7	1694.7	1689.7	1684.7	1679.6	1680.6
22.5°	1674.8	1672.6	1670.5	1668.2	1666.0	1662.4	1657.4	1652.4	1647.4	1642.3	1644.2
25°	1618.0	1615.6	1613.3	1610.9	1608.5	1605.1	1600.3	1595.7	1591.0	1586.3	1586.7
27.5°	1552.9	1550.5	1548.1	1545.7	1543.3	1539.9	1535.6	1531.3	1526.9	1522.5	1521.7
30°	1509.6	1506.9	1504.2	1501.6	1498.9	1495.3	1491.0	1486.7	1482.3	1478.0	1476.7
32.5°	1463.9	1461.4	1459.1	1456.6	1454.2	1450.7	1446.0	1441.4	1436.8	1432.2	1430.6
35°	1392.2	1389.9	1387.5	1385.2	1382.8	1379.3	1374.6	1370.0	1365.3	1360.6	1358.2
37.5°	1316.6	1314.5	1312.4	1310.2	1308.1	1304.5	1299.5	1294.5	1289.4	1284.4	1281.9
40°	1267.2	1264.6	1261.9	1259.2	1256.6	1252.7	1247.7	1242.6	1237.7	1232.7	1229.3
42.5°	1214.3	1212.7	1211.1	1209.5	1207.9	1204.3	1198.7	1193.2	1187.6	1182.0	1178.2
45°	1136.3	1134.0	1131.6	1129.3	1127.0	1123.1	1117.8	1112.4	1107.0	1101.7	1098.1
47.5°	1054.7	1053.1	1051.5	1049.9	1048.3	1045.1	1040.1	1035.2	1030.2	1025.3	1021.2
50°	999.4	998.1	996.6	995.3	994.0	991.0	986.3	981.7	976.9	972.2	967.6
52.5°	945.2	943.6	942.0	940.4	938.8	935.5	930.6	925.6	920.7	915.7	911.5
55°	859.4	858.4	857.4	856.4	855.4	852.5	847.8	843.2	838.5	833.8	829.8
57.5°	777.5	776.4	775.2	774.1	773.0	770.1	765.4	760.8	756.2	751.6	747.8
60°	721.0	719.3	717.6	716.0	714.3	711.2	706.9	702.6	698.1	693.8	690.8
62.5°	665.5	664.1	662.7	661.3	660.0	657.0	652.3	647.7	643.1	638.5	635.7
65°	582.5	580.8	579.1	577.4	575.8	573.3	570.0	566.6	563.3	559.9	556.6
67.5°	498.8	497.3	495.7	494.2	492.7	490.2	487.0	483.8	480.6	477.4	474.2
70°	447.0	444.7	442.3	440.0	437.6	435.2	432.4	429.8	427.1	424.4	421.8
72.5°	391.6	389.3	386.9	384.6	382.3	380.0	377.9	375.7	373.6	371.5	369.3
75°	310.0	308.4	306.7	305.0	303.3	301.7	300.0	298.3	296.7	295.0	293.7
77.5°	232.1	231.3	230.6	229.9	229.1	228.0	226.6	225.1	223.7	222.2	221.8
80°	185.1	184.1	183.1	182.1	181.2	180.3	179.6	178.9	178.2	177.6	176.9
82.5°	139.4	138.9	138.5	138.0	137.5	137.2	137.0	137.0	136.8	136.7	136.3
85°	81.2	81.2	81.2	81.2	81.2	81.0	80.3	79.6	78.9	78.2	78.2
87.5°	31.9	32.0	32.2	32.4	32.6	32.8	32.8	32.9	33.0	33.1	33.3
90°	2.8	5.1	7.4	9.7	12.1	14.0	15.6	17.3	19.0	20.7	22.0
92.5°	20.2	22.8	25.4	28.0	30.6	32.6	33.7	34.9	36.1	37.2	38.0
95°	56.5	58.3	60.2	62.1	64.0	65.6	67.1	68.6	70.0	71.5	72.1
97.5°	98.6	100.1	101.6	103.1	104.6	106.2	107.9	109.6	111.4	113.1	113.9
100°	131.7	132.5	133.4	134.2	135.1	136.4	138.3	140.2	142.0	143.9	144.4
102.5°	166.4	166.6	167.0	167.3	167.7	168.7	170.4	172.1	173.8	175.6	176.2
105°	219.2	219.4	219.6	219.8	220.1	220.6	221.4	222.3	223.1	223.9	224.5
107.5°	274.8	274.9	275.2	275.5	275.7	275.9	276.1	276.2	276.3	276.4	277.0
110°	312.4	312.7	313.2	313.6	314.1	314.1	313.9	313.7	313.5	313.3	312.8



TEST NUMBER: P332704-830

CATALOG NUMBER: S124DIP-S1195D1035U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	351.5	351.6	351.7	351.8	351.9	351.7	351.3	350.9	350.5	350.2	350.1
115°	410.2	410.2	410.2	410.2	410.2	410.0	409.5	409.2	408.7	408.3	408.1
117.5°	465.5	465.7	465.8	466.0	466.2	466.1	465.8	465.5	465.2	465.0	464.2
120°	502.4	503.2	504.1	504.9	505.8	505.9	505.2	504.5	504.0	503.3	502.3
122.5°	540.7	541.1	541.4	541.8	542.1	542.2	541.9	541.5	541.2	540.9	540.3
125°	597.4	597.4	597.4	597.4	597.4	597.3	597.1	596.9	596.6	596.4	596.1
127.5°	648.8	649.4	650.0	650.6	651.3	651.4	651.1	650.7	650.4	650.1	649.7
130°	684.9	685.5	686.2	686.7	687.4	687.7	687.7	687.7	687.7	687.7	687.3
132.5°	721.8	722.3	722.6	723.1	723.6	723.8	723.6	723.4	723.2	723.1	722.6
135°	770.5	771.8	773.0	774.3	775.5	776.2	776.2	776.2	776.2	776.2	775.7
137.5°	823.6	824.2	824.7	825.3	826.0	826.3	826.7	827.1	827.4	827.7	827.2
140°	858.9	859.3	859.8	860.2	860.6	860.8	860.8	860.8	860.8	860.8	860.6
142.5°	891.3	891.7	892.1	892.6	893.0	893.1	893.0	892.8	892.6	892.4	892.4
145°	936.0	936.9	937.7	938.6	939.4	939.9	940.2	940.4	940.6	940.8	940.6
147.5°	980.5	981.5	982.5	983.5	984.5	985.0	984.8	984.6	984.4	984.3	984.1
150°	1007.6	1008.4	1009.3	1010.1	1011.0	1011.3	1011.3	1011.3	1011.3	1011.3	1011.3
152.5°	1033.2	1033.7	1034.2	1034.7	1035.2	1035.5	1035.7	1035.9	1036.0	1036.1	1036.7
155°	1072.5	1072.5	1072.5	1072.5	1072.5	1072.4	1072.1	1072.0	1071.8	1071.6	1072.4
157.5°	1105.6	1105.2	1104.8	1104.5	1104.1	1103.9	1103.8	1103.8	1103.8	1103.7	1104.4
160°	1125.2	1124.9	1124.7	1124.5	1124.4	1124.2	1123.9	1123.7	1123.5	1123.3	1123.9
162.5°	1143.2	1142.7	1142.2	1141.6	1141.0	1140.7	1140.5	1140.3	1140.1	1139.8	1140.9
165°	1167.5	1166.9	1166.3	1165.6	1165.0	1164.5	1164.0	1163.7	1163.2	1162.8	1164.0
167.5°	1186.2	1185.2	1184.4	1183.6	1182.6	1182.2	1182.2	1182.3	1182.3	1182.4	1183.6
170°	1196.7	1195.6	1194.6	1193.5	1192.5	1192.0	1192.3	1192.5	1192.7	1192.9	1194.2
172.5°	1204.2	1203.3	1202.5	1201.6	1200.7	1200.2	1200.3	1200.3	1200.4	1200.4	1201.8
175°	1214.6	1213.5	1212.5	1211.4	1210.4	1209.8	1209.6	1209.3	1209.1	1208.9	1210.4
177.5°	1218.0	1217.1	1216.3	1215.4	1214.6	1214.2	1214.2	1214.2	1214.2	1214.2	1215.3
180°	1216.4	1216.4	1216.4	1216.4	1216.4	1216.4	1216.4	1216.4	1216.4	1216.4	1216.4



TEST NUMBER: P332704-830

CATALOG NUMBER: S124DIP-S1195D1035U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3
2.5°	1871.6	1874.3	1877.0	1878.2	1877.9	1877.6	1877.4	1877.1
5°	1861.6	1865.3	1869.0	1870.5	1869.8	1869.2	1868.5	1867.7
7.5°	1840.9	1843.8	1846.7	1848.0	1847.7	1847.2	1846.8	1846.4
10°	1823.4	1826.2	1828.8	1829.9	1829.2	1828.5	1827.8	1827.1
12.5°	1802.3	1805.3	1808.3	1809.2	1808.3	1807.3	1806.4	1805.4
15°	1761.9	1764.0	1765.9	1766.4	1765.5	1764.4	1763.4	1762.5
17.5°	1715.9	1717.2	1718.4	1718.7	1718.1	1717.4	1716.7	1716.1
20°	1681.7	1682.6	1683.7	1683.9	1683.2	1682.5	1681.9	1681.1
22.5°	1646.0	1647.8	1649.5	1649.8	1648.7	1647.5	1646.2	1645.0
25°	1587.1	1587.3	1587.7	1587.1	1585.8	1584.5	1583.2	1581.9
27.5°	1520.9	1520.1	1519.3	1518.1	1516.4	1514.8	1513.1	1511.4
30°	1475.3	1473.9	1472.6	1471.1	1469.4	1467.8	1466.1	1464.4
32.5°	1429.0	1427.4	1425.8	1424.2	1422.5	1420.8	1419.2	1417.5
35°	1355.9	1353.6	1351.2	1349.2	1347.6	1345.9	1344.2	1342.6
37.5°	1279.3	1276.8	1274.2	1271.9	1269.7	1267.4	1265.3	1263.0
40°	1226.0	1222.6	1219.3	1216.7	1215.1	1213.4	1211.7	1210.0
42.5°	1174.3	1170.4	1166.6	1164.0	1162.9	1161.8	1160.6	1159.5
45°	1094.4	1090.7	1087.0	1084.7	1083.6	1082.6	1081.7	1080.6
47.5°	1017.0	1012.9	1008.7	1005.3	1002.8	1000.2	997.7	995.1
50°	962.9	958.2	953.6	950.2	948.2	946.2	944.1	942.2
52.5°	907.4	903.2	899.1	895.8	893.2	890.7	888.2	885.6
55°	825.8	821.8	817.7	814.7	812.8	810.8	808.7	806.7
57.5°	744.0	740.2	736.4	733.5	731.6	729.6	727.6	725.8
60°	687.8	684.9	681.8	679.5	677.8	676.1	674.5	672.8
62.5°	632.9	630.2	627.5	625.3	623.6	621.9	620.3	618.6
65°	553.2	549.9	546.5	544.0	542.3	540.6	538.9	537.3
67.5°	471.0	467.8	464.6	462.7	462.2	461.8	461.3	460.8
70°	419.1	416.4	413.7	411.9	410.9	409.9	408.9	407.8
72.5°	367.2	365.0	362.9	361.3	360.3	359.3	358.3	357.3
75°	292.3	291.0	289.6	288.8	288.5	288.1	287.8	287.5
77.5°	221.3	220.9	220.6	219.9	219.0	218.2	217.3	216.4
80°	176.3	175.6	174.9	174.5	174.1	173.7	173.4	173.1
82.5°	135.8	135.4	135.1	134.7	134.3	134.0	133.7	133.4
85°	78.2	78.2	78.2	78.1	77.8	77.4	77.1	76.7
87.5°	33.6	33.7	34.0	34.2	34.3	34.4	34.5	34.5
90°	23.2	24.5	25.7	26.6	27.0	27.4	27.8	28.2
92.5°	38.7	39.5	40.2	40.8	41.0	41.3	41.6	41.8
95°	72.8	73.4	74.0	74.4	74.4	74.4	74.4	74.4
97.5°	114.6	115.4	116.1	116.5	116.5	116.5	116.5	116.5
100°	144.8	145.2	145.6	145.8	145.8	145.8	145.8	145.8
102.5°	176.7	177.3	177.9	178.2	178.4	178.6	178.8	178.9
105°	225.2	225.8	226.4	227.1	227.6	228.3	228.9	229.5
107.5°	277.6	278.1	278.7	279.0	279.0	278.9	278.9	278.8
110°	312.5	312.0	311.6	311.7	312.4	312.9	313.6	314.2





TEST NUMBER: P332704-830

CATALOG NUMBER: S124DIP-S1195D1035U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	350.0	349.9	349.9	349.9	350.0	350.1	350.2	350.3
115°	407.8	407.6	407.5	407.3	407.1	406.8	406.6	406.4
117.5°	463.5	462.8	462.1	461.6	461.1	460.7	460.2	459.9
120°	501.2	500.2	499.2	498.8	499.3	499.6	500.1	500.5
122.5°	539.5	538.9	538.1	537.3	536.6	535.8	535.1	534.3
125°	595.6	595.2	594.7	594.4	594.0	593.5	593.1	592.7
127.5°	649.2	648.8	648.4	648.0	647.7	647.3	647.1	646.7
130°	686.9	686.5	686.1	685.4	684.6	683.7	682.9	682.0
132.5°	722.3	721.8	721.4	721.0	720.7	720.4	720.0	719.7
135°	775.3	774.9	774.5	773.9	773.4	772.7	772.0	771.5
137.5°	826.6	826.0	825.6	825.3	825.5	825.6	825.7	825.9
140°	860.4	860.2	860.0	859.8	859.6	859.3	859.1	858.9
142.5°	892.3	892.3	892.3	892.2	892.2	892.1	892.1	892.0
145°	940.4	940.2	939.9	939.5	938.9	938.3	937.6	937.0
147.5°	983.9	983.7	983.5	983.4	983.2	983.0	982.8	982.6
150°	1011.3	1011.3	1011.3	1011.3	1011.1	1010.8	1010.6	1010.4
152.5°	1037.2	1037.6	1038.2	1038.2	1037.6	1037.1	1036.5	1035.9
155°	1073.3	1074.0	1074.9	1074.9	1074.0	1073.3	1072.4	1071.6
157.5°	1104.9	1105.6	1106.3	1106.2	1105.5	1104.8	1104.1	1103.3
160°	1124.5	1125.2	1125.8	1125.6	1124.5	1123.5	1122.5	1121.4
162.5°	1142.1	1143.2	1144.3	1144.4	1143.4	1142.4	1141.3	1140.2
165°	1165.4	1166.6	1167.8	1168.0	1167.2	1166.4	1165.5	1164.7
167.5°	1184.9	1186.2	1187.4	1187.4	1186.1	1184.8	1183.5	1182.2
170°	1195.4	1196.7	1198.0	1197.8	1196.4	1194.9	1193.4	1191.9
172.5°	1203.2	1204.7	1206.2	1206.1	1204.7	1203.2	1201.7	1200.2
175°	1211.8	1213.3	1214.7	1214.7	1213.3	1211.8	1210.4	1208.9
177.5°	1216.5	1217.7	1218.9	1218.8	1217.5	1216.1	1214.7	1213.4
180°	1216.4	1216.4	1216.4	1216.4	1216.4	1216.4	1216.4	1216.4

(END OF REPORT)