

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332348-940

Luminaire Tested: **S123RDIP-S1000D1025U940-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332348-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S1000D1025U940-4F0-1E-UDD-A  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1025 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7186.3 lumens  
Efficiency: N/A  
Efficacy: 118.8 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 60.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332348-940

CATALOG NUMBER: S123RDIP-S1000D1025U940-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P332348-940

CATALOG NUMBER: S123RDIP-S1000D1025U940-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	107	107	107	107	99	99	99	99	83	83	83		69	69	69		55	55	55	49
1	98	94	90	87	90	87	84	81	73	71	69		61	60	58		50	49	48	43
2	90	83	77	72	83	77	72	67	65	61	58		54	52	50		45	43	41	37
3	82	73	66	61	76	68	62	57	58	53	50		49	45	43		40	38	36	32
4	76	65	58	52	70	61	54	49	52	47	43		44	40	37		36	33	31	28
5	70	58	51	45	64	54	47	42	47	41	37		39	35	32		33	30	28	24
6	64	53	45	39	59	49	42	37	42	37	33		36	32	29		30	27	24	22
7	59	48	40	34	55	44	38	33	38	33	29		33	29	25		27	24	22	19
8	55	43	36	31	51	40	34	29	35	30	26		30	26	23		25	22	20	17
9	52	40	32	27	48	37	30	26	32	27	23		28	24	21		23	20	18	16
10	48	36	29	25	45	34	28	23	30	25	21		26	22	19		22	19	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	15259	15259	15259	15259
5°	18189	15324	13493	15324
10°	22710	15235	12191	15235
15°	26658	15081	11117	15081
20°	29751	14848	10204	14848
25°	29276	14602	9644	14602
30°	21044	14375	9066	14375
35°	14051	14082	8692	14082
40°	10352	13728	8304	13728
45°	8683	13108	7926	13108
50°	7661	12295	7398	12295
55°	6718	11365	6673	11365
60°	5983	10478	6114	10478
65°	5254	9521	5687	9521
70°	4126	8670	5196	8670
75°	3635	7573	4741	7573
80°	3161	6434	4668	6434
85°	2544	5175	4940	5175



TEST NUMBER: P332348-940

CATALOG NUMBER: S123RDIP-S1000D1025U940-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	139.4	1.9
10°-20°	435.5	6.1
20°-30°	684.2	9.5
30°-40°	713.8	9.9
40°-50°	610.9	8.5
50°-60°	465.6	6.5
60°-70°	298.4	4.2
70°-80°	143.6	2.0
80°-90°	41.3	0.6
90°-100°	43.6	0.6
100°-110°	207.6	2.9
110°-120°	498.6	6.9
120°-130°	634.9	8.8
130°-140°	678.4	9.4
140°-150°	634.4	8.8
150°-160°	511.7	7.1
160°-170°	330.3	4.6
170°-180°	113.8	1.6
0°-30°	1259.1	17.5
0°-40°	1973.0	27.5
0°-60°	3049.5	42.4
0°-90°	3532.9	49.2
90°-120°	749.8	10.4
90°-150°	2697.6	37.5
90°-180°	3653.0	50.8
0°-180°	7186.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1418	1418	1418	1418	1418	
5°	1683	1418	1249	1418	1683	174
15°	2392	1353	998	1353	2392	678
25°	2465	1230	812	1230	2465	1059
35°	1069	1072	662	1072	1069	701
45°	570	861	521	861	570	449
55°	358	606	356	606	358	324
65°	206	374	223	374	206	203
75°	87	182	114	182	87	94
85°	21	42	40	42	21	24
90°	27	1	27	1	27	13
95°	34	54	34	54	34	28
105°	39	265	39	265	39	89
115°	523	498	523	498	523	484
125°	716	701	716	701	716	639
135°	882	873	882	873	882	680
145°	1017	1008	1017	1008	1017	635
155°	1108	1110	1108	1110	1108	511
165°	1168	1170	1168	1170	1168	330
175°	1194	1198	1194	1198	1194	114
180°	1198	1198	1198	1198	1198	



TEST NUMBER: P332348-940

CATALOG NUMBER: S123RDIP-S1000D1025U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1509.8	1511.7	1505.5	1504.5	1497.2	1495.2	1495.2	1485.1	1478.7	1470.5	1465.6
5°	1683.4	1693.1	1688.2	1677.3	1659.1	1654.8	1643.3	1625.1	1604.5	1579.0	1566.8
7.5°	1900.1	1913.3	1908.3	1891.4	1872.3	1856.9	1824.4	1794.2	1751.9	1714.7	1682.9
10°	2077.8	2063.9	2052.9	2036.6	2018.9	1990.4	1956.4	1909.7	1855.7	1813.2	1765.9
12.5°	2210.8	2208.5	2194.7	2177.8	2152.9	2125.8	2084.1	2027.2	1964.4	1903.1	1848.9
15°	2392.2	2395.8	2386.7	2369.1	2333.9	2286.0	2222.9	2199.2	2109.3	2042.6	1975.9
17.5°	2517.7	2516.9	2515.7	2491.4	2455.4	2421.3	2362.8	2300.5	2219.2	2125.1	2035.2
20°	2597.3	2591.2	2592.4	2565.1	2538.4	2498.9	2442.0	2351.5	2284.7	2176.1	2083.3
22.5°	2595.3	2594.1	2598.7	2589.3	2570.0	2539.8	2494.8	2418.5	2333.3	2223.7	2119.2
25°	2465.0	2460.1	2488.7	2496.5	2527.5	2532.9	2519.6	2477.7	2397.0	2284.1	2154.9
27.5°	2063.0	2060.3	2113.3	2179.5	2263.5	2328.8	2391.9	2422.4	2397.0	2316.2	2186.7
30°	1693.1	1750.2	1776.8	1872.7	1979.5	2106.9	2218.6	2324.8	2350.9	2315.7	2209.5
32.5°	1405.7	1455.5	1477.7	1560.0	1659.6	1808.8	1976.4	2126.7	2232.9	2259.9	2195.9
35°	1069.3	1069.9	1120.8	1157.3	1249.5	1403.0	1565.7	1767.1	1967.4	2119.1	2134.8
37.5°	853.2	856.2	887.1	923.4	992.6	1073.7	1216.9	1384.5	1615.8	1848.7	1985.2
40°	736.7	742.2	765.3	801.0	850.8	912.0	1023.8	1181.5	1374.5	1633.6	1845.4
42.5°	661.9	670.8	682.7	710.2	741.1	798.4	888.8	1010.7	1186.2	1431.2	1675.5
45°	570.4	575.2	584.4	597.1	625.0	665.1	725.8	807.7	953.3	1150.6	1395.1
47.5°	503.2	500.6	510.2	520.6	539.1	566.4	607.1	674.0	777.8	936.1	1143.5
50°	457.5	456.9	463.6	471.5	489.1	509.2	542.5	592.9	675.4	806.5	996.4
52.5°	414.8	417.1	421.9	431.7	444.4	460.6	490.5	526.8	597.7	710.9	869.2
55°	358.0	359.9	366.5	372.0	381.1	397.4	416.3	446.7	495.2	574.1	704.5
57.5°	310.0	309.2	315.6	316.9	327.2	340.5	355.1	378.7	413.8	472.5	560.4
60°	277.9	276.1	281.6	285.8	291.3	302.2	314.3	337.4	365.3	408.4	483.7
62.5°	248.8	248.0	252.0	256.2	260.7	270.6	280.9	298.5	320.7	357.0	416.7
65°	206.3	208.1	210.0	211.8	214.2	220.3	230.0	242.1	257.3	282.8	325.8
67.5°	162.1	164.0	164.6	168.4	173.5	177.4	183.2	194.0	204.6	226.1	250.7
70°	131.1	130.5	131.1	132.9	139.6	146.2	154.2	162.0	168.7	183.9	204.5
72.5°	112.6	111.6	113.2	113.5	116.7	118.6	123.6	131.0	139.6	149.9	164.7
75°	87.4	87.4	87.4	87.4	89.8	91.0	92.8	94.7	97.7	102.5	113.5
77.5°	64.6	64.6	65.5	66.2	66.6	67.3	68.5	70.3	71.3	73.9	78.6
80°	51.0	51.5	51.0	51.5	51.5	52.8	53.4	55.2	55.8	58.9	60.7
82.5°	38.3	38.0	38.3	39.0	39.0	40.2	40.3	41.6	41.7	43.3	45.1
85°	20.6	19.4	20.6	20.1	21.2	20.1	20.6	21.8	21.8	22.5	24.9
87.5°	10.2	11.1	10.1	10.4	10.3	10.7	10.6	10.4	11.2	10.6	10.5
90°	26.7	26.3	25.9	25.5	25.1	24.5	23.7	22.9	22.1	21.4	18.8
92.5°	29.5	29.3	29.1	28.8	28.6	27.8	26.6	25.3	24.1	22.8	20.9
95°	33.8	33.8	33.8	33.8	33.8	33.2	31.7	30.3	29.0	27.6	25.4
97.5°	36.6	36.5	36.3	36.1	35.8	35.0	33.4	31.8	30.2	28.6	42.9
100°	37.4	37.2	37.0	36.8	36.6	35.7	34.2	32.5	30.9	29.3	60.2
102.5°	38.1	37.7	37.4	37.0	36.6	39.0	43.9	48.8	53.7	58.6	92.3
105°	39.1	38.8	38.3	38.0	37.5	54.9	89.9	124.9	159.9	194.9	212.8
107.5°	123.0	149.4	175.8	202.2	228.5	254.6	280.3	305.9	331.6	357.3	354.5
110°	244.8	273.0	301.3	329.6	357.9	375.3	381.8	388.3	394.8	401.4	399.2



TEST NUMBER: P332348-940

CATALOG NUMBER: S123RDIP-S1000D1025U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	419.9	425.9	431.9	437.8	443.8	446.7	446.7	446.5	446.4	446.3	444.1
115°	523.3	522.5	521.7	520.9	520.2	518.8	516.8	514.9	512.9	510.9	509.1
117.5°	581.4	581.2	581.0	580.9	580.8	579.9	578.3	576.8	575.2	573.5	572.7
120°	621.3	621.3	621.3	621.3	621.3	620.5	618.8	617.3	615.7	614.1	613.6
122.5°	660.4	660.2	660.1	660.0	659.8	659.2	658.1	656.9	655.9	654.7	654.0
125°	715.6	715.2	714.8	714.4	714.0	713.6	713.2	712.8	712.5	712.0	711.2
127.5°	768.7	769.0	769.5	769.8	770.3	770.1	769.5	768.8	768.2	767.6	766.6
130°	802.8	803.3	803.6	804.1	804.4	804.2	803.4	802.6	801.8	801.0	800.2
132.5°	834.2	834.7	835.3	835.8	836.3	836.2	835.4	834.6	833.9	833.1	832.5
135°	882.1	882.6	883.2	883.9	884.4	884.4	883.9	883.2	882.6	882.1	881.3
137.5°	927.1	927.5	927.9	928.3	928.6	928.4	927.5	926.5	925.5	924.6	924.2
140°	954.1	954.6	954.9	955.3	955.7	955.6	954.8	954.0	953.1	952.3	951.8
142.5°	979.1	979.6	980.2	980.7	981.2	981.2	980.6	980.0	979.4	978.7	978.1
145°	1017.4	1017.4	1017.4	1017.4	1017.4	1017.2	1016.7	1016.4	1015.9	1015.6	1015.1
147.5°	1045.8	1046.7	1047.7	1048.6	1049.5	1049.7	1049.3	1048.9	1048.6	1048.1	1047.8
150°	1067.2	1067.7	1068.4	1069.0	1069.5	1069.7	1069.3	1068.9	1068.4	1068.1	1067.6
152.5°	1084.2	1085.2	1086.1	1087.0	1087.9	1088.0	1087.3	1086.5	1085.8	1085.1	1084.9
155°	1108.1	1109.3	1110.5	1111.7	1112.9	1112.9	1112.0	1111.0	1110.0	1109.0	1108.8
157.5°	1128.3	1129.8	1131.3	1132.8	1134.4	1134.6	1133.4	1132.2	1131.0	1129.8	1130.1
160°	1141.0	1142.5	1143.8	1145.2	1146.6	1146.7	1145.5	1144.3	1143.2	1141.9	1142.1
162.5°	1153.2	1154.4	1155.6	1156.8	1158.1	1158.0	1156.6	1155.3	1154.0	1152.6	1152.8
165°	1167.8	1169.1	1170.5	1171.9	1173.3	1173.2	1171.6	1170.0	1168.4	1166.9	1167.1
167.5°	1178.2	1179.8	1181.4	1183.0	1184.5	1184.5	1183.0	1181.4	1179.8	1178.2	1178.2
170°	1184.6	1186.2	1187.8	1189.5	1191.0	1191.0	1189.5	1187.8	1186.2	1184.6	1184.6
172.5°	1188.2	1190.0	1191.7	1193.5	1195.2	1195.2	1193.6	1192.1	1190.5	1188.9	1188.7
175°	1193.6	1195.2	1196.8	1198.3	1199.9	1200.0	1198.6	1197.2	1195.9	1194.4	1194.3
177.5°	1195.2	1196.8	1198.4	1199.9	1201.5	1201.7	1200.4	1199.1	1197.8	1196.6	1196.4
180°	1198.0	1198.0	1198.0	1198.0	1198.0	1198.0	1198.0	1198.0	1198.0	1198.0	1198.0



TEST NUMBER: P332348-940

CATALOG NUMBER: S123RDIP-S1000D1025U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1463.7	1462.2	1455.5	1447.7	1437.4	1430.7	1425.3	1422.5	1413.7	1403.0	1395.7
5°	1554.1	1535.9	1516.5	1492.8	1471.0	1448.5	1434.6	1418.2	1398.1	1375.7	1359.9
7.5°	1651.0	1615.2	1576.8	1537.1	1497.9	1462.8	1431.6	1405.1	1373.1	1341.0	1318.4
10°	1725.3	1673.0	1619.1	1563.8	1513.4	1466.2	1429.7	1393.9	1355.7	1318.7	1290.8
12.5°	1792.7	1724.0	1661.8	1593.9	1529.5	1472.9	1420.5	1378.4	1332.4	1292.9	1261.1
15°	1878.1	1807.8	1732.5	1629.3	1543.8	1472.2	1408.5	1353.3	1297.4	1248.8	1217.9
17.5°	1958.0	1852.1	1751.0	1664.9	1553.7	1464.3	1386.5	1320.4	1259.2	1207.7	1169.7
20°	1991.0	1888.5	1778.6	1668.8	1559.6	1459.5	1369.0	1296.2	1232.5	1174.2	1139.1
22.5°	2010.9	1894.8	1779.1	1661.1	1545.0	1441.0	1351.6	1271.5	1202.4	1147.0	1103.6
25°	2034.1	1895.8	1768.4	1651.8	1533.5	1420.6	1314.4	1229.5	1154.9	1095.9	1049.8
27.5°	2049.4	1886.7	1736.1	1606.5	1486.5	1374.1	1276.8	1186.7	1111.0	1048.7	999.3
30°	2052.4	1879.4	1711.3	1571.1	1449.1	1345.9	1242.8	1156.6	1076.6	1010.4	964.3
32.5°	2056.2	1861.4	1677.8	1528.8	1404.0	1301.8	1208.4	1126.1	1044.0	978.8	931.7
35°	2040.2	1851.5	1626.9	1455.8	1330.8	1231.9	1147.5	1071.7	991.0	927.8	879.9
37.5°	1971.2	1812.0	1574.2	1373.5	1242.8	1151.2	1082.4	1016.4	942.3	874.2	829.0
40°	1901.8	1773.2	1533.5	1323.5	1187.0	1092.9	1031.0	977.0	905.4	841.7	793.2
42.5°	1798.4	1720.3	1494.7	1271.0	1123.8	1033.2	981.0	930.4	867.5	802.8	757.2
45°	1608.7	1619.1	1415.1	1187.6	1036.4	945.5	896.3	861.1	805.3	751.9	705.2
47.5°	1370.8	1467.3	1321.8	1098.6	944.3	858.9	815.9	785.2	747.6	695.2	652.6
50°	1215.5	1353.3	1247.1	1038.9	886.6	801.6	759.1	734.2	701.5	660.2	619.6
52.5°	1072.3	1220.2	1156.7	972.4	823.9	746.3	704.8	684.3	658.3	619.5	582.6
55°	874.4	1024.3	1009.8	872.0	730.0	660.2	628.7	605.6	588.0	558.9	529.8
57.5°	707.3	849.4	856.9	760.4	647.3	578.3	551.2	533.8	522.3	500.2	473.3
60°	602.0	732.5	758.0	685.1	588.0	527.4	500.6	486.7	477.6	459.9	439.3
62.5°	514.6	625.6	654.5	602.1	531.2	474.4	453.5	440.1	433.9	418.7	400.6
65°	393.9	486.1	514.0	484.8	447.8	402.3	385.3	373.8	368.4	359.9	346.5
67.5°	296.1	363.4	394.0	373.4	360.1	331.4	320.6	314.3	309.5	303.6	292.5
70°	237.9	287.7	319.2	313.7	302.8	287.7	279.7	275.5	270.6	265.8	256.1
72.5°	191.3	225.5	255.1	257.9	249.0	245.9	239.0	237.2	234.3	228.5	223.1
75°	126.8	150.5	171.1	179.1	182.6	185.7	182.6	182.1	181.5	176.6	173.5
77.5°	83.1	95.9	108.9	122.3	128.0	132.2	133.1	135.4	133.8	131.2	129.7
80°	63.8	66.8	75.9	87.4	96.5	100.1	102.5	103.8	103.2	102.5	100.1
82.5°	46.3	48.8	53.1	61.2	68.8	74.9	76.3	76.1	77.4	77.8	75.9
85°	24.9	25.5	26.7	27.9	32.2	38.9	40.7	41.9	43.1	43.1	39.4
87.5°	11.0	10.0	10.4	10.0	11.1	11.1	13.6	15.7	16.6	15.1	15.4
90°	16.2	13.6	11.1	8.8	6.9	4.8	2.9	0.9	2.9	4.8	6.9
92.5°	18.9	16.9	15.1	14.4	14.9	15.4	16.0	16.6	16.0	15.4	14.9
95°	23.3	21.0	18.9	21.8	30.0	38.1	46.2	54.3	46.2	38.1	30.0
97.5°	57.2	71.4	85.6	94.5	98.2	101.8	105.5	109.1	105.5	101.8	98.2
100°	91.0	121.9	152.8	166.2	162.3	158.4	154.4	150.4	154.4	158.4	162.3
102.5°	126.0	159.7	193.4	208.8	206.0	203.1	200.3	197.4	200.3	203.1	206.0
105°	230.5	248.3	266.1	273.9	271.8	269.6	267.4	265.2	267.4	269.6	271.8
107.5°	351.7	348.8	346.1	343.8	342.1	340.3	338.6	336.8	338.6	340.3	342.1
110°	397.1	394.8	392.7	390.8	389.2	387.6	386.1	384.5	386.1	387.6	389.2





TEST NUMBER: P332348-940

CATALOG NUMBER: S123RDIP-S1000D1025U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	441.9	439.8	437.6	435.8	434.4	432.9	431.5	430.1	431.5	432.9	434.4
115°	507.3	505.5	503.8	502.3	501.1	499.9	498.7	497.6	498.7	499.9	501.1
117.5°	571.8	570.8	569.9	568.7	567.3	565.8	564.4	562.8	564.4	565.8	567.3
120°	613.0	612.3	611.8	610.6	608.8	607.0	605.2	603.4	605.2	607.0	608.8
122.5°	653.3	652.5	651.8	650.6	649.2	647.6	646.2	644.8	646.2	647.6	649.2
125°	710.4	709.7	708.9	707.7	706.1	704.5	702.9	701.3	702.9	704.5	706.1
127.5°	765.7	764.7	763.8	762.5	760.9	759.4	757.8	756.2	757.8	759.4	760.9
130°	799.5	798.7	797.9	796.7	795.1	793.5	791.9	790.4	791.9	793.5	795.1
132.5°	831.8	831.2	830.5	829.5	827.9	826.3	824.7	823.1	824.7	826.3	827.9
135°	880.5	879.7	878.9	877.9	876.7	875.5	874.3	873.2	874.3	875.5	876.7
137.5°	923.7	923.3	922.8	921.9	920.4	918.9	917.4	915.9	917.4	918.9	920.4
140°	951.2	950.6	950.0	949.1	947.9	946.7	945.6	944.3	945.6	946.7	947.9
142.5°	977.5	977.0	976.3	975.4	974.3	973.0	971.9	970.7	971.9	973.0	974.3
145°	1014.8	1014.4	1014.0	1013.1	1011.7	1010.3	1009.0	1007.5	1009.0	1010.3	1011.7
147.5°	1047.3	1047.0	1046.5	1045.9	1045.0	1044.1	1043.2	1042.2	1043.2	1044.1	1045.0
150°	1067.3	1066.8	1066.5	1066.0	1065.4	1064.8	1064.3	1063.6	1064.3	1064.8	1065.4
152.5°	1084.7	1084.4	1084.2	1084.0	1083.7	1083.4	1083.2	1082.8	1083.2	1083.4	1083.7
155°	1108.6	1108.4	1108.2	1108.3	1108.8	1109.1	1109.5	1109.9	1109.5	1109.1	1108.8
157.5°	1130.2	1130.4	1130.6	1130.8	1130.8	1130.9	1130.9	1130.9	1130.9	1130.9	1130.8
160°	1142.4	1142.5	1142.7	1142.9	1143.2	1143.4	1143.5	1143.7	1143.5	1143.4	1143.2
162.5°	1153.0	1153.2	1153.4	1153.8	1154.3	1154.8	1155.3	1155.8	1155.3	1154.8	1154.3
165°	1167.2	1167.4	1167.7	1168.1	1168.7	1169.2	1169.8	1170.5	1169.8	1169.2	1168.7
167.5°	1178.2	1178.2	1178.2	1178.7	1179.5	1180.3	1181.1	1181.8	1181.1	1180.3	1179.5
170°	1184.6	1184.6	1184.6	1185.1	1185.9	1186.7	1187.4	1188.2	1187.4	1186.7	1185.9
172.5°	1188.7	1188.5	1188.3	1188.7	1189.6	1190.6	1191.6	1192.5	1191.6	1190.6	1189.6
175°	1194.1	1193.8	1193.6	1194.1	1195.1	1196.1	1197.0	1198.0	1197.0	1196.1	1195.1
177.5°	1196.3	1196.1	1196.0	1196.3	1197.0	1197.8	1198.6	1199.4	1198.6	1197.8	1197.0
180°	1198.0	1198.0	1198.0	1198.0	1198.0	1198.0	1198.0	1198.0	1198.0	1198.0	1198.0



TEST NUMBER: P332348-940

CATALOG NUMBER: S123RDIP-S1000D1025U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1393.3	1387.0	1382.6	1372.9	1366.6	1359.8	1353.0	1357.4	1356.9	1356.4	1356.4
5°	1346.6	1332.6	1319.9	1303.5	1293.2	1280.4	1270.7	1269.5	1271.9	1263.5	1258.6
7.5°	1300.2	1281.1	1263.1	1245.0	1225.8	1210.5	1201.0	1196.4	1190.3	1185.0	1179.6
10°	1267.7	1245.3	1227.6	1205.1	1184.5	1166.4	1154.9	1146.9	1142.6	1138.4	1130.5
12.5°	1234.2	1212.2	1189.8	1164.4	1144.8	1123.6	1115.0	1106.2	1098.1	1093.2	1082.4
15°	1185.2	1156.6	1133.0	1106.3	1084.4	1063.8	1051.7	1034.0	1031.6	1025.6	1014.7
17.5°	1136.0	1105.0	1072.4	1052.7	1028.0	1006.5	988.0	982.1	964.7	958.2	948.7
20°	1097.2	1068.6	1043.7	1017.7	981.9	961.8	947.3	939.4	925.4	916.9	910.9
22.5°	1063.6	1034.7	1005.9	975.4	945.9	923.5	912.8	900.5	892.9	881.0	874.4
25°	1015.8	984.3	949.7	916.9	895.7	878.7	861.7	850.8	839.9	834.4	822.2
27.5°	960.3	927.3	894.9	870.0	844.0	827.2	811.8	802.1	789.0	779.8	773.1
30°	929.7	890.8	862.9	840.4	807.1	791.3	779.8	767.7	758.0	748.2	741.5
32.5°	894.2	858.8	832.3	804.6	778.9	761.7	746.8	736.1	727.8	718.6	711.9
35°	838.7	809.0	781.6	753.7	734.9	717.3	699.7	690.5	682.7	674.2	668.2
37.5°	788.4	760.6	734.7	708.2	684.8	670.6	656.4	649.4	638.7	633.0	626.9
40°	757.3	730.0	702.1	676.6	652.4	641.4	628.7	618.4	608.7	604.4	597.7
42.5°	723.4	696.1	672.5	645.1	625.2	610.4	598.6	587.3	580.1	573.8	570.1
45°	673.0	648.7	625.6	598.3	579.5	566.8	553.4	543.1	536.5	532.2	525.5
47.5°	624.1	599.8	576.4	552.6	534.4	519.8	506.5	499.3	490.4	485.3	480.7
50°	588.6	566.8	541.9	520.0	501.9	487.3	476.4	467.3	459.4	452.7	449.7
52.5°	556.1	532.8	511.3	491.0	471.7	455.2	445.3	435.7	429.8	422.1	418.6
55°	502.5	480.0	461.8	441.8	422.9	409.0	396.9	388.3	382.3	373.8	369.0
57.5°	452.1	431.9	410.2	392.9	373.4	361.7	351.6	340.1	332.7	326.0	321.3
60°	418.1	395.0	376.2	359.9	342.9	327.7	318.6	309.5	301.6	294.9	290.7
62.5°	382.6	362.6	344.6	326.8	311.3	298.1	287.5	279.9	273.0	268.7	264.5
65°	328.3	312.5	294.4	279.7	265.2	255.5	247.0	240.3	235.4	232.4	228.8
67.5°	278.3	263.0	247.1	232.8	223.1	215.7	210.1	204.4	202.0	198.0	195.6
70°	245.8	230.0	216.1	205.1	195.4	189.9	186.3	182.1	179.6	174.8	172.4
72.5°	210.4	198.9	188.9	179.9	172.1	167.1	162.5	157.3	153.4	148.0	145.6
75°	165.7	155.3	147.5	141.4	136.5	129.8	123.1	117.7	115.9	114.0	113.5
77.5°	122.7	116.2	110.5	105.3	99.2	94.4	93.0	91.8	91.4	90.4	90.4
80°	96.5	90.4	86.1	80.1	76.4	76.4	76.4	75.3	75.9	75.9	75.9
82.5°	71.7	66.2	63.8	61.6	60.9	61.4	61.4	61.6	61.3	62.2	61.8
85°	37.0	37.6	38.9	38.3	38.9	38.9	40.0	39.4	40.0	38.9	40.0
87.5°	15.3	17.3	18.3	19.3	20.2	20.3	21.0	21.1	21.8	21.9	22.0
90°	8.8	11.1	13.6	16.2	18.8	21.4	22.1	22.9	23.7	24.5	25.1
92.5°	14.4	15.1	16.9	18.9	20.9	22.8	24.1	25.3	26.6	27.8	28.6
95°	21.8	18.9	21.0	23.3	25.4	27.6	29.0	30.3	31.7	33.2	33.8
97.5°	94.5	85.6	71.4	57.2	42.9	28.6	30.2	31.8	33.4	35.0	35.8
100°	166.2	152.8	121.9	91.0	60.2	29.3	30.9	32.5	34.2	35.7	36.6
102.5°	208.8	193.4	159.7	126.0	92.3	58.6	53.7	48.8	43.9	39.0	36.6
105°	273.9	266.1	248.3	230.5	212.8	194.9	159.9	124.9	89.9	54.9	37.5
107.5°	343.8	346.1	348.8	351.7	354.5	357.3	331.6	305.9	280.3	254.6	228.5
110°	390.8	392.7	394.8	397.1	399.2	401.4	394.8	388.3	381.8	375.3	357.9



TEST NUMBER: P332348-940

CATALOG NUMBER: S123RDIP-S1000D1025U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	435.8	437.6	439.8	441.9	444.1	446.3	446.4	446.5	446.7	446.7	443.8
115°	502.3	503.8	505.5	507.3	509.1	510.9	512.9	514.9	516.8	518.8	520.2
117.5°	568.7	569.9	570.8	571.8	572.7	573.5	575.2	576.8	578.3	579.9	580.8
120°	610.6	611.8	612.3	613.0	613.6	614.1	615.7	617.3	618.8	620.5	621.3
122.5°	650.6	651.8	652.5	653.3	654.0	654.7	655.9	656.9	658.1	659.2	659.8
125°	707.7	708.9	709.7	710.4	711.2	712.0	712.5	712.8	713.2	713.6	714.0
127.5°	762.5	763.8	764.7	765.7	766.6	767.6	768.2	768.8	769.5	770.1	770.3
130°	796.7	797.9	798.7	799.5	800.2	801.0	801.8	802.6	803.4	804.2	804.4
132.5°	829.5	830.5	831.2	831.8	832.5	833.1	833.9	834.6	835.4	836.2	836.3
135°	877.9	878.9	879.7	880.5	881.3	882.1	882.6	883.2	883.9	884.4	884.4
137.5°	921.9	922.8	923.3	923.7	924.2	924.6	925.5	926.5	927.5	928.4	928.6
140°	949.1	950.0	950.6	951.2	951.8	952.3	953.1	954.0	954.8	955.6	955.7
142.5°	975.4	976.3	977.0	977.5	978.1	978.7	979.4	980.0	980.6	981.2	981.2
145°	1013.1	1014.0	1014.4	1014.8	1015.1	1015.6	1015.9	1016.4	1016.7	1017.2	1017.4
147.5°	1045.9	1046.5	1047.0	1047.3	1047.8	1048.1	1048.6	1048.9	1049.3	1049.7	1049.5
150°	1066.0	1066.5	1066.8	1067.3	1067.6	1068.1	1068.4	1068.9	1069.3	1069.7	1069.5
152.5°	1084.0	1084.2	1084.4	1084.7	1084.9	1085.1	1085.8	1086.5	1087.3	1088.0	1087.9
155°	1108.3	1108.2	1108.4	1108.6	1108.8	1109.0	1110.0	1111.0	1112.0	1112.9	1112.9
157.5°	1130.8	1130.6	1130.4	1130.2	1130.1	1129.8	1131.0	1132.2	1133.4	1134.6	1134.4
160°	1142.9	1142.7	1142.5	1142.4	1142.1	1141.9	1143.2	1144.3	1145.5	1146.7	1146.6
162.5°	1153.8	1153.4	1153.2	1153.0	1152.8	1152.6	1154.0	1155.3	1156.6	1158.0	1158.1
165°	1168.1	1167.7	1167.4	1167.2	1167.1	1166.9	1168.4	1170.0	1171.6	1173.2	1173.3
167.5°	1178.7	1178.2	1178.2	1178.2	1178.2	1178.2	1179.8	1181.4	1183.0	1184.5	1184.5
170°	1185.1	1184.6	1184.6	1184.6	1184.6	1184.6	1186.2	1187.8	1189.5	1191.0	1191.0
172.5°	1188.7	1188.3	1188.5	1188.7	1188.7	1188.9	1190.5	1192.1	1193.6	1195.2	1195.2
175°	1194.1	1193.6	1193.8	1194.1	1194.3	1194.4	1195.9	1197.2	1198.6	1200.0	1199.9
177.5°	1196.3	1196.0	1196.1	1196.3	1196.4	1196.6	1197.8	1199.1	1200.4	1201.7	1201.5
180°	1198.0	1198.0	1198.0	1198.0	1198.0	1198.0	1198.0	1198.0	1198.0	1198.0	1198.0



TEST NUMBER: P332348-940

CATALOG NUMBER: S123RDIP-S1000D1025U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1350.6	1350.1	1350.6	1348.6	1350.6	1350.1	1350.6	1356.4	1356.4	1356.9	1357.4
5°	1256.8	1256.2	1254.4	1248.8	1254.4	1256.2	1256.8	1258.6	1263.5	1271.9	1269.5
7.5°	1174.8	1174.0	1168.7	1168.8	1168.7	1174.0	1174.8	1179.6	1185.0	1190.3	1196.4
10°	1126.3	1126.9	1119.6	1115.4	1119.6	1126.9	1126.3	1130.5	1138.4	1142.6	1146.9
12.5°	1079.2	1076.4	1070.6	1065.9	1070.6	1076.4	1079.2	1082.4	1093.2	1098.1	1106.2
15°	1017.1	1011.0	996.4	997.6	996.4	1011.0	1017.1	1014.7	1025.6	1031.6	1034.0
17.5°	943.9	939.4	939.1	930.7	939.1	939.4	943.9	948.7	958.2	964.7	982.1
20°	901.2	898.1	899.3	890.8	899.3	898.1	901.2	910.9	916.9	925.4	939.4
22.5°	867.6	864.6	859.5	856.8	859.5	864.6	867.6	874.4	881.0	892.9	900.5
25°	818.6	813.8	809.0	812.0	809.0	813.8	818.6	822.2	834.4	839.9	850.8
27.5°	769.6	766.0	761.1	760.5	761.1	766.0	769.6	773.1	779.8	789.0	802.1
30°	738.5	734.9	732.5	729.4	732.5	734.9	738.5	741.5	748.2	758.0	767.7
32.5°	706.9	706.2	701.9	701.2	701.9	706.2	706.9	711.9	718.6	727.8	736.1
35°	665.7	662.1	660.8	661.5	660.8	662.1	665.7	668.2	674.2	682.7	690.5
37.5°	626.5	621.6	619.5	617.2	619.5	621.6	626.5	626.9	633.0	638.7	649.4
40°	598.3	593.5	592.3	591.0	592.3	593.5	598.3	597.7	604.4	608.7	618.4
42.5°	566.8	564.8	564.1	562.0	564.1	564.8	566.8	570.1	573.8	580.1	587.3
45°	523.7	523.1	519.4	520.7	519.4	523.1	523.7	525.5	532.2	536.5	543.1
47.5°	478.3	475.6	473.1	474.7	473.1	475.6	478.3	480.7	485.3	490.4	499.3
50°	447.3	446.0	440.6	441.8	440.6	446.0	447.3	449.7	452.7	459.4	467.3
52.5°	416.2	411.5	409.5	408.8	409.5	411.5	416.2	418.6	422.1	429.8	435.7
55°	364.7	359.3	356.9	355.6	356.9	359.3	364.7	369.0	373.8	382.3	388.3
57.5°	314.2	312.7	310.9	312.2	310.9	312.7	314.2	321.3	326.0	332.7	340.1
60°	284.6	284.6	284.6	284.0	284.6	284.6	284.6	290.7	294.9	301.6	309.5
62.5°	261.8	260.3	259.8	260.7	259.8	260.3	261.8	264.5	268.7	273.0	279.9
65°	226.9	226.3	223.9	223.3	223.9	226.3	226.9	228.8	232.4	235.4	240.3
67.5°	194.0	191.9	191.2	190.3	191.2	191.9	194.0	195.6	198.0	202.0	204.4
70°	169.3	168.1	164.4	165.1	164.4	168.1	169.3	172.4	174.8	179.6	182.1
72.5°	142.6	141.4	140.6	139.8	140.6	141.4	142.6	145.6	148.0	153.4	157.3
75°	112.9	112.3	111.6	114.0	111.6	112.3	112.9	113.5	114.0	115.9	117.7
77.5°	90.4	90.4	90.8	89.8	90.8	90.4	90.4	90.4	90.4	91.4	91.8
80°	75.9	75.9	75.3	75.3	75.3	75.9	75.9	75.9	75.9	75.9	75.3
82.5°	60.8	61.3	61.6	60.7	61.6	61.3	60.8	61.8	62.2	61.3	61.6
85°	40.0	39.4	40.7	40.0	40.7	39.4	40.0	40.0	38.9	40.0	39.4
87.5°	23.1	22.2	22.3	22.8	22.3	22.2	23.1	22.0	21.9	21.8	21.1
90°	25.5	25.9	26.3	26.7	26.3	25.9	25.5	25.1	24.5	23.7	22.9
92.5°	28.8	29.1	29.3	29.5	29.3	29.1	28.8	28.6	27.8	26.6	25.3
95°	33.8	33.8	33.8	33.8	33.8	33.8	33.8	33.8	33.2	31.7	30.3
97.5°	36.1	36.3	36.5	36.6	36.5	36.3	36.1	35.8	35.0	33.4	31.8
100°	36.8	37.0	37.2	37.4	37.2	37.0	36.8	36.6	35.7	34.2	32.5
102.5°	37.0	37.4	37.7	38.1	37.7	37.4	37.0	36.6	39.0	43.9	48.8
105°	38.0	38.3	38.8	39.1	38.8	38.3	38.0	37.5	54.9	89.9	124.9
107.5°	202.2	175.8	149.4	123.0	149.4	175.8	202.2	228.5	254.6	280.3	305.9
110°	329.6	301.3	273.0	244.8	273.0	301.3	329.6	357.9	375.3	381.8	388.3



TEST NUMBER: P332348-940

CATALOG NUMBER: S123RDIP-S1000D1025U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	437.8	431.9	425.9	419.9	425.9	431.9	437.8	443.8	446.7	446.7	446.5
115°	520.9	521.7	522.5	523.3	522.5	521.7	520.9	520.2	518.8	516.8	514.9
117.5°	580.9	581.0	581.2	581.4	581.2	581.0	580.9	580.8	579.9	578.3	576.8
120°	621.3	621.3	621.3	621.3	621.3	621.3	621.3	621.3	620.5	618.8	617.3
122.5°	660.0	660.1	660.2	660.4	660.2	660.1	660.0	659.8	659.2	658.1	656.9
125°	714.4	714.8	715.2	715.6	715.2	714.8	714.4	714.0	713.6	713.2	712.8
127.5°	769.8	769.5	769.0	768.7	769.0	769.5	769.8	770.3	770.1	769.5	768.8
130°	804.1	803.6	803.3	802.8	803.3	803.6	804.1	804.4	804.2	803.4	802.6
132.5°	835.8	835.3	834.7	834.2	834.7	835.3	835.8	836.3	836.2	835.4	834.6
135°	883.9	883.2	882.6	882.1	882.6	883.2	883.9	884.4	884.4	883.9	883.2
137.5°	928.3	927.9	927.5	927.1	927.5	927.9	928.3	928.6	928.4	927.5	926.5
140°	955.3	954.9	954.6	954.1	954.6	954.9	955.3	955.7	955.6	954.8	954.0
142.5°	980.7	980.2	979.6	979.1	979.6	980.2	980.7	981.2	981.2	980.6	980.0
145°	1017.4	1017.4	1017.4	1017.4	1017.4	1017.4	1017.4	1017.4	1017.2	1016.7	1016.4
147.5°	1048.6	1047.7	1046.7	1045.8	1046.7	1047.7	1048.6	1049.5	1049.7	1049.3	1048.9
150°	1069.0	1068.4	1067.7	1067.2	1067.7	1068.4	1069.0	1069.5	1069.7	1069.3	1068.9
152.5°	1087.0	1086.1	1085.2	1084.2	1085.2	1086.1	1087.0	1087.9	1088.0	1087.3	1086.5
155°	1111.7	1110.5	1109.3	1108.1	1109.3	1110.5	1111.7	1112.9	1112.9	1112.0	1111.0
157.5°	1132.8	1131.3	1129.8	1128.3	1129.8	1131.3	1132.8	1134.4	1134.6	1133.4	1132.2
160°	1145.2	1143.8	1142.5	1141.0	1142.5	1143.8	1145.2	1146.6	1146.7	1145.5	1144.3
162.5°	1156.8	1155.6	1154.4	1153.2	1154.4	1155.6	1156.8	1158.1	1158.0	1156.6	1155.3
165°	1171.9	1170.5	1169.1	1167.8	1169.1	1170.5	1171.9	1173.3	1173.2	1171.6	1170.0
167.5°	1183.0	1181.4	1179.8	1178.2	1179.8	1181.4	1183.0	1184.5	1184.5	1183.0	1181.4
170°	1189.5	1187.8	1186.2	1184.6	1186.2	1187.8	1189.5	1191.0	1191.0	1189.5	1187.8
172.5°	1193.5	1191.7	1190.0	1188.2	1190.0	1191.7	1193.5	1195.2	1195.2	1193.6	1192.1
175°	1198.3	1196.8	1195.2	1193.6	1195.2	1196.8	1198.3	1199.9	1200.0	1198.6	1197.2
177.5°	1199.9	1198.4	1196.8	1195.2	1196.8	1198.4	1199.9	1201.5	1201.7	1200.4	1199.1
180°	1198.0	1198.0	1198.0	1198.0	1198.0	1198.0	1198.0	1198.0	1198.0	1198.0	1198.0



TEST NUMBER: P332348-940

CATALOG NUMBER: S123RDIP-S1000D1025U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1353.0	1359.8	1366.6	1372.9	1382.6	1387.0	1393.3	1395.7	1403.0	1413.7	1422.5
5°	1270.7	1280.4	1293.2	1303.5	1319.9	1332.6	1346.6	1359.9	1375.7	1398.1	1418.2
7.5°	1201.0	1210.5	1225.8	1245.0	1263.1	1281.1	1300.2	1318.4	1341.0	1373.1	1405.1
10°	1154.9	1166.4	1184.5	1205.1	1227.6	1245.3	1267.7	1290.8	1318.7	1355.7	1393.9
12.5°	1115.0	1123.6	1144.8	1164.4	1189.8	1212.2	1234.2	1261.1	1292.9	1332.4	1378.4
15°	1051.7	1063.8	1084.4	1106.3	1133.0	1156.6	1185.2	1217.9	1248.8	1297.4	1353.3
17.5°	988.0	1006.5	1028.0	1052.7	1072.4	1105.0	1136.0	1169.7	1207.7	1259.2	1320.4
20°	947.3	961.8	981.9	1017.7	1043.7	1068.6	1097.2	1139.1	1174.2	1232.5	1296.2
22.5°	912.8	923.5	945.9	975.4	1005.9	1034.7	1063.6	1103.6	1147.0	1202.4	1271.5
25°	861.7	878.7	895.7	916.9	949.7	984.3	1015.8	1049.8	1095.9	1154.9	1229.5
27.5°	811.8	827.2	844.0	870.0	894.9	927.3	960.3	999.3	1048.7	1111.0	1186.7
30°	779.8	791.3	807.1	840.4	862.9	890.8	929.7	964.3	1010.4	1076.6	1156.6
32.5°	746.8	761.7	778.9	804.6	832.3	858.8	894.2	931.7	978.8	1044.0	1126.1
35°	699.7	717.3	734.9	753.7	781.6	809.0	838.7	879.9	927.8	991.0	1071.7
37.5°	656.4	670.6	684.8	708.2	734.7	760.6	788.4	829.0	874.2	942.3	1016.4
40°	628.7	641.4	652.4	676.6	702.1	730.0	757.3	793.2	841.7	905.4	977.0
42.5°	598.6	610.4	625.2	645.1	672.5	696.1	723.4	757.2	802.8	867.5	930.4
45°	553.4	566.8	579.5	598.3	625.6	648.7	673.0	705.2	751.9	805.3	861.1
47.5°	506.5	519.8	534.4	552.6	576.4	599.8	624.1	652.6	695.2	747.6	785.2
50°	476.4	487.3	501.9	520.0	541.9	566.8	588.6	619.6	660.2	701.5	734.2
52.5°	445.3	455.2	471.7	491.0	511.3	532.8	556.1	582.6	619.5	658.3	684.3
55°	396.9	409.0	422.9	441.8	461.8	480.0	502.5	529.8	558.9	588.0	605.6
57.5°	351.6	361.7	373.4	392.9	410.2	431.9	452.1	473.3	500.2	522.3	533.8
60°	318.6	327.7	342.9	359.9	376.2	395.0	418.1	439.3	459.9	477.6	486.7
62.5°	287.5	298.1	311.3	326.8	344.6	362.6	382.6	400.6	418.7	433.9	440.1
65°	247.0	255.5	265.2	279.7	294.4	312.5	328.3	346.5	359.9	368.4	373.8
67.5°	210.1	215.7	223.1	232.8	247.1	263.0	278.3	292.5	303.6	309.5	314.3
70°	186.3	189.9	195.4	205.1	216.1	230.0	245.8	256.1	265.8	270.6	275.5
72.5°	162.5	167.1	172.1	179.9	188.9	198.9	210.4	223.1	228.5	234.3	237.2
75°	123.1	129.8	136.5	141.4	147.5	155.3	165.7	173.5	176.6	181.5	182.1
77.5°	93.0	94.4	99.2	105.3	110.5	116.2	122.7	129.7	131.2	133.8	135.4
80°	76.4	76.4	76.4	80.1	86.1	90.4	96.5	100.1	102.5	103.2	103.8
82.5°	61.4	61.4	60.9	61.6	63.8	66.2	71.7	75.9	77.8	77.4	76.1
85°	40.0	38.9	38.9	38.3	38.9	37.6	37.0	39.4	43.1	43.1	41.9
87.5°	21.0	20.3	20.2	19.3	18.3	17.3	15.3	15.4	15.1	16.6	15.7
90°	22.1	21.4	18.8	16.2	13.6	11.1	8.8	6.9	4.8	2.9	0.9
92.5°	24.1	22.8	20.9	18.9	16.9	15.1	14.4	14.9	15.4	16.0	16.6
95°	29.0	27.6	25.4	23.3	21.0	18.9	21.8	30.0	38.1	46.2	54.3
97.5°	30.2	28.6	42.9	57.2	71.4	85.6	94.5	98.2	101.8	105.5	109.1
100°	30.9	29.3	60.2	91.0	121.9	152.8	166.2	162.3	158.4	154.4	150.4
102.5°	53.7	58.6	92.3	126.0	159.7	193.4	208.8	206.0	203.1	200.3	197.4
105°	159.9	194.9	212.8	230.5	248.3	266.1	273.9	271.8	269.6	267.4	265.2
107.5°	331.6	357.3	354.5	351.7	348.8	346.1	343.8	342.1	340.3	338.6	336.8
110°	394.8	401.4	399.2	397.1	394.8	392.7	390.8	389.2	387.6	386.1	384.5



TEST NUMBER: P332348-940

CATALOG NUMBER: S123RDIP-S1000D1025U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	446.4	446.3	444.1	441.9	439.8	437.6	435.8	434.4	432.9	431.5	430.1
115°	512.9	510.9	509.1	507.3	505.5	503.8	502.3	501.1	499.9	498.7	497.6
117.5°	575.2	573.5	572.7	571.8	570.8	569.9	568.7	567.3	565.8	564.4	562.8
120°	615.7	614.1	613.6	613.0	612.3	611.8	610.6	608.8	607.0	605.2	603.4
122.5°	655.9	654.7	654.0	653.3	652.5	651.8	650.6	649.2	647.6	646.2	644.8
125°	712.5	712.0	711.2	710.4	709.7	708.9	707.7	706.1	704.5	702.9	701.3
127.5°	768.2	767.6	766.6	765.7	764.7	763.8	762.5	760.9	759.4	757.8	756.2
130°	801.8	801.0	800.2	799.5	798.7	797.9	796.7	795.1	793.5	791.9	790.4
132.5°	833.9	833.1	832.5	831.8	831.2	830.5	829.5	827.9	826.3	824.7	823.1
135°	882.6	882.1	881.3	880.5	879.7	878.9	877.9	876.7	875.5	874.3	873.2
137.5°	925.5	924.6	924.2	923.7	923.3	922.8	921.9	920.4	918.9	917.4	915.9
140°	953.1	952.3	951.8	951.2	950.6	950.0	949.1	947.9	946.7	945.6	944.3
142.5°	979.4	978.7	978.1	977.5	977.0	976.3	975.4	974.3	973.0	971.9	970.7
145°	1015.9	1015.6	1015.1	1014.8	1014.4	1014.0	1013.1	1011.7	1010.3	1009.0	1007.5
147.5°	1048.6	1048.1	1047.8	1047.3	1047.0	1046.5	1045.9	1045.0	1044.1	1043.2	1042.2
150°	1068.4	1068.1	1067.6	1067.3	1066.8	1066.5	1066.0	1065.4	1064.8	1064.3	1063.6
152.5°	1085.8	1085.1	1084.9	1084.7	1084.4	1084.2	1084.0	1083.7	1083.4	1083.2	1082.8
155°	1110.0	1109.0	1108.8	1108.6	1108.4	1108.2	1108.3	1108.8	1109.1	1109.5	1109.9
157.5°	1131.0	1129.8	1130.1	1130.2	1130.4	1130.6	1130.8	1130.8	1130.9	1130.9	1130.9
160°	1143.2	1141.9	1142.1	1142.4	1142.5	1142.7	1142.9	1143.2	1143.4	1143.5	1143.7
162.5°	1154.0	1152.6	1152.8	1153.0	1153.2	1153.4	1153.8	1154.3	1154.8	1155.3	1155.8
165°	1168.4	1166.9	1167.1	1167.2	1167.4	1167.7	1168.1	1168.7	1169.2	1169.8	1170.5
167.5°	1179.8	1178.2	1178.2	1178.2	1178.2	1178.2	1178.7	1179.5	1180.3	1181.1	1181.8
170°	1186.2	1184.6	1184.6	1184.6	1184.6	1184.6	1185.1	1185.9	1186.7	1187.4	1188.2
172.5°	1190.5	1188.9	1188.7	1188.7	1188.5	1188.3	1188.7	1189.6	1190.6	1191.6	1192.5
175°	1195.9	1194.4	1194.3	1194.1	1193.8	1193.6	1194.1	1195.1	1196.1	1197.0	1198.0
177.5°	1197.8	1196.6	1196.4	1196.3	1196.1	1196.0	1196.3	1197.0	1197.8	1198.6	1199.4
180°	1198.0	1198.0	1198.0	1198.0	1198.0	1198.0	1198.0	1198.0	1198.0	1198.0	1198.0



TEST NUMBER: P332348-940

CATALOG NUMBER: S123RDIP-S1000D1025U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1425.3	1430.7	1437.4	1447.7	1455.5	1462.2	1463.7	1465.6	1470.5	1478.7	1485.1
5°	1434.6	1448.5	1471.0	1492.8	1516.5	1535.9	1554.1	1566.8	1579.0	1604.5	1625.1
7.5°	1431.6	1462.8	1497.9	1537.1	1576.8	1615.2	1651.0	1682.9	1714.7	1751.9	1794.2
10°	1429.7	1466.2	1513.4	1563.8	1619.1	1673.0	1725.3	1765.9	1813.2	1855.7	1909.7
12.5°	1420.5	1472.9	1529.5	1593.9	1661.8	1724.0	1792.7	1848.9	1903.1	1964.4	2027.2
15°	1408.5	1472.2	1543.8	1629.3	1732.5	1807.8	1878.1	1975.9	2042.6	2109.3	2199.2
17.5°	1386.5	1464.3	1553.7	1664.9	1751.0	1852.1	1958.0	2035.2	2125.1	2219.2	2300.5
20°	1369.0	1459.5	1559.6	1668.8	1778.6	1888.5	1991.0	2083.3	2176.1	2284.7	2351.5
22.5°	1351.6	1441.0	1545.0	1661.1	1779.1	1894.8	2010.9	2119.2	2223.7	2333.3	2418.5
25°	1314.4	1420.6	1533.5	1651.8	1768.4	1895.8	2034.1	2154.9	2284.1	2397.0	2477.7
27.5°	1276.8	1374.1	1486.5	1606.5	1736.1	1886.7	2049.4	2186.7	2316.2	2397.0	2422.4
30°	1242.8	1345.9	1449.1	1571.1	1711.3	1879.4	2052.4	2209.5	2315.7	2350.9	2324.8
32.5°	1208.4	1301.8	1404.0	1528.8	1677.8	1861.4	2056.2	2195.9	2259.9	2232.9	2126.7
35°	1147.5	1231.9	1330.8	1455.8	1626.9	1851.5	2040.2	2134.8	2119.1	1967.4	1767.1
37.5°	1082.4	1151.2	1242.8	1373.5	1574.2	1812.0	1971.2	1985.2	1848.7	1615.8	1384.5
40°	1031.0	1092.9	1187.0	1323.5	1533.5	1773.2	1901.8	1845.4	1633.6	1374.5	1181.5
42.5°	981.0	1033.2	1123.8	1271.0	1494.7	1720.3	1798.4	1675.5	1431.2	1186.2	1010.7
45°	896.3	945.5	1036.4	1187.6	1415.1	1619.1	1608.7	1395.1	1150.6	953.3	807.7
47.5°	815.9	858.9	944.3	1098.6	1321.8	1467.3	1370.8	1143.5	936.1	777.8	674.0
50°	759.1	801.6	886.6	1038.9	1247.1	1353.3	1215.5	996.4	806.5	675.4	592.9
52.5°	704.8	746.3	823.9	972.4	1156.7	1220.2	1072.3	869.2	710.9	597.7	526.8
55°	628.7	660.2	730.0	872.0	1009.8	1024.3	874.4	704.5	574.1	495.2	446.7
57.5°	551.2	578.3	647.3	760.4	856.9	849.4	707.3	560.4	472.5	413.8	378.7
60°	500.6	527.4	588.0	685.1	758.0	732.5	602.0	483.7	408.4	365.3	337.4
62.5°	453.5	474.4	531.2	602.1	654.5	625.6	514.6	416.7	357.0	320.7	298.5
65°	385.3	402.3	447.8	484.8	514.0	486.1	393.9	325.8	282.8	257.3	242.1
67.5°	320.6	331.4	360.1	373.4	394.0	363.4	296.1	250.7	226.1	204.6	194.0
70°	279.7	287.7	302.8	313.7	319.2	287.7	237.9	204.5	183.9	168.7	162.0
72.5°	239.0	245.9	249.0	257.9	255.1	225.5	191.3	164.7	149.9	139.6	131.0
75°	182.6	185.7	182.6	179.1	171.1	150.5	126.8	113.5	102.5	97.7	94.7
77.5°	133.1	132.2	128.0	122.3	108.9	95.9	83.1	78.6	73.9	71.3	70.3
80°	102.5	100.1	96.5	87.4	75.9	66.8	63.8	60.7	58.9	55.8	55.2
82.5°	76.3	74.9	68.8	61.2	53.1	48.8	46.3	45.1	43.3	41.7	41.6
85°	40.7	38.9	32.2	27.9	26.7	25.5	24.9	24.9	22.5	21.8	21.8
87.5°	13.6	11.1	11.1	10.0	10.4	10.0	11.0	10.5	10.6	11.2	10.4
90°	2.9	4.8	6.9	8.8	11.1	13.6	16.2	18.8	21.4	22.1	22.9
92.5°	16.0	15.4	14.9	14.4	15.1	16.9	18.9	20.9	22.8	24.1	25.3
95°	46.2	38.1	30.0	21.8	18.9	21.0	23.3	25.4	27.6	29.0	30.3
97.5°	105.5	101.8	98.2	94.5	85.6	71.4	57.2	42.9	28.6	30.2	31.8
100°	154.4	158.4	162.3	166.2	152.8	121.9	91.0	60.2	29.3	30.9	32.5
102.5°	200.3	203.1	206.0	208.8	193.4	159.7	126.0	92.3	58.6	53.7	48.8
105°	267.4	269.6	271.8	273.9	266.1	248.3	230.5	212.8	194.9	159.9	124.9
107.5°	338.6	340.3	342.1	343.8	346.1	348.8	351.7	354.5	357.3	331.6	305.9
110°	386.1	387.6	389.2	390.8	392.7	394.8	397.1	399.2	401.4	394.8	388.3





TEST NUMBER: P332348-940

CATALOG NUMBER: S123RDIP-S1000D1025U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	431.5	432.9	434.4	435.8	437.6	439.8	441.9	444.1	446.3	446.4	446.5
115°	498.7	499.9	501.1	502.3	503.8	505.5	507.3	509.1	510.9	512.9	514.9
117.5°	564.4	565.8	567.3	568.7	569.9	570.8	571.8	572.7	573.5	575.2	576.8
120°	605.2	607.0	608.8	610.6	611.8	612.3	613.0	613.6	614.1	615.7	617.3
122.5°	646.2	647.6	649.2	650.6	651.8	652.5	653.3	654.0	654.7	655.9	656.9
125°	702.9	704.5	706.1	707.7	708.9	709.7	710.4	711.2	712.0	712.5	712.8
127.5°	757.8	759.4	760.9	762.5	763.8	764.7	765.7	766.6	767.6	768.2	768.8
130°	791.9	793.5	795.1	796.7	797.9	798.7	799.5	800.2	801.0	801.8	802.6
132.5°	824.7	826.3	827.9	829.5	830.5	831.2	831.8	832.5	833.1	833.9	834.6
135°	874.3	875.5	876.7	877.9	878.9	879.7	880.5	881.3	882.1	882.6	883.2
137.5°	917.4	918.9	920.4	921.9	922.8	923.3	923.7	924.2	924.6	925.5	926.5
140°	945.6	946.7	947.9	949.1	950.0	950.6	951.2	951.8	952.3	953.1	954.0
142.5°	971.9	973.0	974.3	975.4	976.3	977.0	977.5	978.1	978.7	979.4	980.0
145°	1009.0	1010.3	1011.7	1013.1	1014.0	1014.4	1014.8	1015.1	1015.6	1015.9	1016.4
147.5°	1043.2	1044.1	1045.0	1045.9	1046.5	1047.0	1047.3	1047.8	1048.1	1048.6	1048.9
150°	1064.3	1064.8	1065.4	1066.0	1066.5	1066.8	1067.3	1067.6	1068.1	1068.4	1068.9
152.5°	1083.2	1083.4	1083.7	1084.0	1084.2	1084.4	1084.7	1084.9	1085.1	1085.8	1086.5
155°	1109.5	1109.1	1108.8	1108.3	1108.2	1108.4	1108.6	1108.8	1109.0	1110.0	1111.0
157.5°	1130.9	1130.9	1130.8	1130.8	1130.6	1130.4	1130.2	1130.1	1129.8	1131.0	1132.2
160°	1143.5	1143.4	1143.2	1142.9	1142.7	1142.5	1142.4	1142.1	1141.9	1143.2	1144.3
162.5°	1155.3	1154.8	1154.3	1153.8	1153.4	1153.2	1153.0	1152.8	1152.6	1154.0	1155.3
165°	1169.8	1169.2	1168.7	1168.1	1167.7	1167.4	1167.2	1167.1	1166.9	1168.4	1170.0
167.5°	1181.1	1180.3	1179.5	1178.7	1178.2	1178.2	1178.2	1178.2	1178.2	1179.8	1181.4
170°	1187.4	1186.7	1185.9	1185.1	1184.6	1184.6	1184.6	1184.6	1184.6	1186.2	1187.8
172.5°	1191.6	1190.6	1189.6	1188.7	1188.3	1188.5	1188.7	1188.7	1188.9	1190.5	1192.1
175°	1197.0	1196.1	1195.1	1194.1	1193.6	1193.8	1194.1	1194.3	1194.4	1195.9	1197.2
177.5°	1198.6	1197.8	1197.0	1196.3	1196.0	1196.1	1196.3	1196.4	1196.6	1197.8	1199.1
180°	1198.0	1198.0	1198.0	1198.0	1198.0	1198.0	1198.0	1198.0	1198.0	1198.0	1198.0



TEST NUMBER: P332348-940

CATALOG NUMBER: S123RDIP-S1000D1025U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1495.2	1495.2	1497.2	1504.5	1505.5	1511.7	1509.8
5°	1643.3	1654.8	1659.1	1677.3	1688.2	1693.1	1683.4
7.5°	1824.4	1856.9	1872.3	1891.4	1908.3	1913.3	1900.1
10°	1956.4	1990.4	2018.9	2036.6	2052.9	2063.9	2077.8
12.5°	2084.1	2125.8	2152.9	2177.8	2194.7	2208.5	2210.8
15°	2222.9	2286.0	2333.9	2369.1	2386.7	2395.8	2392.2
17.5°	2362.8	2421.3	2455.4	2491.4	2515.7	2516.9	2517.7
20°	2442.0	2498.9	2538.4	2565.1	2592.4	2591.2	2597.3
22.5°	2494.8	2539.8	2570.0	2589.3	2598.7	2594.1	2595.3
25°	2519.6	2532.9	2527.5	2496.5	2488.7	2460.1	2465.0
27.5°	2391.9	2328.8	2263.5	2179.5	2113.3	2060.3	2063.0
30°	2218.6	2106.9	1979.5	1872.7	1776.8	1750.2	1693.1
32.5°	1976.4	1808.8	1659.6	1560.0	1477.7	1455.5	1405.7
35°	1565.7	1403.0	1249.5	1157.3	1120.8	1069.9	1069.3
37.5°	1216.9	1073.7	992.6	923.4	887.1	856.2	853.2
40°	1023.8	912.0	850.8	801.0	765.3	742.2	736.7
42.5°	888.8	798.4	741.1	710.2	682.7	670.8	661.9
45°	725.8	665.1	625.0	597.1	584.4	575.2	570.4
47.5°	607.1	566.4	539.1	520.6	510.2	500.6	503.2
50°	542.5	509.2	489.1	471.5	463.6	456.9	457.5
52.5°	490.5	460.6	444.4	431.7	421.9	417.1	414.8
55°	416.3	397.4	381.1	372.0	366.5	359.9	358.0
57.5°	355.1	340.5	327.2	316.9	315.6	309.2	310.0
60°	314.3	302.2	291.3	285.8	281.6	276.1	277.9
62.5°	280.9	270.6	260.7	256.2	252.0	248.0	248.8
65°	230.0	220.3	214.2	211.8	210.0	208.1	206.3
67.5°	183.2	177.4	173.5	168.4	164.6	164.0	162.1
70°	154.2	146.2	139.6	132.9	131.1	130.5	131.1
72.5°	123.6	118.6	116.7	113.5	113.2	111.6	112.6
75°	92.8	91.0	89.8	87.4	87.4	87.4	87.4
77.5°	68.5	67.3	66.6	66.2	65.5	64.6	64.6
80°	53.4	52.8	51.5	51.5	51.0	51.5	51.0
82.5°	40.3	40.2	39.0	39.0	38.3	38.0	38.3
85°	20.6	20.1	21.2	20.1	20.6	19.4	20.6
87.5°	10.6	10.7	10.3	10.4	10.1	11.1	10.2
90°	23.7	24.5	25.1	25.5	25.9	26.3	26.7
92.5°	26.6	27.8	28.6	28.8	29.1	29.3	29.5
95°	31.7	33.2	33.8	33.8	33.8	33.8	33.8
97.5°	33.4	35.0	35.8	36.1	36.3	36.5	36.6
100°	34.2	35.7	36.6	36.8	37.0	37.2	37.4
102.5°	43.9	39.0	36.6	37.0	37.4	37.7	38.1
105°	89.9	54.9	37.5	38.0	38.3	38.8	39.1
107.5°	280.3	254.6	228.5	202.2	175.8	149.4	123.0
110°	381.8	375.3	357.9	329.6	301.3	273.0	244.8



TEST NUMBER: P332348-940

CATALOG NUMBER: S123RDIP-S1000D1025U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	446.7	446.7	443.8	437.8	431.9	425.9	419.9
115°	516.8	518.8	520.2	520.9	521.7	522.5	523.3
117.5°	578.3	579.9	580.8	580.9	581.0	581.2	581.4
120°	618.8	620.5	621.3	621.3	621.3	621.3	621.3
122.5°	658.1	659.2	659.8	660.0	660.1	660.2	660.4
125°	713.2	713.6	714.0	714.4	714.8	715.2	715.6
127.5°	769.5	770.1	770.3	769.8	769.5	769.0	768.7
130°	803.4	804.2	804.4	804.1	803.6	803.3	802.8
132.5°	835.4	836.2	836.3	835.8	835.3	834.7	834.2
135°	883.9	884.4	884.4	883.9	883.2	882.6	882.1
137.5°	927.5	928.4	928.6	928.3	927.9	927.5	927.1
140°	954.8	955.6	955.7	955.3	954.9	954.6	954.1
142.5°	980.6	981.2	981.2	980.7	980.2	979.6	979.1
145°	1016.7	1017.2	1017.4	1017.4	1017.4	1017.4	1017.4
147.5°	1049.3	1049.7	1049.5	1048.6	1047.7	1046.7	1045.8
150°	1069.3	1069.7	1069.5	1069.0	1068.4	1067.7	1067.2
152.5°	1087.3	1088.0	1087.9	1087.0	1086.1	1085.2	1084.2
155°	1112.0	1112.9	1112.9	1111.7	1110.5	1109.3	1108.1
157.5°	1133.4	1134.6	1134.4	1132.8	1131.3	1129.8	1128.3
160°	1145.5	1146.7	1146.6	1145.2	1143.8	1142.5	1141.0
162.5°	1156.6	1158.0	1158.1	1156.8	1155.6	1154.4	1153.2
165°	1171.6	1173.2	1173.3	1171.9	1170.5	1169.1	1167.8
167.5°	1183.0	1184.5	1184.5	1183.0	1181.4	1179.8	1178.2
170°	1189.5	1191.0	1191.0	1189.5	1187.8	1186.2	1184.6
172.5°	1193.6	1195.2	1195.2	1193.5	1191.7	1190.0	1188.2
175°	1198.6	1200.0	1199.9	1198.3	1196.8	1195.2	1193.6
177.5°	1200.4	1201.7	1201.5	1199.9	1198.4	1196.8	1195.2
180°	1198.0	1198.0	1198.0	1198.0	1198.0	1198.0	1198.0

(END OF REPORT)