

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332676-830

Luminaire Tested: **S124DIP-S1195D365U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332676-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIP-S1195D365U830-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 365 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6199.0 lumens  
Efficiency: N/A  
Efficacy: 124.5 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Direct  
  
Input Watts (W): 49.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332676-830

CATALOG NUMBER: S124DIP-S1195D365U830-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332676-830

CATALOG NUMBER: S124DIP-S1195D365U830-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	114	114	114	114	109	109	109	109	99	99	99	90	90	90	82	82	82	78
1	104	99	95	92	99	95	91	88	87	84	81	79	77	75	72	70	69	65
2	95	87	80	75	90	83	77	72	76	71	67	69	66	63	63	61	58	55
3	86	76	69	63	82	73	66	61	67	61	57	61	57	53	56	53	49	46
4	79	68	59	53	75	65	57	51	60	53	48	55	50	45	50	46	43	40
5	73	61	52	46	69	58	50	44	54	47	42	49	44	40	45	41	37	35
6	67	55	46	40	64	52	45	39	48	42	37	45	39	35	41	36	33	30
7	62	49	41	35	59	48	40	34	44	37	33	41	35	31	38	33	29	27
8	58	45	37	31	55	43	36	31	40	34	29	37	32	28	35	30	26	24
9	54	41	33	28	52	40	32	27	37	31	26	34	29	25	32	27	24	22
10	51	38	30	25	48	37	30	25	34	28	24	32	26	23	30	25	22	20

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	15163	15163	15163
5°	15209	15027	15135
10°	15114	14905	14978
15°	14931	14692	14730
20°	14689	14430	14442
25°	14412	14130	14091
30°	14072	13778	13651
35°	13720	13409	13232
40°	13354	12991	12752
45°	12973	12578	12337
50°	12552	12210	11833
55°	12096	11736	11354
60°	11641	11202	10863
65°	11127	10695	10264
70°	10551	10017	9626
75°	9669	9201	8968
80°	8605	8257	8047
85°	7521	7243	7104



TEST NUMBER: P332676-830

CATALOG NUMBER: S124DIP-S1195D365U830-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	176.9	2.9
10°-20°	498.4	8.0
20°-30°	733.6	11.8
30°-40°	852.8	13.8
40°-50°	852.8	13.8
50°-60°	746.0	12.0
60°-70°	554.0	8.9
70°-80°	314.7	5.1
80°-90°	92.1	1.5
90°-100°	15.2	0.2
100°-110°	97.1	1.6
110°-120°	185.8	3.0
120°-130°	235.8	3.8
130°-140°	252.3	4.1
140°-150°	236.0	3.8
150°-160°	190.3	3.1
160°-170°	122.7	2.0
170°-180°	42.3	0.7
0°-30°	1408.8	22.7
0°-40°	2261.6	36.5
0°-60°	3860.5	62.3
0°-90°	4821.3	77.8
90°-120°	298.1	4.8
90°-150°	1022.3	16.5
90°-180°	1378.0	22.2
0°-180°	6199.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1878	1878	1878	1878	1878	
5°	1877	1870	1854	1870	1868	178
15°	1786	1780	1758	1766	1762	503
25°	1618	1607	1586	1587	1582	744
35°	1392	1381	1361	1350	1343	870
45°	1136	1125	1102	1086	1081	876
55°	859	854	834	816	807	769
65°	582	575	560	545	537	577
75°	310	302	295	289	288	329
85°	81	81	78	78	77	89
90°	1	5	7	9	10	5
95°	18	8	7	9	10	24
105°	100	102	104	106	95	105
115°	187	188	188	188	188	184
125°	263	264	264	265	265	235
135°	326	326	327	328	329	251
145°	376	377	377	378	378	235
155°	413	413	412	413	412	190
165°	435	434	434	436	433	123
175°	445	444	444	446	443	42
180°	445	445	445	445	445	



TEST NUMBER: P332676-830

CATALOG NUMBER: S124DIP-S1195D365U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3
2.5°	1883.1	1882.4	1881.5	1880.7	1879.9	1878.0	1875.1	1872.2	1869.3	1866.3	1869.0
5°	1876.8	1875.5	1874.2	1872.8	1871.5	1869.0	1865.3	1861.6	1857.9	1854.3	1857.9
7.5°	1859.4	1858.0	1856.7	1855.3	1854.0	1851.3	1847.2	1843.1	1839.1	1834.9	1838.0
10°	1843.7	1842.4	1841.1	1839.7	1838.3	1835.5	1831.2	1826.8	1822.5	1818.2	1820.8
12.5°	1823.3	1821.9	1820.5	1819.2	1817.9	1814.9	1810.3	1805.7	1801.1	1796.5	1799.4
15°	1786.5	1785.2	1783.9	1782.5	1781.1	1778.0	1772.9	1767.9	1762.9	1757.9	1759.9
17.5°	1742.3	1740.6	1738.9	1737.3	1735.6	1732.4	1727.6	1722.9	1718.2	1713.4	1714.7
20°	1709.8	1708.1	1706.4	1704.8	1703.1	1699.7	1694.7	1689.7	1684.7	1679.6	1680.6
22.5°	1674.8	1672.6	1670.5	1668.2	1666.0	1662.4	1657.4	1652.4	1647.4	1642.3	1644.2
25°	1618.0	1615.6	1613.3	1610.9	1608.5	1605.1	1600.3	1595.7	1591.0	1586.3	1586.7
27.5°	1552.9	1550.5	1548.1	1545.7	1543.3	1539.9	1535.6	1531.3	1526.9	1522.5	1521.7
30°	1509.6	1506.9	1504.2	1501.6	1498.9	1495.3	1491.0	1486.7	1482.3	1478.0	1476.7
32.5°	1463.9	1461.4	1459.1	1456.6	1454.2	1450.7	1446.0	1441.4	1436.8	1432.2	1430.6
35°	1392.2	1389.9	1387.5	1385.2	1382.8	1379.3	1374.6	1370.0	1365.3	1360.6	1358.2
37.5°	1316.6	1314.5	1312.4	1310.2	1308.1	1304.5	1299.5	1294.5	1289.4	1284.4	1281.9
40°	1267.2	1264.6	1261.9	1259.2	1256.6	1252.7	1247.7	1242.6	1237.7	1232.7	1229.3
42.5°	1214.3	1212.7	1211.1	1209.5	1207.9	1204.3	1198.7	1193.2	1187.6	1182.0	1178.2
45°	1136.3	1134.0	1131.6	1129.3	1127.0	1123.1	1117.8	1112.4	1107.0	1101.7	1098.1
47.5°	1054.7	1053.1	1051.5	1049.9	1048.3	1045.1	1040.1	1035.2	1030.2	1025.3	1021.2
50°	999.4	998.1	996.6	995.3	994.0	991.0	986.3	981.7	976.9	972.2	967.6
52.5°	945.2	943.6	942.0	940.4	938.8	935.5	930.6	925.6	920.7	915.7	911.5
55°	859.4	858.4	857.4	856.4	855.4	852.5	847.8	843.2	838.5	833.8	829.8
57.5°	777.5	776.4	775.2	774.1	773.0	770.1	765.4	760.8	756.2	751.6	747.8
60°	721.0	719.3	717.6	716.0	714.3	711.2	706.9	702.6	698.1	693.8	690.8
62.5°	665.5	664.1	662.7	661.3	660.0	657.0	652.3	647.7	643.1	638.5	635.7
65°	582.5	580.8	579.1	577.4	575.8	573.3	570.0	566.6	563.3	559.9	556.6
67.5°	498.8	497.3	495.7	494.2	492.7	490.2	487.0	483.8	480.6	477.4	474.2
70°	447.0	444.7	442.3	440.0	437.6	435.2	432.4	429.8	427.1	424.4	421.8
72.5°	391.6	389.3	386.9	384.6	382.3	380.0	377.9	375.7	373.6	371.5	369.3
75°	310.0	308.4	306.7	305.0	303.3	301.7	300.0	298.3	296.7	295.0	293.7
77.5°	232.1	231.3	230.6	229.9	229.1	228.0	226.6	225.1	223.7	222.2	221.8
80°	185.1	184.1	183.1	182.1	181.2	180.3	179.6	178.9	178.2	177.6	176.9
82.5°	139.4	138.9	138.5	138.0	137.5	137.2	137.0	137.0	136.8	136.7	136.3
85°	81.2	81.2	81.2	81.2	81.2	81.0	80.3	79.6	78.9	78.2	78.2
87.5°	31.5	31.4	31.3	31.2	31.1	30.9	30.8	30.6	30.5	30.3	30.4
90°	1.0	1.8	2.6	3.5	4.2	5.0	5.6	6.1	6.7	7.4	7.7
92.5°	4.2	4.2	4.2	4.3	4.3	4.7	5.3	5.8	6.5	7.1	7.5
95°	18.3	15.8	13.3	10.7	8.3	7.1	7.1	7.2	7.3	7.4	7.7
97.5°	38.9	40.4	42.0	43.6	45.1	41.8	33.6	25.4	17.1	8.8	8.9
100°	54.7	56.0	57.3	58.6	59.9	55.5	45.3	35.1	24.9	14.7	13.4
102.5°	72.2	73.2	74.2	75.1	76.2	76.0	74.6	73.3	71.9	70.6	57.0
105°	100.3	100.7	101.1	101.6	102.1	102.5	102.8	103.2	103.6	104.0	104.6
107.5°	126.3	126.5	126.8	127.0	127.2	127.5	128.1	128.6	129.0	129.6	129.9
110°	143.9	144.1	144.3	144.6	144.8	145.2	145.5	146.0	146.5	146.9	147.0



TEST NUMBER: P332676-830

CATALOG NUMBER: S124DIP-S1195D365U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	161.0	161.4	161.7	162.1	162.6	162.9	163.1	163.2	163.4	163.7	163.6
115°	187.2	187.5	187.7	187.8	188.1	188.1	188.1	188.0	187.9	187.8	188.0
117.5°	210.8	211.1	211.4	211.8	212.1	212.3	212.4	212.6	212.7	212.9	212.9
120°	226.9	227.2	227.4	227.7	228.0	228.1	228.1	228.0	227.9	227.8	228.0
122.5°	241.8	242.0	242.1	242.3	242.5	242.6	242.7	242.8	242.9	243.1	243.1
125°	263.2	263.4	263.7	264.0	264.4	264.4	264.3	264.1	264.0	263.8	264.0
127.5°	283.4	283.5	283.5	283.6	283.7	283.9	284.3	284.6	284.9	285.3	285.2
130°	296.4	296.5	296.6	296.7	296.8	296.9	297.1	297.4	297.6	297.8	297.8
132.5°	308.5	308.6	308.7	308.9	309.0	309.2	309.4	309.7	310.0	310.3	310.4
135°	326.4	326.4	326.3	326.2	326.1	326.2	326.6	326.9	327.2	327.4	327.6
137.5°	342.3	342.4	342.4	342.4	342.5	342.7	343.0	343.3	343.7	343.9	344.1
140°	352.8	352.9	353.1	353.2	353.4	353.5	353.6	353.8	353.9	354.1	354.3
142.5°	362.1	362.3	362.6	362.9	363.2	363.4	363.4	363.5	363.6	363.7	363.8
145°	376.5	376.6	376.8	377.1	377.3	377.4	377.4	377.4	377.4	377.4	377.5
147.5°	387.8	388.2	388.6	389.1	389.5	389.6	389.6	389.5	389.4	389.4	389.4
150°	396.1	396.3	396.6	397.0	397.3	397.4	397.3	397.2	397.1	397.1	397.1
152.5°	403.0	403.2	403.5	403.7	404.0	404.0	403.9	403.7	403.6	403.5	403.6
155°	412.7	412.8	412.8	412.9	413.0	412.9	412.7	412.5	412.3	412.1	412.4
157.5°	420.9	420.8	420.8	420.8	420.8	420.6	420.4	420.1	419.8	419.6	420.0
160°	425.7	425.5	425.3	425.1	424.8	424.7	424.6	424.5	424.4	424.3	424.8
162.5°	430.0	429.7	429.4	429.1	428.9	428.7	428.6	428.5	428.5	428.4	428.9
165°	435.4	435.0	434.6	434.2	433.9	433.7	433.7	433.7	433.7	433.7	434.3
167.5°	439.6	439.2	438.8	438.5	438.1	437.9	437.8	437.8	437.7	437.7	438.4
170°	442.1	441.6	441.1	440.7	440.3	440.1	440.2	440.3	440.3	440.4	440.9
172.5°	443.7	443.2	442.7	442.3	441.9	441.7	441.8	441.9	441.9	442.0	442.5
175°	445.4	444.9	444.5	444.0	443.6	443.4	443.5	443.6	443.7	443.7	444.4
177.5°	446.2	445.7	445.4	444.9	444.5	444.3	444.5	444.6	444.7	444.8	445.4
180°	445.4	445.4	445.4	445.4	445.4	445.4	445.4	445.4	445.4	445.4	445.4



TEST NUMBER: P332676-830

CATALOG NUMBER: S124DIP-S1195D365U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3	1878.3
2.5°	1871.6	1874.3	1877.0	1878.2	1877.9	1877.6	1877.4	1877.1
5°	1861.6	1865.3	1869.0	1870.5	1869.8	1869.2	1868.5	1867.7
7.5°	1840.9	1843.8	1846.7	1848.0	1847.7	1847.2	1846.8	1846.4
10°	1823.4	1826.2	1828.8	1829.9	1829.2	1828.5	1827.8	1827.1
12.5°	1802.3	1805.3	1808.3	1809.2	1808.3	1807.3	1806.4	1805.4
15°	1761.9	1764.0	1765.9	1766.4	1765.5	1764.4	1763.4	1762.5
17.5°	1715.9	1717.2	1718.4	1718.7	1718.1	1717.4	1716.7	1716.1
20°	1681.7	1682.6	1683.7	1683.9	1683.2	1682.5	1681.9	1681.1
22.5°	1646.0	1647.8	1649.5	1649.8	1648.7	1647.5	1646.2	1645.0
25°	1587.1	1587.3	1587.7	1587.1	1585.8	1584.5	1583.2	1581.9
27.5°	1520.9	1520.1	1519.3	1518.1	1516.4	1514.8	1513.1	1511.4
30°	1475.3	1473.9	1472.6	1471.1	1469.4	1467.8	1466.1	1464.4
32.5°	1429.0	1427.4	1425.8	1424.2	1422.5	1420.8	1419.2	1417.5
35°	1355.9	1353.6	1351.2	1349.2	1347.6	1345.9	1344.2	1342.6
37.5°	1279.3	1276.8	1274.2	1271.9	1269.7	1267.4	1265.3	1263.0
40°	1226.0	1222.6	1219.3	1216.7	1215.1	1213.4	1211.7	1210.0
42.5°	1174.3	1170.4	1166.6	1164.0	1162.9	1161.8	1160.6	1159.5
45°	1094.4	1090.7	1087.0	1084.7	1083.6	1082.6	1081.7	1080.6
47.5°	1017.0	1012.9	1008.7	1005.3	1002.8	1000.2	997.7	995.1
50°	962.9	958.2	953.6	950.2	948.2	946.2	944.1	942.2
52.5°	907.4	903.2	899.1	895.8	893.2	890.7	888.2	885.6
55°	825.8	821.8	817.7	814.7	812.8	810.8	808.7	806.7
57.5°	744.0	740.2	736.4	733.5	731.6	729.6	727.6	725.8
60°	687.8	684.9	681.8	679.5	677.8	676.1	674.5	672.8
62.5°	632.9	630.2	627.5	625.3	623.6	621.9	620.3	618.6
65°	553.2	549.9	546.5	544.0	542.3	540.6	538.9	537.3
67.5°	471.0	467.8	464.6	462.7	462.2	461.8	461.3	460.8
70°	419.1	416.4	413.7	411.9	410.9	409.9	408.9	407.8
72.5°	367.2	365.0	362.9	361.3	360.3	359.3	358.3	357.3
75°	292.3	291.0	289.6	288.8	288.5	288.1	287.8	287.5
77.5°	221.3	220.9	220.6	219.9	219.0	218.2	217.3	216.4
80°	176.3	175.6	174.9	174.5	174.1	173.7	173.4	173.1
82.5°	135.8	135.4	135.1	134.7	134.3	134.0	133.7	133.4
85°	78.2	78.2	78.2	78.1	77.8	77.4	77.1	76.7
87.5°	30.5	30.6	30.7	30.8	30.8	30.8	30.8	30.9
90°	8.2	8.7	9.1	9.4	9.5	9.7	9.8	10.0
92.5°	7.9	8.4	8.9	9.0	9.1	9.1	9.1	9.2
95°	8.2	8.7	9.1	9.3	9.4	9.5	9.6	9.6
97.5°	8.9	9.0	9.0	9.0	9.1	9.1	9.2	9.3
100°	12.2	10.8	9.6	9.0	9.1	9.1	9.2	9.3
102.5°	43.5	29.9	16.3	9.5	9.5	9.5	9.6	9.6
105°	105.3	105.9	106.6	105.6	102.9	100.3	97.6	94.9
107.5°	130.3	130.5	130.9	131.2	131.5	131.8	132.1	132.3
110°	147.2	147.3	147.5	147.7	147.9	148.2	148.4	148.5





TEST NUMBER: P332676-830

CATALOG NUMBER: S124DIP-S1195D365U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	163.6	163.6	163.5	163.7	164.0	164.3	164.6	164.9
115°	188.1	188.3	188.5	188.5	188.5	188.5	188.5	188.5
117.5°	212.8	212.8	212.8	212.7	212.7	212.7	212.7	212.6
120°	228.1	228.3	228.5	228.5	228.3	228.1	228.0	227.8
122.5°	243.2	243.3	243.4	243.4	243.2	243.1	242.9	242.8
125°	264.3	264.5	264.7	264.9	264.9	265.0	265.0	265.1
127.5°	285.2	285.1	285.1	285.0	285.0	284.9	284.8	284.8
130°	297.9	298.0	298.1	298.1	298.1	298.1	298.1	298.1
132.5°	310.5	310.6	310.7	310.7	310.6	310.5	310.5	310.4
135°	327.7	327.9	328.0	328.2	328.3	328.5	328.7	328.8
137.5°	344.3	344.5	344.6	344.7	344.6	344.6	344.5	344.5
140°	354.5	354.8	355.0	355.2	355.2	355.2	355.3	355.4
142.5°	364.0	364.2	364.3	364.4	364.5	364.5	364.5	364.5
145°	377.6	377.7	377.7	377.8	378.0	378.1	378.2	378.4
147.5°	389.5	389.6	389.6	389.6	389.7	389.7	389.8	389.9
150°	397.1	397.1	397.1	397.1	397.2	397.3	397.3	397.4
152.5°	403.7	403.8	404.0	404.0	403.9	403.9	403.9	403.8
155°	412.6	412.9	413.2	413.3	413.0	412.8	412.6	412.4
157.5°	420.4	420.8	421.1	421.1	420.8	420.4	420.0	419.6
160°	425.3	425.7	426.1	426.1	425.7	425.3	424.8	424.3
162.5°	429.2	429.7	430.2	430.1	429.6	429.1	428.6	428.1
165°	434.9	435.5	436.1	436.0	435.4	434.7	434.0	433.4
167.5°	439.0	439.7	440.3	440.3	439.5	438.8	438.0	437.3
170°	441.6	442.1	442.7	442.6	442.0	441.2	440.5	439.7
172.5°	443.2	443.7	444.3	444.2	443.5	442.6	441.9	441.0
175°	445.1	445.7	446.4	446.3	445.4	444.5	443.6	442.7
177.5°	445.8	446.3	446.8	446.6	445.9	445.2	444.5	443.7
180°	445.4	445.4	445.4	445.4	445.4	445.4	445.4	445.4

(END OF REPORT)