

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332357-940

Luminaire Tested: **S123RDIP-S1000D1195U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332357-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1000D1195U940-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1195 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7636.9 lumens
Efficiency: N/A
Efficacy: 116.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 65.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332357-940

CATALOG NUMBER: S123RDIP-S1000D1195U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332357-940

CATALOG NUMBER: S123RDIP-S1000D1195U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44
1	97	93	89	85	89	85	82	79	71	68	66	58	56	55	45	44	44	38
2	88	81	75	70	81	75	70	65	62	59	55	51	48	46	40	39	37	32
3	81	72	64	59	74	66	60	55	55	51	47	45	42	39	36	34	32	28
4	74	63	56	50	68	59	52	47	49	44	40	40	37	34	32	30	28	24
5	68	57	49	43	62	52	45	40	44	39	35	36	32	29	29	26	24	21
6	63	51	43	37	57	47	40	35	40	34	30	33	29	26	27	24	21	18
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	24	21	19	16
8	54	42	34	29	49	39	32	27	33	28	24	27	23	21	22	19	17	15
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	21	18	16	13
10	47	35	28	23	43	33	26	22	28	23	19	23	19	17	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16108	16108	16108
5°	16170	15946	16038
10°	16078	15746	15692
15°	15905	15377	15216
20°	15668	14917	14569
25°	15423	14400	13938
30°	15100	13803	13048
35°	14767	13205	12232
40°	14462	12500	11221
45°	14059	11805	10310
50°	13618	11015	9287
55°	13165	10113	8336
60°	12751	9145	7289
65°	12210	8099	6243
70°	11534	6801	5042
75°	10551	5352	4741
80°	9403	4736	4364
85°	7941	4199	3903



TEST NUMBER: P332357-940

CATALOG NUMBER: S123RDIP-S1000D1195U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.5	1.8
10°-20°	391.0	5.1
20°-30°	563.0	7.4
30°-40°	634.1	8.3
40°-50°	606.7	7.9
50°-60°	496.8	6.5
60°-70°	335.2	4.4
70°-80°	168.6	2.2
80°-90°	48.5	0.6
90°-100°	50.7	0.7
100°-110°	241.6	3.2
110°-120°	580.4	7.6
120°-130°	739.1	9.7
130°-140°	789.7	10.3
140°-150°	738.4	9.7
150°-160°	595.6	7.8
160°-170°	384.4	5.0
170°-180°	132.5	1.7
0°-30°	1094.5	14.3
0°-40°	1728.6	22.6
0°-60°	2832.1	37.1
0°-90°	3384.5	44.3
90°-120°	872.7	11.4
90°-150°	3139.9	41.1
90°-180°	4252.0	55.7
0°-180°	7636.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1496	1496	1496	1496	1496	
5°	1496	1490	1476	1486	1484	142
15°	1427	1413	1380	1374	1365	402
25°	1299	1267	1212	1188	1174	597
35°	1124	1078	1005	954	931	703
45°	924	867	776	709	677	712
55°	702	640	539	471	444	629
65°	479	411	318	261	245	474
75°	254	195	129	117	114	270
85°	64	39	34	32	32	72
90°	1	12	25	29	31	6
95°	63	24	32	39	39	78
105°	309	314	227	54	46	327
115°	579	586	595	605	609	571
125°	816	824	829	831	833	729
135°	1016	1022	1027	1030	1027	782
145°	1173	1180	1182	1184	1184	734
155°	1292	1290	1291	1295	1290	595
165°	1362	1359	1358	1366	1359	385
175°	1394	1390	1390	1397	1389	133
180°	1394	1394	1394	1394	1394	



TEST NUMBER: P332357-940

CATALOG NUMBER: S123RDIP-S1000D1195U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5
2.5°	1501.3	1500.4	1499.6	1498.7	1497.8	1496.1	1493.5	1490.9	1488.4	1485.8	1488.1
5°	1496.5	1495.0	1493.7	1492.4	1491.0	1488.7	1485.5	1482.3	1479.1	1475.8	1478.2
7.5°	1482.6	1481.1	1479.7	1478.2	1476.8	1473.9	1469.7	1465.5	1461.3	1457.1	1458.5
10°	1471.0	1469.1	1467.1	1465.3	1463.4	1460.0	1455.2	1450.3	1445.5	1440.6	1440.9
12.5°	1454.5	1452.3	1450.3	1448.1	1446.0	1442.0	1436.1	1430.1	1424.2	1418.3	1418.1
15°	1427.3	1424.3	1421.3	1418.4	1415.4	1410.2	1402.6	1395.0	1387.5	1379.9	1378.6
17.5°	1393.0	1389.6	1386.2	1382.7	1379.2	1372.7	1363.1	1353.5	1343.9	1334.3	1331.4
20°	1367.8	1363.5	1359.1	1354.9	1350.5	1343.3	1333.0	1322.8	1312.5	1302.3	1298.8
22.5°	1339.6	1334.7	1329.7	1324.7	1319.8	1311.9	1300.9	1290.0	1279.2	1268.3	1263.9
25°	1298.6	1291.9	1285.1	1278.4	1271.7	1262.0	1249.6	1237.2	1224.9	1212.5	1206.8
27.5°	1248.8	1241.4	1233.9	1226.5	1219.1	1208.4	1194.6	1180.8	1167.0	1153.2	1145.3
30°	1214.9	1206.8	1198.7	1190.6	1182.5	1170.9	1155.8	1140.7	1125.6	1110.5	1101.4
32.5°	1180.9	1171.7	1162.5	1153.3	1144.2	1131.7	1115.7	1099.7	1083.7	1067.7	1057.7
35°	1123.8	1114.1	1104.4	1094.8	1085.0	1071.7	1055.1	1038.3	1021.6	1004.9	993.3
37.5°	1066.0	1055.3	1044.5	1033.7	1022.9	1008.6	990.8	972.9	955.0	937.2	924.0
40°	1029.2	1017.4	1005.4	993.5	981.7	966.2	947.1	927.9	908.7	889.6	875.6
42.5°	987.4	975.5	963.7	951.8	940.0	924.2	904.4	884.6	864.8	845.0	829.6
45°	923.6	911.4	899.3	887.2	875.0	858.6	837.9	817.1	796.3	775.5	760.2
47.5°	859.8	846.4	833.1	819.7	806.5	789.4	768.7	747.9	727.1	706.3	689.6
50°	813.2	800.5	787.8	775.2	762.4	745.2	723.4	701.5	679.7	657.8	641.1
52.5°	771.4	757.7	743.9	730.1	716.4	698.7	677.1	655.4	633.8	612.2	594.8
55°	701.5	688.3	675.0	661.8	648.6	630.5	607.6	584.7	561.8	538.9	523.3
57.5°	636.9	622.5	608.1	593.7	579.3	560.6	537.5	514.5	491.5	468.5	453.7
60°	592.3	577.5	562.6	547.8	532.9	514.3	492.0	469.6	447.2	424.8	410.2
62.5°	547.6	532.8	517.9	503.1	488.3	469.7	447.3	424.9	402.5	380.1	366.4
65°	479.4	464.6	449.7	434.9	420.1	402.2	381.1	360.1	339.0	318.0	304.8
67.5°	411.2	396.2	381.2	366.2	351.2	333.6	313.4	293.3	273.1	252.9	243.1
70°	366.5	352.0	337.4	322.8	308.3	291.6	272.7	253.8	234.9	216.1	206.6
72.5°	321.8	307.6	293.2	278.8	264.5	248.7	231.6	214.5	197.2	180.1	172.4
75°	253.7	240.7	227.7	214.8	201.9	188.0	173.2	158.3	143.5	128.7	125.9
77.5°	191.5	179.8	168.1	156.4	144.7	134.0	124.5	114.9	105.4	95.9	94.4
80°	151.7	140.6	129.6	118.5	107.5	99.2	93.5	87.7	82.1	76.4	75.6
82.5°	113.9	104.3	94.8	85.2	75.6	69.6	66.9	64.3	61.6	58.9	58.1
85°	64.3	58.4	52.4	46.5	40.6	37.2	36.4	35.6	34.8	34.0	33.4
87.5°	23.5	21.6	19.7	17.7	15.9	15.2	15.8	16.4	17.0	17.6	17.6
90°	1.1	3.3	5.6	7.9	10.3	12.9	15.9	18.9	21.8	24.9	25.8
92.5°	19.3	18.6	18.0	17.3	16.7	17.5	19.8	22.0	24.3	26.5	28.0
95°	63.2	53.8	44.3	34.9	25.4	22.0	24.5	27.0	29.6	32.1	33.7
97.5°	127.0	122.8	118.5	114.3	110.0	99.7	83.1	66.5	49.9	33.3	35.2
100°	175.0	179.7	184.3	188.9	193.5	177.8	142.0	106.0	70.1	34.2	36.0
102.5°	229.8	233.1	236.4	239.7	243.1	225.1	185.8	146.6	107.4	68.1	62.4
105°	308.7	311.3	313.8	316.3	318.9	309.8	289.0	268.3	247.6	226.9	186.1
107.5°	392.0	394.0	396.1	398.1	400.1	402.8	406.1	409.3	412.6	415.9	385.9
110°	447.5	449.4	451.2	453.1	455.0	457.1	459.7	462.2	464.7	467.3	459.7



TEST NUMBER: P332357-940

CATALOG NUMBER: S123RDIP-S1000D1195U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	500.6	502.2	503.9	505.6	507.2	509.3	511.8	514.4	516.9	519.4	519.6
115°	579.2	580.5	581.8	583.3	584.6	586.4	588.4	590.5	592.6	594.7	597.0
117.5°	655.1	656.8	658.5	660.3	662.0	663.3	664.4	665.5	666.6	667.6	669.4
120°	702.4	704.5	706.6	708.6	710.7	712.1	712.7	713.5	714.2	714.8	716.7
122.5°	750.5	752.2	753.9	755.5	757.3	758.6	759.5	760.4	761.2	762.1	763.4
125°	816.4	818.2	820.0	821.9	823.8	825.1	826.0	827.0	827.9	828.8	829.3
127.5°	880.2	882.0	883.9	885.7	887.5	889.0	890.1	891.3	892.3	893.4	894.2
130°	920.0	921.9	923.6	925.5	927.3	928.7	929.6	930.6	931.5	932.4	933.4
132.5°	958.1	959.9	961.8	963.6	965.5	966.7	967.5	968.2	968.9	969.7	970.6
135°	1016.3	1017.7	1019.0	1020.5	1021.8	1023.0	1024.0	1024.8	1025.7	1026.7	1027.3
137.5°	1066.0	1067.8	1069.5	1071.3	1073.1	1074.2	1074.7	1075.2	1075.7	1076.2	1077.3
140°	1099.2	1100.5	1102.0	1103.3	1104.7	1105.7	1106.4	1107.1	1107.9	1108.5	1109.5
142.5°	1129.9	1131.2	1132.7	1134.0	1135.4	1136.4	1137.1	1137.8	1138.5	1139.2	1140.0
145°	1172.8	1174.4	1176.0	1177.6	1179.2	1180.3	1180.7	1181.2	1181.6	1182.1	1182.5
147.5°	1213.2	1214.2	1215.3	1216.3	1217.4	1218.2	1218.6	1219.1	1219.5	1219.9	1220.5
150°	1238.1	1238.7	1239.4	1240.1	1240.8	1241.4	1241.8	1242.2	1242.8	1243.2	1243.7
152.5°	1260.4	1260.7	1261.1	1261.3	1261.7	1261.9	1262.2	1262.6	1262.8	1263.1	1263.9
155°	1291.9	1291.5	1290.9	1290.5	1290.0	1289.9	1290.1	1290.4	1290.7	1290.8	1292.0
157.5°	1316.3	1316.3	1316.3	1316.2	1316.2	1316.0	1315.8	1315.5	1315.4	1315.1	1316.5
160°	1331.2	1331.1	1330.8	1330.6	1330.3	1330.1	1329.9	1329.6	1329.5	1329.2	1330.6
162.5°	1345.3	1344.8	1344.2	1343.5	1342.9	1342.6	1342.3	1342.1	1341.8	1341.6	1343.2
165°	1362.4	1361.6	1360.9	1360.3	1359.6	1359.1	1358.9	1358.6	1358.4	1358.2	1360.0
167.5°	1375.6	1374.7	1373.8	1372.9	1371.9	1371.5	1371.5	1371.5	1371.5	1371.5	1373.3
170°	1383.0	1382.2	1381.3	1380.3	1379.4	1378.9	1378.9	1378.9	1378.9	1378.9	1380.7
172.5°	1388.0	1387.0	1385.8	1384.7	1383.6	1383.1	1383.3	1383.5	1383.7	1383.8	1385.7
175°	1394.5	1393.3	1392.1	1391.0	1389.8	1389.4	1389.6	1389.8	1390.1	1390.3	1392.0
177.5°	1396.2	1395.2	1394.3	1393.4	1392.4	1392.0	1392.2	1392.4	1392.6	1392.8	1394.3
180°	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5



TEST NUMBER: P332357-940

CATALOG NUMBER: S123RDIP-S1000D1195U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5
2.5°	1490.5	1492.9	1495.2	1496.2	1495.8	1495.4	1495.0	1494.5
5°	1480.7	1483.1	1485.5	1486.5	1485.9	1485.4	1484.9	1484.3
7.5°	1459.8	1461.2	1462.5	1462.8	1461.8	1460.9	1460.0	1459.0
10°	1441.2	1441.5	1441.7	1441.2	1439.8	1438.4	1437.1	1435.7
12.5°	1417.9	1417.8	1417.6	1416.8	1415.2	1413.6	1412.1	1410.5
15°	1377.2	1375.9	1374.6	1372.9	1371.0	1369.1	1367.3	1365.4
17.5°	1328.6	1325.7	1322.9	1320.0	1317.2	1314.4	1311.6	1308.8
20°	1295.2	1291.7	1288.3	1284.9	1281.7	1278.4	1275.1	1271.9
22.5°	1259.5	1255.2	1250.8	1247.1	1244.1	1241.1	1238.1	1235.0
25°	1201.1	1195.4	1189.8	1185.4	1182.5	1179.6	1176.6	1173.6
27.5°	1137.5	1129.6	1121.7	1115.5	1111.0	1106.4	1101.9	1097.4
30°	1092.2	1083.0	1073.8	1067.1	1062.7	1058.5	1054.1	1049.8
32.5°	1047.7	1037.7	1027.6	1020.4	1015.8	1011.3	1006.7	1002.2
35°	981.7	970.1	958.5	950.3	945.5	940.6	935.8	930.9
37.5°	910.9	897.7	884.6	874.9	869.0	863.0	857.0	851.0
40°	861.6	847.6	833.5	823.4	817.2	811.0	804.8	798.6
42.5°	814.3	799.0	783.6	773.2	767.7	762.1	756.5	751.0
45°	744.8	729.4	714.0	703.1	696.6	690.2	683.7	677.3
47.5°	672.9	656.2	639.4	628.2	622.4	616.7	610.9	605.1
50°	624.4	607.6	590.9	579.4	573.3	567.0	560.9	554.6
52.5°	577.5	560.1	542.7	531.2	525.7	520.1	514.6	509.0
55°	507.6	492.0	476.3	465.7	460.4	455.0	449.6	444.2
57.5°	438.9	424.1	409.4	399.7	395.1	390.5	385.9	381.3
60°	395.7	381.1	366.5	357.0	352.4	347.8	343.2	338.6
62.5°	352.7	339.0	325.3	316.0	311.3	306.5	301.7	296.9
65°	291.6	278.3	265.1	257.0	254.0	251.1	248.2	245.1
67.5°	233.2	223.3	213.5	206.9	203.8	200.5	197.3	194.2
70°	197.2	187.7	178.3	172.1	169.1	166.1	163.2	160.2
72.5°	164.7	156.9	149.3	144.8	143.6	142.3	141.1	139.8
75°	123.2	120.6	117.9	116.3	115.7	115.1	114.6	114.0
77.5°	93.0	91.5	90.1	89.1	88.5	88.0	87.5	86.9
80°	74.8	74.0	73.2	72.6	72.1	71.5	70.9	70.4
82.5°	57.3	56.5	55.7	55.3	55.2	55.1	54.9	54.8
85°	32.9	32.4	31.8	31.6	31.6	31.6	31.6	31.6
87.5°	17.6	17.5	17.5	17.4	17.3	17.1	17.0	16.9
90°	26.7	27.6	28.5	29.2	29.7	30.1	30.6	31.1
92.5°	29.4	30.9	32.5	33.3	33.5	33.9	34.2	34.4
95°	35.3	36.9	38.5	39.3	39.3	39.3	39.3	39.3
97.5°	37.0	38.9	40.8	41.7	42.0	42.3	42.4	42.7
100°	37.9	39.7	41.6	42.6	42.8	43.1	43.2	43.5
102.5°	56.7	51.0	45.3	42.7	43.1	43.5	44.0	44.3
105°	145.3	104.6	63.8	43.8	44.2	44.7	45.1	45.6
107.5°	356.1	326.2	296.3	266.0	235.3	204.6	173.9	143.2
110°	452.0	444.4	436.8	416.6	383.7	350.7	317.8	284.9



TEST NUMBER: P332357-940

CATALOG NUMBER: S123RDIP-S1000D1195U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	519.7	519.9	520.0	516.6	509.6	502.7	495.7	488.7
115°	599.2	601.5	603.9	605.5	606.4	607.3	608.2	609.1
117.5°	671.3	673.2	674.9	676.0	676.2	676.4	676.5	676.7
120°	718.5	720.3	722.2	723.1	723.1	723.1	723.1	723.1
122.5°	764.6	766.0	767.2	767.9	768.1	768.3	768.6	768.7
125°	829.7	830.2	830.6	831.1	831.5	832.1	832.5	832.9
127.5°	894.9	895.6	896.3	896.5	896.1	895.6	895.2	894.7
130°	934.2	935.1	936.1	936.3	935.9	935.4	935.0	934.5
132.5°	971.5	972.5	973.4	973.5	972.9	972.2	971.6	970.9
135°	1028.1	1028.8	1029.5	1029.5	1028.8	1028.1	1027.3	1026.7
137.5°	1078.4	1079.5	1080.6	1080.9	1080.5	1080.0	1079.6	1079.1
140°	1110.4	1111.3	1112.2	1112.4	1112.0	1111.5	1111.1	1110.6
142.5°	1140.7	1141.4	1142.1	1142.2	1141.6	1140.9	1140.2	1139.6
145°	1183.0	1183.5	1183.9	1184.1	1184.1	1184.1	1184.1	1184.1
147.5°	1220.9	1221.4	1221.8	1221.6	1220.5	1219.4	1218.3	1217.3
150°	1244.1	1244.6	1245.0	1244.9	1244.2	1243.6	1242.9	1242.2
152.5°	1264.7	1265.6	1266.4	1266.3	1265.2	1264.2	1263.1	1262.0
155°	1293.2	1294.3	1295.5	1295.3	1294.0	1292.6	1291.2	1289.9
157.5°	1317.9	1319.2	1320.6	1320.4	1318.7	1316.8	1315.0	1313.2
160°	1331.9	1333.3	1334.7	1334.6	1333.0	1331.4	1329.7	1328.1
162.5°	1344.8	1346.3	1347.9	1347.9	1346.5	1345.1	1343.6	1342.2
165°	1361.9	1363.7	1365.6	1365.7	1364.1	1362.4	1360.8	1359.2
167.5°	1375.1	1377.0	1378.9	1378.9	1377.0	1375.1	1373.3	1371.5
170°	1382.6	1384.5	1386.3	1386.3	1384.5	1382.6	1380.7	1378.9
172.5°	1387.6	1389.4	1391.2	1391.2	1389.1	1387.1	1385.1	1383.0
175°	1393.6	1395.2	1396.8	1396.6	1394.8	1392.9	1391.2	1389.3
177.5°	1395.7	1397.2	1398.6	1398.5	1396.7	1394.8	1392.9	1391.2
180°	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5

(END OF REPORT)