

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332525-830

Luminaire Tested: **S124DIP-S350D1035U830-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332525-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIP-S350D1035U830-4F0-1E-UDD-F4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4914.7 lumens
Efficiency: N/A
Efficacy: 131.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 37.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332525-830

CATALOG NUMBER: S124DIP-S350D1035U830-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332525-830

CATALOG NUMBER: S124DIP-S350D1035U830-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	37	37	37	29
1	93	89	85	82	83	80	77	74	63	61	59	47	46	44	33	32	31	24
2	85	78	72	67	76	70	65	60	55	51	48	41	39	37	29	27	26	20
3	77	68	61	55	69	61	55	50	48	44	41	36	34	31	25	24	22	17
4	71	60	53	47	63	54	48	43	43	38	35	32	29	27	23	21	19	15
5	65	53	46	40	58	48	41	36	38	33	30	29	26	23	20	18	17	13
6	59	48	40	34	53	43	36	31	34	29	26	26	23	20	18	16	15	11
7	55	43	35	30	49	39	32	27	31	26	23	24	20	18	17	15	13	10
8	51	39	31	26	45	35	29	24	28	23	20	22	18	16	15	13	12	9
9	47	35	28	23	42	32	26	21	26	21	18	20	16	14	14	12	10	8
10	44	32	25	21	39	29	23	19	24	19	16	18	15	13	13	11	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4495	4495	4495
5°	4508	4454	4486
10°	4480	4418	4440
15°	4425	4355	4367
20°	4354	4277	4281
25°	4272	4188	4177
30°	4172	4084	4047
35°	4066	3975	3921
40°	3958	3851	3780
45°	3846	3729	3658
50°	3720	3620	3508
55°	3586	3478	3365
60°	3450	3321	3219
65°	3299	3171	3043
70°	3127	2969	2854
75°	2866	2729	2658
80°	2552	2450	2385
85°	2232	2149	2103



TEST NUMBER: P332525-830

CATALOG NUMBER: S124DIP-S350D1035U830-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.4	1.1
10°-20°	147.7	3.0
20°-30°	217.4	4.4
30°-40°	252.8	5.1
40°-50°	252.8	5.1
50°-60°	221.1	4.5
60°-70°	164.2	3.3
70°-80°	93.3	1.9
80°-90°	29.6	0.6
90°-100°	345.9	7.0
100°-110°	720.0	14.6
110°-120°	644.9	13.1
120°-130°	542.4	11.0
130°-140°	452.3	9.2
140°-150°	345.5	7.0
150°-160°	242.9	4.9
160°-170°	142.9	2.9
170°-180°	46.5	0.9
0°-30°	417.6	8.5
0°-40°	670.4	13.6
0°-60°	1144.3	23.3
0°-90°	1431.4	29.1
90°-120°	1710.8	34.8
90°-150°	3051.1	62.1
90°-180°	3483.0	70.9
0°-180°	4914.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	557	557	557	557	557	
5°	556	554	550	554	554	53
15°	530	528	521	524	522	149
25°	480	476	470	471	469	221
35°	413	409	403	400	398	258
45°	337	333	327	322	320	260
55°	255	253	247	242	239	228
65°	173	170	166	162	159	171
75°	92	90	88	86	85	98
85°	24	24	23	23	23	27
90°	1	8	17	19	20	3
95°	31	98	767	380	230	35
105°	110	159	617	1329	1324	117
115°	194	243	550	1058	1271	192
125°	270	321	548	900	1014	240
135°	321	382	543	799	907	248
145°	370	423	540	674	741	232
155°	421	454	525	595	620	194
165°	458	472	503	533	541	129
175°	478	479	483	489	487	45
180°	479	479	479	479	479	



TEST NUMBER: P332525-830

CATALOG NUMBER: S124DIP-S350D1035U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8
2.5°	558.2	558.0	557.7	557.5	557.2	556.7	555.8	555.0	554.1	553.2	554.0
5°	556.3	555.9	555.5	555.2	554.8	554.0	552.9	551.9	550.7	549.6	550.7
7.5°	551.2	550.7	550.4	550.0	549.6	548.7	547.5	546.4	545.2	543.9	544.8
10°	546.5	546.1	545.7	545.4	545.0	544.1	542.8	541.5	540.3	538.9	539.7
12.5°	540.5	540.1	539.7	539.2	538.9	538.0	536.6	535.3	533.9	532.5	533.4
15°	529.5	529.1	528.8	528.4	528.0	527.1	525.6	524.1	522.5	521.1	521.7
17.5°	516.4	515.9	515.5	515.0	514.4	513.5	512.1	510.7	509.3	507.8	508.2
20°	506.8	506.3	505.9	505.3	504.8	503.9	502.4	500.9	499.4	497.9	498.2
22.5°	496.4	495.8	495.1	494.5	493.8	492.8	491.3	489.8	488.3	486.8	487.4
25°	479.6	478.9	478.2	477.5	476.8	475.8	474.4	473.0	471.6	470.2	470.3
27.5°	460.3	459.6	458.9	458.2	457.5	456.5	455.2	453.9	452.6	451.3	451.1
30°	447.5	446.7	445.9	445.1	444.3	443.3	442.0	440.6	439.4	438.1	437.7
32.5°	433.9	433.2	432.4	431.8	431.0	430.0	428.7	427.3	425.9	424.5	424.0
35°	412.6	412.0	411.3	410.6	409.9	408.9	407.5	406.0	404.7	403.3	402.7
37.5°	390.3	389.6	389.0	388.4	387.8	386.7	385.2	383.7	382.2	380.7	379.9
40°	375.6	374.8	374.1	373.2	372.5	371.4	369.9	368.3	366.8	365.4	364.4
42.5°	360.0	359.5	359.0	358.5	358.1	356.9	355.3	353.6	352.0	350.4	349.2
45°	336.9	336.1	335.5	334.8	334.0	332.9	331.3	329.7	328.2	326.6	325.5
47.5°	312.6	312.2	311.7	311.2	310.8	309.8	308.3	306.8	305.4	303.9	302.7
50°	296.2	295.9	295.5	295.0	294.6	293.8	292.4	291.0	289.5	288.2	286.8
52.5°	280.2	279.7	279.2	278.7	278.2	277.3	275.8	274.4	272.9	271.5	270.2
55°	254.8	254.5	254.1	253.8	253.5	252.7	251.3	250.0	248.5	247.1	246.0
57.5°	230.5	230.2	229.8	229.5	229.1	228.3	226.9	225.6	224.1	222.8	221.7
60°	213.7	213.2	212.7	212.2	211.7	210.8	209.5	208.2	207.0	205.7	204.8
62.5°	197.3	196.9	196.4	196.0	195.6	194.7	193.3	192.0	190.6	189.3	188.4
65°	172.7	172.2	171.6	171.2	170.7	169.9	168.9	168.0	166.9	166.0	164.9
67.5°	147.9	147.4	146.9	146.5	146.0	145.3	144.4	143.5	142.5	141.5	140.5
70°	132.5	131.8	131.1	130.4	129.7	128.9	128.2	127.4	126.6	125.8	125.0
72.5°	116.1	115.4	114.7	114.0	113.3	112.6	112.0	111.4	110.7	110.1	109.4
75°	91.9	91.4	91.0	90.4	89.9	89.4	89.0	88.4	87.9	87.5	87.1
77.5°	68.8	68.6	68.3	68.1	68.0	67.6	67.2	66.7	66.3	65.9	65.7
80°	54.9	54.6	54.3	54.0	53.7	53.4	53.3	53.1	52.9	52.7	52.4
82.5°	41.3	41.2	41.0	40.9	40.7	40.6	40.6	40.6	40.5	40.5	40.4
85°	24.1	24.1	24.1	24.1	24.1	24.0	23.8	23.6	23.4	23.2	23.2
87.5°	9.4	9.8	10.3	10.4	10.5	10.4	11.4	11.4	11.7	12.0	11.8
90°	0.9	2.8	5.7	6.6	7.5	7.5	13.2	13.2	15.1	17.0	16.0
92.5°	10.7	15.6	24.5	35.9	49.7	69.3	117.1	190.1	261.2	298.5	248.6
95°	31.0	33.8	43.3	55.5	78.1	117.6	199.4	353.8	578.7	766.9	788.5
97.5°	55.7	55.7	63.8	75.1	94.4	127.6	190.7	318.0	541.6	807.7	990.6
100°	71.5	71.5	78.1	89.4	107.3	137.4	192.9	299.3	491.2	756.5	997.4
102.5°	86.5	88.0	93.9	104.4	121.6	150.1	200.4	294.0	457.3	692.6	940.9
105°	110.1	112.9	117.6	128.9	145.8	173.1	218.3	296.4	428.1	617.3	838.4
107.5°	136.1	138.0	142.6	154.7	170.9	197.7	239.2	310.3	422.8	575.1	755.5
110°	153.4	155.2	159.9	171.3	188.2	213.6	255.0	320.8	424.3	560.8	714.2



TEST NUMBER: P332525-830

CATALOG NUMBER: S124DIP-S350D1035U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	169.9	171.8	177.3	187.8	204.7	230.2	270.0	332.2	428.9	554.0	690.9
115°	193.9	196.6	203.2	212.6	230.5	255.9	293.6	350.1	437.5	550.4	669.0
117.5°	218.7	221.3	227.2	237.5	254.2	280.6	316.3	368.3	446.8	549.5	659.2
120°	235.3	237.1	243.7	254.0	270.0	296.4	332.2	381.1	453.6	549.5	653.9
122.5°	250.3	252.1	258.7	268.3	285.9	311.4	347.2	393.1	460.3	548.7	647.9
125°	270.0	273.8	279.5	289.8	307.6	334.0	367.9	411.2	470.5	547.6	638.0
127.5°	287.6	290.6	297.4	309.2	327.8	354.4	387.1	426.8	478.5	545.5	624.6
130°	297.4	301.1	308.6	322.7	340.6	367.9	399.9	436.6	484.6	544.8	616.3
132.5°	307.1	310.1	319.9	333.3	352.7	378.4	410.5	446.4	489.8	544.0	608.8
135°	320.8	324.6	334.0	350.1	369.8	394.3	425.3	459.2	497.8	542.9	597.5
137.5°	334.6	338.2	348.6	363.7	384.3	407.6	436.6	468.3	502.5	542.7	587.7
140°	344.4	347.2	357.6	373.5	393.3	415.9	444.1	474.2	506.2	542.0	582.5
142.5°	355.0	357.8	367.3	382.6	401.6	423.4	450.9	478.7	509.3	542.0	578.0
145°	369.8	372.6	382.0	395.2	413.1	433.8	458.3	483.6	511.0	540.1	570.2
147.5°	386.5	387.5	395.8	409.3	424.1	442.8	465.8	488.0	511.9	536.7	563.3
150°	397.1	398.0	405.6	416.9	430.9	448.8	469.6	490.2	511.9	534.4	558.0
152.5°	406.9	407.1	414.6	425.1	437.7	454.1	472.6	491.7	510.4	530.7	552.0
155°	420.6	421.5	427.2	436.6	447.0	461.1	477.0	493.0	508.1	525.1	542.9
157.5°	433.9	433.9	439.2	446.6	455.6	466.7	480.2	493.0	505.7	519.2	533.7
160°	442.2	442.2	446.0	452.6	460.1	470.5	481.7	493.0	503.4	514.7	527.0
162.5°	449.8	449.0	452.0	457.9	464.7	472.8	483.2	493.0	501.1	510.2	520.9
165°	458.3	458.3	460.1	464.9	469.6	475.1	483.6	491.2	496.8	503.4	511.0
167.5°	466.7	465.8	466.7	470.3	473.0	477.2	483.4	488.9	492.3	496.6	501.9
170°	470.5	469.6	470.5	473.3	475.1	478.0	482.7	487.4	489.3	492.1	495.9
172.5°	474.2	473.3	473.4	475.5	476.6	478.7	481.9	485.9	486.3	487.6	490.6
175°	478.0	477.0	477.0	478.0	478.9	478.9	480.8	483.6	482.7	482.7	484.6
177.5°	479.7	478.9	478.2	478.9	478.9	478.9	479.7	481.2	479.7	479.7	480.4
180°	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9



TEST NUMBER: P332525-830

CATALOG NUMBER: S124DIP-S350D1035U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8
2.5°	554.8	555.6	556.4	556.8	556.7	556.6	556.5	556.4
5°	551.9	552.9	554.0	554.4	554.2	554.0	553.8	553.6
7.5°	545.6	546.6	547.4	547.8	547.7	547.5	547.4	547.3
10°	540.5	541.3	542.2	542.4	542.2	542.0	541.8	541.6
12.5°	534.2	535.1	536.0	536.3	536.0	535.7	535.5	535.2
15°	522.3	522.8	523.5	523.6	523.3	523.0	522.7	522.5
17.5°	508.6	509.0	509.3	509.4	509.3	509.1	508.9	508.7
20°	498.5	498.8	499.1	499.2	498.9	498.7	498.5	498.3
22.5°	487.9	488.4	489.0	489.1	488.7	488.3	488.0	487.7
25°	470.4	470.5	470.6	470.5	470.0	469.7	469.3	468.9
27.5°	450.8	450.6	450.3	450.0	449.5	449.0	448.5	448.0
30°	437.3	437.0	436.5	436.1	435.5	435.1	434.6	434.1
32.5°	423.6	423.1	422.6	422.2	421.7	421.1	420.7	420.2
35°	401.9	401.2	400.5	399.9	399.4	399.0	398.4	397.9
37.5°	379.2	378.4	377.7	377.0	376.4	375.7	375.0	374.4
40°	363.4	362.4	361.5	360.7	360.1	359.7	359.2	358.7
42.5°	348.1	346.9	345.8	345.1	344.7	344.4	344.0	343.7
45°	324.4	323.3	322.3	321.5	321.2	320.9	320.7	320.4
47.5°	301.4	300.2	299.0	298.0	297.3	296.5	295.8	295.0
50°	285.4	284.1	282.7	281.6	281.1	280.5	279.8	279.3
52.5°	269.0	267.8	266.6	265.5	264.8	264.0	263.3	262.5
55°	244.8	243.6	242.4	241.5	240.9	240.3	239.7	239.1
57.5°	220.6	219.4	218.3	217.4	216.9	216.3	215.7	215.1
60°	203.9	203.0	202.1	201.4	201.0	200.4	199.9	199.4
62.5°	187.7	186.8	186.0	185.3	184.8	184.4	183.9	183.3
65°	164.0	163.0	162.0	161.3	160.8	160.2	159.8	159.3
67.5°	139.6	138.6	137.7	137.1	137.0	136.9	136.8	136.6
70°	124.2	123.5	122.6	122.1	121.8	121.5	121.2	120.9
72.5°	108.9	108.2	107.5	107.1	106.8	106.5	106.2	105.9
75°	86.6	86.2	85.9	85.6	85.5	85.4	85.3	85.2
77.5°	65.6	65.5	65.4	65.2	64.9	64.7	64.4	64.2
80°	52.2	52.0	51.8	51.7	51.6	51.5	51.4	51.3
82.5°	40.2	40.2	40.1	40.0	39.9	39.7	39.6	39.5
85°	23.2	23.2	23.2	23.2	23.1	23.0	22.8	22.7
87.5°	12.0	12.2	12.3	12.3	12.5	12.7	12.5	12.5
90°	17.0	17.9	18.9	18.9	19.8	20.7	19.8	19.8
92.5°	184.8	139.1	110.7	91.8	80.8	75.7	72.5	72.5
95°	697.2	551.4	425.3	334.0	287.9	258.7	241.9	229.6
97.5°	1030.2	975.9	883.9	785.7	718.1	661.5	633.3	613.7
100°	1134.8	1153.6	1107.5	1037.8	956.0	898.6	870.3	862.9
102.5°	1129.5	1222.9	1236.2	1207.2	1157.0	1115.4	1085.7	1079.7
105°	1053.9	1216.6	1309.8	1348.4	1350.3	1342.7	1329.6	1323.9
107.5°	946.4	1119.7	1250.9	1334.8	1381.3	1402.8	1412.2	1414.7
110°	881.7	1044.4	1180.9	1284.4	1351.2	1390.7	1407.7	1416.2



TEST NUMBER: P332525-830

CATALOG NUMBER: S124DIP-S350D1035U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	834.2	978.2	1107.1	1210.6	1286.5	1334.3	1358.0	1371.7
115°	786.6	902.4	1012.5	1102.8	1177.1	1233.6	1263.7	1271.2
117.5°	763.3	859.1	945.7	1022.3	1085.7	1133.1	1163.6	1169.4
120°	752.7	840.3	915.6	982.3	1035.9	1077.4	1101.8	1112.2
122.5°	743.8	828.2	896.7	955.3	1000.6	1035.9	1056.7	1067.1
125°	728.3	809.2	874.1	925.9	963.6	990.8	1008.7	1014.4
127.5°	709.5	786.8	851.6	900.7	938.5	962.8	977.8	983.4
130°	694.5	768.7	832.7	882.6	921.1	944.7	959.8	965.4
132.5°	678.6	748.5	810.9	860.8	898.6	925.1	939.4	945.1
135°	656.8	717.9	775.3	822.4	860.1	886.4	901.4	907.1
137.5°	637.1	688.8	737.2	779.7	814.8	840.8	853.3	860.1
140°	625.8	670.0	712.3	751.8	784.8	805.5	818.6	826.1
142.5°	615.2	654.1	690.5	724.7	753.8	773.1	784.8	790.0
145°	600.3	632.4	660.5	686.9	710.4	726.4	735.8	740.6
147.5°	588.1	613.5	636.1	656.8	674.1	687.9	695.0	696.6
150°	580.6	602.2	621.0	638.0	653.0	665.2	670.9	671.8
152.5°	572.3	590.9	608.2	622.2	635.0	644.9	648.3	649.2
155°	559.9	575.0	589.0	600.3	609.7	617.3	620.1	620.1
157.5°	546.5	559.1	571.0	580.0	587.1	592.8	594.5	594.5
160°	538.2	548.6	558.9	566.5	572.1	577.8	578.7	578.7
162.5°	529.9	538.8	546.9	553.6	557.8	563.5	564.4	563.6
165°	518.5	524.1	530.7	535.4	539.1	542.9	542.0	541.0
167.5°	507.4	511.7	517.0	519.8	521.7	524.1	524.0	523.2
170°	500.6	503.4	507.2	510.0	511.9	512.8	511.9	511.9
172.5°	494.6	496.6	498.9	501.0	502.1	503.0	502.1	500.6
175°	486.4	487.4	489.3	489.3	489.3	491.2	489.3	487.4
177.5°	481.2	481.9	481.9	482.7	481.9	482.7	481.2	479.7
180°	478.9	478.9	478.9	478.9	478.9	478.9	478.9	478.9

(END OF REPORT)