

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332498-830

Luminaire Tested: **S124DIP-S350D365U830-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332498-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIP-S350D365U830-4F0-1E-UDD-F4  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2662.9 lumens  
Efficiency: N/A  
Efficacy: 131.2 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 20.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332498-830

CATALOG NUMBER: S124DIP-S350D365U830-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P332498-830

CATALOG NUMBER: S124DIP-S350D365U830-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	60	60	60	54
1	99	94	90	87	91	87	84	81	75	72	70	63	61	60	53	51	50	45
2	90	82	76	71	83	76	71	66	66	61	58	56	53	50	46	44	42	38
3	82	72	65	59	76	67	61	56	58	53	49	49	45	42	41	38	36	32
4	75	64	56	50	69	60	53	47	51	46	42	44	40	36	37	34	31	27
5	69	57	49	43	63	53	46	40	46	40	36	39	35	31	33	30	27	24
6	63	51	43	37	59	48	41	35	41	36	31	36	31	28	30	26	24	21
7	59	46	38	33	54	43	36	31	38	32	28	32	28	24	27	24	21	19
8	54	42	34	29	50	39	32	27	34	29	25	30	25	22	25	22	19	17
9	51	38	31	26	47	36	29	24	31	26	22	27	23	20	23	20	17	15
10	47	35	28	23	44	33	26	22	29	24	20	25	21	18	22	18	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	4495	4495	4495
5°	4508	4454	4486
10°	4480	4418	4440
15°	4425	4355	4367
20°	4354	4277	4281
25°	4272	4188	4177
30°	4172	4084	4047
35°	4066	3975	3921
40°	3958	3851	3780
45°	3846	3729	3658
50°	3720	3620	3508
55°	3586	3478	3365
60°	3450	3321	3219
65°	3299	3171	3043
70°	3127	2969	2854
75°	2866	2729	2658
80°	2552	2450	2385
85°	2232	2149	2103



TEST NUMBER: P332498-830

CATALOG NUMBER: S124DIP-S350D365U830-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	52.4	2.0
10°-20°	147.7	5.5
20°-30°	217.4	8.2
30°-40°	252.8	9.5
40°-50°	252.8	9.5
50°-60°	221.1	8.3
60°-70°	164.2	6.2
70°-80°	93.3	3.5
80°-90°	27.9	1.0
90°-100°	122.5	4.6
100°-110°	254.9	9.6
110°-120°	228.3	8.6
120°-130°	192.0	7.2
130°-140°	160.1	6.0
140°-150°	122.3	4.6
150°-160°	86.0	3.2
160°-170°	50.6	1.9
170°-180°	16.5	0.6
0°-30°	417.6	15.7
0°-40°	670.4	25.2
0°-60°	1144.3	43.0
0°-90°	1429.7	53.7
90°-120°	605.7	22.7
90°-150°	1080.2	40.6
90°-180°	1233.0	46.3
0°-180°	2662.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	557	557	557	557	557	
5°	556	554	550	554	554	53
15°	530	528	521	524	522	149
25°	480	476	470	471	469	221
35°	413	409	403	400	398	258
45°	337	333	327	322	320	260
55°	255	253	247	242	239	228
65°	173	170	166	162	159	171
75°	92	90	88	86	85	98
85°	24	24	23	23	23	27
90°	0	3	6	7	7	2
95°	11	35	272	134	81	12
105°	39	56	218	471	469	42
115°	69	86	195	374	450	68
125°	96	114	194	319	359	85
135°	114	135	192	283	321	88
145°	131	150	191	238	262	82
155°	149	161	186	210	220	69
165°	162	167	178	189	192	46
175°	169	170	171	173	173	16
180°	170	170	170	170	170	



TEST NUMBER: P332498-830

CATALOG NUMBER: S124DIP-S350D365U830-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8
2.5°	558.2	558.0	557.7	557.5	557.2	556.7	555.8	555.0	554.1	553.2	554.0
5°	556.3	555.9	555.5	555.2	554.8	554.0	552.9	551.9	550.7	549.6	550.7
7.5°	551.2	550.7	550.4	550.0	549.6	548.7	547.5	546.4	545.2	543.9	544.8
10°	546.5	546.1	545.7	545.4	545.0	544.1	542.8	541.5	540.3	538.9	539.7
12.5°	540.5	540.1	539.7	539.2	538.9	538.0	536.6	535.3	533.9	532.5	533.4
15°	529.5	529.1	528.8	528.4	528.0	527.1	525.6	524.1	522.5	521.1	521.7
17.5°	516.4	515.9	515.5	515.0	514.4	513.5	512.1	510.7	509.3	507.8	508.2
20°	506.8	506.3	505.9	505.3	504.8	503.9	502.4	500.9	499.4	497.9	498.2
22.5°	496.4	495.8	495.1	494.5	493.8	492.8	491.3	489.8	488.3	486.8	487.4
25°	479.6	478.9	478.2	477.5	476.8	475.8	474.4	473.0	471.6	470.2	470.3
27.5°	460.3	459.6	458.9	458.2	457.5	456.5	455.2	453.9	452.6	451.3	451.1
30°	447.5	446.7	445.9	445.1	444.3	443.3	442.0	440.6	439.4	438.1	437.7
32.5°	433.9	433.2	432.4	431.8	431.0	430.0	428.7	427.3	425.9	424.5	424.0
35°	412.6	412.0	411.3	410.6	409.9	408.9	407.5	406.0	404.7	403.3	402.7
37.5°	390.3	389.6	389.0	388.4	387.8	386.7	385.2	383.7	382.2	380.7	379.9
40°	375.6	374.8	374.1	373.2	372.5	371.4	369.9	368.3	366.8	365.4	364.4
42.5°	360.0	359.5	359.0	358.5	358.1	356.9	355.3	353.6	352.0	350.4	349.2
45°	336.9	336.1	335.5	334.8	334.0	332.9	331.3	329.7	328.2	326.6	325.5
47.5°	312.6	312.2	311.7	311.2	310.8	309.8	308.3	306.8	305.4	303.9	302.7
50°	296.2	295.9	295.5	295.0	294.6	293.8	292.4	291.0	289.5	288.2	286.8
52.5°	280.2	279.7	279.2	278.7	278.2	277.3	275.8	274.4	272.9	271.5	270.2
55°	254.8	254.5	254.1	253.8	253.5	252.7	251.3	250.0	248.5	247.1	246.0
57.5°	230.5	230.2	229.8	229.5	229.1	228.3	226.9	225.6	224.1	222.8	221.7
60°	213.7	213.2	212.7	212.2	211.7	210.8	209.5	208.2	207.0	205.7	204.8
62.5°	197.3	196.9	196.4	196.0	195.6	194.7	193.3	192.0	190.6	189.3	188.4
65°	172.7	172.2	171.6	171.2	170.7	169.9	168.9	168.0	166.9	166.0	164.9
67.5°	147.9	147.4	146.9	146.5	146.0	145.3	144.4	143.5	142.5	141.5	140.5
70°	132.5	131.8	131.1	130.4	129.7	128.9	128.2	127.4	126.6	125.8	125.0
72.5°	116.1	115.4	114.7	114.0	113.3	112.6	112.0	111.4	110.7	110.1	109.4
75°	91.9	91.4	91.0	90.4	89.9	89.4	89.0	88.4	87.9	87.5	87.1
77.5°	68.8	68.6	68.3	68.1	68.0	67.6	67.2	66.7	66.3	65.9	65.7
80°	54.9	54.6	54.3	54.0	53.7	53.4	53.3	53.1	52.9	52.7	52.4
82.5°	41.3	41.2	41.0	40.9	40.7	40.6	40.6	40.6	40.5	40.5	40.4
85°	24.1	24.1	24.1	24.1	24.1	24.0	23.8	23.6	23.4	23.2	23.2
87.5°	9.3	9.4	9.5	9.5	9.5	9.4	9.7	9.6	9.7	9.8	9.7
90°	0.4	1.0	2.0	2.4	2.6	2.6	4.6	4.6	5.4	6.0	5.7
92.5°	3.8	5.6	8.7	12.7	17.6	24.5	41.5	67.3	92.5	105.7	88.0
95°	11.0	12.0	15.4	19.7	27.6	41.7	70.6	125.3	204.9	271.5	279.2
97.5°	19.7	19.7	22.6	26.6	33.5	45.1	67.5	112.6	191.7	286.0	350.7
100°	25.4	25.4	27.6	31.7	38.0	48.6	68.3	105.9	173.9	267.9	353.1
102.5°	30.6	31.2	33.3	36.9	43.1	53.2	71.0	104.1	161.9	245.2	333.1
105°	39.0	40.0	41.7	45.6	51.7	61.3	77.3	104.9	151.6	218.5	296.8
107.5°	48.2	48.8	50.5	54.8	60.5	70.0	84.6	109.9	149.7	203.6	267.5
110°	54.3	55.0	56.6	60.6	66.6	75.6	90.3	113.6	150.2	198.5	252.9



TEST NUMBER: P332498-830

CATALOG NUMBER: S124DIP-S350D365U830-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	60.1	60.8	62.8	66.4	72.5	81.4	95.6	117.6	151.8	196.1	244.6
115°	68.6	69.7	71.9	75.3	81.6	90.6	104.0	123.9	154.9	194.9	236.9
117.5°	77.4	78.3	80.4	84.1	90.0	99.3	112.0	130.4	158.2	194.5	233.4
120°	83.3	84.0	86.2	89.9	95.6	104.9	117.6	134.9	160.6	194.5	231.5
122.5°	88.6	89.3	91.6	95.0	101.2	110.3	122.9	139.2	163.0	194.3	229.4
125°	95.6	96.9	99.0	102.6	109.0	118.3	130.3	145.5	166.5	193.9	225.8
127.5°	101.8	102.8	105.3	109.4	116.0	125.5	137.0	151.1	169.5	193.1	221.1
130°	105.3	106.6	109.2	114.2	120.6	130.3	141.6	154.6	171.5	192.8	218.2
132.5°	108.8	109.8	113.3	118.0	124.9	133.9	145.3	158.1	173.4	192.7	215.6
135°	113.6	114.9	118.3	123.9	130.9	139.6	150.5	162.6	176.3	192.2	211.5
137.5°	118.5	119.7	123.4	128.8	136.0	144.3	154.6	165.8	177.9	192.2	208.1
140°	122.0	122.9	126.6	132.2	139.2	147.2	157.2	167.9	179.2	191.9	206.2
142.5°	125.6	126.7	130.1	135.4	142.1	149.9	159.7	169.5	180.3	191.9	204.6
145°	130.9	132.0	135.3	139.9	146.3	153.5	162.2	171.3	180.9	191.2	201.9
147.5°	136.9	137.1	140.2	144.9	150.1	156.7	164.9	172.8	181.3	190.0	199.4
150°	140.5	140.9	143.5	147.6	152.6	158.9	166.3	173.5	181.3	189.2	197.6
152.5°	144.0	144.1	146.8	150.5	155.0	160.8	167.3	174.1	180.7	187.8	195.4
155°	148.9	149.2	151.3	154.6	158.3	163.2	168.9	174.6	179.9	185.9	192.2
157.5°	153.6	153.6	155.5	158.1	161.3	165.2	170.0	174.6	179.0	183.8	189.0
160°	156.6	156.6	157.9	160.2	162.9	166.5	170.6	174.6	178.2	182.2	186.5
162.5°	159.2	159.0	160.0	162.1	164.5	167.4	171.1	174.6	177.4	180.6	184.5
165°	162.2	162.2	162.9	164.6	166.3	168.2	171.3	173.9	175.9	178.2	180.9
167.5°	165.2	164.9	165.2	166.5	167.4	169.0	171.2	173.1	174.3	175.8	177.7
170°	166.5	166.3	166.5	167.6	168.2	169.2	170.9	172.6	173.2	174.2	175.6
172.5°	167.9	167.6	167.6	168.3	168.7	169.5	170.6	172.0	172.2	172.6	173.7
175°	169.2	168.9	168.9	169.2	169.6	169.6	170.2	171.3	170.9	170.9	171.5
177.5°	169.8	169.6	169.3	169.6	169.6	169.6	169.8	170.3	169.8	169.8	170.1
180°	169.6	169.6	169.6	169.6	169.6	169.6	169.6	169.6	169.6	169.6	169.6



TEST NUMBER: P332498-830

CATALOG NUMBER: S124DIP-S350D365U830-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8
2.5°	554.8	555.6	556.4	556.8	556.7	556.6	556.5	556.4
5°	551.9	552.9	554.0	554.4	554.2	554.0	553.8	553.6
7.5°	545.6	546.6	547.4	547.8	547.7	547.5	547.4	547.3
10°	540.5	541.3	542.2	542.4	542.2	542.0	541.8	541.6
12.5°	534.2	535.1	536.0	536.3	536.0	535.7	535.5	535.2
15°	522.3	522.8	523.5	523.6	523.3	523.0	522.7	522.5
17.5°	508.6	509.0	509.3	509.4	509.3	509.1	508.9	508.7
20°	498.5	498.8	499.1	499.2	498.9	498.7	498.5	498.3
22.5°	487.9	488.4	489.0	489.1	488.7	488.3	488.0	487.7
25°	470.4	470.5	470.6	470.5	470.0	469.7	469.3	468.9
27.5°	450.8	450.6	450.3	450.0	449.5	449.0	448.5	448.0
30°	437.3	437.0	436.5	436.1	435.5	435.1	434.6	434.1
32.5°	423.6	423.1	422.6	422.2	421.7	421.1	420.7	420.2
35°	401.9	401.2	400.5	399.9	399.4	399.0	398.4	397.9
37.5°	379.2	378.4	377.7	377.0	376.4	375.7	375.0	374.4
40°	363.4	362.4	361.5	360.7	360.1	359.7	359.2	358.7
42.5°	348.1	346.9	345.8	345.1	344.7	344.4	344.0	343.7
45°	324.4	323.3	322.3	321.5	321.2	320.9	320.7	320.4
47.5°	301.4	300.2	299.0	298.0	297.3	296.5	295.8	295.0
50°	285.4	284.1	282.7	281.6	281.1	280.5	279.8	279.3
52.5°	269.0	267.8	266.6	265.5	264.8	264.0	263.3	262.5
55°	244.8	243.6	242.4	241.5	240.9	240.3	239.7	239.1
57.5°	220.6	219.4	218.3	217.4	216.9	216.3	215.7	215.1
60°	203.9	203.0	202.1	201.4	201.0	200.4	199.9	199.4
62.5°	187.7	186.8	186.0	185.3	184.8	184.4	183.9	183.3
65°	164.0	163.0	162.0	161.3	160.8	160.2	159.8	159.3
67.5°	139.6	138.6	137.7	137.1	137.0	136.9	136.8	136.6
70°	124.2	123.5	122.6	122.1	121.8	121.5	121.2	120.9
72.5°	108.9	108.2	107.5	107.1	106.8	106.5	106.2	105.9
75°	86.6	86.2	85.9	85.6	85.5	85.4	85.3	85.2
77.5°	65.6	65.5	65.4	65.2	64.9	64.7	64.4	64.2
80°	52.2	52.0	51.8	51.7	51.6	51.5	51.4	51.3
82.5°	40.2	40.2	40.1	40.0	39.9	39.7	39.6	39.5
85°	23.2	23.2	23.2	23.2	23.1	23.0	22.8	22.7
87.5°	9.8	9.8	9.9	9.9	10.0	10.0	10.0	10.0
90°	6.0	6.3	6.7	6.7	7.0	7.4	7.0	7.0
92.5°	65.4	49.2	39.2	32.5	28.6	26.8	25.6	25.6
95°	246.9	195.2	150.5	118.3	101.9	91.6	85.6	81.2
97.5°	364.7	345.5	312.9	278.1	254.2	234.2	224.2	217.3
100°	401.7	408.4	392.1	367.4	338.5	318.1	308.1	305.5
102.5°	399.9	432.9	437.6	427.3	409.6	394.9	384.4	382.2
105°	373.1	430.7	463.7	477.4	478.1	475.3	470.7	468.7
107.5°	335.1	396.4	442.8	472.6	489.0	496.6	499.9	500.8
110°	312.2	369.8	418.1	454.7	478.3	492.4	498.3	501.3





TEST NUMBER: P332498-830

CATALOG NUMBER: S124DIP-S350D365U830-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	295.3	346.3	391.9	428.6	455.4	472.4	480.8	485.6
115°	278.5	319.4	358.4	390.4	416.7	436.7	447.4	450.1
117.5°	270.2	304.2	334.8	361.9	384.4	401.1	411.9	414.0
120°	266.5	297.5	324.1	347.8	366.7	381.4	390.1	393.8
122.5°	263.3	293.2	317.4	338.2	354.2	366.7	374.1	377.8
125°	257.9	286.4	309.4	327.8	341.1	350.8	357.1	359.1
127.5°	251.2	278.5	301.5	318.9	332.2	340.8	346.2	348.2
130°	245.8	272.2	294.8	312.5	326.1	334.4	339.8	341.8
132.5°	240.3	264.9	287.1	304.7	318.1	327.5	332.6	334.6
135°	232.5	254.2	274.5	291.2	304.4	313.8	319.1	321.1
137.5°	225.6	243.8	261.0	276.0	288.5	297.7	302.1	304.4
140°	221.5	237.1	252.1	266.2	277.9	285.1	289.8	292.5
142.5°	217.8	231.6	244.4	256.6	266.9	273.7	277.9	279.7
145°	212.5	223.9	233.8	243.2	251.5	257.1	260.5	262.1
147.5°	208.2	217.2	225.2	232.5	238.7	243.6	246.0	246.7
150°	205.6	213.2	219.9	225.8	231.2	235.5	237.5	237.8
152.5°	202.6	209.2	215.4	220.3	224.8	228.3	229.5	229.9
155°	198.2	203.5	208.5	212.5	215.8	218.5	219.5	219.5
157.5°	193.5	197.9	202.2	205.4	207.8	209.9	210.5	210.5
160°	190.6	194.2	197.8	200.6	202.6	204.5	204.9	204.9
162.5°	187.7	190.8	193.6	196.0	197.5	199.4	199.8	199.5
165°	183.5	185.6	187.8	189.5	190.9	192.2	191.9	191.5
167.5°	179.6	181.2	183.0	184.0	184.6	185.6	185.5	185.2
170°	177.2	178.2	179.6	180.6	181.3	181.5	181.3	181.3
172.5°	175.1	175.8	176.6	177.4	177.8	178.0	177.8	177.2
175°	172.2	172.6	173.2	173.2	173.2	173.9	173.2	172.6
177.5°	170.3	170.6	170.6	170.9	170.6	170.9	170.3	169.8
180°	169.6	169.6	169.6	169.6	169.6	169.6	169.6	169.6

(END OF REPORT)