

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332342-940

Luminaire Tested: **S123RDIP-S1000D805U940-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332342-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1000D805U940-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 805 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6393.7 lumens
Efficiency: N/A
Efficacy: 117.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 54.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332342-940

CATALOG NUMBER: S123RDIP-S1000D805U940-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332342-940

CATALOG NUMBER: S123RDIP-S1000D805U940-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55
1	100	95	92	88	92	89	86	83	77	74	72	65	64	62	55	54	53	48
2	91	84	78	73	85	78	73	69	68	64	61	58	55	53	49	47	45	41
3	84	75	67	62	78	70	63	58	60	56	52	52	48	46	44	42	39	36
4	77	66	59	53	71	62	55	50	54	49	45	47	43	40	40	37	34	31
5	71	59	52	46	66	56	49	44	49	43	39	42	38	35	36	33	30	27
6	65	54	46	40	61	50	43	38	44	39	34	38	34	31	33	30	27	24
7	61	49	41	35	56	46	39	34	40	35	31	35	31	27	30	27	24	22
8	56	44	37	31	52	42	35	30	37	31	27	32	28	25	28	24	22	20
9	53	41	33	28	49	38	32	27	34	28	25	30	25	22	26	22	20	18
10	49	37	30	25	46	35	29	24	31	26	22	28	23	20	24	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15259	15259	15259	15259
5°	18189	15324	13493	15324
10°	22710	15235	12191	15235
15°	26658	15081	11117	15081
20°	29751	14848	10204	14848
25°	29276	14602	9644	14602
30°	21044	14375	9066	14375
35°	14051	14082	8692	14082
40°	10352	13728	8304	13728
45°	8683	13108	7926	13108
50°	7661	12295	7398	12295
55°	6718	11365	6673	11365
60°	5983	10478	6114	10478
65°	5254	9521	5687	9521
70°	4126	8670	5196	8670
75°	3635	7573	4741	7573
80°	3161	6434	4668	6434
85°	2544	5175	4940	5175



TEST NUMBER: P332342-940

CATALOG NUMBER: S123RDIP-S1000D805U940-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	139.4	2.2
10°-20°	435.5	6.8
20°-30°	684.2	10.7
30°-40°	713.8	11.2
40°-50°	610.9	9.6
50°-60°	465.6	7.3
60°-70°	298.4	4.7
70°-80°	143.6	2.2
80°-90°	40.6	0.6
90°-100°	34.1	0.5
100°-110°	162.6	2.5
110°-120°	390.6	6.1
120°-130°	497.3	7.8
130°-140°	531.4	8.3
140°-150°	496.9	7.8
150°-160°	400.8	6.3
160°-170°	258.7	4.0
170°-180°	89.2	1.4
0°-30°	1259.1	19.7
0°-40°	1973.0	30.9
0°-60°	3049.5	47.7
0°-90°	3532.1	55.2
90°-120°	587.3	9.2
90°-150°	2112.9	33.0
90°-180°	2862.0	44.8
0°-180°	6393.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1418	1418	1418	1418	1418	
5°	1683	1418	1249	1418	1683	174
15°	2392	1353	998	1353	2392	678
25°	2465	1230	812	1230	2465	1059
35°	1069	1072	662	1072	1069	701
45°	570	861	521	861	570	449
55°	358	606	356	606	358	324
65°	206	374	223	374	206	203
75°	87	182	114	182	87	94
85°	21	42	40	42	21	24
90°	21	1	21	1	21	10
95°	26	42	26	42	26	22
105°	31	208	31	208	31	70
115°	410	390	410	390	410	379
125°	560	549	560	549	560	501
135°	691	684	691	684	691	533
145°	797	789	797	789	797	497
155°	868	869	868	869	868	400
165°	915	917	915	917	915	258
175°	935	938	935	938	935	89
180°	938	938	938	938	938	



TEST NUMBER: P332342-940

CATALOG NUMBER: S123RDIP-S1000D805U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1509.8	1511.7	1505.5	1504.5	1497.2	1495.2	1495.2	1485.1	1478.7	1470.5	1465.6
5°	1683.4	1693.1	1688.2	1677.3	1659.1	1654.8	1643.3	1625.1	1604.5	1579.0	1566.8
7.5°	1900.1	1913.3	1908.3	1891.4	1872.3	1856.9	1824.4	1794.2	1751.9	1714.7	1682.9
10°	2077.8	2063.9	2052.9	2036.6	2018.9	1990.4	1956.4	1909.7	1855.7	1813.2	1765.9
12.5°	2210.8	2208.5	2194.7	2177.8	2152.9	2125.8	2084.1	2027.2	1964.4	1903.1	1848.9
15°	2392.2	2395.8	2386.7	2369.1	2333.9	2286.0	2222.9	2199.2	2109.3	2042.6	1975.9
17.5°	2517.7	2516.9	2515.7	2491.4	2455.4	2421.3	2362.8	2300.5	2219.2	2125.1	2035.2
20°	2597.3	2591.2	2592.4	2565.1	2538.4	2498.9	2442.0	2351.5	2284.7	2176.1	2083.3
22.5°	2595.3	2594.1	2598.7	2589.3	2570.0	2539.8	2494.8	2418.5	2333.3	2223.7	2119.2
25°	2465.0	2460.1	2488.7	2496.5	2527.5	2532.9	2519.6	2477.7	2397.0	2284.1	2154.9
27.5°	2063.0	2060.3	2113.3	2179.5	2263.5	2328.8	2391.9	2422.4	2397.0	2316.2	2186.7
30°	1693.1	1750.2	1776.8	1872.7	1979.5	2106.9	2218.6	2324.8	2350.9	2315.7	2209.5
32.5°	1405.7	1455.5	1477.7	1560.0	1659.6	1808.8	1976.4	2126.7	2232.9	2259.9	2195.9
35°	1069.3	1069.9	1120.8	1157.3	1249.5	1403.0	1565.7	1767.1	1967.4	2119.1	2134.8
37.5°	853.2	856.2	887.1	923.4	992.6	1073.7	1216.9	1384.5	1615.8	1848.7	1985.2
40°	736.7	742.2	765.3	801.0	850.8	912.0	1023.8	1181.5	1374.5	1633.6	1845.4
42.5°	661.9	670.8	682.7	710.2	741.1	798.4	888.8	1010.7	1186.2	1431.2	1675.5
45°	570.4	575.2	584.4	597.1	625.0	665.1	725.8	807.7	953.3	1150.6	1395.1
47.5°	503.2	500.6	510.2	520.6	539.1	566.4	607.1	674.0	777.8	936.1	1143.5
50°	457.5	456.9	463.6	471.5	489.1	509.2	542.5	592.9	675.4	806.5	996.4
52.5°	414.8	417.1	421.9	431.7	444.4	460.6	490.5	526.8	597.7	710.9	869.2
55°	358.0	359.9	366.5	372.0	381.1	397.4	416.3	446.7	495.2	574.1	704.5
57.5°	310.0	309.2	315.6	316.9	327.2	340.5	355.1	378.7	413.8	472.5	560.4
60°	277.9	276.1	281.6	285.8	291.3	302.2	314.3	337.4	365.3	408.4	483.7
62.5°	248.8	248.0	252.0	256.2	260.7	270.6	280.9	298.5	320.7	357.0	416.7
65°	206.3	208.1	210.0	211.8	214.2	220.3	230.0	242.1	257.3	282.8	325.8
67.5°	162.1	164.0	164.6	168.4	173.5	177.4	183.2	194.0	204.6	226.1	250.7
70°	131.1	130.5	131.1	132.9	139.6	146.2	154.2	162.0	168.7	183.9	204.5
72.5°	112.6	111.6	113.2	113.5	116.7	118.6	123.6	131.0	139.6	149.9	164.7
75°	87.4	87.4	87.4	87.4	89.8	91.0	92.8	94.7	97.7	102.5	113.5
77.5°	64.6	64.6	65.5	66.2	66.6	67.3	68.5	70.3	71.3	73.9	78.6
80°	51.0	51.5	51.0	51.5	51.5	52.8	53.4	55.2	55.8	58.9	60.7
82.5°	38.3	38.0	38.3	39.0	39.0	40.2	40.3	41.6	41.7	43.3	45.1
85°	20.6	19.4	20.6	20.1	21.2	20.1	20.6	21.8	21.8	22.5	24.9
87.5°	9.0	10.0	8.9	9.4	9.3	9.6	9.5	9.5	10.3	9.6	9.7
90°	21.0	20.6	20.3	20.0	19.7	19.2	18.5	18.0	17.4	16.8	14.7
92.5°	23.2	22.9	22.7	22.6	22.4	21.8	20.8	19.8	18.8	17.8	16.3
95°	26.5	26.5	26.5	26.5	26.5	25.9	24.9	23.8	22.7	21.6	19.9
97.5°	28.7	28.5	28.4	28.3	28.1	27.4	26.1	25.0	23.7	22.5	33.6
100°	29.2	29.2	29.0	28.8	28.6	28.0	26.8	25.5	24.3	23.0	47.2
102.5°	29.9	29.5	29.2	29.0	28.7	30.5	34.3	38.2	42.0	45.8	72.2
105°	30.7	30.4	30.1	29.8	29.4	43.0	70.4	97.8	125.3	152.7	166.6
107.5°	96.3	117.0	137.7	158.4	179.0	199.4	219.5	239.6	259.8	279.8	277.6
110°	191.7	213.8	236.0	258.2	280.4	294.0	299.1	304.2	309.3	314.4	312.7



TEST NUMBER: P332342-940

CATALOG NUMBER: S123RDIP-S1000D805U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	329.0	333.6	338.2	343.0	347.6	349.9	349.8	349.7	349.6	349.6	347.9
115°	409.9	409.3	408.7	408.0	407.4	406.4	404.8	403.2	401.7	400.2	398.8
117.5°	455.4	455.2	455.1	455.0	454.9	454.1	453.0	451.7	450.5	449.2	448.5
120°	486.6	486.6	486.6	486.6	486.6	486.0	484.7	483.5	482.2	481.0	480.5
122.5°	517.3	517.2	517.0	516.9	516.7	516.3	515.4	514.5	513.7	512.8	512.2
125°	560.5	560.2	559.9	559.5	559.3	558.9	558.7	558.3	558.0	557.7	557.1
127.5°	602.1	602.4	602.7	603.0	603.2	603.2	602.7	602.2	601.7	601.2	600.5
130°	628.8	629.1	629.5	629.7	630.1	629.9	629.3	628.7	628.0	627.4	626.8
132.5°	653.4	653.8	654.2	654.7	655.1	655.0	654.3	653.7	653.2	652.6	652.0
135°	690.9	691.3	691.8	692.2	692.7	692.7	692.2	691.8	691.3	690.9	690.3
137.5°	726.1	726.5	726.7	727.1	727.4	727.2	726.4	725.7	725.0	724.2	723.8
140°	747.3	747.6	748.0	748.2	748.6	748.4	747.8	747.2	746.5	745.9	745.5
142.5°	766.9	767.3	767.7	768.1	768.6	768.6	768.0	767.6	767.0	766.6	766.1
145°	796.8	796.8	796.8	796.8	796.8	796.7	796.4	796.0	795.8	795.4	795.1
147.5°	819.1	819.8	820.6	821.3	822.0	822.2	821.9	821.5	821.3	820.9	820.6
150°	835.9	836.3	836.8	837.2	837.8	837.8	837.5	837.1	836.9	836.6	836.2
152.5°	849.3	850.0	850.7	851.4	852.1	852.2	851.6	851.0	850.5	850.0	849.8
155°	867.9	868.9	869.8	870.8	871.6	871.7	870.9	870.2	869.4	868.6	868.4
157.5°	883.7	884.9	886.1	887.3	888.5	888.7	887.7	886.8	885.9	884.9	885.1
160°	893.8	894.8	895.9	897.0	898.0	898.1	897.2	896.3	895.4	894.4	894.6
162.5°	903.2	904.2	905.1	906.1	907.0	907.0	906.0	904.9	903.8	902.8	902.9
165°	914.6	915.7	916.8	917.9	919.0	918.9	917.7	916.4	915.2	913.9	914.1
167.5°	922.8	924.1	925.3	926.6	927.8	927.8	926.6	925.3	924.1	922.8	922.8
170°	927.9	929.2	930.3	931.6	932.8	932.8	931.6	930.3	929.2	927.9	927.9
172.5°	930.7	932.0	933.4	934.8	936.1	936.2	935.0	933.7	932.5	931.2	931.1
175°	934.9	936.1	937.4	938.6	939.8	939.9	938.8	937.7	936.7	935.6	935.4
177.5°	936.1	937.4	938.6	939.9	941.1	941.2	940.2	939.2	938.3	937.2	937.1
180°	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3



TEST NUMBER: P332342-940

CATALOG NUMBER: S123RDIP-S1000D805U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1463.7	1462.2	1455.5	1447.7	1437.4	1430.7	1425.3	1422.5	1413.7	1403.0	1395.7
5°	1554.1	1535.9	1516.5	1492.8	1471.0	1448.5	1434.6	1418.2	1398.1	1375.7	1359.9
7.5°	1651.0	1615.2	1576.8	1537.1	1497.9	1462.8	1431.6	1405.1	1373.1	1341.0	1318.4
10°	1725.3	1673.0	1619.1	1563.8	1513.4	1466.2	1429.7	1393.9	1355.7	1318.7	1290.8
12.5°	1792.7	1724.0	1661.8	1593.9	1529.5	1472.9	1420.5	1378.4	1332.4	1292.9	1261.1
15°	1878.1	1807.8	1732.5	1629.3	1543.8	1472.2	1408.5	1353.3	1297.4	1248.8	1217.9
17.5°	1958.0	1852.1	1751.0	1664.9	1553.7	1464.3	1386.5	1320.4	1259.2	1207.7	1169.7
20°	1991.0	1888.5	1778.6	1668.8	1559.6	1459.5	1369.0	1296.2	1232.5	1174.2	1139.1
22.5°	2010.9	1894.8	1779.1	1661.1	1545.0	1441.0	1351.6	1271.5	1202.4	1147.0	1103.6
25°	2034.1	1895.8	1768.4	1651.8	1533.5	1420.6	1314.4	1229.5	1154.9	1095.9	1049.8
27.5°	2049.4	1886.7	1736.1	1606.5	1486.5	1374.1	1276.8	1186.7	1111.0	1048.7	999.3
30°	2052.4	1879.4	1711.3	1571.1	1449.1	1345.9	1242.8	1156.6	1076.6	1010.4	964.3
32.5°	2056.2	1861.4	1677.8	1528.8	1404.0	1301.8	1208.4	1126.1	1044.0	978.8	931.7
35°	2040.2	1851.5	1626.9	1455.8	1330.8	1231.9	1147.5	1071.7	991.0	927.8	879.9
37.5°	1971.2	1812.0	1574.2	1373.5	1242.8	1151.2	1082.4	1016.4	942.3	874.2	829.0
40°	1901.8	1773.2	1533.5	1323.5	1187.0	1092.9	1031.0	977.0	905.4	841.7	793.2
42.5°	1798.4	1720.3	1494.7	1271.0	1123.8	1033.2	981.0	930.4	867.5	802.8	757.2
45°	1608.7	1619.1	1415.1	1187.6	1036.4	945.5	896.3	861.1	805.3	751.9	705.2
47.5°	1370.8	1467.3	1321.8	1098.6	944.3	858.9	815.9	785.2	747.6	695.2	652.6
50°	1215.5	1353.3	1247.1	1038.9	886.6	801.6	759.1	734.2	701.5	660.2	619.6
52.5°	1072.3	1220.2	1156.7	972.4	823.9	746.3	704.8	684.3	658.3	619.5	582.6
55°	874.4	1024.3	1009.8	872.0	730.0	660.2	628.7	605.6	588.0	558.9	529.8
57.5°	707.3	849.4	856.9	760.4	647.3	578.3	551.2	533.8	522.3	500.2	473.3
60°	602.0	732.5	758.0	685.1	588.0	527.4	500.6	486.7	477.6	459.9	439.3
62.5°	514.6	625.6	654.5	602.1	531.2	474.4	453.5	440.1	433.9	418.7	400.6
65°	393.9	486.1	514.0	484.8	447.8	402.3	385.3	373.8	368.4	359.9	346.5
67.5°	296.1	363.4	394.0	373.4	360.1	331.4	320.6	314.3	309.5	303.6	292.5
70°	237.9	287.7	319.2	313.7	302.8	287.7	279.7	275.5	270.6	265.8	256.1
72.5°	191.3	225.5	255.1	257.9	249.0	245.9	239.0	237.2	234.3	228.5	223.1
75°	126.8	150.5	171.1	179.1	182.6	185.7	182.6	182.1	181.5	176.6	173.5
77.5°	83.1	95.9	108.9	122.3	128.0	132.2	133.1	135.4	133.8	131.2	129.7
80°	63.8	66.8	75.9	87.4	96.5	100.1	102.5	103.8	103.2	102.5	100.1
82.5°	46.3	48.8	53.1	61.2	68.8	74.9	76.3	76.1	77.4	77.8	75.9
85°	24.9	25.5	26.7	27.9	32.2	38.9	40.7	41.9	43.1	43.1	39.4
87.5°	10.3	9.5	10.0	9.6	10.8	11.0	13.6	15.7	16.5	14.8	15.2
90°	12.7	10.7	8.6	6.9	5.4	3.8	2.2	0.7	2.2	3.8	5.4
92.5°	14.8	13.3	11.8	11.2	11.7	12.1	12.6	12.9	12.6	12.1	11.7
95°	18.2	16.5	14.8	17.1	23.5	29.8	36.2	42.5	36.2	29.8	23.5
97.5°	44.8	55.9	67.1	74.1	77.0	79.8	82.7	85.4	82.7	79.8	77.0
100°	71.3	95.5	119.7	130.2	127.1	124.0	120.9	117.8	120.9	124.0	127.1
102.5°	98.6	125.1	151.5	163.5	161.3	159.1	156.9	154.6	156.9	159.1	161.3
105°	180.6	194.5	208.5	214.5	212.9	211.2	209.5	207.8	209.5	211.2	212.9
107.5°	275.4	273.2	271.0	269.2	267.9	266.5	265.2	263.8	265.2	266.5	267.9
110°	311.0	309.3	307.6	306.1	304.9	303.6	302.4	301.1	302.4	303.6	304.9



TEST NUMBER: P332342-940

CATALOG NUMBER: S123RDIP-S1000D805U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	346.2	344.5	342.7	341.3	340.2	339.1	338.0	336.9	338.0	339.1	340.2
115°	397.3	396.0	394.6	393.4	392.5	391.6	390.7	389.7	390.7	391.6	392.5
117.5°	447.8	447.1	446.4	445.4	444.3	443.2	442.0	440.9	442.0	443.2	444.3
120°	480.1	479.7	479.2	478.2	476.8	475.5	474.0	472.7	474.0	475.5	476.8
122.5°	511.7	511.0	510.4	509.6	508.5	507.3	506.1	505.0	506.1	507.3	508.5
125°	556.4	555.9	555.3	554.3	553.0	551.8	550.5	549.4	550.5	551.8	553.0
127.5°	599.8	599.0	598.2	597.3	596.0	594.8	593.5	592.3	593.5	594.8	596.0
130°	626.2	625.5	624.9	624.0	622.8	621.5	620.3	619.0	620.3	621.5	622.8
132.5°	651.5	651.0	650.5	649.7	648.5	647.2	646.0	644.7	646.0	647.2	648.5
135°	689.6	689.0	688.4	687.6	686.7	685.7	684.8	683.9	684.8	685.7	686.7
137.5°	723.5	723.2	722.8	722.0	720.9	719.7	718.5	717.4	718.5	719.7	720.9
140°	745.0	744.6	744.0	743.4	742.4	741.5	740.6	739.7	740.6	741.5	742.4
142.5°	765.6	765.2	764.7	764.0	763.1	762.1	761.3	760.3	761.3	762.1	763.1
145°	794.8	794.5	794.2	793.5	792.4	791.3	790.2	789.2	790.2	791.3	792.4
147.5°	820.3	820.0	819.7	819.2	818.5	817.8	817.1	816.4	817.1	817.8	818.5
150°	836.0	835.6	835.4	834.9	834.5	834.0	833.6	833.0	833.6	834.0	834.5
152.5°	849.5	849.4	849.2	849.0	848.8	848.6	848.4	848.1	848.4	848.6	848.8
155°	868.3	868.2	868.0	868.1	868.4	868.7	869.1	869.3	869.1	868.7	868.4
157.5°	885.3	885.4	885.6	885.6	885.6	885.7	885.7	885.7	885.7	885.7	885.6
160°	894.7	894.9	895.0	895.2	895.4	895.5	895.6	895.8	895.6	895.5	895.4
162.5°	903.1	903.2	903.4	903.7	904.1	904.5	904.9	905.3	904.9	904.5	904.1
165°	914.3	914.4	914.5	914.9	915.3	915.8	916.2	916.8	916.2	915.8	915.3
167.5°	922.8	922.8	922.8	923.2	923.8	924.4	925.1	925.7	925.1	924.4	923.8
170°	927.9	927.9	927.9	928.2	928.8	929.4	930.1	930.7	930.1	929.4	928.8
172.5°	930.9	930.9	930.8	931.0	931.7	932.6	933.3	934.0	933.3	932.6	931.7
175°	935.2	935.0	935.0	935.2	936.0	936.8	937.5	938.3	937.5	936.8	936.0
177.5°	937.0	936.8	936.7	937.0	937.6	938.3	938.9	939.4	938.9	938.3	937.6
180°	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3



TEST NUMBER: P332342-940

CATALOG NUMBER: S123RDIP-S1000D805U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1393.3	1387.0	1382.6	1372.9	1366.6	1359.8	1353.0	1357.4	1356.9	1356.4	1356.4
5°	1346.6	1332.6	1319.9	1303.5	1293.2	1280.4	1270.7	1269.5	1271.9	1263.5	1258.6
7.5°	1300.2	1281.1	1263.1	1245.0	1225.8	1210.5	1201.0	1196.4	1190.3	1185.0	1179.6
10°	1267.7	1245.3	1227.6	1205.1	1184.5	1166.4	1154.9	1146.9	1142.6	1138.4	1130.5
12.5°	1234.2	1212.2	1189.8	1164.4	1144.8	1123.6	1115.0	1106.2	1098.1	1093.2	1082.4
15°	1185.2	1156.6	1133.0	1106.3	1084.4	1063.8	1051.7	1034.0	1031.6	1025.6	1014.7
17.5°	1136.0	1105.0	1072.4	1052.7	1028.0	1006.5	988.0	982.1	964.7	958.2	948.7
20°	1097.2	1068.6	1043.7	1017.7	981.9	961.8	947.3	939.4	925.4	916.9	910.9
22.5°	1063.6	1034.7	1005.9	975.4	945.9	923.5	912.8	900.5	892.9	881.0	874.4
25°	1015.8	984.3	949.7	916.9	895.7	878.7	861.7	850.8	839.9	834.4	822.2
27.5°	960.3	927.3	894.9	870.0	844.0	827.2	811.8	802.1	789.0	779.8	773.1
30°	929.7	890.8	862.9	840.4	807.1	791.3	779.8	767.7	758.0	748.2	741.5
32.5°	894.2	858.8	832.3	804.6	778.9	761.7	746.8	736.1	727.8	718.6	711.9
35°	838.7	809.0	781.6	753.7	734.9	717.3	699.7	690.5	682.7	674.2	668.2
37.5°	788.4	760.6	734.7	708.2	684.8	670.6	656.4	649.4	638.7	633.0	626.9
40°	757.3	730.0	702.1	676.6	652.4	641.4	628.7	618.4	608.7	604.4	597.7
42.5°	723.4	696.1	672.5	645.1	625.2	610.4	598.6	587.3	580.1	573.8	570.1
45°	673.0	648.7	625.6	598.3	579.5	566.8	553.4	543.1	536.5	532.2	525.5
47.5°	624.1	599.8	576.4	552.6	534.4	519.8	506.5	499.3	490.4	485.3	480.7
50°	588.6	566.8	541.9	520.0	501.9	487.3	476.4	467.3	459.4	452.7	449.7
52.5°	556.1	532.8	511.3	491.0	471.7	455.2	445.3	435.7	429.8	422.1	418.6
55°	502.5	480.0	461.8	441.8	422.9	409.0	396.9	388.3	382.3	373.8	369.0
57.5°	452.1	431.9	410.2	392.9	373.4	361.7	351.6	340.1	332.7	326.0	321.3
60°	418.1	395.0	376.2	359.9	342.9	327.7	318.6	309.5	301.6	294.9	290.7
62.5°	382.6	362.6	344.6	326.8	311.3	298.1	287.5	279.9	273.0	268.7	264.5
65°	328.3	312.5	294.4	279.7	265.2	255.5	247.0	240.3	235.4	232.4	228.8
67.5°	278.3	263.0	247.1	232.8	223.1	215.7	210.1	204.4	202.0	198.0	195.6
70°	245.8	230.0	216.1	205.1	195.4	189.9	186.3	182.1	179.6	174.8	172.4
72.5°	210.4	198.9	188.9	179.9	172.1	167.1	162.5	157.3	153.4	148.0	145.6
75°	165.7	155.3	147.5	141.4	136.5	129.8	123.1	117.7	115.9	114.0	113.5
77.5°	122.7	116.2	110.5	105.3	99.2	94.4	93.0	91.8	91.4	90.4	90.4
80°	96.5	90.4	86.1	80.1	76.4	76.4	76.4	75.3	75.9	75.9	75.9
82.5°	71.7	66.2	63.8	61.6	60.9	61.4	61.4	61.6	61.3	62.2	61.8
85°	37.0	37.6	38.9	38.3	38.9	38.9	40.0	39.4	40.0	38.9	40.0
87.5°	15.0	16.8	17.7	18.5	19.4	19.4	20.0	20.1	20.7	20.9	21.0
90°	6.9	8.6	10.7	12.7	14.7	16.8	17.4	18.0	18.5	19.2	19.7
92.5°	11.2	11.8	13.3	14.8	16.3	17.8	18.8	19.8	20.8	21.8	22.4
95°	17.1	14.8	16.5	18.2	19.9	21.6	22.7	23.8	24.9	25.9	26.5
97.5°	74.1	67.1	55.9	44.8	33.6	22.5	23.7	25.0	26.1	27.4	28.1
100°	130.2	119.7	95.5	71.3	47.2	23.0	24.3	25.5	26.8	28.0	28.6
102.5°	163.5	151.5	125.1	98.6	72.2	45.8	42.0	38.2	34.3	30.5	28.7
105°	214.5	208.5	194.5	180.6	166.6	152.7	125.3	97.8	70.4	43.0	29.4
107.5°	269.2	271.0	273.2	275.4	277.6	279.8	259.8	239.6	219.5	199.4	179.0
110°	306.1	307.6	309.3	311.0	312.7	314.4	309.3	304.2	299.1	294.0	280.4



TEST NUMBER: P332342-940

CATALOG NUMBER: S123RDIP-S1000D805U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	341.3	342.7	344.5	346.2	347.9	349.6	349.6	349.7	349.8	349.9	347.6
115°	393.4	394.6	396.0	397.3	398.8	400.2	401.7	403.2	404.8	406.4	407.4
117.5°	445.4	446.4	447.1	447.8	448.5	449.2	450.5	451.7	453.0	454.1	454.9
120°	478.2	479.2	479.7	480.1	480.5	481.0	482.2	483.5	484.7	486.0	486.6
122.5°	509.6	510.4	511.0	511.7	512.2	512.8	513.7	514.5	515.4	516.3	516.7
125°	554.3	555.3	555.9	556.4	557.1	557.7	558.0	558.3	558.7	558.9	559.3
127.5°	597.3	598.2	599.0	599.8	600.5	601.2	601.7	602.2	602.7	603.2	603.2
130°	624.0	624.9	625.5	626.2	626.8	627.4	628.0	628.7	629.3	629.9	630.1
132.5°	649.7	650.5	651.0	651.5	652.0	652.6	653.2	653.7	654.3	655.0	655.1
135°	687.6	688.4	689.0	689.6	690.3	690.9	691.3	691.8	692.2	692.7	692.7
137.5°	722.0	722.8	723.2	723.5	723.8	724.2	725.0	725.7	726.4	727.2	727.4
140°	743.4	744.0	744.6	745.0	745.5	745.9	746.5	747.2	747.8	748.4	748.6
142.5°	764.0	764.7	765.2	765.6	766.1	766.6	767.0	767.6	768.0	768.6	768.6
145°	793.5	794.2	794.5	794.8	795.1	795.4	795.8	796.0	796.4	796.7	796.8
147.5°	819.2	819.7	820.0	820.3	820.6	820.9	821.3	821.5	821.9	822.2	822.0
150°	834.9	835.4	835.6	836.0	836.2	836.6	836.9	837.1	837.5	837.8	837.8
152.5°	849.0	849.2	849.4	849.5	849.8	850.0	850.5	851.0	851.6	852.2	852.1
155°	868.1	868.0	868.2	868.3	868.4	868.6	869.4	870.2	870.9	871.7	871.6
157.5°	885.6	885.6	885.4	885.3	885.1	884.9	885.9	886.8	887.7	888.7	888.5
160°	895.2	895.0	894.9	894.7	894.6	894.4	895.4	896.3	897.2	898.1	898.0
162.5°	903.7	903.4	903.2	903.1	902.9	902.8	903.8	904.9	906.0	907.0	907.0
165°	914.9	914.5	914.4	914.3	914.1	913.9	915.2	916.4	917.7	918.9	919.0
167.5°	923.2	922.8	922.8	922.8	922.8	922.8	924.1	925.3	926.6	927.8	927.8
170°	928.2	927.9	927.9	927.9	927.9	927.9	929.2	930.3	931.6	932.8	932.8
172.5°	931.0	930.8	930.9	930.9	931.1	931.2	932.5	933.7	935.0	936.2	936.1
175°	935.2	935.0	935.0	935.2	935.4	935.6	936.7	937.7	938.8	939.9	939.8
177.5°	937.0	936.7	936.8	937.0	937.1	937.2	938.3	939.2	940.2	941.2	941.1
180°	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3



TEST NUMBER: P332342-940

CATALOG NUMBER: S123RDIP-S1000D805U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1350.6	1350.1	1350.6	1348.6	1350.6	1350.1	1350.6	1356.4	1356.4	1356.9	1357.4
5°	1256.8	1256.2	1254.4	1248.8	1254.4	1256.2	1256.8	1258.6	1263.5	1271.9	1269.5
7.5°	1174.8	1174.0	1168.7	1168.8	1168.7	1174.0	1174.8	1179.6	1185.0	1190.3	1196.4
10°	1126.3	1126.9	1119.6	1115.4	1119.6	1126.9	1126.3	1130.5	1138.4	1142.6	1146.9
12.5°	1079.2	1076.4	1070.6	1065.9	1070.6	1076.4	1079.2	1082.4	1093.2	1098.1	1106.2
15°	1017.1	1011.0	996.4	997.6	996.4	1011.0	1017.1	1014.7	1025.6	1031.6	1034.0
17.5°	943.9	939.4	939.1	930.7	939.1	939.4	943.9	948.7	958.2	964.7	982.1
20°	901.2	898.1	899.3	890.8	899.3	898.1	901.2	910.9	916.9	925.4	939.4
22.5°	867.6	864.6	859.5	856.8	859.5	864.6	867.6	874.4	881.0	892.9	900.5
25°	818.6	813.8	809.0	812.0	809.0	813.8	818.6	822.2	834.4	839.9	850.8
27.5°	769.6	766.0	761.1	760.5	761.1	766.0	769.6	773.1	779.8	789.0	802.1
30°	738.5	734.9	732.5	729.4	732.5	734.9	738.5	741.5	748.2	758.0	767.7
32.5°	706.9	706.2	701.9	701.2	701.9	706.2	706.9	711.9	718.6	727.8	736.1
35°	665.7	662.1	660.8	661.5	660.8	662.1	665.7	668.2	674.2	682.7	690.5
37.5°	626.5	621.6	619.5	617.2	619.5	621.6	626.5	626.9	633.0	638.7	649.4
40°	598.3	593.5	592.3	591.0	592.3	593.5	598.3	597.7	604.4	608.7	618.4
42.5°	566.8	564.8	564.1	562.0	564.1	564.8	566.8	570.1	573.8	580.1	587.3
45°	523.7	523.1	519.4	520.7	519.4	523.1	523.7	525.5	532.2	536.5	543.1
47.5°	478.3	475.6	473.1	474.7	473.1	475.6	478.3	480.7	485.3	490.4	499.3
50°	447.3	446.0	440.6	441.8	440.6	446.0	447.3	449.7	452.7	459.4	467.3
52.5°	416.2	411.5	409.5	408.8	409.5	411.5	416.2	418.6	422.1	429.8	435.7
55°	364.7	359.3	356.9	355.6	356.9	359.3	364.7	369.0	373.8	382.3	388.3
57.5°	314.2	312.7	310.9	312.2	310.9	312.7	314.2	321.3	326.0	332.7	340.1
60°	284.6	284.6	284.6	284.0	284.6	284.6	284.6	290.7	294.9	301.6	309.5
62.5°	261.8	260.3	259.8	260.7	259.8	260.3	261.8	264.5	268.7	273.0	279.9
65°	226.9	226.3	223.9	223.3	223.9	226.3	226.9	228.8	232.4	235.4	240.3
67.5°	194.0	191.9	191.2	190.3	191.2	191.9	194.0	195.6	198.0	202.0	204.4
70°	169.3	168.1	164.4	165.1	164.4	168.1	169.3	172.4	174.8	179.6	182.1
72.5°	142.6	141.4	140.6	139.8	140.6	141.4	142.6	145.6	148.0	153.4	157.3
75°	112.9	112.3	111.6	114.0	111.6	112.3	112.9	113.5	114.0	115.9	117.7
77.5°	90.4	90.4	90.8	89.8	90.8	90.4	90.4	90.4	90.4	91.4	91.8
80°	75.9	75.9	75.3	75.3	75.3	75.9	75.9	75.9	75.9	75.9	75.3
82.5°	60.8	61.3	61.6	60.7	61.6	61.3	60.8	61.8	62.2	61.3	61.6
85°	40.0	39.4	40.7	40.0	40.7	39.4	40.0	40.0	38.9	40.0	39.4
87.5°	21.9	21.0	21.1	21.7	21.1	21.0	21.9	21.0	20.9	20.7	20.1
90°	20.0	20.3	20.6	21.0	20.6	20.3	20.0	19.7	19.2	18.5	18.0
92.5°	22.6	22.7	22.9	23.2	22.9	22.7	22.6	22.4	21.8	20.8	19.8
95°	26.5	26.5	26.5	26.5	26.5	26.5	26.5	26.5	25.9	24.9	23.8
97.5°	28.3	28.4	28.5	28.7	28.5	28.4	28.3	28.1	27.4	26.1	25.0
100°	28.8	29.0	29.2	29.2	29.2	29.0	28.8	28.6	28.0	26.8	25.5
102.5°	29.0	29.2	29.5	29.9	29.5	29.2	29.0	28.7	30.5	34.3	38.2
105°	29.8	30.1	30.4	30.7	30.4	30.1	29.8	29.4	43.0	70.4	97.8
107.5°	158.4	137.7	117.0	96.3	117.0	137.7	158.4	179.0	199.4	219.5	239.6
110°	258.2	236.0	213.8	191.7	213.8	236.0	258.2	280.4	294.0	299.1	304.2



TEST NUMBER: P332342-940

CATALOG NUMBER: S123RDIP-S1000D805U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	343.0	338.2	333.6	329.0	333.6	338.2	343.0	347.6	349.9	349.8	349.7
115°	408.0	408.7	409.3	409.9	409.3	408.7	408.0	407.4	406.4	404.8	403.2
117.5°	455.0	455.1	455.2	455.4	455.2	455.1	455.0	454.9	454.1	453.0	451.7
120°	486.6	486.6	486.6	486.6	486.6	486.6	486.6	486.6	486.0	484.7	483.5
122.5°	516.9	517.0	517.2	517.3	517.2	517.0	516.9	516.7	516.3	515.4	514.5
125°	559.5	559.9	560.2	560.5	560.2	559.9	559.5	559.3	558.9	558.7	558.3
127.5°	603.0	602.7	602.4	602.1	602.4	602.7	603.0	603.2	603.2	602.7	602.2
130°	629.7	629.5	629.1	628.8	629.1	629.5	629.7	630.1	629.9	629.3	628.7
132.5°	654.7	654.2	653.8	653.4	653.8	654.2	654.7	655.1	655.0	654.3	653.7
135°	692.2	691.8	691.3	690.9	691.3	691.8	692.2	692.7	692.7	692.2	691.8
137.5°	727.1	726.7	726.5	726.1	726.5	726.7	727.1	727.4	727.2	726.4	725.7
140°	748.2	748.0	747.6	747.3	747.6	748.0	748.2	748.6	748.4	747.8	747.2
142.5°	768.1	767.7	767.3	766.9	767.3	767.7	768.1	768.6	768.6	768.0	767.6
145°	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.7	796.4	796.0
147.5°	821.3	820.6	819.8	819.1	819.8	820.6	821.3	822.0	822.2	821.9	821.5
150°	837.2	836.8	836.3	835.9	836.3	836.8	837.2	837.8	837.8	837.5	837.1
152.5°	851.4	850.7	850.0	849.3	850.0	850.7	851.4	852.1	852.2	851.6	851.0
155°	870.8	869.8	868.9	867.9	868.9	869.8	870.8	871.6	871.7	870.9	870.2
157.5°	887.3	886.1	884.9	883.7	884.9	886.1	887.3	888.5	888.7	887.7	886.8
160°	897.0	895.9	894.8	893.8	894.8	895.9	897.0	898.0	898.1	897.2	896.3
162.5°	906.1	905.1	904.2	903.2	904.2	905.1	906.1	907.0	907.0	906.0	904.9
165°	917.9	916.8	915.7	914.6	915.7	916.8	917.9	919.0	918.9	917.7	916.4
167.5°	926.6	925.3	924.1	922.8	924.1	925.3	926.6	927.8	927.8	926.6	925.3
170°	931.6	930.3	929.2	927.9	929.2	930.3	931.6	932.8	932.8	931.6	930.3
172.5°	934.8	933.4	932.0	930.7	932.0	933.4	934.8	936.1	936.2	935.0	933.7
175°	938.6	937.4	936.1	934.9	936.1	937.4	938.6	939.8	939.9	938.8	937.7
177.5°	939.9	938.6	937.4	936.1	937.4	938.6	939.9	941.1	941.2	940.2	939.2
180°	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3



TEST NUMBER: P332342-940

CATALOG NUMBER: S123RDIP-S1000D805U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1353.0	1359.8	1366.6	1372.9	1382.6	1387.0	1393.3	1395.7	1403.0	1413.7	1422.5
5°	1270.7	1280.4	1293.2	1303.5	1319.9	1332.6	1346.6	1359.9	1375.7	1398.1	1418.2
7.5°	1201.0	1210.5	1225.8	1245.0	1263.1	1281.1	1300.2	1318.4	1341.0	1373.1	1405.1
10°	1154.9	1166.4	1184.5	1205.1	1227.6	1245.3	1267.7	1290.8	1318.7	1355.7	1393.9
12.5°	1115.0	1123.6	1144.8	1164.4	1189.8	1212.2	1234.2	1261.1	1292.9	1332.4	1378.4
15°	1051.7	1063.8	1084.4	1106.3	1133.0	1156.6	1185.2	1217.9	1248.8	1297.4	1353.3
17.5°	988.0	1006.5	1028.0	1052.7	1072.4	1105.0	1136.0	1169.7	1207.7	1259.2	1320.4
20°	947.3	961.8	981.9	1017.7	1043.7	1068.6	1097.2	1139.1	1174.2	1232.5	1296.2
22.5°	912.8	923.5	945.9	975.4	1005.9	1034.7	1063.6	1103.6	1147.0	1202.4	1271.5
25°	861.7	878.7	895.7	916.9	949.7	984.3	1015.8	1049.8	1095.9	1154.9	1229.5
27.5°	811.8	827.2	844.0	870.0	894.9	927.3	960.3	999.3	1048.7	1111.0	1186.7
30°	779.8	791.3	807.1	840.4	862.9	890.8	929.7	964.3	1010.4	1076.6	1156.6
32.5°	746.8	761.7	778.9	804.6	832.3	858.8	894.2	931.7	978.8	1044.0	1126.1
35°	699.7	717.3	734.9	753.7	781.6	809.0	838.7	879.9	927.8	991.0	1071.7
37.5°	656.4	670.6	684.8	708.2	734.7	760.6	788.4	829.0	874.2	942.3	1016.4
40°	628.7	641.4	652.4	676.6	702.1	730.0	757.3	793.2	841.7	905.4	977.0
42.5°	598.6	610.4	625.2	645.1	672.5	696.1	723.4	757.2	802.8	867.5	930.4
45°	553.4	566.8	579.5	598.3	625.6	648.7	673.0	705.2	751.9	805.3	861.1
47.5°	506.5	519.8	534.4	552.6	576.4	599.8	624.1	652.6	695.2	747.6	785.2
50°	476.4	487.3	501.9	520.0	541.9	566.8	588.6	619.6	660.2	701.5	734.2
52.5°	445.3	455.2	471.7	491.0	511.3	532.8	556.1	582.6	619.5	658.3	684.3
55°	396.9	409.0	422.9	441.8	461.8	480.0	502.5	529.8	558.9	588.0	605.6
57.5°	351.6	361.7	373.4	392.9	410.2	431.9	452.1	473.3	500.2	522.3	533.8
60°	318.6	327.7	342.9	359.9	376.2	395.0	418.1	439.3	459.9	477.6	486.7
62.5°	287.5	298.1	311.3	326.8	344.6	362.6	382.6	400.6	418.7	433.9	440.1
65°	247.0	255.5	265.2	279.7	294.4	312.5	328.3	346.5	359.9	368.4	373.8
67.5°	210.1	215.7	223.1	232.8	247.1	263.0	278.3	292.5	303.6	309.5	314.3
70°	186.3	189.9	195.4	205.1	216.1	230.0	245.8	256.1	265.8	270.6	275.5
72.5°	162.5	167.1	172.1	179.9	188.9	198.9	210.4	223.1	228.5	234.3	237.2
75°	123.1	129.8	136.5	141.4	147.5	155.3	165.7	173.5	176.6	181.5	182.1
77.5°	93.0	94.4	99.2	105.3	110.5	116.2	122.7	129.7	131.2	133.8	135.4
80°	76.4	76.4	76.4	80.1	86.1	90.4	96.5	100.1	102.5	103.2	103.8
82.5°	61.4	61.4	60.9	61.6	63.8	66.2	71.7	75.9	77.8	77.4	76.1
85°	40.0	38.9	38.9	38.3	38.9	37.6	37.0	39.4	43.1	43.1	41.9
87.5°	20.0	19.4	19.4	18.5	17.7	16.8	15.0	15.2	14.8	16.5	15.7
90°	17.4	16.8	14.7	12.7	10.7	8.6	6.9	5.4	3.8	2.2	0.7
92.5°	18.8	17.8	16.3	14.8	13.3	11.8	11.2	11.7	12.1	12.6	12.9
95°	22.7	21.6	19.9	18.2	16.5	14.8	17.1	23.5	29.8	36.2	42.5
97.5°	23.7	22.5	33.6	44.8	55.9	67.1	74.1	77.0	79.8	82.7	85.4
100°	24.3	23.0	47.2	71.3	95.5	119.7	130.2	127.1	124.0	120.9	117.8
102.5°	42.0	45.8	72.2	98.6	125.1	151.5	163.5	161.3	159.1	156.9	154.6
105°	125.3	152.7	166.6	180.6	194.5	208.5	214.5	212.9	211.2	209.5	207.8
107.5°	259.8	279.8	277.6	275.4	273.2	271.0	269.2	267.9	266.5	265.2	263.8
110°	309.3	314.4	312.7	311.0	309.3	307.6	306.1	304.9	303.6	302.4	301.1



TEST NUMBER: P332342-940

CATALOG NUMBER: S123RDIP-S1000D805U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	349.6	349.6	347.9	346.2	344.5	342.7	341.3	340.2	339.1	338.0	336.9
115°	401.7	400.2	398.8	397.3	396.0	394.6	393.4	392.5	391.6	390.7	389.7
117.5°	450.5	449.2	448.5	447.8	447.1	446.4	445.4	444.3	443.2	442.0	440.9
120°	482.2	481.0	480.5	480.1	479.7	479.2	478.2	476.8	475.5	474.0	472.7
122.5°	513.7	512.8	512.2	511.7	511.0	510.4	509.6	508.5	507.3	506.1	505.0
125°	558.0	557.7	557.1	556.4	555.9	555.3	554.3	553.0	551.8	550.5	549.4
127.5°	601.7	601.2	600.5	599.8	599.0	598.2	597.3	596.0	594.8	593.5	592.3
130°	628.0	627.4	626.8	626.2	625.5	624.9	624.0	622.8	621.5	620.3	619.0
132.5°	653.2	652.6	652.0	651.5	651.0	650.5	649.7	648.5	647.2	646.0	644.7
135°	691.3	690.9	690.3	689.6	689.0	688.4	687.6	686.7	685.7	684.8	683.9
137.5°	725.0	724.2	723.8	723.5	723.2	722.8	722.0	720.9	719.7	718.5	717.4
140°	746.5	745.9	745.5	745.0	744.6	744.0	743.4	742.4	741.5	740.6	739.7
142.5°	767.0	766.6	766.1	765.6	765.2	764.7	764.0	763.1	762.1	761.3	760.3
145°	795.8	795.4	795.1	794.8	794.5	794.2	793.5	792.4	791.3	790.2	789.2
147.5°	821.3	820.9	820.6	820.3	820.0	819.7	819.2	818.5	817.8	817.1	816.4
150°	836.9	836.6	836.2	836.0	835.6	835.4	834.9	834.5	834.0	833.6	833.0
152.5°	850.5	850.0	849.8	849.5	849.4	849.2	849.0	848.8	848.6	848.4	848.1
155°	869.4	868.6	868.4	868.3	868.2	868.0	868.1	868.4	868.7	869.1	869.3
157.5°	885.9	884.9	885.1	885.3	885.4	885.6	885.6	885.6	885.7	885.7	885.7
160°	895.4	894.4	894.6	894.7	894.9	895.0	895.2	895.4	895.5	895.6	895.8
162.5°	903.8	902.8	902.9	903.1	903.2	903.4	903.7	904.1	904.5	904.9	905.3
165°	915.2	913.9	914.1	914.3	914.4	914.5	914.9	915.3	915.8	916.2	916.8
167.5°	924.1	922.8	922.8	922.8	922.8	922.8	923.2	923.8	924.4	925.1	925.7
170°	929.2	927.9	927.9	927.9	927.9	927.9	928.2	928.8	929.4	930.1	930.7
172.5°	932.5	931.2	931.1	930.9	930.9	930.8	931.0	931.7	932.6	933.3	934.0
175°	936.7	935.6	935.4	935.2	935.0	935.0	935.2	936.0	936.8	937.5	938.3
177.5°	938.3	937.2	937.1	937.0	936.8	936.7	937.0	937.6	938.3	938.9	939.4
180°	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3



TEST NUMBER: P332342-940

CATALOG NUMBER: S123RDIP-S1000D805U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1425.3	1430.7	1437.4	1447.7	1455.5	1462.2	1463.7	1465.6	1470.5	1478.7	1485.1
5°	1434.6	1448.5	1471.0	1492.8	1516.5	1535.9	1554.1	1566.8	1579.0	1604.5	1625.1
7.5°	1431.6	1462.8	1497.9	1537.1	1576.8	1615.2	1651.0	1682.9	1714.7	1751.9	1794.2
10°	1429.7	1466.2	1513.4	1563.8	1619.1	1673.0	1725.3	1765.9	1813.2	1855.7	1909.7
12.5°	1420.5	1472.9	1529.5	1593.9	1661.8	1724.0	1792.7	1848.9	1903.1	1964.4	2027.2
15°	1408.5	1472.2	1543.8	1629.3	1732.5	1807.8	1878.1	1975.9	2042.6	2109.3	2199.2
17.5°	1386.5	1464.3	1553.7	1664.9	1751.0	1852.1	1958.0	2035.2	2125.1	2219.2	2300.5
20°	1369.0	1459.5	1559.6	1668.8	1778.6	1888.5	1991.0	2083.3	2176.1	2284.7	2351.5
22.5°	1351.6	1441.0	1545.0	1661.1	1779.1	1894.8	2010.9	2119.2	2223.7	2333.3	2418.5
25°	1314.4	1420.6	1533.5	1651.8	1768.4	1895.8	2034.1	2154.9	2284.1	2397.0	2477.7
27.5°	1276.8	1374.1	1486.5	1606.5	1736.1	1886.7	2049.4	2186.7	2316.2	2397.0	2422.4
30°	1242.8	1345.9	1449.1	1571.1	1711.3	1879.4	2052.4	2209.5	2315.7	2350.9	2324.8
32.5°	1208.4	1301.8	1404.0	1528.8	1677.8	1861.4	2056.2	2195.9	2259.9	2232.9	2126.7
35°	1147.5	1231.9	1330.8	1455.8	1626.9	1851.5	2040.2	2134.8	2119.1	1967.4	1767.1
37.5°	1082.4	1151.2	1242.8	1373.5	1574.2	1812.0	1971.2	1985.2	1848.7	1615.8	1384.5
40°	1031.0	1092.9	1187.0	1323.5	1533.5	1773.2	1901.8	1845.4	1633.6	1374.5	1181.5
42.5°	981.0	1033.2	1123.8	1271.0	1494.7	1720.3	1798.4	1675.5	1431.2	1186.2	1010.7
45°	896.3	945.5	1036.4	1187.6	1415.1	1619.1	1608.7	1395.1	1150.6	953.3	807.7
47.5°	815.9	858.9	944.3	1098.6	1321.8	1467.3	1370.8	1143.5	936.1	777.8	674.0
50°	759.1	801.6	886.6	1038.9	1247.1	1353.3	1215.5	996.4	806.5	675.4	592.9
52.5°	704.8	746.3	823.9	972.4	1156.7	1220.2	1072.3	869.2	710.9	597.7	526.8
55°	628.7	660.2	730.0	872.0	1009.8	1024.3	874.4	704.5	574.1	495.2	446.7
57.5°	551.2	578.3	647.3	760.4	856.9	849.4	707.3	560.4	472.5	413.8	378.7
60°	500.6	527.4	588.0	685.1	758.0	732.5	602.0	483.7	408.4	365.3	337.4
62.5°	453.5	474.4	531.2	602.1	654.5	625.6	514.6	416.7	357.0	320.7	298.5
65°	385.3	402.3	447.8	484.8	514.0	486.1	393.9	325.8	282.8	257.3	242.1
67.5°	320.6	331.4	360.1	373.4	394.0	363.4	296.1	250.7	226.1	204.6	194.0
70°	279.7	287.7	302.8	313.7	319.2	287.7	237.9	204.5	183.9	168.7	162.0
72.5°	239.0	245.9	249.0	257.9	255.1	225.5	191.3	164.7	149.9	139.6	131.0
75°	182.6	185.7	182.6	179.1	171.1	150.5	126.8	113.5	102.5	97.7	94.7
77.5°	133.1	132.2	128.0	122.3	108.9	95.9	83.1	78.6	73.9	71.3	70.3
80°	102.5	100.1	96.5	87.4	75.9	66.8	63.8	60.7	58.9	55.8	55.2
82.5°	76.3	74.9	68.8	61.2	53.1	48.8	46.3	45.1	43.3	41.7	41.6
85°	40.7	38.9	32.2	27.9	26.7	25.5	24.9	24.9	22.5	21.8	21.8
87.5°	13.6	11.0	10.8	9.6	10.0	9.5	10.3	9.7	9.6	10.3	9.5
90°	2.2	3.8	5.4	6.9	8.6	10.7	12.7	14.7	16.8	17.4	18.0
92.5°	12.6	12.1	11.7	11.2	11.8	13.3	14.8	16.3	17.8	18.8	19.8
95°	36.2	29.8	23.5	17.1	14.8	16.5	18.2	19.9	21.6	22.7	23.8
97.5°	82.7	79.8	77.0	74.1	67.1	55.9	44.8	33.6	22.5	23.7	25.0
100°	120.9	124.0	127.1	130.2	119.7	95.5	71.3	47.2	23.0	24.3	25.5
102.5°	156.9	159.1	161.3	163.5	151.5	125.1	98.6	72.2	45.8	42.0	38.2
105°	209.5	211.2	212.9	214.5	208.5	194.5	180.6	166.6	152.7	125.3	97.8
107.5°	265.2	266.5	267.9	269.2	271.0	273.2	275.4	277.6	279.8	259.8	239.6
110°	302.4	303.6	304.9	306.1	307.6	309.3	311.0	312.7	314.4	309.3	304.2



TEST NUMBER: P332342-940

CATALOG NUMBER: S123RDIP-S1000D805U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	338.0	339.1	340.2	341.3	342.7	344.5	346.2	347.9	349.6	349.6	349.7
115°	390.7	391.6	392.5	393.4	394.6	396.0	397.3	398.8	400.2	401.7	403.2
117.5°	442.0	443.2	444.3	445.4	446.4	447.1	447.8	448.5	449.2	450.5	451.7
120°	474.0	475.5	476.8	478.2	479.2	479.7	480.1	480.5	481.0	482.2	483.5
122.5°	506.1	507.3	508.5	509.6	510.4	511.0	511.7	512.2	512.8	513.7	514.5
125°	550.5	551.8	553.0	554.3	555.3	555.9	556.4	557.1	557.7	558.0	558.3
127.5°	593.5	594.8	596.0	597.3	598.2	599.0	599.8	600.5	601.2	601.7	602.2
130°	620.3	621.5	622.8	624.0	624.9	625.5	626.2	626.8	627.4	628.0	628.7
132.5°	646.0	647.2	648.5	649.7	650.5	651.0	651.5	652.0	652.6	653.2	653.7
135°	684.8	685.7	686.7	687.6	688.4	689.0	689.6	690.3	690.9	691.3	691.8
137.5°	718.5	719.7	720.9	722.0	722.8	723.2	723.5	723.8	724.2	725.0	725.7
140°	740.6	741.5	742.4	743.4	744.0	744.6	745.0	745.5	745.9	746.5	747.2
142.5°	761.3	762.1	763.1	764.0	764.7	765.2	765.6	766.1	766.6	767.0	767.6
145°	790.2	791.3	792.4	793.5	794.2	794.5	794.8	795.1	795.4	795.8	796.0
147.5°	817.1	817.8	818.5	819.2	819.7	820.0	820.3	820.6	820.9	821.3	821.5
150°	833.6	834.0	834.5	834.9	835.4	835.6	836.0	836.2	836.6	836.9	837.1
152.5°	848.4	848.6	848.8	849.0	849.2	849.4	849.5	849.8	850.0	850.5	851.0
155°	869.1	868.7	868.4	868.1	868.0	868.2	868.3	868.4	868.6	869.4	870.2
157.5°	885.7	885.7	885.6	885.6	885.6	885.4	885.3	885.1	884.9	885.9	886.8
160°	895.6	895.5	895.4	895.2	895.0	894.9	894.7	894.6	894.4	895.4	896.3
162.5°	904.9	904.5	904.1	903.7	903.4	903.2	903.1	902.9	902.8	903.8	904.9
165°	916.2	915.8	915.3	914.9	914.5	914.4	914.3	914.1	913.9	915.2	916.4
167.5°	925.1	924.4	923.8	923.2	922.8	922.8	922.8	922.8	922.8	924.1	925.3
170°	930.1	929.4	928.8	928.2	927.9	927.9	927.9	927.9	927.9	929.2	930.3
172.5°	933.3	932.6	931.7	931.0	930.8	930.9	930.9	931.1	931.2	932.5	933.7
175°	937.5	936.8	936.0	935.2	935.0	935.0	935.2	935.4	935.6	936.7	937.7
177.5°	938.9	938.3	937.6	937.0	936.7	936.8	937.0	937.1	937.2	938.3	939.2
180°	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3



TEST NUMBER: P332342-940

CATALOG NUMBER: S123RDIP-S1000D805U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1495.2	1495.2	1497.2	1504.5	1505.5	1511.7	1509.8
5°	1643.3	1654.8	1659.1	1677.3	1688.2	1693.1	1683.4
7.5°	1824.4	1856.9	1872.3	1891.4	1908.3	1913.3	1900.1
10°	1956.4	1990.4	2018.9	2036.6	2052.9	2063.9	2077.8
12.5°	2084.1	2125.8	2152.9	2177.8	2194.7	2208.5	2210.8
15°	2222.9	2286.0	2333.9	2369.1	2386.7	2395.8	2392.2
17.5°	2362.8	2421.3	2455.4	2491.4	2515.7	2516.9	2517.7
20°	2442.0	2498.9	2538.4	2565.1	2592.4	2591.2	2597.3
22.5°	2494.8	2539.8	2570.0	2589.3	2598.7	2594.1	2595.3
25°	2519.6	2532.9	2527.5	2496.5	2488.7	2460.1	2465.0
27.5°	2391.9	2328.8	2263.5	2179.5	2113.3	2060.3	2063.0
30°	2218.6	2106.9	1979.5	1872.7	1776.8	1750.2	1693.1
32.5°	1976.4	1808.8	1659.6	1560.0	1477.7	1455.5	1405.7
35°	1565.7	1403.0	1249.5	1157.3	1120.8	1069.9	1069.3
37.5°	1216.9	1073.7	992.6	923.4	887.1	856.2	853.2
40°	1023.8	912.0	850.8	801.0	765.3	742.2	736.7
42.5°	888.8	798.4	741.1	710.2	682.7	670.8	661.9
45°	725.8	665.1	625.0	597.1	584.4	575.2	570.4
47.5°	607.1	566.4	539.1	520.6	510.2	500.6	503.2
50°	542.5	509.2	489.1	471.5	463.6	456.9	457.5
52.5°	490.5	460.6	444.4	431.7	421.9	417.1	414.8
55°	416.3	397.4	381.1	372.0	366.5	359.9	358.0
57.5°	355.1	340.5	327.2	316.9	315.6	309.2	310.0
60°	314.3	302.2	291.3	285.8	281.6	276.1	277.9
62.5°	280.9	270.6	260.7	256.2	252.0	248.0	248.8
65°	230.0	220.3	214.2	211.8	210.0	208.1	206.3
67.5°	183.2	177.4	173.5	168.4	164.6	164.0	162.1
70°	154.2	146.2	139.6	132.9	131.1	130.5	131.1
72.5°	123.6	118.6	116.7	113.5	113.2	111.6	112.6
75°	92.8	91.0	89.8	87.4	87.4	87.4	87.4
77.5°	68.5	67.3	66.6	66.2	65.5	64.6	64.6
80°	53.4	52.8	51.5	51.5	51.0	51.5	51.0
82.5°	40.3	40.2	39.0	39.0	38.3	38.0	38.3
85°	20.6	20.1	21.2	20.1	20.6	19.4	20.6
87.5°	9.5	9.6	9.3	9.4	8.9	10.0	9.0
90°	18.5	19.2	19.7	20.0	20.3	20.6	21.0
92.5°	20.8	21.8	22.4	22.6	22.7	22.9	23.2
95°	24.9	25.9	26.5	26.5	26.5	26.5	26.5
97.5°	26.1	27.4	28.1	28.3	28.4	28.5	28.7
100°	26.8	28.0	28.6	28.8	29.0	29.2	29.2
102.5°	34.3	30.5	28.7	29.0	29.2	29.5	29.9
105°	70.4	43.0	29.4	29.8	30.1	30.4	30.7
107.5°	219.5	199.4	179.0	158.4	137.7	117.0	96.3
110°	299.1	294.0	280.4	258.2	236.0	213.8	191.7



TEST NUMBER: P332342-940

CATALOG NUMBER: S123RDIP-S1000D805U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	349.8	349.9	347.6	343.0	338.2	333.6	329.0
115°	404.8	406.4	407.4	408.0	408.7	409.3	409.9
117.5°	453.0	454.1	454.9	455.0	455.1	455.2	455.4
120°	484.7	486.0	486.6	486.6	486.6	486.6	486.6
122.5°	515.4	516.3	516.7	516.9	517.0	517.2	517.3
125°	558.7	558.9	559.3	559.5	559.9	560.2	560.5
127.5°	602.7	603.2	603.2	603.0	602.7	602.4	602.1
130°	629.3	629.9	630.1	629.7	629.5	629.1	628.8
132.5°	654.3	655.0	655.1	654.7	654.2	653.8	653.4
135°	692.2	692.7	692.7	692.2	691.8	691.3	690.9
137.5°	726.4	727.2	727.4	727.1	726.7	726.5	726.1
140°	747.8	748.4	748.6	748.2	748.0	747.6	747.3
142.5°	768.0	768.6	768.6	768.1	767.7	767.3	766.9
145°	796.4	796.7	796.8	796.8	796.8	796.8	796.8
147.5°	821.9	822.2	822.0	821.3	820.6	819.8	819.1
150°	837.5	837.8	837.8	837.2	836.8	836.3	835.9
152.5°	851.6	852.2	852.1	851.4	850.7	850.0	849.3
155°	870.9	871.7	871.6	870.8	869.8	868.9	867.9
157.5°	887.7	888.7	888.5	887.3	886.1	884.9	883.7
160°	897.2	898.1	898.0	897.0	895.9	894.8	893.8
162.5°	906.0	907.0	907.0	906.1	905.1	904.2	903.2
165°	917.7	918.9	919.0	917.9	916.8	915.7	914.6
167.5°	926.6	927.8	927.8	926.6	925.3	924.1	922.8
170°	931.6	932.8	932.8	931.6	930.3	929.2	927.9
172.5°	935.0	936.2	936.1	934.8	933.4	932.0	930.7
175°	938.8	939.9	939.8	938.6	937.4	936.1	934.9
177.5°	940.2	941.2	941.1	939.9	938.6	937.4	936.1
180°	938.3	938.3	938.3	938.3	938.3	938.3	938.3

(END OF REPORT)