

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332379-940

Luminaire Tested: **S123RDIP-S1165D1025U940-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332379-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1165D1025U940-4F0-1E-UDD-A1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1025 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7219.2 lumens
Efficiency: N/A
Efficacy: 108.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 66.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332379-940

CATALOG NUMBER: S123RDIP-S1165D1025U940-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P332379-940

CATALOG NUMBER: S123RDIP-S1165D1025U940-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	57
1	100	96	92	89	93	89	86	83	77	75	73	66	65	63	56	55	54	49
2	92	84	79	74	85	79	74	69	68	65	61	59	56	54	50	48	46	42
3	84	75	68	62	78	70	64	59	61	56	52	53	49	46	45	42	40	36
4	77	67	59	53	72	62	56	50	55	49	45	47	43	40	41	38	35	32
5	71	60	52	46	66	56	49	44	49	44	39	43	39	35	37	34	31	28
6	66	54	46	40	61	51	44	38	45	39	35	39	35	31	34	30	28	25
7	61	49	41	36	57	46	39	34	41	35	31	36	31	28	31	27	25	22
8	57	44	37	32	53	42	35	30	37	32	28	33	28	25	28	25	22	20
9	53	41	33	28	49	39	32	27	34	29	25	30	26	23	26	23	20	18
10	49	37	30	26	46	35	29	25	32	26	23	28	24	21	24	21	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	17623	17623	17623	17623
5°	21007	17698	15584	17698
10°	26230	17596	14080	17596
15°	30788	17416	12840	17416
20°	34360	17148	11786	17148
25°	33812	16865	11137	16865
30°	24304	16604	10470	16604
35°	16227	16264	10038	16264
40°	11956	15855	9591	15855
45°	10029	15139	9155	15139
50°	8848	14200	8544	14200
55°	7760	13127	7707	13127
60°	6910	12099	7061	12099
65°	6069	10998	6569	10998
70°	4765	10014	5998	10014
75°	4196	8746	5481	8746
80°	3651	7426	5387	7426
85°	2939	5965	5718	5965



TEST NUMBER: P332379-940

CATALOG NUMBER: S123RDIP-S1165D1025U940-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	161.0	2.2
10°-20°	503.0	7.0
20°-30°	790.2	10.9
30°-40°	824.4	11.4
40°-50°	705.6	9.8
50°-60°	537.8	7.4
60°-70°	344.7	4.8
70°-80°	165.8	2.3
80°-90°	47.2	0.7
90°-100°	73.8	1.0
100°-110°	220.9	3.1
110°-120°	375.8	5.2
120°-130°	494.3	6.8
130°-140°	555.6	7.7
140°-150°	546.1	7.6
150°-160°	459.7	6.4
160°-170°	306.0	4.2
170°-180°	107.2	1.5
0°-30°	1454.2	20.1
0°-40°	2278.7	31.6
0°-60°	3522.0	48.8
0°-90°	4079.7	56.5
90°-120°	670.6	9.3
90°-150°	2266.5	31.4
90°-180°	3139.0	43.5
0°-180°	7219.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1637	1637	1637	1637	1637	
5°	1944	1638	1442	1638	1944	201
15°	2763	1563	1152	1563	2763	783
25°	2847	1420	938	1420	2847	1224
35°	1235	1238	764	1238	1235	810
45°	659	994	601	994	659	518
55°	414	700	411	700	414	374
65°	238	432	258	432	238	234
75°	101	210	132	210	101	108
85°	24	48	46	48	24	28
90°	27	1	27	1	27	14
95°	70	52	70	52	70	71
105°	212	200	212	200	212	225
115°	379	378	379	378	379	375
125°	547	554	547	554	547	489
135°	718	718	718	718	718	552
145°	871	871	871	871	871	544
155°	996	998	996	998	996	459
165°	1083	1087	1083	1087	1083	306
175°	1126	1130	1126	1130	1126	107
180°	1133	1133	1133	1133	1133	



TEST NUMBER: P332379-940

CATALOG NUMBER: S123RDIP-S1165D1025U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2
2.5°	1743.7	1746.0	1738.7	1737.6	1729.1	1726.9	1726.9	1715.1	1707.8	1698.4	1692.7
5°	1944.2	1955.4	1949.8	1937.2	1916.1	1911.2	1897.9	1876.9	1853.1	1823.6	1809.6
7.5°	2194.5	2209.8	2204.0	2184.4	2162.4	2144.7	2107.0	2072.2	2023.2	1980.3	1943.6
10°	2399.8	2383.6	2371.0	2352.1	2331.7	2298.8	2259.6	2205.6	2143.2	2094.2	2039.5
12.5°	2553.3	2550.7	2534.7	2515.2	2486.5	2455.2	2407.0	2341.3	2268.8	2197.9	2135.4
15°	2762.8	2767.0	2756.5	2736.1	2695.5	2640.1	2567.2	2539.9	2436.2	2359.1	2282.0
17.5°	2907.7	2906.9	2905.5	2877.3	2835.8	2796.4	2728.8	2656.9	2563.0	2454.4	2350.5
20°	2999.6	2992.7	2994.1	2962.5	2931.7	2886.1	2820.2	2715.8	2638.8	2513.3	2406.0
22.5°	2997.4	2996.1	3001.3	2990.5	2968.1	2933.2	2881.4	2793.2	2694.8	2568.2	2447.6
25°	2846.9	2841.3	2874.3	2883.3	2919.1	2925.3	2909.9	2861.6	2768.4	2638.0	2488.8
27.5°	2382.7	2379.5	2440.7	2517.2	2614.2	2689.6	2762.5	2797.7	2768.4	2675.0	2525.5
30°	1955.4	2021.2	2052.1	2162.8	2286.2	2433.4	2562.3	2684.9	2715.1	2674.5	2551.8
32.5°	1623.4	1681.0	1706.7	1801.8	1916.7	2089.1	2282.5	2456.2	2578.9	2609.9	2536.1
35°	1234.9	1235.6	1294.5	1336.5	1443.1	1620.4	1808.2	2040.9	2272.2	2447.4	2465.6
37.5°	985.4	988.9	1024.5	1066.4	1146.3	1240.1	1405.5	1598.9	1866.1	2135.1	2292.8
40°	850.9	857.1	883.8	925.1	982.6	1053.4	1182.3	1364.6	1587.4	1886.7	2131.3
42.5°	764.5	774.7	788.5	820.3	855.9	922.2	1026.4	1167.2	1369.9	1652.9	1935.1
45°	658.8	664.4	674.9	689.6	721.8	768.1	838.2	932.8	1101.1	1328.8	1611.2
47.5°	581.1	578.2	589.2	601.2	622.7	654.2	701.2	778.4	898.4	1081.1	1320.7
50°	528.4	527.7	535.5	544.6	564.9	588.0	626.6	684.7	780.1	931.5	1150.8
52.5°	479.1	481.8	487.2	498.6	513.3	532.0	566.6	608.5	690.4	821.0	1003.9
55°	413.5	415.6	423.3	429.6	440.1	459.1	480.8	515.9	571.9	663.0	813.7
57.5°	358.0	357.0	364.4	366.0	377.9	393.3	410.1	437.3	478.0	545.7	647.2
60°	321.0	318.9	325.2	330.1	336.4	349.0	363.0	389.7	422.0	471.7	558.6
62.5°	287.3	286.3	291.0	295.9	301.1	312.5	324.3	344.8	370.3	412.2	481.2
65°	238.3	240.4	242.5	244.6	247.4	254.4	265.6	279.6	297.2	326.6	376.4
67.5°	187.3	189.4	190.1	194.4	200.5	204.8	211.7	224.2	236.3	261.2	289.4
70°	151.4	150.7	151.4	153.5	161.2	168.9	178.0	187.2	194.8	212.3	236.2
72.5°	130.1	128.9	130.6	131.1	134.8	137.0	142.7	151.2	161.2	173.1	190.2
75°	100.9	100.9	100.9	100.9	103.7	105.1	107.3	109.3	112.8	118.4	131.1
77.5°	74.5	74.7	75.7	76.4	77.0	77.8	79.1	81.1	82.4	85.3	90.9
80°	58.9	59.6	58.9	59.6	59.6	61.0	61.7	63.8	64.5	67.9	70.1
82.5°	44.3	43.9	44.3	45.0	45.0	46.4	46.5	48.1	48.2	50.0	52.2
85°	23.8	22.5	23.8	23.1	24.5	23.1	23.8	25.2	25.2	25.9	28.7
87.5°	11.0	11.9	10.8	11.2	11.2	11.6	11.5	11.3	12.3	11.6	11.6
90°	26.7	26.3	25.9	25.5	25.1	24.5	23.7	22.9	22.1	21.4	18.8
92.5°	35.9	36.2	36.5	36.6	36.9	36.7	36.1	35.5	34.8	34.2	32.7
95°	69.5	69.5	69.5	69.5	69.5	69.0	68.2	67.4	66.7	65.9	64.3
97.5°	106.8	106.9	107.0	107.1	107.1	106.7	105.8	104.9	104.0	103.1	101.9
100°	135.3	134.9	134.5	134.1	133.8	133.2	132.6	132.1	131.4	130.8	129.8
102.5°	164.5	164.6	164.6	164.7	164.8	164.5	164.0	163.4	162.7	162.2	160.9
105°	211.9	211.4	211.1	210.6	210.3	210.1	210.1	210.1	210.1	210.1	208.3
107.5°	261.2	261.4	261.6	261.9	262.1	261.9	261.3	260.6	260.0	259.4	258.7
110°	294.6	295.1	295.4	295.8	296.2	296.0	295.2	294.4	293.6	292.8	292.5



TEST NUMBER: P332379-940

CATALOG NUMBER: S123RDIP-S1165D1025U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	330.2	330.3	330.4	330.5	330.6	330.1	329.1	328.2	327.3	326.3	326.3
115°	379.2	379.4	379.6	379.8	380.0	380.0	379.8	379.6	379.4	379.2	379.6
117.5°	428.8	429.4	430.0	430.5	431.1	431.4	431.4	431.4	431.5	431.5	432.0
120°	463.8	464.1	464.6	464.9	465.3	465.7	465.8	466.0	466.2	466.5	467.4
122.5°	497.2	497.8	498.3	498.9	499.4	500.0	500.5	501.0	501.5	502.0	502.6
125°	547.4	548.2	549.0	549.8	550.5	551.3	552.1	552.9	553.8	554.6	554.9
127.5°	597.4	598.3	599.2	600.2	601.1	602.1	603.2	604.3	605.4	606.5	607.0
130°	630.2	631.6	632.9	634.4	635.7	636.9	637.6	638.4	639.2	640.0	640.6
132.5°	664.4	665.5	666.6	667.6	668.7	669.7	670.7	671.5	672.5	673.4	673.9
135°	717.5	717.8	718.2	718.6	719.0	719.6	720.4	721.2	722.0	722.7	723.0
137.5°	764.3	765.0	765.7	766.5	767.2	768.0	768.9	769.7	770.5	771.3	770.9
140°	794.9	796.3	797.6	799.1	800.4	801.2	801.4	801.6	801.8	802.0	801.8
142.5°	826.2	827.2	828.3	829.4	830.5	831.1	831.3	831.5	831.7	831.9	831.5
145°	871.4	872.2	873.0	873.8	874.6	875.0	875.3	875.5	875.7	875.8	875.3
147.5°	911.7	912.8	914.0	915.3	916.4	917.0	917.0	917.0	917.0	917.0	916.4
150°	937.3	938.4	939.7	940.8	942.0	942.6	942.6	942.6	942.6	942.6	942.3
152.5°	962.2	963.2	964.3	965.3	966.3	966.7	966.3	966.1	965.7	965.5	965.2
155°	996.0	997.4	998.8	1000.2	1001.6	1001.8	1001.1	1000.3	999.5	998.7	998.5
157.5°	1026.8	1028.0	1029.0	1030.2	1031.3	1031.4	1030.6	1029.7	1028.9	1028.1	1028.0
160°	1046.8	1047.6	1048.4	1049.2	1049.9	1049.8	1048.8	1047.8	1046.9	1045.9	1045.9
162.5°	1061.8	1063.0	1064.3	1065.5	1066.8	1066.9	1066.0	1065.0	1064.0	1063.0	1062.8
165°	1083.3	1084.7	1086.0	1087.4	1088.8	1088.9	1087.7	1086.5	1085.3	1084.1	1084.1
167.5°	1101.6	1102.9	1104.0	1105.3	1106.5	1106.5	1105.3	1104.0	1102.9	1101.6	1101.4
170°	1110.9	1112.2	1113.7	1115.0	1116.4	1116.4	1115.0	1113.7	1112.2	1110.9	1110.9
172.5°	1117.9	1119.4	1120.8	1122.1	1123.6	1123.6	1122.4	1121.1	1119.9	1118.7	1118.7
175°	1126.0	1127.4	1128.7	1130.2	1131.5	1131.7	1130.4	1129.3	1128.1	1126.9	1126.9
177.5°	1130.2	1131.4	1132.5	1133.6	1134.7	1134.8	1133.8	1132.9	1131.9	1131.0	1131.0
180°	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1



TEST NUMBER: P332379-940

CATALOG NUMBER: S123RDIP-S1165D1025U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2
2.5°	1690.5	1688.8	1681.0	1672.0	1660.2	1652.3	1646.2	1642.8	1632.7	1620.4	1611.9
5°	1794.9	1773.9	1751.4	1724.1	1698.9	1672.9	1656.8	1637.9	1614.8	1588.9	1570.7
7.5°	1906.7	1865.5	1821.1	1775.3	1730.0	1689.3	1653.5	1622.7	1585.9	1548.7	1522.7
10°	1992.5	1932.2	1869.9	1806.1	1747.9	1693.3	1651.2	1609.9	1565.8	1523.0	1490.8
12.5°	2070.5	1991.1	1919.2	1840.8	1766.5	1701.1	1640.6	1591.9	1538.8	1493.3	1456.5
15°	2169.2	2087.9	2000.9	1881.8	1783.0	1700.3	1626.7	1562.9	1498.4	1442.3	1406.6
17.5°	2261.4	2139.0	2022.2	1922.9	1794.5	1691.1	1601.3	1525.1	1454.3	1394.8	1350.9
20°	2299.5	2181.0	2054.2	1927.3	1801.2	1685.6	1581.1	1497.0	1423.4	1356.1	1315.5
22.5°	2322.5	2188.3	2054.8	1918.4	1784.4	1664.3	1560.9	1468.5	1388.7	1324.7	1274.6
25°	2349.3	2189.5	2042.3	1907.7	1771.0	1640.7	1518.0	1420.0	1333.7	1265.8	1212.5
27.5°	2367.0	2179.0	2005.0	1855.5	1716.8	1587.0	1474.6	1370.6	1283.2	1211.2	1154.1
30°	2370.3	2170.5	1976.4	1814.5	1673.7	1554.5	1435.4	1335.9	1243.3	1166.9	1113.7
32.5°	2374.8	2149.8	1937.7	1765.8	1621.5	1503.5	1395.5	1300.5	1205.8	1130.5	1076.1
35°	2356.3	2138.3	1879.0	1681.3	1537.0	1422.7	1325.3	1237.7	1144.5	1071.6	1016.3
37.5°	2276.6	2092.8	1818.2	1586.4	1435.4	1329.5	1250.2	1173.8	1088.3	1009.7	957.5
40°	2196.5	2047.9	1771.0	1528.6	1370.9	1262.2	1190.8	1128.4	1045.7	972.1	916.1
42.5°	2077.1	1986.8	1726.2	1468.0	1298.0	1193.3	1133.0	1074.5	1001.9	927.2	874.5
45°	1858.0	1869.9	1634.4	1371.5	1197.0	1091.9	1035.2	994.5	930.1	868.3	814.4
47.5°	1583.2	1694.7	1526.6	1268.8	1090.7	992.0	942.4	906.9	863.4	802.9	753.7
50°	1403.8	1562.9	1440.3	1199.9	1024.0	925.9	876.7	848.0	810.2	762.5	715.6
52.5°	1238.4	1409.3	1336.0	1123.0	951.6	861.9	814.0	790.3	760.3	715.4	673.0
55°	1010.0	1183.0	1166.3	1007.1	843.1	762.5	726.1	699.5	679.1	645.5	611.9
57.5°	816.9	981.1	989.7	878.2	747.5	667.9	636.5	616.4	603.2	577.8	546.7
60°	695.3	846.0	875.4	791.3	679.1	609.0	578.2	562.0	551.6	531.3	507.4
62.5°	594.3	722.6	755.9	695.4	613.5	548.0	523.8	508.3	501.1	483.6	462.5
65°	454.9	561.4	593.6	560.0	517.2	464.7	445.1	431.8	425.4	415.6	400.2
67.5°	342.1	419.6	455.0	431.3	415.9	382.6	370.1	363.0	357.4	350.7	337.8
70°	274.7	332.2	368.6	362.3	349.7	332.2	323.1	318.2	312.5	307.0	295.8
72.5°	220.9	260.5	294.6	297.8	287.5	284.0	276.0	273.9	270.5	263.8	257.6
75°	146.5	173.8	197.6	206.8	211.0	214.5	211.0	210.3	209.6	203.9	200.5
77.5°	96.0	110.8	125.7	141.3	147.8	152.7	153.7	156.3	154.4	151.5	149.8
80°	73.6	77.1	87.6	100.9	111.5	115.7	118.4	119.8	119.1	118.4	115.7
82.5°	53.4	56.4	61.3	70.6	79.5	86.5	88.2	87.9	89.4	89.9	87.6
85°	28.7	29.4	30.9	32.3	37.2	44.9	47.0	48.3	49.8	49.8	45.6
87.5°	12.2	11.1	11.8	11.3	12.6	12.8	15.7	18.1	19.1	17.2	17.7
90°	16.2	13.6	11.1	8.8	6.9	4.8	2.9	0.9	2.9	4.8	6.9
92.5°	31.2	29.8	28.4	26.9	25.6	24.3	22.9	21.6	22.9	24.3	25.6
95°	62.7	61.1	59.6	58.1	56.7	55.3	53.9	52.5	53.9	55.3	56.7
97.5°	100.8	99.6	98.4	97.4	96.4	95.3	94.3	93.3	94.3	95.3	96.4
100°	128.9	127.9	126.9	125.8	124.6	123.4	122.3	121.1	122.3	123.4	124.6
102.5°	159.5	158.3	156.9	156.0	155.2	154.5	153.8	153.1	153.8	154.5	155.2
105°	206.5	204.7	203.0	201.9	201.4	201.1	200.6	200.3	200.6	201.1	201.4
107.5°	258.0	257.3	256.5	256.1	255.8	255.6	255.4	255.1	255.4	255.6	255.8
110°	292.0	291.7	291.2	290.9	290.4	290.1	289.7	289.3	289.7	290.1	290.4



TEST NUMBER: P332379-940

CATALOG NUMBER: S123RDIP-S1165D1025U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	326.2	326.1	326.0	325.8	325.6	325.4	325.1	324.9	325.1	325.4	325.6
115°	380.0	380.4	380.8	380.7	380.0	379.5	378.9	378.3	378.9	379.5	380.0
117.5°	432.6	433.1	433.5	433.6	433.3	432.8	432.5	432.0	432.5	432.8	433.3
120°	468.4	469.4	470.4	470.3	469.1	467.9	466.7	465.6	466.7	467.9	469.1
122.5°	503.0	503.5	504.1	503.9	503.0	502.1	501.3	500.4	501.3	502.1	503.0
125°	555.4	555.7	556.2	556.0	555.4	554.8	554.3	553.7	554.3	554.8	555.4
127.5°	607.4	607.8	608.2	607.9	606.5	605.3	604.0	602.8	604.0	605.3	606.5
130°	641.1	641.8	642.4	641.9	640.2	638.7	637.1	635.5	637.1	638.7	640.2
132.5°	674.3	674.8	675.2	674.7	673.1	671.5	669.9	668.3	669.9	671.5	673.1
135°	723.2	723.4	723.5	723.1	721.8	720.7	719.5	718.4	719.5	720.7	721.8
137.5°	770.3	769.8	769.3	768.6	767.6	766.6	765.6	764.6	765.6	766.6	767.6
140°	801.6	801.4	801.2	800.6	799.6	798.6	797.6	796.7	797.6	798.6	799.6
142.5°	831.2	830.8	830.5	829.8	828.8	827.9	826.8	825.8	826.8	827.9	828.8
145°	874.7	874.1	873.5	873.0	872.6	872.2	871.8	871.4	871.8	872.2	872.6
147.5°	915.9	915.3	914.8	914.2	913.5	912.8	912.0	911.3	912.0	912.8	913.5
150°	941.8	941.5	941.0	940.7	940.2	939.9	939.5	939.1	939.5	939.9	940.2
152.5°	964.9	964.7	964.5	964.0	963.5	963.0	962.4	961.9	962.4	963.0	963.5
155°	998.3	998.1	997.9	997.8	997.8	997.8	997.8	997.8	997.8	997.8	997.8
157.5°	1027.8	1027.6	1027.4	1027.5	1027.7	1028.0	1028.2	1028.4	1028.2	1028.0	1027.7
160°	1045.9	1045.9	1045.9	1046.1	1046.5	1046.9	1047.2	1047.7	1047.2	1046.9	1046.5
162.5°	1062.7	1062.5	1062.4	1062.6	1063.1	1063.6	1064.2	1064.8	1064.2	1063.6	1063.1
165°	1084.1	1084.1	1084.1	1084.5	1085.0	1085.7	1086.2	1086.8	1086.2	1085.7	1085.0
167.5°	1101.3	1101.2	1101.0	1101.3	1102.1	1102.9	1103.7	1104.5	1103.7	1102.9	1102.1
170°	1110.9	1110.9	1110.9	1111.3	1112.1	1112.9	1113.7	1114.5	1113.7	1112.9	1112.1
172.5°	1118.7	1118.7	1118.7	1119.1	1119.9	1120.7	1121.5	1122.2	1121.5	1120.7	1119.9
175°	1126.9	1126.9	1126.9	1127.3	1128.1	1128.8	1129.6	1130.4	1129.6	1128.8	1128.1
177.5°	1131.0	1131.0	1131.0	1131.3	1131.9	1132.6	1133.2	1133.8	1133.2	1132.6	1131.9
180°	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1



TEST NUMBER: P332379-940

CATALOG NUMBER: S123RDIP-S1165D1025U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2
2.5°	1609.2	1601.9	1596.9	1585.6	1578.3	1570.5	1562.6	1567.7	1567.1	1566.6	1566.6
5°	1555.2	1539.1	1524.4	1505.5	1493.5	1478.8	1467.6	1466.2	1469.0	1459.2	1453.6
7.5°	1501.6	1479.6	1458.7	1437.9	1415.8	1398.1	1387.0	1381.8	1374.7	1368.6	1362.4
10°	1464.1	1438.2	1417.8	1391.9	1368.1	1347.0	1333.7	1324.6	1319.7	1314.8	1305.7
12.5°	1425.4	1400.1	1374.1	1344.8	1322.1	1297.7	1287.7	1277.6	1268.1	1262.7	1250.2
15°	1368.8	1335.9	1308.5	1277.6	1252.4	1228.6	1214.6	1194.3	1191.4	1184.5	1171.8
17.5°	1312.0	1276.2	1238.6	1215.7	1187.2	1162.4	1141.1	1134.3	1114.2	1106.6	1095.7
20°	1267.1	1234.2	1205.5	1175.4	1134.0	1110.9	1094.0	1084.9	1068.8	1059.0	1052.0
22.5°	1228.4	1195.0	1161.7	1126.6	1092.5	1066.6	1054.3	1040.1	1031.3	1017.5	1010.0
25°	1173.2	1136.8	1096.8	1059.0	1034.5	1014.9	995.2	982.6	970.0	963.7	949.7
27.5°	1109.0	1070.9	1033.6	1004.9	974.7	955.4	937.6	926.4	911.2	900.6	892.9
30°	1073.7	1028.9	996.6	970.7	932.1	913.9	900.6	886.6	875.4	864.2	856.5
32.5°	1032.8	991.8	961.3	929.2	899.6	879.7	862.5	850.2	840.6	829.9	822.2
35°	968.6	934.2	902.7	870.5	848.7	828.4	808.1	797.5	788.5	778.6	771.7
37.5°	910.5	878.4	848.5	817.9	790.9	774.5	758.0	750.0	737.7	731.1	724.0
40°	874.7	843.1	810.9	781.5	753.4	740.8	726.1	714.2	702.9	698.0	690.4
42.5°	835.4	803.9	776.7	745.0	722.0	704.9	691.3	678.3	669.9	662.7	658.4
45°	777.2	749.2	722.6	691.1	669.3	654.6	639.2	627.2	619.6	614.7	606.9
47.5°	720.8	692.8	665.7	638.2	617.2	600.4	585.0	576.7	566.4	560.4	555.2
50°	679.8	654.6	625.9	600.7	579.6	562.8	550.2	539.7	530.6	522.8	519.3
52.5°	642.3	615.4	590.6	566.9	544.8	525.8	514.2	503.2	496.3	487.5	483.5
55°	580.3	554.4	533.3	510.2	488.5	472.3	458.3	448.5	441.6	431.8	426.1
57.5°	522.1	498.9	473.8	453.7	431.3	417.7	406.1	392.8	384.2	376.5	371.0
60°	482.9	456.3	434.5	415.6	396.0	378.4	367.9	357.4	348.3	340.6	335.7
62.5°	441.9	418.7	398.1	377.5	359.5	344.3	332.1	323.2	315.2	310.3	305.4
65°	379.2	361.0	339.9	323.1	306.3	295.1	285.3	277.5	272.0	268.4	264.2
67.5°	321.4	303.7	285.3	268.9	257.6	249.1	242.6	236.0	233.3	228.7	226.0
70°	283.8	265.6	249.5	236.9	225.7	219.4	215.2	210.3	207.4	201.9	199.0
72.5°	242.9	229.7	218.1	207.8	198.8	193.1	187.7	181.6	177.2	171.0	168.2
75°	191.4	179.4	170.3	163.3	157.7	150.0	142.3	136.0	133.8	131.8	131.1
77.5°	141.7	134.1	127.5	121.6	114.7	109.1	107.4	105.9	105.6	104.4	104.4
80°	111.5	104.4	99.5	92.5	88.3	88.3	88.3	86.9	87.6	87.6	87.6
82.5°	82.8	76.4	73.7	71.2	70.4	70.9	70.9	71.2	70.8	71.9	71.3
85°	42.7	43.4	44.9	44.1	44.9	44.9	46.3	45.6	46.3	44.9	46.3
87.5°	17.5	19.6	20.7	21.8	22.8	22.7	23.5	23.6	24.3	24.5	24.6
90°	8.8	11.1	13.6	16.2	18.8	21.4	22.1	22.9	23.7	24.5	25.1
92.5°	26.9	28.4	29.8	31.2	32.7	34.2	34.8	35.5	36.1	36.7	36.9
95°	58.1	59.6	61.1	62.7	64.3	65.9	66.7	67.4	68.2	69.0	69.5
97.5°	97.4	98.4	99.6	100.8	101.9	103.1	104.0	104.9	105.8	106.7	107.1
100°	125.8	126.9	127.9	128.9	129.8	130.8	131.4	132.1	132.6	133.2	133.8
102.5°	156.0	156.9	158.3	159.5	160.9	162.2	162.7	163.4	164.0	164.5	164.8
105°	201.9	203.0	204.7	206.5	208.3	210.1	210.1	210.1	210.1	210.1	210.3
107.5°	256.1	256.5	257.3	258.0	258.7	259.4	260.0	260.6	261.3	261.9	262.1
110°	290.9	291.2	291.7	292.0	292.5	292.8	293.6	294.4	295.2	296.0	296.2



TEST NUMBER: P332379-940

CATALOG NUMBER: S123RDIP-S1165D1025U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	325.8	326.0	326.1	326.2	326.3	326.3	327.3	328.2	329.1	330.1	330.6
115°	380.7	380.8	380.4	380.0	379.6	379.2	379.4	379.6	379.8	380.0	380.0
117.5°	433.6	433.5	433.1	432.6	432.0	431.5	431.5	431.4	431.4	431.4	431.1
120°	470.3	470.4	469.4	468.4	467.4	466.5	466.2	466.0	465.8	465.7	465.3
122.5°	503.9	504.1	503.5	503.0	502.6	502.0	501.5	501.0	500.5	500.0	499.4
125°	556.0	556.2	555.7	555.4	554.9	554.6	553.8	552.9	552.1	551.3	550.5
127.5°	607.9	608.2	607.8	607.4	607.0	606.5	605.4	604.3	603.2	602.1	601.1
130°	641.9	642.4	641.8	641.1	640.6	640.0	639.2	638.4	637.6	636.9	635.7
132.5°	674.7	675.2	674.8	674.3	673.9	673.4	672.5	671.5	670.7	669.7	668.7
135°	723.1	723.5	723.4	723.2	723.0	722.7	722.0	721.2	720.4	719.6	719.0
137.5°	768.6	769.3	769.8	770.3	770.9	771.3	770.5	769.7	768.9	768.0	767.2
140°	800.6	801.2	801.4	801.6	801.8	802.0	801.8	801.6	801.4	801.2	800.4
142.5°	829.8	830.5	830.8	831.2	831.5	831.9	831.7	831.5	831.3	831.1	830.5
145°	873.0	873.5	874.1	874.7	875.3	875.8	875.7	875.5	875.3	875.0	874.6
147.5°	914.2	914.8	915.3	915.9	916.4	917.0	917.0	917.0	917.0	917.0	916.4
150°	940.7	941.0	941.5	941.8	942.3	942.6	942.6	942.6	942.6	942.6	942.0
152.5°	964.0	964.5	964.7	964.9	965.2	965.5	965.7	966.1	966.3	966.7	966.3
155°	997.8	997.9	998.1	998.3	998.5	998.7	999.5	1000.3	1001.1	1001.8	1001.6
157.5°	1027.5	1027.4	1027.6	1027.8	1028.0	1028.1	1028.9	1029.7	1030.6	1031.4	1031.3
160°	1046.1	1045.9	1045.9	1045.9	1045.9	1045.9	1046.9	1047.8	1048.8	1049.8	1049.9
162.5°	1062.6	1062.4	1062.5	1062.7	1062.8	1063.0	1064.0	1065.0	1066.0	1066.9	1066.8
165°	1084.5	1084.1	1084.1	1084.1	1084.1	1084.1	1085.3	1086.5	1087.7	1088.9	1088.8
167.5°	1101.3	1101.0	1101.2	1101.3	1101.4	1101.6	1102.9	1104.0	1105.3	1106.5	1106.5
170°	1111.3	1110.9	1110.9	1110.9	1110.9	1110.9	1112.2	1113.7	1115.0	1116.4	1116.4
172.5°	1119.1	1118.7	1118.7	1118.7	1118.7	1118.7	1119.9	1121.1	1122.4	1123.6	1123.6
175°	1127.3	1126.9	1126.9	1126.9	1126.9	1126.9	1128.1	1129.3	1130.4	1131.7	1131.5
177.5°	1131.3	1131.0	1131.0	1131.0	1131.0	1131.0	1131.9	1132.9	1133.8	1134.8	1134.7
180°	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1



TEST NUMBER: P332379-940

CATALOG NUMBER: S123RDIP-S1165D1025U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2
2.5°	1559.9	1559.2	1559.9	1557.6	1559.9	1559.2	1559.9	1566.6	1566.6	1567.1	1567.7
5°	1451.4	1450.8	1448.7	1442.3	1448.7	1450.8	1451.4	1453.6	1459.2	1469.0	1466.2
7.5°	1356.8	1355.8	1349.7	1349.9	1349.7	1355.8	1356.8	1362.4	1368.6	1374.7	1381.8
10°	1300.8	1301.5	1293.1	1288.2	1293.1	1301.5	1300.8	1305.7	1314.8	1319.7	1324.6
12.5°	1246.4	1243.2	1236.4	1231.0	1236.4	1243.2	1246.4	1250.2	1262.7	1268.1	1277.6
15°	1174.7	1167.6	1150.8	1152.2	1150.8	1167.6	1174.7	1171.8	1184.5	1191.4	1194.3
17.5°	1090.1	1084.9	1084.7	1074.9	1084.7	1084.9	1090.1	1095.7	1106.6	1114.2	1134.3
20°	1040.8	1037.2	1038.7	1028.9	1038.7	1037.2	1040.8	1052.0	1059.0	1068.8	1084.9
22.5°	1002.1	998.5	992.7	989.6	992.7	998.5	1002.1	1010.0	1017.5	1031.3	1040.1
25°	945.5	939.9	934.2	937.7	934.2	939.9	945.5	949.7	963.7	970.0	982.6
27.5°	888.9	884.7	879.0	878.3	879.0	884.7	888.9	892.9	900.6	911.2	926.4
30°	852.9	848.7	846.0	842.4	846.0	848.7	852.9	856.5	864.2	875.4	886.6
32.5°	816.5	815.6	810.7	809.9	810.7	815.6	816.5	822.2	829.9	840.6	850.2
35°	768.8	764.6	763.2	763.9	763.2	764.6	768.8	771.7	778.6	788.5	797.5
37.5°	723.5	717.9	715.4	712.9	715.4	717.9	723.5	724.0	731.1	737.7	750.0
40°	691.1	685.5	684.0	682.6	684.0	685.5	691.1	690.4	698.0	702.9	714.2
42.5°	654.6	652.4	651.5	649.0	651.5	652.4	654.6	658.4	662.7	669.9	678.3
45°	604.8	604.1	599.9	601.4	599.9	604.1	604.8	606.9	614.7	619.6	627.2
47.5°	552.4	549.3	546.4	548.3	546.4	549.3	552.4	555.2	560.4	566.4	576.7
50°	516.6	515.1	508.8	510.2	508.8	515.1	516.6	519.3	522.8	530.6	539.7
52.5°	480.6	475.3	473.0	472.1	473.0	475.3	480.6	483.5	487.5	496.3	503.2
55°	421.2	414.9	412.1	410.7	412.1	414.9	421.2	426.1	431.8	441.6	448.5
57.5°	362.9	361.2	359.0	360.5	359.0	361.2	362.9	371.0	376.5	384.2	392.8
60°	328.7	328.7	328.7	328.0	328.7	328.7	328.7	335.7	340.6	348.3	357.4
62.5°	302.4	300.7	300.1	301.1	300.1	300.7	302.4	305.4	310.3	315.2	323.2
65°	262.2	261.4	258.6	257.9	258.6	261.4	262.2	264.2	268.4	272.0	277.5
67.5°	224.2	221.6	220.8	219.8	220.8	221.6	224.2	226.0	228.7	233.3	236.0
70°	195.6	194.1	189.9	190.6	189.9	194.1	195.6	199.0	201.9	207.4	210.3
72.5°	164.7	163.3	162.5	161.5	162.5	163.3	164.7	168.2	171.0	177.2	181.6
75°	130.4	129.7	128.9	131.8	128.9	129.7	130.4	131.1	131.8	133.8	136.0
77.5°	104.4	104.4	104.9	103.7	104.9	104.4	104.4	104.4	104.4	105.6	105.9
80°	87.6	87.6	86.9	86.9	86.9	87.6	87.6	87.6	87.6	87.6	86.9
82.5°	70.3	70.8	71.2	70.1	71.2	70.8	70.3	71.3	71.9	70.8	71.2
85°	46.3	45.6	47.0	46.3	47.0	45.6	46.3	46.3	44.9	46.3	45.6
87.5°	25.9	24.8	24.9	25.5	24.9	24.8	25.9	24.6	24.5	24.3	23.6
90°	25.5	25.9	26.3	26.7	26.3	25.9	25.5	25.1	24.5	23.7	22.9
92.5°	36.6	36.5	36.2	35.9	36.2	36.5	36.6	36.9	36.7	36.1	35.5
95°	69.5	69.5	69.5	69.5	69.5	69.5	69.5	69.5	69.0	68.2	67.4
97.5°	107.1	107.0	106.9	106.8	106.9	107.0	107.1	107.1	106.7	105.8	104.9
100°	134.1	134.5	134.9	135.3	134.9	134.5	134.1	133.8	133.2	132.6	132.1
102.5°	164.7	164.6	164.6	164.5	164.6	164.6	164.7	164.8	164.5	164.0	163.4
105°	210.6	211.1	211.4	211.9	211.4	211.1	210.6	210.3	210.1	210.1	210.1
107.5°	261.9	261.6	261.4	261.2	261.4	261.6	261.9	262.1	261.9	261.3	260.6
110°	295.8	295.4	295.1	294.6	295.1	295.4	295.8	296.2	296.0	295.2	294.4



TEST NUMBER: P332379-940

CATALOG NUMBER: S123RDIP-S1165D1025U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	330.5	330.4	330.3	330.2	330.3	330.4	330.5	330.6	330.1	329.1	328.2
115°	379.8	379.6	379.4	379.2	379.4	379.6	379.8	380.0	380.0	379.8	379.6
117.5°	430.5	430.0	429.4	428.8	429.4	430.0	430.5	431.1	431.4	431.4	431.4
120°	464.9	464.6	464.1	463.8	464.1	464.6	464.9	465.3	465.7	465.8	466.0
122.5°	498.9	498.3	497.8	497.2	497.8	498.3	498.9	499.4	500.0	500.5	501.0
125°	549.8	549.0	548.2	547.4	548.2	549.0	549.8	550.5	551.3	552.1	552.9
127.5°	600.2	599.2	598.3	597.4	598.3	599.2	600.2	601.1	602.1	603.2	604.3
130°	634.4	632.9	631.6	630.2	631.6	632.9	634.4	635.7	636.9	637.6	638.4
132.5°	667.6	666.6	665.5	664.4	665.5	666.6	667.6	668.7	669.7	670.7	671.5
135°	718.6	718.2	717.8	717.5	717.8	718.2	718.6	719.0	719.6	720.4	721.2
137.5°	766.5	765.7	765.0	764.3	765.0	765.7	766.5	767.2	768.0	768.9	769.7
140°	799.1	797.6	796.3	794.9	796.3	797.6	799.1	800.4	801.2	801.4	801.6
142.5°	829.4	828.3	827.2	826.2	827.2	828.3	829.4	830.5	831.1	831.3	831.5
145°	873.8	873.0	872.2	871.4	872.2	873.0	873.8	874.6	875.0	875.3	875.5
147.5°	915.3	914.0	912.8	911.7	912.8	914.0	915.3	916.4	917.0	917.0	917.0
150°	940.8	939.7	938.4	937.3	938.4	939.7	940.8	942.0	942.6	942.6	942.6
152.5°	965.3	964.3	963.2	962.2	963.2	964.3	965.3	966.3	966.7	966.3	966.1
155°	1000.2	998.8	997.4	996.0	997.4	998.8	1000.2	1001.6	1001.8	1001.1	1000.3
157.5°	1030.2	1029.0	1028.0	1026.8	1028.0	1029.0	1030.2	1031.3	1031.4	1030.6	1029.7
160°	1049.2	1048.4	1047.6	1046.8	1047.6	1048.4	1049.2	1049.9	1049.8	1048.8	1047.8
162.5°	1065.5	1064.3	1063.0	1061.8	1063.0	1064.3	1065.5	1066.8	1066.9	1066.0	1065.0
165°	1087.4	1086.0	1084.7	1083.3	1084.7	1086.0	1087.4	1088.8	1088.9	1087.7	1086.5
167.5°	1105.3	1104.0	1102.9	1101.6	1102.9	1104.0	1105.3	1106.5	1106.5	1105.3	1104.0
170°	1115.0	1113.7	1112.2	1110.9	1112.2	1113.7	1115.0	1116.4	1116.4	1115.0	1113.7
172.5°	1122.1	1120.8	1119.4	1117.9	1119.4	1120.8	1122.1	1123.6	1123.6	1122.4	1121.1
175°	1130.2	1128.7	1127.4	1126.0	1127.4	1128.7	1130.2	1131.5	1131.7	1130.4	1129.3
177.5°	1133.6	1132.5	1131.4	1130.2	1131.4	1132.5	1133.6	1134.7	1134.8	1133.8	1132.9
180°	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1



TEST NUMBER: P332379-940

CATALOG NUMBER: S123RDIP-S1165D1025U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2
2.5°	1562.6	1570.5	1578.3	1585.6	1596.9	1601.9	1609.2	1611.9	1620.4	1632.7	1642.8
5°	1467.6	1478.8	1493.5	1505.5	1524.4	1539.1	1555.2	1570.7	1588.9	1614.8	1637.9
7.5°	1387.0	1398.1	1415.8	1437.9	1458.7	1479.6	1501.6	1522.7	1548.7	1585.9	1622.7
10°	1333.7	1347.0	1368.1	1391.9	1417.8	1438.2	1464.1	1490.8	1523.0	1565.8	1609.9
12.5°	1287.7	1297.7	1322.1	1344.8	1374.1	1400.1	1425.4	1456.5	1493.3	1538.8	1591.9
15°	1214.6	1228.6	1252.4	1277.6	1308.5	1335.9	1368.8	1406.6	1442.3	1498.4	1562.9
17.5°	1141.1	1162.4	1187.2	1215.7	1238.6	1276.2	1312.0	1350.9	1394.8	1454.3	1525.1
20°	1094.0	1110.9	1134.0	1175.4	1205.5	1234.2	1267.1	1315.5	1356.1	1423.4	1497.0
22.5°	1054.3	1066.6	1092.5	1126.6	1161.7	1195.0	1228.4	1274.6	1324.7	1388.7	1468.5
25°	995.2	1014.9	1034.5	1059.0	1096.8	1136.8	1173.2	1212.5	1265.8	1333.7	1420.0
27.5°	937.6	955.4	974.7	1004.9	1033.6	1070.9	1109.0	1154.1	1211.2	1283.2	1370.6
30°	900.6	913.9	932.1	970.7	996.6	1028.9	1073.7	1113.7	1166.9	1243.3	1335.9
32.5°	862.5	879.7	899.6	929.2	961.3	991.8	1032.8	1076.1	1130.5	1205.8	1300.5
35°	808.1	828.4	848.7	870.5	902.7	934.2	968.6	1016.3	1071.6	1144.5	1237.7
37.5°	758.0	774.5	790.9	817.9	848.5	878.4	910.5	957.5	1009.7	1088.3	1173.8
40°	726.1	740.8	753.4	781.5	810.9	843.1	874.7	916.1	972.1	1045.7	1128.4
42.5°	691.3	704.9	722.0	745.0	776.7	803.9	835.4	874.5	927.2	1001.9	1074.5
45°	639.2	654.6	669.3	691.1	722.6	749.2	777.2	814.4	868.3	930.1	994.5
47.5°	585.0	600.4	617.2	638.2	665.7	692.8	720.8	753.7	802.9	863.4	906.9
50°	550.2	562.8	579.6	600.7	625.9	654.6	679.8	715.6	762.5	810.2	848.0
52.5°	514.2	525.8	544.8	566.9	590.6	615.4	642.3	673.0	715.4	760.3	790.3
55°	458.3	472.3	488.5	510.2	533.3	554.4	580.3	611.9	645.5	679.1	699.5
57.5°	406.1	417.7	431.3	453.7	473.8	498.9	522.1	546.7	577.8	603.2	616.4
60°	367.9	378.4	396.0	415.6	434.5	456.3	482.9	507.4	531.3	551.6	562.0
62.5°	332.1	344.3	359.5	377.5	398.1	418.7	441.9	462.5	483.6	501.1	508.3
65°	285.3	295.1	306.3	323.1	339.9	361.0	379.2	400.2	415.6	425.4	431.8
67.5°	242.6	249.1	257.6	268.9	285.3	303.7	321.4	337.8	350.7	357.4	363.0
70°	215.2	219.4	225.7	236.9	249.5	265.6	283.8	295.8	307.0	312.5	318.2
72.5°	187.7	193.1	198.8	207.8	218.1	229.7	242.9	257.6	263.8	270.5	273.9
75°	142.3	150.0	157.7	163.3	170.3	179.4	191.4	200.5	203.9	209.6	210.3
77.5°	107.4	109.1	114.7	121.6	127.5	134.1	141.7	149.8	151.5	154.4	156.3
80°	88.3	88.3	88.3	92.5	99.5	104.4	111.5	115.7	118.4	119.1	119.8
82.5°	70.9	70.9	70.4	71.2	73.7	76.4	82.8	87.6	89.9	89.4	87.9
85°	46.3	44.9	44.9	44.1	44.9	43.4	42.7	45.6	49.8	49.8	48.3
87.5°	23.5	22.7	22.8	21.8	20.7	19.6	17.5	17.7	17.2	19.1	18.1
90°	22.1	21.4	18.8	16.2	13.6	11.1	8.8	6.9	4.8	2.9	0.9
92.5°	34.8	34.2	32.7	31.2	29.8	28.4	26.9	25.6	24.3	22.9	21.6
95°	66.7	65.9	64.3	62.7	61.1	59.6	58.1	56.7	55.3	53.9	52.5
97.5°	104.0	103.1	101.9	100.8	99.6	98.4	97.4	96.4	95.3	94.3	93.3
100°	131.4	130.8	129.8	128.9	127.9	126.9	125.8	124.6	123.4	122.3	121.1
102.5°	162.7	162.2	160.9	159.5	158.3	156.9	156.0	155.2	154.5	153.8	153.1
105°	210.1	210.1	208.3	206.5	204.7	203.0	201.9	201.4	201.1	200.6	200.3
107.5°	260.0	259.4	258.7	258.0	257.3	256.5	256.1	255.8	255.6	255.4	255.1
110°	293.6	292.8	292.5	292.0	291.7	291.2	290.9	290.4	290.1	289.7	289.3



TEST NUMBER: P332379-940

CATALOG NUMBER: S123RDIP-S1165D1025U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	327.3	326.3	326.3	326.2	326.1	326.0	325.8	325.6	325.4	325.1	324.9
115°	379.4	379.2	379.6	380.0	380.4	380.8	380.7	380.0	379.5	378.9	378.3
117.5°	431.5	431.5	432.0	432.6	433.1	433.5	433.6	433.3	432.8	432.5	432.0
120°	466.2	466.5	467.4	468.4	469.4	470.4	470.3	469.1	467.9	466.7	465.6
122.5°	501.5	502.0	502.6	503.0	503.5	504.1	503.9	503.0	502.1	501.3	500.4
125°	553.8	554.6	554.9	555.4	555.7	556.2	556.0	555.4	554.8	554.3	553.7
127.5°	605.4	606.5	607.0	607.4	607.8	608.2	607.9	606.5	605.3	604.0	602.8
130°	639.2	640.0	640.6	641.1	641.8	642.4	641.9	640.2	638.7	637.1	635.5
132.5°	672.5	673.4	673.9	674.3	674.8	675.2	674.7	673.1	671.5	669.9	668.3
135°	722.0	722.7	723.0	723.2	723.4	723.5	723.1	721.8	720.7	719.5	718.4
137.5°	770.5	771.3	770.9	770.3	769.8	769.3	768.6	767.6	766.6	765.6	764.6
140°	801.8	802.0	801.8	801.6	801.4	801.2	800.6	799.6	798.6	797.6	796.7
142.5°	831.7	831.9	831.5	831.2	830.8	830.5	829.8	828.8	827.9	826.8	825.8
145°	875.7	875.8	875.3	874.7	874.1	873.5	873.0	872.6	872.2	871.8	871.4
147.5°	917.0	917.0	916.4	915.9	915.3	914.8	914.2	913.5	912.8	912.0	911.3
150°	942.6	942.6	942.3	941.8	941.5	941.0	940.7	940.2	939.9	939.5	939.1
152.5°	965.7	965.5	965.2	964.9	964.7	964.5	964.0	963.5	963.0	962.4	961.9
155°	999.5	998.7	998.5	998.3	998.1	997.9	997.8	997.8	997.8	997.8	997.8
157.5°	1028.9	1028.1	1028.0	1027.8	1027.6	1027.4	1027.5	1027.7	1028.0	1028.2	1028.4
160°	1046.9	1045.9	1045.9	1045.9	1045.9	1045.9	1046.1	1046.5	1046.9	1047.2	1047.7
162.5°	1064.0	1063.0	1062.8	1062.7	1062.5	1062.4	1062.6	1063.1	1063.6	1064.2	1064.8
165°	1085.3	1084.1	1084.1	1084.1	1084.1	1084.1	1084.5	1085.0	1085.7	1086.2	1086.8
167.5°	1102.9	1101.6	1101.4	1101.3	1101.2	1101.0	1101.3	1102.1	1102.9	1103.7	1104.5
170°	1112.2	1110.9	1110.9	1110.9	1110.9	1110.9	1111.3	1112.1	1112.9	1113.7	1114.5
172.5°	1119.9	1118.7	1118.7	1118.7	1118.7	1118.7	1119.1	1119.9	1120.7	1121.5	1122.2
175°	1128.1	1126.9	1126.9	1126.9	1126.9	1126.9	1127.3	1128.1	1128.8	1129.6	1130.4
177.5°	1131.9	1131.0	1131.0	1131.0	1131.0	1131.0	1131.3	1131.9	1132.6	1133.2	1133.8
180°	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1



TEST NUMBER: P332379-940

CATALOG NUMBER: S123RDIP-S1165D1025U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2
2.5°	1646.2	1652.3	1660.2	1672.0	1681.0	1688.8	1690.5	1692.7	1698.4	1707.8	1715.1
5°	1656.8	1672.9	1698.9	1724.1	1751.4	1773.9	1794.9	1809.6	1823.6	1853.1	1876.9
7.5°	1653.5	1689.3	1730.0	1775.3	1821.1	1865.5	1906.7	1943.6	1980.3	2023.2	2072.2
10°	1651.2	1693.3	1747.9	1806.1	1869.9	1932.2	1992.5	2039.5	2094.2	2143.2	2205.6
12.5°	1640.6	1701.1	1766.5	1840.8	1919.2	1991.1	2070.5	2135.4	2197.9	2268.8	2341.3
15°	1626.7	1700.3	1783.0	1881.8	2000.9	2087.9	2169.2	2282.0	2359.1	2436.2	2539.9
17.5°	1601.3	1691.1	1794.5	1922.9	2022.2	2139.0	2261.4	2350.5	2454.4	2563.0	2656.9
20°	1581.1	1685.6	1801.2	1927.3	2054.2	2181.0	2299.5	2406.0	2513.3	2638.8	2715.8
22.5°	1560.9	1664.3	1784.4	1918.4	2054.8	2188.3	2322.5	2447.6	2568.2	2694.8	2793.2
25°	1518.0	1640.7	1771.0	1907.7	2042.3	2189.5	2349.3	2488.8	2638.0	2768.4	2861.6
27.5°	1474.6	1587.0	1716.8	1855.5	2005.0	2179.0	2367.0	2525.5	2675.0	2768.4	2797.7
30°	1435.4	1554.5	1673.7	1814.5	1976.4	2170.5	2370.3	2551.8	2674.5	2715.1	2684.9
32.5°	1395.5	1503.5	1621.5	1765.8	1937.7	2149.8	2374.8	2536.1	2609.9	2578.9	2456.2
35°	1325.3	1422.7	1537.0	1681.3	1879.0	2138.3	2356.3	2465.6	2447.4	2272.2	2040.9
37.5°	1250.2	1329.5	1435.4	1586.4	1818.2	2092.8	2276.6	2292.8	2135.1	1866.1	1598.9
40°	1190.8	1262.2	1370.9	1528.6	1771.0	2047.9	2196.5	2131.3	1886.7	1587.4	1364.6
42.5°	1133.0	1193.3	1298.0	1468.0	1726.2	1986.8	2077.1	1935.1	1652.9	1369.9	1167.2
45°	1035.2	1091.9	1197.0	1371.5	1634.4	1869.9	1858.0	1611.2	1328.8	1101.1	932.8
47.5°	942.4	992.0	1090.7	1268.8	1526.6	1694.7	1583.2	1320.7	1081.1	898.4	778.4
50°	876.7	925.9	1024.0	1199.9	1440.3	1562.9	1403.8	1150.8	931.5	780.1	684.7
52.5°	814.0	861.9	951.6	1123.0	1336.0	1409.3	1238.4	1003.9	821.0	690.4	608.5
55°	726.1	762.5	843.1	1007.1	1166.3	1183.0	1010.0	813.7	663.0	571.9	515.9
57.5°	636.5	667.9	747.5	878.2	989.7	981.1	816.9	647.2	545.7	478.0	437.3
60°	578.2	609.0	679.1	791.3	875.4	846.0	695.3	558.6	471.7	422.0	389.7
62.5°	523.8	548.0	613.5	695.4	755.9	722.6	594.3	481.2	412.2	370.3	344.8
65°	445.1	464.7	517.2	560.0	593.6	561.4	454.9	376.4	326.6	297.2	279.6
67.5°	370.1	382.6	415.9	431.3	455.0	419.6	342.1	289.4	261.2	236.3	224.2
70°	323.1	332.2	349.7	362.3	368.6	332.2	274.7	236.2	212.3	194.8	187.2
72.5°	276.0	284.0	287.5	297.8	294.6	260.5	220.9	190.2	173.1	161.2	151.2
75°	211.0	214.5	211.0	206.8	197.6	173.8	146.5	131.1	118.4	112.8	109.3
77.5°	153.7	152.7	147.8	141.3	125.7	110.8	96.0	90.9	85.3	82.4	81.1
80°	118.4	115.7	111.5	100.9	87.6	77.1	73.6	70.1	67.9	64.5	63.8
82.5°	88.2	86.5	79.5	70.6	61.3	56.4	53.4	52.2	50.0	48.2	48.1
85°	47.0	44.9	37.2	32.3	30.9	29.4	28.7	28.7	25.9	25.2	25.2
87.5°	15.7	12.8	12.6	11.3	11.8	11.1	12.2	11.6	11.6	12.3	11.3
90°	2.9	4.8	6.9	8.8	11.1	13.6	16.2	18.8	21.4	22.1	22.9
92.5°	22.9	24.3	25.6	26.9	28.4	29.8	31.2	32.7	34.2	34.8	35.5
95°	53.9	55.3	56.7	58.1	59.6	61.1	62.7	64.3	65.9	66.7	67.4
97.5°	94.3	95.3	96.4	97.4	98.4	99.6	100.8	101.9	103.1	104.0	104.9
100°	122.3	123.4	124.6	125.8	126.9	127.9	128.9	129.8	130.8	131.4	132.1
102.5°	153.8	154.5	155.2	156.0	156.9	158.3	159.5	160.9	162.2	162.7	163.4
105°	200.6	201.1	201.4	201.9	203.0	204.7	206.5	208.3	210.1	210.1	210.1
107.5°	255.4	255.6	255.8	256.1	256.5	257.3	258.0	258.7	259.4	260.0	260.6
110°	289.7	290.1	290.4	290.9	291.2	291.7	292.0	292.5	292.8	293.6	294.4



TEST NUMBER: P332379-940

CATALOG NUMBER: S123RDIP-S1165D1025U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	325.1	325.4	325.6	325.8	326.0	326.1	326.2	326.3	326.3	327.3	328.2
115°	378.9	379.5	380.0	380.7	380.8	380.4	380.0	379.6	379.2	379.4	379.6
117.5°	432.5	432.8	433.3	433.6	433.5	433.1	432.6	432.0	431.5	431.5	431.4
120°	466.7	467.9	469.1	470.3	470.4	469.4	468.4	467.4	466.5	466.2	466.0
122.5°	501.3	502.1	503.0	503.9	504.1	503.5	503.0	502.6	502.0	501.5	501.0
125°	554.3	554.8	555.4	556.0	556.2	555.7	555.4	554.9	554.6	553.8	552.9
127.5°	604.0	605.3	606.5	607.9	608.2	607.8	607.4	607.0	606.5	605.4	604.3
130°	637.1	638.7	640.2	641.9	642.4	641.8	641.1	640.6	640.0	639.2	638.4
132.5°	669.9	671.5	673.1	674.7	675.2	674.8	674.3	673.9	673.4	672.5	671.5
135°	719.5	720.7	721.8	723.1	723.5	723.4	723.2	723.0	722.7	722.0	721.2
137.5°	765.6	766.6	767.6	768.6	769.3	769.8	770.3	770.9	771.3	770.5	769.7
140°	797.6	798.6	799.6	800.6	801.2	801.4	801.6	801.8	802.0	801.8	801.6
142.5°	826.8	827.9	828.8	829.8	830.5	830.8	831.2	831.5	831.9	831.7	831.5
145°	871.8	872.2	872.6	873.0	873.5	874.1	874.7	875.3	875.8	875.7	875.5
147.5°	912.0	912.8	913.5	914.2	914.8	915.3	915.9	916.4	917.0	917.0	917.0
150°	939.5	939.9	940.2	940.7	941.0	941.5	941.8	942.3	942.6	942.6	942.6
152.5°	962.4	963.0	963.5	964.0	964.5	964.7	964.9	965.2	965.5	965.7	966.1
155°	997.8	997.8	997.8	997.8	997.9	998.1	998.3	998.5	998.7	999.5	1000.3
157.5°	1028.2	1028.0	1027.7	1027.5	1027.4	1027.6	1027.8	1028.0	1028.1	1028.9	1029.7
160°	1047.2	1046.9	1046.5	1046.1	1045.9	1045.9	1045.9	1045.9	1045.9	1046.9	1047.8
162.5°	1064.2	1063.6	1063.1	1062.6	1062.4	1062.5	1062.7	1062.8	1063.0	1064.0	1065.0
165°	1086.2	1085.7	1085.0	1084.5	1084.1	1084.1	1084.1	1084.1	1084.1	1085.3	1086.5
167.5°	1103.7	1102.9	1102.1	1101.3	1101.0	1101.2	1101.3	1101.4	1101.6	1102.9	1104.0
170°	1113.7	1112.9	1112.1	1111.3	1110.9	1110.9	1110.9	1110.9	1110.9	1112.2	1113.7
172.5°	1121.5	1120.7	1119.9	1119.1	1118.7	1118.7	1118.7	1118.7	1118.7	1119.9	1121.1
175°	1129.6	1128.8	1128.1	1127.3	1126.9	1126.9	1126.9	1126.9	1126.9	1128.1	1129.3
177.5°	1133.2	1132.6	1131.9	1131.3	1131.0	1131.0	1131.0	1131.0	1131.0	1131.9	1132.9
180°	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1



TEST NUMBER: P332379-940

CATALOG NUMBER: S123RDIP-S1165D1025U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2
2.5°	1726.9	1726.9	1729.1	1737.6	1738.7	1746.0	1743.7
5°	1897.9	1911.2	1916.1	1937.2	1949.8	1955.4	1944.2
7.5°	2107.0	2144.7	2162.4	2184.4	2204.0	2209.8	2194.5
10°	2259.6	2298.8	2331.7	2352.1	2371.0	2383.6	2399.8
12.5°	2407.0	2455.2	2486.5	2515.2	2534.7	2550.7	2553.3
15°	2567.2	2640.1	2695.5	2736.1	2756.5	2767.0	2762.8
17.5°	2728.8	2796.4	2835.8	2877.3	2905.5	2906.9	2907.7
20°	2820.2	2886.1	2931.7	2962.5	2994.1	2992.7	2999.6
22.5°	2881.4	2933.2	2968.1	2990.5	3001.3	2996.1	2997.4
25°	2909.9	2925.3	2919.1	2883.3	2874.3	2841.3	2846.9
27.5°	2762.5	2689.6	2614.2	2517.2	2440.7	2379.5	2382.7
30°	2562.3	2433.4	2286.2	2162.8	2052.1	2021.2	1955.4
32.5°	2282.5	2089.1	1916.7	1801.8	1706.7	1681.0	1623.4
35°	1808.2	1620.4	1443.1	1336.5	1294.5	1235.6	1234.9
37.5°	1405.5	1240.1	1146.3	1066.4	1024.5	988.9	985.4
40°	1182.3	1053.4	982.6	925.1	883.8	857.1	850.9
42.5°	1026.4	922.2	855.9	820.3	788.5	774.7	764.5
45°	838.2	768.1	721.8	689.6	674.9	664.4	658.8
47.5°	701.2	654.2	622.7	601.2	589.2	578.2	581.1
50°	626.6	588.0	564.9	544.6	535.5	527.7	528.4
52.5°	566.6	532.0	513.3	498.6	487.2	481.8	479.1
55°	480.8	459.1	440.1	429.6	423.3	415.6	413.5
57.5°	410.1	393.3	377.9	366.0	364.4	357.0	358.0
60°	363.0	349.0	336.4	330.1	325.2	318.9	321.0
62.5°	324.3	312.5	301.1	295.9	291.0	286.3	287.3
65°	265.6	254.4	247.4	244.6	242.5	240.4	238.3
67.5°	211.7	204.8	200.5	194.4	190.1	189.4	187.3
70°	178.0	168.9	161.2	153.5	151.4	150.7	151.4
72.5°	142.7	137.0	134.8	131.1	130.6	128.9	130.1
75°	107.3	105.1	103.7	100.9	100.9	100.9	100.9
77.5°	79.1	77.8	77.0	76.4	75.7	74.7	74.5
80°	61.7	61.0	59.6	59.6	58.9	59.6	58.9
82.5°	46.5	46.4	45.0	45.0	44.3	43.9	44.3
85°	23.8	23.1	24.5	23.1	23.8	22.5	23.8
87.5°	11.5	11.6	11.2	11.2	10.8	11.9	11.0
90°	23.7	24.5	25.1	25.5	25.9	26.3	26.7
92.5°	36.1	36.7	36.9	36.6	36.5	36.2	35.9
95°	68.2	69.0	69.5	69.5	69.5	69.5	69.5
97.5°	105.8	106.7	107.1	107.1	107.0	106.9	106.8
100°	132.6	133.2	133.8	134.1	134.5	134.9	135.3
102.5°	164.0	164.5	164.8	164.7	164.6	164.6	164.5
105°	210.1	210.1	210.3	210.6	211.1	211.4	211.9
107.5°	261.3	261.9	262.1	261.9	261.6	261.4	261.2
110°	295.2	296.0	296.2	295.8	295.4	295.1	294.6



TEST NUMBER: P332379-940

CATALOG NUMBER: S123RDIP-S1165D1025U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	329.1	330.1	330.6	330.5	330.4	330.3	330.2
115°	379.8	380.0	380.0	379.8	379.6	379.4	379.2
117.5°	431.4	431.4	431.1	430.5	430.0	429.4	428.8
120°	465.8	465.7	465.3	464.9	464.6	464.1	463.8
122.5°	500.5	500.0	499.4	498.9	498.3	497.8	497.2
125°	552.1	551.3	550.5	549.8	549.0	548.2	547.4
127.5°	603.2	602.1	601.1	600.2	599.2	598.3	597.4
130°	637.6	636.9	635.7	634.4	632.9	631.6	630.2
132.5°	670.7	669.7	668.7	667.6	666.6	665.5	664.4
135°	720.4	719.6	719.0	718.6	718.2	717.8	717.5
137.5°	768.9	768.0	767.2	766.5	765.7	765.0	764.3
140°	801.4	801.2	800.4	799.1	797.6	796.3	794.9
142.5°	831.3	831.1	830.5	829.4	828.3	827.2	826.2
145°	875.3	875.0	874.6	873.8	873.0	872.2	871.4
147.5°	917.0	917.0	916.4	915.3	914.0	912.8	911.7
150°	942.6	942.6	942.0	940.8	939.7	938.4	937.3
152.5°	966.3	966.7	966.3	965.3	964.3	963.2	962.2
155°	1001.1	1001.8	1001.6	1000.2	998.8	997.4	996.0
157.5°	1030.6	1031.4	1031.3	1030.2	1029.0	1028.0	1026.8
160°	1048.8	1049.8	1049.9	1049.2	1048.4	1047.6	1046.8
162.5°	1066.0	1066.9	1066.8	1065.5	1064.3	1063.0	1061.8
165°	1087.7	1088.9	1088.8	1087.4	1086.0	1084.7	1083.3
167.5°	1105.3	1106.5	1106.5	1105.3	1104.0	1102.9	1101.6
170°	1115.0	1116.4	1116.4	1115.0	1113.7	1112.2	1110.9
172.5°	1122.4	1123.6	1123.6	1122.1	1120.8	1119.4	1117.9
175°	1130.4	1131.7	1131.5	1130.2	1128.7	1127.4	1126.0
177.5°	1133.8	1134.8	1134.7	1133.6	1132.5	1131.4	1130.2
180°	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1

(END OF REPORT)