

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332874-830

Luminaire Tested: **S124RDIP-S350D590U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332874-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIP-S350D590U830-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 590 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3571.8 lumens
Efficiency: N/A
Efficacy: 139.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 25.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332874-830

CATALOG NUMBER: S124RDIP-S350D590U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332874-830

CATALOG NUMBER: S124RDIP-S350D590U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45
1	95	91	87	84	86	83	80	77	67	65	63	53	52	50	40	39	38
2	87	80	74	69	79	73	68	63	59	56	53	47	44	42	35	34	32
3	79	70	63	58	72	64	58	53	52	48	44	42	38	36	31	30	28
4	73	62	55	49	66	57	50	45	47	42	38	37	34	31	28	26	24
5	67	55	48	42	60	51	44	39	42	37	33	33	30	27	26	23	21
6	61	50	42	36	56	45	39	34	38	32	29	30	26	24	23	21	19
7	57	45	37	32	51	41	34	29	34	29	25	27	24	21	21	19	17
8	53	41	33	28	48	37	31	26	31	26	22	25	21	19	19	17	15
9	49	37	30	25	44	34	28	23	28	23	20	23	19	17	18	15	13
10	46	34	27	22	41	31	25	21	26	21	18	21	18	15	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4704	4704	4704
5°	4714	4657	4686
10°	4685	4601	4601
15°	4631	4504	4471
20°	4558	4376	4296
25°	4464	4228	4121
30°	4371	4072	3901
35°	4269	3909	3680
40°	4147	3724	3442
45°	4035	3540	3199
50°	3905	3328	2941
55°	3768	3108	2663
60°	3615	2868	2377
65°	3477	2565	2096
70°	3274	2231	1780
75°	3019	1853	1447
80°	2631	1409	1330
85°	2232	1288	1195



TEST NUMBER: P332874-830

CATALOG NUMBER: S124RDIP-S350D590U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.7	1.5
10°-20°	152.6	4.3
20°-30°	220.4	6.2
30°-40°	249.8	7.0
40°-50°	241.2	6.8
50°-60°	200.6	5.6
60°-70°	138.5	3.9
70°-80°	70.2	2.0
80°-90°	20.1	0.6
90°-100°	24.6	0.7
100°-110°	156.8	4.4
110°-120°	299.9	8.4
120°-130°	380.7	10.7
130°-140°	407.3	11.4
140°-150°	380.9	10.7
150°-160°	307.1	8.6
160°-170°	198.1	5.5
170°-180°	68.3	1.9
0°-30°	427.8	12.0
0°-40°	677.6	19.0
0°-60°	1119.4	31.3
0°-90°	1348.2	37.7
90°-120°	481.2	13.5
90°-150°	1650.1	46.2
90°-180°	2224.0	62.3
0°-180°	3571.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	583	583	583	583	583	
5°	582	580	575	579	578	55
15°	554	550	539	538	535	156
25°	501	492	475	467	463	231
35°	433	418	397	382	373	271
45°	353	336	310	289	280	272
55°	268	249	221	198	189	239
65°	182	162	134	116	110	180
75°	97	80	59	50	46	102
85°	24	16	14	13	13	27
90°	2	7	12	15	16	3
95°	30	12	12	15	16	38
105°	162	165	168	171	153	169
115°	302	304	303	304	304	297
125°	425	427	426	427	428	379
135°	527	526	528	530	531	406
145°	608	609	609	610	611	380
155°	666	667	665	667	666	307
165°	703	700	700	704	700	198
175°	719	716	716	720	714	68
180°	719	719	719	719	719	



TEST NUMBER: P332874-830

CATALOG NUMBER: S124RDIP-S350D590U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	582.7	582.7	582.7	582.7	582.7	582.7	582.7	582.7	582.7	582.7	582.7
2.5°	584.1	583.7	583.4	583.2	582.8	582.2	581.4	580.5	579.6	578.7	579.6
5°	581.7	581.4	581.0	580.6	580.1	579.4	578.2	577.0	575.8	574.7	575.6
7.5°	576.5	576.1	575.7	575.2	574.9	573.8	572.3	570.7	569.2	567.7	568.3
10°	571.5	571.0	570.5	570.0	569.5	568.4	566.6	564.8	563.0	561.3	561.7
12.5°	565.1	564.5	563.9	563.4	562.8	561.5	559.3	557.2	555.2	553.0	553.3
15°	554.1	553.2	552.3	551.4	550.5	548.8	546.4	543.8	541.4	538.9	538.8
17.5°	540.8	539.5	538.2	537.0	535.6	533.5	530.6	527.5	524.6	521.6	521.0
20°	530.5	529.1	527.9	526.6	525.3	523.0	519.6	516.2	512.8	509.4	508.7
22.5°	519.1	517.6	516.1	514.7	513.2	510.7	507.1	503.5	499.9	496.2	495.1
25°	501.1	499.3	497.5	495.7	493.9	491.0	486.9	482.9	478.7	474.7	473.0
27.5°	482.1	479.8	477.6	475.4	473.2	469.9	465.5	461.2	456.9	452.5	450.3
30°	468.9	466.4	463.9	461.5	459.0	455.4	450.7	446.1	441.4	436.8	434.3
32.5°	455.0	452.1	449.4	446.6	443.7	440.0	435.2	430.4	425.6	420.8	417.8
35°	433.2	430.0	426.9	423.7	420.5	416.4	411.5	406.5	401.6	396.6	393.2
37.5°	409.9	406.6	403.4	400.1	396.8	392.5	386.9	381.4	376.0	370.5	366.7
40°	393.5	390.2	386.9	383.7	380.4	376.0	370.3	364.7	359.0	353.4	349.2
42.5°	377.8	374.4	370.9	367.5	364.1	359.4	353.5	347.6	341.8	335.8	331.6
45°	353.4	349.7	346.0	342.3	338.7	333.8	327.9	322.0	316.0	310.1	305.2
47.5°	328.1	324.3	320.6	316.7	312.9	307.9	301.8	295.6	289.4	283.2	278.1
50°	310.9	307.1	303.2	299.4	295.5	290.4	284.1	277.7	271.4	265.0	260.0
52.5°	293.5	289.6	285.9	282.1	278.3	273.1	266.6	260.1	253.6	247.1	242.1
55°	267.7	263.7	259.8	255.8	251.8	246.6	240.2	233.8	227.2	220.8	215.7
57.5°	242.1	238.0	233.9	229.8	225.6	220.5	214.1	207.7	201.4	195.0	189.8
60°	223.9	220.0	216.0	212.1	208.1	202.9	196.6	190.2	183.9	177.6	172.4
62.5°	207.5	203.4	199.3	195.2	191.1	185.8	179.3	172.8	166.3	159.8	155.0
65°	182.0	177.8	173.5	169.3	164.9	159.7	153.4	146.9	140.6	134.3	130.1
67.5°	155.5	151.5	147.3	143.3	139.2	134.2	128.3	122.4	116.5	110.7	107.0
70°	138.7	134.6	130.4	126.3	122.1	117.2	111.5	105.8	100.2	94.5	91.3
72.5°	120.9	117.2	113.4	109.6	105.8	101.3	96.0	90.6	85.3	79.9	77.2
75°	96.8	93.1	89.4	85.8	82.1	77.9	73.3	68.6	64.0	59.4	57.0
77.5°	72.4	69.3	66.2	63.1	59.9	56.5	52.7	48.9	45.1	41.4	40.1
80°	56.6	53.8	50.9	48.1	45.1	42.2	39.3	36.3	33.3	30.3	30.1
82.5°	43.1	40.4	37.8	35.2	32.5	30.3	28.7	27.0	25.3	23.6	23.4
85°	24.1	22.1	20.2	18.1	16.1	15.0	14.7	14.4	14.1	13.9	13.7
87.5°	8.6	8.2	7.8	7.4	7.1	6.9	7.1	7.2	7.3	7.4	7.4
90°	1.6	2.9	4.2	5.6	6.9	8.0	9.0	9.9	10.8	11.8	12.5
92.5°	6.8	6.9	6.9	7.0	7.1	7.5	8.6	9.5	10.5	11.4	12.2
95°	29.6	25.5	21.5	17.3	13.3	11.3	11.5	11.6	11.7	11.8	12.5
97.5°	62.8	65.3	67.9	70.4	73.0	67.5	54.2	40.9	27.5	14.2	14.2
100°	88.1	90.3	92.5	94.6	96.8	89.6	73.1	56.6	40.2	23.7	21.6
102.5°	116.6	118.1	119.7	121.3	122.9	122.6	120.5	118.3	116.1	114.0	92.1
105°	161.8	162.6	163.2	164.0	164.7	165.3	166.0	166.5	167.1	167.8	168.8
107.5°	203.9	204.2	204.6	204.9	205.3	205.9	206.7	207.5	208.3	209.2	209.7
110°	232.2	232.6	233.0	233.4	233.7	234.2	235.0	235.6	236.4	237.1	237.3



TEST NUMBER: P332874-830

CATALOG NUMBER: S124RDIP-S350D590U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	259.8	260.4	261.1	261.7	262.4	262.9	263.2	263.5	263.9	264.2	264.2
115°	302.2	302.6	302.8	303.2	303.6	303.7	303.6	303.5	303.3	303.2	303.5
117.5°	340.4	340.8	341.3	341.8	342.2	342.6	342.9	343.2	343.4	343.7	343.7
120°	366.2	366.6	367.1	367.6	368.1	368.3	368.2	368.0	367.9	367.8	368.0
122.5°	390.2	390.5	390.8	391.1	391.3	391.6	391.8	391.9	392.1	392.3	392.4
125°	424.7	425.2	425.7	426.2	426.7	426.8	426.5	426.3	426.0	425.8	426.2
127.5°	457.4	457.5	457.7	457.8	457.9	458.3	458.8	459.3	459.9	460.4	460.3
130°	478.5	478.6	478.7	478.9	479.0	479.2	479.6	479.9	480.3	480.7	480.8
132.5°	497.9	498.0	498.3	498.5	498.7	499.1	499.5	499.9	500.4	500.9	501.0
135°	526.9	526.8	526.7	526.5	526.4	526.6	527.1	527.5	528.0	528.5	528.8
137.5°	552.6	552.6	552.7	552.7	552.8	553.1	553.6	554.1	554.7	555.2	555.4
140°	569.4	569.6	569.9	570.0	570.3	570.5	570.8	571.1	571.3	571.6	571.8
142.5°	584.5	584.8	585.3	585.7	586.2	586.4	586.5	586.7	586.8	587.0	587.3
145°	607.6	607.9	608.2	608.6	609.0	609.2	609.2	609.2	609.2	609.2	609.3
147.5°	625.9	626.6	627.3	627.9	628.6	628.9	628.8	628.7	628.5	628.4	628.5
150°	639.2	639.7	640.3	640.7	641.2	641.4	641.2	641.1	641.0	640.8	640.8
152.5°	650.4	650.8	651.2	651.6	652.0	652.1	651.9	651.7	651.4	651.2	651.4
155°	666.2	666.3	666.4	666.5	666.7	666.5	666.2	665.8	665.4	665.1	665.5
157.5°	679.4	679.3	679.2	679.2	679.1	678.8	678.4	678.1	677.6	677.2	677.9
160°	687.1	686.7	686.4	686.1	685.7	685.4	685.3	685.2	685.0	684.9	685.7
162.5°	694.0	693.5	693.1	692.7	692.2	691.9	691.7	691.6	691.5	691.4	692.1
165°	702.7	702.1	701.5	700.9	700.3	700.0	700.0	700.0	700.0	700.0	701.0
167.5°	709.5	709.0	708.3	707.8	707.1	706.7	706.7	706.6	706.5	706.4	707.6
170°	713.5	712.8	712.0	711.3	710.6	710.3	710.4	710.5	710.7	710.8	711.7
172.5°	716.0	715.3	714.6	713.9	713.2	712.8	713.0	713.1	713.2	713.3	714.4
175°	718.9	718.1	717.4	716.7	716.0	715.7	715.8	716.0	716.0	716.1	717.2
177.5°	720.1	719.4	718.8	718.1	717.5	717.2	717.4	717.6	717.7	717.9	718.8
180°	718.9	718.9	718.9	718.9	718.9	718.9	718.9	718.9	718.9	718.9	718.9



TEST NUMBER: P332874-830

CATALOG NUMBER: S124RDIP-S350D590U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	582.7	582.7	582.7	582.7	582.7	582.7	582.7	582.7
2.5°	580.5	581.4	582.2	582.6	582.5	582.5	582.4	582.3
5°	576.6	577.6	578.6	579.0	578.8	578.6	578.3	578.2
7.5°	568.9	569.6	570.2	570.3	570.0	569.8	569.4	569.1
10°	562.0	562.4	562.8	562.8	562.4	562.0	561.7	561.3
12.5°	553.5	553.7	554.0	553.8	553.3	552.7	552.1	551.6
15°	538.6	538.4	538.1	537.7	537.0	536.3	535.6	534.9
17.5°	520.5	520.0	519.4	518.6	517.6	516.5	515.5	514.4
20°	507.9	507.1	506.3	505.3	504.0	502.7	501.4	500.1
22.5°	493.9	492.7	491.5	490.4	489.4	488.3	487.3	486.2
25°	471.3	469.7	468.0	466.7	465.6	464.6	463.6	462.6
27.5°	448.3	446.2	444.1	442.4	440.9	439.5	438.1	436.7
30°	431.8	429.3	426.9	424.8	423.2	421.7	420.1	418.5
32.5°	415.0	412.1	409.3	407.0	405.5	404.0	402.5	401.0
35°	389.8	386.5	383.1	380.6	378.8	377.0	375.2	373.4
37.5°	363.0	359.2	355.4	352.6	350.8	349.0	347.2	345.4
40°	345.0	340.8	336.7	333.8	332.0	330.2	328.4	326.6
42.5°	327.3	323.1	318.9	315.8	314.0	312.1	310.2	308.4
45°	300.4	295.5	290.6	287.3	285.5	283.7	281.9	280.2
47.5°	273.1	268.1	263.1	259.6	257.6	255.6	253.6	251.8
50°	255.1	250.2	245.2	241.8	239.9	238.0	236.1	234.2
52.5°	237.0	232.1	227.1	223.5	221.6	219.6	217.6	215.7
55°	210.6	205.4	200.2	196.7	194.8	192.9	191.1	189.2
57.5°	184.5	179.4	174.1	170.8	169.4	168.0	166.5	165.0
60°	167.2	162.1	156.9	153.5	151.9	150.4	148.8	147.2
62.5°	150.2	145.4	140.7	137.7	136.4	135.2	133.8	132.6
65°	125.7	121.5	117.3	114.5	113.3	112.2	110.9	109.7
67.5°	103.3	99.6	96.0	93.5	92.2	90.9	89.5	88.2
70°	88.0	84.7	81.5	79.4	78.3	77.4	76.3	75.4
72.5°	74.4	71.5	68.8	66.9	66.0	65.1	64.2	63.2
75°	54.8	52.5	50.2	48.8	48.2	47.6	47.0	46.4
77.5°	38.7	37.4	36.1	35.3	35.2	35.0	34.8	34.6
80°	29.8	29.4	29.1	28.9	28.8	28.7	28.7	28.6
82.5°	23.1	22.9	22.7	22.5	22.4	22.3	22.2	22.1
85°	13.5	13.2	13.0	12.9	12.9	12.9	12.9	12.9
87.5°	7.4	7.5	7.6	7.7	7.8	8.0	8.1	8.2
90°	13.3	13.9	14.7	15.2	15.5	15.6	15.9	16.1
92.5°	12.8	13.6	14.2	14.6	14.7	14.7	14.8	14.8
95°	13.3	13.9	14.7	15.1	15.3	15.4	15.5	15.6
97.5°	14.3	14.4	14.5	14.6	14.7	14.8	14.9	15.1
100°	19.6	17.5	15.6	14.6	14.7	14.8	14.9	15.1
102.5°	70.1	48.3	26.3	15.4	15.5	15.5	15.5	15.5
105°	169.9	171.0	172.0	170.4	166.2	161.8	157.5	153.3
107.5°	210.2	210.8	211.2	211.7	212.2	212.6	213.1	213.6
110°	237.6	237.8	238.1	238.4	238.7	239.0	239.4	239.8



TEST NUMBER: P332874-830

CATALOG NUMBER: S124RDIP-S350D590U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	264.1	264.1	264.0	264.2	264.7	265.1	265.6	266.0
115°	303.7	304.0	304.2	304.3	304.3	304.3	304.3	304.3
117.5°	343.6	343.6	343.5	343.5	343.4	343.4	343.3	343.3
120°	368.3	368.4	368.7	368.7	368.4	368.3	368.0	367.8
122.5°	392.6	392.7	392.9	392.8	392.6	392.3	392.1	391.8
125°	426.5	426.9	427.3	427.5	427.6	427.7	427.8	428.0
127.5°	460.3	460.2	460.1	460.1	460.0	459.9	459.8	459.7
130°	480.9	481.0	481.2	481.2	481.2	481.2	481.2	481.2
132.5°	501.1	501.2	501.3	501.3	501.2	501.1	501.1	501.0
135°	529.0	529.2	529.4	529.7	529.9	530.2	530.5	530.7
137.5°	555.7	556.0	556.2	556.3	556.3	556.2	556.1	556.0
140°	572.2	572.6	573.0	573.2	573.3	573.4	573.5	573.6
142.5°	587.5	587.8	588.1	588.2	588.2	588.2	588.2	588.3
145°	609.4	609.5	609.6	609.8	610.0	610.3	610.6	610.8
147.5°	628.6	628.7	628.8	628.9	629.1	629.1	629.2	629.3
150°	640.8	640.8	640.8	640.9	641.0	641.2	641.3	641.4
152.5°	651.6	651.8	652.0	652.1	652.0	651.9	651.8	651.8
155°	666.0	666.5	666.9	667.0	666.7	666.3	666.0	665.6
157.5°	678.4	679.1	679.7	679.7	679.1	678.4	677.9	677.2
160°	686.4	687.1	687.9	687.9	687.1	686.4	685.7	684.9
162.5°	692.9	693.5	694.3	694.3	693.4	692.6	691.8	691.0
165°	701.9	702.9	703.9	703.8	702.7	701.6	700.6	699.5
167.5°	708.6	709.6	710.7	710.6	709.5	708.2	707.0	705.9
170°	712.7	713.6	714.6	714.4	713.3	712.1	710.9	709.7
172.5°	715.3	716.2	717.2	717.0	715.8	714.4	713.1	711.8
175°	718.3	719.3	720.5	720.3	718.9	717.4	716.0	714.5
177.5°	719.5	720.3	721.0	720.9	719.7	718.6	717.4	716.2
180°	718.9	718.9	718.9	718.9	718.9	718.9	718.9	718.9

(END OF REPORT)