

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332376-940

Luminaire Tested: **S123RDIP-S1165D805U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332376-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1165D805U940-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 805 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6365.9 lumens
Efficiency: N/A
Efficacy: 104.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 60.7
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332376-940

CATALOG NUMBER: S123RDIP-S1165D805U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332376-940

CATALOG NUMBER: S123RDIP-S1165D805U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67
1	101	96	93	89	94	90	87	84	79	77	75	69	67	66	59	58	57
2	92	85	79	74	86	80	74	70	70	66	62	61	58	55	53	51	49
3	84	75	68	62	79	70	64	59	62	57	53	54	50	47	47	44	42
4	77	67	59	53	72	63	56	50	55	50	45	49	44	41	42	39	36
5	71	60	51	45	66	56	49	43	50	44	40	44	39	36	38	35	32
6	66	54	45	40	61	51	43	38	45	39	35	40	35	31	35	31	28
7	61	49	41	35	57	46	39	34	41	35	31	36	32	28	32	28	25
8	57	44	36	31	53	42	35	30	38	32	28	33	29	25	29	26	23
9	53	41	33	28	49	38	32	27	35	29	25	31	26	23	27	23	21
10	49	37	30	25	46	35	29	24	32	26	22	29	24	21	25	22	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18603	18603	18603
5°	18674	18416	18522
10°	18569	18185	18124
15°	18369	17761	17572
20°	18095	17228	16827
25°	17813	16631	16098
30°	17439	15940	15070
35°	17056	15251	14127
40°	16703	14436	12960
45°	16238	13633	11905
50°	15726	12722	10727
55°	15204	11678	9627
60°	14725	10562	8420
65°	14103	9352	7210
70°	13322	7852	5822
75°	12181	6180	5481
80°	10860	5473	5040
85°	9176	4841	4508



TEST NUMBER: P332376-940

CATALOG NUMBER: S123RDIP-S1165D805U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	162.3	2.5
10°-20°	451.6	7.1
20°-30°	650.2	10.2
30°-40°	732.4	11.5
40°-50°	700.7	11.0
50°-60°	573.8	9.0
60°-70°	387.1	6.1
70°-80°	194.8	3.1
80°-90°	54.2	0.9
90°-100°	57.8	0.9
100°-110°	173.1	2.7
110°-120°	294.3	4.6
120°-130°	387.1	6.1
130°-140°	435.1	6.8
140°-150°	427.7	6.7
150°-160°	360.1	5.7
160°-170°	239.7	3.8
170°-180°	83.9	1.3
0°-30°	1264.1	19.9
0°-40°	1996.5	31.4
0°-60°	3270.9	51.4
0°-90°	3907.0	61.4
90°-120°	525.2	8.3
90°-150°	1775.2	27.9
90°-180°	2459.0	38.6
0°-180°	6365.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1728	1728	1728	1728	1728	
5°	1728	1721	1704	1716	1714	164
15°	1648	1632	1594	1587	1577	464
25°	1500	1463	1400	1372	1355	689
35°	1298	1246	1161	1102	1075	812
45°	1067	1001	896	818	782	823
55°	810	739	622	544	513	726
65°	554	475	367	302	283	548
75°	293	225	149	135	132	312
85°	74	45	39	37	36	83
90°	1	8	17	19	21	6
95°	41	46	52	54	54	46
105°	157	159	164	165	166	168
115°	296	298	297	298	297	293
125°	434	436	434	432	429	387
135°	563	567	566	563	562	433
145°	682	684	686	685	682	426
155°	782	782	782	785	780	360
165°	851	849	849	853	848	240
175°	885	883	883	886	882	84
180°	888	888	888	888	888	



TEST NUMBER: P332376-940

CATALOG NUMBER: S123RDIP-S1165D805U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3
2.5°	1733.9	1732.9	1731.9	1730.9	1729.9	1727.9	1724.9	1721.9	1719.0	1715.9	1718.7
5°	1728.3	1726.7	1725.2	1723.6	1722.1	1719.4	1715.7	1711.9	1708.2	1704.4	1707.3
7.5°	1712.3	1710.7	1709.0	1707.3	1705.6	1702.3	1697.5	1692.6	1687.7	1682.8	1684.4
10°	1698.9	1696.7	1694.5	1692.3	1690.1	1686.2	1680.6	1675.0	1669.4	1663.8	1664.1
12.5°	1679.8	1677.4	1674.9	1672.5	1670.1	1665.4	1658.6	1651.7	1644.8	1638.0	1637.8
15°	1648.4	1644.9	1641.6	1638.1	1634.7	1628.6	1619.9	1611.1	1602.4	1593.8	1592.1
17.5°	1608.8	1604.9	1600.9	1596.9	1593.0	1585.4	1574.3	1563.2	1552.1	1541.1	1537.8
20°	1579.7	1574.8	1569.8	1564.8	1559.8	1551.4	1539.5	1527.7	1515.8	1504.0	1499.9
22.5°	1547.2	1541.4	1535.7	1530.0	1524.3	1515.1	1502.5	1490.0	1477.4	1464.7	1459.7
25°	1499.8	1492.0	1484.3	1476.4	1468.6	1457.6	1443.2	1429.0	1414.6	1400.3	1393.7
27.5°	1442.3	1433.8	1425.1	1416.6	1407.9	1395.7	1379.7	1363.8	1347.8	1331.9	1322.8
30°	1403.1	1393.7	1384.4	1375.0	1365.7	1352.3	1334.9	1317.4	1300.0	1282.5	1271.9
32.5°	1363.9	1353.3	1342.6	1332.0	1321.5	1307.0	1288.5	1270.1	1251.6	1233.2	1221.6
35°	1298.0	1286.7	1275.5	1264.4	1253.1	1237.9	1218.5	1199.3	1179.9	1160.6	1147.2
37.5°	1231.3	1218.8	1206.3	1193.8	1181.4	1164.8	1144.2	1123.6	1103.0	1082.4	1067.2
40°	1188.7	1174.9	1161.2	1147.5	1133.8	1115.9	1093.8	1071.7	1049.5	1027.4	1011.2
42.5°	1140.4	1126.7	1113.0	1099.3	1085.6	1067.3	1044.5	1021.5	998.7	975.9	958.1
45°	1066.7	1052.7	1038.7	1024.7	1010.6	991.6	967.6	943.6	919.6	895.6	877.9
47.5°	992.9	977.6	962.2	946.8	931.4	911.7	887.7	863.7	839.7	815.8	796.5
50°	939.1	924.5	909.8	895.2	880.6	860.7	835.4	810.2	785.0	759.7	740.4
52.5°	890.9	875.0	859.2	843.3	827.3	806.9	781.9	757.0	732.0	707.0	687.0
55°	810.2	794.9	779.6	764.4	749.1	728.3	701.8	675.3	648.8	622.3	604.3
57.5°	735.6	719.0	702.3	685.7	669.1	647.5	620.9	594.2	567.7	541.1	524.0
60°	684.0	666.9	649.8	632.7	615.5	594.0	568.1	542.3	516.5	490.6	473.8
62.5°	632.4	615.3	598.2	581.0	563.9	542.4	516.6	490.7	464.8	439.0	423.2
65°	553.7	536.5	519.4	502.3	485.2	464.4	440.1	415.8	391.6	367.2	352.0
67.5°	474.9	457.5	440.2	422.9	405.6	385.3	362.0	338.7	315.4	292.1	280.7
70°	423.3	406.5	389.7	372.8	356.1	336.7	315.0	293.1	271.3	249.5	238.6
72.5°	371.8	355.2	338.6	322.0	305.4	287.2	267.4	247.6	227.8	208.0	199.1
75°	292.9	278.0	263.1	248.1	233.2	217.1	200.0	182.8	165.7	148.6	145.4
77.5°	221.1	207.7	194.1	180.7	167.1	154.8	143.8	132.8	121.7	110.8	109.1
80°	175.2	162.5	149.6	136.9	124.1	114.5	107.9	101.4	94.9	88.3	87.4
82.5°	131.4	120.5	109.4	98.4	87.4	80.3	77.3	74.2	71.2	68.1	67.1
85°	74.3	67.4	60.5	53.8	46.9	43.0	42.1	41.1	40.2	39.2	38.6
87.5°	27.0	24.6	22.2	19.8	17.3	16.3	16.7	17.1	17.5	17.9	17.8
90°	0.7	2.2	3.8	5.4	6.9	8.6	10.7	12.7	14.7	16.8	17.4
92.5°	16.9	17.9	19.0	20.1	21.0	22.2	23.4	24.5	25.6	26.8	27.3
95°	41.1	42.2	43.3	44.4	45.5	46.6	47.9	49.1	50.4	51.6	52.3
97.5°	73.0	73.8	74.6	75.4	76.3	77.1	78.0	78.9	79.8	80.7	81.4
100°	94.8	95.8	96.7	97.6	98.5	99.4	100.1	100.9	101.7	102.5	103.0
102.5°	119.9	120.5	121.0	121.6	122.2	123.0	123.9	125.0	126.0	127.1	127.5
105°	156.9	157.2	157.5	157.8	158.1	159.0	160.3	161.8	163.2	164.5	164.5
107.5°	199.8	200.0	200.2	200.4	200.5	200.9	201.5	202.1	202.6	203.1	203.7
110°	226.6	226.9	227.2	227.5	227.8	228.1	228.5	228.7	229.1	229.3	230.0



TEST NUMBER: P332376-940

CATALOG NUMBER: S123RDIP-S1165D805U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	254.5	254.7	254.9	255.0	255.2	255.3	255.4	255.5	255.6	255.6	256.4
115°	296.3	296.8	297.2	297.7	298.2	298.3	297.9	297.7	297.3	297.0	297.1
117.5°	338.4	338.8	339.0	339.3	339.7	339.6	339.2	338.8	338.4	338.0	338.0
120°	364.6	365.5	366.5	367.4	368.4	368.5	367.7	366.8	366.1	365.3	365.2
122.5°	392.0	392.6	393.3	394.0	394.7	394.8	394.4	394.0	393.6	393.2	392.8
125°	433.6	434.1	434.5	435.1	435.5	435.6	435.2	435.0	434.6	434.4	433.7
127.5°	472.2	473.1	474.1	475.1	476.1	476.4	476.1	475.7	475.4	475.0	474.2
130°	497.8	499.0	500.2	501.5	502.7	503.1	502.7	502.2	501.8	501.2	500.6
132.5°	523.4	524.7	525.9	527.2	528.4	528.9	528.5	528.2	527.8	527.4	526.7
135°	562.6	563.6	564.5	565.4	566.3	566.8	566.6	566.4	566.2	566.1	565.5
137.5°	598.9	599.7	600.4	601.2	602.0	602.5	603.0	603.3	603.8	604.1	603.5
140°	623.9	624.7	625.5	626.3	627.1	627.5	627.7	627.9	628.0	628.1	628.0
142.5°	646.8	647.6	648.4	649.2	650.0	650.5	650.8	651.0	651.3	651.6	651.4
145°	682.5	682.9	683.1	683.5	683.8	684.1	684.7	685.1	685.5	686.0	685.9
147.5°	713.8	714.3	714.9	715.4	716.0	716.5	716.9	717.4	717.8	718.3	718.3
150°	735.5	735.8	736.1	736.5	736.7	737.1	737.4	737.7	738.0	738.3	738.3
152.5°	753.4	753.8	754.2	754.7	755.1	755.5	755.6	755.8	756.0	756.2	756.4
155°	781.5	781.5	781.5	781.5	781.5	781.6	781.8	781.9	782.1	782.2	782.8
157.5°	805.5	805.3	805.1	804.9	804.8	804.8	804.9	805.0	805.1	805.2	805.9
160°	820.6	820.3	819.9	819.7	819.3	819.2	819.2	819.2	819.2	819.2	819.9
162.5°	833.9	833.6	833.1	832.7	832.2	832.1	832.2	832.3	832.4	832.6	833.3
165°	851.2	850.8	850.3	849.9	849.4	849.2	849.2	849.2	849.2	849.2	850.1
167.5°	865.0	864.4	863.8	863.2	862.6	862.4	862.5	862.6	862.7	862.8	863.8
170°	872.9	872.3	871.6	871.0	870.4	870.0	870.0	870.0	870.0	870.0	871.2
172.5°	879.0	878.4	877.8	877.2	876.6	876.2	876.2	876.2	876.2	876.2	877.2
175°	885.4	884.8	884.2	883.6	883.0	882.6	882.6	882.6	882.6	882.6	883.6
177.5°	888.1	887.6	887.1	886.5	886.1	885.8	885.8	885.8	885.8	885.8	886.5
180°	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5



TEST NUMBER: P332376-940

CATALOG NUMBER: S123RDIP-S1165D805U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3
2.5°	1721.4	1724.2	1726.9	1728.0	1727.5	1727.1	1726.5	1726.0
5°	1710.0	1712.9	1715.7	1716.7	1716.1	1715.5	1714.8	1714.2
7.5°	1686.0	1687.6	1689.1	1689.3	1688.3	1687.2	1686.1	1685.1
10°	1664.5	1664.7	1665.1	1664.5	1662.9	1661.3	1659.7	1658.2
12.5°	1637.6	1637.4	1637.3	1636.3	1634.5	1632.6	1630.8	1629.1
15°	1590.6	1589.0	1587.5	1585.6	1583.4	1581.3	1579.0	1576.9
17.5°	1534.5	1531.1	1527.8	1524.6	1521.3	1518.0	1514.8	1511.5
20°	1495.9	1491.8	1487.8	1483.9	1480.2	1476.4	1472.7	1469.0
22.5°	1454.6	1449.7	1444.6	1440.3	1436.8	1433.3	1429.9	1426.4
25°	1387.2	1380.6	1374.1	1369.1	1365.7	1362.3	1358.9	1355.4
27.5°	1313.7	1304.6	1295.5	1288.3	1283.1	1277.9	1272.6	1267.4
30°	1261.3	1250.8	1240.2	1232.4	1227.4	1222.4	1217.5	1212.5
32.5°	1210.1	1198.5	1186.9	1178.5	1173.2	1168.0	1162.8	1157.5
35°	1133.8	1120.4	1107.1	1097.5	1091.9	1086.3	1080.7	1075.1
37.5°	1052.0	1036.8	1021.5	1010.5	1003.6	996.7	989.8	982.8
40°	995.1	978.8	962.7	951.0	943.8	936.7	929.5	922.3
42.5°	940.5	922.7	905.1	893.0	886.6	880.2	873.8	867.4
45°	860.1	842.4	824.7	812.1	804.6	797.1	789.6	782.1
47.5°	777.1	757.9	738.5	725.6	718.9	712.2	705.5	698.9
50°	721.1	701.8	682.4	669.2	662.1	654.9	647.7	640.6
52.5°	666.9	646.8	626.8	613.5	607.1	600.7	594.3	587.9
55°	586.2	568.1	550.1	538.0	531.7	525.5	519.2	513.0
57.5°	506.9	489.8	472.8	461.5	456.3	451.0	445.7	440.4
60°	456.9	440.1	423.3	412.2	407.0	401.6	396.4	391.1
62.5°	407.3	391.6	375.7	365.1	359.4	353.9	348.4	342.9
65°	336.7	321.5	306.2	296.9	293.5	290.0	286.6	283.1
67.5°	269.3	257.9	246.5	239.0	235.3	231.6	227.9	224.3
70°	227.7	216.8	205.9	198.8	195.3	191.9	188.4	185.0
72.5°	190.2	181.3	172.4	167.2	165.8	164.3	162.9	161.5
75°	142.3	139.2	136.1	134.3	133.7	133.0	132.4	131.8
77.5°	107.4	105.7	104.0	102.8	102.2	101.6	100.9	100.3
80°	86.4	85.5	84.5	83.8	83.2	82.6	81.9	81.3
82.5°	66.3	65.4	64.4	63.8	63.8	63.6	63.5	63.4
85°	38.0	37.4	36.7	36.5	36.5	36.5	36.5	36.5
87.5°	17.7	17.6	17.4	17.3	17.1	16.9	16.7	16.5
90°	18.0	18.5	19.2	19.7	20.0	20.3	20.6	21.0
92.5°	27.7	28.3	28.7	28.9	28.7	28.5	28.4	28.2
95°	52.8	53.4	54.0	54.4	54.4	54.4	54.4	54.4
97.5°	82.1	82.8	83.6	83.9	83.8	83.8	83.7	83.6
100°	103.4	103.9	104.3	104.8	105.0	105.3	105.7	105.9
102.5°	128.0	128.4	128.9	129.1	129.0	128.9	128.9	128.9
105°	164.5	164.5	164.5	164.7	165.0	165.3	165.6	165.9
107.5°	204.1	204.6	205.2	205.3	205.1	204.9	204.7	204.6
110°	230.6	231.2	231.8	232.0	231.7	231.4	231.0	230.8



TEST NUMBER: P332376-940

CATALOG NUMBER: S123RDIP-S1165D805U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	257.1	257.8	258.6	258.9	258.9	258.8	258.7	258.7
115°	297.3	297.5	297.7	297.7	297.5	297.3	297.1	297.0
117.5°	338.0	337.9	337.9	337.6	337.2	336.8	336.4	335.9
120°	365.0	364.9	364.7	364.4	364.2	363.8	363.6	363.2
122.5°	392.4	392.0	391.6	391.2	390.7	390.3	389.9	389.4
125°	433.1	432.5	431.9	431.2	430.6	430.0	429.4	428.7
127.5°	473.3	472.4	471.6	470.8	470.1	469.4	468.7	468.0
130°	500.1	499.4	498.8	497.9	496.9	495.8	494.7	493.6
132.5°	526.0	525.2	524.5	523.7	522.9	522.0	521.2	520.4
135°	564.9	564.3	563.7	563.2	562.8	562.6	562.2	562.0
137.5°	602.9	602.3	601.5	600.9	600.4	599.8	599.2	598.6
140°	627.9	627.7	627.5	627.0	625.8	624.7	623.7	622.6
142.5°	651.3	651.1	650.9	650.5	649.6	648.8	647.9	647.1
145°	685.7	685.5	685.4	685.0	684.4	683.8	683.1	682.5
147.5°	718.3	718.3	718.3	717.7	716.8	715.9	715.0	714.1
150°	738.3	738.3	738.3	737.9	736.9	736.0	735.0	734.1
152.5°	756.6	756.9	757.2	756.9	756.1	755.3	754.5	753.7
155°	783.5	784.1	784.7	784.4	783.4	782.3	781.2	780.2
157.5°	806.6	807.2	807.8	807.7	806.9	806.0	805.1	804.2
160°	820.7	821.5	822.2	822.3	821.7	821.1	820.5	819.8
162.5°	834.1	834.9	835.7	835.5	834.6	833.6	832.6	831.6
165°	851.0	851.9	852.9	852.8	851.8	850.6	849.5	848.5
167.5°	864.8	865.7	866.7	866.7	865.7	864.8	863.8	862.8
170°	872.3	873.3	874.4	874.4	873.3	872.3	871.2	870.0
172.5°	878.2	879.1	880.0	880.0	878.9	877.8	876.7	875.7
175°	884.5	885.4	886.4	886.3	885.2	884.1	883.0	881.9
177.5°	887.3	888.1	888.8	888.8	887.9	887.0	886.2	885.3
180°	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5

(END OF REPORT)