

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332267-940

Luminaire Tested: **S123RDIP-S340D1195U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332267-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S340D1195U940-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1195 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5413.6 lumens
Efficiency: N/A
Efficacy: 128.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 42.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332267-940

CATALOG NUMBER: S123RDIP-S340D1195U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332267-940

CATALOG NUMBER: S123RDIP-S340D1195U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	100	100	100	100	89	89	89	89	67	67	67	48	48	48	30	30	30	21
1	92	87	84	80	81	78	75	72	59	57	55	42	41	40	27	26	25	18
2	83	76	71	66	74	68	63	59	52	49	46	37	35	33	24	22	22	16
3	76	67	60	55	67	60	54	49	46	42	39	33	30	28	21	20	18	13
4	70	59	52	46	61	53	47	42	41	36	33	29	27	24	19	17	16	12
5	64	53	45	40	56	47	41	36	36	32	28	26	23	21	17	15	14	10
6	59	47	40	34	52	42	36	31	33	28	25	24	21	18	15	14	12	9
7	54	42	35	30	48	38	32	27	29	25	22	21	18	16	14	12	11	8
8	50	38	31	26	44	34	28	24	27	22	19	20	17	14	13	11	10	7
9	46	35	28	23	41	31	25	21	24	20	17	18	15	13	12	10	9	6
10	43	32	25	20	38	29	23	19	22	18	15	17	14	12	11	9	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5514	5514	5514
5°	5535	5459	5491
10°	5503	5391	5372
15°	5446	5264	5209
20°	5363	5108	4987
25°	5280	4930	4772
30°	5169	4724	4467
35°	5056	4520	4188
40°	4950	4279	3842
45°	4813	4042	3529
50°	4662	3771	3178
55°	4506	3462	2852
60°	4366	3130	2495
65°	4182	2774	2137
70°	3950	2326	1725
75°	3614	1834	1626
80°	3217	1624	1494
85°	2717	1433	1334



TEST NUMBER: P332267-940

CATALOG NUMBER: S123RDIP-S340D1195U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.1	0.9
10°-20°	133.9	2.5
20°-30°	192.7	3.6
30°-40°	217.1	4.0
40°-50°	207.7	3.8
50°-60°	170.1	3.1
60°-70°	114.8	2.1
70°-80°	57.7	1.1
80°-90°	19.2	0.4
90°-100°	50.7	0.9
100°-110°	241.6	4.5
110°-120°	580.4	10.7
120°-130°	739.1	13.7
130°-140°	789.7	14.6
140°-150°	738.4	13.6
150°-160°	595.6	11.0
160°-170°	384.4	7.1
170°-180°	132.5	2.4
0°-30°	374.7	6.9
0°-40°	591.8	10.9
0°-60°	969.6	17.9
0°-90°	1161.2	21.5
90°-120°	872.7	16.1
90°-150°	3139.9	58.0
90°-180°	4252.0	78.5
0°-180°	5413.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	512	512	512	512	512	
5°	512	510	505	509	508	49
15°	489	484	472	470	467	138
25°	445	434	415	407	402	204
35°	385	369	344	327	319	241
45°	316	297	266	243	232	244
55°	240	219	184	161	152	215
65°	164	141	109	89	84	162
75°	87	67	44	40	39	93
85°	22	13	12	11	11	25
90°	1	12	25	29	31	4
95°	63	24	32	39	39	78
105°	309	314	227	54	46	327
115°	579	586	595	605	609	571
125°	816	824	829	831	833	729
135°	1016	1022	1027	1030	1027	782
145°	1173	1180	1182	1184	1184	734
155°	1292	1290	1291	1295	1290	595
165°	1362	1359	1358	1366	1359	385
175°	1394	1390	1390	1397	1389	133
180°	1394	1394	1394	1394	1394	



TEST NUMBER: P332267-940

CATALOG NUMBER: S123RDIP-S340D1195U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	512.3	512.3	512.3	512.3	512.3	512.3	512.3	512.3	512.3	512.3	512.3
2.5°	514.0	513.6	513.4	513.1	512.8	512.2	511.3	510.4	509.5	508.6	509.4
5°	512.3	511.8	511.4	511.0	510.4	509.7	508.5	507.5	506.3	505.2	506.0
7.5°	507.6	507.0	506.6	506.0	505.6	504.6	503.2	501.8	500.2	498.8	499.3
10°	503.5	502.9	502.3	501.7	501.0	499.8	498.2	496.5	494.8	493.2	493.3
12.5°	497.9	497.2	496.5	495.8	495.1	493.7	491.6	489.6	487.6	485.5	485.4
15°	488.7	487.6	486.6	485.5	484.6	482.8	480.2	477.6	475.0	472.4	472.0
17.5°	476.9	475.7	474.6	473.3	472.2	469.9	466.6	463.3	460.1	456.8	455.8
20°	468.2	466.8	465.3	463.9	462.4	459.9	456.4	452.8	449.3	445.9	444.6
22.5°	458.6	456.9	455.2	453.5	451.8	449.2	445.4	441.7	437.9	434.2	432.7
25°	444.6	442.3	440.0	437.7	435.3	432.0	427.8	423.6	419.3	415.1	413.1
27.5°	427.6	425.0	422.4	419.9	417.3	413.8	409.0	404.2	399.5	394.8	392.1
30°	415.9	413.1	410.4	407.6	404.8	400.8	395.7	390.5	385.3	380.1	377.0
32.5°	404.3	401.1	398.0	394.8	391.7	387.4	381.9	376.5	371.0	365.5	362.1
35°	384.8	381.4	378.1	374.8	371.5	366.9	361.2	355.4	349.7	344.0	340.1
37.5°	365.0	361.2	357.6	353.9	350.2	345.3	339.2	333.1	327.0	320.8	316.4
40°	352.3	348.3	344.2	340.2	336.1	330.7	324.2	317.6	311.1	304.5	299.8
42.5°	338.0	333.9	329.9	325.8	321.8	316.4	309.6	302.8	296.0	289.3	284.0
45°	316.2	312.0	307.9	303.7	299.5	293.9	286.9	279.7	272.6	265.5	260.2
47.5°	294.4	289.8	285.2	280.6	276.1	270.3	263.1	256.0	249.0	241.8	236.1
50°	278.4	274.0	269.7	265.4	261.0	255.1	247.6	240.1	232.6	225.2	219.5
52.5°	264.1	259.4	254.7	249.9	245.2	239.2	231.8	224.4	217.0	209.6	203.7
55°	240.1	235.6	231.1	226.6	222.0	215.9	208.0	200.2	192.3	184.5	179.1
57.5°	218.0	213.1	208.2	203.2	198.3	191.9	184.0	176.1	168.3	160.4	155.3
60°	202.8	197.7	192.6	187.5	182.4	176.1	168.4	160.8	153.1	145.4	140.4
62.5°	187.4	182.4	177.3	172.3	167.2	160.8	153.1	145.4	137.8	130.1	125.5
65°	164.2	159.1	154.0	148.9	143.8	137.7	130.5	123.2	116.1	108.9	104.3
67.5°	140.8	135.6	130.5	125.4	120.2	114.2	107.3	100.4	93.5	86.6	83.2
70°	125.5	120.5	115.5	110.5	105.6	99.8	93.4	86.9	80.4	73.9	70.7
72.5°	110.2	105.3	100.4	95.4	90.5	85.2	79.3	73.4	67.5	61.6	59.0
75°	86.9	82.4	77.9	73.6	69.1	64.4	59.3	54.2	49.1	44.1	43.2
77.5°	65.5	61.5	57.5	53.5	49.6	45.9	42.6	39.3	36.1	32.8	32.4
80°	51.9	48.2	44.4	40.6	36.8	34.0	32.0	30.1	28.1	26.2	25.9
82.5°	39.0	35.7	32.5	29.2	25.9	23.8	22.9	22.0	21.1	20.2	19.9
85°	22.0	20.0	17.9	16.0	13.9	12.8	12.5	12.2	11.9	11.6	11.4
87.5°	8.2	7.8	7.5	7.1	6.8	6.9	7.5	8.1	8.7	9.3	9.4
90°	1.1	3.3	5.6	7.9	10.3	12.9	15.9	18.9	21.8	24.9	25.8
92.5°	19.3	18.6	18.0	17.3	16.7	17.5	19.8	22.0	24.3	26.5	28.0
95°	63.2	53.8	44.3	34.9	25.4	22.0	24.5	27.0	29.6	32.1	33.7
97.5°	127.0	122.8	118.5	114.3	110.0	99.7	83.1	66.5	49.9	33.3	35.2
100°	175.0	179.7	184.3	188.9	193.5	177.8	142.0	106.0	70.1	34.2	36.0
102.5°	229.8	233.1	236.4	239.7	243.1	225.1	185.8	146.6	107.4	68.1	62.4
105°	308.7	311.3	313.8	316.3	318.9	309.8	289.0	268.3	247.6	226.9	186.1
107.5°	392.0	394.0	396.1	398.1	400.1	402.8	406.1	409.3	412.6	415.9	385.9
110°	447.5	449.4	451.2	453.1	455.0	457.1	459.7	462.2	464.7	467.3	459.7



TEST NUMBER: P332267-940

CATALOG NUMBER: S123RDIP-S340D1195U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	500.6	502.2	503.9	505.6	507.2	509.3	511.8	514.4	516.9	519.4	519.6
115°	579.2	580.5	581.8	583.3	584.6	586.4	588.4	590.5	592.6	594.7	597.0
117.5°	655.1	656.8	658.5	660.3	662.0	663.3	664.4	665.5	666.6	667.6	669.4
120°	702.4	704.5	706.6	708.6	710.7	712.1	712.7	713.5	714.2	714.8	716.7
122.5°	750.5	752.2	753.9	755.5	757.3	758.6	759.5	760.4	761.2	762.1	763.4
125°	816.4	818.2	820.0	821.9	823.8	825.1	826.0	827.0	827.9	828.8	829.3
127.5°	880.2	882.0	883.9	885.7	887.5	889.0	890.1	891.3	892.3	893.4	894.2
130°	920.0	921.9	923.6	925.5	927.3	928.7	929.6	930.6	931.5	932.4	933.4
132.5°	958.1	959.9	961.8	963.6	965.5	966.7	967.5	968.2	968.9	969.7	970.6
135°	1016.3	1017.7	1019.0	1020.5	1021.8	1023.0	1024.0	1024.8	1025.7	1026.7	1027.3
137.5°	1066.0	1067.8	1069.5	1071.3	1073.1	1074.2	1074.7	1075.2	1075.7	1076.2	1077.3
140°	1099.2	1100.5	1102.0	1103.3	1104.7	1105.7	1106.4	1107.1	1107.9	1108.5	1109.5
142.5°	1129.9	1131.2	1132.7	1134.0	1135.4	1136.4	1137.1	1137.8	1138.5	1139.2	1140.0
145°	1172.8	1174.4	1176.0	1177.6	1179.2	1180.3	1180.7	1181.2	1181.6	1182.1	1182.5
147.5°	1213.2	1214.2	1215.3	1216.3	1217.4	1218.2	1218.6	1219.1	1219.5	1219.9	1220.5
150°	1238.1	1238.7	1239.4	1240.1	1240.8	1241.4	1241.8	1242.2	1242.8	1243.2	1243.7
152.5°	1260.4	1260.7	1261.1	1261.3	1261.7	1261.9	1262.2	1262.6	1262.8	1263.1	1263.9
155°	1291.9	1291.5	1290.9	1290.5	1290.0	1289.9	1290.1	1290.4	1290.7	1290.8	1292.0
157.5°	1316.3	1316.3	1316.3	1316.2	1316.2	1316.0	1315.8	1315.5	1315.4	1315.1	1316.5
160°	1331.2	1331.1	1330.8	1330.6	1330.3	1330.1	1329.9	1329.6	1329.5	1329.2	1330.6
162.5°	1345.3	1344.8	1344.2	1343.5	1342.9	1342.6	1342.3	1342.1	1341.8	1341.6	1343.2
165°	1362.4	1361.6	1360.9	1360.3	1359.6	1359.1	1358.9	1358.6	1358.4	1358.2	1360.0
167.5°	1375.6	1374.7	1373.8	1372.9	1371.9	1371.5	1371.5	1371.5	1371.5	1371.5	1373.3
170°	1383.0	1382.2	1381.3	1380.3	1379.4	1378.9	1378.9	1378.9	1378.9	1378.9	1380.7
172.5°	1388.0	1387.0	1385.8	1384.7	1383.6	1383.1	1383.3	1383.5	1383.7	1383.8	1385.7
175°	1394.5	1393.3	1392.1	1391.0	1389.8	1389.4	1389.6	1389.8	1390.1	1390.3	1392.0
177.5°	1396.2	1395.2	1394.3	1393.4	1392.4	1392.0	1392.2	1392.4	1392.6	1392.8	1394.3
180°	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5



TEST NUMBER: P332267-940

CATALOG NUMBER: S123RDIP-S340D1195U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	512.3	512.3	512.3	512.3	512.3	512.3	512.3	512.3
2.5°	510.2	511.0	511.9	512.2	512.1	511.9	511.8	511.7
5°	506.9	507.7	508.5	508.9	508.7	508.5	508.4	508.2
7.5°	499.8	500.2	500.7	500.8	500.4	500.2	499.8	499.5
10°	493.4	493.5	493.6	493.4	492.9	492.5	492.0	491.5
12.5°	485.4	485.4	485.4	485.0	484.5	483.9	483.4	482.9
15°	471.4	471.0	470.6	470.0	469.4	468.7	468.1	467.4
17.5°	454.9	453.9	452.9	451.9	450.9	450.0	449.1	448.1
20°	443.4	442.2	441.0	439.9	438.7	437.7	436.6	435.4
22.5°	431.2	429.7	428.2	427.0	425.9	424.9	423.8	422.8
25°	411.2	409.3	407.3	405.8	404.8	403.9	402.8	401.8
27.5°	389.4	386.7	384.1	381.9	380.3	378.8	377.3	375.7
30°	373.9	370.8	367.7	365.3	363.8	362.4	360.9	359.4
32.5°	358.6	355.3	351.8	349.3	347.8	346.3	344.6	343.1
35°	336.1	332.1	328.1	325.3	323.7	322.0	320.3	318.7
37.5°	311.8	307.3	302.8	299.5	297.5	295.4	293.4	291.3
40°	295.0	290.2	285.3	281.9	279.7	277.7	275.5	273.4
42.5°	278.7	273.6	268.3	264.7	262.8	260.9	259.0	257.1
45°	254.9	249.7	244.4	240.7	238.5	236.3	234.1	231.8
47.5°	230.3	224.6	218.9	215.1	213.1	211.2	209.1	207.1
50°	213.7	208.0	202.3	198.4	196.3	194.1	192.0	189.8
52.5°	197.7	191.7	185.8	181.9	179.9	178.1	176.2	174.2
55°	173.8	168.4	163.1	159.4	157.7	155.8	153.9	152.0
57.5°	150.3	145.2	140.2	136.8	135.3	133.7	132.2	130.5
60°	135.5	130.5	125.5	122.2	120.6	119.0	117.5	115.9
62.5°	120.7	116.1	111.4	108.2	106.6	105.0	103.3	101.7
65°	99.8	95.3	90.8	88.0	86.9	86.0	85.0	83.9
67.5°	79.8	76.4	73.0	70.8	69.7	68.7	67.6	66.5
70°	67.5	64.3	61.0	58.9	57.9	56.9	55.8	54.8
72.5°	56.4	53.8	51.1	49.6	49.1	48.7	48.3	47.9
75°	42.2	41.3	40.3	39.8	39.6	39.4	39.2	39.1
77.5°	31.8	31.3	30.9	30.5	30.3	30.1	30.0	29.8
80°	25.6	25.3	25.1	24.9	24.6	24.4	24.3	24.1
82.5°	19.6	19.4	19.1	18.9	18.9	18.8	18.8	18.8
85°	11.2	11.1	10.9	10.8	10.8	10.8	10.8	10.8
87.5°	9.5	9.6	9.7	9.8	9.8	9.8	9.9	9.9
90°	26.7	27.6	28.5	29.2	29.7	30.1	30.6	31.1
92.5°	29.4	30.9	32.5	33.3	33.5	33.9	34.2	34.4
95°	35.3	36.9	38.5	39.3	39.3	39.3	39.3	39.3
97.5°	37.0	38.9	40.8	41.7	42.0	42.3	42.4	42.7
100°	37.9	39.7	41.6	42.6	42.8	43.1	43.2	43.5
102.5°	56.7	51.0	45.3	42.7	43.1	43.5	44.0	44.3
105°	145.3	104.6	63.8	43.8	44.2	44.7	45.1	45.6
107.5°	356.1	326.2	296.3	266.0	235.3	204.6	173.9	143.2
110°	452.0	444.4	436.8	416.6	383.7	350.7	317.8	284.9



TEST NUMBER: P332267-940

CATALOG NUMBER: S123RDIP-S340D1195U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	519.7	519.9	520.0	516.6	509.6	502.7	495.7	488.7
115°	599.2	601.5	603.9	605.5	606.4	607.3	608.2	609.1
117.5°	671.3	673.2	674.9	676.0	676.2	676.4	676.5	676.7
120°	718.5	720.3	722.2	723.1	723.1	723.1	723.1	723.1
122.5°	764.6	766.0	767.2	767.9	768.1	768.3	768.6	768.7
125°	829.7	830.2	830.6	831.1	831.5	832.1	832.5	832.9
127.5°	894.9	895.6	896.3	896.5	896.1	895.6	895.2	894.7
130°	934.2	935.1	936.1	936.3	935.9	935.4	935.0	934.5
132.5°	971.5	972.5	973.4	973.5	972.9	972.2	971.6	970.9
135°	1028.1	1028.8	1029.5	1029.5	1028.8	1028.1	1027.3	1026.7
137.5°	1078.4	1079.5	1080.6	1080.9	1080.5	1080.0	1079.6	1079.1
140°	1110.4	1111.3	1112.2	1112.4	1112.0	1111.5	1111.1	1110.6
142.5°	1140.7	1141.4	1142.1	1142.2	1141.6	1140.9	1140.2	1139.6
145°	1183.0	1183.5	1183.9	1184.1	1184.1	1184.1	1184.1	1184.1
147.5°	1220.9	1221.4	1221.8	1221.6	1220.5	1219.4	1218.3	1217.3
150°	1244.1	1244.6	1245.0	1244.9	1244.2	1243.6	1242.9	1242.2
152.5°	1264.7	1265.6	1266.4	1266.3	1265.2	1264.2	1263.1	1262.0
155°	1293.2	1294.3	1295.5	1295.3	1294.0	1292.6	1291.2	1289.9
157.5°	1317.9	1319.2	1320.6	1320.4	1318.7	1316.8	1315.0	1313.2
160°	1331.9	1333.3	1334.7	1334.6	1333.0	1331.4	1329.7	1328.1
162.5°	1344.8	1346.3	1347.9	1347.9	1346.5	1345.1	1343.6	1342.2
165°	1361.9	1363.7	1365.6	1365.7	1364.1	1362.4	1360.8	1359.2
167.5°	1375.1	1377.0	1378.9	1378.9	1377.0	1375.1	1373.3	1371.5
170°	1382.6	1384.5	1386.3	1386.3	1384.5	1382.6	1380.7	1378.9
172.5°	1387.6	1389.4	1391.2	1391.2	1389.1	1387.1	1385.1	1383.0
175°	1393.6	1395.2	1396.8	1396.6	1394.8	1392.9	1391.2	1389.3
177.5°	1395.7	1397.2	1398.6	1398.5	1396.7	1394.8	1392.9	1391.2
180°	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5

(END OF REPORT)