

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P832083

Luminaire Tested: S123RDIP-S340D1195U940-4F0-1E-UDD-G

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P832083
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-2, G3-1807-864-5)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-S340D1195U940-4F0-1E-UDD-G
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, GRAZE OPTIC
UPLIGHT 1195 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5567.1 lumens
Efficiency: N/A
Efficacy: 128.3 lumens/watt
Spacing Criteria (0/90/45): 0.55 / 1.17 / 0.8
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 43.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P832083

CATALOG NUMBER: S123RDIP-S340D1195U940-4F0-1E-UDD-G

Luminous Intensity Polar Plot





TEST NUMBER: P832083

CATALOG NUMBER: S123RDIP-S340D1195U940-4F0-1E-UDD-G

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	32	32	32	24				24
1	92	88	85	81	82	79	76	73	61	59	57	44	43	42	29	28	28	21				21
2	84	77	72	67	75	69	64	60	53	50	48	39	37	35	26	25	24	18				18
3	77	68	62	56	68	61	55	51	48	44	40	35	32	30	23	22	21	16				16
4	71	61	53	48	63	54	48	43	42	38	35	31	29	26	21	19	18	14				14
5	65	54	47	41	58	49	42	37	38	34	30	28	25	23	19	17	16	12				12
6	60	49	41	36	53	44	37	33	34	30	26	26	23	20	18	16	14	11				11
7	55	44	37	31	49	40	33	29	31	27	23	23	20	18	16	14	13	10				10
8	51	40	33	28	46	36	30	25	29	24	21	22	19	16	15	13	12	9				9
9	48	36	29	25	43	33	27	23	26	22	19	20	17	15	14	12	11	9				9
10	45	33	27	22	40	30	24	20	24	20	17	18	15	13	13	11	10	8				8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	10663	10663	10663	10663	10663
5°	12661	12257	10730	8674	8053
10°	11471	12450	10676	6949	5962
15°	7899	10674	10564	5680	4716
20°	5495	8219	10352	4789	4145
25°	4187	6264	10043	4257	3821
30°	3644	5008	9657	3952	3539
35°	3347	4225	9110	3696	3282
40°	3053	3773	8396	3444	3048
45°	2757	3449	7623	3206	2813
50°	2503	3183	6713	2972	2524
55°	2263	2924	5838	2744	2164
60°	2028	2659	5072	2493	2045
65°	1872	2358	4365	2239	1936
70°	1520	2039	3808	2027	1574
75°	1335	1622	3227	1680	1385
80°	1209	1370	2641	1407	1308
85°	1099	1198	2001	1284	1198

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 8044 cd/sqm



TEST NUMBER: P832083

CATALOG NUMBER: S123RDIP-S340D1195U940-4F0-1E-UDD-G

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.3	1.6
10°-20°	208.9	3.8
20°-30°	239.7	4.3
30°-40°	236.3	4.2
40°-50°	208.4	3.7
50°-60°	160.3	2.9
60°-70°	105.4	1.9
70°-80°	51.2	0.9
80°-90°	15.7	0.3
90°-100°	49.2	0.9
100°-110°	237.7	4.3
110°-120°	582.6	10.5
120°-130°	739.6	13.3
130°-140°	790.1	14.2
140°-150°	738.8	13.3
150°-160°	595.9	10.7
160°-170°	384.6	6.9
170°-180°	132.5	2.4
0°-30°	539.0	9.7
0°-40°	775.3	13.9
0°-60°	1143.9	20.5
0°-90°	1316.2	23.6
90°-120°	869.4	15.6
90°-150°	3137.9	56.4
90°-180°	4251.0	76.4
0°-180°	5567.1	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	991	991	991	991	991	
5°	1172	1134	993	803	745	107
15°	709	958	948	510	423	200
25°	352	527	846	358	322	167
35°	255	322	693	281	250	159
45°	181	227	501	211	185	141
55°	121	156	311	146	115	108
65°	74	93	171	88	76	72
75°	32	39	78	40	33	35
85°	9	10	16	10	10	9
90°	31	25	1	25	31	14
95°	39	32	63	32	39	33
105°	46	227	309	227	46	95
115°	609	595	579	595	609	573
125°	833	829	816	829	833	744
135°	1027	1027	1016	1027	1027	792
145°	1184	1182	1173	1182	1184	739
155°	1290	1291	1292	1291	1290	595
165°	1359	1358	1362	1358	1359	384
175°	1389	1390	1394	1390	1389	132
180°	1394	1394	1394	1394	1394	



TEST NUMBER: P832083

CATALOG NUMBER: S123RDIP-S340D1195U940-4F0-1E-UDD-G

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	990.6	990.6	990.6	990.6	990.6	990.6	990.6	990.6	990.6	990.6	990.6
2.5°	1097.9	1094.4	1090.9	1089.9	1088.9	1085.7	1082.4	1075.1	1067.8	1060.3	1052.8
5°	1171.8	1172.2	1172.6	1171.6	1170.6	1166.3	1162.0	1153.1	1144.2	1134.4	1124.7
7.5°	1149.0	1155.5	1162.0	1163.2	1164.5	1167.7	1171.0	1168.9	1166.9	1163.2	1159.6
10°	1049.5	1049.1	1048.7	1056.0	1063.3	1085.1	1106.8	1118.0	1129.1	1139.1	1149.0
12.5°	887.1	887.7	888.3	912.2	936.2	956.7	977.2	1005.7	1034.1	1064.8	1095.4
15°	708.8	718.7	728.7	750.0	771.3	802.2	833.0	871.2	909.4	957.9	1006.5
17.5°	582.0	586.3	590.6	611.1	631.6	660.8	690.1	733.3	776.6	839.1	901.7
20°	479.7	483.5	487.4	502.2	517.0	545.1	573.1	614.3	655.5	717.5	779.4
22.5°	400.5	408.0	415.5	425.5	435.4	455.7	476.0	518.1	560.1	616.6	673.0
25°	352.5	356.0	359.5	368.0	376.5	396.0	415.5	443.3	471.1	527.4	583.7
27.5°	320.1	321.1	322.1	328.4	334.7	347.3	359.9	385.6	411.4	457.7	504.0
30°	293.2	295.1	296.9	301.8	306.7	315.8	324.9	343.2	361.5	402.9	444.3
32.5°	272.5	273.5	274.6	278.6	282.7	289.4	296.1	310.5	324.9	356.6	388.3
35°	254.7	254.9	255.1	258.1	261.2	267.7	274.2	286.1	298.1	321.5	344.8
37.5°	234.4	235.8	237.2	239.4	241.7	247.4	253.0	262.8	272.5	291.8	311.1
40°	217.3	218.5	219.7	222.4	225.0	229.5	233.9	242.9	251.8	268.5	285.1
42.5°	200.2	201.0	201.9	204.5	207.1	212.6	218.1	225.2	232.3	246.1	259.9
45°	181.1	183.2	185.2	188.1	190.9	195.6	200.2	207.5	214.9	226.6	238.4
47.5°	165.3	166.3	167.3	169.8	172.2	177.9	183.6	190.1	196.6	207.5	218.5
50°	149.5	149.9	150.3	152.5	154.7	159.8	164.9	172.4	179.9	190.1	200.2
52.5°	134.4	135.5	136.5	138.7	140.9	144.4	147.8	155.6	163.3	173.2	183.2
55°	120.6	121.2	121.8	123.5	125.1	129.2	133.2	139.9	146.6	155.8	164.9
57.5°	107.6	108.4	109.3	110.5	111.7	115.3	119.0	124.9	130.8	139.9	149.1
60°	94.2	95.2	96.3	97.7	99.1	101.9	104.8	110.1	115.3	123.5	131.6
62.5°	84.5	84.7	84.9	86.1	87.3	89.4	91.4	95.7	99.9	108.0	116.2
65°	73.5	74.1	74.7	75.3	76.0	77.6	79.2	82.9	86.5	92.6	98.7
67.5°	62.1	62.8	63.4	64.4	65.4	66.8	68.2	70.7	73.1	78.8	84.5
70°	48.3	48.3	48.3	50.0	51.6	54.0	56.5	58.3	60.1	64.8	69.5
72.5°	39.4	39.6	39.8	40.0	40.2	41.6	43.1	46.1	49.1	52.0	54.8
75°	32.1	32.3	32.5	32.7	32.9	33.3	33.7	34.7	35.7	39.0	42.2
77.5°	25.6	25.8	26.0	26.2	26.4	26.8	27.2	27.6	28.0	29.2	30.5
80°	19.5	19.7	19.9	20.1	20.3	20.5	20.7	21.1	21.5	22.1	22.7
82.5°	14.2	14.2	14.2	14.2	14.2	14.6	15.0	15.0	15.0	15.4	15.8
85°	8.9	8.9	8.9	9.1	9.3	9.3	9.3	9.5	9.7	9.7	9.7
87.5°	4.1	3.9	3.7	3.9	4.1	4.1	4.1	4.3	4.5	4.5	4.5
90°	31.1	30.6	30.2	29.7	29.2	28.5	27.6	26.7	25.8	24.9	21.9
92.5°	35.2	35.0	34.8	34.5	34.3	33.4	31.8	30.2	28.5	26.9	24.9
95°	39.4	39.4	39.4	39.4	39.4	38.6	37.0	35.3	33.7	32.1	29.6
97.5°	42.5	42.2	42.0	41.8	41.6	40.5	38.7	36.8	35.0	33.2	44.9
100°	43.5	43.3	43.1	42.8	42.6	41.6	39.7	37.9	36.0	34.2	70.1
102.5°	44.5	44.1	43.6	43.2	42.7	46.3	53.9	61.5	69.1	76.7	116.7
105°	45.6	45.1	44.7	44.2	43.7	63.9	104.6	145.4	186.1	226.9	247.6
107.5°	107.7	137.9	168.1	198.2	228.4	261.2	296.6	332.1	367.5	403.0	399.5
110°	284.9	317.8	350.7	383.7	416.6	436.8	444.4	452.0	459.6	467.2	464.7



TEST NUMBER: P832083

CATALOG NUMBER: S123RDIP-S340D1195U940-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	539.8	540.2	540.7	541.1	541.6	540.8	538.7	536.6	534.6	532.5	530.0
115°	609.2	608.2	607.3	606.4	605.5	603.9	601.6	599.3	597.0	594.7	592.6
117.5°	665.1	664.9	664.7	664.4	664.2	663.2	661.3	659.5	657.6	655.8	654.6
120°	723.1	723.1	723.1	723.1	723.1	722.2	720.4	718.5	716.7	714.8	714.1
122.5°	780.1	779.9	779.6	779.4	779.2	778.5	777.3	776.2	775.0	773.9	773.0
125°	832.9	832.5	832.0	831.6	831.1	830.6	830.2	829.7	829.3	828.8	827.9
127.5°	884.7	885.2	885.7	886.1	886.6	886.5	885.8	885.1	884.4	883.7	882.6
130°	934.5	934.9	935.4	935.9	936.3	936.1	935.2	934.2	933.3	932.4	931.5
132.5°	980.1	980.7	981.4	982.1	982.8	982.7	981.8	980.9	979.9	979.0	978.3
135°	1026.7	1027.4	1028.1	1028.7	1029.4	1029.4	1028.7	1028.1	1027.4	1026.7	1025.8
137.5°	1071.2	1071.7	1072.1	1072.6	1073.1	1072.7	1071.6	1070.4	1069.3	1068.1	1067.7
140°	1110.6	1111.1	1111.5	1112.0	1112.4	1112.2	1111.3	1110.4	1109.4	1108.5	1107.8
142.5°	1146.8	1147.5	1148.2	1148.9	1149.6	1149.6	1148.9	1148.2	1147.5	1146.8	1146.2
145°	1184.1	1184.1	1184.1	1184.1	1184.1	1183.9	1183.5	1183.0	1182.5	1182.1	1181.6
147.5°	1211.1	1212.2	1213.4	1214.5	1215.7	1216.0	1215.6	1215.1	1214.7	1214.2	1213.7
150°	1242.2	1242.9	1243.5	1244.2	1244.9	1245.0	1244.6	1244.1	1243.7	1243.2	1242.7
152.5°	1267.0	1268.2	1269.3	1270.5	1271.6	1271.7	1270.8	1269.9	1269.0	1268.1	1267.8
155°	1289.8	1291.2	1292.6	1294.0	1295.3	1295.5	1294.3	1293.2	1292.0	1290.9	1290.6
157.5°	1309.5	1311.3	1313.2	1315.0	1316.9	1317.1	1315.7	1314.3	1313.0	1311.6	1311.8
160°	1328.1	1329.8	1331.4	1333.0	1334.6	1334.7	1333.3	1331.9	1330.6	1329.2	1329.4
162.5°	1345.8	1347.1	1348.5	1349.9	1351.3	1351.2	1349.6	1347.9	1346.3	1344.7	1345.0
165°	1359.2	1360.8	1362.5	1364.1	1365.7	1365.6	1363.7	1361.9	1360.0	1358.2	1358.4
167.5°	1369.6	1371.4	1373.3	1375.1	1377.0	1377.0	1375.1	1373.3	1371.4	1369.6	1369.6
170°	1378.9	1380.8	1382.6	1384.4	1386.3	1386.3	1384.4	1382.6	1380.8	1378.9	1378.9
172.5°	1384.1	1386.2	1388.2	1390.3	1392.4	1392.5	1390.7	1388.8	1387.0	1385.1	1384.9
175°	1389.3	1391.1	1393.0	1394.8	1396.6	1396.8	1395.1	1393.5	1391.9	1390.3	1390.1
177.5°	1390.3	1392.6	1394.9	1397.2	1399.5	1399.7	1397.9	1396.1	1394.2	1392.4	1392.2
180°	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5



TEST NUMBER: P832083

CATALOG NUMBER: S123RDIP-S340D1195U940-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	990.6	990.6	990.6	990.6	990.6	990.6	990.6	990.6	990.6	990.6	990.6
2.5°	1051.8	1050.7	1041.0	1031.2	1021.7	1012.2	1005.0	997.9	986.0	974.0	966.5
5°	1116.9	1109.2	1093.8	1078.4	1055.2	1032.1	1012.6	993.1	968.3	943.5	922.8
7.5°	1153.3	1147.0	1128.3	1109.6	1079.0	1048.3	1017.8	987.4	950.8	914.3	883.0
10°	1154.3	1159.6	1144.2	1128.7	1094.2	1059.7	1018.2	976.8	927.7	878.5	838.1
12.5°	1118.2	1140.9	1137.7	1134.4	1099.3	1064.1	1013.8	963.4	903.1	842.8	792.2
15°	1050.5	1094.6	1107.6	1120.6	1091.6	1062.5	1005.2	948.0	877.1	806.2	748.1
17.5°	963.4	1025.1	1059.5	1093.8	1072.7	1051.6	988.8	926.0	846.2	766.4	703.3
20°	860.2	941.1	994.9	1048.7	1041.0	1033.3	968.5	903.7	817.6	731.5	663.1
22.5°	758.3	843.6	917.9	992.3	1000.2	1008.1	942.7	877.3	783.1	688.8	619.2
25°	670.4	757.1	845.6	934.2	952.0	969.9	907.8	845.6	747.9	650.3	581.0
27.5°	586.5	668.9	766.4	863.9	896.4	928.9	872.0	815.2	713.4	611.7	542.6
30°	518.1	591.8	691.3	790.8	836.1	881.4	829.2	777.0	676.1	575.1	507.5
32.5°	454.3	520.3	620.2	720.1	772.7	825.3	780.2	735.2	638.1	541.0	474.2
35°	403.9	463.0	556.2	649.5	708.3	767.2	730.3	693.3	598.5	503.6	440.5
37.5°	360.7	410.2	497.7	585.3	647.8	710.4	679.5	648.6	559.5	470.3	410.6
40°	324.9	364.7	446.2	527.6	588.9	650.3	623.9	597.5	517.7	437.8	382.0
42.5°	294.3	328.6	401.7	474.8	531.1	587.3	569.8	552.4	480.1	407.8	356.0
45°	267.3	296.1	360.5	424.8	476.6	528.4	514.6	500.8	438.5	376.1	328.6
47.5°	243.3	268.1	325.5	383.0	429.5	476.0	463.2	450.4	398.8	347.3	304.0
50°	221.4	242.5	290.4	338.3	380.2	422.0	411.4	400.9	358.2	315.6	278.2
52.5°	200.6	218.1	261.2	304.2	337.9	371.6	363.5	355.4	322.5	289.6	255.7
55°	180.9	197.0	233.3	269.7	298.5	327.4	319.2	311.1	285.5	259.9	230.1
57.5°	163.1	177.1	206.5	236.0	258.9	281.9	278.0	274.2	252.8	231.5	206.9
60°	144.2	156.8	182.2	207.5	226.0	244.5	240.0	235.6	220.3	205.1	184.0
62.5°	127.3	138.5	158.8	179.1	194.1	209.2	205.9	202.7	191.1	179.5	162.1
65°	109.7	120.6	137.1	153.5	165.3	177.1	174.2	171.4	162.7	153.9	139.9
67.5°	93.6	102.8	117.0	131.2	139.1	147.0	145.4	143.8	137.1	130.4	119.4
70°	77.4	85.3	97.1	108.9	114.3	119.8	120.4	121.0	114.9	108.9	100.7
72.5°	61.1	67.4	78.4	89.4	93.6	97.9	97.7	97.5	93.8	90.2	82.9
75°	46.9	51.6	60.1	68.6	72.3	76.0	76.8	77.6	74.1	70.7	66.6
77.5°	33.7	37.0	43.5	50.0	54.0	58.1	58.5	58.9	57.3	55.6	51.8
80°	23.8	24.8	28.8	32.9	37.2	41.4	42.0	42.6	41.0	39.4	37.0
82.5°	16.4	17.1	18.5	19.9	23.4	26.8	27.6	28.4	27.6	26.8	24.2
85°	10.0	10.2	10.8	11.4	13.0	14.6	15.4	16.2	15.8	15.4	14.0
87.5°	4.5	4.5	4.7	4.9	5.3	5.7	6.7	7.7	7.1	6.5	5.9
90°	18.9	15.9	12.9	10.2	7.9	5.6	3.3	1.0	3.3	5.6	7.9
92.5°	22.8	20.7	18.6	18.3	19.7	21.1	22.4	23.8	22.4	21.1	19.7
95°	27.1	24.5	22.0	25.4	34.9	44.3	53.8	63.2	53.8	44.3	34.9
97.5°	56.6	68.4	80.1	89.2	95.7	102.1	108.5	115.0	108.5	102.1	95.7
100°	106.0	141.9	177.8	193.5	188.9	184.3	179.7	175.1	179.7	184.3	188.9
102.5°	156.8	196.8	236.9	255.4	252.4	249.4	246.5	243.5	246.5	249.4	252.4
105°	268.3	289.0	309.8	318.9	316.3	313.8	311.3	308.7	311.3	313.8	316.3
107.5°	396.1	392.6	389.2	386.4	384.4	382.3	380.2	378.1	380.2	382.3	384.4
110°	462.2	459.6	457.1	454.9	453.1	451.2	449.4	447.6	449.4	451.2	453.1



TEST NUMBER: P832083

CATALOG NUMBER: S123RDIP-S340D1195U940-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	527.4	524.9	522.4	520.3	518.7	517.1	515.5	513.9	515.5	517.1	518.7
115°	590.5	588.4	586.4	584.6	583.3	581.9	580.5	579.1	580.5	581.9	583.3
117.5°	653.5	652.3	651.2	649.8	648.2	646.6	645.0	643.4	645.0	646.6	648.2
120°	713.5	712.8	712.1	710.7	708.6	706.6	704.5	702.4	704.5	706.6	708.6
122.5°	772.0	771.1	770.2	768.9	767.3	765.7	764.1	762.5	764.1	765.7	767.3
125°	827.0	826.0	825.1	823.7	821.9	820.0	818.2	816.4	818.2	820.0	821.9
127.5°	881.4	880.3	879.1	877.6	875.8	873.9	872.1	870.2	872.1	873.9	875.8
130°	930.6	929.6	928.7	927.3	925.5	923.6	921.8	920.0	921.8	923.6	925.5
132.5°	977.6	976.9	976.3	975.0	973.1	971.3	969.5	967.6	969.5	971.3	973.1
135°	1024.8	1023.9	1023.0	1021.8	1020.5	1019.1	1017.7	1016.3	1017.7	1019.1	1020.5
137.5°	1067.2	1066.7	1066.3	1065.1	1063.3	1061.4	1059.6	1057.8	1059.6	1061.4	1063.3
140°	1107.1	1106.4	1105.8	1104.7	1103.3	1102.0	1100.6	1099.2	1100.6	1102.0	1103.3
142.5°	1145.5	1144.8	1144.1	1143.1	1141.7	1140.3	1138.9	1137.5	1138.9	1140.3	1141.7
145°	1181.2	1180.7	1180.2	1179.2	1177.6	1176.0	1174.4	1172.7	1174.4	1176.0	1177.6
147.5°	1213.3	1212.8	1212.3	1211.5	1210.4	1209.2	1208.1	1206.9	1208.1	1209.2	1210.4
150°	1242.3	1241.8	1241.4	1240.8	1240.1	1239.4	1238.7	1238.0	1238.7	1239.4	1240.1
152.5°	1267.6	1267.4	1267.1	1266.9	1266.7	1266.4	1266.2	1266.0	1266.2	1266.4	1266.7
155°	1290.4	1290.2	1289.9	1290.0	1290.5	1291.0	1291.4	1291.9	1291.4	1291.0	1290.5
157.5°	1312.0	1312.3	1312.5	1312.6	1312.6	1312.6	1312.6	1312.6	1312.6	1312.6	1312.6
160°	1329.6	1329.9	1330.1	1330.3	1330.6	1330.8	1331.0	1331.3	1331.0	1330.8	1330.6
162.5°	1345.2	1345.4	1345.6	1346.1	1346.8	1347.5	1348.2	1348.9	1348.2	1347.5	1346.8
165°	1358.7	1358.9	1359.1	1359.6	1360.3	1361.0	1361.6	1362.3	1361.6	1361.0	1360.3
167.5°	1369.6	1369.6	1369.6	1370.0	1371.0	1371.9	1372.8	1373.7	1372.8	1371.9	1371.0
170°	1378.9	1378.9	1378.9	1379.4	1380.3	1381.2	1382.1	1383.1	1382.1	1381.2	1380.3
172.5°	1384.7	1384.4	1384.2	1384.7	1385.8	1387.0	1388.1	1389.3	1388.1	1387.0	1385.8
175°	1389.8	1389.6	1389.4	1389.8	1391.0	1392.2	1393.3	1394.5	1393.3	1392.2	1391.0
177.5°	1391.9	1391.7	1391.5	1391.9	1393.1	1394.2	1395.4	1396.5	1395.4	1394.2	1393.1
180°	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5



TEST NUMBER: P832083

CATALOG NUMBER: S123RDIP-S340D1195U940-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	990.6	990.6	990.6	990.6	990.6	990.6	990.6	990.6	990.6	990.6	990.6
2.5°	958.9	947.4	935.8	927.5	919.1	908.8	898.4	898.0	897.6	889.9	882.2
5°	902.1	882.0	861.9	842.2	822.5	802.8	783.1	778.6	774.1	767.4	760.7
7.5°	851.7	819.6	787.5	762.4	737.2	717.5	697.8	684.4	671.0	660.6	650.3
10°	797.7	757.9	718.1	687.6	657.2	635.8	614.5	599.1	583.7	576.3	569.0
12.5°	741.6	698.4	655.1	625.3	595.4	569.8	544.3	530.2	516.2	506.1	495.9
15°	690.1	643.6	597.1	565.4	533.7	509.7	485.8	471.8	457.7	447.6	437.4
17.5°	640.1	593.2	546.3	514.2	482.1	460.4	438.7	425.0	411.4	405.1	398.8
20°	594.6	547.3	500.0	469.7	439.5	418.1	396.8	389.5	382.2	376.3	370.4
22.5°	549.5	504.0	458.6	429.5	400.5	385.0	369.6	363.7	357.8	353.4	348.9
25°	511.8	466.5	421.2	395.8	370.4	358.4	346.5	342.6	338.7	334.3	329.8
27.5°	473.6	430.5	387.5	367.2	346.9	337.1	327.4	322.5	317.6	314.0	310.3
30°	439.9	400.1	360.3	343.4	326.6	318.0	309.5	304.2	298.9	295.5	292.0
32.5°	407.4	372.0	336.7	322.3	307.9	299.5	291.2	286.1	281.1	277.0	272.9
35°	377.3	346.7	316.0	302.8	289.6	281.3	272.9	267.9	262.8	258.7	254.7
37.5°	350.9	323.1	295.3	282.9	270.5	263.2	255.9	250.6	245.3	241.1	236.8
40°	326.1	301.6	277.0	265.0	253.0	245.1	237.2	232.5	227.9	224.0	220.1
42.5°	304.2	281.7	259.1	247.4	235.6	228.1	220.5	215.1	209.6	207.3	205.1
45°	281.1	261.2	241.3	229.9	218.5	210.6	202.7	198.0	193.3	191.3	189.3
47.5°	260.8	242.3	223.8	212.6	201.5	194.3	187.2	183.6	179.9	177.1	174.2
50°	240.9	223.0	205.1	194.3	183.6	177.5	171.4	166.9	162.5	160.4	158.4
52.5°	221.8	205.5	189.3	178.3	167.3	161.4	155.6	151.7	147.8	143.6	139.3
55°	200.2	186.0	171.8	162.1	152.3	146.2	140.1	135.7	131.2	126.7	122.3
57.5°	182.4	168.4	154.3	145.6	136.9	131.0	125.1	120.2	115.3	111.7	108.0
60°	162.9	150.7	138.5	130.0	121.4	115.8	110.1	105.4	100.7	98.9	97.1
62.5°	144.6	133.2	121.8	114.3	106.8	101.3	95.9	92.8	89.8	88.5	87.3
65°	125.9	116.2	106.4	99.5	92.6	87.9	83.3	81.8	80.4	79.4	78.4
67.5°	108.4	100.1	91.8	85.7	79.6	76.4	73.1	71.5	69.9	68.6	67.4
70°	92.6	85.3	78.0	72.7	67.4	64.4	61.3	59.9	58.5	56.3	54.0
72.5°	75.5	69.9	64.2	60.1	56.1	53.4	50.8	47.9	45.1	43.1	41.0
75°	62.5	56.9	51.2	47.3	43.5	40.4	37.4	36.4	35.3	34.7	34.1
77.5°	47.9	43.1	38.2	35.1	32.1	30.7	29.2	28.6	28.0	27.8	27.6
80°	34.5	30.5	26.4	24.8	23.2	22.7	22.3	21.9	21.5	21.3	21.1
82.5°	21.5	19.5	17.5	17.1	16.7	16.4	16.2	16.0	15.8	15.6	15.4
85°	12.6	11.8	11.0	10.8	10.6	10.4	10.2	10.2	10.2	10.2	10.2
87.5°	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.1	4.9
90°	10.2	12.9	15.9	18.9	21.9	24.9	25.8	26.7	27.6	28.5	29.2
92.5°	18.3	18.6	20.7	22.8	24.9	26.9	28.5	30.2	31.8	33.4	34.3
95°	25.4	22.0	24.5	27.1	29.6	32.1	33.7	35.3	37.0	38.6	39.4
97.5°	89.2	80.1	68.4	56.6	44.9	33.2	35.0	36.8	38.7	40.5	41.6
100°	193.5	177.8	141.9	106.0	70.1	34.2	36.0	37.9	39.7	41.6	42.6
102.5°	255.4	236.9	196.8	156.8	116.7	76.7	69.1	61.5	53.9	46.3	42.7
105°	318.9	309.8	289.0	268.3	247.6	226.9	186.1	145.4	104.6	63.9	43.7
107.5°	386.4	389.2	392.6	396.1	399.5	403.0	367.5	332.1	296.6	261.2	228.4
110°	454.9	457.1	459.6	462.2	464.7	467.2	459.6	452.0	444.4	436.8	416.6



TEST NUMBER: P832083

CATALOG NUMBER: S123RDIP-S340D1195U940-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	520.3	522.4	524.9	527.4	530.0	532.5	534.6	536.6	538.7	540.8	541.6
115°	584.6	586.4	588.4	590.5	592.6	594.7	597.0	599.3	601.6	603.9	605.5
117.5°	649.8	651.2	652.3	653.5	654.6	655.8	657.6	659.5	661.3	663.2	664.2
120°	710.7	712.1	712.8	713.5	714.1	714.8	716.7	718.5	720.4	722.2	723.1
122.5°	768.9	770.2	771.1	772.0	773.0	773.9	775.0	776.2	777.3	778.5	779.2
125°	823.7	825.1	826.0	827.0	827.9	828.8	829.3	829.7	830.2	830.6	831.1
127.5°	877.6	879.1	880.3	881.4	882.6	883.7	884.4	885.1	885.8	886.5	886.6
130°	927.3	928.7	929.6	930.6	931.5	932.4	933.3	934.2	935.2	936.1	936.3
132.5°	975.0	976.3	976.9	977.6	978.3	979.0	979.9	980.9	981.8	982.7	982.8
135°	1021.8	1023.0	1023.9	1024.8	1025.8	1026.7	1027.4	1028.1	1028.7	1029.4	1029.4
137.5°	1065.1	1066.3	1066.7	1067.2	1067.7	1068.1	1069.3	1070.4	1071.6	1072.7	1073.1
140°	1104.7	1105.8	1106.4	1107.1	1107.8	1108.5	1109.4	1110.4	1111.3	1112.2	1112.4
142.5°	1143.1	1144.1	1144.8	1145.5	1146.2	1146.8	1147.5	1148.2	1148.9	1149.6	1149.6
145°	1179.2	1180.2	1180.7	1181.2	1181.6	1182.1	1182.5	1183.0	1183.5	1183.9	1184.1
147.5°	1211.5	1212.3	1212.8	1213.3	1213.7	1214.2	1214.7	1215.1	1215.6	1216.0	1215.7
150°	1240.8	1241.4	1241.8	1242.3	1242.7	1243.2	1243.7	1244.1	1244.6	1245.0	1244.9
152.5°	1266.9	1267.1	1267.4	1267.6	1267.8	1268.1	1269.0	1269.9	1270.8	1271.7	1271.6
155°	1290.0	1289.9	1290.2	1290.4	1290.6	1290.9	1292.0	1293.2	1294.3	1295.5	1295.3
157.5°	1312.6	1312.5	1312.3	1312.0	1311.8	1311.6	1313.0	1314.3	1315.7	1317.1	1316.9
160°	1330.3	1330.1	1329.9	1329.6	1329.4	1329.2	1330.6	1331.9	1333.3	1334.7	1334.6
162.5°	1346.1	1345.6	1345.4	1345.2	1345.0	1344.7	1346.3	1347.9	1349.6	1351.2	1351.3
165°	1359.6	1359.1	1358.9	1358.7	1358.4	1358.2	1360.0	1361.9	1363.7	1365.6	1365.7
167.5°	1370.0	1369.6	1369.6	1369.6	1369.6	1369.6	1371.4	1373.3	1375.1	1377.0	1377.0
170°	1379.4	1378.9	1378.9	1378.9	1378.9	1378.9	1380.8	1382.6	1384.4	1386.3	1386.3
172.5°	1384.7	1384.2	1384.4	1384.7	1384.9	1385.1	1387.0	1388.8	1390.7	1392.5	1392.4
175°	1389.8	1389.4	1389.6	1389.8	1390.1	1390.3	1391.9	1393.5	1395.1	1396.8	1396.6
177.5°	1391.9	1391.5	1391.7	1391.9	1392.2	1392.4	1394.2	1396.1	1397.9	1399.7	1399.5
180°	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5



TEST NUMBER: P832083

CATALOG NUMBER: S123RDIP-S340D1195U940-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	990.6	990.6	990.6	990.6
2.5°	880.2	878.1	877.3	876.5
5°	754.4	748.1	746.7	745.3
7.5°	647.6	645.0	636.3	627.5
10°	560.9	552.8	549.1	545.5
12.5°	488.4	480.9	479.7	478.5
15°	432.2	426.9	425.0	423.2
17.5°	395.2	391.5	389.3	387.1
20°	367.8	365.1	363.5	361.9
22.5°	346.9	344.8	343.6	342.4
25°	326.8	323.7	322.7	321.7
27.5°	307.7	305.0	304.0	303.0
30°	289.8	287.6	286.1	284.7
32.5°	270.3	267.7	266.8	266.0
35°	253.0	251.4	250.6	249.8
37.5°	234.8	232.7	231.5	230.3
40°	219.1	218.1	217.5	216.9
42.5°	203.3	201.5	201.3	201.0
45°	187.4	185.6	185.2	184.8
47.5°	172.6	171.0	170.8	170.6
50°	156.2	153.9	152.3	150.7
52.5°	137.3	135.3	133.8	132.4
55°	120.0	117.8	116.6	115.3
57.5°	107.0	106.0	105.4	104.8
60°	96.5	95.9	95.4	95.0
62.5°	86.7	86.1	86.1	86.1
65°	77.8	77.2	76.6	76.0
67.5°	66.2	65.0	64.8	64.6
70°	52.2	50.4	50.2	50.0
72.5°	40.8	40.6	40.2	39.8
75°	33.7	33.3	33.3	33.3
77.5°	27.2	26.8	26.8	26.8
80°	20.9	20.7	20.9	21.1
82.5°	15.4	15.4	15.2	15.0
85°	10.0	9.7	9.7	9.7
87.5°	4.9	4.9	4.9	4.9
90°	29.7	30.2	30.6	31.1
92.5°	34.5	34.8	35.0	35.2
95°	39.4	39.4	39.4	39.4
97.5°	41.8	42.0	42.2	42.5
100°	42.8	43.1	43.3	43.5
102.5°	43.2	43.6	44.1	44.5
105°	44.2	44.7	45.1	45.6
107.5°	198.2	168.1	137.9	107.7
110°	383.7	350.7	317.8	284.9



TEST NUMBER: P832083

CATALOG NUMBER: S123RDIP-S340D1195U940-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
112.5°	541.1	540.7	540.2	539.8
115°	606.4	607.3	608.2	609.2
117.5°	664.4	664.7	664.9	665.1
120°	723.1	723.1	723.1	723.1
122.5°	779.4	779.6	779.9	780.1
125°	831.6	832.0	832.5	832.9
127.5°	886.1	885.7	885.2	884.7
130°	935.9	935.4	934.9	934.5
132.5°	982.1	981.4	980.7	980.1
135°	1028.7	1028.1	1027.4	1026.7
137.5°	1072.6	1072.1	1071.7	1071.2
140°	1112.0	1111.5	1111.1	1110.6
142.5°	1148.9	1148.2	1147.5	1146.8
145°	1184.1	1184.1	1184.1	1184.1
147.5°	1214.5	1213.4	1212.2	1211.1
150°	1244.2	1243.5	1242.9	1242.2
152.5°	1270.5	1269.3	1268.2	1267.0
155°	1294.0	1292.6	1291.2	1289.8
157.5°	1315.0	1313.2	1311.3	1309.5
160°	1333.0	1331.4	1329.8	1328.1
162.5°	1349.9	1348.5	1347.1	1345.8
165°	1364.1	1362.5	1360.8	1359.2
167.5°	1375.1	1373.3	1371.4	1369.6
170°	1384.4	1382.6	1380.8	1378.9
172.5°	1390.3	1388.2	1386.2	1384.1
175°	1394.8	1393.0	1391.1	1389.3
177.5°	1397.2	1394.9	1392.6	1390.3
180°	1394.5	1394.5	1394.5	1394.5



TEST NUMBER: P832083

CATALOG NUMBER: S123RDIP-S340D1195U940-4F0-1E-UDD-G

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.76	6.40	6.92	7.55	9.15	10.42	11.07	11.58	12.21	13.82
	3H	6.97	7.54	8.13	8.69	10.31	11.91	12.48	13.08	13.63	15.25
	4H	7.34	7.89	8.52	9.04	10.66	12.39	12.93	13.56	14.09	15.71
	6H	7.61	8.11	8.80	9.27	10.90	12.69	13.19	13.87	14.35	15.98
	8H	7.69	8.17	8.88	9.34	10.97	12.76	13.24	13.95	14.41	16.04
	12H	7.74	8.19	8.93	9.35	11.00	12.79	13.24	13.98	14.40	16.05
4H	2H	6.46	7.01	7.64	8.16	9.78	10.39	10.94	11.58	12.09	13.72
	3H	7.81	8.27	9.00	9.44	11.08	12.04	12.49	13.22	13.67	15.30
	4H	8.26	8.68	9.45	9.85	11.50	12.64	13.06	13.83	14.22	15.88
	6H	8.62	8.98	9.81	10.16	11.81	13.06	13.42	14.26	14.61	16.25
	8H	8.74	9.07	9.93	10.25	11.91	13.19	13.53	14.38	14.70	16.37
	12H	8.81	9.11	10.02	10.30	11.97	13.25	13.55	14.45	14.74	16.40
8H	4H	8.56	8.90	9.75	10.07	11.74	12.59	12.92	13.78	14.10	15.76
	6H	9.02	9.29	10.23	10.52	12.17	13.08	13.36	14.29	14.58	16.23
	8H	9.21	9.45	10.43	10.65	12.33	13.27	13.50	14.48	14.70	16.38
	12H	9.35	9.56	10.57	10.75	12.46	13.37	13.58	14.59	14.78	16.49
12H	4H	8.57	8.87	9.77	10.06	11.72	12.53	12.84	13.74	14.02	15.69
	6H	9.08	9.32	10.29	10.51	12.19	13.06	13.29	14.27	14.49	16.17
	8H	9.29	9.50	10.51	10.69	12.40	13.24	13.45	14.46	14.64	16.35