

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332669-930

Luminaire Tested: **S124DIP-S1020D1205U930-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332669-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIP-S1020D1205U930-4F0-1E-UDD-F4  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7119.8 lumens  
Efficiency: N/A  
Efficacy: 108.9 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 65.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332669-930  
CATALOG NUMBER: S124DIP-S1020D1205U930-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P332669-930

CATALOG NUMBER: S124DIP-S1020D1205U930-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51					51			
1	98	94	90	86	90	87	83	80	73	71	69	61	60	58	50	49	48	43					43			
2	89	82	76	70	82	76	70	66	64	60	57	54	51	48	44	42	40	36					36			
3	81	72	64	59	75	67	60	55	57	52	48	48	44	41	39	37	34	30					30			
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	35	32	30	26					26			
5	68	57	48	42	63	53	45	40	45	39	35	38	34	30	31	28	26	23					23			
6	63	51	43	37	58	47	40	35	41	35	31	34	30	27	29	25	23	20					20			
7	58	46	38	32	54	43	36	31	37	31	27	31	27	24	26	23	20	18					18			
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	16					16			
9	50	38	31	25	46	36	29	24	31	25	21	26	22	19	22	19	16	14					14			
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	21	17	15	13					13			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11357	11357	11357
5°	11391	11255	11336
10°	11320	11163	11218
15°	11183	11004	11032
20°	11001	10808	10817
25°	10794	10583	10553
30°	10540	10318	10224
35°	10276	10042	9909
40°	10003	9729	9551
45°	9717	9421	9240
50°	9401	9146	8862
55°	9060	8790	8504
60°	8719	8391	8136
65°	8334	8010	7687
70°	7903	7504	7211
75°	7243	6890	6716
80°	6448	6183	6025
85°	5641	5428	5326



TEST NUMBER: P332669-930

CATALOG NUMBER: S124DIP-S1020D1205U930-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	132.5	1.9
10°-20°	373.3	5.2
20°-30°	549.4	7.7
30°-40°	638.7	9.0
40°-50°	638.7	9.0
50°-60°	558.7	7.8
60°-70°	414.9	5.8
70°-80°	235.7	3.3
80°-90°	70.7	1.0
90°-100°	348.3	4.9
100°-110°	724.9	10.2
110°-120°	649.3	9.1
120°-130°	546.2	7.7
130°-140°	455.4	6.4
140°-150°	347.9	4.9
150°-160°	244.5	3.4
160°-170°	143.8	2.0
170°-180°	46.8	0.7
0°-30°	1055.2	14.8
0°-40°	1693.9	23.8
0°-60°	2891.3	40.6
0°-90°	3612.7	50.7
90°-120°	1722.5	24.2
90°-150°	3071.9	43.1
90°-180°	3507.0	49.3
0°-180°	7119.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1407	1407	1407	1407	1407	
5°	1406	1401	1389	1400	1399	133
15°	1338	1333	1317	1323	1320	377
25°	1212	1204	1188	1189	1185	557
35°	1043	1034	1019	1011	1006	652
45°	851	843	825	813	809	656
55°	644	640	624	611	604	576
65°	436	430	419	408	402	432
75°	232	227	221	217	215	247
85°	61	61	59	59	58	67
90°	1	8	17	19	20	5
95°	31	99	772	382	231	35
105°	111	161	622	1338	1333	118
115°	195	245	554	1065	1280	193
125°	272	323	551	906	1021	242
135°	323	385	547	804	913	250
145°	372	426	544	678	746	234
155°	424	457	529	599	624	195
165°	461	476	507	537	545	130
175°	481	482	486	493	491	46
180°	482	482	482	482	482	



TEST NUMBER: P332669-930

CATALOG NUMBER: S124DIP-S1020D1205U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1406.8	1406.8	1406.8	1406.8	1406.8	1406.8	1406.8	1406.8	1406.8	1406.8	1406.8
2.5°	1410.4	1409.8	1409.2	1408.6	1408.0	1406.6	1404.4	1402.2	1400.0	1397.7	1399.8
5°	1405.7	1404.7	1403.7	1402.6	1401.7	1399.8	1397.0	1394.2	1391.6	1388.8	1391.6
7.5°	1392.6	1391.6	1390.6	1389.6	1388.6	1386.6	1383.5	1380.5	1377.4	1374.4	1376.6
10°	1380.9	1379.9	1378.8	1377.9	1376.9	1374.8	1371.5	1368.2	1365.0	1361.7	1363.7
12.5°	1365.5	1364.6	1363.5	1362.5	1361.5	1359.3	1355.8	1352.4	1348.9	1345.5	1347.7
15°	1338.1	1337.0	1336.0	1335.1	1334.0	1331.6	1327.9	1324.1	1320.4	1316.6	1318.1
17.5°	1304.9	1303.7	1302.4	1301.1	1299.9	1297.5	1293.9	1290.4	1286.8	1283.3	1284.2
20°	1280.5	1279.3	1278.1	1276.8	1275.5	1273.0	1269.3	1265.5	1261.8	1258.0	1258.7
22.5°	1254.4	1252.7	1251.1	1249.4	1247.8	1245.0	1241.3	1237.5	1233.8	1230.0	1231.4
25°	1211.8	1210.1	1208.3	1206.5	1204.8	1202.2	1198.7	1195.1	1191.6	1188.1	1188.4
27.5°	1163.1	1161.3	1159.4	1157.6	1155.8	1153.3	1150.1	1146.8	1143.5	1140.3	1139.7
30°	1130.7	1128.6	1126.6	1124.6	1122.6	1120.0	1116.7	1113.5	1110.2	1106.9	1106.0
32.5°	1096.3	1094.5	1092.7	1091.0	1089.2	1086.5	1083.0	1079.6	1076.1	1072.7	1071.5
35°	1042.7	1041.0	1039.2	1037.5	1035.7	1033.1	1029.6	1026.1	1022.5	1019.0	1017.2
37.5°	986.1	984.5	982.9	981.3	979.7	977.1	973.2	969.5	965.7	962.0	960.1
40°	949.2	947.1	945.1	943.1	941.1	938.2	934.5	930.7	927.0	923.2	920.7
42.5°	909.5	908.2	907.0	905.9	904.7	902.0	897.8	893.6	889.5	885.3	882.4
45°	851.1	849.3	847.6	845.8	844.1	841.1	837.1	833.2	829.2	825.2	822.4
47.5°	789.9	788.8	787.6	786.4	785.1	782.7	779.0	775.3	771.6	767.8	764.8
50°	748.5	747.5	746.5	745.5	744.4	742.2	738.7	735.2	731.7	728.2	724.7
52.5°	707.9	706.7	705.5	704.3	703.1	700.7	696.9	693.2	689.5	685.8	682.7
55°	643.7	642.9	642.1	641.4	640.7	638.5	635.0	631.5	628.0	624.5	621.5
57.5°	582.4	581.5	580.7	579.8	578.9	576.7	573.3	569.9	566.4	563.0	560.1
60°	540.0	538.7	537.4	536.2	534.9	532.7	529.5	526.2	522.9	519.7	517.4
62.5°	498.5	497.4	496.4	495.3	494.2	492.0	488.5	485.1	481.6	478.2	476.1
65°	436.3	435.0	433.7	432.5	431.2	429.3	426.8	424.4	421.8	419.3	416.9
67.5°	373.6	372.4	371.3	370.1	368.9	367.2	364.8	362.4	360.0	357.6	355.1
70°	334.8	333.0	331.3	329.5	327.8	325.9	323.9	321.9	319.9	317.9	315.8
72.5°	293.3	291.6	289.8	288.0	286.3	284.6	283.0	281.4	279.8	278.2	276.6
75°	232.2	231.0	229.7	228.4	227.2	225.9	224.7	223.5	222.2	220.9	220.0
77.5°	173.8	173.3	172.7	172.2	171.6	170.8	169.7	168.6	167.5	166.4	166.1
80°	138.7	137.9	137.1	136.4	135.7	135.0	134.5	134.0	133.5	133.0	132.5
82.5°	104.4	104.0	103.7	103.3	103.0	102.7	102.6	102.6	102.5	102.3	102.1
85°	60.9	60.9	60.9	60.9	60.9	60.7	60.1	59.6	59.1	58.6	58.6
87.5°	23.6	23.8	24.2	24.1	24.1	24.0	24.9	24.7	24.9	25.0	24.9
90°	1.0	2.9	5.7	6.6	7.6	7.6	13.3	13.3	15.2	17.0	16.1
92.5°	10.8	15.7	24.6	36.2	50.1	69.7	117.9	191.4	263.0	300.5	250.3
95°	31.2	34.1	43.6	55.9	78.6	118.5	200.8	356.2	582.6	772.1	793.9
97.5°	56.1	56.1	64.2	75.6	95.1	128.5	191.9	320.2	545.3	813.3	997.4
100°	72.0	72.0	78.6	90.0	108.0	138.4	194.2	301.3	494.6	761.7	1004.2
102.5°	87.2	88.7	94.6	105.2	122.4	151.2	201.8	296.0	460.4	697.2	947.4
105°	110.9	113.7	118.5	129.8	146.8	174.3	219.8	298.4	431.0	621.5	844.1
107.5°	137.0	138.8	143.7	155.7	172.0	199.2	240.8	312.4	425.7	579.0	760.8
110°	154.4	156.3	161.0	172.4	189.5	215.1	256.7	323.0	427.3	564.7	719.1



TEST NUMBER: P332669-930

CATALOG NUMBER: S124DIP-S1020D1205U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	171.1	173.0	178.5	189.1	206.2	231.7	271.9	334.4	431.8	557.8	695.5
115°	195.2	198.0	204.6	214.1	232.1	257.7	295.5	352.5	440.5	554.2	673.6
117.5°	220.1	222.8	228.7	239.1	256.0	282.5	318.5	370.8	449.8	553.3	663.7
120°	236.8	238.7	245.4	255.8	271.9	298.4	334.4	383.7	456.6	553.3	658.4
122.5°	252.0	253.9	260.6	270.2	287.8	313.6	349.6	395.8	463.5	552.5	652.4
125°	271.9	275.7	281.4	291.8	309.8	336.3	370.4	414.0	473.7	551.4	642.3
127.5°	289.5	292.5	299.4	311.3	330.0	356.8	389.7	429.7	481.8	549.3	628.8
130°	299.4	303.1	310.7	325.0	342.9	370.4	402.7	439.6	487.9	548.5	620.5
132.5°	309.2	312.3	322.1	335.6	355.1	381.1	413.3	449.5	493.2	547.8	612.9
135°	323.0	326.9	336.3	352.5	372.3	397.0	428.2	462.4	501.2	546.7	601.6
137.5°	336.9	340.5	350.9	366.2	386.9	410.4	439.6	471.4	505.9	546.4	591.7
140°	346.7	349.6	360.0	376.1	396.0	418.7	447.2	477.4	509.7	545.7	586.4
142.5°	357.3	360.2	369.8	385.2	404.3	426.3	454.0	482.0	512.7	545.7	581.9
145°	372.3	375.2	384.7	397.9	415.9	436.8	461.4	487.0	514.5	543.8	574.1
147.5°	389.1	390.1	398.4	412.1	427.1	445.8	469.0	491.3	515.4	540.4	567.1
150°	399.8	400.7	408.3	419.7	433.9	451.9	472.7	493.6	515.4	538.1	561.8
152.5°	409.6	409.9	417.4	428.0	440.8	457.2	475.8	495.1	513.9	534.3	555.7
155°	423.5	424.4	430.1	439.6	450.0	464.2	480.3	496.4	511.6	528.6	546.7
157.5°	436.9	436.9	442.2	449.6	458.7	469.9	483.6	496.4	509.2	522.8	537.4
160°	445.2	445.2	449.1	455.7	463.3	473.7	485.0	496.4	506.9	518.2	530.5
162.5°	452.8	452.1	455.1	461.0	467.8	476.0	486.6	496.4	504.6	513.6	524.5
165°	461.4	461.4	463.3	468.0	472.7	478.4	487.0	494.6	500.2	506.9	514.5
167.5°	469.9	469.0	469.9	473.5	476.1	480.5	486.7	492.3	495.7	500.0	505.3
170°	473.7	472.7	473.7	476.5	478.4	481.3	486.0	490.7	492.6	495.5	499.3
172.5°	477.4	476.5	476.7	478.8	480.0	482.0	485.3	489.3	489.6	490.9	494.0
175°	481.3	480.3	480.3	481.3	482.2	482.2	484.1	487.0	486.0	486.0	487.9
177.5°	483.0	482.2	481.4	482.2	482.2	482.2	483.0	484.5	483.0	483.0	483.7
180°	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2



TEST NUMBER: P332669-930

CATALOG NUMBER: S124DIP-S1020D1205U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1406.8	1406.8	1406.8	1406.8	1406.8	1406.8	1406.8	1406.8
2.5°	1401.7	1403.8	1405.8	1406.7	1406.5	1406.3	1406.1	1405.9
5°	1394.2	1397.0	1399.8	1400.9	1400.4	1399.9	1399.4	1398.9
7.5°	1378.8	1381.0	1383.2	1384.1	1383.8	1383.5	1383.2	1382.9
10°	1365.7	1367.7	1369.7	1370.4	1369.9	1369.5	1369.0	1368.5
12.5°	1349.9	1352.1	1354.3	1355.0	1354.4	1353.6	1352.9	1352.3
15°	1319.6	1321.1	1322.7	1323.0	1322.3	1321.5	1320.8	1320.0
17.5°	1285.2	1286.1	1287.0	1287.3	1286.8	1286.3	1285.8	1285.2
20°	1259.5	1260.3	1261.0	1261.1	1260.6	1260.1	1259.6	1259.1
22.5°	1232.7	1234.1	1235.4	1235.7	1234.8	1233.9	1233.0	1232.1
25°	1188.6	1188.9	1189.1	1188.7	1187.7	1186.7	1185.7	1184.7
27.5°	1139.1	1138.5	1137.9	1137.0	1135.7	1134.5	1133.2	1132.0
30°	1105.0	1103.9	1102.9	1101.8	1100.6	1099.3	1098.0	1096.8
32.5°	1070.2	1069.1	1067.9	1066.7	1065.4	1064.1	1062.9	1061.6
35°	1015.5	1013.7	1012.0	1010.5	1009.3	1008.0	1006.7	1005.5
37.5°	958.1	956.3	954.4	952.6	951.0	949.3	947.6	946.0
40°	918.2	915.7	913.2	911.3	910.0	908.8	907.6	906.3
42.5°	879.5	876.6	873.7	871.8	871.0	870.1	869.3	868.5
45°	819.6	816.8	814.1	812.4	811.6	810.9	810.1	809.3
47.5°	761.7	758.6	755.5	752.9	751.1	749.1	747.2	745.3
50°	721.2	717.7	714.2	711.7	710.1	708.7	707.2	705.6
52.5°	679.6	676.5	673.4	670.9	669.0	667.1	665.2	663.2
55°	618.5	615.5	612.5	610.3	608.7	607.2	605.7	604.2
57.5°	557.3	554.4	551.5	549.3	547.9	546.5	545.0	543.6
60°	515.2	512.9	510.6	508.9	507.6	506.4	505.2	503.9
62.5°	474.1	472.0	469.9	468.3	467.1	465.8	464.6	463.3
65°	414.3	411.8	409.3	407.4	406.2	405.0	403.7	402.4
67.5°	352.8	350.3	348.0	346.6	346.2	345.8	345.5	345.2
70°	313.9	311.9	309.9	308.5	307.8	307.0	306.2	305.5
72.5°	275.0	273.4	271.8	270.6	269.9	269.1	268.4	267.6
75°	218.9	217.9	217.0	216.3	216.1	215.8	215.6	215.3
77.5°	165.8	165.5	165.2	164.7	164.0	163.4	162.7	162.1
80°	132.0	131.5	131.0	130.6	130.4	130.1	129.9	129.6
82.5°	101.7	101.4	101.2	100.9	100.6	100.4	100.1	99.9
85°	58.6	58.6	58.6	58.5	58.2	58.0	57.7	57.5
87.5°	25.0	25.3	25.4	25.4	25.6	25.8	25.6	25.6
90°	17.0	18.0	18.9	18.9	19.9	20.9	19.9	19.9
92.5°	186.1	140.0	111.5	92.5	81.3	76.1	73.0	73.0
95°	702.0	555.1	428.2	336.3	289.9	260.6	243.4	231.1
97.5°	1037.2	982.6	890.0	791.1	723.0	666.0	637.6	617.9
100°	1142.6	1161.5	1115.1	1045.0	962.5	904.7	876.4	868.8
102.5°	1137.3	1231.2	1244.6	1215.4	1164.9	1123.0	1093.1	1087.0
105°	1061.0	1225.0	1318.7	1357.6	1359.5	1351.9	1338.6	1332.9
107.5°	952.8	1127.4	1259.5	1343.9	1390.7	1412.3	1421.8	1424.3
110°	887.7	1051.6	1189.0	1293.1	1360.4	1400.2	1417.3	1425.8





TEST NUMBER: P332669-930

CATALOG NUMBER: S124DIP-S1020D1205U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	839.9	984.9	1114.7	1218.9	1295.3	1343.4	1367.3	1381.1
115°	792.0	908.6	1019.4	1110.4	1185.2	1242.0	1272.4	1279.9
117.5°	768.5	865.0	952.1	1029.2	1093.1	1140.8	1171.5	1177.4
120°	757.9	846.0	921.8	989.0	1043.1	1084.8	1109.4	1119.8
122.5°	748.8	833.9	902.9	961.8	1007.5	1043.1	1063.9	1074.3
125°	733.3	814.7	880.1	932.2	970.1	997.6	1015.6	1021.2
127.5°	714.3	792.2	857.4	906.9	944.9	969.4	984.6	990.2
130°	699.2	774.0	838.5	888.7	927.5	951.1	966.3	972.0
132.5°	683.2	753.6	816.4	866.7	904.7	931.5	945.8	951.5
135°	661.3	722.8	780.6	828.0	865.9	892.4	907.6	913.3
137.5°	641.4	693.5	742.2	785.0	820.4	846.6	859.1	865.9
140°	630.0	674.5	717.1	756.9	790.1	811.0	824.2	831.8
142.5°	619.4	658.6	695.2	729.7	759.0	778.4	790.1	795.4
145°	604.5	636.7	665.0	691.6	715.3	731.4	740.9	745.6
147.5°	592.2	617.7	640.4	661.3	678.7	692.5	699.8	701.4
150°	584.6	606.3	625.3	642.3	657.5	669.8	675.5	676.5
152.5°	576.2	594.9	612.4	626.4	639.3	649.3	652.7	653.7
155°	563.7	578.9	593.0	604.5	613.9	621.5	624.4	624.4
157.5°	550.2	563.0	574.9	584.0	591.2	596.9	598.6	598.6
160°	541.9	552.3	562.7	570.3	576.0	581.7	582.6	582.6
162.5°	533.5	542.5	550.7	557.4	561.6	567.3	568.3	567.4
165°	522.0	527.7	534.3	539.1	542.8	546.7	545.7	544.8
167.5°	510.9	515.2	520.5	523.3	525.2	527.7	527.5	526.8
170°	504.0	506.9	510.6	513.5	515.4	516.3	515.4	515.4
172.5°	497.9	500.0	502.3	504.3	505.5	506.5	505.5	504.0
175°	489.8	490.7	492.6	492.6	492.6	494.6	492.6	490.7
177.5°	484.5	485.3	485.3	486.0	485.3	486.0	484.5	483.0
180°	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2

(END OF REPORT)