

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332640-930

Luminaire Tested: **S124DIP-S1020D590U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332640-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIP-S1020D590U930-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 590 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5535.2 lumens
Efficiency: N/A
Efficacy: 113.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 48.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332640-930
CATALOG NUMBER: S124DIP-S1020D590U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332640-930

CATALOG NUMBER: S124DIP-S1020D590U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	70	70	70	65
1	101	97	93	89	95	91	88	84	81	78	75	71	69	67	62	61	59	55
2	92	84	78	73	86	80	74	69	71	66	62	62	59	56	54	52	50	46
3	84	74	67	61	79	70	63	58	62	57	53	55	51	47	48	45	42	39
4	77	66	58	51	72	62	55	49	55	50	45	49	44	41	43	40	37	33
5	71	59	50	44	66	56	48	42	50	43	39	44	39	35	39	35	32	29
6	65	53	44	38	61	50	42	37	45	39	34	40	35	31	35	31	28	25
7	60	48	40	34	57	45	38	33	41	34	30	36	31	27	32	28	25	23
8	56	43	35	30	53	41	34	29	37	31	27	33	28	25	30	26	22	20
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	27	23	20	18
10	49	37	29	24	46	35	28	23	32	26	22	28	24	20	25	21	18	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11357	11357	11357
5°	11391	11255	11336
10°	11320	11163	11218
15°	11183	11004	11032
20°	11001	10808	10817
25°	10794	10583	10553
30°	10540	10318	10224
35°	10276	10042	9909
40°	10003	9729	9551
45°	9717	9421	9240
50°	9401	9146	8862
55°	9060	8790	8504
60°	8719	8391	8136
65°	8334	8010	7687
70°	7903	7504	7211
75°	7243	6890	6716
80°	6448	6183	6025
85°	5641	5428	5326



TEST NUMBER: P332640-930

CATALOG NUMBER: S124DIP-S1020D590U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	132.5	2.4
10°-20°	373.3	6.7
20°-30°	549.4	9.9
30°-40°	638.7	11.5
40°-50°	638.7	11.5
50°-60°	558.7	10.1
60°-70°	414.9	7.5
70°-80°	235.7	4.3
80°-90°	69.8	1.3
90°-100°	21.3	0.4
100°-110°	135.6	2.4
110°-120°	259.4	4.7
120°-130°	329.3	5.9
130°-140°	352.3	6.4
140°-150°	329.4	6.0
150°-160°	265.7	4.8
160°-170°	171.4	3.1
170°-180°	59.1	1.1
0°-30°	1055.2	19.1
0°-40°	1693.9	30.6
0°-60°	2891.3	52.2
0°-90°	3611.8	65.3
90°-120°	416.3	7.5
90°-150°	1427.3	25.8
90°-180°	1923.0	34.7
0°-180°	5535.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1407	1407	1407	1407	1407	
5°	1406	1401	1389	1400	1399	133
15°	1338	1333	1317	1323	1320	377
25°	1212	1204	1188	1189	1185	557
35°	1043	1034	1019	1011	1006	652
45°	851	843	825	813	809	656
55°	644	640	624	611	604	576
65°	436	430	419	408	402	432
75°	232	227	221	217	215	247
85°	61	61	59	59	58	67
90°	1	6	10	13	14	4
95°	26	11	10	13	14	33
105°	140	143	145	148	133	146
115°	261	263	262	263	263	257
125°	367	369	368	370	370	328
135°	456	455	457	458	459	351
145°	526	527	527	527	528	328
155°	576	577	575	577	576	266
165°	608	606	606	609	605	172
175°	622	619	620	623	618	59
180°	622	622	622	622	622	



TEST NUMBER: P332640-930

CATALOG NUMBER: S124DIP-S1020D590U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1406.8	1406.8	1406.8	1406.8	1406.8	1406.8	1406.8	1406.8	1406.8	1406.8	1406.8
2.5°	1410.4	1409.8	1409.2	1408.6	1408.0	1406.6	1404.4	1402.2	1400.0	1397.7	1399.8
5°	1405.7	1404.7	1403.7	1402.6	1401.7	1399.8	1397.0	1394.2	1391.6	1388.8	1391.6
7.5°	1392.6	1391.6	1390.6	1389.6	1388.6	1386.6	1383.5	1380.5	1377.4	1374.4	1376.6
10°	1380.9	1379.9	1378.8	1377.9	1376.9	1374.8	1371.5	1368.2	1365.0	1361.7	1363.7
12.5°	1365.5	1364.6	1363.5	1362.5	1361.5	1359.3	1355.8	1352.4	1348.9	1345.5	1347.7
15°	1338.1	1337.0	1336.0	1335.1	1334.0	1331.6	1327.9	1324.1	1320.4	1316.6	1318.1
17.5°	1304.9	1303.7	1302.4	1301.1	1299.9	1297.5	1293.9	1290.4	1286.8	1283.3	1284.2
20°	1280.5	1279.3	1278.1	1276.8	1275.5	1273.0	1269.3	1265.5	1261.8	1258.0	1258.7
22.5°	1254.4	1252.7	1251.1	1249.4	1247.8	1245.0	1241.3	1237.5	1233.8	1230.0	1231.4
25°	1211.8	1210.1	1208.3	1206.5	1204.8	1202.2	1198.7	1195.1	1191.6	1188.1	1188.4
27.5°	1163.1	1161.3	1159.4	1157.6	1155.8	1153.3	1150.1	1146.8	1143.5	1140.3	1139.7
30°	1130.7	1128.6	1126.6	1124.6	1122.6	1120.0	1116.7	1113.5	1110.2	1106.9	1106.0
32.5°	1096.3	1094.5	1092.7	1091.0	1089.2	1086.5	1083.0	1079.6	1076.1	1072.7	1071.5
35°	1042.7	1041.0	1039.2	1037.5	1035.7	1033.1	1029.6	1026.1	1022.5	1019.0	1017.2
37.5°	986.1	984.5	982.9	981.3	979.7	977.1	973.2	969.5	965.7	962.0	960.1
40°	949.2	947.1	945.1	943.1	941.1	938.2	934.5	930.7	927.0	923.2	920.7
42.5°	909.5	908.2	907.0	905.9	904.7	902.0	897.8	893.6	889.5	885.3	882.4
45°	851.1	849.3	847.6	845.8	844.1	841.1	837.1	833.2	829.2	825.2	822.4
47.5°	789.9	788.8	787.6	786.4	785.1	782.7	779.0	775.3	771.6	767.8	764.8
50°	748.5	747.5	746.5	745.5	744.4	742.2	738.7	735.2	731.7	728.2	724.7
52.5°	707.9	706.7	705.5	704.3	703.1	700.7	696.9	693.2	689.5	685.8	682.7
55°	643.7	642.9	642.1	641.4	640.7	638.5	635.0	631.5	628.0	624.5	621.5
57.5°	582.4	581.5	580.7	579.8	578.9	576.7	573.3	569.9	566.4	563.0	560.1
60°	540.0	538.7	537.4	536.2	534.9	532.7	529.5	526.2	522.9	519.7	517.4
62.5°	498.5	497.4	496.4	495.3	494.2	492.0	488.5	485.1	481.6	478.2	476.1
65°	436.3	435.0	433.7	432.5	431.2	429.3	426.8	424.4	421.8	419.3	416.9
67.5°	373.6	372.4	371.3	370.1	368.9	367.2	364.8	362.4	360.0	357.6	355.1
70°	334.8	333.0	331.3	329.5	327.8	325.9	323.9	321.9	319.9	317.9	315.8
72.5°	293.3	291.6	289.8	288.0	286.3	284.6	283.0	281.4	279.8	278.2	276.6
75°	232.2	231.0	229.7	228.4	227.2	225.9	224.7	223.5	222.2	220.9	220.0
77.5°	173.8	173.3	172.7	172.2	171.6	170.8	169.7	168.6	167.5	166.4	166.1
80°	138.7	137.9	137.1	136.4	135.7	135.0	134.5	134.0	133.5	133.0	132.5
82.5°	104.4	104.0	103.7	103.3	103.0	102.7	102.6	102.6	102.5	102.3	102.1
85°	60.9	60.9	60.9	60.9	60.9	60.7	60.1	59.6	59.1	58.6	58.6
87.5°	23.7	23.7	23.8	23.8	23.8	23.8	23.8	23.7	23.7	23.7	23.8
90°	1.4	2.5	3.7	4.8	6.0	6.9	7.7	8.6	9.4	10.2	10.8
92.5°	5.9	6.0	6.0	6.0	6.1	6.5	7.4	8.2	9.0	9.9	10.5
95°	25.6	22.1	18.6	15.0	11.5	9.8	9.9	10.0	10.1	10.2	10.8
97.5°	54.3	56.5	58.7	60.9	63.1	58.4	46.9	35.4	23.8	12.3	12.3
100°	76.2	78.1	80.0	81.9	83.7	77.5	63.3	49.0	34.7	20.5	18.7
102.5°	100.9	102.2	103.5	104.9	106.3	106.1	104.2	102.3	100.4	98.6	79.7
105°	140.0	140.6	141.2	141.9	142.4	143.0	143.6	144.1	144.6	145.1	146.0
107.5°	176.3	176.7	177.0	177.2	177.6	178.1	178.8	179.5	180.2	180.9	181.4
110°	200.9	201.2	201.5	201.9	202.1	202.6	203.3	203.8	204.5	205.1	205.3



TEST NUMBER: P332640-930

CATALOG NUMBER: S124DIP-S1020D590U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	224.7	225.3	225.8	226.4	227.0	227.4	227.6	228.0	228.3	228.5	228.5
115°	261.4	261.7	262.0	262.3	262.6	262.7	262.6	262.5	262.4	262.3	262.5
117.5°	294.4	294.8	295.2	295.6	296.0	296.4	296.6	296.9	297.0	297.3	297.3
120°	316.7	317.2	317.6	318.0	318.4	318.5	318.5	318.3	318.2	318.1	318.3
122.5°	337.5	337.8	338.0	338.3	338.5	338.8	338.9	339.0	339.2	339.3	339.4
125°	367.4	367.8	368.3	368.7	369.1	369.2	368.9	368.8	368.5	368.4	368.7
127.5°	395.7	395.7	395.9	396.0	396.1	396.4	396.9	397.3	397.8	398.3	398.2
130°	413.9	414.0	414.1	414.3	414.3	414.5	414.8	415.2	415.5	415.8	415.9
132.5°	430.6	430.8	431.0	431.2	431.4	431.7	432.1	432.4	432.8	433.3	433.3
135°	455.8	455.7	455.6	455.4	455.3	455.5	455.9	456.3	456.7	457.1	457.4
137.5°	478.0	478.0	478.1	478.1	478.2	478.4	478.8	479.3	479.8	480.2	480.5
140°	492.5	492.7	492.9	493.1	493.3	493.5	493.7	494.0	494.2	494.4	494.6
142.5°	505.6	505.9	506.3	506.6	507.0	507.3	507.4	507.5	507.6	507.8	508.0
145°	525.5	525.9	526.1	526.4	526.8	526.9	526.9	526.9	526.9	526.9	527.0
147.5°	541.4	542.0	542.6	543.2	543.7	544.0	543.9	543.8	543.6	543.6	543.6
150°	552.9	553.3	553.8	554.2	554.6	554.8	554.6	554.6	554.5	554.3	554.3
152.5°	562.6	563.0	563.3	563.6	563.9	564.0	563.9	563.7	563.5	563.3	563.5
155°	576.3	576.3	576.4	576.5	576.7	576.5	576.3	575.9	575.6	575.3	575.7
157.5°	587.7	587.6	587.5	587.5	587.4	587.2	586.9	586.5	586.1	585.8	586.4
160°	594.4	594.0	593.7	593.5	593.1	592.9	592.8	592.7	592.6	592.5	593.1
162.5°	600.3	599.9	599.5	599.2	598.8	598.5	598.3	598.3	598.2	598.1	598.7
165°	607.8	607.3	606.8	606.3	605.8	605.5	605.5	605.5	605.5	605.5	606.3
167.5°	613.8	613.3	612.7	612.2	611.6	611.3	611.3	611.2	611.1	611.1	612.0
170°	617.2	616.5	615.9	615.3	614.7	614.4	614.5	614.6	614.7	614.8	615.6
172.5°	619.4	618.7	618.2	617.5	616.9	616.6	616.8	616.9	616.9	617.0	617.9
175°	621.8	621.2	620.5	620.0	619.3	619.1	619.1	619.3	619.4	619.5	620.4
177.5°	622.9	622.3	621.7	621.2	620.6	620.4	620.5	620.7	620.9	621.0	621.7
180°	621.8	621.8	621.8	621.8	621.8	621.8	621.8	621.8	621.8	621.8	621.8



TEST NUMBER: P332640-930

CATALOG NUMBER: S124DIP-S1020D590U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1406.8	1406.8	1406.8	1406.8	1406.8	1406.8	1406.8	1406.8
2.5°	1401.7	1403.8	1405.8	1406.7	1406.5	1406.3	1406.1	1405.9
5°	1394.2	1397.0	1399.8	1400.9	1400.4	1399.9	1399.4	1398.9
7.5°	1378.8	1381.0	1383.2	1384.1	1383.8	1383.5	1383.2	1382.9
10°	1365.7	1367.7	1369.7	1370.4	1369.9	1369.5	1369.0	1368.5
12.5°	1349.9	1352.1	1354.3	1355.0	1354.4	1353.6	1352.9	1352.3
15°	1319.6	1321.1	1322.7	1323.0	1322.3	1321.5	1320.8	1320.0
17.5°	1285.2	1286.1	1287.0	1287.3	1286.8	1286.3	1285.8	1285.2
20°	1259.5	1260.3	1261.0	1261.1	1260.6	1260.1	1259.6	1259.1
22.5°	1232.7	1234.1	1235.4	1235.7	1234.8	1233.9	1233.0	1232.1
25°	1188.6	1188.9	1189.1	1188.7	1187.7	1186.7	1185.7	1184.7
27.5°	1139.1	1138.5	1137.9	1137.0	1135.7	1134.5	1133.2	1132.0
30°	1105.0	1103.9	1102.9	1101.8	1100.6	1099.3	1098.0	1096.8
32.5°	1070.2	1069.1	1067.9	1066.7	1065.4	1064.1	1062.9	1061.6
35°	1015.5	1013.7	1012.0	1010.5	1009.3	1008.0	1006.7	1005.5
37.5°	958.1	956.3	954.4	952.6	951.0	949.3	947.6	946.0
40°	918.2	915.7	913.2	911.3	910.0	908.8	907.6	906.3
42.5°	879.5	876.6	873.7	871.8	871.0	870.1	869.3	868.5
45°	819.6	816.8	814.1	812.4	811.6	810.9	810.1	809.3
47.5°	761.7	758.6	755.5	752.9	751.1	749.1	747.2	745.3
50°	721.2	717.7	714.2	711.7	710.1	708.7	707.2	705.6
52.5°	679.6	676.5	673.4	670.9	669.0	667.1	665.2	663.2
55°	618.5	615.5	612.5	610.3	608.7	607.2	605.7	604.2
57.5°	557.3	554.4	551.5	549.3	547.9	546.5	545.0	543.6
60°	515.2	512.9	510.6	508.9	507.6	506.4	505.2	503.9
62.5°	474.1	472.0	469.9	468.3	467.1	465.8	464.6	463.3
65°	414.3	411.8	409.3	407.4	406.2	405.0	403.7	402.4
67.5°	352.8	350.3	348.0	346.6	346.2	345.8	345.5	345.2
70°	313.9	311.9	309.9	308.5	307.8	307.0	306.2	305.5
72.5°	275.0	273.4	271.8	270.6	269.9	269.1	268.4	267.6
75°	218.9	217.9	217.0	216.3	216.1	215.8	215.6	215.3
77.5°	165.8	165.5	165.2	164.7	164.0	163.4	162.7	162.1
80°	132.0	131.5	131.0	130.6	130.4	130.1	129.9	129.6
82.5°	101.7	101.4	101.2	100.9	100.6	100.4	100.1	99.9
85°	58.6	58.6	58.6	58.5	58.2	58.0	57.7	57.5
87.5°	24.0	24.1	24.2	24.3	24.3	24.4	24.4	24.5
90°	11.5	12.1	12.7	13.1	13.4	13.5	13.8	13.9
92.5°	11.1	11.7	12.3	12.6	12.7	12.7	12.8	12.8
95°	11.5	12.1	12.7	13.0	13.2	13.3	13.4	13.5
97.5°	12.4	12.5	12.6	12.6	12.7	12.8	12.9	13.0
100°	17.0	15.2	13.5	12.6	12.7	12.8	12.9	13.0
102.5°	60.7	41.7	22.7	13.3	13.4	13.4	13.4	13.4
105°	147.0	147.9	148.8	147.4	143.7	140.0	136.2	132.6
107.5°	181.8	182.3	182.7	183.1	183.5	183.9	184.3	184.7
110°	205.5	205.7	205.9	206.2	206.5	206.8	207.1	207.4



TEST NUMBER: P332640-930

CATALOG NUMBER: S124DIP-S1020D590U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	228.4	228.4	228.4	228.5	228.9	229.3	229.8	230.1
115°	262.7	262.9	263.1	263.3	263.3	263.3	263.3	263.3
117.5°	297.2	297.2	297.1	297.1	297.0	297.0	296.9	296.9
120°	318.5	318.7	318.9	318.9	318.7	318.5	318.3	318.1
122.5°	339.6	339.7	339.8	339.7	339.6	339.3	339.2	338.9
125°	368.9	369.2	369.6	369.8	369.9	370.0	370.1	370.2
127.5°	398.2	398.1	398.0	397.9	397.9	397.8	397.7	397.6
130°	416.0	416.0	416.2	416.2	416.2	416.2	416.2	416.2
132.5°	433.5	433.6	433.7	433.7	433.6	433.5	433.4	433.3
135°	457.5	457.8	458.0	458.2	458.4	458.6	458.9	459.0
137.5°	480.7	480.9	481.1	481.2	481.2	481.1	481.0	480.9
140°	495.0	495.3	495.6	495.8	495.9	496.0	496.1	496.2
142.5°	508.2	508.4	508.7	508.8	508.8	508.8	508.8	508.9
145°	527.1	527.3	527.3	527.5	527.7	527.9	528.2	528.3
147.5°	543.7	543.8	543.9	544.0	544.1	544.2	544.3	544.4
150°	554.3	554.3	554.3	554.4	554.5	554.6	554.7	554.8
152.5°	563.6	563.8	563.9	564.0	563.9	563.9	563.8	563.8
155°	576.1	576.5	576.9	577.0	576.7	576.3	576.1	575.8
157.5°	586.9	587.4	587.9	587.9	587.4	586.9	586.4	585.8
160°	593.7	594.4	595.0	595.0	594.4	593.7	593.1	592.5
162.5°	599.3	599.9	600.5	600.5	599.8	599.1	598.4	597.7
165°	607.2	608.0	608.9	608.8	607.8	606.9	606.0	605.0
167.5°	612.9	613.8	614.7	614.7	613.7	612.6	611.6	610.6
170°	616.4	617.3	618.2	618.0	617.0	616.0	614.9	613.9
172.5°	618.7	619.5	620.4	620.2	619.1	618.0	616.9	615.7
175°	621.3	622.2	623.2	623.1	621.8	620.5	619.3	618.1
177.5°	622.4	623.1	623.7	623.5	622.6	621.6	620.5	619.5
180°	621.8	621.8	621.8	621.8	621.8	621.8	621.8	621.8

(END OF REPORT)