

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332250-940

Luminaire Tested: **S123RDIP-S340D585U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332250-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S340D585U940-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 585 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2953.2 lumens
Efficiency: N/A
Efficacy: 115.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 25.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332250-940

CATALOG NUMBER: S123RDIP-S340D585U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332250-940

CATALOG NUMBER: S123RDIP-S340D585U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39
1	96	91	88	84	87	83	80	77	68	66	64	54	53	51	41	40	40	34
2	87	80	74	69	79	73	68	64	60	56	53	48	45	43	37	35	34	29
3	80	71	64	58	72	65	58	54	53	49	45	42	39	37	33	31	29	24
4	73	63	55	49	66	57	51	46	47	42	39	38	34	32	29	27	25	21
5	67	56	48	42	61	51	44	39	42	37	33	34	30	28	26	24	22	19
6	62	50	42	37	56	46	39	34	38	33	29	31	27	24	24	21	19	16
7	57	45	37	32	52	42	35	30	35	29	26	28	24	21	22	19	17	15
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	20	18	16	13
9	49	37	30	25	45	34	28	24	29	24	20	24	20	17	19	16	14	12
10	46	34	27	23	42	32	25	21	27	22	18	22	18	16	17	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5514	5514	5514
5°	5535	5459	5491
10°	5503	5391	5372
15°	5446	5264	5209
20°	5363	5108	4987
25°	5280	4930	4772
30°	5169	4724	4467
35°	5056	4520	4188
40°	4950	4279	3842
45°	4813	4042	3529
50°	4662	3771	3178
55°	4506	3462	2852
60°	4366	3130	2495
65°	4182	2774	2137
70°	3950	2326	1725
75°	3614	1834	1626
80°	3217	1624	1494
85°	2717	1433	1334



TEST NUMBER: P332250-940

CATALOG NUMBER: S123RDIP-S340D585U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.1	1.6
10°-20°	133.9	4.5
20°-30°	192.7	6.5
30°-40°	217.1	7.4
40°-50°	207.7	7.0
50°-60°	170.1	5.8
60°-70°	114.8	3.9
70°-80°	57.7	2.0
80°-90°	17.2	0.6
90°-100°	42.2	1.4
100°-110°	126.2	4.3
110°-120°	214.7	7.3
120°-130°	282.4	9.6
130°-140°	317.5	10.7
140°-150°	312.1	10.6
150°-160°	262.7	8.9
160°-170°	174.9	5.9
170°-180°	61.2	2.1
0°-30°	374.7	12.7
0°-40°	591.8	20.0
0°-60°	969.6	32.8
0°-90°	1159.3	39.3
90°-120°	383.2	13.0
90°-150°	1295.1	43.9
90°-180°	1794.0	60.7
0°-180°	2953.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	512	512	512	512	512	
5°	512	510	505	509	508	49
15°	489	484	472	470	467	138
25°	445	434	415	407	402	204
35°	385	369	344	327	319	241
45°	316	297	266	243	232	244
55°	240	219	184	161	152	215
65°	164	141	109	89	84	162
75°	87	67	44	40	39	93
85°	22	13	12	11	11	25
90°	0	6	12	14	15	3
95°	30	34	38	40	40	34
105°	114	116	120	120	121	123
115°	216	218	217	217	217	214
125°	316	318	317	315	313	282
135°	410	413	413	411	410	316
145°	498	499	500	500	498	311
155°	570	570	571	572	569	262
165°	621	620	620	622	619	175
175°	646	644	644	647	643	61
180°	648	648	648	648	648	



TEST NUMBER: P332250-940

CATALOG NUMBER: S123RDIP-S340D585U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	512.3	512.3	512.3	512.3	512.3	512.3	512.3	512.3	512.3	512.3	512.3
2.5°	514.0	513.6	513.4	513.1	512.8	512.2	511.3	510.4	509.5	508.6	509.4
5°	512.3	511.8	511.4	511.0	510.4	509.7	508.5	507.5	506.3	505.2	506.0
7.5°	507.6	507.0	506.6	506.0	505.6	504.6	503.2	501.8	500.2	498.8	499.3
10°	503.5	502.9	502.3	501.7	501.0	499.8	498.2	496.5	494.8	493.2	493.3
12.5°	497.9	497.2	496.5	495.8	495.1	493.7	491.6	489.6	487.6	485.5	485.4
15°	488.7	487.6	486.6	485.5	484.6	482.8	480.2	477.6	475.0	472.4	472.0
17.5°	476.9	475.7	474.6	473.3	472.2	469.9	466.6	463.3	460.1	456.8	455.8
20°	468.2	466.8	465.3	463.9	462.4	459.9	456.4	452.8	449.3	445.9	444.6
22.5°	458.6	456.9	455.2	453.5	451.8	449.2	445.4	441.7	437.9	434.2	432.7
25°	444.6	442.3	440.0	437.7	435.3	432.0	427.8	423.6	419.3	415.1	413.1
27.5°	427.6	425.0	422.4	419.9	417.3	413.8	409.0	404.2	399.5	394.8	392.1
30°	415.9	413.1	410.4	407.6	404.8	400.8	395.7	390.5	385.3	380.1	377.0
32.5°	404.3	401.1	398.0	394.8	391.7	387.4	381.9	376.5	371.0	365.5	362.1
35°	384.8	381.4	378.1	374.8	371.5	366.9	361.2	355.4	349.7	344.0	340.1
37.5°	365.0	361.2	357.6	353.9	350.2	345.3	339.2	333.1	327.0	320.8	316.4
40°	352.3	348.3	344.2	340.2	336.1	330.7	324.2	317.6	311.1	304.5	299.8
42.5°	338.0	333.9	329.9	325.8	321.8	316.4	309.6	302.8	296.0	289.3	284.0
45°	316.2	312.0	307.9	303.7	299.5	293.9	286.9	279.7	272.6	265.5	260.2
47.5°	294.4	289.8	285.2	280.6	276.1	270.3	263.1	256.0	249.0	241.8	236.1
50°	278.4	274.0	269.7	265.4	261.0	255.1	247.6	240.1	232.6	225.2	219.5
52.5°	264.1	259.4	254.7	249.9	245.2	239.2	231.8	224.4	217.0	209.6	203.7
55°	240.1	235.6	231.1	226.6	222.0	215.9	208.0	200.2	192.3	184.5	179.1
57.5°	218.0	213.1	208.2	203.2	198.3	191.9	184.0	176.1	168.3	160.4	155.3
60°	202.8	197.7	192.6	187.5	182.4	176.1	168.4	160.8	153.1	145.4	140.4
62.5°	187.4	182.4	177.3	172.3	167.2	160.8	153.1	145.4	137.8	130.1	125.5
65°	164.2	159.1	154.0	148.9	143.8	137.7	130.5	123.2	116.1	108.9	104.3
67.5°	140.8	135.6	130.5	125.4	120.2	114.2	107.3	100.4	93.5	86.6	83.2
70°	125.5	120.5	115.5	110.5	105.6	99.8	93.4	86.9	80.4	73.9	70.7
72.5°	110.2	105.3	100.4	95.4	90.5	85.2	79.3	73.4	67.5	61.6	59.0
75°	86.9	82.4	77.9	73.6	69.1	64.4	59.3	54.2	49.1	44.1	43.2
77.5°	65.5	61.5	57.5	53.5	49.6	45.9	42.6	39.3	36.1	32.8	32.4
80°	51.9	48.2	44.4	40.6	36.8	34.0	32.0	30.1	28.1	26.2	25.9
82.5°	39.0	35.7	32.5	29.2	25.9	23.8	22.9	22.0	21.1	20.2	19.9
85°	22.0	20.0	17.9	16.0	13.9	12.8	12.5	12.2	11.9	11.6	11.4
87.5°	8.1	7.5	6.9	6.3	5.7	5.6	5.9	6.2	6.5	6.8	6.8
90°	0.5	1.6	2.8	3.9	5.0	6.3	7.8	9.3	10.7	12.2	12.7
92.5°	12.3	13.1	13.8	14.6	15.4	16.2	17.0	17.8	18.7	19.5	19.9
95°	30.1	30.8	31.6	32.4	33.2	34.1	35.0	35.8	36.7	37.6	38.1
97.5°	53.3	53.9	54.5	55.1	55.6	56.3	56.9	57.6	58.2	58.9	59.4
100°	69.2	69.8	70.5	71.2	71.9	72.5	73.0	73.7	74.2	74.7	75.1
102.5°	87.5	87.9	88.3	88.7	89.1	89.7	90.4	91.2	91.9	92.6	93.0
105°	114.4	114.7	114.9	115.1	115.4	115.9	117.0	118.0	119.0	120.0	120.0
107.5°	145.8	145.9	146.1	146.2	146.3	146.6	147.0	147.4	147.8	148.2	148.6
110°	165.3	165.5	165.8	165.9	166.2	166.4	166.7	166.9	167.1	167.4	167.8



TEST NUMBER: P332250-940

CATALOG NUMBER: S123RDIP-S340D585U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	185.7	185.7	185.9	186.0	186.2	186.3	186.4	186.4	186.5	186.5	187.0
115°	216.2	216.5	216.9	217.2	217.5	217.6	217.3	217.1	216.9	216.7	216.8
117.5°	246.9	247.1	247.4	247.5	247.8	247.7	247.4	247.2	246.9	246.6	246.6
120°	266.0	266.7	267.3	268.0	268.8	268.8	268.2	267.7	267.1	266.5	266.4
122.5°	286.0	286.4	287.0	287.4	287.9	288.0	287.8	287.5	287.1	286.9	286.6
125°	316.4	316.7	317.0	317.4	317.7	317.8	317.5	317.4	317.1	316.9	316.4
127.5°	344.5	345.2	345.9	346.6	347.3	347.6	347.3	347.1	346.8	346.6	346.0
130°	363.2	364.1	365.0	365.9	366.8	367.0	366.8	366.4	366.0	365.7	365.2
132.5°	381.8	382.8	383.7	384.6	385.5	385.8	385.6	385.3	385.0	384.9	384.2
135°	410.5	411.2	411.8	412.5	413.1	413.5	413.3	413.2	413.1	413.0	412.6
137.5°	436.9	437.5	438.0	438.6	439.2	439.6	439.9	440.1	440.5	440.8	440.3
140°	455.2	455.8	456.4	456.9	457.4	457.8	457.9	458.1	458.2	458.3	458.2
142.5°	471.9	472.4	473.1	473.6	474.1	474.6	474.7	474.9	475.2	475.4	475.3
145°	497.9	498.2	498.4	498.6	498.8	499.1	499.4	499.8	500.2	500.5	500.3
147.5°	520.8	521.1	521.6	521.9	522.4	522.7	523.1	523.3	523.7	524.0	524.0
150°	536.6	536.8	537.1	537.3	537.5	537.7	538.0	538.1	538.4	538.6	538.6
152.5°	549.7	549.9	550.3	550.5	550.9	551.1	551.3	551.3	551.5	551.6	551.8
155°	570.2	570.2	570.2	570.2	570.2	570.2	570.3	570.4	570.6	570.7	571.1
157.5°	587.6	587.5	587.4	587.3	587.1	587.1	587.2	587.3	587.4	587.5	587.9
160°	598.6	598.4	598.2	598.0	597.7	597.6	597.6	597.6	597.6	597.6	598.2
162.5°	608.4	608.1	607.8	607.4	607.2	607.1	607.2	607.3	607.3	607.4	608.0
165°	621.0	620.7	620.4	620.0	619.6	619.5	619.5	619.5	619.5	619.5	620.2
167.5°	631.1	630.6	630.2	629.7	629.3	629.1	629.2	629.3	629.4	629.5	630.2
170°	636.8	636.3	635.9	635.4	635.0	634.7	634.7	634.7	634.7	634.7	635.5
172.5°	641.2	640.8	640.3	639.9	639.4	639.3	639.3	639.3	639.3	639.3	640.0
175°	646.0	645.5	645.1	644.6	644.2	643.9	643.9	643.9	643.9	643.9	644.6
177.5°	647.9	647.6	647.2	646.8	646.4	646.2	646.2	646.2	646.2	646.2	646.8
180°	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5



TEST NUMBER: P332250-940

CATALOG NUMBER: S123RDIP-S340D585U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	512.3	512.3	512.3	512.3	512.3	512.3	512.3	512.3
2.5°	510.2	511.0	511.9	512.2	512.1	511.9	511.8	511.7
5°	506.9	507.7	508.5	508.9	508.7	508.5	508.4	508.2
7.5°	499.8	500.2	500.7	500.8	500.4	500.2	499.8	499.5
10°	493.4	493.5	493.6	493.4	492.9	492.5	492.0	491.5
12.5°	485.4	485.4	485.4	485.0	484.5	483.9	483.4	482.9
15°	471.4	471.0	470.6	470.0	469.4	468.7	468.1	467.4
17.5°	454.9	453.9	452.9	451.9	450.9	450.0	449.1	448.1
20°	443.4	442.2	441.0	439.9	438.7	437.7	436.6	435.4
22.5°	431.2	429.7	428.2	427.0	425.9	424.9	423.8	422.8
25°	411.2	409.3	407.3	405.8	404.8	403.9	402.8	401.8
27.5°	389.4	386.7	384.1	381.9	380.3	378.8	377.3	375.7
30°	373.9	370.8	367.7	365.3	363.8	362.4	360.9	359.4
32.5°	358.6	355.3	351.8	349.3	347.8	346.3	344.6	343.1
35°	336.1	332.1	328.1	325.3	323.7	322.0	320.3	318.7
37.5°	311.8	307.3	302.8	299.5	297.5	295.4	293.4	291.3
40°	295.0	290.2	285.3	281.9	279.7	277.7	275.5	273.4
42.5°	278.7	273.6	268.3	264.7	262.8	260.9	259.0	257.1
45°	254.9	249.7	244.4	240.7	238.5	236.3	234.1	231.8
47.5°	230.3	224.6	218.9	215.1	213.1	211.2	209.1	207.1
50°	213.7	208.0	202.3	198.4	196.3	194.1	192.0	189.8
52.5°	197.7	191.7	185.8	181.9	179.9	178.1	176.2	174.2
55°	173.8	168.4	163.1	159.4	157.7	155.8	153.9	152.0
57.5°	150.3	145.2	140.2	136.8	135.3	133.7	132.2	130.5
60°	135.5	130.5	125.5	122.2	120.6	119.0	117.5	115.9
62.5°	120.7	116.1	111.4	108.2	106.6	105.0	103.3	101.7
65°	99.8	95.3	90.8	88.0	86.9	86.0	85.0	83.9
67.5°	79.8	76.4	73.0	70.8	69.7	68.7	67.6	66.5
70°	67.5	64.3	61.0	58.9	57.9	56.9	55.8	54.8
72.5°	56.4	53.8	51.1	49.6	49.1	48.7	48.3	47.9
75°	42.2	41.3	40.3	39.8	39.6	39.4	39.2	39.1
77.5°	31.8	31.3	30.9	30.5	30.3	30.1	30.0	29.8
80°	25.6	25.3	25.1	24.9	24.6	24.4	24.3	24.1
82.5°	19.6	19.4	19.1	18.9	18.9	18.8	18.8	18.8
85°	11.2	11.1	10.9	10.8	10.8	10.8	10.8	10.8
87.5°	6.8	6.8	6.9	6.9	6.8	6.8	6.8	6.7
90°	13.1	13.6	14.0	14.4	14.6	14.8	15.1	15.2
92.5°	20.2	20.6	21.0	21.1	21.0	20.8	20.7	20.5
95°	38.5	39.0	39.4	39.7	39.7	39.7	39.7	39.7
97.5°	59.9	60.5	61.0	61.2	61.2	61.1	61.1	61.0
100°	75.4	75.8	76.2	76.4	76.6	76.9	77.0	77.3
102.5°	93.4	93.7	94.0	94.2	94.2	94.1	94.1	94.0
105°	120.0	120.0	120.0	120.1	120.4	120.6	120.8	121.1
107.5°	148.9	149.3	149.6	149.8	149.6	149.5	149.4	149.3
110°	168.3	168.7	169.2	169.2	169.1	168.8	168.6	168.4



TEST NUMBER: P332250-940

CATALOG NUMBER: S123RDIP-S340D585U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	187.5	188.1	188.6	188.9	188.9	188.8	188.8	188.7
115°	216.9	217.0	217.1	217.1	217.0	216.9	216.8	216.7
117.5°	246.6	246.5	246.5	246.3	246.0	245.7	245.4	245.0
120°	266.3	266.2	266.1	265.9	265.6	265.5	265.2	265.0
122.5°	286.2	286.0	285.7	285.3	285.1	284.7	284.5	284.1
125°	315.9	315.5	315.0	314.6	314.1	313.7	313.3	312.8
127.5°	345.3	344.6	344.0	343.5	343.0	342.4	341.9	341.3
130°	364.8	364.4	363.9	363.3	362.5	361.7	360.9	360.1
132.5°	383.7	383.2	382.6	382.1	381.5	380.8	380.2	379.6
135°	412.1	411.6	411.2	410.8	410.6	410.4	410.2	409.9
137.5°	439.8	439.3	438.9	438.5	438.0	437.6	437.1	436.7
140°	458.1	457.9	457.8	457.4	456.6	455.8	455.0	454.2
142.5°	475.1	475.0	474.9	474.6	473.9	473.3	472.7	472.1
145°	500.2	500.2	500.1	499.7	499.3	498.8	498.4	497.9
147.5°	524.0	524.0	524.0	523.6	523.0	522.3	521.7	520.9
150°	538.6	538.6	538.6	538.3	537.6	536.9	536.3	535.6
152.5°	552.1	552.2	552.4	552.1	551.6	551.0	550.5	549.8
155°	571.6	572.0	572.5	572.3	571.5	570.7	570.0	569.2
157.5°	588.4	588.9	589.3	589.2	588.6	588.0	587.4	586.7
160°	598.8	599.3	599.9	599.9	599.5	599.1	598.6	598.2
162.5°	608.5	609.1	609.7	609.6	608.9	608.1	607.4	606.7
165°	620.9	621.5	622.2	622.1	621.3	620.5	619.8	619.0
167.5°	630.9	631.6	632.3	632.3	631.6	630.9	630.2	629.5
170°	636.3	637.1	637.9	637.9	637.1	636.3	635.5	634.7
172.5°	640.6	641.3	642.0	642.0	641.2	640.4	639.6	638.8
175°	645.2	646.0	646.7	646.6	645.8	645.0	644.2	643.4
177.5°	647.4	647.9	648.5	648.4	647.7	647.1	646.5	645.9
180°	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5

(END OF REPORT)