

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332643-930

Luminaire Tested: **S124DIP-S1020D810U930-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332643-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIP-S1020D810U930-4F0-1E-UDD-A
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 810 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6392.8 lumens
Efficiency: N/A
Efficacy: 117.5 lumens/watt
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 54.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332643-930
CATALOG NUMBER: S124DIP-S1020D810U930-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332643-930

CATALOG NUMBER: S124DIP-S1020D810U930-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59
1	100	96	92	88	93	89	86	83	78	75	73	67	65	64	57	56	55	50
2	91	84	78	73	85	79	73	69	68	64	61	59	56	54	51	48	46	42
3	83	74	67	61	78	69	63	58	61	56	52	53	49	46	45	42	40	36
4	77	66	58	52	71	62	55	49	54	49	44	47	43	39	40	37	35	31
5	70	59	51	45	65	55	48	42	49	43	38	42	38	34	37	33	30	27
6	65	53	45	39	60	50	42	37	44	38	34	38	34	30	33	30	27	24
7	60	48	40	34	56	45	38	33	40	34	30	35	30	27	30	27	24	21
8	56	43	36	30	52	41	34	29	36	31	27	32	27	24	28	24	21	19
9	52	40	32	27	49	38	31	26	33	28	24	30	25	22	26	22	19	17
10	49	37	29	24	45	35	28	23	31	25	22	27	23	20	24	20	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10984	10984	10984	10984
5°	12935	11012	9720	11012
10°	15488	10964	8751	10964
15°	18324	10853	8037	10853
20°	20405	10740	7399	10740
25°	20735	10573	6959	10573
30°	17643	10413	6820	10413
35°	13565	10154	6821	10154
40°	10572	9848	6949	9848
45°	8816	9388	7066	9388
50°	7759	8828	7304	8828
55°	7108	8155	7600	8155
60°	6660	7553	7953	7553
65°	6202	6879	8246	6879
70°	5667	6212	8434	6212
75°	5062	5468	8334	5468
80°	4245	4482	8071	4482
85°	3131	3242	7725	3242



TEST NUMBER: P332643-930

CATALOG NUMBER: S124DIP-S1020D810U930-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	132.5	2.1
10°-20°	408.6	6.4
20°-30°	647.9	10.1
30°-40°	721.0	11.3
40°-50°	656.3	10.3
50°-60°	536.3	8.4
60°-70°	382.9	6.0
70°-80°	210.8	3.3
80°-90°	60.0	0.9
90°-100°	29.1	0.5
100°-110°	185.9	2.9
110°-120°	355.6	5.6
120°-130°	451.4	7.1
130°-140°	482.9	7.6
140°-150°	451.6	7.1
150°-160°	364.2	5.7
160°-170°	234.9	3.7
170°-180°	81.0	1.3
0°-30°	1189.0	18.6
0°-40°	1910.0	29.9
0°-60°	3102.6	48.5
0°-90°	3756.3	58.8
90°-120°	570.6	8.9
90°-150°	1956.4	30.6
90°-180°	2636.0	41.2
0°-180°	6392.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1361	1361	1361	1361	1361	
5°	1596	1359	1199	1359	1596	162
15°	2192	1299	962	1299	2192	619
25°	2328	1187	781	1187	2328	1026
35°	1376	1030	692	1030	1376	874
45°	772	822	619	822	772	608
55°	505	579	540	579	505	456
65°	325	360	432	360	325	321
75°	162	175	267	175	162	173
85°	34	35	83	35	34	42
90°	19	2	19	2	19	10
95°	18	35	18	35	18	15
105°	182	192	182	192	182	158
115°	361	358	361	358	361	357
125°	507	504	507	504	507	452
135°	629	625	629	625	629	484
145°	724	720	724	720	724	453
155°	789	790	789	790	789	364
165°	829	833	829	833	829	234
175°	847	852	847	852	847	81
180°	852	852	852	852	852	



TEST NUMBER: P332643-930

CATALOG NUMBER: S124DIP-S1020D810U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6
2.5°	1448.1	1447.6	1443.1	1442.2	1439.0	1435.0	1434.1	1426.9	1412.4	1405.7	1403.9
5°	1596.2	1607.4	1592.8	1590.0	1588.3	1569.7	1560.1	1548.8	1522.9	1507.7	1495.8
7.5°	1772.9	1774.3	1767.9	1762.7	1748.3	1732.1	1707.8	1681.9	1651.0	1618.9	1594.6
10°	1889.3	1893.8	1886.4	1885.3	1856.6	1838.5	1802.5	1772.1	1737.1	1698.2	1662.7
12.5°	2011.9	2005.6	2001.9	1977.8	1972.5	1939.5	1897.6	1866.3	1812.4	1767.7	1720.4
15°	2192.5	2180.1	2172.2	2138.9	2122.6	2077.0	2032.4	1998.1	1927.6	1860.5	1809.8
17.5°	2298.4	2310.9	2292.6	2278.9	2236.7	2204.7	2159.2	2087.0	2031.9	1948.6	1884.6
20°	2375.1	2376.2	2366.1	2352.0	2318.7	2278.2	2228.5	2149.6	2083.7	2000.8	1912.9
22.5°	2395.8	2396.1	2391.8	2378.6	2353.4	2320.5	2270.5	2204.7	2124.8	2034.7	1946.8
25°	2327.8	2325.5	2330.6	2345.2	2335.7	2325.5	2296.8	2247.7	2173.3	2078.0	1983.4
27.5°	2074.8	2090.3	2119.0	2155.1	2189.8	2216.3	2223.7	2213.7	2167.6	2089.2	1990.1
30°	1892.6	1911.8	1933.2	1969.3	2039.1	2079.2	2123.2	2156.4	2137.8	2075.3	1982.8
32.5°	1692.5	1697.2	1729.0	1770.0	1834.0	1911.0	1980.7	2048.2	2070.6	2037.8	1960.7
35°	1376.4	1384.2	1418.6	1459.2	1537.6	1631.7	1736.5	1830.1	1907.3	1938.3	1898.8
37.5°	1123.2	1145.8	1170.1	1213.7	1282.7	1367.4	1476.3	1597.4	1712.5	1789.6	1802.7
40°	1003.2	1017.3	1034.8	1068.0	1126.7	1210.1	1303.7	1442.3	1564.6	1675.1	1711.2
42.5°	908.6	916.8	927.5	957.6	1002.2	1085.2	1170.6	1292.6	1415.4	1547.4	1607.9
45°	772.2	780.6	798.7	816.1	849.9	907.4	986.9	1087.2	1210.6	1338.1	1449.6
47.5°	673.6	679.1	689.7	708.5	737.2	775.1	839.8	923.6	1038.0	1161.6	1280.5
50°	617.8	622.2	630.7	647.6	669.6	703.4	756.4	834.7	924.3	1048.9	1165.6
52.5°	573.6	575.4	581.6	593.0	610.5	639.0	682.4	747.2	830.5	941.6	1057.8
55°	505.0	507.3	512.9	521.4	536.5	554.6	587.8	636.3	709.1	805.4	906.3
57.5°	448.7	450.2	454.9	458.2	470.8	485.4	510.9	545.6	600.7	682.4	772.5
60°	412.5	411.5	417.1	419.9	428.4	440.8	460.5	493.7	541.6	607.6	690.4
62.5°	377.4	375.9	380.6	384.3	389.1	399.7	415.8	441.9	480.8	540.4	612.0
65°	324.7	322.4	325.2	329.7	334.2	339.9	351.7	374.8	405.8	448.7	503.3
67.5°	271.7	274.0	274.5	276.7	279.3	287.0	295.1	311.4	333.3	367.6	413.9
70°	240.1	240.7	243.0	243.0	244.6	251.4	258.1	267.7	289.1	320.7	358.5
72.5°	208.6	210.9	210.0	211.8	213.0	217.5	222.5	231.6	249.9	273.4	305.2
75°	162.3	164.0	164.0	164.6	166.2	168.0	171.9	178.6	191.6	209.1	231.1
77.5°	118.4	118.6	119.4	121.4	121.4	124.1	127.0	132.5	138.8	150.8	164.2
80°	91.3	92.5	91.9	93.0	93.0	95.2	96.4	103.1	106.0	113.8	124.6
82.5°	66.9	68.1	68.0	69.5	70.4	70.9	72.5	75.2	78.0	85.0	89.4
85°	33.8	35.0	33.8	35.0	36.6	37.2	38.9	39.5	41.7	43.4	47.4
87.5°	13.8	15.0	15.0	15.4	16.2	16.6	16.9	16.2	17.9	18.1	19.7
90°	19.2	18.8	18.6	18.3	18.0	17.4	16.6	15.7	14.8	14.0	12.9
92.5°	17.6	17.5	17.4	17.4	17.4	16.9	16.1	15.2	14.3	13.5	12.4
95°	18.5	18.3	18.2	18.1	17.9	17.4	16.6	15.7	14.8	14.0	13.9
97.5°	17.9	17.7	17.5	17.4	17.3	17.2	17.1	17.0	16.9	16.8	32.6
100°	17.9	17.7	17.5	17.4	17.3	18.4	20.8	23.2	25.6	28.0	47.6
102.5°	18.3	18.3	18.3	18.3	18.3	31.2	57.2	83.2	109.2	135.2	137.7
105°	181.6	186.8	191.8	197.0	202.1	204.0	202.7	201.5	200.2	198.9	198.2
107.5°	253.2	252.7	252.1	251.6	251.0	250.5	249.8	249.2	248.6	248.0	247.0
110°	284.3	283.9	283.5	283.1	282.6	282.3	282.0	281.7	281.4	281.1	280.3



TEST NUMBER: P332643-930

CATALOG NUMBER: S124DIP-S1020D810U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	315.4	314.9	314.4	313.8	313.2	313.0	313.1	313.2	313.2	313.2	312.8
115°	360.9	360.9	360.9	360.9	360.9	360.7	360.4	360.1	359.8	359.5	359.7
117.5°	407.0	407.0	407.1	407.2	407.2	407.2	407.3	407.3	407.4	407.5	407.2
120°	436.0	436.3	436.6	436.9	437.2	437.2	436.9	436.6	436.3	436.0	436.2
122.5°	464.6	464.9	465.1	465.5	465.7	465.8	465.6	465.5	465.3	465.1	464.9
125°	507.4	507.3	507.1	507.0	506.9	506.5	506.1	505.7	505.3	504.9	505.2
127.5°	545.0	545.2	545.3	545.4	545.5	545.6	545.7	545.8	545.8	545.9	545.3
130°	570.5	570.5	570.5	570.5	570.5	570.5	570.3	570.2	570.1	569.9	569.5
132.5°	594.0	594.1	594.2	594.4	594.4	594.4	594.3	594.2	594.0	593.9	593.3
135°	629.2	628.9	628.6	628.4	628.0	627.8	627.5	627.2	626.9	626.6	626.1
137.5°	659.3	659.3	659.4	659.5	659.6	659.5	659.2	658.8	658.6	658.3	657.6
140°	680.2	680.0	679.9	679.8	679.6	679.3	678.9	678.5	678.1	677.6	677.4
142.5°	697.5	697.5	697.5	697.4	697.4	697.2	696.9	696.6	696.3	696.0	695.9
145°	724.1	723.9	723.6	723.3	723.0	722.8	722.7	722.5	722.4	722.3	722.3
147.5°	746.2	746.1	745.9	745.8	745.7	745.5	745.4	745.3	745.2	745.1	745.2
150°	760.5	760.3	760.2	760.1	759.9	759.9	759.9	759.9	759.9	759.9	760.0
152.5°	772.7	772.8	772.9	773.0	773.1	773.0	772.8	772.6	772.3	772.1	772.3
155°	789.2	789.6	790.0	790.4	790.9	790.8	790.3	789.7	789.1	788.6	789.0
157.5°	803.0	803.7	804.5	805.2	805.9	805.9	805.2	804.5	803.7	803.0	803.5
160°	812.1	813.0	813.8	814.7	815.5	815.5	814.7	813.8	813.0	812.1	812.3
162.5°	819.3	820.3	821.2	822.1	823.1	823.2	822.3	821.5	820.7	819.8	819.9
165°	829.3	830.6	831.9	833.2	834.5	834.5	833.4	832.3	831.1	830.0	830.0
167.5°	836.9	838.3	839.7	841.1	842.5	842.6	841.4	840.2	838.9	837.6	837.7
170°	841.5	842.9	844.3	845.7	847.1	847.3	846.1	845.0	843.8	842.8	842.6
172.5°	844.0	845.5	847.1	848.6	850.1	850.4	849.2	848.1	846.9	845.8	845.6
175°	847.2	848.9	850.6	852.3	854.0	854.2	853.0	851.7	850.4	849.1	849.0
177.5°	849.2	850.6	852.0	853.3	854.7	854.9	854.0	853.1	852.2	851.3	851.1
180°	852.3	852.3	852.3	852.3	852.3	852.3	852.3	852.3	852.3	852.3	852.3



TEST NUMBER: P332643-930

CATALOG NUMBER: S124DIP-S1020D810U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6
2.5°	1404.4	1398.0	1393.5	1389.9	1380.0	1374.1	1369.6	1363.3	1356.1	1348.4	1339.0
5°	1484.0	1464.8	1450.7	1429.4	1409.1	1392.1	1374.7	1358.9	1339.7	1318.9	1303.7
7.5°	1567.7	1539.3	1502.8	1471.0	1435.4	1404.4	1376.7	1348.3	1318.7	1290.1	1263.9
10°	1621.0	1584.4	1543.8	1495.8	1450.7	1410.7	1373.5	1337.5	1302.5	1267.5	1237.7
12.5°	1678.2	1632.6	1572.6	1516.6	1466.1	1412.6	1367.7	1323.5	1281.3	1244.6	1209.7
15°	1755.1	1689.1	1619.8	1544.9	1478.4	1415.8	1354.4	1298.6	1251.2	1202.7	1169.0
17.5°	1802.4	1720.8	1641.5	1563.2	1482.6	1403.8	1337.5	1273.1	1213.8	1165.7	1123.1
20°	1833.4	1752.3	1653.7	1575.3	1479.5	1398.3	1321.7	1250.1	1188.1	1136.9	1092.8
22.5°	1860.5	1766.8	1668.1	1565.0	1469.6	1383.5	1299.6	1227.6	1164.2	1110.2	1068.0
25°	1875.2	1767.5	1660.4	1557.9	1449.6	1347.6	1271.5	1187.0	1119.3	1062.4	1017.3
27.5°	1876.7	1761.6	1640.5	1526.5	1414.8	1319.8	1223.8	1148.2	1078.0	1017.8	974.5
30°	1871.8	1751.8	1621.5	1498.1	1385.9	1282.8	1199.4	1117.1	1045.5	985.8	940.7
32.5°	1856.0	1731.0	1597.2	1466.6	1350.3	1249.4	1163.4	1085.1	1015.3	956.4	909.1
35°	1810.4	1686.9	1544.3	1408.5	1289.6	1187.6	1109.8	1030.3	960.4	904.6	859.0
37.5°	1739.0	1627.4	1482.5	1341.9	1225.1	1122.6	1045.5	973.7	910.7	854.0	807.2
40°	1676.7	1578.7	1433.3	1296.3	1170.1	1072.6	1000.5	934.5	872.0	818.4	773.9
42.5°	1605.1	1519.6	1385.5	1240.4	1118.7	1020.8	950.4	891.2	832.3	782.8	738.3
45°	1477.2	1420.9	1294.6	1160.5	1033.7	941.3	874.2	822.3	772.7	724.2	687.1
47.5°	1330.2	1302.3	1196.0	1068.6	948.3	857.1	799.0	751.1	707.6	666.5	633.7
50°	1231.5	1218.0	1126.1	1003.2	888.3	802.6	744.0	702.9	665.6	629.6	598.6
52.5°	1134.1	1133.7	1050.8	938.3	831.9	749.4	691.2	652.8	620.5	591.3	563.4
55°	985.2	1001.0	936.2	835.8	740.6	666.2	613.8	579.4	556.8	532.6	511.8
57.5°	848.5	874.7	821.2	732.8	653.4	584.8	539.2	513.3	489.3	474.7	459.5
60°	759.2	784.0	742.3	667.9	593.0	534.3	490.9	467.8	446.9	436.8	426.1
62.5°	679.9	702.0	671.1	602.1	537.0	480.6	444.0	421.8	407.7	396.6	389.6
65°	566.5	585.1	558.6	508.4	452.6	407.5	377.6	360.1	346.7	342.1	334.2
67.5°	457.9	474.8	460.5	417.8	373.1	339.0	315.6	298.8	290.8	286.9	281.3
70°	393.4	410.3	395.1	357.9	323.5	294.8	272.8	263.2	254.8	253.1	245.2
72.5°	338.8	350.3	335.2	306.1	276.6	252.4	235.4	225.3	220.9	217.9	213.6
75°	254.2	264.3	254.2	231.6	210.8	193.9	179.2	175.3	170.2	168.5	165.7
77.5°	179.9	188.7	180.9	166.8	151.2	138.2	130.3	125.2	124.1	121.2	122.5
80°	137.5	143.2	135.8	126.3	113.8	104.8	99.2	96.4	93.0	91.9	94.1
82.5°	98.7	101.3	97.5	91.1	81.9	76.0	72.2	68.9	68.2	68.4	68.4
85°	51.3	50.7	50.1	44.5	41.7	37.7	35.5	35.0	34.4	35.5	36.6
87.5°	19.5	19.7	19.0	17.0	15.3	13.6	12.9	12.1	12.9	13.6	14.4
90°	11.7	10.6	9.5	8.2	6.6	5.1	3.5	1.9	3.5	5.1	6.6
92.5°	11.3	10.1	9.0	8.4	8.3	8.2	8.2	8.1	8.2	8.2	8.3
95°	13.8	13.6	13.5	15.8	20.6	25.4	30.2	35.1	30.2	25.4	20.6
97.5°	48.4	64.2	80.1	86.5	83.5	80.5	77.5	74.4	77.5	80.5	83.5
100°	67.2	86.7	106.2	114.7	112.2	109.7	107.1	104.5	107.1	109.7	112.2
102.5°	140.2	142.8	145.4	145.7	143.8	141.9	140.1	138.2	140.1	141.9	143.8
105°	197.5	196.7	196.1	195.3	194.4	193.6	192.7	191.8	192.7	193.6	194.4
107.5°	246.1	245.1	244.1	243.4	243.0	242.6	242.1	241.7	242.1	242.6	243.0
110°	279.4	278.6	277.7	277.1	276.6	276.2	275.8	275.4	275.8	276.2	276.6



TEST NUMBER: P332643-930

CATALOG NUMBER: S124DIP-S1020D810U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	312.4	312.1	311.7	311.1	310.3	309.6	308.8	308.0	308.8	309.6	310.3
115°	359.8	360.0	360.1	360.0	359.5	359.1	358.7	358.2	358.7	359.1	359.5
117.5°	406.8	406.5	406.3	405.8	405.2	404.6	404.1	403.5	404.1	404.6	405.2
120°	436.3	436.4	436.6	436.3	435.9	435.3	434.7	434.1	434.7	435.3	435.9
122.5°	464.7	464.5	464.3	464.1	463.7	463.3	463.0	462.7	463.0	463.3	463.7
125°	505.5	505.7	506.0	505.9	505.3	504.8	504.2	503.6	504.2	504.8	505.3
127.5°	544.6	544.0	543.3	542.9	542.8	542.7	542.5	542.3	542.5	542.7	542.8
130°	569.1	568.6	568.2	567.9	567.8	567.6	567.5	567.4	567.5	567.6	567.8
132.5°	592.8	592.2	591.7	591.3	591.1	590.8	590.5	590.3	590.5	590.8	591.1
135°	625.5	624.9	624.4	624.2	624.3	624.4	624.6	624.8	624.6	624.4	624.3
137.5°	657.0	656.4	655.7	655.4	655.3	655.3	655.3	655.2	655.3	655.3	655.3
140°	677.1	676.8	676.5	676.2	676.0	675.6	675.4	675.1	675.4	675.6	676.0
142.5°	695.7	695.5	695.3	695.0	694.5	694.0	693.4	692.9	693.4	694.0	694.5
145°	722.3	722.3	722.3	722.0	721.6	721.2	720.8	720.3	720.8	721.2	721.6
147.5°	745.3	745.5	745.7	745.3	744.5	743.7	743.0	742.2	743.0	743.7	744.5
150°	760.2	760.3	760.4	760.2	759.7	759.1	758.6	758.0	758.6	759.1	759.7
152.5°	772.7	772.9	773.1	773.1	772.6	772.1	771.7	771.2	771.7	772.1	772.6
155°	789.4	789.9	790.3	790.4	790.3	790.1	789.9	789.9	789.9	790.1	790.3
157.5°	804.0	804.4	804.9	805.2	805.3	805.4	805.4	805.5	805.4	805.4	805.3
160°	812.4	812.6	812.7	813.0	813.4	813.8	814.2	814.7	814.2	813.8	813.4
162.5°	820.1	820.2	820.4	820.7	821.3	821.7	822.3	822.9	822.3	821.7	821.3
165°	830.0	830.0	830.0	830.4	831.0	831.8	832.5	833.2	832.5	831.8	831.0
167.5°	837.8	837.9	838.0	838.4	839.1	839.8	840.6	841.3	840.6	839.8	839.1
170°	842.4	842.3	842.2	842.5	843.3	844.2	845.1	846.0	845.1	844.2	843.3
172.5°	845.5	845.4	845.2	845.6	846.4	847.3	848.2	849.0	848.2	847.3	846.4
175°	848.8	848.7	848.6	848.9	849.8	850.6	851.4	852.3	851.4	850.6	849.8
177.5°	850.8	850.6	850.4	850.7	851.4	852.2	853.0	853.9	853.0	852.2	851.4
180°	852.3	852.3	852.3	852.3	852.3	852.3	852.3	852.3	852.3	852.3	852.3



TEST NUMBER: P332643-930

CATALOG NUMBER: S124DIP-S1020D810U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6
2.5°	1334.4	1330.4	1324.5	1316.4	1309.6	1302.4	1300.6	1297.9	1303.3	1298.8	1297.5
5°	1290.7	1278.9	1263.6	1246.2	1236.0	1221.4	1218.5	1212.9	1207.3	1206.7	1201.1
7.5°	1244.4	1227.0	1207.1	1189.3	1172.8	1156.7	1146.3	1144.0	1135.7	1130.8	1125.2
10°	1214.6	1193.2	1170.1	1153.2	1134.0	1117.1	1105.3	1098.5	1092.8	1086.6	1081.0
12.5°	1179.4	1156.7	1137.6	1119.3	1096.6	1083.7	1064.2	1052.5	1051.4	1051.5	1036.8
15°	1138.5	1116.0	1086.6	1060.7	1048.3	1023.5	1012.8	999.3	990.8	982.4	975.7
17.5°	1091.8	1063.6	1040.8	1011.1	987.3	967.6	953.6	945.4	932.7	920.7	912.1
20°	1062.4	1032.6	1008.3	976.7	950.8	926.6	914.8	903.5	893.9	883.8	874.2
22.5°	1032.7	1001.4	971.8	941.1	917.0	891.4	880.0	864.7	855.6	849.9	840.3
25°	985.8	951.9	918.1	888.8	864.1	841.5	826.3	814.4	804.3	799.8	793.6
27.5°	934.8	901.2	868.5	835.3	807.1	790.8	778.6	769.6	763.9	757.8	755.0
30°	902.4	867.4	832.5	801.4	775.5	759.2	748.0	741.8	737.2	734.4	731.6
32.5°	869.4	834.9	798.2	769.9	746.7	732.1	723.6	717.4	715.1	714.1	713.1
35°	816.7	781.7	748.0	722.6	700.6	695.0	687.6	684.2	683.1	687.1	688.8
37.5°	765.6	733.2	702.1	677.4	663.1	654.8	652.3	652.5	656.5	660.0	664.1
40°	732.7	701.2	671.8	650.4	636.9	631.9	630.7	633.5	638.1	642.0	646.5
42.5°	700.7	669.6	642.9	622.9	613.4	608.8	609.5	612.3	618.6	623.5	630.2
45°	651.0	625.1	599.2	582.8	574.9	576.0	576.0	581.1	587.3	594.6	601.9
47.5°	604.2	578.0	556.8	543.0	538.9	537.9	541.1	547.7	556.6	565.7	575.9
50°	572.7	547.8	529.2	516.8	512.3	514.0	518.5	524.7	535.4	546.7	557.4
52.5°	540.6	518.0	500.8	489.3	486.2	489.3	493.7	503.5	512.9	525.1	538.0
55°	490.9	471.7	458.2	449.8	448.7	450.4	455.4	466.1	479.6	494.9	507.3
57.5°	441.4	425.4	413.0	407.2	407.7	409.3	417.7	430.4	444.8	461.1	477.0
60°	408.1	393.4	383.3	378.8	379.3	382.7	392.8	404.7	422.7	438.5	455.4
62.5°	376.5	363.6	353.9	349.9	349.1	356.5	366.2	378.5	396.6	414.2	432.4
65°	325.8	315.6	307.8	305.5	307.2	312.8	325.2	341.5	356.8	375.4	394.5
67.5°	276.1	267.8	262.4	263.4	265.5	273.8	284.2	298.2	315.5	334.8	353.8
70°	244.6	236.7	232.2	232.8	236.2	246.3	255.4	269.4	288.0	307.8	323.5
72.5°	212.1	206.9	202.9	205.3	208.6	215.6	226.9	241.0	257.4	275.7	292.4
75°	162.9	162.9	160.6	162.3	167.4	174.1	182.6	197.3	213.6	228.3	241.8
77.5°	120.8	119.6	121.1	123.1	126.0	134.0	143.7	154.2	166.5	181.2	192.3
80°	92.5	93.0	95.8	99.2	100.4	106.6	116.7	126.3	135.8	148.2	158.9
82.5°	69.5	70.0	71.5	75.7	76.9	83.6	90.1	99.6	108.4	116.7	125.6
85°	37.7	37.7	40.6	42.2	45.1	49.6	53.6	59.2	67.1	72.7	81.1
87.5°	16.1	16.3	18.3	19.5	21.0	23.6	24.6	29.8	31.7	34.2	38.3
90°	8.2	9.5	10.6	11.7	12.9	14.0	14.8	15.7	16.6	17.4	18.0
92.5°	8.4	9.0	10.1	11.3	12.4	13.5	14.3	15.2	16.1	16.9	17.4
95°	15.8	13.5	13.6	13.8	13.9	14.0	14.8	15.7	16.6	17.4	17.9
97.5°	86.5	80.1	64.2	48.4	32.6	16.8	16.9	17.0	17.1	17.2	17.3
100°	114.7	106.2	86.7	67.2	47.6	28.0	25.6	23.2	20.8	18.4	17.3
102.5°	145.7	145.4	142.8	140.2	137.7	135.2	109.2	83.2	57.2	31.2	18.3
105°	195.3	196.1	196.7	197.5	198.2	198.9	200.2	201.5	202.7	204.0	202.1
107.5°	243.4	244.1	245.1	246.1	247.0	248.0	248.6	249.2	249.8	250.5	251.0
110°	277.1	277.7	278.6	279.4	280.3	281.1	281.4	281.7	282.0	282.3	282.6



TEST NUMBER: P332643-930

CATALOG NUMBER: S124DIP-S1020D810U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	311.1	311.7	312.1	312.4	312.8	313.2	313.2	313.2	313.1	313.0	313.2
115°	360.0	360.1	360.0	359.8	359.7	359.5	359.8	360.1	360.4	360.7	360.9
117.5°	405.8	406.3	406.5	406.8	407.2	407.5	407.4	407.3	407.3	407.2	407.2
120°	436.3	436.6	436.4	436.3	436.2	436.0	436.3	436.6	436.9	437.2	437.2
122.5°	464.1	464.3	464.5	464.7	464.9	465.1	465.3	465.5	465.6	465.8	465.7
125°	505.9	506.0	505.7	505.5	505.2	504.9	505.3	505.7	506.1	506.5	506.9
127.5°	542.9	543.3	544.0	544.6	545.3	545.9	545.8	545.8	545.7	545.6	545.5
130°	567.9	568.2	568.6	569.1	569.5	569.9	570.1	570.2	570.3	570.5	570.5
132.5°	591.3	591.7	592.2	592.8	593.3	593.9	594.0	594.2	594.3	594.4	594.4
135°	624.2	624.4	624.9	625.5	626.1	626.6	626.9	627.2	627.5	627.8	628.0
137.5°	655.4	655.7	656.4	657.0	657.6	658.3	658.6	658.8	659.2	659.5	659.6
140°	676.2	676.5	676.8	677.1	677.4	677.6	678.1	678.5	678.9	679.3	679.6
142.5°	695.0	695.3	695.5	695.7	695.9	696.0	696.3	696.6	696.9	697.2	697.4
145°	722.0	722.3	722.3	722.3	722.3	722.3	722.4	722.5	722.7	722.8	723.0
147.5°	745.3	745.7	745.5	745.3	745.2	745.1	745.2	745.3	745.4	745.5	745.7
150°	760.2	760.4	760.3	760.2	760.0	759.9	759.9	759.9	759.9	759.9	759.9
152.5°	773.1	773.1	772.9	772.7	772.3	772.1	772.3	772.6	772.8	773.0	773.1
155°	790.4	790.3	789.9	789.4	789.0	788.6	789.1	789.7	790.3	790.8	790.9
157.5°	805.2	804.9	804.4	804.0	803.5	803.0	803.7	804.5	805.2	805.9	805.9
160°	813.0	812.7	812.6	812.4	812.3	812.1	813.0	813.8	814.7	815.5	815.5
162.5°	820.7	820.4	820.2	820.1	819.9	819.8	820.7	821.5	822.3	823.2	823.1
165°	830.4	830.0	830.0	830.0	830.0	830.0	831.1	832.3	833.4	834.5	834.5
167.5°	838.4	838.0	837.9	837.8	837.7	837.6	838.9	840.2	841.4	842.6	842.5
170°	842.5	842.2	842.3	842.4	842.6	842.8	843.8	845.0	846.1	847.3	847.1
172.5°	845.6	845.2	845.4	845.5	845.6	845.8	846.9	848.1	849.2	850.4	850.1
175°	848.9	848.6	848.7	848.8	849.0	849.1	850.4	851.7	853.0	854.2	854.0
177.5°	850.7	850.4	850.6	850.8	851.1	851.3	852.2	853.1	854.0	854.9	854.7
180°	852.3	852.3	852.3	852.3	852.3	852.3	852.3	852.3	852.3	852.3	852.3



TEST NUMBER: P332643-930

CATALOG NUMBER: S124DIP-S1020D810U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6
2.5°	1296.6	1295.7	1292.5	1292.1	1292.5	1295.7	1296.6	1297.5	1298.8	1303.3	1297.9
5°	1197.7	1194.9	1193.2	1199.4	1193.2	1194.9	1197.7	1201.1	1206.7	1207.3	1212.9
7.5°	1123.2	1121.0	1116.0	1114.4	1116.0	1121.0	1123.2	1125.2	1130.8	1135.7	1144.0
10°	1075.4	1073.1	1068.6	1067.5	1068.6	1073.1	1075.4	1081.0	1086.6	1092.8	1098.5
12.5°	1029.4	1024.9	1024.0	1025.1	1024.0	1024.9	1029.4	1036.8	1051.5	1051.4	1052.5
15°	968.3	966.0	959.9	961.6	959.9	966.0	968.3	975.7	982.4	990.8	999.3
17.5°	908.1	905.4	897.9	904.5	897.9	905.4	908.1	912.1	920.7	932.7	945.4
20°	870.3	865.7	861.8	861.2	861.8	865.7	870.3	874.2	883.8	893.9	903.5
22.5°	834.1	830.1	829.7	826.1	829.7	830.1	834.1	840.3	849.9	855.6	864.7
25°	789.0	785.1	784.0	781.2	784.0	785.1	789.0	793.6	799.8	804.3	814.4
27.5°	754.5	752.5	750.5	751.4	750.5	752.5	754.5	755.0	757.8	763.9	769.6
30°	733.3	732.7	731.6	731.6	731.6	732.7	733.3	731.6	734.4	737.2	741.8
32.5°	715.7	715.6	716.2	716.2	716.2	715.6	715.7	713.1	714.1	715.1	717.4
35°	691.0	692.7	693.8	692.1	693.8	692.7	691.0	688.8	687.1	683.1	684.2
37.5°	668.7	670.3	672.0	673.8	672.0	670.3	668.7	664.1	660.0	656.5	652.5
40°	651.5	655.5	656.6	659.4	656.6	655.5	651.5	646.5	642.0	638.1	633.5
42.5°	635.3	639.7	642.6	643.2	642.6	639.7	635.3	630.2	623.5	618.6	612.3
45°	610.4	614.9	618.9	618.9	618.9	614.9	610.4	601.9	594.6	587.3	581.1
47.5°	584.6	591.1	595.1	596.1	595.1	591.1	584.6	575.9	565.7	556.6	547.7
50°	567.0	574.9	578.9	581.6	578.9	574.9	567.0	557.4	546.7	535.4	524.7
52.5°	549.8	557.7	563.0	564.5	563.0	557.7	549.8	538.0	525.1	512.9	503.5
55°	520.2	531.5	537.7	540.0	537.7	531.5	520.2	507.3	494.9	479.6	466.1
57.5°	492.3	502.6	509.9	511.5	509.9	502.6	492.3	477.0	461.1	444.8	430.4
60°	470.6	481.9	490.9	492.6	490.9	481.9	470.6	455.4	438.5	422.7	404.7
62.5°	448.5	460.2	468.4	472.8	468.4	460.2	448.5	432.4	414.2	396.6	378.5
65°	410.3	422.2	430.1	431.7	430.1	422.2	410.3	394.5	375.4	356.8	341.5
67.5°	368.6	380.4	385.6	388.9	385.6	380.4	368.6	353.8	334.8	315.5	298.2
70°	339.3	348.9	354.5	357.3	354.5	348.9	339.3	323.5	307.8	288.0	269.4
72.5°	305.9	315.9	322.5	323.1	322.5	315.9	305.9	292.4	275.7	257.4	241.0
75°	254.8	263.7	267.2	267.2	267.2	263.7	254.8	241.8	228.3	213.6	197.3
77.5°	201.6	206.3	210.6	211.5	210.6	206.3	201.6	192.3	181.2	166.5	154.2
80°	167.4	170.2	173.6	173.6	173.6	170.2	167.4	158.9	148.2	135.8	126.3
82.5°	132.2	134.6	137.9	137.5	137.9	134.6	132.2	125.6	116.7	108.4	99.6
85°	80.1	85.1	84.5	83.4	84.5	85.1	80.1	81.1	72.7	67.1	59.2
87.5°	39.7	40.2	41.7	42.6	41.7	40.2	39.7	38.3	34.2	31.7	29.8
90°	18.3	18.6	18.8	19.2	18.8	18.6	18.3	18.0	17.4	16.6	15.7
92.5°	17.4	17.4	17.5	17.6	17.5	17.4	17.4	17.4	16.9	16.1	15.2
95°	18.1	18.2	18.3	18.5	18.3	18.2	18.1	17.9	17.4	16.6	15.7
97.5°	17.4	17.5	17.7	17.9	17.7	17.5	17.4	17.3	17.2	17.1	17.0
100°	17.4	17.5	17.7	17.9	17.7	17.5	17.4	17.3	18.4	20.8	23.2
102.5°	18.3	18.3	18.3	18.3	18.3	18.3	18.3	18.3	31.2	57.2	83.2
105°	197.0	191.8	186.8	181.6	186.8	191.8	197.0	202.1	204.0	202.7	201.5
107.5°	251.6	252.1	252.7	253.2	252.7	252.1	251.6	251.0	250.5	249.8	249.2
110°	283.1	283.5	283.9	284.3	283.9	283.5	283.1	282.6	282.3	282.0	281.7



TEST NUMBER: P332643-930

CATALOG NUMBER: S124DIP-S1020D810U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	313.8	314.4	314.9	315.4	314.9	314.4	313.8	313.2	313.0	313.1	313.2
115°	360.9	360.9	360.9	360.9	360.9	360.9	360.9	360.9	360.7	360.4	360.1
117.5°	407.2	407.1	407.0	407.0	407.0	407.1	407.2	407.2	407.2	407.3	407.3
120°	436.9	436.6	436.3	436.0	436.3	436.6	436.9	437.2	437.2	436.9	436.6
122.5°	465.5	465.1	464.9	464.6	464.9	465.1	465.5	465.7	465.8	465.6	465.5
125°	507.0	507.1	507.3	507.4	507.3	507.1	507.0	506.9	506.5	506.1	505.7
127.5°	545.4	545.3	545.2	545.0	545.2	545.3	545.4	545.5	545.6	545.7	545.8
130°	570.5	570.5	570.5	570.5	570.5	570.5	570.5	570.5	570.5	570.3	570.2
132.5°	594.4	594.2	594.1	594.0	594.1	594.2	594.4	594.4	594.4	594.3	594.2
135°	628.4	628.6	628.9	629.2	628.9	628.6	628.4	628.0	627.8	627.5	627.2
137.5°	659.5	659.4	659.3	659.3	659.3	659.4	659.5	659.6	659.5	659.2	658.8
140°	679.8	679.9	680.0	680.2	680.0	679.9	679.8	679.6	679.3	678.9	678.5
142.5°	697.4	697.5	697.5	697.5	697.5	697.5	697.4	697.4	697.2	696.9	696.6
145°	723.3	723.6	723.9	724.1	723.9	723.6	723.3	723.0	722.8	722.7	722.5
147.5°	745.8	745.9	746.1	746.2	746.1	745.9	745.8	745.7	745.5	745.4	745.3
150°	760.1	760.2	760.3	760.5	760.3	760.2	760.1	759.9	759.9	759.9	759.9
152.5°	773.0	772.9	772.8	772.7	772.8	772.9	773.0	773.1	773.0	772.8	772.6
155°	790.4	790.0	789.6	789.2	789.6	790.0	790.4	790.9	790.8	790.3	789.7
157.5°	805.2	804.5	803.7	803.0	803.7	804.5	805.2	805.9	805.9	805.2	804.5
160°	814.7	813.8	813.0	812.1	813.0	813.8	814.7	815.5	815.5	814.7	813.8
162.5°	822.1	821.2	820.3	819.3	820.3	821.2	822.1	823.1	823.2	822.3	821.5
165°	833.2	831.9	830.6	829.3	830.6	831.9	833.2	834.5	834.5	833.4	832.3
167.5°	841.1	839.7	838.3	836.9	838.3	839.7	841.1	842.5	842.6	841.4	840.2
170°	845.7	844.3	842.9	841.5	842.9	844.3	845.7	847.1	847.3	846.1	845.0
172.5°	848.6	847.1	845.5	844.0	845.5	847.1	848.6	850.1	850.4	849.2	848.1
175°	852.3	850.6	848.9	847.2	848.9	850.6	852.3	854.0	854.2	853.0	851.7
177.5°	853.3	852.0	850.6	849.2	850.6	852.0	853.3	854.7	854.9	854.0	853.1
180°	852.3	852.3	852.3	852.3	852.3	852.3	852.3	852.3	852.3	852.3	852.3



TEST NUMBER: P332643-930

CATALOG NUMBER: S124DIP-S1020D810U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6
2.5°	1300.6	1302.4	1309.6	1316.4	1324.5	1330.4	1334.4	1339.0	1348.4	1356.1	1363.3
5°	1218.5	1221.4	1236.0	1246.2	1263.6	1278.9	1290.7	1303.7	1318.9	1339.7	1358.9
7.5°	1146.3	1156.7	1172.8	1189.3	1207.1	1227.0	1244.4	1263.9	1290.1	1318.7	1348.3
10°	1105.3	1117.1	1134.0	1153.2	1170.1	1193.2	1214.6	1237.7	1267.5	1302.5	1337.5
12.5°	1064.2	1083.7	1096.6	1119.3	1137.6	1156.7	1179.4	1209.7	1244.6	1281.3	1323.5
15°	1012.8	1023.5	1048.3	1060.7	1086.6	1116.0	1138.5	1169.0	1202.7	1251.2	1298.6
17.5°	953.6	967.6	987.3	1011.1	1040.8	1063.6	1091.8	1123.1	1165.7	1213.8	1273.1
20°	914.8	926.6	950.8	976.7	1008.3	1032.6	1062.4	1092.8	1136.9	1188.1	1250.1
22.5°	880.0	891.4	917.0	941.1	971.8	1001.4	1032.7	1068.0	1110.2	1164.2	1227.6
25°	826.3	841.5	864.1	888.8	918.1	951.9	985.8	1017.3	1062.4	1119.3	1187.0
27.5°	778.6	790.8	807.1	835.3	868.5	901.2	934.8	974.5	1017.8	1078.0	1148.2
30°	748.0	759.2	775.5	801.4	832.5	867.4	902.4	940.7	985.8	1045.5	1117.1
32.5°	723.6	732.1	746.7	769.9	798.2	834.9	869.4	909.1	956.4	1015.3	1085.1
35°	687.6	695.0	700.6	722.6	748.0	781.7	816.7	859.0	904.6	960.4	1030.3
37.5°	652.3	654.8	663.1	677.4	702.1	733.2	765.6	807.2	854.0	910.7	973.7
40°	630.7	631.9	636.9	650.4	671.8	701.2	732.7	773.9	818.4	872.0	934.5
42.5°	609.5	608.8	613.4	622.9	642.9	669.6	700.7	738.3	782.8	832.3	891.2
45°	576.0	576.0	574.9	582.8	599.2	625.1	651.0	687.1	724.2	772.7	822.3
47.5°	541.1	537.9	538.9	543.0	556.8	578.0	604.2	633.7	666.5	707.6	751.1
50°	518.5	514.0	512.3	516.8	529.2	547.8	572.7	598.6	629.6	665.6	702.9
52.5°	493.7	489.3	486.2	489.3	500.8	518.0	540.6	563.4	591.3	620.5	652.8
55°	455.4	450.4	448.7	449.8	458.2	471.7	490.9	511.8	532.6	556.8	579.4
57.5°	417.7	409.3	407.7	407.2	413.0	425.4	441.4	459.5	474.7	489.3	513.3
60°	392.8	382.7	379.3	378.8	383.3	393.4	408.1	426.1	436.8	446.9	467.8
62.5°	366.2	356.5	349.1	349.9	353.9	363.6	376.5	389.6	396.6	407.7	421.8
65°	325.2	312.8	307.2	305.5	307.8	315.6	325.8	334.2	342.1	346.7	360.1
67.5°	284.2	273.8	265.5	263.4	262.4	267.8	276.1	281.3	286.9	290.8	298.8
70°	255.4	246.3	236.2	232.8	232.2	236.7	244.6	245.2	253.1	254.8	263.2
72.5°	226.9	215.6	208.6	205.3	202.9	206.9	212.1	213.6	217.9	220.9	225.3
75°	182.6	174.1	167.4	162.3	160.6	162.9	162.9	165.7	168.5	170.2	175.3
77.5°	143.7	134.0	126.0	123.1	121.1	119.6	120.8	122.5	121.2	124.1	125.2
80°	116.7	106.6	100.4	99.2	95.8	93.0	92.5	94.1	91.9	93.0	96.4
82.5°	90.1	83.6	76.9	75.7	71.5	70.0	69.5	68.4	68.4	68.2	68.9
85°	53.6	49.6	45.1	42.2	40.6	37.7	37.7	36.6	35.5	34.4	35.0
87.5°	24.6	23.6	21.0	19.5	18.3	16.3	16.1	14.4	13.6	12.9	12.1
90°	14.8	14.0	12.9	11.7	10.6	9.5	8.2	6.6	5.1	3.5	1.9
92.5°	14.3	13.5	12.4	11.3	10.1	9.0	8.4	8.3	8.2	8.2	8.1
95°	14.8	14.0	13.9	13.8	13.6	13.5	15.8	20.6	25.4	30.2	35.1
97.5°	16.9	16.8	32.6	48.4	64.2	80.1	86.5	83.5	80.5	77.5	74.4
100°	25.6	28.0	47.6	67.2	86.7	106.2	114.7	112.2	109.7	107.1	104.5
102.5°	109.2	135.2	137.7	140.2	142.8	145.4	145.7	143.8	141.9	140.1	138.2
105°	200.2	198.9	198.2	197.5	196.7	196.1	195.3	194.4	193.6	192.7	191.8
107.5°	248.6	248.0	247.0	246.1	245.1	244.1	243.4	243.0	242.6	242.1	241.7
110°	281.4	281.1	280.3	279.4	278.6	277.7	277.1	276.6	276.2	275.8	275.4



TEST NUMBER: P332643-930

CATALOG NUMBER: S124DIP-S1020D810U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	313.2	313.2	312.8	312.4	312.1	311.7	311.1	310.3	309.6	308.8	308.0
115°	359.8	359.5	359.7	359.8	360.0	360.1	360.0	359.5	359.1	358.7	358.2
117.5°	407.4	407.5	407.2	406.8	406.5	406.3	405.8	405.2	404.6	404.1	403.5
120°	436.3	436.0	436.2	436.3	436.4	436.6	436.3	435.9	435.3	434.7	434.1
122.5°	465.3	465.1	464.9	464.7	464.5	464.3	464.1	463.7	463.3	463.0	462.7
125°	505.3	504.9	505.2	505.5	505.7	506.0	505.9	505.3	504.8	504.2	503.6
127.5°	545.8	545.9	545.3	544.6	544.0	543.3	542.9	542.8	542.7	542.5	542.3
130°	570.1	569.9	569.5	569.1	568.6	568.2	567.9	567.8	567.6	567.5	567.4
132.5°	594.0	593.9	593.3	592.8	592.2	591.7	591.3	591.1	590.8	590.5	590.3
135°	626.9	626.6	626.1	625.5	624.9	624.4	624.2	624.3	624.4	624.6	624.8
137.5°	658.6	658.3	657.6	657.0	656.4	655.7	655.4	655.3	655.3	655.3	655.2
140°	678.1	677.6	677.4	677.1	676.8	676.5	676.2	676.0	675.6	675.4	675.1
142.5°	696.3	696.0	695.9	695.7	695.5	695.3	695.0	694.5	694.0	693.4	692.9
145°	722.4	722.3	722.3	722.3	722.3	722.3	722.0	721.6	721.2	720.8	720.3
147.5°	745.2	745.1	745.2	745.3	745.5	745.7	745.3	744.5	743.7	743.0	742.2
150°	759.9	759.9	760.0	760.2	760.3	760.4	760.2	759.7	759.1	758.6	758.0
152.5°	772.3	772.1	772.3	772.7	772.9	773.1	773.1	772.6	772.1	771.7	771.2
155°	789.1	788.6	789.0	789.4	789.9	790.3	790.4	790.3	790.1	789.9	789.9
157.5°	803.7	803.0	803.5	804.0	804.4	804.9	805.2	805.3	805.4	805.4	805.5
160°	813.0	812.1	812.3	812.4	812.6	812.7	813.0	813.4	813.8	814.2	814.7
162.5°	820.7	819.8	819.9	820.1	820.2	820.4	820.7	821.3	821.7	822.3	822.9
165°	831.1	830.0	830.0	830.0	830.0	830.0	830.4	831.0	831.8	832.5	833.2
167.5°	838.9	837.6	837.7	837.8	837.9	838.0	838.4	839.1	839.8	840.6	841.3
170°	843.8	842.8	842.6	842.4	842.3	842.2	842.5	843.3	844.2	845.1	846.0
172.5°	846.9	845.8	845.6	845.5	845.4	845.2	845.6	846.4	847.3	848.2	849.0
175°	850.4	849.1	849.0	848.8	848.7	848.6	848.9	849.8	850.6	851.4	852.3
177.5°	852.2	851.3	851.1	850.8	850.6	850.4	850.7	851.4	852.2	853.0	853.9
180°	852.3	852.3	852.3	852.3	852.3	852.3	852.3	852.3	852.3	852.3	852.3



TEST NUMBER: P332643-930
 CATALOG NUMBER: S124DIP-S1020D810U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6
2.5°	1369.6	1374.1	1380.0	1389.9	1393.5	1398.0	1404.4	1403.9	1405.7	1412.4	1426.9
5°	1374.7	1392.1	1409.1	1429.4	1450.7	1464.8	1484.0	1495.8	1507.7	1522.9	1548.8
7.5°	1376.7	1404.4	1435.4	1471.0	1502.8	1539.3	1567.7	1594.6	1618.9	1651.0	1681.9
10°	1373.5	1410.7	1450.7	1495.8	1543.8	1584.4	1621.0	1662.7	1698.2	1737.1	1772.1
12.5°	1367.7	1412.6	1466.1	1516.6	1572.6	1632.6	1678.2	1720.4	1767.7	1812.4	1866.3
15°	1354.4	1415.8	1478.4	1544.9	1619.8	1689.1	1755.1	1809.8	1860.5	1927.6	1998.1
17.5°	1337.5	1403.8	1482.6	1563.2	1641.5	1720.8	1802.4	1884.6	1948.6	2031.9	2087.0
20°	1321.7	1398.3	1479.5	1575.3	1653.7	1752.3	1833.4	1912.9	2000.8	2083.7	2149.6
22.5°	1299.6	1383.5	1469.6	1565.0	1668.1	1766.8	1860.5	1946.8	2034.7	2124.8	2204.7
25°	1271.5	1347.6	1449.6	1557.9	1660.4	1767.5	1875.2	1983.4	2078.0	2173.3	2247.7
27.5°	1223.8	1319.8	1414.8	1526.5	1640.5	1761.6	1876.7	1990.1	2089.2	2167.6	2213.7
30°	1199.4	1282.8	1385.9	1498.1	1621.5	1751.8	1871.8	1982.8	2075.3	2137.8	2156.4
32.5°	1163.4	1249.4	1350.3	1466.6	1597.2	1731.0	1856.0	1960.7	2037.8	2070.6	2048.2
35°	1109.8	1187.6	1289.6	1408.5	1544.3	1686.9	1810.4	1898.8	1938.3	1907.3	1830.1
37.5°	1045.5	1122.6	1225.1	1341.9	1482.5	1627.4	1739.0	1802.7	1789.6	1712.5	1597.4
40°	1000.5	1072.6	1170.1	1296.3	1433.3	1578.7	1676.7	1711.2	1675.1	1564.6	1442.3
42.5°	950.4	1020.8	1118.7	1240.4	1385.5	1519.6	1605.1	1607.9	1547.4	1415.4	1292.6
45°	874.2	941.3	1033.7	1160.5	1294.6	1420.9	1477.2	1449.6	1338.1	1210.6	1087.2
47.5°	799.0	857.1	948.3	1068.6	1196.0	1302.3	1330.2	1280.5	1161.6	1038.0	923.6
50°	744.0	802.6	888.3	1003.2	1126.1	1218.0	1231.5	1165.6	1048.9	924.3	834.7
52.5°	691.2	749.4	831.9	938.3	1050.8	1133.7	1134.1	1057.8	941.6	830.5	747.2
55°	613.8	666.2	740.6	835.8	936.2	1001.0	985.2	906.3	805.4	709.1	636.3
57.5°	539.2	584.8	653.4	732.8	821.2	874.7	848.5	772.5	682.4	600.7	545.6
60°	490.9	534.3	593.0	667.9	742.3	784.0	759.2	690.4	607.6	541.6	493.7
62.5°	444.0	480.6	537.0	602.1	671.1	702.0	679.9	612.0	540.4	480.8	441.9
65°	377.6	407.5	452.6	508.4	558.6	585.1	566.5	503.3	448.7	405.8	374.8
67.5°	315.6	339.0	373.1	417.8	460.5	474.8	457.9	413.9	367.6	333.3	311.4
70°	272.8	294.8	323.5	357.9	395.1	410.3	393.4	358.5	320.7	289.1	267.7
72.5°	235.4	252.4	276.6	306.1	335.2	350.3	338.8	305.2	273.4	249.9	231.6
75°	179.2	193.9	210.8	231.6	254.2	264.3	254.2	231.1	209.1	191.6	178.6
77.5°	130.3	138.2	151.2	166.8	180.9	188.7	179.9	164.2	150.8	138.8	132.5
80°	99.2	104.8	113.8	126.3	135.8	143.2	137.5	124.6	113.8	106.0	103.1
82.5°	72.2	76.0	81.9	91.1	97.5	101.3	98.7	89.4	85.0	78.0	75.2
85°	35.5	37.7	41.7	44.5	50.1	50.7	51.3	47.4	43.4	41.7	39.5
87.5°	12.9	13.6	15.3	17.0	19.0	19.7	19.5	19.7	18.1	17.9	16.2
90°	3.5	5.1	6.6	8.2	9.5	10.6	11.7	12.9	14.0	14.8	15.7
92.5°	8.2	8.2	8.3	8.4	9.0	10.1	11.3	12.4	13.5	14.3	15.2
95°	30.2	25.4	20.6	15.8	13.5	13.6	13.8	13.9	14.0	14.8	15.7
97.5°	77.5	80.5	83.5	86.5	80.1	64.2	48.4	32.6	16.8	16.9	17.0
100°	107.1	109.7	112.2	114.7	106.2	86.7	67.2	47.6	28.0	25.6	23.2
102.5°	140.1	141.9	143.8	145.7	145.4	142.8	140.2	137.7	135.2	109.2	83.2
105°	192.7	193.6	194.4	195.3	196.1	196.7	197.5	198.2	198.9	200.2	201.5
107.5°	242.1	242.6	243.0	243.4	244.1	245.1	246.1	247.0	248.0	248.6	249.2
110°	275.8	276.2	276.6	277.1	277.7	278.6	279.4	280.3	281.1	281.4	281.7



TEST NUMBER: P332643-930

CATALOG NUMBER: S124DIP-S1020D810U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	308.8	309.6	310.3	311.1	311.7	312.1	312.4	312.8	313.2	313.2	313.2
115°	358.7	359.1	359.5	360.0	360.1	360.0	359.8	359.7	359.5	359.8	360.1
117.5°	404.1	404.6	405.2	405.8	406.3	406.5	406.8	407.2	407.5	407.4	407.3
120°	434.7	435.3	435.9	436.3	436.6	436.4	436.3	436.2	436.0	436.3	436.6
122.5°	463.0	463.3	463.7	464.1	464.3	464.5	464.7	464.9	465.1	465.3	465.5
125°	504.2	504.8	505.3	505.9	506.0	505.7	505.5	505.2	504.9	505.3	505.7
127.5°	542.5	542.7	542.8	542.9	543.3	544.0	544.6	545.3	545.9	545.8	545.8
130°	567.5	567.6	567.8	567.9	568.2	568.6	569.1	569.5	569.9	570.1	570.2
132.5°	590.5	590.8	591.1	591.3	591.7	592.2	592.8	593.3	593.9	594.0	594.2
135°	624.6	624.4	624.3	624.2	624.4	624.9	625.5	626.1	626.6	626.9	627.2
137.5°	655.3	655.3	655.3	655.4	655.7	656.4	657.0	657.6	658.3	658.6	658.8
140°	675.4	675.6	676.0	676.2	676.5	676.8	677.1	677.4	677.6	678.1	678.5
142.5°	693.4	694.0	694.5	695.0	695.3	695.5	695.7	695.9	696.0	696.3	696.6
145°	720.8	721.2	721.6	722.0	722.3	722.3	722.3	722.3	722.3	722.4	722.5
147.5°	743.0	743.7	744.5	745.3	745.7	745.5	745.3	745.2	745.1	745.2	745.3
150°	758.6	759.1	759.7	760.2	760.4	760.3	760.2	760.0	759.9	759.9	759.9
152.5°	771.7	772.1	772.6	773.1	773.1	772.9	772.7	772.3	772.1	772.3	772.6
155°	789.9	790.1	790.3	790.4	790.3	789.9	789.4	789.0	788.6	789.1	789.7
157.5°	805.4	805.4	805.3	805.2	804.9	804.4	804.0	803.5	803.0	803.7	804.5
160°	814.2	813.8	813.4	813.0	812.7	812.6	812.4	812.3	812.1	813.0	813.8
162.5°	822.3	821.7	821.3	820.7	820.4	820.2	820.1	819.9	819.8	820.7	821.5
165°	832.5	831.8	831.0	830.4	830.0	830.0	830.0	830.0	830.0	831.1	832.3
167.5°	840.6	839.8	839.1	838.4	838.0	837.9	837.8	837.7	837.6	838.9	840.2
170°	845.1	844.2	843.3	842.5	842.2	842.3	842.4	842.6	842.8	843.8	845.0
172.5°	848.2	847.3	846.4	845.6	845.2	845.4	845.5	845.6	845.8	846.9	848.1
175°	851.4	850.6	849.8	848.9	848.6	848.7	848.8	849.0	849.1	850.4	851.7
177.5°	853.0	852.2	851.4	850.7	850.4	850.6	850.8	851.1	851.3	852.2	853.1
180°	852.3	852.3	852.3	852.3	852.3	852.3	852.3	852.3	852.3	852.3	852.3



TEST NUMBER: P332643-930
 CATALOG NUMBER: S124DIP-S1020D810U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6	1360.6
2.5°	1434.1	1435.0	1439.0	1442.2	1443.1	1447.6	1448.1
5°	1560.1	1569.7	1588.3	1590.0	1592.8	1607.4	1596.2
7.5°	1707.8	1732.1	1748.3	1762.7	1767.9	1774.3	1772.9
10°	1802.5	1838.5	1856.6	1885.3	1886.4	1893.8	1889.3
12.5°	1897.6	1939.5	1972.5	1977.8	2001.9	2005.6	2011.9
15°	2032.4	2077.0	2122.6	2138.9	2172.2	2180.1	2192.5
17.5°	2159.2	2204.7	2236.7	2278.9	2292.6	2310.9	2298.4
20°	2228.5	2278.2	2318.7	2352.0	2366.1	2376.2	2375.1
22.5°	2270.5	2320.5	2353.4	2378.6	2391.8	2396.1	2395.8
25°	2296.8	2325.5	2335.7	2345.2	2330.6	2325.5	2327.8
27.5°	2223.7	2216.3	2189.8	2155.1	2119.0	2090.3	2074.8
30°	2123.2	2079.2	2039.1	1969.3	1933.2	1911.8	1892.6
32.5°	1980.7	1911.0	1834.0	1770.0	1729.0	1697.2	1692.5
35°	1736.5	1631.7	1537.6	1459.2	1418.6	1384.2	1376.4
37.5°	1476.3	1367.4	1282.7	1213.7	1170.1	1145.8	1123.2
40°	1303.7	1210.1	1126.7	1068.0	1034.8	1017.3	1003.2
42.5°	1170.6	1085.2	1002.2	957.6	927.5	916.8	908.6
45°	986.9	907.4	849.9	816.1	798.7	780.6	772.2
47.5°	839.8	775.1	737.2	708.5	689.7	679.1	673.6
50°	756.4	703.4	669.6	647.6	630.7	622.2	617.8
52.5°	682.4	639.0	610.5	593.0	581.6	575.4	573.6
55°	587.8	554.6	536.5	521.4	512.9	507.3	505.0
57.5°	510.9	485.4	470.8	458.2	454.9	450.2	448.7
60°	460.5	440.8	428.4	419.9	417.1	411.5	412.5
62.5°	415.8	399.7	389.1	384.3	380.6	375.9	377.4
65°	351.7	339.9	334.2	329.7	325.2	322.4	324.7
67.5°	295.1	287.0	279.3	276.7	274.5	274.0	271.7
70°	258.1	251.4	244.6	243.0	243.0	240.7	240.1
72.5°	222.5	217.5	213.0	211.8	210.0	210.9	208.6
75°	171.9	168.0	166.2	164.6	164.0	164.0	162.3
77.5°	127.0	124.1	121.4	121.4	119.4	118.6	118.4
80°	96.4	95.2	93.0	93.0	91.9	92.5	91.3
82.5°	72.5	70.9	70.4	69.5	68.0	68.1	66.9
85°	38.9	37.2	36.6	35.0	33.8	35.0	33.8
87.5°	16.9	16.6	16.2	15.4	15.0	15.0	13.8
90°	16.6	17.4	18.0	18.3	18.6	18.8	19.2
92.5°	16.1	16.9	17.4	17.4	17.4	17.5	17.6
95°	16.6	17.4	17.9	18.1	18.2	18.3	18.5
97.5°	17.1	17.2	17.3	17.4	17.5	17.7	17.9
100°	20.8	18.4	17.3	17.4	17.5	17.7	17.9
102.5°	57.2	31.2	18.3	18.3	18.3	18.3	18.3
105°	202.7	204.0	202.1	197.0	191.8	186.8	181.6
107.5°	249.8	250.5	251.0	251.6	252.1	252.7	253.2
110°	282.0	282.3	282.6	283.1	283.5	283.9	284.3



TEST NUMBER: P332643-930

CATALOG NUMBER: S124DIP-S1020D810U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	313.1	313.0	313.2	313.8	314.4	314.9	315.4
115°	360.4	360.7	360.9	360.9	360.9	360.9	360.9
117.5°	407.3	407.2	407.2	407.2	407.1	407.0	407.0
120°	436.9	437.2	437.2	436.9	436.6	436.3	436.0
122.5°	465.6	465.8	465.7	465.5	465.1	464.9	464.6
125°	506.1	506.5	506.9	507.0	507.1	507.3	507.4
127.5°	545.7	545.6	545.5	545.4	545.3	545.2	545.0
130°	570.3	570.5	570.5	570.5	570.5	570.5	570.5
132.5°	594.3	594.4	594.4	594.4	594.2	594.1	594.0
135°	627.5	627.8	628.0	628.4	628.6	628.9	629.2
137.5°	659.2	659.5	659.6	659.5	659.4	659.3	659.3
140°	678.9	679.3	679.6	679.8	679.9	680.0	680.2
142.5°	696.9	697.2	697.4	697.4	697.5	697.5	697.5
145°	722.7	722.8	723.0	723.3	723.6	723.9	724.1
147.5°	745.4	745.5	745.7	745.8	745.9	746.1	746.2
150°	759.9	759.9	759.9	760.1	760.2	760.3	760.5
152.5°	772.8	773.0	773.1	773.0	772.9	772.8	772.7
155°	790.3	790.8	790.9	790.4	790.0	789.6	789.2
157.5°	805.2	805.9	805.9	805.2	804.5	803.7	803.0
160°	814.7	815.5	815.5	814.7	813.8	813.0	812.1
162.5°	822.3	823.2	823.1	822.1	821.2	820.3	819.3
165°	833.4	834.5	834.5	833.2	831.9	830.6	829.3
167.5°	841.4	842.6	842.5	841.1	839.7	838.3	836.9
170°	846.1	847.3	847.1	845.7	844.3	842.9	841.5
172.5°	849.2	850.4	850.1	848.6	847.1	845.5	844.0
175°	853.0	854.2	854.0	852.3	850.6	848.9	847.2
177.5°	854.0	854.9	854.7	853.3	852.0	850.6	849.2
180°	852.3	852.3	852.3	852.3	852.3	852.3	852.3

(END OF REPORT)