

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332253-940

Luminaire Tested: **S123RDIP-S340D805U940-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332253-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S340D805U940-4F0-1E-UDD-A1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 805 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3669.9 lumens
Efficiency: N/A
Efficacy: 117.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332253-940

CATALOG NUMBER: S123RDIP-S340D805U940-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P332253-940

CATALOG NUMBER: S123RDIP-S340D805U940-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	41	41	41	33
1	94	90	87	83	85	82	78	76	65	63	61	50	49	48	36	36	35	29
2	86	79	73	69	78	72	67	63	58	54	51	45	42	40	32	31	30	25
3	79	70	63	58	71	63	58	53	51	47	44	40	37	35	29	27	26	21
4	72	62	55	49	65	56	50	45	46	41	37	36	32	30	26	24	23	19
5	66	55	48	42	60	50	44	39	41	36	32	32	29	26	24	22	20	16
6	61	50	42	36	55	45	39	34	37	32	28	29	26	23	22	19	18	15
7	57	45	37	32	51	41	34	30	33	28	25	26	23	20	20	18	16	13
8	52	41	33	28	47	37	31	26	30	26	22	24	21	18	18	16	14	12
9	49	37	30	25	44	34	28	23	28	23	20	22	19	16	17	15	13	11
10	45	34	27	22	41	31	25	21	26	21	18	21	17	15	16	13	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5224	5224	5224	5224
5°	6227	5246	4620	5246
10°	7774	5216	4173	5216
15°	9126	5162	3806	5162
20°	10186	5082	3494	5082
25°	10023	4999	3301	4999
30°	7204	4922	3104	4922
35°	4809	4820	2975	4820
40°	3544	4700	2843	4700
45°	2973	4488	2714	4488
50°	2624	4210	2532	4210
55°	2301	3890	2284	3890
60°	2047	3587	2093	3587
65°	1798	3260	1946	3260
70°	1413	2968	1778	2968
75°	1243	2591	1626	2591
80°	1085	2201	1599	2201
85°	865	1778	1692	1778



TEST NUMBER: P332253-940

CATALOG NUMBER: S123RDIP-S340D805U940-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.7	1.3
10°-20°	149.1	4.1
20°-30°	234.2	6.4
30°-40°	244.4	6.7
40°-50°	209.1	5.7
50°-60°	159.4	4.3
60°-70°	102.2	2.8
70°-80°	49.1	1.3
80°-90°	15.6	0.4
90°-100°	57.8	1.6
100°-110°	173.1	4.7
110°-120°	294.3	8.0
120°-130°	387.1	10.5
130°-140°	435.1	11.9
140°-150°	427.7	11.7
150°-160°	360.1	9.8
160°-170°	239.7	6.5
170°-180°	83.9	2.3
0°-30°	431.1	11.7
0°-40°	675.4	18.4
0°-60°	1044.0	28.4
0°-90°	1210.9	33.0
90°-120°	525.2	14.3
90°-150°	1775.2	48.4
90°-180°	2459.0	67.0
0°-180°	3669.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	485	485	485	485	485	
5°	576	486	428	486	576	59
15°	819	463	342	463	819	232
25°	844	421	278	421	844	363
35°	366	367	226	367	366	240
45°	195	295	178	295	195	154
55°	123	207	122	207	123	111
65°	71	128	76	128	71	69
75°	30	62	39	62	30	32
85°	7	14	14	14	7	9
90°	21	1	21	1	21	10
95°	54	41	54	41	54	56
105°	166	157	166	157	166	176
115°	297	296	297	296	297	294
125°	429	434	429	434	429	383
135°	562	563	562	563	562	432
145°	682	682	682	682	682	426
155°	780	782	780	782	780	359
165°	848	851	848	851	848	239
175°	882	885	882	885	882	84
180°	888	888	888	888	888	



TEST NUMBER: P332253-940

CATALOG NUMBER: S123RDIP-S340D805U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3
2.5°	516.9	517.5	515.4	515.1	512.6	511.9	511.9	508.4	506.2	503.5	501.8
5°	576.3	579.6	577.9	574.3	568.0	566.5	562.6	556.3	549.3	540.6	536.5
7.5°	650.5	655.1	653.3	647.6	641.0	635.7	624.6	614.2	599.8	587.0	576.1
10°	711.3	706.6	702.8	697.2	691.2	681.4	669.8	653.8	635.3	620.7	604.6
12.5°	756.9	756.1	751.4	745.6	737.1	727.8	713.5	694.0	672.5	651.5	632.9
15°	818.9	820.2	817.1	811.1	799.0	782.6	761.0	752.9	722.1	699.3	676.5
17.5°	861.9	861.7	861.2	852.9	840.6	828.9	808.9	787.6	759.7	727.5	696.8
20°	889.2	887.1	887.5	878.2	869.1	855.5	836.0	805.0	782.2	745.0	713.2
22.5°	888.5	888.1	889.7	886.4	879.9	869.5	854.1	828.0	798.8	761.3	725.5
25°	843.9	842.2	851.9	854.7	865.3	867.2	862.6	848.3	820.6	781.9	737.7
27.5°	706.2	705.3	723.4	746.2	774.9	797.3	818.9	829.3	820.6	792.9	748.6
30°	579.6	599.1	608.3	641.1	677.7	721.3	759.6	795.9	804.9	792.7	756.4
32.5°	481.3	498.3	506.0	534.0	568.2	619.3	676.6	728.1	764.5	773.6	751.8
35°	366.0	366.2	383.7	396.2	427.8	480.3	536.0	604.9	673.5	725.5	730.8
37.5°	292.1	293.1	303.7	316.1	339.8	367.6	416.6	473.9	553.1	632.8	679.7
40°	252.2	254.0	262.0	274.2	291.2	312.3	350.4	404.5	470.6	559.3	631.8
42.5°	226.6	229.6	233.7	243.2	253.7	273.4	304.3	346.0	406.1	490.0	573.6
45°	195.3	197.0	200.1	204.5	214.0	227.7	248.4	276.5	326.4	393.9	477.6
47.5°	172.3	171.4	174.7	178.2	184.6	193.9	207.9	230.7	266.3	320.5	391.5
50°	156.7	156.4	158.7	161.4	167.5	174.3	185.7	203.0	231.2	276.1	341.2
52.5°	142.0	142.8	144.5	147.8	152.1	157.7	167.9	180.4	204.6	243.3	297.6
55°	122.6	123.2	125.5	127.3	130.5	136.1	142.5	152.9	169.5	196.5	241.2
57.5°	106.1	105.8	108.0	108.5	112.0	116.5	121.5	129.7	141.7	161.8	191.8
60°	95.1	94.5	96.4	97.8	99.7	103.4	107.6	115.5	125.1	139.8	165.6
62.5°	85.2	84.9	86.2	87.7	89.3	92.6	96.1	102.2	109.8	122.2	142.7
65°	70.6	71.2	71.9	72.5	73.3	75.4	78.7	82.9	88.1	96.8	111.6
67.5°	55.6	56.2	56.4	57.6	59.4	60.7	62.8	66.4	70.1	77.4	85.8
70°	44.9	44.7	44.9	45.5	47.8	50.0	52.8	55.5	57.8	63.0	70.0
72.5°	38.5	38.2	38.7	38.9	39.9	40.6	42.3	44.9	47.8	51.3	56.4
75°	29.9	29.9	29.9	29.9	30.8	31.1	31.7	32.4	33.4	35.1	38.9
77.5°	22.1	22.1	22.5	22.6	22.8	23.1	23.5	24.1	24.4	25.3	26.9
80°	17.5	17.7	17.5	17.7	17.7	18.1	18.3	18.9	19.1	20.2	20.8
82.5°	13.1	13.0	13.1	13.4	13.4	13.7	13.8	14.3	14.3	14.8	15.4
85°	7.0	6.7	7.0	6.9	7.3	6.9	7.0	7.5	7.5	7.7	8.6
87.5°	5.9	6.2	5.7	5.8	5.8	5.8	5.7	5.6	5.8	5.5	5.3
90°	21.0	20.6	20.3	20.0	19.7	19.2	18.5	18.0	17.4	16.8	14.7
92.5°	28.2	28.4	28.5	28.7	28.9	28.7	28.3	27.7	27.3	26.8	25.6
95°	54.4	54.4	54.4	54.4	54.4	54.0	53.4	52.8	52.3	51.6	50.4
97.5°	83.6	83.7	83.8	83.8	83.9	83.6	82.8	82.1	81.4	80.7	79.8
100°	105.9	105.7	105.3	105.0	104.8	104.3	103.9	103.4	103.0	102.5	101.7
102.5°	128.9	128.9	128.9	129.0	129.1	128.9	128.4	128.0	127.5	127.1	126.0
105°	165.9	165.6	165.3	165.0	164.7	164.5	164.5	164.5	164.5	164.5	163.2
107.5°	204.6	204.7	204.9	205.1	205.3	205.2	204.6	204.1	203.7	203.1	202.6
110°	230.8	231.0	231.4	231.7	232.0	231.8	231.2	230.6	230.0	229.3	229.1



TEST NUMBER: P332253-940

CATALOG NUMBER: S123RDIP-S340D805U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	258.7	258.7	258.8	258.9	258.9	258.6	257.8	257.1	256.4	255.6	255.6
115°	297.0	297.1	297.3	297.5	297.7	297.7	297.5	297.3	297.1	297.0	297.3
117.5°	335.9	336.4	336.8	337.2	337.6	337.9	337.9	338.0	338.0	338.0	338.4
120°	363.2	363.6	363.8	364.2	364.4	364.7	364.9	365.0	365.2	365.3	366.1
122.5°	389.4	389.9	390.3	390.7	391.2	391.6	392.0	392.4	392.8	393.2	393.6
125°	428.7	429.4	430.0	430.6	431.2	431.9	432.5	433.1	433.7	434.4	434.6
127.5°	468.0	468.7	469.4	470.1	470.8	471.6	472.4	473.3	474.2	475.0	475.4
130°	493.6	494.7	495.8	496.9	497.9	498.8	499.4	500.1	500.6	501.2	501.8
132.5°	520.4	521.2	522.0	522.9	523.7	524.5	525.2	526.0	526.7	527.4	527.8
135°	562.0	562.2	562.6	562.8	563.2	563.7	564.3	564.9	565.5	566.1	566.2
137.5°	598.6	599.2	599.8	600.4	600.9	601.5	602.3	602.9	603.5	604.1	603.8
140°	622.6	623.7	624.7	625.8	627.0	627.5	627.7	627.9	628.0	628.1	628.0
142.5°	647.1	647.9	648.8	649.6	650.5	650.9	651.1	651.3	651.4	651.6	651.3
145°	682.5	683.1	683.8	684.4	685.0	685.4	685.5	685.7	685.9	686.0	685.5
147.5°	714.1	715.0	715.9	716.8	717.7	718.3	718.3	718.3	718.3	718.3	717.8
150°	734.1	735.0	736.0	736.9	737.9	738.3	738.3	738.3	738.3	738.3	738.0
152.5°	753.7	754.5	755.3	756.1	756.9	757.2	756.9	756.6	756.4	756.2	756.0
155°	780.2	781.2	782.3	783.4	784.4	784.7	784.1	783.5	782.8	782.2	782.1
157.5°	804.2	805.1	806.0	806.9	807.7	807.8	807.2	806.6	805.9	805.2	805.1
160°	819.8	820.5	821.1	821.7	822.3	822.2	821.5	820.7	819.9	819.2	819.2
162.5°	831.6	832.6	833.6	834.6	835.5	835.7	834.9	834.1	833.3	832.6	832.4
165°	848.5	849.5	850.6	851.8	852.8	852.9	851.9	851.0	850.1	849.2	849.2
167.5°	862.8	863.8	864.8	865.7	866.7	866.7	865.7	864.8	863.8	862.8	862.7
170°	870.0	871.2	872.3	873.3	874.4	874.4	873.3	872.3	871.2	870.0	870.0
172.5°	875.7	876.7	877.8	878.9	880.0	880.0	879.1	878.2	877.2	876.2	876.2
175°	881.9	883.0	884.1	885.2	886.3	886.4	885.4	884.5	883.6	882.6	882.6
177.5°	885.3	886.2	887.0	887.9	888.8	888.8	888.1	887.3	886.5	885.8	885.8
180°	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5



TEST NUMBER: P332253-940

CATALOG NUMBER: S123RDIP-S340D805U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3
2.5°	501.1	500.6	498.3	495.6	492.1	489.8	487.9	487.0	483.9	480.3	477.9
5°	532.1	525.8	519.2	511.0	503.5	495.9	491.2	485.5	478.7	471.0	465.6
7.5°	565.2	552.9	539.8	526.2	512.8	500.8	490.1	481.0	470.1	459.1	451.4
10°	590.7	572.7	554.3	535.4	518.2	501.9	489.5	477.2	464.1	451.5	441.8
12.5°	613.8	590.2	568.9	545.6	523.6	504.3	486.3	471.9	456.1	442.6	431.8
15°	643.0	618.8	593.2	557.8	528.5	504.0	482.1	463.2	444.2	427.6	417.0
17.5°	670.3	634.1	599.4	570.0	531.9	501.3	474.7	452.1	431.1	413.5	400.4
20°	681.6	646.5	608.9	571.3	534.0	499.6	468.7	443.7	422.0	402.0	389.9
22.5°	688.4	648.7	609.0	568.6	529.0	493.3	462.7	435.2	411.6	392.7	377.8
25°	696.3	649.0	605.4	565.5	525.0	486.3	450.0	420.9	395.4	375.2	359.4
27.5°	701.6	645.9	594.3	550.0	508.9	470.5	437.1	406.3	380.3	359.0	342.1
30°	702.6	643.4	585.9	537.9	496.1	460.7	425.4	396.0	368.5	345.9	330.1
32.5°	703.9	637.2	574.4	523.4	480.6	445.7	413.7	385.5	357.4	335.1	319.0
35°	698.5	633.8	557.0	498.4	455.6	421.7	392.9	366.8	339.3	317.6	301.2
37.5°	674.8	620.4	539.0	470.2	425.4	394.1	370.6	347.9	322.6	299.3	283.8
40°	651.1	607.1	525.0	453.1	406.4	374.2	352.9	334.5	310.0	288.1	271.5
42.5°	615.7	588.9	511.7	435.2	384.8	353.7	335.8	318.5	297.0	274.8	259.2
45°	550.7	554.3	484.5	406.5	354.8	323.7	306.8	294.8	275.7	257.4	241.4
47.5°	469.3	502.3	452.5	376.1	323.3	294.1	279.4	268.9	255.9	238.0	223.4
50°	416.2	463.2	427.0	355.7	303.5	274.5	259.9	251.4	240.1	226.0	212.1
52.5°	367.1	417.8	396.0	332.9	282.0	255.5	241.3	234.3	225.3	212.0	199.5
55°	299.3	350.7	345.7	298.5	249.9	226.0	215.3	207.3	201.3	191.4	181.4
57.5°	242.2	290.8	293.4	260.3	221.6	198.0	188.7	182.7	178.8	171.3	162.0
60°	206.1	250.7	259.5	234.5	201.3	180.6	171.4	166.6	163.5	157.5	150.4
62.5°	176.2	214.2	224.1	206.2	181.9	162.4	155.2	150.7	148.6	143.4	137.1
65°	134.8	166.4	175.9	166.0	153.3	137.8	131.9	128.0	126.1	123.2	118.6
67.5°	101.4	124.4	134.9	127.9	123.2	113.4	109.8	107.6	105.9	104.0	100.1
70°	81.4	98.4	109.2	107.5	103.7	98.4	95.8	94.3	92.6	91.0	87.7
72.5°	65.5	77.2	87.3	88.3	85.2	84.2	81.8	81.1	80.2	78.2	76.3
75°	43.4	51.5	58.6	61.3	62.5	63.6	62.5	62.3	62.2	60.5	59.4
77.5°	28.4	32.8	37.3	41.9	43.9	45.2	45.6	46.4	45.7	44.9	44.4
80°	21.8	22.8	25.9	29.9	33.0	34.2	35.1	35.5	35.3	35.1	34.2
82.5°	15.9	16.7	18.2	21.0	23.5	25.6	26.1	26.0	26.5	26.7	25.9
85°	8.6	8.7	9.2	9.5	11.0	13.3	13.9	14.4	14.7	14.7	13.5
87.5°	5.2	4.6	4.5	4.2	4.4	4.3	4.9	5.4	6.0	5.6	5.9
90°	12.7	10.7	8.6	6.9	5.4	3.8	2.2	0.7	2.2	3.8	5.4
92.5°	24.5	23.4	22.2	21.0	20.1	19.0	17.9	16.9	17.9	19.0	20.1
95°	49.1	47.9	46.6	45.5	44.4	43.3	42.2	41.1	42.2	43.3	44.4
97.5°	78.9	78.0	77.1	76.3	75.4	74.6	73.8	73.0	73.8	74.6	75.4
100°	100.9	100.1	99.4	98.5	97.6	96.7	95.8	94.8	95.8	96.7	97.6
102.5°	125.0	123.9	123.0	122.2	121.6	121.0	120.5	119.9	120.5	121.0	121.6
105°	161.8	160.3	159.0	158.1	157.8	157.5	157.2	156.9	157.2	157.5	157.8
107.5°	202.1	201.5	200.9	200.5	200.4	200.2	200.0	199.8	200.0	200.2	200.4
110°	228.7	228.5	228.1	227.8	227.5	227.2	226.9	226.6	226.9	227.2	227.5



TEST NUMBER: P332253-940

CATALOG NUMBER: S123RDIP-S340D805U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	255.5	255.4	255.3	255.2	255.0	254.9	254.7	254.5	254.7	254.9	255.0
115°	297.7	297.9	298.3	298.2	297.7	297.2	296.8	296.3	296.8	297.2	297.7
117.5°	338.8	339.2	339.6	339.7	339.3	339.0	338.8	338.4	338.8	339.0	339.3
120°	366.8	367.7	368.5	368.4	367.4	366.5	365.5	364.6	365.5	366.5	367.4
122.5°	394.0	394.4	394.8	394.7	394.0	393.3	392.6	392.0	392.6	393.3	394.0
125°	435.0	435.2	435.6	435.5	435.1	434.5	434.1	433.6	434.1	434.5	435.1
127.5°	475.7	476.1	476.4	476.1	475.1	474.1	473.1	472.2	473.1	474.1	475.1
130°	502.2	502.7	503.1	502.7	501.5	500.2	499.0	497.8	499.0	500.2	501.5
132.5°	528.2	528.5	528.9	528.4	527.2	525.9	524.7	523.4	524.7	525.9	527.2
135°	566.4	566.6	566.8	566.3	565.4	564.5	563.6	562.6	563.6	564.5	565.4
137.5°	603.3	603.0	602.5	602.0	601.2	600.4	599.7	598.9	599.7	600.4	601.2
140°	627.9	627.7	627.5	627.1	626.3	625.5	624.7	623.9	624.7	625.5	626.3
142.5°	651.0	650.8	650.5	650.0	649.2	648.4	647.6	646.8	647.6	648.4	649.2
145°	685.1	684.7	684.1	683.8	683.5	683.1	682.9	682.5	682.9	683.1	683.5
147.5°	717.4	716.9	716.5	716.0	715.4	714.9	714.3	713.8	714.3	714.9	715.4
150°	737.7	737.4	737.1	736.7	736.5	736.1	735.8	735.5	735.8	736.1	736.5
152.5°	755.8	755.6	755.5	755.1	754.7	754.2	753.8	753.4	753.8	754.2	754.7
155°	781.9	781.8	781.6	781.5	781.5	781.5	781.5	781.5	781.5	781.5	781.5
157.5°	805.0	804.9	804.8	804.8	804.9	805.1	805.3	805.5	805.3	805.1	804.9
160°	819.2	819.2	819.2	819.3	819.7	819.9	820.3	820.6	820.3	819.9	819.7
162.5°	832.3	832.2	832.1	832.2	832.7	833.1	833.6	833.9	833.6	833.1	832.7
165°	849.2	849.2	849.2	849.4	849.9	850.3	850.8	851.2	850.8	850.3	849.9
167.5°	862.6	862.5	862.4	862.6	863.2	863.8	864.4	865.0	864.4	863.8	863.2
170°	870.0	870.0	870.0	870.4	871.0	871.6	872.3	872.9	872.3	871.6	871.0
172.5°	876.2	876.2	876.2	876.6	877.2	877.8	878.4	879.0	878.4	877.8	877.2
175°	882.6	882.6	882.6	883.0	883.6	884.2	884.8	885.4	884.8	884.2	883.6
177.5°	885.8	885.8	885.8	886.1	886.5	887.1	887.6	888.1	887.6	887.1	886.5
180°	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5



TEST NUMBER: P332253-940

CATALOG NUMBER: S123RDIP-S340D805U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3
2.5°	477.0	474.8	473.3	470.0	467.9	465.6	463.2	464.7	464.5	464.4	464.4
5°	461.0	456.2	451.8	446.2	442.7	438.4	435.1	434.6	435.4	432.6	430.9
7.5°	445.1	438.6	432.4	426.2	419.6	414.4	411.2	409.6	407.5	405.7	403.9
10°	434.0	426.3	420.3	412.6	405.6	399.3	395.4	392.6	391.2	389.8	387.0
12.5°	422.5	415.0	407.3	398.6	391.9	384.7	381.7	378.7	375.9	374.3	370.6
15°	405.7	396.0	387.9	378.7	371.2	364.2	360.1	354.0	353.2	351.1	347.3
17.5°	388.9	378.4	367.1	360.3	352.0	344.6	338.2	336.3	330.3	328.1	324.8
20°	375.6	365.9	357.3	348.4	336.2	329.3	324.3	321.6	316.8	313.9	311.8
22.5°	364.2	354.2	344.4	333.9	323.9	316.1	312.5	308.3	305.7	301.6	299.3
25°	347.8	337.0	325.1	313.9	306.7	300.9	295.0	291.2	287.5	285.6	281.5
27.5°	328.8	317.4	306.4	297.8	288.9	283.2	277.9	274.6	270.1	267.0	264.7
30°	318.3	305.0	295.4	287.8	276.3	270.9	267.0	262.8	259.5	256.2	253.9
32.5°	306.1	294.0	285.0	275.4	266.7	260.7	255.7	252.0	249.1	246.0	243.7
35°	287.1	277.0	267.6	258.1	251.6	245.6	239.5	236.4	233.7	230.8	228.7
37.5°	269.9	260.4	251.5	242.5	234.4	229.5	224.7	222.3	218.6	216.7	214.6
40°	259.3	249.9	240.4	231.7	223.4	219.6	215.3	211.7	208.4	206.9	204.6
42.5°	247.6	238.3	230.2	220.9	214.0	208.9	204.9	201.1	198.6	196.4	195.2
45°	230.4	222.1	214.2	204.8	198.4	194.0	189.5	185.9	183.7	182.2	179.9
47.5°	213.7	205.4	197.3	189.2	183.0	178.0	173.3	170.9	167.9	166.1	164.6
50°	201.5	194.0	185.6	178.1	171.8	166.8	163.1	160.0	157.3	155.0	153.9
52.5°	190.4	182.4	175.0	168.1	161.5	155.9	152.5	149.2	147.1	144.5	143.3
55°	172.0	164.3	158.1	151.2	144.8	140.0	135.9	133.0	130.9	128.0	126.4
57.5°	154.8	147.8	140.4	134.5	127.9	123.9	120.4	116.5	113.9	111.6	109.9
60°	143.1	135.3	128.8	123.2	117.3	112.2	109.1	105.9	103.3	100.9	99.5
62.5°	131.0	124.1	118.0	111.9	106.6	102.0	98.4	95.9	93.5	92.0	90.5
65°	112.4	107.0	100.8	95.8	90.8	87.5	84.5	82.3	80.6	79.5	78.3
67.5°	95.2	90.1	84.6	79.7	76.3	73.8	72.0	70.0	69.1	67.8	67.0
70°	84.2	78.7	73.9	70.2	66.9	65.0	63.8	62.3	61.5	59.8	59.0
72.5°	72.1	68.1	64.6	61.6	58.9	57.2	55.6	53.9	52.5	50.6	49.8
75°	56.7	53.1	50.5	48.4	46.7	44.5	42.2	40.3	39.7	39.1	38.9
77.5°	42.0	39.8	37.8	36.0	34.0	32.4	31.8	31.4	31.3	30.9	30.9
80°	33.0	30.9	29.5	27.5	26.2	26.2	26.2	25.8	25.9	25.9	25.9
82.5°	24.5	22.6	21.8	21.1	20.9	21.0	21.0	21.1	21.0	21.3	21.1
85°	12.7	12.8	13.3	13.1	13.3	13.3	13.7	13.5	13.7	13.3	13.7
87.5°	6.1	6.9	7.5	8.0	8.6	8.8	9.1	9.3	9.5	9.6	9.7
90°	6.9	8.6	10.7	12.7	14.7	16.8	17.4	18.0	18.5	19.2	19.7
92.5°	21.0	22.2	23.4	24.5	25.6	26.8	27.3	27.7	28.3	28.7	28.9
95°	45.5	46.6	47.9	49.1	50.4	51.6	52.3	52.8	53.4	54.0	54.4
97.5°	76.3	77.1	78.0	78.9	79.8	80.7	81.4	82.1	82.8	83.6	83.9
100°	98.5	99.4	100.1	100.9	101.7	102.5	103.0	103.4	103.9	104.3	104.8
102.5°	122.2	123.0	123.9	125.0	126.0	127.1	127.5	128.0	128.4	128.9	129.1
105°	158.1	159.0	160.3	161.8	163.2	164.5	164.5	164.5	164.5	164.5	164.7
107.5°	200.5	200.9	201.5	202.1	202.6	203.1	203.7	204.1	204.6	205.2	205.3
110°	227.8	228.1	228.5	228.7	229.1	229.3	230.0	230.6	231.2	231.8	232.0



TEST NUMBER: P332253-940

CATALOG NUMBER: S123RDIP-S340D805U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	255.2	255.3	255.4	255.5	255.6	255.6	256.4	257.1	257.8	258.6	258.9
115°	298.2	298.3	297.9	297.7	297.3	297.0	297.1	297.3	297.5	297.7	297.7
117.5°	339.7	339.6	339.2	338.8	338.4	338.0	338.0	338.0	337.9	337.9	337.6
120°	368.4	368.5	367.7	366.8	366.1	365.3	365.2	365.0	364.9	364.7	364.4
122.5°	394.7	394.8	394.4	394.0	393.6	393.2	392.8	392.4	392.0	391.6	391.2
125°	435.5	435.6	435.2	435.0	434.6	434.4	433.7	433.1	432.5	431.9	431.2
127.5°	476.1	476.4	476.1	475.7	475.4	475.0	474.2	473.3	472.4	471.6	470.8
130°	502.7	503.1	502.7	502.2	501.8	501.2	500.6	500.1	499.4	498.8	497.9
132.5°	528.4	528.9	528.5	528.2	527.8	527.4	526.7	526.0	525.2	524.5	523.7
135°	566.3	566.8	566.6	566.4	566.2	566.1	565.5	564.9	564.3	563.7	563.2
137.5°	602.0	602.5	603.0	603.3	603.8	604.1	603.5	602.9	602.3	601.5	600.9
140°	627.1	627.5	627.7	627.9	628.0	628.1	628.0	627.9	627.7	627.5	627.0
142.5°	650.0	650.5	650.8	651.0	651.3	651.6	651.4	651.3	651.1	650.9	650.5
145°	683.8	684.1	684.7	685.1	685.5	686.0	685.9	685.7	685.5	685.4	685.0
147.5°	716.0	716.5	716.9	717.4	717.8	718.3	718.3	718.3	718.3	718.3	717.7
150°	736.7	737.1	737.4	737.7	738.0	738.3	738.3	738.3	738.3	738.3	737.9
152.5°	755.1	755.5	755.6	755.8	756.0	756.2	756.4	756.6	756.9	757.2	756.9
155°	781.5	781.6	781.8	781.9	782.1	782.2	782.8	783.5	784.1	784.7	784.4
157.5°	804.8	804.8	804.9	805.0	805.1	805.2	805.9	806.6	807.2	807.8	807.7
160°	819.3	819.2	819.2	819.2	819.2	819.2	819.9	820.7	821.5	822.2	822.3
162.5°	832.2	832.1	832.2	832.3	832.4	832.6	833.3	834.1	834.9	835.7	835.5
165°	849.4	849.2	849.2	849.2	849.2	849.2	850.1	851.0	851.9	852.9	852.8
167.5°	862.6	862.4	862.5	862.6	862.7	862.8	863.8	864.8	865.7	866.7	866.7
170°	870.4	870.0	870.0	870.0	870.0	870.0	871.2	872.3	873.3	874.4	874.4
172.5°	876.6	876.2	876.2	876.2	876.2	876.2	877.2	878.2	879.1	880.0	880.0
175°	883.0	882.6	882.6	882.6	882.6	882.6	883.6	884.5	885.4	886.4	886.3
177.5°	886.1	885.8	885.8	885.8	885.8	885.8	886.5	887.3	888.1	888.8	888.8
180°	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5



TEST NUMBER: P332253-940

CATALOG NUMBER: S123RDIP-S340D805U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3
2.5°	462.4	462.2	462.4	461.7	462.4	462.2	462.4	464.4	464.4	464.5	464.7
5°	430.3	430.1	429.4	427.6	429.4	430.1	430.3	430.9	432.6	435.4	434.6
7.5°	402.2	401.9	400.1	400.1	400.1	401.9	402.2	403.9	405.7	407.5	409.6
10°	385.6	385.8	383.3	381.8	383.3	385.8	385.6	387.0	389.8	391.2	392.6
12.5°	369.4	368.5	366.5	364.9	366.5	368.5	369.4	370.6	374.3	375.9	378.7
15°	348.2	346.1	341.2	341.5	341.2	346.1	348.2	347.3	351.1	353.2	354.0
17.5°	323.2	321.6	321.6	318.6	321.6	321.6	323.2	324.8	328.1	330.3	336.3
20°	308.5	307.5	307.9	305.0	307.9	307.5	308.5	311.8	313.9	316.8	321.6
22.5°	297.0	296.0	294.3	293.4	294.3	296.0	297.0	299.3	301.6	305.7	308.3
25°	280.3	278.6	277.0	277.9	277.0	278.6	280.3	281.5	285.6	287.5	291.2
27.5°	263.5	262.3	260.6	260.4	260.6	262.3	263.5	264.7	267.0	270.1	274.6
30°	252.8	251.6	250.7	249.7	250.7	251.6	252.8	253.9	256.2	259.5	262.8
32.5°	242.0	241.7	240.3	240.0	240.3	241.7	242.0	243.7	246.0	249.1	252.0
35°	227.9	226.7	226.2	226.4	226.2	226.7	227.9	228.7	230.8	233.7	236.4
37.5°	214.5	212.9	212.0	211.3	212.0	212.9	214.5	214.6	216.7	218.6	222.3
40°	204.8	203.2	202.8	202.3	202.8	203.2	204.8	204.6	206.9	208.4	211.7
42.5°	194.0	193.4	193.1	192.3	193.1	193.4	194.0	195.2	196.4	198.6	201.1
45°	179.3	179.1	177.8	178.3	177.8	179.1	179.3	179.9	182.2	183.7	185.9
47.5°	163.7	162.8	161.9	162.6	161.9	162.8	163.7	164.6	166.1	167.9	170.9
50°	153.1	152.7	150.8	151.2	150.8	152.7	153.1	153.9	155.0	157.3	160.0
52.5°	142.5	140.9	140.2	139.9	140.2	140.9	142.5	143.3	144.5	147.1	149.2
55°	124.8	123.0	122.2	121.7	122.2	123.0	124.8	126.4	128.0	130.9	133.0
57.5°	107.5	107.1	106.4	106.8	106.4	107.1	107.5	109.9	111.6	113.9	116.5
60°	97.5	97.5	97.5	97.2	97.5	97.5	97.5	99.5	100.9	103.3	105.9
62.5°	89.6	89.1	89.0	89.3	89.0	89.1	89.6	90.5	92.0	93.5	95.9
65°	77.7	77.5	76.7	76.4	76.7	77.5	77.7	78.3	79.5	80.6	82.3
67.5°	66.4	65.7	65.5	65.2	65.5	65.7	66.4	67.0	67.8	69.1	70.0
70°	58.0	57.5	56.3	56.5	56.3	57.5	58.0	59.0	59.8	61.5	62.3
72.5°	48.9	48.4	48.2	47.9	48.2	48.4	48.9	49.8	50.6	52.5	53.9
75°	38.6	38.4	38.3	39.1	38.3	38.4	38.6	38.9	39.1	39.7	40.3
77.5°	30.9	30.9	31.1	30.8	31.1	30.9	30.9	30.9	30.9	31.3	31.4
80°	25.9	25.9	25.8	25.8	25.8	25.9	25.9	25.9	25.9	25.9	25.8
82.5°	20.8	21.0	21.1	20.8	21.1	21.0	20.8	21.1	21.3	21.0	21.1
85°	13.7	13.5	13.9	13.7	13.9	13.5	13.7	13.7	13.3	13.7	13.5
87.5°	10.2	9.9	9.9	10.2	9.9	9.9	10.2	9.7	9.6	9.5	9.3
90°	20.0	20.3	20.6	21.0	20.6	20.3	20.0	19.7	19.2	18.5	18.0
92.5°	28.7	28.5	28.4	28.2	28.4	28.5	28.7	28.9	28.7	28.3	27.7
95°	54.4	54.4	54.4	54.4	54.4	54.4	54.4	54.4	54.0	53.4	52.8
97.5°	83.8	83.8	83.7	83.6	83.7	83.8	83.8	83.9	83.6	82.8	82.1
100°	105.0	105.3	105.7	105.9	105.7	105.3	105.0	104.8	104.3	103.9	103.4
102.5°	129.0	128.9	128.9	128.9	128.9	128.9	129.0	129.1	128.9	128.4	128.0
105°	165.0	165.3	165.6	165.9	165.6	165.3	165.0	164.7	164.5	164.5	164.5
107.5°	205.1	204.9	204.7	204.6	204.7	204.9	205.1	205.3	205.2	204.6	204.1
110°	231.7	231.4	231.0	230.8	231.0	231.4	231.7	232.0	231.8	231.2	230.6



TEST NUMBER: P332253-940

CATALOG NUMBER: S123RDIP-S340D805U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	258.9	258.8	258.7	258.7	258.7	258.8	258.9	258.9	258.6	257.8	257.1
115°	297.5	297.3	297.1	297.0	297.1	297.3	297.5	297.7	297.7	297.5	297.3
117.5°	337.2	336.8	336.4	335.9	336.4	336.8	337.2	337.6	337.9	337.9	338.0
120°	364.2	363.8	363.6	363.2	363.6	363.8	364.2	364.4	364.7	364.9	365.0
122.5°	390.7	390.3	389.9	389.4	389.9	390.3	390.7	391.2	391.6	392.0	392.4
125°	430.6	430.0	429.4	428.7	429.4	430.0	430.6	431.2	431.9	432.5	433.1
127.5°	470.1	469.4	468.7	468.0	468.7	469.4	470.1	470.8	471.6	472.4	473.3
130°	496.9	495.8	494.7	493.6	494.7	495.8	496.9	497.9	498.8	499.4	500.1
132.5°	522.9	522.0	521.2	520.4	521.2	522.0	522.9	523.7	524.5	525.2	526.0
135°	562.8	562.6	562.2	562.0	562.2	562.6	562.8	563.2	563.7	564.3	564.9
137.5°	600.4	599.8	599.2	598.6	599.2	599.8	600.4	600.9	601.5	602.3	602.9
140°	625.8	624.7	623.7	622.6	623.7	624.7	625.8	627.0	627.5	627.7	627.9
142.5°	649.6	648.8	647.9	647.1	647.9	648.8	649.6	650.5	650.9	651.1	651.3
145°	684.4	683.8	683.1	682.5	683.1	683.8	684.4	685.0	685.4	685.5	685.7
147.5°	716.8	715.9	715.0	714.1	715.0	715.9	716.8	717.7	718.3	718.3	718.3
150°	736.9	736.0	735.0	734.1	735.0	736.0	736.9	737.9	738.3	738.3	738.3
152.5°	756.1	755.3	754.5	753.7	754.5	755.3	756.1	756.9	757.2	756.9	756.6
155°	783.4	782.3	781.2	780.2	781.2	782.3	783.4	784.4	784.7	784.1	783.5
157.5°	806.9	806.0	805.1	804.2	805.1	806.0	806.9	807.7	807.8	807.2	806.6
160°	821.7	821.1	820.5	819.8	820.5	821.1	821.7	822.3	822.2	821.5	820.7
162.5°	834.6	833.6	832.6	831.6	832.6	833.6	834.6	835.5	835.7	834.9	834.1
165°	851.8	850.6	849.5	848.5	849.5	850.6	851.8	852.8	852.9	851.9	851.0
167.5°	865.7	864.8	863.8	862.8	863.8	864.8	865.7	866.7	866.7	865.7	864.8
170°	873.3	872.3	871.2	870.0	871.2	872.3	873.3	874.4	874.4	873.3	872.3
172.5°	878.9	877.8	876.7	875.7	876.7	877.8	878.9	880.0	880.0	879.1	878.2
175°	885.2	884.1	883.0	881.9	883.0	884.1	885.2	886.3	886.4	885.4	884.5
177.5°	887.9	887.0	886.2	885.3	886.2	887.0	887.9	888.8	888.8	888.1	887.3
180°	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5



TEST NUMBER: P332253-940

CATALOG NUMBER: S123RDIP-S340D805U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3
2.5°	463.2	465.6	467.9	470.0	473.3	474.8	477.0	477.9	480.3	483.9	487.0
5°	435.1	438.4	442.7	446.2	451.8	456.2	461.0	465.6	471.0	478.7	485.5
7.5°	411.2	414.4	419.6	426.2	432.4	438.6	445.1	451.4	459.1	470.1	481.0
10°	395.4	399.3	405.6	412.6	420.3	426.3	434.0	441.8	451.5	464.1	477.2
12.5°	381.7	384.7	391.9	398.6	407.3	415.0	422.5	431.8	442.6	456.1	471.9
15°	360.1	364.2	371.2	378.7	387.9	396.0	405.7	417.0	427.6	444.2	463.2
17.5°	338.2	344.6	352.0	360.3	367.1	378.4	388.9	400.4	413.5	431.1	452.1
20°	324.3	329.3	336.2	348.4	357.3	365.9	375.6	389.9	402.0	422.0	443.7
22.5°	312.5	316.1	323.9	333.9	344.4	354.2	364.2	377.8	392.7	411.6	435.2
25°	295.0	300.9	306.7	313.9	325.1	337.0	347.8	359.4	375.2	395.4	420.9
27.5°	277.9	283.2	288.9	297.8	306.4	317.4	328.8	342.1	359.0	380.3	406.3
30°	267.0	270.9	276.3	287.8	295.4	305.0	318.3	330.1	345.9	368.5	396.0
32.5°	255.7	260.7	266.7	275.4	285.0	294.0	306.1	319.0	335.1	357.4	385.5
35°	239.5	245.6	251.6	258.1	267.6	277.0	287.1	301.2	317.6	339.3	366.8
37.5°	224.7	229.5	234.4	242.5	251.5	260.4	269.9	283.8	299.3	322.6	347.9
40°	215.3	219.6	223.4	231.7	240.4	249.9	259.3	271.5	288.1	310.0	334.5
42.5°	204.9	208.9	214.0	220.9	230.2	238.3	247.6	259.2	274.8	297.0	318.5
45°	189.5	194.0	198.4	204.8	214.2	222.1	230.4	241.4	257.4	275.7	294.8
47.5°	173.3	178.0	183.0	189.2	197.3	205.4	213.7	223.4	238.0	255.9	268.9
50°	163.1	166.8	171.8	178.1	185.6	194.0	201.5	212.1	226.0	240.1	251.4
52.5°	152.5	155.9	161.5	168.1	175.0	182.4	190.4	199.5	212.0	225.3	234.3
55°	135.9	140.0	144.8	151.2	158.1	164.3	172.0	181.4	191.4	201.3	207.3
57.5°	120.4	123.9	127.9	134.5	140.4	147.8	154.8	162.0	171.3	178.8	182.7
60°	109.1	112.2	117.3	123.2	128.8	135.3	143.1	150.4	157.5	163.5	166.6
62.5°	98.4	102.0	106.6	111.9	118.0	124.1	131.0	137.1	143.4	148.6	150.7
65°	84.5	87.5	90.8	95.8	100.8	107.0	112.4	118.6	123.2	126.1	128.0
67.5°	72.0	73.8	76.3	79.7	84.6	90.1	95.2	100.1	104.0	105.9	107.6
70°	63.8	65.0	66.9	70.2	73.9	78.7	84.2	87.7	91.0	92.6	94.3
72.5°	55.6	57.2	58.9	61.6	64.6	68.1	72.1	76.3	78.2	80.2	81.1
75°	42.2	44.5	46.7	48.4	50.5	53.1	56.7	59.4	60.5	62.2	62.3
77.5°	31.8	32.4	34.0	36.0	37.8	39.8	42.0	44.4	44.9	45.7	46.4
80°	26.2	26.2	26.2	27.5	29.5	30.9	33.0	34.2	35.1	35.3	35.5
82.5°	21.0	21.0	20.9	21.1	21.8	22.6	24.5	25.9	26.7	26.5	26.0
85°	13.7	13.3	13.3	13.1	13.3	12.8	12.7	13.5	14.7	14.7	14.4
87.5°	9.1	8.8	8.6	8.0	7.5	6.9	6.1	5.9	5.6	6.0	5.4
90°	17.4	16.8	14.7	12.7	10.7	8.6	6.9	5.4	3.8	2.2	0.7
92.5°	27.3	26.8	25.6	24.5	23.4	22.2	21.0	20.1	19.0	17.9	16.9
95°	52.3	51.6	50.4	49.1	47.9	46.6	45.5	44.4	43.3	42.2	41.1
97.5°	81.4	80.7	79.8	78.9	78.0	77.1	76.3	75.4	74.6	73.8	73.0
100°	103.0	102.5	101.7	100.9	100.1	99.4	98.5	97.6	96.7	95.8	94.8
102.5°	127.5	127.1	126.0	125.0	123.9	123.0	122.2	121.6	121.0	120.5	119.9
105°	164.5	164.5	163.2	161.8	160.3	159.0	158.1	157.8	157.5	157.2	156.9
107.5°	203.7	203.1	202.6	202.1	201.5	200.9	200.5	200.4	200.2	200.0	199.8
110°	230.0	229.3	229.1	228.7	228.5	228.1	227.8	227.5	227.2	226.9	226.6



TEST NUMBER: P332253-940

CATALOG NUMBER: S123RDIP-S340D805U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	256.4	255.6	255.6	255.5	255.4	255.3	255.2	255.0	254.9	254.7	254.5
115°	297.1	297.0	297.3	297.7	297.9	298.3	298.2	297.7	297.2	296.8	296.3
117.5°	338.0	338.0	338.4	338.8	339.2	339.6	339.7	339.3	339.0	338.8	338.4
120°	365.2	365.3	366.1	366.8	367.7	368.5	368.4	367.4	366.5	365.5	364.6
122.5°	392.8	393.2	393.6	394.0	394.4	394.8	394.7	394.0	393.3	392.6	392.0
125°	433.7	434.4	434.6	435.0	435.2	435.6	435.5	435.1	434.5	434.1	433.6
127.5°	474.2	475.0	475.4	475.7	476.1	476.4	476.1	475.1	474.1	473.1	472.2
130°	500.6	501.2	501.8	502.2	502.7	503.1	502.7	501.5	500.2	499.0	497.8
132.5°	526.7	527.4	527.8	528.2	528.5	528.9	528.4	527.2	525.9	524.7	523.4
135°	565.5	566.1	566.2	566.4	566.6	566.8	566.3	565.4	564.5	563.6	562.6
137.5°	603.5	604.1	603.8	603.3	603.0	602.5	602.0	601.2	600.4	599.7	598.9
140°	628.0	628.1	628.0	627.9	627.7	627.5	627.1	626.3	625.5	624.7	623.9
142.5°	651.4	651.6	651.3	651.0	650.8	650.5	650.0	649.2	648.4	647.6	646.8
145°	685.9	686.0	685.5	685.1	684.7	684.1	683.8	683.5	683.1	682.9	682.5
147.5°	718.3	718.3	717.8	717.4	716.9	716.5	716.0	715.4	714.9	714.3	713.8
150°	738.3	738.3	738.0	737.7	737.4	737.1	736.7	736.5	736.1	735.8	735.5
152.5°	756.4	756.2	756.0	755.8	755.6	755.5	755.1	754.7	754.2	753.8	753.4
155°	782.8	782.2	782.1	781.9	781.8	781.6	781.5	781.5	781.5	781.5	781.5
157.5°	805.9	805.2	805.1	805.0	804.9	804.8	804.8	804.9	805.1	805.3	805.5
160°	819.9	819.2	819.2	819.2	819.2	819.2	819.3	819.7	819.9	820.3	820.6
162.5°	833.3	832.6	832.4	832.3	832.2	832.1	832.2	832.7	833.1	833.6	833.9
165°	850.1	849.2	849.2	849.2	849.2	849.2	849.4	849.9	850.3	850.8	851.2
167.5°	863.8	862.8	862.7	862.6	862.5	862.4	862.6	863.2	863.8	864.4	865.0
170°	871.2	870.0	870.0	870.0	870.0	870.0	870.4	871.0	871.6	872.3	872.9
172.5°	877.2	876.2	876.2	876.2	876.2	876.2	876.6	877.2	877.8	878.4	879.0
175°	883.6	882.6	882.6	882.6	882.6	882.6	883.0	883.6	884.2	884.8	885.4
177.5°	886.5	885.8	885.8	885.8	885.8	885.8	886.1	886.5	887.1	887.6	888.1
180°	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5



TEST NUMBER: P332253-940

CATALOG NUMBER: S123RDIP-S340D805U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3
2.5°	487.9	489.8	492.1	495.6	498.3	500.6	501.1	501.8	503.5	506.2	508.4
5°	491.2	495.9	503.5	511.0	519.2	525.8	532.1	536.5	540.6	549.3	556.3
7.5°	490.1	500.8	512.8	526.2	539.8	552.9	565.2	576.1	587.0	599.8	614.2
10°	489.5	501.9	518.2	535.4	554.3	572.7	590.7	604.6	620.7	635.3	653.8
12.5°	486.3	504.3	523.6	545.6	568.9	590.2	613.8	632.9	651.5	672.5	694.0
15°	482.1	504.0	528.5	557.8	593.2	618.8	643.0	676.5	699.3	722.1	752.9
17.5°	474.7	501.3	531.9	570.0	599.4	634.1	670.3	696.8	727.5	759.7	787.6
20°	468.7	499.6	534.0	571.3	608.9	646.5	681.6	713.2	745.0	782.2	805.0
22.5°	462.7	493.3	529.0	568.6	609.0	648.7	688.4	725.5	761.3	798.8	828.0
25°	450.0	486.3	525.0	565.5	605.4	649.0	696.3	737.7	781.9	820.6	848.3
27.5°	437.1	470.5	508.9	550.0	594.3	645.9	701.6	748.6	792.9	820.6	829.3
30°	425.4	460.7	496.1	537.9	585.9	643.4	702.6	756.4	792.7	804.9	795.9
32.5°	413.7	445.7	480.6	523.4	574.4	637.2	703.9	751.8	773.6	764.5	728.1
35°	392.9	421.7	455.6	498.4	557.0	633.8	698.5	730.8	725.5	673.5	604.9
37.5°	370.6	394.1	425.4	470.2	539.0	620.4	674.8	679.7	632.8	553.1	473.9
40°	352.9	374.2	406.4	453.1	525.0	607.1	651.1	631.8	559.3	470.6	404.5
42.5°	335.8	353.7	384.8	435.2	511.7	588.9	615.7	573.6	490.0	406.1	346.0
45°	306.8	323.7	354.8	406.5	484.5	554.3	550.7	477.6	393.9	326.4	276.5
47.5°	279.4	294.1	323.3	376.1	452.5	502.3	469.3	391.5	320.5	266.3	230.7
50°	259.9	274.5	303.5	355.7	427.0	463.2	416.2	341.2	276.1	231.2	203.0
52.5°	241.3	255.5	282.0	332.9	396.0	417.8	367.1	297.6	243.3	204.6	180.4
55°	215.3	226.0	249.9	298.5	345.7	350.7	299.3	241.2	196.5	169.5	152.9
57.5°	188.7	198.0	221.6	260.3	293.4	290.8	242.2	191.8	161.8	141.7	129.7
60°	171.4	180.6	201.3	234.5	259.5	250.7	206.1	165.6	139.8	125.1	115.5
62.5°	155.2	162.4	181.9	206.2	224.1	214.2	176.2	142.7	122.2	109.8	102.2
65°	131.9	137.8	153.3	166.0	175.9	166.4	134.8	111.6	96.8	88.1	82.9
67.5°	109.8	113.4	123.2	127.9	134.9	124.4	101.4	85.8	77.4	70.1	66.4
70°	95.8	98.4	103.7	107.5	109.2	98.4	81.4	70.0	63.0	57.8	55.5
72.5°	81.8	84.2	85.2	88.3	87.3	77.2	65.5	56.4	51.3	47.8	44.9
75°	62.5	63.6	62.5	61.3	58.6	51.5	43.4	38.9	35.1	33.4	32.4
77.5°	45.6	45.2	43.9	41.9	37.3	32.8	28.4	26.9	25.3	24.4	24.1
80°	35.1	34.2	33.0	29.9	25.9	22.8	21.8	20.8	20.2	19.1	18.9
82.5°	26.1	25.6	23.5	21.0	18.2	16.7	15.9	15.4	14.8	14.3	14.3
85°	13.9	13.3	11.0	9.5	9.2	8.7	8.6	8.6	7.7	7.5	7.5
87.5°	4.9	4.3	4.4	4.2	4.5	4.6	5.2	5.3	5.5	5.8	5.6
90°	2.2	3.8	5.4	6.9	8.6	10.7	12.7	14.7	16.8	17.4	18.0
92.5°	17.9	19.0	20.1	21.0	22.2	23.4	24.5	25.6	26.8	27.3	27.7
95°	42.2	43.3	44.4	45.5	46.6	47.9	49.1	50.4	51.6	52.3	52.8
97.5°	73.8	74.6	75.4	76.3	77.1	78.0	78.9	79.8	80.7	81.4	82.1
100°	95.8	96.7	97.6	98.5	99.4	100.1	100.9	101.7	102.5	103.0	103.4
102.5°	120.5	121.0	121.6	122.2	123.0	123.9	125.0	126.0	127.1	127.5	128.0
105°	157.2	157.5	157.8	158.1	159.0	160.3	161.8	163.2	164.5	164.5	164.5
107.5°	200.0	200.2	200.4	200.5	200.9	201.5	202.1	202.6	203.1	203.7	204.1
110°	226.9	227.2	227.5	227.8	228.1	228.5	228.7	229.1	229.3	230.0	230.6



TEST NUMBER: P332253-940

CATALOG NUMBER: S123RDIP-S340D805U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	254.7	254.9	255.0	255.2	255.3	255.4	255.5	255.6	255.6	256.4	257.1
115°	296.8	297.2	297.7	298.2	298.3	297.9	297.7	297.3	297.0	297.1	297.3
117.5°	338.8	339.0	339.3	339.7	339.6	339.2	338.8	338.4	338.0	338.0	338.0
120°	365.5	366.5	367.4	368.4	368.5	367.7	366.8	366.1	365.3	365.2	365.0
122.5°	392.6	393.3	394.0	394.7	394.8	394.4	394.0	393.6	393.2	392.8	392.4
125°	434.1	434.5	435.1	435.5	435.6	435.2	435.0	434.6	434.4	433.7	433.1
127.5°	473.1	474.1	475.1	476.1	476.4	476.1	475.7	475.4	475.0	474.2	473.3
130°	499.0	500.2	501.5	502.7	503.1	502.7	502.2	501.8	501.2	500.6	500.1
132.5°	524.7	525.9	527.2	528.4	528.9	528.5	528.2	527.8	527.4	526.7	526.0
135°	563.6	564.5	565.4	566.3	566.8	566.6	566.4	566.2	566.1	565.5	564.9
137.5°	599.7	600.4	601.2	602.0	602.5	603.0	603.3	603.8	604.1	603.5	602.9
140°	624.7	625.5	626.3	627.1	627.5	627.7	627.9	628.0	628.1	628.0	627.9
142.5°	647.6	648.4	649.2	650.0	650.5	650.8	651.0	651.3	651.6	651.4	651.3
145°	682.9	683.1	683.5	683.8	684.1	684.7	685.1	685.5	686.0	685.9	685.7
147.5°	714.3	714.9	715.4	716.0	716.5	716.9	717.4	717.8	718.3	718.3	718.3
150°	735.8	736.1	736.5	736.7	737.1	737.4	737.7	738.0	738.3	738.3	738.3
152.5°	753.8	754.2	754.7	755.1	755.5	755.6	755.8	756.0	756.2	756.4	756.6
155°	781.5	781.5	781.5	781.5	781.6	781.8	781.9	782.1	782.2	782.8	783.5
157.5°	805.3	805.1	804.9	804.8	804.8	804.9	805.0	805.1	805.2	805.9	806.6
160°	820.3	819.9	819.7	819.3	819.2	819.2	819.2	819.2	819.2	819.9	820.7
162.5°	833.6	833.1	832.7	832.2	832.1	832.2	832.3	832.4	832.6	833.3	834.1
165°	850.8	850.3	849.9	849.4	849.2	849.2	849.2	849.2	849.2	850.1	851.0
167.5°	864.4	863.8	863.2	862.6	862.4	862.5	862.6	862.7	862.8	863.8	864.8
170°	872.3	871.6	871.0	870.4	870.0	870.0	870.0	870.0	870.0	871.2	872.3
172.5°	878.4	877.8	877.2	876.6	876.2	876.2	876.2	876.2	876.2	877.2	878.2
175°	884.8	884.2	883.6	883.0	882.6	882.6	882.6	882.6	882.6	883.6	884.5
177.5°	887.6	887.1	886.5	886.1	885.8	885.8	885.8	885.8	885.8	886.5	887.3
180°	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5



TEST NUMBER: P332253-940

CATALOG NUMBER: S123RDIP-S340D805U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	485.3	485.3	485.3	485.3	485.3	485.3	485.3
2.5°	511.9	511.9	512.6	515.1	515.4	517.5	516.9
5°	562.6	566.5	568.0	574.3	577.9	579.6	576.3
7.5°	624.6	635.7	641.0	647.6	653.3	655.1	650.5
10°	669.8	681.4	691.2	697.2	702.8	706.6	711.3
12.5°	713.5	727.8	737.1	745.6	751.4	756.1	756.9
15°	761.0	782.6	799.0	811.1	817.1	820.2	818.9
17.5°	808.9	828.9	840.6	852.9	861.2	861.7	861.9
20°	836.0	855.5	869.1	878.2	887.5	887.1	889.2
22.5°	854.1	869.5	879.9	886.4	889.7	888.1	888.5
25°	862.6	867.2	865.3	854.7	851.9	842.2	843.9
27.5°	818.9	797.3	774.9	746.2	723.4	705.3	706.2
30°	759.6	721.3	677.7	641.1	608.3	599.1	579.6
32.5°	676.6	619.3	568.2	534.0	506.0	498.3	481.3
35°	536.0	480.3	427.8	396.2	383.7	366.2	366.0
37.5°	416.6	367.6	339.8	316.1	303.7	293.1	292.1
40°	350.4	312.3	291.2	274.2	262.0	254.0	252.2
42.5°	304.3	273.4	253.7	243.2	233.7	229.6	226.6
45°	248.4	227.7	214.0	204.5	200.1	197.0	195.3
47.5°	207.9	193.9	184.6	178.2	174.7	171.4	172.3
50°	185.7	174.3	167.5	161.4	158.7	156.4	156.7
52.5°	167.9	157.7	152.1	147.8	144.5	142.8	142.0
55°	142.5	136.1	130.5	127.3	125.5	123.2	122.6
57.5°	121.5	116.5	112.0	108.5	108.0	105.8	106.1
60°	107.6	103.4	99.7	97.8	96.4	94.5	95.1
62.5°	96.1	92.6	89.3	87.7	86.2	84.9	85.2
65°	78.7	75.4	73.3	72.5	71.9	71.2	70.6
67.5°	62.8	60.7	59.4	57.6	56.4	56.2	55.6
70°	52.8	50.0	47.8	45.5	44.9	44.7	44.9
72.5°	42.3	40.6	39.9	38.9	38.7	38.2	38.5
75°	31.7	31.1	30.8	29.9	29.9	29.9	29.9
77.5°	23.5	23.1	22.8	22.6	22.5	22.1	22.1
80°	18.3	18.1	17.7	17.7	17.5	17.7	17.5
82.5°	13.8	13.7	13.4	13.4	13.1	13.0	13.1
85°	7.0	6.9	7.3	6.9	7.0	6.7	7.0
87.5°	5.7	5.8	5.8	5.8	5.7	6.2	5.9
90°	18.5	19.2	19.7	20.0	20.3	20.6	21.0
92.5°	28.3	28.7	28.9	28.7	28.5	28.4	28.2
95°	53.4	54.0	54.4	54.4	54.4	54.4	54.4
97.5°	82.8	83.6	83.9	83.8	83.8	83.7	83.6
100°	103.9	104.3	104.8	105.0	105.3	105.7	105.9
102.5°	128.4	128.9	129.1	129.0	128.9	128.9	128.9
105°	164.5	164.5	164.7	165.0	165.3	165.6	165.9
107.5°	204.6	205.2	205.3	205.1	204.9	204.7	204.6
110°	231.2	231.8	232.0	231.7	231.4	231.0	230.8



TEST NUMBER: P332253-940

CATALOG NUMBER: S123RDIP-S340D805U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	257.8	258.6	258.9	258.9	258.8	258.7	258.7
115°	297.5	297.7	297.7	297.5	297.3	297.1	297.0
117.5°	337.9	337.9	337.6	337.2	336.8	336.4	335.9
120°	364.9	364.7	364.4	364.2	363.8	363.6	363.2
122.5°	392.0	391.6	391.2	390.7	390.3	389.9	389.4
125°	432.5	431.9	431.2	430.6	430.0	429.4	428.7
127.5°	472.4	471.6	470.8	470.1	469.4	468.7	468.0
130°	499.4	498.8	497.9	496.9	495.8	494.7	493.6
132.5°	525.2	524.5	523.7	522.9	522.0	521.2	520.4
135°	564.3	563.7	563.2	562.8	562.6	562.2	562.0
137.5°	602.3	601.5	600.9	600.4	599.8	599.2	598.6
140°	627.7	627.5	627.0	625.8	624.7	623.7	622.6
142.5°	651.1	650.9	650.5	649.6	648.8	647.9	647.1
145°	685.5	685.4	685.0	684.4	683.8	683.1	682.5
147.5°	718.3	718.3	717.7	716.8	715.9	715.0	714.1
150°	738.3	738.3	737.9	736.9	736.0	735.0	734.1
152.5°	756.9	757.2	756.9	756.1	755.3	754.5	753.7
155°	784.1	784.7	784.4	783.4	782.3	781.2	780.2
157.5°	807.2	807.8	807.7	806.9	806.0	805.1	804.2
160°	821.5	822.2	822.3	821.7	821.1	820.5	819.8
162.5°	834.9	835.7	835.5	834.6	833.6	832.6	831.6
165°	851.9	852.9	852.8	851.8	850.6	849.5	848.5
167.5°	865.7	866.7	866.7	865.7	864.8	863.8	862.8
170°	873.3	874.4	874.4	873.3	872.3	871.2	870.0
172.5°	879.1	880.0	880.0	878.9	877.8	876.7	875.7
175°	885.4	886.4	886.3	885.2	884.1	883.0	881.9
177.5°	888.1	888.8	888.8	887.9	887.0	886.2	885.3
180°	887.5	887.5	887.5	887.5	887.5	887.5	887.5

(END OF REPORT)