

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P832165

Luminaire Tested: S123RDIP-S340D805U940-4F0-1E-UDD-G1

Issue Date: 05/03/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P832165  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-2, G3-1807-864-9)  
Test Lab: INNOVATION CENTER  
Issue Date: 05/03/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S340D805U940-4F0-1E-UDD-G1  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 340 LUMENS PER FOOT, GRAZE OPTIC  
UPLIGHT 805 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3774.4 lumens  
Efficiency: N/A  
Efficacy: 114.4 lumens/watt  
Spacing Criteria (0/90/45): 0.55 / 1.17 / 0.8  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 33  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P832165

CATALOG NUMBER: S123RDIP-S340D805U940-4F0-1E-UDD-G1

### Luminous Intensity Polar Plot





TEST NUMBER: P832165

CATALOG NUMBER: S123RDIP-S340D805U940-4F0-1E-UDD-G1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	42	42	42	35				
1	95	91	87	84	86	82	79	77	66	64	62	52	50	49	38	37	37	30				
2	87	80	74	70	78	73	68	64	59	55	53	46	44	42	34	33	32	26				
3	80	71	64	59	72	64	59	54	52	48	45	41	39	36	31	29	28	23				
4	73	63	56	50	66	58	51	46	47	42	39	37	34	32	28	26	24	20				
5	67	57	49	43	61	52	45	40	42	38	34	34	30	28	26	24	22	18				
6	62	51	43	38	56	47	40	35	38	34	30	31	27	25	24	21	20	16				
7	58	46	39	33	52	42	36	31	35	30	27	28	25	22	22	19	18	15				
8	54	42	35	30	49	39	32	28	32	27	24	26	22	20	20	18	16	14				
9	50	38	31	27	45	35	29	25	30	25	22	24	21	18	19	16	15	13				
10	47	35	29	24	43	33	27	23	27	23	20	22	19	17	18	15	14	12				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°	135°	180°
0°	10663	10663	10663	10663	10663
5°	12661	12257	10730	8674	8053
10°	11471	12450	10676	6949	5962
15°	7899	10674	10564	5680	4716
20°	5495	8219	10352	4789	4145
25°	4187	6264	10043	4257	3821
30°	3644	5008	9657	3952	3539
35°	3347	4225	9110	3696	3282
40°	3053	3773	8396	3444	3048
45°	2757	3449	7623	3206	2813
50°	2503	3183	6713	2972	2524
55°	2263	2924	5838	2744	2164
60°	2028	2659	5072	2493	2045
65°	1872	2358	4365	2239	1936
70°	1520	2039	3808	2027	1574
75°	1335	1622	3227	1680	1385
80°	1209	1370	2641	1407	1308
85°	1099	1198	2001	1284	1198

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 80°  
 Vertical Angle: 45°  
 Luminance: 8044 cd/sqm



TEST NUMBER: P832165

CATALOG NUMBER: S123RDIP-S340D805U940-4F0-1E-UDD-G1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	90.3	2.4
10°-20°	208.9	5.5
20°-30°	239.7	6.4
30°-40°	236.3	6.3
40°-50°	208.4	5.5
50°-60°	160.3	4.2
60°-70°	105.4	2.8
70°-80°	51.2	1.4
80°-90°	14.8	0.4
90°-100°	57.1	1.5
100°-110°	172.9	4.6
110°-120°	294.4	7.8
120°-130°	387.3	10.3
130°-140°	435.3	11.5
140°-150°	428.0	11.3
150°-160°	360.3	9.5
160°-170°	239.9	6.4
170°-180°	84.0	2.2
0°-30°	539.0	14.3
0°-40°	775.3	20.5
0°-60°	1143.9	30.3
0°-90°	1315.3	34.8
90°-120°	524.4	13.9
90°-150°	1774.9	47.0
90°-180°	2459.0	65.1
0°-180°	3774.4	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	991	991	991	991	991	
5°	1172	1134	993	803	745	107
15°	709	958	948	510	423	200
25°	352	527	846	358	322	167
35°	255	322	693	281	250	159
45°	181	227	501	211	185	141
55°	121	156	311	146	115	108
65°	74	93	171	88	76	72
75°	32	39	78	40	33	35
85°	9	10	16	10	10	9
90°	21	17	1	17	21	10
95°	54	52	41	52	54	55
105°	166	164	157	164	166	176
115°	297	297	296	297	297	294
125°	429	434	434	434	429	383
135°	562	566	563	566	562	432
145°	682	686	682	686	682	426
155°	780	782	782	782	780	359
165°	848	849	851	849	848	239
175°	882	883	885	883	882	84
180°	888	888	888	888	888	



TEST NUMBER: P832165

CATALOG NUMBER: S123RDIP-S340D805U940-4F0-1E-UDD-G1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	990.6	990.6	990.6	990.6	990.6	990.6	990.6	990.6	990.6	990.6	990.6
2.5°	1097.9	1094.4	1090.9	1089.9	1088.9	1085.7	1082.4	1075.1	1067.8	1060.3	1052.8
5°	1171.8	1172.2	1172.6	1171.6	1170.6	1166.3	1162.0	1153.1	1144.2	1134.4	1124.7
7.5°	1149.0	1155.5	1162.0	1163.2	1164.5	1167.7	1171.0	1168.9	1166.9	1163.2	1159.6
10°	1049.5	1049.1	1048.7	1056.0	1063.3	1085.1	1106.8	1118.0	1129.1	1139.1	1149.0
12.5°	887.1	887.7	888.3	912.2	936.2	956.7	977.2	1005.7	1034.1	1064.8	1095.4
15°	708.8	718.7	728.7	750.0	771.3	802.2	833.0	871.2	909.4	957.9	1006.5
17.5°	582.0	586.3	590.6	611.1	631.6	660.8	690.1	733.3	776.6	839.1	901.7
20°	479.7	483.5	487.4	502.2	517.0	545.1	573.1	614.3	655.5	717.5	779.4
22.5°	400.5	408.0	415.5	425.5	435.4	455.7	476.0	518.1	560.1	616.6	673.0
25°	352.5	356.0	359.5	368.0	376.5	396.0	415.5	443.3	471.1	527.4	583.7
27.5°	320.1	321.1	322.1	328.4	334.7	347.3	359.9	385.6	411.4	457.7	504.0
30°	293.2	295.1	296.9	301.8	306.7	315.8	324.9	343.2	361.5	402.9	444.3
32.5°	272.5	273.5	274.6	278.6	282.7	289.4	296.1	310.5	324.9	356.6	388.3
35°	254.7	254.9	255.1	258.1	261.2	267.7	274.2	286.1	298.1	321.5	344.8
37.5°	234.4	235.8	237.2	239.4	241.7	247.4	253.0	262.8	272.5	291.8	311.1
40°	217.3	218.5	219.7	222.4	225.0	229.5	233.9	242.9	251.8	268.5	285.1
42.5°	200.2	201.0	201.9	204.5	207.1	212.6	218.1	225.2	232.3	246.1	259.9
45°	181.1	183.2	185.2	188.1	190.9	195.6	200.2	207.5	214.9	226.6	238.4
47.5°	165.3	166.3	167.3	169.8	172.2	177.9	183.6	190.1	196.6	207.5	218.5
50°	149.5	149.9	150.3	152.5	154.7	159.8	164.9	172.4	179.9	190.1	200.2
52.5°	134.4	135.5	136.5	138.7	140.9	144.4	147.8	155.6	163.3	173.2	183.2
55°	120.6	121.2	121.8	123.5	125.1	129.2	133.2	139.9	146.6	155.8	164.9
57.5°	107.6	108.4	109.3	110.5	111.7	115.3	119.0	124.9	130.8	139.9	149.1
60°	94.2	95.2	96.3	97.7	99.1	101.9	104.8	110.1	115.3	123.5	131.6
62.5°	84.5	84.7	84.9	86.1	87.3	89.4	91.4	95.7	99.9	108.0	116.2
65°	73.5	74.1	74.7	75.3	76.0	77.6	79.2	82.9	86.5	92.6	98.7
67.5°	62.1	62.8	63.4	64.4	65.4	66.8	68.2	70.7	73.1	78.8	84.5
70°	48.3	48.3	48.3	50.0	51.6	54.0	56.5	58.3	60.1	64.8	69.5
72.5°	39.4	39.6	39.8	40.0	40.2	41.6	43.1	46.1	49.1	52.0	54.8
75°	32.1	32.3	32.5	32.7	32.9	33.3	33.7	34.7	35.7	39.0	42.2
77.5°	25.6	25.8	26.0	26.2	26.4	26.8	27.2	27.6	28.0	29.2	30.5
80°	19.5	19.7	19.9	20.1	20.3	20.5	20.7	21.1	21.5	22.1	22.7
82.5°	14.2	14.2	14.2	14.2	14.2	14.6	15.0	15.0	15.0	15.4	15.8
85°	8.9	8.9	8.9	9.1	9.3	9.3	9.3	9.5	9.7	9.7	9.7
87.5°	4.1	3.9	3.7	3.9	4.1	4.1	4.1	4.3	4.5	4.5	4.5
90°	20.9	20.6	20.3	20.0	19.7	19.2	18.6	18.0	17.4	16.7	14.7
92.5°	30.0	30.3	30.6	30.9	31.2	31.1	30.7	30.2	29.7	29.3	28.4
95°	54.4	54.4	54.4	54.4	54.4	54.1	53.5	52.8	52.2	51.6	50.4
97.5°	78.1	78.2	78.4	78.5	78.7	78.4	77.6	76.8	76.1	75.3	74.4
100°	106.0	105.7	105.4	105.0	104.7	104.3	103.9	103.4	102.9	102.5	101.7
102.5°	134.6	134.7	134.9	135.0	135.2	135.0	134.6	134.1	133.6	133.2	132.1
105°	165.9	165.6	165.3	165.0	164.7	164.5	164.5	164.5	164.5	164.5	163.1
107.5°	198.0	198.2	198.3	198.5	198.6	198.5	198.0	197.5	197.1	196.6	196.0
110°	230.8	231.1	231.4	231.7	232.0	231.9	231.2	230.6	230.0	229.4	229.1



TEST NUMBER: P832165

CATALOG NUMBER: S123RDIP-S340D805U940-4F0-1E-UDD-G1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	265.6	265.6	265.6	265.6	265.6	265.2	264.5	263.7	262.9	262.1	262.1
115°	297.0	297.2	297.3	297.5	297.6	297.6	297.5	297.3	297.2	297.0	297.3
117.5°	329.1	329.5	330.0	330.5	330.9	331.2	331.2	331.2	331.2	331.2	331.5
120°	363.2	363.5	363.8	364.2	364.5	364.7	364.9	365.0	365.2	365.3	366.1
122.5°	396.0	396.5	396.9	397.4	397.9	398.3	398.8	399.3	399.7	400.2	400.5
125°	428.8	429.4	430.0	430.6	431.2	431.9	432.5	433.1	433.7	434.3	434.7
127.5°	461.5	462.2	462.8	463.4	464.0	464.8	465.7	466.6	467.6	468.5	468.8
130°	493.6	494.7	495.8	496.9	497.9	498.8	499.4	500.0	500.7	501.3	501.7
132.5°	527.1	527.8	528.6	529.4	530.2	530.9	531.7	532.5	533.3	534.0	534.3
135°	561.9	562.2	562.5	562.9	563.2	563.6	564.2	564.9	565.5	566.1	566.3
137.5°	592.6	593.1	593.5	594.0	594.5	595.1	595.9	596.6	597.4	598.2	597.7
140°	622.6	623.7	624.7	625.8	626.9	627.5	627.7	627.8	628.0	628.2	628.0
142.5°	653.3	654.0	654.8	655.6	656.4	656.8	657.0	657.1	657.3	657.4	657.1
145°	682.5	683.2	683.8	684.4	685.0	685.4	685.6	685.7	685.9	686.0	685.6
147.5°	709.0	710.0	710.9	711.8	712.7	713.2	713.2	713.2	713.2	713.2	712.7
150°	734.1	735.1	736.0	736.9	737.8	738.3	738.3	738.3	738.3	738.3	738.0
152.5°	758.5	759.3	760.1	760.9	761.6	761.9	761.5	761.2	760.9	760.6	760.5
155°	780.1	781.2	782.3	783.4	784.5	784.7	784.1	783.5	782.9	782.2	782.1
157.5°	800.4	801.3	802.2	803.1	804.1	804.2	803.6	803.0	802.4	801.8	801.6
160°	819.9	820.5	821.1	821.7	822.4	822.3	821.5	820.7	820.0	819.2	819.2
162.5°	834.5	835.6	836.7	837.8	838.9	839.0	838.2	837.5	836.7	835.9	835.8
165°	848.5	849.5	850.6	851.7	852.8	852.9	852.0	851.0	850.1	849.2	849.2
167.5°	861.0	861.9	862.9	863.8	864.7	864.7	863.8	862.9	861.9	861.0	860.9
170°	870.1	871.2	872.2	873.3	874.4	874.4	873.3	872.2	871.2	870.1	870.1
172.5°	877.0	878.1	879.2	880.3	881.4	881.5	880.5	879.6	878.7	877.7	877.7
175°	881.9	883.0	884.1	885.2	886.3	886.3	885.4	884.5	883.6	882.6	882.6
177.5°	884.7	885.8	886.9	888.0	889.1	889.1	888.2	887.3	886.3	885.4	885.4
180°	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5



TEST NUMBER: P832165

CATALOG NUMBER: S123RDIP-S340D805U940-4F0-1E-UDD-G1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	990.6	990.6	990.6	990.6	990.6	990.6	990.6	990.6	990.6	990.6	990.6
2.5°	1051.8	1050.7	1041.0	1031.2	1021.7	1012.2	1005.0	997.9	986.0	974.0	966.5
5°	1116.9	1109.2	1093.8	1078.4	1055.2	1032.1	1012.6	993.1	968.3	943.5	922.8
7.5°	1153.3	1147.0	1128.3	1109.6	1079.0	1048.3	1017.8	987.4	950.8	914.3	883.0
10°	1154.3	1159.6	1144.2	1128.7	1094.2	1059.7	1018.2	976.8	927.7	878.5	838.1
12.5°	1118.2	1140.9	1137.7	1134.4	1099.3	1064.1	1013.8	963.4	903.1	842.8	792.2
15°	1050.5	1094.6	1107.6	1120.6	1091.6	1062.5	1005.2	948.0	877.1	806.2	748.1
17.5°	963.4	1025.1	1059.5	1093.8	1072.7	1051.6	988.8	926.0	846.2	766.4	703.3
20°	860.2	941.1	994.9	1048.7	1041.0	1033.3	968.5	903.7	817.6	731.5	663.1
22.5°	758.3	843.6	917.9	992.3	1000.2	1008.1	942.7	877.3	783.1	688.8	619.2
25°	670.4	757.1	845.6	934.2	952.0	969.9	907.8	845.6	747.9	650.3	581.0
27.5°	586.5	668.9	766.4	863.9	896.4	928.9	872.0	815.2	713.4	611.7	542.6
30°	518.1	591.8	691.3	790.8	836.1	881.4	829.2	777.0	676.1	575.1	507.5
32.5°	454.3	520.3	620.2	720.1	772.7	825.3	780.2	735.2	638.1	541.0	474.2
35°	403.9	463.0	556.2	649.5	708.3	767.2	730.3	693.3	598.5	503.6	440.5
37.5°	360.7	410.2	497.7	585.3	647.8	710.4	679.5	648.6	559.5	470.3	410.6
40°	324.9	364.7	446.2	527.6	588.9	650.3	623.9	597.5	517.7	437.8	382.0
42.5°	294.3	328.6	401.7	474.8	531.1	587.3	569.8	552.4	480.1	407.8	356.0
45°	267.3	296.1	360.5	424.8	476.6	528.4	514.6	500.8	438.5	376.1	328.6
47.5°	243.3	268.1	325.5	383.0	429.5	476.0	463.2	450.4	398.8	347.3	304.0
50°	221.4	242.5	290.4	338.3	380.2	422.0	411.4	400.9	358.2	315.6	278.2
52.5°	200.6	218.1	261.2	304.2	337.9	371.6	363.5	355.4	322.5	289.6	255.7
55°	180.9	197.0	233.3	269.7	298.5	327.4	319.2	311.1	285.5	259.9	230.1
57.5°	163.1	177.1	206.5	236.0	258.9	281.9	278.0	274.2	252.8	231.5	206.9
60°	144.2	156.8	182.2	207.5	226.0	244.5	240.0	235.6	220.3	205.1	184.0
62.5°	127.3	138.5	158.8	179.1	194.1	209.2	205.9	202.7	191.1	179.5	162.1
65°	109.7	120.6	137.1	153.5	165.3	177.1	174.2	171.4	162.7	153.9	139.9
67.5°	93.6	102.8	117.0	131.2	139.1	147.0	145.4	143.8	137.1	130.4	119.4
70°	77.4	85.3	97.1	108.9	114.3	119.8	120.4	121.0	114.9	108.9	100.7
72.5°	61.1	67.4	78.4	89.4	93.6	97.9	97.7	97.5	93.8	90.2	82.9
75°	46.9	51.6	60.1	68.6	72.3	76.0	76.8	77.6	74.1	70.7	66.6
77.5°	33.7	37.0	43.5	50.0	54.0	58.1	58.5	58.9	57.3	55.6	51.8
80°	23.8	24.8	28.8	32.9	37.2	41.4	42.0	42.6	41.0	39.4	37.0
82.5°	16.4	17.1	18.5	19.9	23.4	26.8	27.6	28.4	27.6	26.8	24.2
85°	10.0	10.2	10.8	11.4	13.0	14.6	15.4	16.2	15.8	15.4	14.0
87.5°	4.5	4.5	4.7	4.9	5.3	5.7	6.7	7.7	7.1	6.5	5.9
90°	12.7	10.7	8.7	6.9	5.3	3.8	2.2	0.7	2.2	3.8	5.3
92.5°	27.4	26.5	25.6	24.6	23.7	22.8	21.8	20.9	21.8	22.8	23.7
95°	49.1	47.9	46.6	45.5	44.4	43.3	42.2	41.1	42.2	43.3	44.4
97.5°	73.4	72.5	71.6	70.7	70.0	69.2	68.4	67.6	68.4	69.2	70.0
100°	100.9	100.2	99.4	98.5	97.6	96.7	95.7	94.8	95.7	96.7	97.6
102.5°	131.0	129.9	128.8	128.0	127.6	127.1	126.7	126.2	126.7	127.1	127.6
105°	161.7	160.4	159.0	158.1	157.8	157.5	157.2	156.9	157.2	157.5	157.8
107.5°	195.4	194.7	194.1	193.7	193.6	193.4	193.3	193.1	193.3	193.4	193.6
110°	228.8	228.4	228.1	227.8	227.5	227.2	226.9	226.6	226.9	227.2	227.5





TEST NUMBER: P832165

CATALOG NUMBER: S123RDIP-S340D805U940-4F0-1E-UDD-G1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	262.1	262.1	262.1	262.1	261.9	261.8	261.6	261.4	261.6	261.8	261.9
115°	297.6	297.9	298.2	298.2	297.7	297.2	296.8	296.3	296.8	297.2	297.7
117.5°	331.8	332.1	332.4	332.5	332.3	332.2	332.0	331.9	332.0	332.2	332.3
120°	366.9	367.6	368.4	368.3	367.4	366.5	365.6	364.6	365.6	366.5	367.4
122.5°	400.8	401.1	401.4	401.3	400.6	400.0	399.4	398.8	399.4	400.0	400.6
125°	435.0	435.3	435.6	435.5	435.0	434.6	434.1	433.6	434.1	434.6	435.0
127.5°	469.1	469.4	469.7	469.4	468.5	467.6	466.6	465.7	466.6	467.6	468.5
130°	502.2	502.7	503.1	502.7	501.5	500.3	499.0	497.8	499.0	500.3	501.5
132.5°	534.7	535.0	535.3	534.8	533.6	532.3	531.1	529.9	531.1	532.3	533.6
135°	566.4	566.6	566.7	566.3	565.4	564.5	563.6	562.6	563.6	564.5	565.4
137.5°	597.2	596.8	596.3	595.7	594.9	594.1	593.4	592.6	593.4	594.1	594.9
140°	627.8	627.7	627.5	627.1	626.3	625.5	624.7	624.0	624.7	625.5	626.3
142.5°	656.8	656.5	656.2	655.7	654.9	654.1	653.3	652.6	653.3	654.1	654.9
145°	685.1	684.6	684.2	683.8	683.5	683.2	682.8	682.5	682.8	683.2	683.5
147.5°	712.3	711.8	711.4	710.8	710.2	709.6	709.0	708.3	709.0	709.6	710.2
150°	737.7	737.4	737.1	736.8	736.5	736.1	735.8	735.5	735.8	736.1	736.5
152.5°	760.3	760.2	760.0	759.7	759.2	758.8	758.3	757.8	758.3	758.8	759.2
155°	781.9	781.8	781.6	781.5	781.5	781.5	781.5	781.5	781.5	781.5	781.5
157.5°	801.4	801.3	801.1	801.1	801.3	801.4	801.6	801.8	801.6	801.4	801.3
160°	819.2	819.2	819.2	819.3	819.6	820.0	820.3	820.6	820.3	820.0	819.6
162.5°	835.6	835.5	835.3	835.5	835.9	836.4	836.8	837.3	836.8	836.4	835.9
165°	849.2	849.2	849.2	849.4	849.9	850.3	850.8	851.3	850.8	850.3	849.9
167.5°	860.7	860.5	860.4	860.6	861.2	861.9	862.5	863.1	862.5	861.9	861.2
170°	870.1	870.1	870.1	870.4	871.0	871.6	872.2	872.9	872.2	871.6	871.0
172.5°	877.7	877.7	877.7	878.1	878.7	879.3	879.9	880.5	879.9	879.3	878.7
175°	882.6	882.6	882.6	882.9	883.6	884.2	884.8	885.4	884.8	884.2	883.6
177.5°	885.4	885.4	885.4	885.7	886.3	887.0	887.6	888.2	887.6	887.0	886.3
180°	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5



TEST NUMBER: P832165

CATALOG NUMBER: S123RDIP-S340D805U940-4F0-1E-UDD-G1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	990.6	990.6	990.6	990.6	990.6	990.6	990.6	990.6	990.6	990.6	990.6
2.5°	958.9	947.4	935.8	927.5	919.1	908.8	898.4	898.0	897.6	889.9	882.2
5°	902.1	882.0	861.9	842.2	822.5	802.8	783.1	778.6	774.1	767.4	760.7
7.5°	851.7	819.6	787.5	762.4	737.2	717.5	697.8	684.4	671.0	660.6	650.3
10°	797.7	757.9	718.1	687.6	657.2	635.8	614.5	599.1	583.7	576.3	569.0
12.5°	741.6	698.4	655.1	625.3	595.4	569.8	544.3	530.2	516.2	506.1	495.9
15°	690.1	643.6	597.1	565.4	533.7	509.7	485.8	471.8	457.7	447.6	437.4
17.5°	640.1	593.2	546.3	514.2	482.1	460.4	438.7	425.0	411.4	405.1	398.8
20°	594.6	547.3	500.0	469.7	439.5	418.1	396.8	389.5	382.2	376.3	370.4
22.5°	549.5	504.0	458.6	429.5	400.5	385.0	369.6	363.7	357.8	353.4	348.9
25°	511.8	466.5	421.2	395.8	370.4	358.4	346.5	342.6	338.7	334.3	329.8
27.5°	473.6	430.5	387.5	367.2	346.9	337.1	327.4	322.5	317.6	314.0	310.3
30°	439.9	400.1	360.3	343.4	326.6	318.0	309.5	304.2	298.9	295.5	292.0
32.5°	407.4	372.0	336.7	322.3	307.9	299.5	291.2	286.1	281.1	277.0	272.9
35°	377.3	346.7	316.0	302.8	289.6	281.3	272.9	267.9	262.8	258.7	254.7
37.5°	350.9	323.1	295.3	282.9	270.5	263.2	255.9	250.6	245.3	241.1	236.8
40°	326.1	301.6	277.0	265.0	253.0	245.1	237.2	232.5	227.9	224.0	220.1
42.5°	304.2	281.7	259.1	247.4	235.6	228.1	220.5	215.1	209.6	207.3	205.1
45°	281.1	261.2	241.3	229.9	218.5	210.6	202.7	198.0	193.3	191.3	189.3
47.5°	260.8	242.3	223.8	212.6	201.5	194.3	187.2	183.6	179.9	177.1	174.2
50°	240.9	223.0	205.1	194.3	183.6	177.5	171.4	166.9	162.5	160.4	158.4
52.5°	221.8	205.5	189.3	178.3	167.3	161.4	155.6	151.7	147.8	143.6	139.3
55°	200.2	186.0	171.8	162.1	152.3	146.2	140.1	135.7	131.2	126.7	122.3
57.5°	182.4	168.4	154.3	145.6	136.9	131.0	125.1	120.2	115.3	111.7	108.0
60°	162.9	150.7	138.5	130.0	121.4	115.8	110.1	105.4	100.7	98.9	97.1
62.5°	144.6	133.2	121.8	114.3	106.8	101.3	95.9	92.8	89.8	88.5	87.3
65°	125.9	116.2	106.4	99.5	92.6	87.9	83.3	81.8	80.4	79.4	78.4
67.5°	108.4	100.1	91.8	85.7	79.6	76.4	73.1	71.5	69.9	68.6	67.4
70°	92.6	85.3	78.0	72.7	67.4	64.4	61.3	59.9	58.5	56.3	54.0
72.5°	75.5	69.9	64.2	60.1	56.1	53.4	50.8	47.9	45.1	43.1	41.0
75°	62.5	56.9	51.2	47.3	43.5	40.4	37.4	36.4	35.3	34.7	34.1
77.5°	47.9	43.1	38.2	35.1	32.1	30.7	29.2	28.6	28.0	27.8	27.6
80°	34.5	30.5	26.4	24.8	23.2	22.7	22.3	21.9	21.5	21.3	21.1
82.5°	21.5	19.5	17.5	17.1	16.7	16.4	16.2	16.0	15.8	15.6	15.4
85°	12.6	11.8	11.0	10.8	10.6	10.4	10.2	10.2	10.2	10.2	10.2
87.5°	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.1	4.9
90°	6.9	8.7	10.7	12.7	14.7	16.7	17.4	18.0	18.6	19.2	19.7
92.5°	24.6	25.6	26.5	27.4	28.4	29.3	29.7	30.2	30.7	31.1	31.2
95°	45.5	46.6	47.9	49.1	50.4	51.6	52.2	52.8	53.5	54.1	54.4
97.5°	70.7	71.6	72.5	73.4	74.4	75.3	76.1	76.8	77.6	78.4	78.7
100°	98.5	99.4	100.2	100.9	101.7	102.5	102.9	103.4	103.9	104.3	104.7
102.5°	128.0	128.8	129.9	131.0	132.1	133.2	133.6	134.1	134.6	135.0	135.2
105°	158.1	159.0	160.4	161.7	163.1	164.5	164.5	164.5	164.5	164.5	164.7
107.5°	193.7	194.1	194.7	195.4	196.0	196.6	197.1	197.5	198.0	198.5	198.6
110°	227.8	228.1	228.4	228.8	229.1	229.4	230.0	230.6	231.2	231.9	232.0



TEST NUMBER: P832165

CATALOG NUMBER: S123RDIP-S340D805U940-4F0-1E-UDD-G1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	262.1	262.1	262.1	262.1	262.1	262.1	262.9	263.7	264.5	265.2	265.6
115°	298.2	298.2	297.9	297.6	297.3	297.0	297.2	297.3	297.5	297.6	297.6
117.5°	332.5	332.4	332.1	331.8	331.5	331.2	331.2	331.2	331.2	331.2	330.9
120°	368.3	368.4	367.6	366.9	366.1	365.3	365.2	365.0	364.9	364.7	364.5
122.5°	401.3	401.4	401.1	400.8	400.5	400.2	399.7	399.3	398.8	398.3	397.9
125°	435.5	435.6	435.3	435.0	434.7	434.3	433.7	433.1	432.5	431.9	431.2
127.5°	469.4	469.7	469.4	469.1	468.8	468.5	467.6	466.6	465.7	464.8	464.0
130°	502.7	503.1	502.7	502.2	501.7	501.3	500.7	500.0	499.4	498.8	497.9
132.5°	534.8	535.3	535.0	534.7	534.3	534.0	533.3	532.5	531.7	530.9	530.2
135°	566.3	566.7	566.6	566.4	566.3	566.1	565.5	564.9	564.2	563.6	563.2
137.5°	595.7	596.3	596.8	597.2	597.7	598.2	597.4	596.6	595.9	595.1	594.5
140°	627.1	627.5	627.7	627.8	628.0	628.2	628.0	627.8	627.7	627.5	626.9
142.5°	655.7	656.2	656.5	656.8	657.1	657.4	657.3	657.1	657.0	656.8	656.4
145°	683.8	684.2	684.6	685.1	685.6	686.0	685.9	685.7	685.6	685.4	685.0
147.5°	710.8	711.4	711.8	712.3	712.7	713.2	713.2	713.2	713.2	713.2	712.7
150°	736.8	737.1	737.4	737.7	738.0	738.3	738.3	738.3	738.3	738.3	737.8
152.5°	759.7	760.0	760.2	760.3	760.5	760.6	760.9	761.2	761.5	761.9	761.6
155°	781.5	781.6	781.8	781.9	782.1	782.2	782.9	783.5	784.1	784.7	784.5
157.5°	801.1	801.1	801.3	801.4	801.6	801.8	802.4	803.0	803.6	804.2	804.1
160°	819.3	819.2	819.2	819.2	819.2	819.2	820.0	820.7	821.5	822.3	822.4
162.5°	835.5	835.3	835.5	835.6	835.8	835.9	836.7	837.5	838.2	839.0	838.9
165°	849.4	849.2	849.2	849.2	849.2	849.2	850.1	851.0	852.0	852.9	852.8
167.5°	860.6	860.4	860.5	860.7	860.9	861.0	861.9	862.9	863.8	864.7	864.7
170°	870.4	870.1	870.1	870.1	870.1	870.1	871.2	872.2	873.3	874.4	874.4
172.5°	878.1	877.7	877.7	877.7	877.7	877.7	878.7	879.6	880.5	881.5	881.4
175°	882.9	882.6	882.6	882.6	882.6	882.6	883.6	884.5	885.4	886.3	886.3
177.5°	885.7	885.4	885.4	885.4	885.4	885.4	886.3	887.3	888.2	889.1	889.1
180°	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5



TEST NUMBER: P832165

CATALOG NUMBER: S123RDIP-S340D805U940-4F0-1E-UDD-G1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
0°	990.6	990.6	990.6	990.6
2.5°	880.2	878.1	877.3	876.5
5°	754.4	748.1	746.7	745.3
7.5°	647.6	645.0	636.3	627.5
10°	560.9	552.8	549.1	545.5
12.5°	488.4	480.9	479.7	478.5
15°	432.2	426.9	425.0	423.2
17.5°	395.2	391.5	389.3	387.1
20°	367.8	365.1	363.5	361.9
22.5°	346.9	344.8	343.6	342.4
25°	326.8	323.7	322.7	321.7
27.5°	307.7	305.0	304.0	303.0
30°	289.8	287.6	286.1	284.7
32.5°	270.3	267.7	266.8	266.0
35°	253.0	251.4	250.6	249.8
37.5°	234.8	232.7	231.5	230.3
40°	219.1	218.1	217.5	216.9
42.5°	203.3	201.5	201.3	201.0
45°	187.4	185.6	185.2	184.8
47.5°	172.6	171.0	170.8	170.6
50°	156.2	153.9	152.3	150.7
52.5°	137.3	135.3	133.8	132.4
55°	120.0	117.8	116.6	115.3
57.5°	107.0	106.0	105.4	104.8
60°	96.5	95.9	95.4	95.0
62.5°	86.7	86.1	86.1	86.1
65°	77.8	77.2	76.6	76.0
67.5°	66.2	65.0	64.8	64.6
70°	52.2	50.4	50.2	50.0
72.5°	40.8	40.6	40.2	39.8
75°	33.7	33.3	33.3	33.3
77.5°	27.2	26.8	26.8	26.8
80°	20.9	20.7	20.9	21.1
82.5°	15.4	15.4	15.2	15.0
85°	10.0	9.7	9.7	9.7
87.5°	4.9	4.9	4.9	4.9
90°	20.0	20.3	20.6	20.9
92.5°	30.9	30.6	30.3	30.0
95°	54.4	54.4	54.4	54.4
97.5°	78.5	78.4	78.2	78.1
100°	105.0	105.4	105.7	106.0
102.5°	135.0	134.9	134.7	134.6
105°	165.0	165.3	165.6	165.9
107.5°	198.5	198.3	198.2	198.0
110°	231.7	231.4	231.1	230.8



TEST NUMBER: P832165

CATALOG NUMBER: S123RDIP-S340D805U940-4F0-1E-UDD-G1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
112.5°	265.6	265.6	265.6	265.6
115°	297.5	297.3	297.2	297.0
117.5°	330.5	330.0	329.5	329.1
120°	364.2	363.8	363.5	363.2
122.5°	397.4	396.9	396.5	396.0
125°	430.6	430.0	429.4	428.8
127.5°	463.4	462.8	462.2	461.5
130°	496.9	495.8	494.7	493.6
132.5°	529.4	528.6	527.8	527.1
135°	562.9	562.5	562.2	561.9
137.5°	594.0	593.5	593.1	592.6
140°	625.8	624.7	623.7	622.6
142.5°	655.6	654.8	654.0	653.3
145°	684.4	683.8	683.2	682.5
147.5°	711.8	710.9	710.0	709.0
150°	736.9	736.0	735.1	734.1
152.5°	760.9	760.1	759.3	758.5
155°	783.4	782.3	781.2	780.1
157.5°	803.1	802.2	801.3	800.4
160°	821.7	821.1	820.5	819.9
162.5°	837.8	836.7	835.6	834.5
165°	851.7	850.6	849.5	848.5
167.5°	863.8	862.9	861.9	861.0
170°	873.3	872.2	871.2	870.1
172.5°	880.3	879.2	878.1	877.0
175°	885.2	884.1	883.0	881.9
177.5°	888.0	886.9	885.8	884.7
180°	887.5	887.5	887.5	887.5



TEST NUMBER: P832165

CATALOG NUMBER: S123RDIP-S340D805U940-4F0-1E-UDD-G1

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.35	8.06	8.44	9.14	10.61	12.02	12.72	13.10	13.80	15.28
	3H	8.57	9.20	9.66	10.28	11.78	13.51	14.14	14.60	15.22	16.72
	4H	8.94	9.54	10.05	10.63	12.13	13.99	14.59	15.10	15.68	17.18
	6H	9.22	9.77	10.33	10.86	12.37	14.30	14.85	15.41	15.94	17.45
	8H	9.30	9.82	10.42	10.93	12.44	14.37	14.89	15.49	16.00	17.51
	12H	9.35	9.84	10.47	10.94	12.47	14.40	14.89	15.52	16.00	17.52
4H	2H	8.06	8.66	9.17	9.75	11.25	12.00	12.59	13.11	13.68	15.18
	3H	9.42	9.92	10.54	11.03	12.54	13.64	14.14	14.76	15.26	16.77
	4H	9.87	10.33	10.99	11.43	12.97	14.25	14.70	15.37	15.81	17.34
	6H	10.23	10.62	11.36	11.75	13.28	14.68	15.07	15.81	16.20	17.72
	8H	10.35	10.72	11.48	11.84	13.38	14.81	15.17	15.93	16.29	17.83
	12H	10.42	10.75	11.57	11.89	13.43	14.86	15.19	16.01	16.32	17.87
8H	4H	10.18	10.54	11.30	11.66	13.20	14.20	14.57	15.33	15.69	17.23
	6H	10.64	10.94	11.78	12.10	13.64	14.70	15.00	15.85	16.16	17.70
	8H	10.83	11.09	11.98	12.23	13.79	14.88	15.14	16.04	16.29	17.84
	12H	10.96	11.19	12.12	12.33	13.93	14.99	15.22	16.15	16.36	17.96
12H	4H	10.18	10.51	11.33	11.64	13.19	14.15	14.48	15.29	15.61	17.16
	6H	10.69	10.96	11.85	12.10	13.66	14.67	14.93	15.83	16.08	17.63
	8H	10.91	11.14	12.06	12.28	13.87	14.86	15.09	16.02	16.23	17.82