

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332292-940

Luminaire Tested: **S123RDIP-S560D1025U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332292-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S560D1025U940-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1025 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5045.5 lumens
Efficiency: N/A
Efficacy: 113.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 44.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332292-940

CATALOG NUMBER: S123RDIP-S560D1025U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332292-940

CATALOG NUMBER: S123RDIP-S560D1025U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45	38
1	95	91	87	84	86	83	80	77	67	65	63	53	52	50	40	39	38	32
2	87	80	74	69	79	73	68	63	59	56	53	47	45	42	35	34	33	27
3	79	70	63	58	72	64	58	53	52	48	45	42	39	36	32	30	28	23
4	73	62	55	49	66	57	50	45	47	42	38	37	34	31	28	26	24	20
5	67	56	48	42	60	51	44	39	42	37	33	33	30	27	26	23	21	18
6	61	50	42	36	56	46	39	34	38	33	29	30	27	24	23	21	19	16
7	57	45	37	32	51	41	34	30	34	29	25	28	24	21	21	19	17	14
8	53	41	33	28	48	37	31	26	31	26	22	25	21	19	20	17	15	13
9	49	37	30	25	45	34	28	23	29	24	20	23	20	17	18	16	14	11
10	46	34	27	22	42	31	25	21	26	21	18	21	18	15	17	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9065	9065	9065
5°	9100	8975	9027
10°	9049	8862	8833
15°	8952	8655	8564
20°	8818	8395	8200
25°	8679	8105	7845
30°	8499	7768	7343
35°	8311	7432	6884
40°	8140	7035	6315
45°	7913	6645	5801
50°	7663	6199	5228
55°	7409	5692	4692
60°	7175	5147	4103
65°	6872	4559	3512
70°	6493	3827	2839
75°	5939	3011	2670
80°	5294	2672	2455
85°	4471	2359	2186



TEST NUMBER: P332292-940

CATALOG NUMBER: S123RDIP-S560D1025U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.1	1.6
10°-20°	220.1	4.4
20°-30°	316.9	6.3
30°-40°	356.9	7.1
40°-50°	341.4	6.8
50°-60°	279.6	5.5
60°-70°	188.7	3.7
70°-80°	94.9	1.9
80°-90°	28.5	0.6
90°-100°	73.8	1.5
100°-110°	220.9	4.4
110°-120°	375.8	7.4
120°-130°	494.3	9.8
130°-140°	555.6	11.0
140°-150°	546.1	10.8
150°-160°	459.7	9.1
160°-170°	306.0	6.1
170°-180°	107.2	2.1
0°-30°	616.0	12.2
0°-40°	972.9	19.3
0°-60°	1594.0	31.6
0°-90°	1906.0	37.8
90°-120°	670.6	13.3
90°-150°	2266.5	44.9
90°-180°	3139.0	62.2
0°-180°	5045.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	842	842	842	842	842	
5°	842	839	831	836	835	80
15°	803	795	777	773	768	226
25°	731	713	682	668	660	336
35°	632	607	566	537	524	396
45°	520	488	436	399	381	401
55°	395	360	303	265	250	354
65°	270	231	179	147	138	267
75°	143	110	72	66	64	152
85°	36	22	19	18	18	41
90°	1	10	21	25	27	5
95°	52	59	66	69	70	59
105°	200	202	210	210	212	214
115°	378	381	379	380	379	374
125°	554	556	555	551	547	494
135°	718	723	723	719	718	553
145°	871	873	876	875	871	544
155°	998	998	999	1002	996	459
165°	1087	1084	1084	1089	1083	306
175°	1130	1127	1127	1132	1126	107
180°	1133	1133	1133	1133	1133	



TEST NUMBER: P332292-940

CATALOG NUMBER: S123RDIP-S560D1025U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	842.2	842.2	842.2	842.2	842.2	842.2	842.2	842.2	842.2	842.2	842.2
2.5°	845.0	844.5	844.0	843.5	843.0	842.0	840.6	839.1	837.7	836.2	837.6
5°	842.2	841.5	840.7	840.0	839.2	837.9	836.1	834.3	832.4	830.6	832.0
7.5°	834.5	833.7	832.8	832.0	831.2	829.6	827.2	824.8	822.4	820.1	820.8
10°	827.9	826.8	825.7	824.7	823.7	821.7	819.0	816.3	813.5	810.8	810.9
12.5°	818.6	817.4	816.2	815.0	813.9	811.6	808.2	804.9	801.6	798.3	798.2
15°	803.3	801.6	800.0	798.3	796.7	793.6	789.4	785.2	780.9	776.7	775.9
17.5°	784.0	782.1	780.2	778.2	776.2	772.6	767.1	761.8	756.3	751.0	749.4
20°	769.8	767.4	765.0	762.5	760.1	756.0	750.2	744.5	738.7	732.9	730.9
22.5°	753.9	751.2	748.4	745.6	742.8	738.3	732.2	726.0	720.0	713.8	711.3
25°	730.8	727.1	723.3	719.5	715.7	710.3	703.3	696.3	689.4	682.4	679.2
27.5°	702.8	698.7	694.5	690.3	686.1	680.1	672.3	664.6	656.8	649.1	644.6
30°	683.8	679.2	674.7	670.1	665.6	659.0	650.5	642.0	633.5	625.0	619.8
32.5°	664.6	659.5	654.3	649.2	644.0	636.9	627.9	618.9	609.9	600.9	595.3
35°	632.5	627.1	621.6	616.2	610.6	603.2	593.8	584.4	575.0	565.6	559.0
37.5°	600.0	594.0	587.9	581.8	575.7	567.7	557.6	547.6	537.5	527.4	520.0
40°	579.3	572.6	565.9	559.2	552.5	543.8	533.1	522.3	511.5	500.7	492.8
42.5°	555.7	549.0	542.4	535.7	529.1	520.1	509.0	497.8	486.7	475.5	466.9
45°	519.8	513.0	506.1	499.4	492.5	483.2	471.5	459.9	448.2	436.5	427.8
47.5°	483.8	476.4	468.9	461.4	453.9	444.3	432.6	420.9	409.2	397.5	388.2
50°	457.6	450.5	443.4	436.2	429.1	419.4	407.1	394.8	382.5	370.2	360.8
52.5°	434.2	426.4	418.7	410.9	403.2	393.2	381.0	368.9	356.7	344.6	334.7
55°	394.8	387.4	380.0	372.5	365.1	354.9	342.0	329.1	316.2	303.3	294.4
57.5°	358.5	350.4	342.2	334.1	326.0	315.5	302.6	289.6	276.6	263.7	255.4
60°	333.3	325.0	316.6	308.3	300.0	289.4	276.9	264.3	251.6	239.1	230.9
62.5°	308.2	299.9	291.5	283.1	274.8	264.3	251.7	239.2	226.5	213.9	206.3
65°	269.8	261.4	253.2	244.8	236.4	226.3	214.5	202.7	190.8	179.0	171.6
67.5°	231.4	223.0	214.5	206.1	197.7	187.8	176.4	165.1	153.7	142.3	136.8
70°	206.3	198.0	189.9	181.7	173.5	164.1	153.5	142.9	132.2	121.6	116.3
72.5°	181.1	173.1	165.0	156.9	148.8	140.0	130.4	120.6	111.0	101.4	97.0
75°	142.8	135.5	128.2	120.9	113.6	105.8	97.5	89.1	80.8	72.4	70.9
77.5°	107.8	101.2	94.6	88.0	81.4	75.4	70.1	64.7	59.3	53.9	53.1
80°	85.4	79.2	72.9	66.7	60.5	55.8	52.6	49.4	46.2	43.1	42.5
82.5°	64.1	58.7	53.3	48.0	42.5	39.1	37.6	36.2	34.7	33.2	32.7
85°	36.2	32.9	29.5	26.2	22.8	21.0	20.5	20.1	19.6	19.1	18.8
87.5°	13.3	12.4	11.4	10.4	9.5	9.4	9.8	10.3	10.9	11.4	11.4
90°	0.9	2.9	4.8	6.9	8.8	11.1	13.6	16.2	18.8	21.4	22.1
92.5°	21.6	22.9	24.3	25.6	26.9	28.4	29.8	31.2	32.7	34.2	34.8
95°	52.5	53.9	55.3	56.7	58.1	59.6	61.1	62.7	64.3	65.9	66.7
97.5°	93.3	94.3	95.3	96.4	97.4	98.4	99.6	100.8	101.9	103.1	104.0
100°	121.1	122.3	123.4	124.6	125.8	126.9	127.9	128.9	129.8	130.8	131.4
102.5°	153.1	153.8	154.5	155.2	156.0	156.9	158.3	159.5	160.9	162.2	162.7
105°	200.3	200.6	201.1	201.4	201.9	203.0	204.7	206.5	208.3	210.1	210.1
107.5°	255.1	255.4	255.6	255.8	256.1	256.5	257.3	258.0	258.7	259.4	260.0
110°	289.3	289.7	290.1	290.4	290.9	291.2	291.7	292.0	292.5	292.8	293.6



TEST NUMBER: P332292-940

CATALOG NUMBER: S123RDIP-S560D1025U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	324.9	325.1	325.4	325.6	325.8	326.0	326.1	326.2	326.3	326.3	327.3
115°	378.3	378.9	379.5	380.0	380.7	380.8	380.4	380.0	379.6	379.2	379.4
117.5°	432.0	432.5	432.8	433.3	433.6	433.5	433.1	432.6	432.0	431.5	431.5
120°	465.6	466.7	467.9	469.1	470.3	470.4	469.4	468.4	467.4	466.5	466.2
122.5°	500.4	501.3	502.1	503.0	503.9	504.1	503.5	503.0	502.6	502.0	501.5
125°	553.7	554.3	554.8	555.4	556.0	556.2	555.7	555.4	554.9	554.6	553.8
127.5°	602.8	604.0	605.3	606.5	607.9	608.2	607.8	607.4	607.0	606.5	605.4
130°	635.5	637.1	638.7	640.2	641.9	642.4	641.8	641.1	640.6	640.0	639.2
132.5°	668.3	669.9	671.5	673.1	674.7	675.2	674.8	674.3	673.9	673.4	672.5
135°	718.4	719.5	720.7	721.8	723.1	723.5	723.4	723.2	723.0	722.7	722.0
137.5°	764.6	765.6	766.6	767.6	768.6	769.3	769.8	770.3	770.9	771.3	770.5
140°	796.7	797.6	798.6	799.6	800.6	801.2	801.4	801.6	801.8	802.0	801.8
142.5°	825.8	826.8	827.9	828.8	829.8	830.5	830.8	831.2	831.5	831.9	831.7
145°	871.4	871.8	872.2	872.6	873.0	873.5	874.1	874.7	875.3	875.8	875.7
147.5°	911.3	912.0	912.8	913.5	914.2	914.8	915.3	915.9	916.4	917.0	917.0
150°	939.1	939.5	939.9	940.2	940.7	941.0	941.5	941.8	942.3	942.6	942.6
152.5°	961.9	962.4	963.0	963.5	964.0	964.5	964.7	964.9	965.2	965.5	965.7
155°	997.8	997.8	997.8	997.8	997.8	997.9	998.1	998.3	998.5	998.7	999.5
157.5°	1028.4	1028.2	1028.0	1027.7	1027.5	1027.4	1027.6	1027.8	1028.0	1028.1	1028.9
160°	1047.7	1047.2	1046.9	1046.5	1046.1	1045.9	1045.9	1045.9	1045.9	1045.9	1046.9
162.5°	1064.8	1064.2	1063.6	1063.1	1062.6	1062.4	1062.5	1062.7	1062.8	1063.0	1064.0
165°	1086.8	1086.2	1085.7	1085.0	1084.5	1084.1	1084.1	1084.1	1084.1	1084.1	1085.3
167.5°	1104.5	1103.7	1102.9	1102.1	1101.3	1101.0	1101.2	1101.3	1101.4	1101.6	1102.9
170°	1114.5	1113.7	1112.9	1112.1	1111.3	1110.9	1110.9	1110.9	1110.9	1110.9	1112.2
172.5°	1122.2	1121.5	1120.7	1119.9	1119.1	1118.7	1118.7	1118.7	1118.7	1118.7	1119.9
175°	1130.4	1129.6	1128.8	1128.1	1127.3	1126.9	1126.9	1126.9	1126.9	1126.9	1128.1
177.5°	1133.8	1133.2	1132.6	1131.9	1131.3	1131.0	1131.0	1131.0	1131.0	1131.0	1131.9
180°	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1



TEST NUMBER: P332292-940

CATALOG NUMBER: S123RDIP-S560D1025U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	842.2	842.2	842.2	842.2	842.2	842.2	842.2	842.2
2.5°	838.9	840.3	841.6	842.1	841.9	841.6	841.4	841.2
5°	833.3	834.7	836.1	836.6	836.3	836.0	835.7	835.4
7.5°	821.6	822.3	823.1	823.2	822.7	822.2	821.7	821.2
10°	811.1	811.3	811.4	811.1	810.4	809.6	808.9	808.1
12.5°	798.1	798.0	797.9	797.4	796.5	795.6	794.8	793.9
15°	775.2	774.4	773.6	772.7	771.6	770.6	769.5	768.5
17.5°	747.8	746.2	744.5	743.0	741.4	739.8	738.2	736.6
20°	729.0	727.0	725.1	723.2	721.3	719.5	717.6	715.9
22.5°	708.9	706.4	704.0	701.9	700.2	698.5	696.8	695.1
25°	676.0	672.8	669.7	667.2	665.6	663.9	662.2	660.5
27.5°	640.2	635.8	631.3	627.9	625.3	622.8	620.2	617.6
30°	614.7	609.5	604.4	600.6	598.2	595.8	593.3	590.8
32.5°	589.7	584.0	578.4	574.3	571.8	569.2	566.6	564.1
35°	552.5	546.0	539.5	534.8	532.1	529.4	526.6	523.9
37.5°	512.6	505.2	497.8	492.5	489.1	485.7	482.3	478.9
40°	484.9	477.0	469.1	463.4	459.9	456.5	453.0	449.4
42.5°	458.3	449.7	441.0	435.2	432.0	428.9	425.8	422.7
45°	419.2	410.5	401.9	395.7	392.1	388.4	384.8	381.1
47.5°	378.7	369.3	359.9	353.6	350.4	347.1	343.8	340.5
50°	351.4	342.0	332.6	326.1	322.6	319.1	315.7	312.2
52.5°	325.0	315.2	305.4	299.0	295.9	292.7	289.6	286.5
55°	285.7	276.9	268.0	262.2	259.1	256.1	253.1	250.0
57.5°	247.0	238.7	230.4	225.0	222.4	219.8	217.2	214.6
60°	222.7	214.5	206.3	200.9	198.3	195.7	193.1	190.6
62.5°	198.5	190.8	183.1	177.9	175.2	172.5	169.8	167.1
65°	164.1	156.7	149.2	144.6	143.0	141.3	139.6	137.9
67.5°	131.3	125.6	120.1	116.5	114.7	112.9	111.1	109.3
70°	110.9	105.7	100.3	96.8	95.1	93.5	91.8	90.2
72.5°	92.6	88.4	84.0	81.5	80.8	80.1	79.4	78.6
75°	69.4	67.9	66.3	65.5	65.1	64.8	64.5	64.2
77.5°	52.3	51.5	50.6	50.1	49.8	49.5	49.2	48.9
80°	42.1	41.6	41.2	40.8	40.6	40.2	39.9	39.6
82.5°	32.3	31.8	31.4	31.1	31.0	31.0	30.9	30.9
85°	18.5	18.2	17.9	17.7	17.7	17.7	17.7	17.7
87.5°	11.4	11.5	11.5	11.5	11.5	11.4	11.4	11.3
90°	22.9	23.7	24.5	25.1	25.5	25.9	26.3	26.7
92.5°	35.5	36.1	36.7	36.9	36.6	36.5	36.2	35.9
95°	67.4	68.2	69.0	69.5	69.5	69.5	69.5	69.5
97.5°	104.9	105.8	106.7	107.1	107.1	107.0	106.9	106.8
100°	132.1	132.6	133.2	133.8	134.1	134.5	134.9	135.3
102.5°	163.4	164.0	164.5	164.8	164.7	164.6	164.6	164.5
105°	210.1	210.1	210.1	210.3	210.6	211.1	211.4	211.9
107.5°	260.6	261.3	261.9	262.1	261.9	261.6	261.4	261.2
110°	294.4	295.2	296.0	296.2	295.8	295.4	295.1	294.6



TEST NUMBER: P332292-940

CATALOG NUMBER: S123RDIP-S560D1025U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	328.2	329.1	330.1	330.6	330.5	330.4	330.3	330.2
115°	379.6	379.8	380.0	380.0	379.8	379.6	379.4	379.2
117.5°	431.4	431.4	431.4	431.1	430.5	430.0	429.4	428.8
120°	466.0	465.8	465.7	465.3	464.9	464.6	464.1	463.8
122.5°	501.0	500.5	500.0	499.4	498.9	498.3	497.8	497.2
125°	552.9	552.1	551.3	550.5	549.8	549.0	548.2	547.4
127.5°	604.3	603.2	602.1	601.1	600.2	599.2	598.3	597.4
130°	638.4	637.6	636.9	635.7	634.4	632.9	631.6	630.2
132.5°	671.5	670.7	669.7	668.7	667.6	666.6	665.5	664.4
135°	721.2	720.4	719.6	719.0	718.6	718.2	717.8	717.5
137.5°	769.7	768.9	768.0	767.2	766.5	765.7	765.0	764.3
140°	801.6	801.4	801.2	800.4	799.1	797.6	796.3	794.9
142.5°	831.5	831.3	831.1	830.5	829.4	828.3	827.2	826.2
145°	875.5	875.3	875.0	874.6	873.8	873.0	872.2	871.4
147.5°	917.0	917.0	917.0	916.4	915.3	914.0	912.8	911.7
150°	942.6	942.6	942.6	942.0	940.8	939.7	938.4	937.3
152.5°	966.1	966.3	966.7	966.3	965.3	964.3	963.2	962.2
155°	1000.3	1001.1	1001.8	1001.6	1000.2	998.8	997.4	996.0
157.5°	1029.7	1030.6	1031.4	1031.3	1030.2	1029.0	1028.0	1026.8
160°	1047.8	1048.8	1049.8	1049.9	1049.2	1048.4	1047.6	1046.8
162.5°	1065.0	1066.0	1066.9	1066.8	1065.5	1064.3	1063.0	1061.8
165°	1086.5	1087.7	1088.9	1088.8	1087.4	1086.0	1084.7	1083.3
167.5°	1104.0	1105.3	1106.5	1106.5	1105.3	1104.0	1102.9	1101.6
170°	1113.7	1115.0	1116.4	1116.4	1115.0	1113.7	1112.2	1110.9
172.5°	1121.1	1122.4	1123.6	1123.6	1122.1	1120.8	1119.4	1117.9
175°	1129.3	1130.4	1131.7	1131.5	1130.2	1128.7	1127.4	1126.0
177.5°	1132.9	1133.8	1134.8	1134.7	1133.6	1132.5	1131.4	1130.2
180°	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1

(END OF REPORT)