

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332286-940

Luminaire Tested: **S123RDIP-S560D805U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332286-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S560D805U940-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 805 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4364.2 lumens
Efficiency: N/A
Efficacy: 113.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332286-940

CATALOG NUMBER: S123RDIP-S560D805U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332286-940

CATALOG NUMBER: S123RDIP-S560D805U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	44
1	97	92	89	85	88	85	82	79	70	68	66	57	56	54	45	44	43	37
2	88	81	75	70	80	74	69	65	62	58	55	50	48	46	40	38	37	32
3	81	71	64	59	74	66	60	55	55	50	47	45	42	39	36	33	31	27
4	74	63	56	50	67	58	52	46	49	44	40	40	36	34	32	29	27	24
5	68	57	49	43	62	52	45	40	44	39	35	36	32	29	29	26	24	21
6	63	51	43	37	57	47	40	35	40	34	30	33	29	26	26	23	21	18
7	58	46	38	33	53	42	36	31	36	31	27	30	26	23	24	21	19	16
8	54	42	34	29	49	39	32	27	33	27	24	27	23	20	22	19	17	15
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	20	18	15	13
10	47	35	28	23	43	32	26	22	28	23	19	23	19	17	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9065	9065	9065
5°	9100	8975	9027
10°	9049	8862	8833
15°	8952	8655	8564
20°	8818	8395	8200
25°	8679	8105	7845
30°	8499	7768	7343
35°	8311	7432	6884
40°	8140	7035	6315
45°	7913	6645	5801
50°	7663	6199	5228
55°	7409	5692	4692
60°	7175	5147	4103
65°	6872	4559	3512
70°	6493	3827	2839
75°	5939	3011	2670
80°	5294	2672	2455
85°	4471	2359	2186



TEST NUMBER: P332286-940

CATALOG NUMBER: S123RDIP-S560D805U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.1	1.8
10°-20°	220.1	5.0
20°-30°	316.9	7.3
30°-40°	356.9	8.2
40°-50°	341.4	7.8
50°-60°	279.6	6.4
60°-70°	188.7	4.3
70°-80°	94.9	2.2
80°-90°	27.7	0.6
90°-100°	57.8	1.3
100°-110°	173.1	4.0
110°-120°	294.3	6.7
120°-130°	387.1	8.9
130°-140°	435.1	10.0
140°-150°	427.7	9.8
150°-160°	360.1	8.3
160°-170°	239.7	5.5
170°-180°	83.9	1.9
0°-30°	616.0	14.1
0°-40°	972.9	22.3
0°-60°	1594.0	36.5
0°-90°	1905.3	43.7
90°-120°	525.2	12.0
90°-150°	1775.2	40.7
90°-180°	2459.0	56.3
0°-180°	4364.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	842	842	842	842	842	
5°	842	839	831	836	835	80
15°	803	795	777	773	768	226
25°	731	713	682	668	660	336
35°	632	607	566	537	524	396
45°	520	488	436	399	381	401
55°	395	360	303	265	250	354
65°	270	231	179	147	138	267
75°	143	110	72	66	64	152
85°	36	22	19	18	18	41
90°	1	8	17	19	21	4
95°	41	46	52	54	54	46
105°	157	159	164	165	166	168
115°	296	298	297	298	297	293
125°	434	436	434	432	429	387
135°	563	567	566	563	562	433
145°	682	684	686	685	682	426
155°	782	782	782	785	780	360
165°	851	849	849	853	848	240
175°	885	883	883	886	882	84
180°	888	888	888	888	888	



TEST NUMBER: P332286-940

CATALOG NUMBER: S123RDIP-S560D805U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	842.2	842.2	842.2	842.2	842.2	842.2	842.2	842.2	842.2	842.2	842.2
2.5°	845.0	844.5	844.0	843.5	843.0	842.0	840.6	839.1	837.7	836.2	837.6
5°	842.2	841.5	840.7	840.0	839.2	837.9	836.1	834.3	832.4	830.6	832.0
7.5°	834.5	833.7	832.8	832.0	831.2	829.6	827.2	824.8	822.4	820.1	820.8
10°	827.9	826.8	825.7	824.7	823.7	821.7	819.0	816.3	813.5	810.8	810.9
12.5°	818.6	817.4	816.2	815.0	813.9	811.6	808.2	804.9	801.6	798.3	798.2
15°	803.3	801.6	800.0	798.3	796.7	793.6	789.4	785.2	780.9	776.7	775.9
17.5°	784.0	782.1	780.2	778.2	776.2	772.6	767.1	761.8	756.3	751.0	749.4
20°	769.8	767.4	765.0	762.5	760.1	756.0	750.2	744.5	738.7	732.9	730.9
22.5°	753.9	751.2	748.4	745.6	742.8	738.3	732.2	726.0	720.0	713.8	711.3
25°	730.8	727.1	723.3	719.5	715.7	710.3	703.3	696.3	689.4	682.4	679.2
27.5°	702.8	698.7	694.5	690.3	686.1	680.1	672.3	664.6	656.8	649.1	644.6
30°	683.8	679.2	674.7	670.1	665.6	659.0	650.5	642.0	633.5	625.0	619.8
32.5°	664.6	659.5	654.3	649.2	644.0	636.9	627.9	618.9	609.9	600.9	595.3
35°	632.5	627.1	621.6	616.2	610.6	603.2	593.8	584.4	575.0	565.6	559.0
37.5°	600.0	594.0	587.9	581.8	575.7	567.7	557.6	547.6	537.5	527.4	520.0
40°	579.3	572.6	565.9	559.2	552.5	543.8	533.1	522.3	511.5	500.7	492.8
42.5°	555.7	549.0	542.4	535.7	529.1	520.1	509.0	497.8	486.7	475.5	466.9
45°	519.8	513.0	506.1	499.4	492.5	483.2	471.5	459.9	448.2	436.5	427.8
47.5°	483.8	476.4	468.9	461.4	453.9	444.3	432.6	420.9	409.2	397.5	388.2
50°	457.6	450.5	443.4	436.2	429.1	419.4	407.1	394.8	382.5	370.2	360.8
52.5°	434.2	426.4	418.7	410.9	403.2	393.2	381.0	368.9	356.7	344.6	334.7
55°	394.8	387.4	380.0	372.5	365.1	354.9	342.0	329.1	316.2	303.3	294.4
57.5°	358.5	350.4	342.2	334.1	326.0	315.5	302.6	289.6	276.6	263.7	255.4
60°	333.3	325.0	316.6	308.3	300.0	289.4	276.9	264.3	251.6	239.1	230.9
62.5°	308.2	299.9	291.5	283.1	274.8	264.3	251.7	239.2	226.5	213.9	206.3
65°	269.8	261.4	253.2	244.8	236.4	226.3	214.5	202.7	190.8	179.0	171.6
67.5°	231.4	223.0	214.5	206.1	197.7	187.8	176.4	165.1	153.7	142.3	136.8
70°	206.3	198.0	189.9	181.7	173.5	164.1	153.5	142.9	132.2	121.6	116.3
72.5°	181.1	173.1	165.0	156.9	148.8	140.0	130.4	120.6	111.0	101.4	97.0
75°	142.8	135.5	128.2	120.9	113.6	105.8	97.5	89.1	80.8	72.4	70.9
77.5°	107.8	101.2	94.6	88.0	81.4	75.4	70.1	64.7	59.3	53.9	53.1
80°	85.4	79.2	72.9	66.7	60.5	55.8	52.6	49.4	46.2	43.1	42.5
82.5°	64.1	58.7	53.3	48.0	42.5	39.1	37.6	36.2	34.7	33.2	32.7
85°	36.2	32.9	29.5	26.2	22.8	21.0	20.5	20.1	19.6	19.1	18.8
87.5°	13.3	12.2	11.2	10.2	9.2	8.8	9.3	9.6	10.1	10.4	10.4
90°	0.7	2.2	3.8	5.4	6.9	8.6	10.7	12.7	14.7	16.8	17.4
92.5°	16.9	17.9	19.0	20.1	21.0	22.2	23.4	24.5	25.6	26.8	27.3
95°	41.1	42.2	43.3	44.4	45.5	46.6	47.9	49.1	50.4	51.6	52.3
97.5°	73.0	73.8	74.6	75.4	76.3	77.1	78.0	78.9	79.8	80.7	81.4
100°	94.8	95.8	96.7	97.6	98.5	99.4	100.1	100.9	101.7	102.5	103.0
102.5°	119.9	120.5	121.0	121.6	122.2	123.0	123.9	125.0	126.0	127.1	127.5
105°	156.9	157.2	157.5	157.8	158.1	159.0	160.3	161.8	163.2	164.5	164.5
107.5°	199.8	200.0	200.2	200.4	200.5	200.9	201.5	202.1	202.6	203.1	203.7
110°	226.6	226.9	227.2	227.5	227.8	228.1	228.5	228.7	229.1	229.3	230.0



TEST NUMBER: P332286-940

CATALOG NUMBER: S123RDIP-S560D805U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	254.5	254.7	254.9	255.0	255.2	255.3	255.4	255.5	255.6	255.6	256.4
115°	296.3	296.8	297.2	297.7	298.2	298.3	297.9	297.7	297.3	297.0	297.1
117.5°	338.4	338.8	339.0	339.3	339.7	339.6	339.2	338.8	338.4	338.0	338.0
120°	364.6	365.5	366.5	367.4	368.4	368.5	367.7	366.8	366.1	365.3	365.2
122.5°	392.0	392.6	393.3	394.0	394.7	394.8	394.4	394.0	393.6	393.2	392.8
125°	433.6	434.1	434.5	435.1	435.5	435.6	435.2	435.0	434.6	434.4	433.7
127.5°	472.2	473.1	474.1	475.1	476.1	476.4	476.1	475.7	475.4	475.0	474.2
130°	497.8	499.0	500.2	501.5	502.7	503.1	502.7	502.2	501.8	501.2	500.6
132.5°	523.4	524.7	525.9	527.2	528.4	528.9	528.5	528.2	527.8	527.4	526.7
135°	562.6	563.6	564.5	565.4	566.3	566.8	566.6	566.4	566.2	566.1	565.5
137.5°	598.9	599.7	600.4	601.2	602.0	602.5	603.0	603.3	603.8	604.1	603.5
140°	623.9	624.7	625.5	626.3	627.1	627.5	627.7	627.9	628.0	628.1	628.0
142.5°	646.8	647.6	648.4	649.2	650.0	650.5	650.8	651.0	651.3	651.6	651.4
145°	682.5	682.9	683.1	683.5	683.8	684.1	684.7	685.1	685.5	686.0	685.9
147.5°	713.8	714.3	714.9	715.4	716.0	716.5	716.9	717.4	717.8	718.3	718.3
150°	735.5	735.8	736.1	736.5	736.7	737.1	737.4	737.7	738.0	738.3	738.3
152.5°	753.4	753.8	754.2	754.7	755.1	755.5	755.6	755.8	756.0	756.2	756.4
155°	781.5	781.5	781.5	781.5	781.5	781.6	781.8	781.9	782.1	782.2	782.8
157.5°	805.5	805.3	805.1	804.9	804.8	804.8	804.9	805.0	805.1	805.2	805.9
160°	820.6	820.3	819.9	819.7	819.3	819.2	819.2	819.2	819.2	819.2	819.9
162.5°	833.9	833.6	833.1	832.7	832.2	832.1	832.2	832.3	832.4	832.6	833.3
165°	851.2	850.8	850.3	849.9	849.4	849.2	849.2	849.2	849.2	849.2	850.1
167.5°	865.0	864.4	863.8	863.2	862.6	862.4	862.5	862.6	862.7	862.8	863.8
170°	872.9	872.3	871.6	871.0	870.4	870.0	870.0	870.0	870.0	870.0	871.2
172.5°	879.0	878.4	877.8	877.2	876.6	876.2	876.2	876.2	876.2	876.2	877.2
175°	885.4	884.8	884.2	883.6	883.0	882.6	882.6	882.6	882.6	882.6	883.6
177.5°	888.1	887.6	887.1	886.5	886.1	885.8	885.8	885.8	885.8	885.8	886.5
180°	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5



TEST NUMBER: P332286-940

CATALOG NUMBER: S123RDIP-S560D805U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	842.2	842.2	842.2	842.2	842.2	842.2	842.2	842.2
2.5°	838.9	840.3	841.6	842.1	841.9	841.6	841.4	841.2
5°	833.3	834.7	836.1	836.6	836.3	836.0	835.7	835.4
7.5°	821.6	822.3	823.1	823.2	822.7	822.2	821.7	821.2
10°	811.1	811.3	811.4	811.1	810.4	809.6	808.9	808.1
12.5°	798.1	798.0	797.9	797.4	796.5	795.6	794.8	793.9
15°	775.2	774.4	773.6	772.7	771.6	770.6	769.5	768.5
17.5°	747.8	746.2	744.5	743.0	741.4	739.8	738.2	736.6
20°	729.0	727.0	725.1	723.2	721.3	719.5	717.6	715.9
22.5°	708.9	706.4	704.0	701.9	700.2	698.5	696.8	695.1
25°	676.0	672.8	669.7	667.2	665.6	663.9	662.2	660.5
27.5°	640.2	635.8	631.3	627.9	625.3	622.8	620.2	617.6
30°	614.7	609.5	604.4	600.6	598.2	595.8	593.3	590.8
32.5°	589.7	584.0	578.4	574.3	571.8	569.2	566.6	564.1
35°	552.5	546.0	539.5	534.8	532.1	529.4	526.6	523.9
37.5°	512.6	505.2	497.8	492.5	489.1	485.7	482.3	478.9
40°	484.9	477.0	469.1	463.4	459.9	456.5	453.0	449.4
42.5°	458.3	449.7	441.0	435.2	432.0	428.9	425.8	422.7
45°	419.2	410.5	401.9	395.7	392.1	388.4	384.8	381.1
47.5°	378.7	369.3	359.9	353.6	350.4	347.1	343.8	340.5
50°	351.4	342.0	332.6	326.1	322.6	319.1	315.7	312.2
52.5°	325.0	315.2	305.4	299.0	295.9	292.7	289.6	286.5
55°	285.7	276.9	268.0	262.2	259.1	256.1	253.1	250.0
57.5°	247.0	238.7	230.4	225.0	222.4	219.8	217.2	214.6
60°	222.7	214.5	206.3	200.9	198.3	195.7	193.1	190.6
62.5°	198.5	190.8	183.1	177.9	175.2	172.5	169.8	167.1
65°	164.1	156.7	149.2	144.6	143.0	141.3	139.6	137.9
67.5°	131.3	125.6	120.1	116.5	114.7	112.9	111.1	109.3
70°	110.9	105.7	100.3	96.8	95.1	93.5	91.8	90.2
72.5°	92.6	88.4	84.0	81.5	80.8	80.1	79.4	78.6
75°	69.4	67.9	66.3	65.5	65.1	64.8	64.5	64.2
77.5°	52.3	51.5	50.6	50.1	49.8	49.5	49.2	48.9
80°	42.1	41.6	41.2	40.8	40.6	40.2	39.9	39.6
82.5°	32.3	31.8	31.4	31.1	31.0	31.0	30.9	30.9
85°	18.5	18.2	17.9	17.7	17.7	17.7	17.7	17.7
87.5°	10.4	10.4	10.4	10.4	10.3	10.3	10.3	10.2
90°	18.0	18.5	19.2	19.7	20.0	20.3	20.6	21.0
92.5°	27.7	28.3	28.7	28.9	28.7	28.5	28.4	28.2
95°	52.8	53.4	54.0	54.4	54.4	54.4	54.4	54.4
97.5°	82.1	82.8	83.6	83.9	83.8	83.8	83.7	83.6
100°	103.4	103.9	104.3	104.8	105.0	105.3	105.7	105.9
102.5°	128.0	128.4	128.9	129.1	129.0	128.9	128.9	128.9
105°	164.5	164.5	164.5	164.7	165.0	165.3	165.6	165.9
107.5°	204.1	204.6	205.2	205.3	205.1	204.9	204.7	204.6
110°	230.6	231.2	231.8	232.0	231.7	231.4	231.0	230.8



TEST NUMBER: P332286-940

CATALOG NUMBER: S123RDIP-S560D805U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	257.1	257.8	258.6	258.9	258.9	258.8	258.7	258.7
115°	297.3	297.5	297.7	297.7	297.5	297.3	297.1	297.0
117.5°	338.0	337.9	337.9	337.6	337.2	336.8	336.4	335.9
120°	365.0	364.9	364.7	364.4	364.2	363.8	363.6	363.2
122.5°	392.4	392.0	391.6	391.2	390.7	390.3	389.9	389.4
125°	433.1	432.5	431.9	431.2	430.6	430.0	429.4	428.7
127.5°	473.3	472.4	471.6	470.8	470.1	469.4	468.7	468.0
130°	500.1	499.4	498.8	497.9	496.9	495.8	494.7	493.6
132.5°	526.0	525.2	524.5	523.7	522.9	522.0	521.2	520.4
135°	564.9	564.3	563.7	563.2	562.8	562.6	562.2	562.0
137.5°	602.9	602.3	601.5	600.9	600.4	599.8	599.2	598.6
140°	627.9	627.7	627.5	627.0	625.8	624.7	623.7	622.6
142.5°	651.3	651.1	650.9	650.5	649.6	648.8	647.9	647.1
145°	685.7	685.5	685.4	685.0	684.4	683.8	683.1	682.5
147.5°	718.3	718.3	718.3	717.7	716.8	715.9	715.0	714.1
150°	738.3	738.3	738.3	737.9	736.9	736.0	735.0	734.1
152.5°	756.6	756.9	757.2	756.9	756.1	755.3	754.5	753.7
155°	783.5	784.1	784.7	784.4	783.4	782.3	781.2	780.2
157.5°	806.6	807.2	807.8	807.7	806.9	806.0	805.1	804.2
160°	820.7	821.5	822.2	822.3	821.7	821.1	820.5	819.8
162.5°	834.1	834.9	835.7	835.5	834.6	833.6	832.6	831.6
165°	851.0	851.9	852.9	852.8	851.8	850.6	849.5	848.5
167.5°	864.8	865.7	866.7	866.7	865.7	864.8	863.8	862.8
170°	872.3	873.3	874.4	874.4	873.3	872.3	871.2	870.0
172.5°	878.2	879.1	880.0	880.0	878.9	877.8	876.7	875.7
175°	884.5	885.4	886.4	886.3	885.2	884.1	883.0	881.9
177.5°	887.3	888.1	888.8	888.8	887.9	887.0	886.2	885.3
180°	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5

(END OF REPORT)