

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332516-930

Luminaire Tested: **S124DIP-S350D810U930-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332516-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIP-S350D810U930-4F0-1E-UDD-F4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3597.6 lumens
Efficiency: N/A
Efficacy: 115.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332516-930

CATALOG NUMBER: S124DIP-S350D810U930-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332516-930

CATALOG NUMBER: S124DIP-S350D810U930-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	75	75	75	58	58	58	42	42	42	34
1	94	90	86	83	85	81	78	75	65	63	61	50	49	48	37	36	35	29
2	86	79	73	68	77	71	66	62	57	54	51	44	42	40	32	31	30	24
3	78	69	62	56	70	63	56	52	50	46	42	39	36	34	29	27	25	20
4	71	61	53	47	64	55	49	44	45	40	36	35	31	29	26	23	22	18
5	66	54	46	40	59	49	42	37	40	35	31	31	28	25	23	21	19	15
6	60	49	41	35	54	44	37	32	36	31	27	28	25	22	21	18	17	13
7	56	44	36	31	50	40	33	28	32	27	24	26	22	19	19	17	15	12
8	52	40	32	27	46	36	29	25	30	24	21	23	20	17	18	15	13	11
9	48	36	29	24	43	33	26	22	27	22	19	21	18	15	16	14	12	10
10	45	33	26	21	40	30	24	20	25	20	17	20	16	14	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3888	3888	3888
5°	3900	3853	3881
10°	3875	3822	3841
15°	3828	3768	3777
20°	3766	3699	3703
25°	3695	3624	3613
30°	3608	3533	3500
35°	3517	3438	3392
40°	3424	3331	3270
45°	3327	3225	3164
50°	3218	3131	3034
55°	3102	3009	2911
60°	2984	2872	2785
65°	2854	2743	2632
70°	2705	2568	2469
75°	2480	2361	2299
80°	2208	2120	2064
85°	1936	1862	1815



TEST NUMBER: P332516-930

CATALOG NUMBER: S124DIP-S350D810U930-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.4	1.3
10°-20°	127.8	3.6
20°-30°	188.1	5.2
30°-40°	218.7	6.1
40°-50°	218.7	6.1
50°-60°	191.3	5.3
60°-70°	142.1	3.9
70°-80°	80.7	2.2
80°-90°	25.1	0.7
90°-100°	234.4	6.5
100°-110°	487.8	13.6
110°-120°	436.9	12.1
120°-130°	367.5	10.2
130°-140°	306.4	8.5
140°-150°	234.1	6.5
150°-160°	164.6	4.6
160°-170°	96.8	2.7
170°-180°	31.5	0.9
0°-30°	361.2	10.0
0°-40°	579.9	16.1
0°-60°	989.8	27.5
0°-90°	1237.7	34.4
90°-120°	1159.1	32.2
90°-150°	2067.1	57.5
90°-180°	2360.0	65.6
0°-180°	3597.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	482	482	482	482	482	
5°	481	480	475	479	479	46
15°	458	456	451	453	452	129
25°	415	412	407	407	406	191
35°	357	354	349	346	344	223
45°	291	288	282	278	277	225
55°	220	219	214	209	207	197
65°	149	147	144	140	138	148
75°	80	78	76	74	74	84
85°	21	21	20	20	20	23
90°	1	5	12	13	13	2
95°	21	66	520	257	156	24
105°	75	108	418	900	897	80
115°	131	165	373	716	861	130
125°	183	217	371	610	687	163
135°	217	259	368	541	615	168
145°	250	287	366	456	502	157
155°	285	308	356	403	420	131
165°	310	320	341	361	367	88
175°	324	324	327	332	330	31
180°	324	324	324	324	324	



TEST NUMBER: P332516-930

CATALOG NUMBER: S124DIP-S350D810U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6
2.5°	482.8	482.7	482.4	482.2	482.0	481.5	480.8	480.0	479.3	478.5	479.2
5°	481.2	480.9	480.5	480.2	479.9	479.2	478.3	477.4	476.4	475.4	476.4
7.5°	476.8	476.4	476.1	475.7	475.4	474.7	473.6	472.6	471.6	470.5	471.2
10°	472.7	472.4	472.1	471.7	471.4	470.7	469.5	468.4	467.3	466.2	466.8
12.5°	467.5	467.2	466.8	466.4	466.1	465.4	464.1	463.0	461.8	460.6	461.4
15°	458.0	457.7	457.4	457.1	456.7	455.9	454.6	453.3	452.0	450.8	451.3
17.5°	446.7	446.3	445.9	445.5	445.0	444.2	443.0	441.7	440.5	439.3	439.6
20°	438.4	438.0	437.6	437.1	436.7	435.9	434.6	433.3	431.9	430.6	431.0
22.5°	429.4	428.8	428.3	427.7	427.1	426.2	424.9	423.7	422.4	421.1	421.6
25°	414.8	414.3	413.7	413.0	412.5	411.6	410.3	409.1	408.0	406.8	406.8
27.5°	398.2	397.5	397.0	396.3	395.7	394.8	393.7	392.6	391.5	390.4	390.2
30°	387.1	386.4	385.7	385.0	384.3	383.4	382.3	381.2	380.1	379.0	378.6
32.5°	375.4	374.7	374.1	373.5	372.8	371.9	370.8	369.6	368.4	367.2	366.8
35°	356.9	356.4	355.8	355.1	354.6	353.7	352.5	351.2	350.1	348.9	348.3
37.5°	337.6	337.0	336.5	336.0	335.4	334.5	333.2	331.9	330.6	329.3	328.6
40°	324.9	324.2	323.6	322.9	322.2	321.2	319.9	318.6	317.3	316.1	315.2
42.5°	311.4	311.0	310.5	310.1	309.7	308.8	307.4	305.9	304.5	303.1	302.1
45°	291.4	290.7	290.2	289.6	288.9	288.0	286.6	285.2	283.9	282.5	281.5
47.5°	270.4	270.0	269.6	269.2	268.8	268.0	266.7	265.4	264.2	262.9	261.8
50°	256.2	255.9	255.6	255.2	254.9	254.1	252.9	251.7	250.5	249.3	248.1
52.5°	242.4	241.9	241.5	241.1	240.7	239.9	238.6	237.3	236.0	234.8	233.7
55°	220.4	220.1	219.8	219.6	219.3	218.6	217.4	216.2	215.0	213.8	212.8
57.5°	199.3	199.1	198.8	198.5	198.2	197.5	196.2	195.1	193.9	192.7	191.8
60°	184.8	184.4	184.0	183.5	183.1	182.4	181.2	180.1	179.0	177.9	177.2
62.5°	170.6	170.3	169.9	169.6	169.2	168.4	167.2	166.1	164.9	163.7	163.0
65°	149.4	149.0	148.5	148.1	147.7	147.0	146.1	145.3	144.4	143.6	142.7
67.5°	127.9	127.5	127.1	126.7	126.3	125.7	124.9	124.1	123.3	122.4	121.6
70°	114.6	114.0	113.4	112.8	112.2	111.5	110.9	110.2	109.5	108.8	108.1
72.5°	100.4	99.8	99.2	98.7	98.0	97.4	96.9	96.4	95.8	95.2	94.7
75°	79.5	79.1	78.7	78.2	77.8	77.4	77.0	76.5	76.1	75.7	75.3
77.5°	59.5	59.4	59.1	58.9	58.8	58.5	58.1	57.7	57.3	57.0	56.8
80°	47.5	47.2	47.0	46.7	46.5	46.2	46.1	45.9	45.7	45.6	45.3
82.5°	35.7	35.6	35.5	35.4	35.2	35.1	35.1	35.1	35.1	35.1	35.0
85°	20.9	20.9	20.9	20.9	20.9	20.8	20.5	20.4	20.2	20.1	20.1
87.5°	8.2	8.3	8.6	8.7	8.8	8.7	9.4	9.3	9.5	9.7	9.5
90°	0.7	1.9	3.8	4.5	5.1	5.1	8.9	8.9	10.2	11.5	10.8
92.5°	7.3	10.6	16.6	24.4	33.7	46.9	79.3	128.7	177.0	202.2	168.4
95°	21.0	22.9	29.4	37.6	52.9	79.7	135.2	239.7	392.1	519.6	534.3
97.5°	37.7	37.7	43.2	50.9	64.0	86.4	129.1	215.5	367.0	547.2	671.2
100°	48.4	48.4	52.9	60.6	72.6	93.1	130.7	202.8	332.8	512.6	675.7
102.5°	58.6	59.7	63.6	70.8	82.3	101.7	135.7	199.2	309.8	469.2	637.5
105°	74.6	76.5	79.7	87.3	98.8	117.3	147.9	200.8	290.1	418.2	568.0
107.5°	92.2	93.4	96.6	104.8	115.8	134.0	162.1	210.3	286.5	389.6	511.9
110°	104.0	105.2	108.4	116.0	127.5	144.7	172.8	217.4	287.5	379.9	483.9



TEST NUMBER: P332516-930

CATALOG NUMBER: S124DIP-S350D810U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	115.1	116.4	120.1	127.3	138.7	156.0	183.0	225.0	290.6	375.4	468.1
115°	131.3	133.2	137.7	144.1	156.2	173.4	198.9	237.2	296.4	372.9	453.2
117.5°	148.1	149.9	153.9	160.9	172.3	190.1	214.3	249.5	302.7	372.3	446.6
120°	159.4	160.6	165.1	172.1	183.0	200.8	225.0	258.2	307.3	372.3	443.0
122.5°	169.6	170.9	175.3	181.8	193.6	211.0	235.2	266.4	311.9	371.8	439.0
125°	183.0	185.5	189.3	196.3	208.5	226.3	249.2	278.6	318.8	371.0	432.2
127.5°	194.9	196.9	201.5	209.5	222.1	240.1	262.3	289.2	324.2	369.7	423.1
130°	201.5	204.0	209.1	218.7	230.8	249.2	270.9	295.8	328.3	369.1	417.6
132.5°	208.1	210.1	216.8	225.8	239.0	256.4	278.1	302.4	331.9	368.6	412.5
135°	217.4	220.0	226.3	237.2	250.5	267.1	288.1	311.1	337.2	367.9	404.8
137.5°	226.7	229.1	236.1	246.5	260.3	276.1	295.8	317.2	340.4	367.7	398.2
140°	233.3	235.2	242.2	253.1	266.4	281.8	300.9	321.3	343.0	367.2	394.6
142.5°	240.4	242.4	248.9	259.2	272.1	286.9	305.5	324.3	345.0	367.2	391.6
145°	250.5	252.4	258.9	267.7	279.9	293.9	310.5	327.7	346.2	365.9	386.3
147.5°	261.9	262.5	268.2	277.3	287.4	300.0	315.6	330.6	346.8	363.6	381.6
150°	269.0	269.7	274.8	282.4	292.0	304.1	318.1	332.2	346.8	362.1	378.1
152.5°	275.7	275.8	280.9	288.0	296.6	307.7	320.2	333.1	345.8	359.5	374.0
155°	284.9	285.6	289.4	295.8	302.8	312.3	323.2	334.0	344.2	355.7	367.9
157.5°	294.0	294.0	297.6	302.6	308.7	316.2	325.4	334.0	342.6	351.8	361.6
160°	299.6	299.6	302.1	306.6	311.8	318.8	326.4	334.0	341.0	348.7	357.0
162.5°	304.8	304.2	306.2	310.2	314.8	320.2	327.4	334.0	339.6	345.7	352.9
165°	310.5	310.5	311.8	315.0	318.1	322.0	327.7	332.8	336.6	341.0	346.2
167.5°	316.2	315.6	316.2	318.6	320.4	323.3	327.6	331.3	333.5	336.5	340.1
170°	318.8	318.1	318.8	320.7	322.0	323.8	327.0	330.2	331.5	333.4	336.0
172.5°	321.3	320.7	320.8	322.2	322.9	324.3	326.5	329.2	329.5	330.4	332.4
175°	323.8	323.2	323.2	323.8	324.5	324.5	325.8	327.7	327.0	327.0	328.3
177.5°	325.0	324.5	324.0	324.5	324.5	324.5	325.0	326.0	325.0	325.0	325.5
180°	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5



TEST NUMBER: P332516-930

CATALOG NUMBER: S124DIP-S350D810U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6
2.5°	479.9	480.6	481.3	481.6	481.5	481.4	481.4	481.3
5°	477.4	478.3	479.2	479.6	479.4	479.2	479.1	478.9
7.5°	472.0	472.8	473.5	473.9	473.8	473.6	473.5	473.4
10°	467.6	468.2	469.0	469.2	469.0	468.8	468.6	468.5
12.5°	462.1	462.8	463.7	463.9	463.7	463.4	463.2	462.9
15°	451.8	452.2	452.8	452.9	452.7	452.4	452.2	451.9
17.5°	439.9	440.3	440.6	440.7	440.5	440.3	440.2	440.0
20°	431.2	431.5	431.7	431.8	431.5	431.4	431.2	431.0
22.5°	422.0	422.5	423.0	423.1	422.7	422.4	422.1	421.8
25°	406.9	407.0	407.1	407.0	406.6	406.3	405.9	405.6
27.5°	390.0	389.8	389.6	389.2	388.8	388.4	387.9	387.5
30°	378.3	378.0	377.6	377.2	376.7	376.3	375.9	375.5
32.5°	366.4	366.0	365.6	365.2	364.8	364.3	363.9	363.5
35°	347.6	347.1	346.4	345.9	345.5	345.1	344.6	344.2
37.5°	328.0	327.3	326.7	326.1	325.5	325.0	324.4	323.8
40°	314.4	313.5	312.7	312.0	311.5	311.1	310.7	310.3
42.5°	301.1	300.1	299.1	298.5	298.2	297.9	297.6	297.3
45°	280.6	279.6	278.8	278.1	277.9	277.6	277.4	277.1
47.5°	260.7	259.7	258.6	257.8	257.1	256.5	255.8	255.2
50°	246.9	245.7	244.5	243.6	243.1	242.6	242.1	241.6
52.5°	232.7	231.6	230.6	229.7	229.0	228.4	227.7	227.1
55°	211.7	210.7	209.7	208.9	208.4	207.9	207.3	206.8
57.5°	190.8	189.8	188.8	188.1	187.6	187.1	186.6	186.1
60°	176.3	175.6	174.8	174.2	173.8	173.3	172.9	172.5
62.5°	162.3	161.6	160.9	160.3	159.9	159.5	159.1	158.6
65°	141.9	141.0	140.1	139.5	139.1	138.6	138.2	137.8
67.5°	120.7	119.9	119.1	118.6	118.5	118.4	118.3	118.1
70°	107.5	106.8	106.1	105.6	105.3	105.1	104.8	104.6
72.5°	94.2	93.6	93.0	92.6	92.4	92.1	91.9	91.6
75°	74.9	74.6	74.3	74.0	73.9	73.9	73.8	73.7
77.5°	56.7	56.7	56.6	56.4	56.2	55.9	55.7	55.5
80°	45.2	45.0	44.8	44.8	44.6	44.5	44.4	44.4
82.5°	34.8	34.7	34.7	34.6	34.5	34.3	34.2	34.2
85°	20.1	20.1	20.1	20.1	20.0	19.9	19.7	19.6
87.5°	9.7	9.9	9.9	9.9	10.1	10.2	10.1	10.1
90°	11.5	12.1	12.7	12.7	13.4	14.0	13.4	13.4
92.5°	125.2	94.2	75.0	62.2	54.7	51.3	49.1	49.1
95°	472.4	373.6	288.1	226.3	195.1	175.3	163.9	155.6
97.5°	697.9	661.2	598.8	532.3	486.6	448.2	429.0	415.8
100°	768.8	781.5	750.3	703.2	647.7	608.8	589.7	584.6
102.5°	765.2	828.5	837.6	817.9	783.9	755.7	735.6	731.5
105°	714.0	824.3	887.4	913.5	914.8	909.7	900.8	897.0
107.5°	641.2	758.6	847.5	904.3	935.9	950.4	956.8	958.4
110°	597.4	707.6	800.1	870.2	915.4	942.2	953.7	959.4



TEST NUMBER: P332516-930

CATALOG NUMBER: S124DIP-S350D810U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	565.2	662.8	750.1	820.2	871.6	904.0	920.1	929.4
115°	533.0	611.4	685.9	747.1	797.5	835.8	856.1	861.3
117.5°	517.1	582.0	640.7	692.6	735.6	767.7	788.3	792.3
120°	510.0	569.3	620.3	665.5	701.9	729.9	746.5	753.5
122.5°	503.9	561.1	607.6	647.2	677.9	701.9	715.9	722.9
125°	493.4	548.3	592.2	627.3	652.8	671.3	683.4	687.2
127.5°	480.7	533.0	576.9	610.3	635.9	652.3	662.5	666.3
130°	470.5	520.8	564.2	597.9	624.1	640.1	650.3	654.1
132.5°	459.7	507.0	549.4	583.2	608.8	626.8	636.5	640.3
135°	445.0	486.4	525.3	557.2	582.7	600.5	610.7	614.6
137.5°	431.6	466.7	499.5	528.2	552.0	569.6	578.0	582.7
140°	424.0	453.9	482.6	509.4	531.7	545.7	554.6	559.7
142.5°	416.8	443.2	467.8	491.0	510.8	523.7	531.7	535.2
145°	406.8	428.4	447.5	465.4	481.4	492.1	498.6	501.7
147.5°	398.4	415.6	431.0	445.0	456.7	466.0	470.8	472.0
150°	393.3	408.0	420.8	432.2	442.5	450.7	454.5	455.2
152.5°	387.8	400.3	412.1	421.5	430.2	436.9	439.2	439.9
155°	379.3	389.6	399.1	406.8	413.1	418.2	420.1	420.1
157.5°	370.2	378.8	386.9	393.0	397.8	401.6	402.8	402.8
160°	364.7	371.7	378.7	383.8	387.6	391.4	392.1	392.1
162.5°	359.1	365.0	370.6	375.1	377.9	381.7	382.4	381.9
165°	351.2	355.1	359.5	362.7	365.3	367.9	367.2	366.6
167.5°	343.7	346.7	350.3	352.1	353.4	355.1	355.0	354.4
170°	339.2	341.0	343.6	345.5	346.8	347.4	346.8	346.8
172.5°	335.1	336.5	338.0	339.4	340.1	340.8	340.1	339.2
175°	329.6	330.2	331.5	331.5	331.5	332.8	331.5	330.2
177.5°	326.0	326.5	326.5	327.0	326.5	327.0	326.0	325.0
180°	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5

(END OF REPORT)