

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332569-930

Luminaire Tested: **S124DIP-S575D1035U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332569-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIP-S575D1035U930-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1035 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4954.2 lumens
Efficiency: N/A
Efficacy: 111.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 44.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332569-930

CATALOG NUMBER: S124DIP-S575D1035U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332569-930

CATALOG NUMBER: S124DIP-S575D1035U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	78	78	78	63	63	63	48	48	48	41
1	96	91	88	84	87	83	80	77	69	66	64	55	53	52	42	41	40	34
2	87	80	74	69	79	73	68	63	60	56	53	48	46	43	37	35	34	29
3	79	70	63	57	72	64	58	53	53	48	45	43	39	37	33	31	29	24
4	73	62	54	48	66	57	50	45	47	42	38	38	34	31	29	27	25	21
5	67	55	47	41	60	51	44	38	42	37	33	34	30	27	26	24	22	18
6	61	49	41	36	56	45	38	33	38	32	28	31	27	24	24	21	19	16
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17	14
8	53	40	33	28	48	37	30	26	31	26	22	25	22	19	20	17	15	13
9	49	37	29	24	45	34	27	23	29	23	20	23	20	17	19	16	14	11
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6391	6391	6391
5°	6412	6334	6380
10°	6370	6283	6314
15°	6294	6193	6209
20°	6192	6082	6088
25°	6075	5956	5940
30°	5931	5808	5754
35°	5784	5653	5577
40°	5630	5476	5376
45°	5469	5302	5200
50°	5291	5148	4987
55°	5098	4947	4787
60°	4907	4721	4579
65°	4690	4508	4327
70°	4447	4223	4057
75°	4077	3877	3780
80°	3626	3477	3394
85°	3168	3057	3001



TEST NUMBER: P332569-930

CATALOG NUMBER: S124DIP-S575D1035U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.6	1.5
10°-20°	210.1	4.2
20°-30°	309.2	6.2
30°-40°	359.5	7.3
40°-50°	359.5	7.3
50°-60°	314.5	6.3
60°-70°	233.5	4.7
70°-80°	132.7	2.7
80°-90°	41.4	0.8
90°-100°	69.4	1.4
100°-110°	205.6	4.1
110°-120°	348.9	7.0
120°-130°	460.1	9.3
130°-140°	516.7	10.4
140°-150°	507.8	10.2
150°-160°	427.1	8.6
160°-170°	284.1	5.7
170°-180°	99.5	2.0
0°-30°	593.9	12.0
0°-40°	953.4	19.2
0°-60°	1627.3	32.8
0°-90°	2034.9	41.1
90°-120°	623.9	12.6
90°-150°	2108.6	42.6
90°-180°	2919.0	58.9
0°-180°	4954.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	792	792	792	792	792	
5°	791	788	782	788	787	75
15°	753	750	741	744	743	212
25°	682	677	669	669	667	314
35°	587	582	574	569	566	367
45°	479	474	464	458	456	369
55°	362	360	352	344	340	324
65°	246	242	236	230	226	243
75°	131	128	124	122	121	139
85°	34	34	33	33	32	38
90°	2	11	18	23	24	5
95°	49	56	62	64	64	54
105°	190	191	194	196	198	201
115°	355	355	353	352	352	350
125°	517	517	516	514	513	460
135°	666	671	671	670	667	515
145°	810	813	814	813	810	507
155°	928	928	927	930	927	427
165°	1010	1008	1006	1010	1008	285
175°	1051	1047	1046	1051	1046	100
180°	1052	1052	1052	1052	1052	



TEST NUMBER: P332569-930

CATALOG NUMBER: S124DIP-S575D1035U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	791.7	791.7	791.7	791.7	791.7	791.7	791.7	791.7	791.7	791.7	791.7
2.5°	793.8	793.4	793.1	792.8	792.5	791.7	790.4	789.2	787.9	786.7	787.8
5°	791.2	790.6	790.0	789.5	788.9	787.8	786.3	784.7	783.2	781.6	783.2
7.5°	783.7	783.2	782.7	782.1	781.5	780.4	778.7	777.0	775.2	773.5	774.8
10°	777.1	776.7	776.1	775.5	774.9	773.7	771.9	770.1	768.3	766.4	767.5
12.5°	768.6	768.0	767.4	766.9	766.3	765.1	763.1	761.2	759.2	757.2	758.5
15°	753.1	752.5	752.0	751.4	750.8	749.5	747.4	745.3	743.1	741.0	741.8
17.5°	734.4	733.7	733.0	732.3	731.6	730.3	728.2	726.3	724.2	722.3	722.8
20°	720.7	720.0	719.3	718.6	717.9	716.5	714.4	712.2	710.1	708.0	708.4
22.5°	706.0	705.1	704.2	703.2	702.3	700.7	698.6	696.5	694.4	692.3	693.1
25°	682.0	681.0	680.0	679.1	678.1	676.6	674.6	672.6	670.7	668.7	668.9
27.5°	654.6	653.6	652.6	651.6	650.5	649.1	647.3	645.5	643.6	641.8	641.5
30°	636.3	635.2	634.1	632.9	631.9	630.3	628.5	626.6	624.8	623.1	622.5
32.5°	617.0	616.0	615.0	614.0	613.0	611.5	609.6	607.6	605.7	603.7	603.1
35°	586.9	585.9	584.9	583.9	582.9	581.4	579.4	577.5	575.5	573.6	572.5
37.5°	555.0	554.1	553.2	552.3	551.4	549.9	547.8	545.7	543.6	541.4	540.4
40°	534.2	533.0	531.9	530.8	529.7	528.1	525.9	523.8	521.7	519.6	518.2
42.5°	511.8	511.2	510.5	509.8	509.2	507.6	505.3	503.0	500.6	498.3	496.7
45°	479.0	478.0	477.0	476.1	475.1	473.4	471.2	468.9	466.7	464.4	462.8
47.5°	444.6	443.9	443.3	442.5	441.9	440.5	438.5	436.3	434.2	432.2	430.4
50°	421.3	420.7	420.1	419.6	419.0	417.8	415.8	413.8	411.8	409.9	407.9
52.5°	398.4	397.8	397.1	396.4	395.7	394.4	392.2	390.2	388.1	386.0	384.3
55°	362.2	361.8	361.4	361.0	360.6	359.4	357.4	355.4	353.4	351.5	349.8
57.5°	327.8	327.3	326.8	326.3	325.8	324.7	322.7	320.7	318.8	316.8	315.2
60°	303.9	303.2	302.5	301.7	301.1	299.8	298.0	296.1	294.3	292.4	291.2
62.5°	280.5	280.0	279.3	278.8	278.2	276.9	275.0	273.0	271.1	269.1	268.0
65°	245.5	244.8	244.1	243.4	242.7	241.7	240.3	238.8	237.4	236.0	234.6
67.5°	210.3	209.6	209.0	208.3	207.7	206.7	205.3	204.0	202.6	201.2	199.9
70°	188.4	187.4	186.5	185.5	184.5	183.4	182.3	181.2	180.0	178.9	177.8
72.5°	165.1	164.1	163.1	162.1	161.1	160.2	159.3	158.4	157.5	156.5	155.6
75°	130.7	130.0	129.3	128.6	127.8	127.2	126.5	125.7	125.1	124.3	123.8
77.5°	97.8	97.5	97.2	96.9	96.6	96.1	95.5	94.9	94.2	93.7	93.4
80°	78.0	77.6	77.2	76.8	76.3	76.0	75.7	75.4	75.2	74.8	74.6
82.5°	58.8	58.5	58.4	58.1	58.0	57.8	57.8	57.7	57.6	57.6	57.4
85°	34.2	34.2	34.2	34.2	34.2	34.1	33.8	33.6	33.3	33.0	33.0
87.5°	13.7	13.9	14.3	14.5	14.8	15.1	15.2	15.4	15.6	15.7	16.0
90°	2.4	4.4	6.4	8.4	10.4	12.1	13.5	15.0	16.5	17.9	19.0
92.5°	17.4	19.7	21.9	24.2	26.5	28.2	29.2	30.2	31.2	32.2	32.9
95°	48.8	50.5	52.1	53.7	55.4	56.7	58.0	59.4	60.6	61.9	62.4
97.5°	85.3	86.6	87.9	89.2	90.5	91.9	93.4	94.8	96.4	97.8	98.5
100°	113.9	114.6	115.4	116.1	116.8	118.0	119.6	121.2	122.9	124.5	124.9
102.5°	143.9	144.1	144.5	144.7	145.0	145.9	147.4	148.9	150.3	151.9	152.4
105°	189.6	189.8	190.0	190.1	190.4	190.8	191.5	192.2	193.0	193.7	194.2
107.5°	237.7	237.8	238.1	238.3	238.5	238.6	238.8	238.9	239.0	239.1	239.6
110°	270.2	270.5	270.9	271.3	271.7	271.7	271.5	271.3	271.2	271.0	270.6



TEST NUMBER: P332569-930

CATALOG NUMBER: S124DIP-S575D1035U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	304.0	304.1	304.2	304.3	304.4	304.2	303.9	303.5	303.2	302.9	302.8
115°	354.8	354.8	354.8	354.8	354.8	354.7	354.2	353.9	353.5	353.2	353.0
117.5°	402.7	402.8	402.9	403.1	403.2	403.2	402.9	402.7	402.4	402.2	401.5
120°	434.6	435.3	436.0	436.8	437.5	437.6	437.0	436.4	435.9	435.4	434.5
122.5°	467.7	468.1	468.3	468.6	468.9	469.0	468.7	468.4	468.1	467.9	467.3
125°	516.7	516.7	516.7	516.7	516.7	516.7	516.5	516.3	516.1	515.9	515.6
127.5°	561.2	561.7	562.2	562.8	563.4	563.5	563.2	562.9	562.6	562.3	562.0
130°	592.4	593.0	593.5	594.0	594.6	594.8	594.8	594.8	594.8	594.8	594.5
132.5°	624.4	624.8	625.1	625.5	625.9	626.1	625.9	625.7	625.6	625.5	625.1
135°	666.5	667.6	668.6	669.8	670.8	671.4	671.4	671.4	671.4	671.4	671.0
137.5°	712.4	712.9	713.4	713.9	714.4	714.8	715.1	715.4	715.7	716.0	715.5
140°	743.0	743.3	743.7	744.0	744.4	744.6	744.6	744.6	744.6	744.6	744.4
142.5°	770.9	771.4	771.7	772.1	772.4	772.5	772.4	772.3	772.1	771.9	771.9
145°	809.7	810.4	811.1	811.9	812.6	813.0	813.3	813.4	813.6	813.8	813.6
147.5°	848.2	849.0	849.9	850.8	851.6	852.0	851.8	851.7	851.5	851.4	851.3
150°	871.6	872.3	873.0	873.8	874.5	874.8	874.8	874.8	874.8	874.8	874.8
152.5°	893.7	894.1	894.5	895.0	895.4	895.7	895.9	896.0	896.2	896.3	896.7
155°	927.7	927.7	927.7	927.7	927.7	927.6	927.4	927.2	927.1	926.9	927.6
157.5°	956.3	956.0	955.7	955.4	955.0	954.9	954.8	954.8	954.8	954.7	955.3
160°	973.3	973.1	972.9	972.7	972.6	972.4	972.2	972.0	971.8	971.7	972.2
162.5°	988.9	988.5	988.0	987.5	987.0	986.7	986.5	986.3	986.2	985.9	986.9
165°	1009.9	1009.3	1008.9	1008.3	1007.7	1007.3	1006.9	1006.6	1006.2	1005.8	1006.9
167.5°	1026.1	1025.2	1024.5	1023.8	1023.0	1022.6	1022.6	1022.7	1022.7	1022.8	1023.9
170°	1035.1	1034.2	1033.3	1032.4	1031.5	1031.1	1031.4	1031.5	1031.7	1031.8	1033.0
172.5°	1041.6	1040.9	1040.2	1039.3	1038.6	1038.2	1038.3	1038.3	1038.4	1038.4	1039.6
175°	1050.6	1049.7	1048.8	1047.9	1047.0	1046.4	1046.3	1046.0	1045.9	1045.7	1047.0
177.5°	1053.5	1052.8	1052.1	1051.3	1050.6	1050.3	1050.3	1050.3	1050.3	1050.3	1051.2
180°	1052.2	1052.2	1052.2	1052.2	1052.2	1052.2	1052.2	1052.2	1052.2	1052.2	1052.2



TEST NUMBER: P332569-930

CATALOG NUMBER: S124DIP-S575D1035U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	791.7	791.7	791.7	791.7	791.7	791.7	791.7	791.7
2.5°	789.0	790.1	791.2	791.7	791.6	791.5	791.4	791.2
5°	784.7	786.3	787.8	788.5	788.1	787.9	787.6	787.3
7.5°	776.0	777.2	778.4	779.0	778.9	778.7	778.5	778.3
10°	768.7	769.8	770.9	771.4	771.0	770.8	770.5	770.2
12.5°	759.8	761.0	762.2	762.6	762.2	761.8	761.5	761.1
15°	742.7	743.6	744.4	744.6	744.2	743.8	743.3	742.9
17.5°	723.3	723.8	724.4	724.5	724.2	723.9	723.7	723.4
20°	708.9	709.3	709.7	709.8	709.5	709.2	709.0	708.7
22.5°	693.8	694.6	695.4	695.5	695.0	694.5	694.0	693.4
25°	669.0	669.1	669.3	669.0	668.5	667.9	667.3	666.8
27.5°	641.2	640.7	640.4	639.9	639.2	638.5	637.8	637.1
30°	621.9	621.3	620.8	620.1	619.4	618.7	618.0	617.3
32.5°	602.3	601.7	601.0	600.3	599.7	598.9	598.2	597.5
35°	571.5	570.5	569.6	568.8	568.0	567.3	566.6	565.9
37.5°	539.3	538.2	537.1	536.1	535.2	534.3	533.4	532.4
40°	516.8	515.4	514.0	512.9	512.2	511.5	510.8	510.1
42.5°	495.0	493.3	491.7	490.6	490.2	489.8	489.3	488.8
45°	461.3	459.7	458.2	457.2	456.8	456.4	455.9	455.5
47.5°	428.7	426.9	425.2	423.8	422.7	421.6	420.5	419.5
50°	405.9	403.9	401.9	400.6	399.7	398.8	398.0	397.1
52.5°	382.5	380.7	379.0	377.6	376.5	375.4	374.4	373.3
55°	348.1	346.4	344.7	343.4	342.6	341.8	340.9	340.1
57.5°	313.6	312.0	310.4	309.2	308.3	307.5	306.7	305.9
60°	289.9	288.7	287.4	286.4	285.7	285.0	284.3	283.6
62.5°	266.8	265.6	264.5	263.6	262.9	262.2	261.5	260.7
65°	233.2	231.8	230.4	229.3	228.6	227.9	227.2	226.5
67.5°	198.5	197.2	195.8	195.0	194.9	194.7	194.4	194.3
70°	176.7	175.5	174.4	173.7	173.2	172.8	172.4	171.9
72.5°	154.7	153.8	153.0	152.3	151.9	151.5	151.1	150.6
75°	123.2	122.6	122.1	121.7	121.6	121.5	121.3	121.2
77.5°	93.3	93.1	92.9	92.7	92.3	92.0	91.6	91.2
80°	74.3	74.0	73.7	73.5	73.4	73.2	73.1	73.0
82.5°	57.2	57.1	56.9	56.7	56.7	56.5	56.3	56.2
85°	33.0	33.0	33.0	32.9	32.8	32.6	32.5	32.4
87.5°	16.2	16.4	16.6	16.8	16.9	17.0	17.0	17.0
90°	20.1	21.2	22.3	23.0	23.3	23.7	24.1	24.4
92.5°	33.5	34.2	34.8	35.3	35.5	35.7	36.0	36.1
95°	62.9	63.5	64.0	64.3	64.3	64.3	64.3	64.3
97.5°	99.1	99.8	100.4	100.8	100.8	100.8	100.8	100.8
100°	125.2	125.6	126.0	126.1	126.1	126.1	126.1	126.1
102.5°	152.9	153.4	153.8	154.2	154.3	154.5	154.7	154.7
105°	194.8	195.3	195.8	196.4	196.9	197.5	198.0	198.5
107.5°	240.1	240.6	241.1	241.3	241.3	241.2	241.2	241.2
110°	270.3	269.9	269.5	269.6	270.2	270.7	271.3	271.8



TEST NUMBER: P332569-930

CATALOG NUMBER: S124DIP-S575D1035U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	302.7	302.6	302.6	302.6	302.7	302.8	303.0	303.0
115°	352.8	352.6	352.5	352.3	352.1	351.9	351.7	351.6
117.5°	401.0	400.3	399.7	399.3	398.8	398.5	398.1	397.8
120°	433.6	432.7	431.8	431.5	431.9	432.2	432.6	432.9
122.5°	466.7	466.1	465.5	464.8	464.1	463.5	462.8	462.2
125°	515.2	514.9	514.5	514.1	513.8	513.4	513.1	512.7
127.5°	561.6	561.3	560.8	560.5	560.3	559.9	559.7	559.4
130°	594.2	593.8	593.5	592.9	592.2	591.4	590.7	590.0
132.5°	624.8	624.4	624.0	623.7	623.4	623.1	622.8	622.6
135°	670.7	670.3	669.9	669.4	669.0	668.4	667.8	667.3
137.5°	715.0	714.5	714.1	713.9	714.0	714.1	714.2	714.4
140°	744.3	744.0	743.9	743.7	743.6	743.3	743.1	743.0
142.5°	771.8	771.8	771.8	771.8	771.8	771.7	771.7	771.6
145°	813.4	813.3	813.0	812.7	812.1	811.6	811.1	810.5
147.5°	851.1	850.9	850.8	850.6	850.4	850.3	850.1	849.9
150°	874.8	874.8	874.8	874.7	874.6	874.3	874.2	874.0
152.5°	897.2	897.6	898.1	898.1	897.6	897.1	896.6	896.1
155°	928.4	929.0	929.8	929.8	929.0	928.4	927.6	926.9
157.5°	955.8	956.3	956.9	956.8	956.3	955.6	955.0	954.4
160°	972.7	973.3	973.8	973.6	972.7	971.8	970.9	970.0
162.5°	987.9	988.9	989.9	989.9	989.0	988.1	987.2	986.3
165°	1008.0	1009.1	1010.2	1010.3	1009.7	1008.9	1008.2	1007.5
167.5°	1024.9	1026.1	1027.1	1027.1	1026.0	1024.8	1023.7	1022.6
170°	1034.0	1035.1	1036.2	1036.1	1034.9	1033.6	1032.3	1031.0
172.5°	1040.8	1042.0	1043.3	1043.3	1042.0	1040.7	1039.5	1038.2
175°	1048.2	1049.5	1050.8	1050.8	1049.5	1048.2	1047.0	1045.7
177.5°	1052.3	1053.3	1054.3	1054.3	1053.1	1051.9	1050.8	1049.6
180°	1052.2	1052.2	1052.2	1052.2	1052.2	1052.2	1052.2	1052.2

(END OF REPORT)