

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332310-940

Luminaire Tested: **S123RDIP-S775D585U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332310-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S775D585U940-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 585 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4396.6 lumens
Efficiency: N/A
Efficacy: 109.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 40.3
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332310-940

CATALOG NUMBER: S123RDIP-S775D585U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332310-940

CATALOG NUMBER: S123RDIP-S775D585U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	109	109	109	109	102	102	102	102	88	88	88		76	76	76		65	65	65	59
1	100	96	92	89	93	90	87	84	78	76	74		68	66	64		58	56	55	51
2	92	84	78	73	85	79	74	69	69	65	61		60	57	54		51	49	47	43
3	84	74	67	61	78	70	63	58	61	56	52		53	49	46		46	43	41	37
4	77	66	58	52	72	62	55	50	55	49	45		48	43	40		41	38	35	32
5	71	59	51	45	66	56	48	43	49	43	39		43	38	35		37	34	31	28
6	65	53	45	39	61	50	43	38	44	39	34		39	34	31		34	30	27	25
7	60	48	40	35	56	46	38	33	40	35	30		36	31	27		31	27	24	22
8	56	44	36	31	52	42	34	30	37	31	27		33	28	25		29	25	22	20
9	52	40	33	28	49	38	31	27	34	28	24		30	25	22		26	23	20	18
10	49	37	30	25	46	35	28	24	31	26	22		28	23	20		25	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12392	12392	12392
5°	12440	12268	12338
10°	12369	12114	12073
15°	12237	11830	11705
20°	12054	11475	11208
25°	11866	11077	10723
30°	11616	10618	10038
35°	11361	10159	9410
40°	11126	9617	8633
45°	10816	9082	7931
50°	10474	8473	7145
55°	10128	7781	6412
60°	9810	7035	5608
65°	9393	6230	4804
70°	8875	5231	3877
75°	8114	4117	3647
80°	7234	3651	3353
85°	6113	3223	3001



TEST NUMBER: P332310-940

CATALOG NUMBER: S123RDIP-S775D585U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	108.1	2.5
10°-20°	300.8	6.8
20°-30°	433.1	9.9
30°-40°	487.9	11.1
40°-50°	466.7	10.6
50°-60°	382.2	8.7
60°-70°	257.9	5.9
70°-80°	129.7	3.0
80°-90°	36.2	0.8
90°-100°	42.2	1.0
100°-110°	126.2	2.9
110°-120°	214.7	4.9
120°-130°	282.4	6.4
130°-140°	317.5	7.2
140°-150°	312.1	7.1
150°-160°	262.7	6.0
160°-170°	174.9	4.0
170°-180°	61.2	1.4
0°-30°	842.0	19.2
0°-40°	1329.9	30.2
0°-60°	2178.8	49.6
0°-90°	2602.7	59.2
90°-120°	383.2	8.7
90°-150°	1295.1	29.5
90°-180°	1794.0	40.8
0°-180°	4396.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1151	1151	1151	1151	1151	
5°	1151	1146	1135	1143	1142	109
15°	1098	1087	1062	1057	1050	309
25°	999	975	933	914	903	459
35°	865	830	773	734	716	541
45°	710	667	597	545	521	548
55°	540	492	415	362	342	484
65°	369	316	245	201	189	365
75°	195	150	99	90	88	208
85°	50	30	26	24	24	56
90°	0	6	12	14	15	4
95°	30	34	38	40	40	34
105°	114	116	120	120	121	123
115°	216	218	217	217	217	214
125°	316	318	317	315	313	282
135°	410	413	413	411	410	316
145°	498	499	500	500	498	311
155°	570	570	571	572	569	262
165°	621	620	620	622	619	175
175°	646	644	644	647	643	61
180°	648	648	648	648	648	



TEST NUMBER: P332310-940

CATALOG NUMBER: S123RDIP-S775D585U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1151.3	1151.3	1151.3	1151.3	1151.3	1151.3	1151.3	1151.3	1151.3	1151.3	1151.3
2.5°	1154.9	1154.3	1153.6	1153.0	1152.4	1151.0	1149.0	1147.0	1145.0	1143.0	1144.9
5°	1151.3	1150.2	1149.1	1148.2	1147.1	1145.3	1142.8	1140.3	1137.8	1135.4	1137.2
7.5°	1140.6	1139.5	1138.4	1137.2	1136.1	1133.9	1130.7	1127.5	1124.3	1121.0	1122.0
10°	1131.7	1130.2	1128.7	1127.3	1125.8	1123.2	1119.5	1115.8	1112.1	1108.3	1108.5
12.5°	1118.9	1117.3	1115.7	1114.1	1112.5	1109.4	1104.8	1100.3	1095.6	1091.1	1091.0
15°	1098.1	1095.7	1093.4	1091.2	1088.9	1084.9	1079.1	1073.3	1067.4	1061.6	1060.6
17.5°	1071.7	1069.1	1066.4	1063.7	1061.0	1056.1	1048.7	1041.3	1033.8	1026.5	1024.3
20°	1052.3	1048.9	1045.6	1042.3	1039.0	1033.4	1025.5	1017.6	1009.8	1001.8	999.2
22.5°	1030.6	1026.8	1023.0	1019.1	1015.3	1009.2	1000.9	992.5	984.1	975.7	972.3
25°	999.1	993.9	988.6	983.5	978.3	970.9	961.4	951.8	942.3	932.7	928.4
27.5°	960.7	955.0	949.3	943.6	937.9	929.7	919.1	908.5	897.8	887.2	881.1
30°	934.6	928.4	922.2	916.0	909.7	900.8	889.2	877.5	865.9	854.3	847.3
32.5°	908.5	901.4	894.4	887.3	880.3	870.6	858.3	846.1	833.7	821.4	813.8
35°	864.6	857.1	849.6	842.2	834.7	824.6	811.7	798.8	786.0	773.1	764.2
37.5°	820.2	811.8	803.5	795.2	786.9	776.0	762.2	748.5	734.8	721.0	710.9
40°	791.8	782.7	773.5	764.4	755.3	743.3	728.6	713.9	699.1	684.4	673.6
42.5°	759.6	750.6	741.4	732.3	723.2	711.0	695.7	680.5	665.3	650.1	638.3
45°	710.5	701.2	691.9	682.5	673.2	660.6	644.5	628.6	612.6	596.6	584.8
47.5°	661.5	651.2	641.0	630.7	620.5	607.3	591.4	575.3	559.4	543.4	530.6
50°	625.5	615.8	606.1	596.3	586.6	573.3	556.5	539.7	522.9	506.0	493.2
52.5°	593.4	582.9	572.3	561.7	551.2	537.5	520.8	504.3	487.6	470.9	457.6
55°	539.7	529.5	519.3	509.2	499.0	485.1	467.4	449.9	432.2	414.6	402.5
57.5°	490.0	478.9	467.9	456.7	445.7	431.3	413.6	395.8	378.1	360.4	349.0
60°	455.7	444.3	432.8	421.4	410.0	395.7	378.4	361.2	344.0	326.8	315.6
62.5°	421.2	409.8	398.4	387.0	375.7	361.3	344.1	326.9	309.7	292.4	281.9
65°	368.8	357.4	346.0	334.6	323.2	309.3	293.2	277.0	260.8	244.6	234.4
67.5°	316.4	304.8	293.3	281.7	270.2	256.6	241.1	225.6	210.1	194.6	187.0
70°	282.0	270.8	259.6	248.3	237.2	224.3	209.7	195.3	180.7	166.2	158.9
72.5°	247.6	236.6	225.5	214.5	203.5	191.4	178.2	165.0	151.8	138.6	132.6
75°	195.1	185.2	175.2	165.2	155.3	144.6	133.2	121.8	110.4	99.0	96.9
77.5°	147.3	138.3	129.3	120.3	111.3	103.2	95.8	88.5	81.1	73.7	72.7
80°	116.7	108.2	99.7	91.2	82.7	76.2	71.9	67.5	63.2	58.9	58.2
82.5°	87.6	80.3	72.9	65.5	58.2	53.5	51.5	49.4	47.4	45.4	44.8
85°	49.5	44.9	40.4	35.8	31.2	28.6	28.0	27.4	26.8	26.1	25.8
87.5°	18.0	16.4	14.8	13.2	11.6	11.0	11.2	11.6	11.9	12.1	12.0
90°	0.5	1.6	2.8	3.9	5.0	6.3	7.8	9.3	10.7	12.2	12.7
92.5°	12.3	13.1	13.8	14.6	15.4	16.2	17.0	17.8	18.7	19.5	19.9
95°	30.1	30.8	31.6	32.4	33.2	34.1	35.0	35.8	36.7	37.6	38.1
97.5°	53.3	53.9	54.5	55.1	55.6	56.3	56.9	57.6	58.2	58.9	59.4
100°	69.2	69.8	70.5	71.2	71.9	72.5	73.0	73.7	74.2	74.7	75.1
102.5°	87.5	87.9	88.3	88.7	89.1	89.7	90.4	91.2	91.9	92.6	93.0
105°	114.4	114.7	114.9	115.1	115.4	115.9	117.0	118.0	119.0	120.0	120.0
107.5°	145.8	145.9	146.1	146.2	146.3	146.6	147.0	147.4	147.8	148.2	148.6
110°	165.3	165.5	165.8	165.9	166.2	166.4	166.7	166.9	167.1	167.4	167.8



TEST NUMBER: P332310-940

CATALOG NUMBER: S123RDIP-S775D585U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	185.7	185.7	185.9	186.0	186.2	186.3	186.4	186.4	186.5	186.5	187.0
115°	216.2	216.5	216.9	217.2	217.5	217.6	217.3	217.1	216.9	216.7	216.8
117.5°	246.9	247.1	247.4	247.5	247.8	247.7	247.4	247.2	246.9	246.6	246.6
120°	266.0	266.7	267.3	268.0	268.8	268.8	268.2	267.7	267.1	266.5	266.4
122.5°	286.0	286.4	287.0	287.4	287.9	288.0	287.8	287.5	287.1	286.9	286.6
125°	316.4	316.7	317.0	317.4	317.7	317.8	317.5	317.4	317.1	316.9	316.4
127.5°	344.5	345.2	345.9	346.6	347.3	347.6	347.3	347.1	346.8	346.6	346.0
130°	363.2	364.1	365.0	365.9	366.8	367.0	366.8	366.4	366.0	365.7	365.2
132.5°	381.8	382.8	383.7	384.6	385.5	385.8	385.6	385.3	385.0	384.9	384.2
135°	410.5	411.2	411.8	412.5	413.1	413.5	413.3	413.2	413.1	413.0	412.6
137.5°	436.9	437.5	438.0	438.6	439.2	439.6	439.9	440.1	440.5	440.8	440.3
140°	455.2	455.8	456.4	456.9	457.4	457.8	457.9	458.1	458.2	458.3	458.2
142.5°	471.9	472.4	473.1	473.6	474.1	474.6	474.7	474.9	475.2	475.4	475.3
145°	497.9	498.2	498.4	498.6	498.8	499.1	499.4	499.8	500.2	500.5	500.3
147.5°	520.8	521.1	521.6	521.9	522.4	522.7	523.1	523.3	523.7	524.0	524.0
150°	536.6	536.8	537.1	537.3	537.5	537.7	538.0	538.1	538.4	538.6	538.6
152.5°	549.7	549.9	550.3	550.5	550.9	551.1	551.3	551.3	551.5	551.6	551.8
155°	570.2	570.2	570.2	570.2	570.2	570.2	570.3	570.4	570.6	570.7	571.1
157.5°	587.6	587.5	587.4	587.3	587.1	587.1	587.2	587.3	587.4	587.5	587.9
160°	598.6	598.4	598.2	598.0	597.7	597.6	597.6	597.6	597.6	597.6	598.2
162.5°	608.4	608.1	607.8	607.4	607.2	607.1	607.2	607.3	607.3	607.4	608.0
165°	621.0	620.7	620.4	620.0	619.6	619.5	619.5	619.5	619.5	619.5	620.2
167.5°	631.1	630.6	630.2	629.7	629.3	629.1	629.2	629.3	629.4	629.5	630.2
170°	636.8	636.3	635.9	635.4	635.0	634.7	634.7	634.7	634.7	634.7	635.5
172.5°	641.2	640.8	640.3	639.9	639.4	639.3	639.3	639.3	639.3	639.3	640.0
175°	646.0	645.5	645.1	644.6	644.2	643.9	643.9	643.9	643.9	643.9	644.6
177.5°	647.9	647.6	647.2	646.8	646.4	646.2	646.2	646.2	646.2	646.2	646.8
180°	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5



TEST NUMBER: P332310-940

CATALOG NUMBER: S123RDIP-S775D585U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1151.3	1151.3	1151.3	1151.3	1151.3	1151.3	1151.3	1151.3
2.5°	1146.7	1148.5	1150.3	1151.1	1150.8	1150.4	1150.0	1149.8
5°	1139.1	1140.9	1142.8	1143.5	1143.2	1142.7	1142.3	1141.9
7.5°	1123.1	1124.1	1125.2	1125.3	1124.6	1123.9	1123.2	1122.5
10°	1108.8	1108.9	1109.1	1108.8	1107.7	1106.6	1105.6	1104.6
12.5°	1090.8	1090.7	1090.7	1089.9	1088.8	1087.5	1086.4	1085.1
15°	1059.5	1058.5	1057.5	1056.2	1054.8	1053.3	1051.9	1050.4
17.5°	1022.1	1019.9	1017.7	1015.6	1013.3	1011.2	1009.1	1006.9
20°	996.5	993.7	991.0	988.5	986.0	983.5	981.0	978.5
22.5°	969.0	965.6	962.2	959.4	957.1	954.8	952.4	950.1
25°	924.1	919.7	915.3	912.0	909.7	907.4	905.2	902.9
27.5°	875.0	869.1	863.0	858.2	854.7	851.2	847.7	844.3
30°	840.3	833.1	826.1	820.9	817.6	814.3	810.9	807.6
32.5°	806.0	798.3	790.6	785.0	781.5	778.0	774.5	771.1
35°	755.3	746.4	737.4	731.1	727.4	723.6	719.9	716.1
37.5°	700.7	690.6	680.5	673.2	668.5	663.9	659.3	654.7
40°	662.8	652.0	641.2	633.5	628.7	623.9	619.1	614.4
42.5°	626.4	614.7	602.9	594.9	590.6	586.3	582.0	577.7
45°	573.0	561.2	549.3	540.9	535.9	530.9	526.0	521.0
47.5°	517.6	504.8	492.0	483.3	478.8	474.4	470.0	465.6
50°	480.4	467.4	454.6	445.8	441.0	436.2	431.5	426.7
52.5°	444.3	430.9	417.5	408.7	404.4	400.1	395.8	391.6
55°	390.5	378.4	366.4	358.3	354.2	350.0	345.9	341.7
57.5°	337.7	326.3	315.0	307.5	304.0	300.4	296.9	293.4
60°	304.3	293.2	282.0	274.6	271.1	267.5	264.0	260.5
62.5°	271.3	260.8	250.3	243.2	239.4	235.8	232.1	228.4
65°	224.3	214.1	203.9	197.7	195.5	193.1	190.9	188.6
67.5°	179.4	171.8	164.2	159.2	156.8	154.3	151.9	149.4
70°	151.7	144.4	137.1	132.4	130.1	127.8	125.6	123.2
72.5°	126.7	120.7	114.9	111.4	110.4	109.5	108.5	107.5
75°	94.8	92.7	90.7	89.4	89.0	88.6	88.2	87.7
77.5°	71.5	70.4	69.3	68.5	68.1	67.7	67.2	66.9
80°	57.6	57.0	56.4	55.8	55.4	55.0	54.6	54.1
82.5°	44.1	43.5	42.9	42.5	42.4	42.4	42.3	42.2
85°	25.3	24.9	24.5	24.3	24.3	24.3	24.3	24.3
87.5°	12.0	11.9	11.9	11.8	11.6	11.5	11.4	11.2
90°	13.1	13.6	14.0	14.4	14.6	14.8	15.1	15.2
92.5°	20.2	20.6	21.0	21.1	21.0	20.8	20.7	20.5
95°	38.5	39.0	39.4	39.7	39.7	39.7	39.7	39.7
97.5°	59.9	60.5	61.0	61.2	61.2	61.1	61.1	61.0
100°	75.4	75.8	76.2	76.4	76.6	76.9	77.0	77.3
102.5°	93.4	93.7	94.0	94.2	94.2	94.1	94.1	94.0
105°	120.0	120.0	120.0	120.1	120.4	120.6	120.8	121.1
107.5°	148.9	149.3	149.6	149.8	149.6	149.5	149.4	149.3
110°	168.3	168.7	169.2	169.2	169.1	168.8	168.6	168.4



TEST NUMBER: P332310-940

CATALOG NUMBER: S123RDIP-S775D585U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	187.5	188.1	188.6	188.9	188.9	188.8	188.8	188.7
115°	216.9	217.0	217.1	217.1	217.0	216.9	216.8	216.7
117.5°	246.6	246.5	246.5	246.3	246.0	245.7	245.4	245.0
120°	266.3	266.2	266.1	265.9	265.6	265.5	265.2	265.0
122.5°	286.2	286.0	285.7	285.3	285.1	284.7	284.5	284.1
125°	315.9	315.5	315.0	314.6	314.1	313.7	313.3	312.8
127.5°	345.3	344.6	344.0	343.5	343.0	342.4	341.9	341.3
130°	364.8	364.4	363.9	363.3	362.5	361.7	360.9	360.1
132.5°	383.7	383.2	382.6	382.1	381.5	380.8	380.2	379.6
135°	412.1	411.6	411.2	410.8	410.6	410.4	410.2	409.9
137.5°	439.8	439.3	438.9	438.5	438.0	437.6	437.1	436.7
140°	458.1	457.9	457.8	457.4	456.6	455.8	455.0	454.2
142.5°	475.1	475.0	474.9	474.6	473.9	473.3	472.7	472.1
145°	500.2	500.2	500.1	499.7	499.3	498.8	498.4	497.9
147.5°	524.0	524.0	524.0	523.6	523.0	522.3	521.7	520.9
150°	538.6	538.6	538.6	538.3	537.6	536.9	536.3	535.6
152.5°	552.1	552.2	552.4	552.1	551.6	551.0	550.5	549.8
155°	571.6	572.0	572.5	572.3	571.5	570.7	570.0	569.2
157.5°	588.4	588.9	589.3	589.2	588.6	588.0	587.4	586.7
160°	598.8	599.3	599.9	599.9	599.5	599.1	598.6	598.2
162.5°	608.5	609.1	609.7	609.6	608.9	608.1	607.4	606.7
165°	620.9	621.5	622.2	622.1	621.3	620.5	619.8	619.0
167.5°	630.9	631.6	632.3	632.3	631.6	630.9	630.2	629.5
170°	636.3	637.1	637.9	637.9	637.1	636.3	635.5	634.7
172.5°	640.6	641.3	642.0	642.0	641.2	640.4	639.6	638.8
175°	645.2	646.0	646.7	646.6	645.8	645.0	644.2	643.4
177.5°	647.4	647.9	648.5	648.4	647.7	647.1	646.5	645.9
180°	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5

(END OF REPORT)