

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332312-940

Luminaire Tested: **S123RDIP-S775D805U940-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332312-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S775D805U940-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 805 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5579.5 lumens
Efficiency: N/A
Efficacy: 121.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332312-940

CATALOG NUMBER: S123RDIP-S775D805U940-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332312-940

CATALOG NUMBER: S123RDIP-S775D805U940-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49
1	98	94	90	87	90	87	84	81	73	71	69	61	59	58	49	48	47	42
2	90	83	77	72	83	77	71	67	65	61	58	54	52	49	44	42	41	36
3	82	73	66	61	76	68	62	57	58	53	49	48	45	42	40	37	35	31
4	75	65	58	52	69	60	54	49	52	47	43	43	40	37	36	33	31	27
5	69	58	50	45	64	54	47	42	46	41	37	39	35	32	32	30	27	24
6	64	52	45	39	59	49	42	37	42	37	33	36	32	28	30	27	24	21
7	59	47	40	34	55	44	37	33	38	33	29	33	28	25	27	24	22	19
8	55	43	36	31	51	40	34	29	35	30	26	30	26	23	25	22	20	17
9	51	40	32	27	47	37	30	26	32	27	23	28	23	20	23	20	18	16
10	48	36	29	25	44	34	28	23	30	25	21	25	21	19	22	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11739	11739	11739	11739
5°	13993	11788	10381	11788
10°	17472	11721	9379	11721
15°	20508	11602	8553	11602
20°	22888	11423	7851	11423
25°	22523	11233	7418	11233
30°	16189	11059	6975	11059
35°	10809	10834	6687	10834
40°	7964	10561	6389	10561
45°	6680	10085	6098	10085
50°	5894	9460	5690	9460
55°	5168	8743	5134	8743
60°	4603	8060	4704	8060
65°	4042	7325	4376	7325
70°	3175	6672	3997	6672
75°	2795	5827	3647	5827
80°	2430	4947	3589	4947
85°	1964	3977	3816	3977



TEST NUMBER: P332312-940

CATALOG NUMBER: S123RDIP-S775D805U940-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	107.2	1.9
10°-20°	335.1	6.0
20°-30°	526.4	9.4
30°-40°	549.2	9.8
40°-50°	470.0	8.4
50°-60°	358.2	6.4
60°-70°	229.6	4.1
70°-80°	110.5	2.0
80°-90°	31.9	0.6
90°-100°	34.1	0.6
100°-110°	162.6	2.9
110°-120°	390.6	7.0
120°-130°	497.3	8.9
130°-140°	531.4	9.5
140°-150°	496.9	8.9
150°-160°	400.8	7.2
160°-170°	258.7	4.6
170°-180°	89.2	1.6
0°-30°	968.7	17.4
0°-40°	1517.9	27.2
0°-60°	2346.1	42.0
0°-90°	2718.0	48.7
90°-120°	587.3	10.5
90°-150°	2112.9	37.9
90°-180°	2862.0	51.3
0°-180°	5579.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1091	1091	1091	1091	1091	
5°	1295	1091	961	1091	1295	134
15°	1840	1041	768	1041	1840	522
25°	1896	946	625	946	1896	815
35°	823	824	509	824	823	539
45°	439	662	401	662	439	345
55°	275	466	274	466	275	249
65°	159	288	172	288	159	156
75°	67	140	88	140	67	72
85°	16	32	31	32	16	19
90°	21	1	21	1	21	10
95°	26	42	26	42	26	22
105°	31	208	31	208	31	70
115°	410	390	410	390	410	379
125°	560	549	560	549	560	501
135°	691	684	691	684	691	533
145°	797	789	797	789	797	497
155°	868	869	868	869	868	400
165°	915	917	915	917	915	258
175°	935	938	935	938	935	89
180°	938	938	938	938	938	



TEST NUMBER: P332312-940

CATALOG NUMBER: S123RDIP-S775D805U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6
2.5°	1161.5	1163.1	1158.2	1157.4	1151.8	1150.3	1150.3	1142.5	1137.6	1131.3	1127.6
5°	1295.0	1302.5	1298.8	1290.4	1276.4	1273.1	1264.3	1250.3	1234.4	1214.8	1205.4
7.5°	1461.8	1472.0	1468.1	1455.1	1440.5	1428.6	1403.6	1380.3	1347.7	1319.1	1294.7
10°	1598.5	1587.8	1579.4	1566.7	1553.3	1531.2	1505.1	1469.2	1427.6	1395.0	1358.5
12.5°	1700.8	1699.1	1688.5	1675.4	1656.4	1635.5	1603.4	1559.6	1511.3	1464.1	1422.5
15°	1840.3	1843.2	1836.1	1822.6	1795.5	1758.6	1710.1	1691.8	1622.8	1571.5	1520.1
17.5°	1936.9	1936.4	1935.4	1916.6	1889.0	1862.8	1817.8	1769.9	1707.3	1635.0	1565.8
20°	1998.1	1993.5	1994.4	1973.4	1952.8	1922.5	1878.7	1809.1	1757.7	1674.2	1602.7
22.5°	1996.6	1995.7	1999.3	1992.1	1977.1	1953.9	1919.3	1860.6	1795.1	1710.7	1630.3
25°	1896.4	1892.7	1914.6	1920.7	1944.5	1948.7	1938.4	1906.2	1844.1	1757.2	1657.8
27.5°	1587.2	1585.1	1625.8	1676.8	1741.3	1791.6	1840.1	1863.6	1844.1	1781.9	1682.3
30°	1302.5	1346.4	1367.0	1440.7	1522.9	1621.0	1706.8	1788.5	1808.6	1781.5	1699.8
32.5°	1081.5	1119.7	1136.8	1200.2	1276.8	1391.6	1520.5	1636.1	1717.9	1738.6	1689.3
35°	822.6	823.0	862.3	890.3	961.3	1079.3	1204.5	1359.5	1513.5	1630.2	1642.4
37.5°	656.4	658.7	682.4	710.3	763.6	826.1	936.2	1065.1	1243.0	1422.2	1527.2
40°	566.8	571.0	588.7	616.3	654.5	701.7	787.6	909.0	1057.4	1256.8	1419.7
42.5°	509.3	516.0	525.2	546.4	570.2	614.3	683.8	777.5	912.5	1101.0	1289.0
45°	438.8	442.6	449.6	459.4	480.9	511.7	558.4	621.3	733.4	885.2	1073.3
47.5°	387.1	385.1	392.5	400.5	414.7	435.8	467.1	518.5	598.4	720.1	879.8
50°	352.0	351.5	356.7	362.7	376.3	391.7	417.4	456.1	519.6	620.5	766.6
52.5°	319.1	320.9	324.6	332.2	341.9	354.4	377.4	405.3	459.9	546.9	668.7
55°	275.4	276.9	282.0	286.1	293.2	305.8	320.3	343.6	380.9	441.7	542.0
57.5°	238.4	237.8	242.7	243.8	251.7	262.0	273.2	291.3	318.4	363.5	431.1
60°	213.8	212.4	216.6	219.9	224.1	232.5	241.8	259.6	281.1	314.1	372.1
62.5°	191.5	190.7	193.9	197.1	200.5	208.2	216.1	229.7	246.6	274.6	320.6
65°	158.7	160.2	161.5	162.9	164.8	169.4	176.9	186.3	198.0	217.6	250.7
67.5°	124.8	126.2	126.6	129.5	133.5	136.4	141.0	149.3	157.4	174.0	192.8
70°	100.9	100.4	100.9	102.3	107.4	112.5	118.6	124.7	129.7	141.4	157.3
72.5°	86.7	85.8	87.0	87.3	89.8	91.2	95.1	100.8	107.4	115.3	126.7
75°	67.2	67.2	67.2	67.2	69.1	70.0	71.4	72.9	75.2	78.9	87.3
77.5°	49.7	49.8	50.4	50.9	51.3	51.8	52.7	54.0	54.9	56.9	60.5
80°	39.2	39.7	39.2	39.7	39.7	40.6	41.1	42.4	43.0	45.3	46.7
82.5°	29.5	29.2	29.5	30.0	30.0	30.9	31.0	32.0	32.1	33.3	34.8
85°	15.9	15.0	15.9	15.4	16.3	15.4	15.9	16.8	16.8	17.3	19.2
87.5°	7.9	8.6	7.8	8.1	8.0	8.3	8.2	8.1	8.7	8.2	8.2
90°	21.0	20.6	20.3	20.0	19.7	19.2	18.5	18.0	17.4	16.8	14.7
92.5°	23.2	22.9	22.7	22.6	22.4	21.8	20.8	19.8	18.8	17.8	16.3
95°	26.5	26.5	26.5	26.5	26.5	25.9	24.9	23.8	22.7	21.6	19.9
97.5°	28.7	28.5	28.4	28.3	28.1	27.4	26.1	25.0	23.7	22.5	33.6
100°	29.2	29.2	29.0	28.8	28.6	28.0	26.8	25.5	24.3	23.0	47.2
102.5°	29.9	29.5	29.2	29.0	28.7	30.5	34.3	38.2	42.0	45.8	72.2
105°	30.7	30.4	30.1	29.8	29.4	43.0	70.4	97.8	125.3	152.7	166.6
107.5°	96.3	117.0	137.7	158.4	179.0	199.4	219.5	239.6	259.8	279.8	277.6
110°	191.7	213.8	236.0	258.2	280.4	294.0	299.1	304.2	309.3	314.4	312.7



TEST NUMBER: P332312-940

CATALOG NUMBER: S123RDIP-S775D805U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	329.0	333.6	338.2	343.0	347.6	349.9	349.8	349.7	349.6	349.6	347.9
115°	409.9	409.3	408.7	408.0	407.4	406.4	404.8	403.2	401.7	400.2	398.8
117.5°	455.4	455.2	455.1	455.0	454.9	454.1	453.0	451.7	450.5	449.2	448.5
120°	486.6	486.6	486.6	486.6	486.6	486.0	484.7	483.5	482.2	481.0	480.5
122.5°	517.3	517.2	517.0	516.9	516.7	516.3	515.4	514.5	513.7	512.8	512.2
125°	560.5	560.2	559.9	559.5	559.3	558.9	558.7	558.3	558.0	557.7	557.1
127.5°	602.1	602.4	602.7	603.0	603.2	603.2	602.7	602.2	601.7	601.2	600.5
130°	628.8	629.1	629.5	629.7	630.1	629.9	629.3	628.7	628.0	627.4	626.8
132.5°	653.4	653.8	654.2	654.7	655.1	655.0	654.3	653.7	653.2	652.6	652.0
135°	690.9	691.3	691.8	692.2	692.7	692.7	692.2	691.8	691.3	690.9	690.3
137.5°	726.1	726.5	726.7	727.1	727.4	727.2	726.4	725.7	725.0	724.2	723.8
140°	747.3	747.6	748.0	748.2	748.6	748.4	747.8	747.2	746.5	745.9	745.5
142.5°	766.9	767.3	767.7	768.1	768.6	768.6	768.0	767.6	767.0	766.6	766.1
145°	796.8	796.8	796.8	796.8	796.8	796.7	796.4	796.0	795.8	795.4	795.1
147.5°	819.1	819.8	820.6	821.3	822.0	822.2	821.9	821.5	821.3	820.9	820.6
150°	835.9	836.3	836.8	837.2	837.8	837.8	837.5	837.1	836.9	836.6	836.2
152.5°	849.3	850.0	850.7	851.4	852.1	852.2	851.6	851.0	850.5	850.0	849.8
155°	867.9	868.9	869.8	870.8	871.6	871.7	870.9	870.2	869.4	868.6	868.4
157.5°	883.7	884.9	886.1	887.3	888.5	888.7	887.7	886.8	885.9	884.9	885.1
160°	893.8	894.8	895.9	897.0	898.0	898.1	897.2	896.3	895.4	894.4	894.6
162.5°	903.2	904.2	905.1	906.1	907.0	907.0	906.0	904.9	903.8	902.8	902.9
165°	914.6	915.7	916.8	917.9	919.0	918.9	917.7	916.4	915.2	913.9	914.1
167.5°	922.8	924.1	925.3	926.6	927.8	927.8	926.6	925.3	924.1	922.8	922.8
170°	927.9	929.2	930.3	931.6	932.8	932.8	931.6	930.3	929.2	927.9	927.9
172.5°	930.7	932.0	933.4	934.8	936.1	936.2	935.0	933.7	932.5	931.2	931.1
175°	934.9	936.1	937.4	938.6	939.8	939.9	938.8	937.7	936.7	935.6	935.4
177.5°	936.1	937.4	938.6	939.9	941.1	941.2	940.2	939.2	938.3	937.2	937.1
180°	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3



TEST NUMBER: P332312-940

CATALOG NUMBER: S123RDIP-S775D805U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6
2.5°	1126.1	1124.9	1119.7	1113.7	1105.9	1100.6	1096.5	1094.3	1087.6	1079.3	1073.8
5°	1195.6	1181.6	1166.7	1148.4	1131.7	1114.4	1103.7	1091.0	1075.7	1058.4	1046.2
7.5°	1270.2	1242.7	1213.1	1182.6	1152.4	1125.3	1101.4	1080.9	1056.4	1031.6	1014.3
10°	1327.3	1287.1	1245.5	1203.1	1164.3	1127.9	1099.9	1072.4	1042.9	1014.5	993.0
12.5°	1379.2	1326.3	1278.4	1226.3	1176.7	1133.2	1092.8	1060.4	1025.0	994.7	970.2
15°	1444.9	1390.8	1332.8	1253.5	1187.7	1132.6	1083.6	1041.1	998.2	960.8	937.0
17.5°	1506.4	1424.9	1347.1	1280.9	1195.3	1126.5	1066.7	1015.8	968.8	929.2	899.8
20°	1531.8	1452.9	1368.3	1283.9	1199.8	1122.8	1053.2	997.2	948.2	903.4	876.3
22.5°	1547.0	1457.7	1368.7	1277.9	1188.7	1108.6	1039.8	978.1	925.1	882.4	849.0
25°	1564.9	1458.5	1360.4	1270.8	1179.7	1092.9	1011.2	945.8	888.4	843.1	807.6
27.5°	1576.6	1451.4	1335.6	1235.9	1143.6	1057.1	982.2	913.0	854.7	806.8	768.7
30°	1578.9	1445.8	1316.5	1208.7	1114.8	1035.5	956.1	889.8	828.2	777.3	741.8
32.5°	1581.9	1432.0	1290.8	1176.2	1080.1	1001.5	929.6	866.3	803.2	753.0	716.8
35°	1569.6	1424.4	1251.6	1120.0	1023.8	947.7	882.8	824.5	762.4	713.8	676.9
37.5°	1516.5	1394.0	1211.1	1056.7	956.1	885.6	832.8	781.9	725.0	672.5	637.8
40°	1463.1	1364.1	1179.7	1018.2	913.2	840.8	793.2	751.6	696.5	647.6	610.2
42.5°	1383.6	1323.5	1149.9	977.9	864.6	794.9	754.7	715.8	667.4	617.7	582.6
45°	1237.6	1245.5	1088.7	913.6	797.4	727.4	689.6	662.5	619.6	578.5	542.5
47.5°	1054.6	1128.8	1016.9	845.2	726.5	660.8	627.8	604.1	575.2	534.8	502.0
50°	935.1	1041.1	959.4	799.2	682.1	616.7	584.1	564.9	539.7	507.9	476.6
52.5°	824.9	938.8	889.9	748.1	633.9	574.2	542.2	526.5	506.4	476.5	448.3
55°	672.7	788.1	776.9	670.8	561.6	507.9	483.7	465.9	452.4	430.0	407.6
57.5°	544.2	653.5	659.3	585.0	497.9	444.9	424.0	410.6	401.8	384.9	364.2
60°	463.2	563.5	583.1	527.1	452.4	405.7	385.1	374.4	367.4	353.9	338.0
62.5°	395.9	481.3	503.5	463.2	408.7	365.0	348.9	338.6	333.8	322.1	308.1
65°	303.0	374.0	395.4	373.0	344.6	309.5	296.5	287.6	283.4	276.9	266.5
67.5°	227.8	279.6	303.1	287.3	277.1	254.9	246.6	241.8	238.1	233.6	225.1
70°	183.0	221.3	245.6	241.4	233.0	221.3	215.3	212.0	208.2	204.5	197.0
72.5°	147.1	173.5	196.3	198.4	191.5	189.1	183.9	182.4	180.2	175.8	171.7
75°	97.6	115.7	131.6	137.7	140.5	142.9	140.5	140.1	139.6	135.9	133.5
77.5°	63.9	73.7	83.7	94.1	98.5	101.7	102.5	104.2	102.9	100.9	99.8
80°	49.0	51.4	58.3	67.2	74.2	77.0	78.9	79.8	79.4	78.9	77.0
82.5°	35.6	37.5	40.8	47.1	53.0	57.6	58.8	58.6	59.6	59.8	58.3
85°	19.2	19.6	20.5	21.5	24.7	29.9	31.3	32.2	33.2	33.2	30.3
87.5°	8.6	7.8	8.1	7.8	8.6	8.6	10.5	12.1	12.8	11.6	11.9
90°	12.7	10.7	8.6	6.9	5.4	3.8	2.2	0.7	2.2	3.8	5.4
92.5°	14.8	13.3	11.8	11.2	11.7	12.1	12.6	12.9	12.6	12.1	11.7
95°	18.2	16.5	14.8	17.1	23.5	29.8	36.2	42.5	36.2	29.8	23.5
97.5°	44.8	55.9	67.1	74.1	77.0	79.8	82.7	85.4	82.7	79.8	77.0
100°	71.3	95.5	119.7	130.2	127.1	124.0	120.9	117.8	120.9	124.0	127.1
102.5°	98.6	125.1	151.5	163.5	161.3	159.1	156.9	154.6	156.9	159.1	161.3
105°	180.6	194.5	208.5	214.5	212.9	211.2	209.5	207.8	209.5	211.2	212.9
107.5°	275.4	273.2	271.0	269.2	267.9	266.5	265.2	263.8	265.2	266.5	267.9
110°	311.0	309.3	307.6	306.1	304.9	303.6	302.4	301.1	302.4	303.6	304.9



TEST NUMBER: P332312-940

CATALOG NUMBER: S123RDIP-S775D805U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	346.2	344.5	342.7	341.3	340.2	339.1	338.0	336.9	338.0	339.1	340.2
115°	397.3	396.0	394.6	393.4	392.5	391.6	390.7	389.7	390.7	391.6	392.5
117.5°	447.8	447.1	446.4	445.4	444.3	443.2	442.0	440.9	442.0	443.2	444.3
120°	480.1	479.7	479.2	478.2	476.8	475.5	474.0	472.7	474.0	475.5	476.8
122.5°	511.7	511.0	510.4	509.6	508.5	507.3	506.1	505.0	506.1	507.3	508.5
125°	556.4	555.9	555.3	554.3	553.0	551.8	550.5	549.4	550.5	551.8	553.0
127.5°	599.8	599.0	598.2	597.3	596.0	594.8	593.5	592.3	593.5	594.8	596.0
130°	626.2	625.5	624.9	624.0	622.8	621.5	620.3	619.0	620.3	621.5	622.8
132.5°	651.5	651.0	650.5	649.7	648.5	647.2	646.0	644.7	646.0	647.2	648.5
135°	689.6	689.0	688.4	687.6	686.7	685.7	684.8	683.9	684.8	685.7	686.7
137.5°	723.5	723.2	722.8	722.0	720.9	719.7	718.5	717.4	718.5	719.7	720.9
140°	745.0	744.6	744.0	743.4	742.4	741.5	740.6	739.7	740.6	741.5	742.4
142.5°	765.6	765.2	764.7	764.0	763.1	762.1	761.3	760.3	761.3	762.1	763.1
145°	794.8	794.5	794.2	793.5	792.4	791.3	790.2	789.2	790.2	791.3	792.4
147.5°	820.3	820.0	819.7	819.2	818.5	817.8	817.1	816.4	817.1	817.8	818.5
150°	836.0	835.6	835.4	834.9	834.5	834.0	833.6	833.0	833.6	834.0	834.5
152.5°	849.5	849.4	849.2	849.0	848.8	848.6	848.4	848.1	848.4	848.6	848.8
155°	868.3	868.2	868.0	868.1	868.4	868.7	869.1	869.3	869.1	868.7	868.4
157.5°	885.3	885.4	885.6	885.6	885.6	885.7	885.7	885.7	885.7	885.7	885.6
160°	894.7	894.9	895.0	895.2	895.4	895.5	895.6	895.8	895.6	895.5	895.4
162.5°	903.1	903.2	903.4	903.7	904.1	904.5	904.9	905.3	904.9	904.5	904.1
165°	914.3	914.4	914.5	914.9	915.3	915.8	916.2	916.8	916.2	915.8	915.3
167.5°	922.8	922.8	922.8	923.2	923.8	924.4	925.1	925.7	925.1	924.4	923.8
170°	927.9	927.9	927.9	928.2	928.8	929.4	930.1	930.7	930.1	929.4	928.8
172.5°	930.9	930.9	930.8	931.0	931.7	932.6	933.3	934.0	933.3	932.6	931.7
175°	935.2	935.0	935.0	935.2	936.0	936.8	937.5	938.3	937.5	936.8	936.0
177.5°	937.0	936.8	936.7	937.0	937.6	938.3	938.9	939.4	938.9	938.3	937.6
180°	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3



TEST NUMBER: P332312-940

CATALOG NUMBER: S123RDIP-S775D805U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6
2.5°	1071.9	1067.0	1063.7	1056.2	1051.3	1046.2	1040.9	1044.3	1043.9	1043.5	1043.5
5°	1036.0	1025.2	1015.4	1002.8	994.9	985.1	977.6	976.7	978.6	972.0	968.2
7.5°	1000.3	985.6	971.7	957.8	943.1	931.3	923.9	920.4	915.7	911.7	907.5
10°	975.3	958.0	944.4	927.2	911.3	897.3	888.4	882.3	879.0	875.8	869.8
12.5°	949.5	932.6	915.3	895.8	880.7	864.4	857.8	851.0	844.7	841.1	832.8
15°	911.8	889.8	871.6	851.0	834.3	818.4	809.0	795.5	793.6	789.0	780.6
17.5°	874.0	850.2	825.0	809.9	790.9	774.4	760.1	755.5	742.2	737.2	729.9
20°	844.1	822.2	803.0	782.9	755.4	739.9	728.8	722.7	711.9	705.4	700.7
22.5°	818.3	796.0	773.8	750.5	727.7	710.4	702.2	692.8	687.0	677.8	672.7
25°	781.5	757.2	730.7	705.4	689.1	676.0	662.9	654.5	646.1	641.9	632.6
27.5°	738.8	713.4	688.5	669.4	649.3	636.4	624.6	617.1	607.0	599.9	594.8
30°	715.2	685.4	663.9	646.6	620.9	608.8	599.9	590.6	583.1	575.6	570.5
32.5°	688.0	660.7	640.3	618.9	599.2	586.0	574.5	566.3	559.9	552.9	547.7
35°	645.2	622.3	601.3	579.8	565.3	551.8	538.3	531.3	525.2	518.7	514.0
37.5°	606.5	585.1	565.2	544.8	526.9	515.9	505.0	499.6	491.4	487.1	482.2
40°	582.6	561.6	540.1	520.6	501.9	493.5	483.7	475.7	468.2	465.0	459.9
42.5°	556.5	535.5	517.4	496.2	481.0	469.6	460.5	451.8	446.2	441.5	438.5
45°	517.7	499.1	481.3	460.3	445.9	436.0	425.8	417.9	412.7	409.5	404.3
47.5°	480.1	461.5	443.4	425.1	411.1	399.9	389.7	384.1	377.3	373.3	369.9
50°	452.8	436.0	416.9	400.1	386.1	374.9	366.5	359.4	353.4	348.3	346.0
52.5°	427.8	409.9	393.3	377.7	362.9	350.3	342.6	335.2	330.6	324.8	322.0
55°	386.6	369.3	355.3	339.8	325.4	314.7	305.3	298.8	294.1	287.6	283.8
57.5°	347.8	332.3	315.6	302.2	287.3	278.2	270.5	261.6	255.9	250.8	247.2
60°	321.6	303.9	289.4	276.9	263.8	252.1	245.1	238.1	232.0	226.9	223.6
62.5°	294.4	278.9	265.2	251.5	239.5	229.3	221.2	215.3	210.0	206.7	203.5
65°	252.5	240.4	226.4	215.3	204.0	196.5	190.0	184.9	181.1	178.8	176.0
67.5°	214.1	202.3	190.1	179.1	171.7	165.9	161.7	157.2	155.3	152.4	150.5
70°	189.0	176.9	166.2	157.8	150.3	146.2	143.3	140.1	138.2	134.5	132.6
72.5°	161.8	153.0	145.3	138.4	132.4	128.6	125.0	121.0	118.1	113.9	112.1
75°	127.4	119.5	113.4	108.8	105.0	99.9	94.8	90.6	89.2	87.7	87.3
77.5°	94.4	89.3	85.0	81.1	76.4	72.7	71.5	70.6	70.3	69.6	69.6
80°	74.2	69.6	66.3	61.6	58.9	58.9	58.9	57.9	58.3	58.3	58.3
82.5°	55.2	50.9	49.1	47.4	46.9	47.3	47.3	47.4	47.2	47.9	47.5
85°	28.4	29.0	29.9	29.4	29.9	29.9	30.9	30.3	30.9	29.9	30.9
87.5°	11.9	13.3	14.1	14.9	15.6	15.7	16.1	16.3	16.8	16.9	17.0
90°	6.9	8.6	10.7	12.7	14.7	16.8	17.4	18.0	18.5	19.2	19.7
92.5°	11.2	11.8	13.3	14.8	16.3	17.8	18.8	19.8	20.8	21.8	22.4
95°	17.1	14.8	16.5	18.2	19.9	21.6	22.7	23.8	24.9	25.9	26.5
97.5°	74.1	67.1	55.9	44.8	33.6	22.5	23.7	25.0	26.1	27.4	28.1
100°	130.2	119.7	95.5	71.3	47.2	23.0	24.3	25.5	26.8	28.0	28.6
102.5°	163.5	151.5	125.1	98.6	72.2	45.8	42.0	38.2	34.3	30.5	28.7
105°	214.5	208.5	194.5	180.6	166.6	152.7	125.3	97.8	70.4	43.0	29.4
107.5°	269.2	271.0	273.2	275.4	277.6	279.8	259.8	239.6	219.5	199.4	179.0
110°	306.1	307.6	309.3	311.0	312.7	314.4	309.3	304.2	299.1	294.0	280.4



TEST NUMBER: P332312-940

CATALOG NUMBER: S123RDIP-S775D805U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	341.3	342.7	344.5	346.2	347.9	349.6	349.6	349.7	349.8	349.9	347.6
115°	393.4	394.6	396.0	397.3	398.8	400.2	401.7	403.2	404.8	406.4	407.4
117.5°	445.4	446.4	447.1	447.8	448.5	449.2	450.5	451.7	453.0	454.1	454.9
120°	478.2	479.2	479.7	480.1	480.5	481.0	482.2	483.5	484.7	486.0	486.6
122.5°	509.6	510.4	511.0	511.7	512.2	512.8	513.7	514.5	515.4	516.3	516.7
125°	554.3	555.3	555.9	556.4	557.1	557.7	558.0	558.3	558.7	558.9	559.3
127.5°	597.3	598.2	599.0	599.8	600.5	601.2	601.7	602.2	602.7	603.2	603.2
130°	624.0	624.9	625.5	626.2	626.8	627.4	628.0	628.7	629.3	629.9	630.1
132.5°	649.7	650.5	651.0	651.5	652.0	652.6	653.2	653.7	654.3	655.0	655.1
135°	687.6	688.4	689.0	689.6	690.3	690.9	691.3	691.8	692.2	692.7	692.7
137.5°	722.0	722.8	723.2	723.5	723.8	724.2	725.0	725.7	726.4	727.2	727.4
140°	743.4	744.0	744.6	745.0	745.5	745.9	746.5	747.2	747.8	748.4	748.6
142.5°	764.0	764.7	765.2	765.6	766.1	766.6	767.0	767.6	768.0	768.6	768.6
145°	793.5	794.2	794.5	794.8	795.1	795.4	795.8	796.0	796.4	796.7	796.8
147.5°	819.2	819.7	820.0	820.3	820.6	820.9	821.3	821.5	821.9	822.2	822.0
150°	834.9	835.4	835.6	836.0	836.2	836.6	836.9	837.1	837.5	837.8	837.8
152.5°	849.0	849.2	849.4	849.5	849.8	850.0	850.5	851.0	851.6	852.2	852.1
155°	868.1	868.0	868.2	868.3	868.4	868.6	869.4	870.2	870.9	871.7	871.6
157.5°	885.6	885.6	885.4	885.3	885.1	884.9	885.9	886.8	887.7	888.7	888.5
160°	895.2	895.0	894.9	894.7	894.6	894.4	895.4	896.3	897.2	898.1	898.0
162.5°	903.7	903.4	903.2	903.1	902.9	902.8	903.8	904.9	906.0	907.0	907.0
165°	914.9	914.5	914.4	914.3	914.1	913.9	915.2	916.4	917.7	918.9	919.0
167.5°	923.2	922.8	922.8	922.8	922.8	922.8	924.1	925.3	926.6	927.8	927.8
170°	928.2	927.9	927.9	927.9	927.9	927.9	929.2	930.3	931.6	932.8	932.8
172.5°	931.0	930.8	930.9	930.9	931.1	931.2	932.5	933.7	935.0	936.2	936.1
175°	935.2	935.0	935.0	935.2	935.4	935.6	936.7	937.7	938.8	939.9	939.8
177.5°	937.0	936.7	936.8	937.0	937.1	937.2	938.3	939.2	940.2	941.2	941.1
180°	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3



TEST NUMBER: P332312-940

CATALOG NUMBER: S123RDIP-S775D805U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6
2.5°	1039.0	1038.7	1039.0	1037.5	1039.0	1038.7	1039.0	1043.5	1043.5	1043.9	1044.3
5°	966.9	966.3	965.0	960.8	965.0	966.3	966.9	968.2	972.0	978.6	976.7
7.5°	903.8	903.2	899.1	899.2	899.1	903.2	903.8	907.5	911.7	915.7	920.4
10°	866.5	866.9	861.4	858.1	861.4	866.9	866.5	869.8	875.8	879.0	882.3
12.5°	830.3	828.1	823.6	820.0	823.6	828.1	830.3	832.8	841.1	844.7	851.0
15°	782.5	777.8	766.6	767.5	766.6	777.8	782.5	780.6	789.0	793.6	795.5
17.5°	726.1	722.7	722.5	716.0	722.5	722.7	726.1	729.9	737.2	742.2	755.5
20°	693.3	691.0	691.9	685.4	691.9	691.0	693.3	700.7	705.4	711.9	722.7
22.5°	667.5	665.2	661.3	659.2	661.3	665.2	667.5	672.7	677.8	687.0	692.8
25°	629.8	626.1	622.3	624.6	622.3	626.1	629.8	632.6	641.9	646.1	654.5
27.5°	592.1	589.2	585.5	585.1	585.5	589.2	592.1	594.8	599.9	607.0	617.1
30°	568.2	565.3	563.5	561.2	563.5	565.3	568.2	570.5	575.6	583.1	590.6
32.5°	543.9	543.3	539.9	539.5	539.9	543.3	543.9	547.7	552.9	559.9	566.3
35°	512.1	509.3	508.4	508.9	508.4	509.3	512.1	514.0	518.7	525.2	531.3
37.5°	482.0	478.2	476.5	474.9	476.5	478.2	482.0	482.2	487.1	491.4	499.6
40°	460.3	456.6	455.7	454.7	455.7	456.6	460.3	459.9	465.0	468.2	475.7
42.5°	436.0	434.5	434.0	432.3	434.0	434.5	436.0	438.5	441.5	446.2	451.8
45°	402.9	402.4	399.7	400.6	399.7	402.4	402.9	404.3	409.5	412.7	417.9
47.5°	368.0	366.0	364.0	365.2	364.0	366.0	368.0	369.9	373.3	377.3	384.1
50°	344.1	343.1	338.9	339.8	338.9	343.1	344.1	346.0	348.3	353.4	359.4
52.5°	320.2	316.6	315.0	314.5	315.0	316.6	320.2	322.0	324.8	330.6	335.2
55°	280.6	276.3	274.5	273.6	274.5	276.3	280.6	283.8	287.6	294.1	298.8
57.5°	241.7	240.6	239.2	240.1	239.2	240.6	241.7	247.2	250.8	255.9	261.6
60°	218.9	218.9	218.9	218.5	218.9	218.9	218.9	223.6	226.9	232.0	238.1
62.5°	201.4	200.3	199.9	200.5	199.9	200.3	201.4	203.5	206.7	210.0	215.3
65°	174.6	174.2	172.3	171.8	172.3	174.2	174.6	176.0	178.8	181.1	184.9
67.5°	149.3	147.6	147.0	146.4	147.0	147.6	149.3	150.5	152.4	155.3	157.2
70°	130.3	129.3	126.5	127.0	126.5	129.3	130.3	132.6	134.5	138.2	140.1
72.5°	109.7	108.8	108.3	107.5	108.3	108.8	109.7	112.1	113.9	118.1	121.0
75°	86.9	86.4	85.9	87.7	85.9	86.4	86.9	87.3	87.7	89.2	90.6
77.5°	69.6	69.6	69.8	69.1	69.8	69.6	69.6	69.6	69.6	70.3	70.6
80°	58.3	58.3	57.9	57.9	57.9	58.3	58.3	58.3	58.3	58.3	57.9
82.5°	46.8	47.2	47.4	46.7	47.4	47.2	46.8	47.5	47.9	47.2	47.4
85°	30.9	30.3	31.3	30.9	31.3	30.3	30.9	30.9	29.9	30.9	30.3
87.5°	17.8	17.1	17.2	17.7	17.2	17.1	17.8	17.0	16.9	16.8	16.3
90°	20.0	20.3	20.6	21.0	20.6	20.3	20.0	19.7	19.2	18.5	18.0
92.5°	22.6	22.7	22.9	23.2	22.9	22.7	22.6	22.4	21.8	20.8	19.8
95°	26.5	26.5	26.5	26.5	26.5	26.5	26.5	26.5	25.9	24.9	23.8
97.5°	28.3	28.4	28.5	28.7	28.5	28.4	28.3	28.1	27.4	26.1	25.0
100°	28.8	29.0	29.2	29.2	29.2	29.0	28.8	28.6	28.0	26.8	25.5
102.5°	29.0	29.2	29.5	29.9	29.5	29.2	29.0	28.7	30.5	34.3	38.2
105°	29.8	30.1	30.4	30.7	30.4	30.1	29.8	29.4	43.0	70.4	97.8
107.5°	158.4	137.7	117.0	96.3	117.0	137.7	158.4	179.0	199.4	219.5	239.6
110°	258.2	236.0	213.8	191.7	213.8	236.0	258.2	280.4	294.0	299.1	304.2



TEST NUMBER: P332312-940

CATALOG NUMBER: S123RDIP-S775D805U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	343.0	338.2	333.6	329.0	333.6	338.2	343.0	347.6	349.9	349.8	349.7
115°	408.0	408.7	409.3	409.9	409.3	408.7	408.0	407.4	406.4	404.8	403.2
117.5°	455.0	455.1	455.2	455.4	455.2	455.1	455.0	454.9	454.1	453.0	451.7
120°	486.6	486.6	486.6	486.6	486.6	486.6	486.6	486.6	486.0	484.7	483.5
122.5°	516.9	517.0	517.2	517.3	517.2	517.0	516.9	516.7	516.3	515.4	514.5
125°	559.5	559.9	560.2	560.5	560.2	559.9	559.5	559.3	558.9	558.7	558.3
127.5°	603.0	602.7	602.4	602.1	602.4	602.7	603.0	603.2	603.2	602.7	602.2
130°	629.7	629.5	629.1	628.8	629.1	629.5	629.7	630.1	629.9	629.3	628.7
132.5°	654.7	654.2	653.8	653.4	653.8	654.2	654.7	655.1	655.0	654.3	653.7
135°	692.2	691.8	691.3	690.9	691.3	691.8	692.2	692.7	692.7	692.2	691.8
137.5°	727.1	726.7	726.5	726.1	726.5	726.7	727.1	727.4	727.2	726.4	725.7
140°	748.2	748.0	747.6	747.3	747.6	748.0	748.2	748.6	748.4	747.8	747.2
142.5°	768.1	767.7	767.3	766.9	767.3	767.7	768.1	768.6	768.6	768.0	767.6
145°	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.8	796.7	796.4	796.0
147.5°	821.3	820.6	819.8	819.1	819.8	820.6	821.3	822.0	822.2	821.9	821.5
150°	837.2	836.8	836.3	835.9	836.3	836.8	837.2	837.8	837.8	837.5	837.1
152.5°	851.4	850.7	850.0	849.3	850.0	850.7	851.4	852.1	852.2	851.6	851.0
155°	870.8	869.8	868.9	867.9	868.9	869.8	870.8	871.6	871.7	870.9	870.2
157.5°	887.3	886.1	884.9	883.7	884.9	886.1	887.3	888.5	888.7	887.7	886.8
160°	897.0	895.9	894.8	893.8	894.8	895.9	897.0	898.0	898.1	897.2	896.3
162.5°	906.1	905.1	904.2	903.2	904.2	905.1	906.1	907.0	907.0	906.0	904.9
165°	917.9	916.8	915.7	914.6	915.7	916.8	917.9	919.0	918.9	917.7	916.4
167.5°	926.6	925.3	924.1	922.8	924.1	925.3	926.6	927.8	927.8	926.6	925.3
170°	931.6	930.3	929.2	927.9	929.2	930.3	931.6	932.8	932.8	931.6	930.3
172.5°	934.8	933.4	932.0	930.7	932.0	933.4	934.8	936.1	936.2	935.0	933.7
175°	938.6	937.4	936.1	934.9	936.1	937.4	938.6	939.8	939.9	938.8	937.7
177.5°	939.9	938.6	937.4	936.1	937.4	938.6	939.9	941.1	941.2	940.2	939.2
180°	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3



TEST NUMBER: P332312-940

CATALOG NUMBER: S123RDIP-S775D805U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6
2.5°	1040.9	1046.2	1051.3	1056.2	1063.7	1067.0	1071.9	1073.8	1079.3	1087.6	1094.3
5°	977.6	985.1	994.9	1002.8	1015.4	1025.2	1036.0	1046.2	1058.4	1075.7	1091.0
7.5°	923.9	931.3	943.1	957.8	971.7	985.6	1000.3	1014.3	1031.6	1056.4	1080.9
10°	888.4	897.3	911.3	927.2	944.4	958.0	975.3	993.0	1014.5	1042.9	1072.4
12.5°	857.8	864.4	880.7	895.8	915.3	932.6	949.5	970.2	994.7	1025.0	1060.4
15°	809.0	818.4	834.3	851.0	871.6	889.8	911.8	937.0	960.8	998.2	1041.1
17.5°	760.1	774.4	790.9	809.9	825.0	850.2	874.0	899.8	929.2	968.8	1015.8
20°	728.8	739.9	755.4	782.9	803.0	822.2	844.1	876.3	903.4	948.2	997.2
22.5°	702.2	710.4	727.7	750.5	773.8	796.0	818.3	849.0	882.4	925.1	978.1
25°	662.9	676.0	689.1	705.4	730.7	757.2	781.5	807.6	843.1	888.4	945.8
27.5°	624.6	636.4	649.3	669.4	688.5	713.4	738.8	768.7	806.8	854.7	913.0
30°	599.9	608.8	620.9	646.6	663.9	685.4	715.2	741.8	777.3	828.2	889.8
32.5°	574.5	586.0	599.2	618.9	640.3	660.7	688.0	716.8	753.0	803.2	866.3
35°	538.3	551.8	565.3	579.8	601.3	622.3	645.2	676.9	713.8	762.4	824.5
37.5°	505.0	515.9	526.9	544.8	565.2	585.1	606.5	637.8	672.5	725.0	781.9
40°	483.7	493.5	501.9	520.6	540.1	561.6	582.6	610.2	647.6	696.5	751.6
42.5°	460.5	469.6	481.0	496.2	517.4	535.5	556.5	582.6	617.7	667.4	715.8
45°	425.8	436.0	445.9	460.3	481.3	499.1	517.7	542.5	578.5	619.6	662.5
47.5°	389.7	399.9	411.1	425.1	443.4	461.5	480.1	502.0	534.8	575.2	604.1
50°	366.5	374.9	386.1	400.1	416.9	436.0	452.8	476.6	507.9	539.7	564.9
52.5°	342.6	350.3	362.9	377.7	393.3	409.9	427.8	448.3	476.5	506.4	526.5
55°	305.3	314.7	325.4	339.8	355.3	369.3	386.6	407.6	430.0	452.4	465.9
57.5°	270.5	278.2	287.3	302.2	315.6	332.3	347.8	364.2	384.9	401.8	410.6
60°	245.1	252.1	263.8	276.9	289.4	303.9	321.6	338.0	353.9	367.4	374.4
62.5°	221.2	229.3	239.5	251.5	265.2	278.9	294.4	308.1	322.1	333.8	338.6
65°	190.0	196.5	204.0	215.3	226.4	240.4	252.5	266.5	276.9	283.4	287.6
67.5°	161.7	165.9	171.7	179.1	190.1	202.3	214.1	225.1	233.6	238.1	241.8
70°	143.3	146.2	150.3	157.8	166.2	176.9	189.0	197.0	204.5	208.2	212.0
72.5°	125.0	128.6	132.4	138.4	145.3	153.0	161.8	171.7	175.8	180.2	182.4
75°	94.8	99.9	105.0	108.8	113.4	119.5	127.4	133.5	135.9	139.6	140.1
77.5°	71.5	72.7	76.4	81.1	85.0	89.3	94.4	99.8	100.9	102.9	104.2
80°	58.9	58.9	58.9	61.6	66.3	69.6	74.2	77.0	78.9	79.4	79.8
82.5°	47.3	47.3	46.9	47.4	49.1	50.9	55.2	58.3	59.8	59.6	58.6
85°	30.9	29.9	29.9	29.4	29.9	29.0	28.4	30.3	33.2	33.2	32.2
87.5°	16.1	15.7	15.6	14.9	14.1	13.3	11.9	11.9	11.6	12.8	12.1
90°	17.4	16.8	14.7	12.7	10.7	8.6	6.9	5.4	3.8	2.2	0.7
92.5°	18.8	17.8	16.3	14.8	13.3	11.8	11.2	11.7	12.1	12.6	12.9
95°	22.7	21.6	19.9	18.2	16.5	14.8	17.1	23.5	29.8	36.2	42.5
97.5°	23.7	22.5	33.6	44.8	55.9	67.1	74.1	77.0	79.8	82.7	85.4
100°	24.3	23.0	47.2	71.3	95.5	119.7	130.2	127.1	124.0	120.9	117.8
102.5°	42.0	45.8	72.2	98.6	125.1	151.5	163.5	161.3	159.1	156.9	154.6
105°	125.3	152.7	166.6	180.6	194.5	208.5	214.5	212.9	211.2	209.5	207.8
107.5°	259.8	279.8	277.6	275.4	273.2	271.0	269.2	267.9	266.5	265.2	263.8
110°	309.3	314.4	312.7	311.0	309.3	307.6	306.1	304.9	303.6	302.4	301.1



TEST NUMBER: P332312-940

CATALOG NUMBER: S123RDIP-S775D805U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	349.6	349.6	347.9	346.2	344.5	342.7	341.3	340.2	339.1	338.0	336.9
115°	401.7	400.2	398.8	397.3	396.0	394.6	393.4	392.5	391.6	390.7	389.7
117.5°	450.5	449.2	448.5	447.8	447.1	446.4	445.4	444.3	443.2	442.0	440.9
120°	482.2	481.0	480.5	480.1	479.7	479.2	478.2	476.8	475.5	474.0	472.7
122.5°	513.7	512.8	512.2	511.7	511.0	510.4	509.6	508.5	507.3	506.1	505.0
125°	558.0	557.7	557.1	556.4	555.9	555.3	554.3	553.0	551.8	550.5	549.4
127.5°	601.7	601.2	600.5	599.8	599.0	598.2	597.3	596.0	594.8	593.5	592.3
130°	628.0	627.4	626.8	626.2	625.5	624.9	624.0	622.8	621.5	620.3	619.0
132.5°	653.2	652.6	652.0	651.5	651.0	650.5	649.7	648.5	647.2	646.0	644.7
135°	691.3	690.9	690.3	689.6	689.0	688.4	687.6	686.7	685.7	684.8	683.9
137.5°	725.0	724.2	723.8	723.5	723.2	722.8	722.0	720.9	719.7	718.5	717.4
140°	746.5	745.9	745.5	745.0	744.6	744.0	743.4	742.4	741.5	740.6	739.7
142.5°	767.0	766.6	766.1	765.6	765.2	764.7	764.0	763.1	762.1	761.3	760.3
145°	795.8	795.4	795.1	794.8	794.5	794.2	793.5	792.4	791.3	790.2	789.2
147.5°	821.3	820.9	820.6	820.3	820.0	819.7	819.2	818.5	817.8	817.1	816.4
150°	836.9	836.6	836.2	836.0	835.6	835.4	834.9	834.5	834.0	833.6	833.0
152.5°	850.5	850.0	849.8	849.5	849.4	849.2	849.0	848.8	848.6	848.4	848.1
155°	869.4	868.6	868.4	868.3	868.2	868.0	868.1	868.4	868.7	869.1	869.3
157.5°	885.9	884.9	885.1	885.3	885.4	885.6	885.6	885.6	885.7	885.7	885.7
160°	895.4	894.4	894.6	894.7	894.9	895.0	895.2	895.4	895.5	895.6	895.8
162.5°	903.8	902.8	902.9	903.1	903.2	903.4	903.7	904.1	904.5	904.9	905.3
165°	915.2	913.9	914.1	914.3	914.4	914.5	914.9	915.3	915.8	916.2	916.8
167.5°	924.1	922.8	922.8	922.8	922.8	922.8	923.2	923.8	924.4	925.1	925.7
170°	929.2	927.9	927.9	927.9	927.9	927.9	928.2	928.8	929.4	930.1	930.7
172.5°	932.5	931.2	931.1	930.9	930.9	930.8	931.0	931.7	932.6	933.3	934.0
175°	936.7	935.6	935.4	935.2	935.0	935.0	935.2	936.0	936.8	937.5	938.3
177.5°	938.3	937.2	937.1	937.0	936.8	936.7	937.0	937.6	938.3	938.9	939.4
180°	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3



TEST NUMBER: P332312-940

CATALOG NUMBER: S123RDIP-S775D805U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6
2.5°	1096.5	1100.6	1105.9	1113.7	1119.7	1124.9	1126.1	1127.6	1131.3	1137.6	1142.5
5°	1103.7	1114.4	1131.7	1148.4	1166.7	1181.6	1195.6	1205.4	1214.8	1234.4	1250.3
7.5°	1101.4	1125.3	1152.4	1182.6	1213.1	1242.7	1270.2	1294.7	1319.1	1347.7	1380.3
10°	1099.9	1127.9	1164.3	1203.1	1245.5	1287.1	1327.3	1358.5	1395.0	1427.6	1469.2
12.5°	1092.8	1133.2	1176.7	1226.3	1278.4	1326.3	1379.2	1422.5	1464.1	1511.3	1559.6
15°	1083.6	1132.6	1187.7	1253.5	1332.8	1390.8	1444.9	1520.1	1571.5	1622.8	1691.8
17.5°	1066.7	1126.5	1195.3	1280.9	1347.1	1424.9	1506.4	1565.8	1635.0	1707.3	1769.9
20°	1053.2	1122.8	1199.8	1283.9	1368.3	1452.9	1531.8	1602.7	1674.2	1757.7	1809.1
22.5°	1039.8	1108.6	1188.7	1277.9	1368.7	1457.7	1547.0	1630.3	1710.7	1795.1	1860.6
25°	1011.2	1092.9	1179.7	1270.8	1360.4	1458.5	1564.9	1657.8	1757.2	1844.1	1906.2
27.5°	982.2	1057.1	1143.6	1235.9	1335.6	1451.4	1576.6	1682.3	1781.9	1844.1	1863.6
30°	956.1	1035.5	1114.8	1208.7	1316.5	1445.8	1578.9	1699.8	1781.5	1808.6	1788.5
32.5°	929.6	1001.5	1080.1	1176.2	1290.8	1432.0	1581.9	1689.3	1738.6	1717.9	1636.1
35°	882.8	947.7	1023.8	1120.0	1251.6	1424.4	1569.6	1642.4	1630.2	1513.5	1359.5
37.5°	832.8	885.6	956.1	1056.7	1211.1	1394.0	1516.5	1527.2	1422.2	1243.0	1065.1
40°	793.2	840.8	913.2	1018.2	1179.7	1364.1	1463.1	1419.7	1256.8	1057.4	909.0
42.5°	754.7	794.9	864.6	977.9	1149.9	1323.5	1383.6	1289.0	1101.0	912.5	777.5
45°	689.6	727.4	797.4	913.6	1088.7	1245.5	1237.6	1073.3	885.2	733.4	621.3
47.5°	627.8	660.8	726.5	845.2	1016.9	1128.8	1054.6	879.8	720.1	598.4	518.5
50°	584.1	616.7	682.1	799.2	959.4	1041.1	935.1	766.6	620.5	519.6	456.1
52.5°	542.2	574.2	633.9	748.1	889.9	938.8	824.9	668.7	546.9	459.9	405.3
55°	483.7	507.9	561.6	670.8	776.9	788.1	672.7	542.0	441.7	380.9	343.6
57.5°	424.0	444.9	497.9	585.0	659.3	653.5	544.2	431.1	363.5	318.4	291.3
60°	385.1	405.7	452.4	527.1	583.1	563.5	463.2	372.1	314.1	281.1	259.6
62.5°	348.9	365.0	408.7	463.2	503.5	481.3	395.9	320.6	274.6	246.6	229.7
65°	296.5	309.5	344.6	373.0	395.4	374.0	303.0	250.7	217.6	198.0	186.3
67.5°	246.6	254.9	277.1	287.3	303.1	279.6	227.8	192.8	174.0	157.4	149.3
70°	215.3	221.3	233.0	241.4	245.6	221.3	183.0	157.3	141.4	129.7	124.7
72.5°	183.9	189.1	191.5	198.4	196.3	173.5	147.1	126.7	115.3	107.4	100.8
75°	140.5	142.9	140.5	137.7	131.6	115.7	97.6	87.3	78.9	75.2	72.9
77.5°	102.5	101.7	98.5	94.1	83.7	73.7	63.9	60.5	56.9	54.9	54.0
80°	78.9	77.0	74.2	67.2	58.3	51.4	49.0	46.7	45.3	43.0	42.4
82.5°	58.8	57.6	53.0	47.1	40.8	37.5	35.6	34.8	33.3	32.1	32.0
85°	31.3	29.9	24.7	21.5	20.5	19.6	19.2	19.2	17.3	16.8	16.8
87.5°	10.5	8.6	8.6	7.8	8.1	7.8	8.6	8.2	8.2	8.7	8.1
90°	2.2	3.8	5.4	6.9	8.6	10.7	12.7	14.7	16.8	17.4	18.0
92.5°	12.6	12.1	11.7	11.2	11.8	13.3	14.8	16.3	17.8	18.8	19.8
95°	36.2	29.8	23.5	17.1	14.8	16.5	18.2	19.9	21.6	22.7	23.8
97.5°	82.7	79.8	77.0	74.1	67.1	55.9	44.8	33.6	22.5	23.7	25.0
100°	120.9	124.0	127.1	130.2	119.7	95.5	71.3	47.2	23.0	24.3	25.5
102.5°	156.9	159.1	161.3	163.5	151.5	125.1	98.6	72.2	45.8	42.0	38.2
105°	209.5	211.2	212.9	214.5	208.5	194.5	180.6	166.6	152.7	125.3	97.8
107.5°	265.2	266.5	267.9	269.2	271.0	273.2	275.4	277.6	279.8	259.8	239.6
110°	302.4	303.6	304.9	306.1	307.6	309.3	311.0	312.7	314.4	309.3	304.2



TEST NUMBER: P332312-940

CATALOG NUMBER: S123RDIP-S775D805U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	338.0	339.1	340.2	341.3	342.7	344.5	346.2	347.9	349.6	349.6	349.7
115°	390.7	391.6	392.5	393.4	394.6	396.0	397.3	398.8	400.2	401.7	403.2
117.5°	442.0	443.2	444.3	445.4	446.4	447.1	447.8	448.5	449.2	450.5	451.7
120°	474.0	475.5	476.8	478.2	479.2	479.7	480.1	480.5	481.0	482.2	483.5
122.5°	506.1	507.3	508.5	509.6	510.4	511.0	511.7	512.2	512.8	513.7	514.5
125°	550.5	551.8	553.0	554.3	555.3	555.9	556.4	557.1	557.7	558.0	558.3
127.5°	593.5	594.8	596.0	597.3	598.2	599.0	599.8	600.5	601.2	601.7	602.2
130°	620.3	621.5	622.8	624.0	624.9	625.5	626.2	626.8	627.4	628.0	628.7
132.5°	646.0	647.2	648.5	649.7	650.5	651.0	651.5	652.0	652.6	653.2	653.7
135°	684.8	685.7	686.7	687.6	688.4	689.0	689.6	690.3	690.9	691.3	691.8
137.5°	718.5	719.7	720.9	722.0	722.8	723.2	723.5	723.8	724.2	725.0	725.7
140°	740.6	741.5	742.4	743.4	744.0	744.6	745.0	745.5	745.9	746.5	747.2
142.5°	761.3	762.1	763.1	764.0	764.7	765.2	765.6	766.1	766.6	767.0	767.6
145°	790.2	791.3	792.4	793.5	794.2	794.5	794.8	795.1	795.4	795.8	796.0
147.5°	817.1	817.8	818.5	819.2	819.7	820.0	820.3	820.6	820.9	821.3	821.5
150°	833.6	834.0	834.5	834.9	835.4	835.6	836.0	836.2	836.6	836.9	837.1
152.5°	848.4	848.6	848.8	849.0	849.2	849.4	849.5	849.8	850.0	850.5	851.0
155°	869.1	868.7	868.4	868.1	868.0	868.2	868.3	868.4	868.6	869.4	870.2
157.5°	885.7	885.7	885.6	885.6	885.6	885.4	885.3	885.1	884.9	885.9	886.8
160°	895.6	895.5	895.4	895.2	895.0	894.9	894.7	894.6	894.4	895.4	896.3
162.5°	904.9	904.5	904.1	903.7	903.4	903.2	903.1	902.9	902.8	903.8	904.9
165°	916.2	915.8	915.3	914.9	914.5	914.4	914.3	914.1	913.9	915.2	916.4
167.5°	925.1	924.4	923.8	923.2	922.8	922.8	922.8	922.8	922.8	924.1	925.3
170°	930.1	929.4	928.8	928.2	927.9	927.9	927.9	927.9	927.9	929.2	930.3
172.5°	933.3	932.6	931.7	931.0	930.8	930.9	930.9	931.1	931.2	932.5	933.7
175°	937.5	936.8	936.0	935.2	935.0	935.0	935.2	935.4	935.6	936.7	937.7
177.5°	938.9	938.3	937.6	937.0	936.7	936.8	937.0	937.1	937.2	938.3	939.2
180°	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3



TEST NUMBER: P332312-940

CATALOG NUMBER: S123RDIP-S775D805U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6	1090.6
2.5°	1150.3	1150.3	1151.8	1157.4	1158.2	1163.1	1161.5
5°	1264.3	1273.1	1276.4	1290.4	1298.8	1302.5	1295.0
7.5°	1403.6	1428.6	1440.5	1455.1	1468.1	1472.0	1461.8
10°	1505.1	1531.2	1553.3	1566.7	1579.4	1587.8	1598.5
12.5°	1603.4	1635.5	1656.4	1675.4	1688.5	1699.1	1700.8
15°	1710.1	1758.6	1795.5	1822.6	1836.1	1843.2	1840.3
17.5°	1817.8	1862.8	1889.0	1916.6	1935.4	1936.4	1936.9
20°	1878.7	1922.5	1952.8	1973.4	1994.4	1993.5	1998.1
22.5°	1919.3	1953.9	1977.1	1992.1	1999.3	1995.7	1996.6
25°	1938.4	1948.7	1944.5	1920.7	1914.6	1892.7	1896.4
27.5°	1840.1	1791.6	1741.3	1676.8	1625.8	1585.1	1587.2
30°	1706.8	1621.0	1522.9	1440.7	1367.0	1346.4	1302.5
32.5°	1520.5	1391.6	1276.8	1200.2	1136.8	1119.7	1081.5
35°	1204.5	1079.3	961.3	890.3	862.3	823.0	822.6
37.5°	936.2	826.1	763.6	710.3	682.4	658.7	656.4
40°	787.6	701.7	654.5	616.3	588.7	571.0	566.8
42.5°	683.8	614.3	570.2	546.4	525.2	516.0	509.3
45°	558.4	511.7	480.9	459.4	449.6	442.6	438.8
47.5°	467.1	435.8	414.7	400.5	392.5	385.1	387.1
50°	417.4	391.7	376.3	362.7	356.7	351.5	352.0
52.5°	377.4	354.4	341.9	332.2	324.6	320.9	319.1
55°	320.3	305.8	293.2	286.1	282.0	276.9	275.4
57.5°	273.2	262.0	251.7	243.8	242.7	237.8	238.4
60°	241.8	232.5	224.1	219.9	216.6	212.4	213.8
62.5°	216.1	208.2	200.5	197.1	193.9	190.7	191.5
65°	176.9	169.4	164.8	162.9	161.5	160.2	158.7
67.5°	141.0	136.4	133.5	129.5	126.6	126.2	124.8
70°	118.6	112.5	107.4	102.3	100.9	100.4	100.9
72.5°	95.1	91.2	89.8	87.3	87.0	85.8	86.7
75°	71.4	70.0	69.1	67.2	67.2	67.2	67.2
77.5°	52.7	51.8	51.3	50.9	50.4	49.8	49.7
80°	41.1	40.6	39.7	39.7	39.2	39.7	39.2
82.5°	31.0	30.9	30.0	30.0	29.5	29.2	29.5
85°	15.9	15.4	16.3	15.4	15.9	15.0	15.9
87.5°	8.2	8.3	8.0	8.1	7.8	8.6	7.9
90°	18.5	19.2	19.7	20.0	20.3	20.6	21.0
92.5°	20.8	21.8	22.4	22.6	22.7	22.9	23.2
95°	24.9	25.9	26.5	26.5	26.5	26.5	26.5
97.5°	26.1	27.4	28.1	28.3	28.4	28.5	28.7
100°	26.8	28.0	28.6	28.8	29.0	29.2	29.2
102.5°	34.3	30.5	28.7	29.0	29.2	29.5	29.9
105°	70.4	43.0	29.4	29.8	30.1	30.4	30.7
107.5°	219.5	199.4	179.0	158.4	137.7	117.0	96.3
110°	299.1	294.0	280.4	258.2	236.0	213.8	191.7



TEST NUMBER: P332312-940

CATALOG NUMBER: S123RDIP-S775D805U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	349.8	349.9	347.6	343.0	338.2	333.6	329.0
115°	404.8	406.4	407.4	408.0	408.7	409.3	409.9
117.5°	453.0	454.1	454.9	455.0	455.1	455.2	455.4
120°	484.7	486.0	486.6	486.6	486.6	486.6	486.6
122.5°	515.4	516.3	516.7	516.9	517.0	517.2	517.3
125°	558.7	558.9	559.3	559.5	559.9	560.2	560.5
127.5°	602.7	603.2	603.2	603.0	602.7	602.4	602.1
130°	629.3	629.9	630.1	629.7	629.5	629.1	628.8
132.5°	654.3	655.0	655.1	654.7	654.2	653.8	653.4
135°	692.2	692.7	692.7	692.2	691.8	691.3	690.9
137.5°	726.4	727.2	727.4	727.1	726.7	726.5	726.1
140°	747.8	748.4	748.6	748.2	748.0	747.6	747.3
142.5°	768.0	768.6	768.6	768.1	767.7	767.3	766.9
145°	796.4	796.7	796.8	796.8	796.8	796.8	796.8
147.5°	821.9	822.2	822.0	821.3	820.6	819.8	819.1
150°	837.5	837.8	837.8	837.2	836.8	836.3	835.9
152.5°	851.6	852.2	852.1	851.4	850.7	850.0	849.3
155°	870.9	871.7	871.6	870.8	869.8	868.9	867.9
157.5°	887.7	888.7	888.5	887.3	886.1	884.9	883.7
160°	897.2	898.1	898.0	897.0	895.9	894.8	893.8
162.5°	906.0	907.0	907.0	906.1	905.1	904.2	903.2
165°	917.7	918.9	919.0	917.9	916.8	915.7	914.6
167.5°	926.6	927.8	927.8	926.6	925.3	924.1	922.8
170°	931.6	932.8	932.8	931.6	930.3	929.2	927.9
172.5°	935.0	936.2	936.1	934.8	933.4	932.0	930.7
175°	938.8	939.9	939.8	938.6	937.4	936.1	934.9
177.5°	940.2	941.2	941.1	939.9	938.6	937.4	936.1
180°	938.3	938.3	938.3	938.3	938.3	938.3	938.3

(END OF REPORT)