

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831110

Luminaire Tested: S123DIP-S1000D365U850-4F0-1E-UDD-G4

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P831110
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-1, G3-1807-864-17)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-S1000D365U850-4F0-1E-UDD-G4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, GRAZE OPTIC
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6570.1 lumens
Efficiency: N/A
Efficacy: 145.7 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 1.19 / 0.89
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 45.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P831110

CATALOG NUMBER: S123DIP-S1000D365U850-4F0-1E-UDD-G4

Luminous Intensity Polar Plot





TEST NUMBER: P831110

CATALOG NUMBER: S123DIP-S1000D365U850-4F0-1E-UDD-G4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	114	114	114	114	109	109	109	109	99	99	99	90	90	90	82	82	82	78				78
1	105	101	97	93	100	96	93	90	88	85	83	80	78	77	73	72	71	67				67
2	96	89	83	78	92	85	80	75	78	74	70	72	68	65	66	63	61	58				58
3	88	79	72	66	84	76	69	64	70	65	60	64	60	57	59	56	53	50				50
4	82	71	63	57	78	68	61	56	63	57	52	58	53	49	54	50	47	44				44
5	75	64	56	50	72	62	54	49	57	51	46	53	48	44	49	45	41	39				39
6	70	58	50	44	67	56	49	43	52	46	41	48	43	39	45	41	37	35				35
7	65	53	45	40	62	51	44	39	48	42	37	45	39	35	42	37	34	31				31
8	61	49	41	36	58	47	40	35	44	38	34	41	36	32	39	34	31	29				29
9	57	45	38	33	55	44	37	32	41	35	31	38	33	29	36	31	28	26				26
10	54	42	35	30	52	41	34	29	38	32	28	36	31	27	34	29	26	24				24

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	34235	34235	34235	34235	34235
5°	43296	40864	34540	27835	25579
10°	43715	45038	34311	22189	19390
15°	32926	41815	34077	18790	16397
20°	22942	33837	33643	16433	14893
25°	17493	26021	32901	15118	13971
30°	15134	20673	31717	14189	13226
35°	14040	17454	30350	13517	12703
40°	13293	15657	28431	12878	12525
45°	12851	14490	25994	12379	12446
50°	12630	13569	23107	11925	12382
55°	12159	12892	20273	11494	12436
60°	11724	12170	17474	11089	12232
65°	11013	11484	15073	10656	11991
70°	10172	10612	12818	9939	11286
75°	9208	9515	10988	9237	10310
80°	7593	8325	8691	8052	8691
85°	6015	6743	6385	6830	6928

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 29678 cd/sqm



TEST NUMBER: P831110

CATALOG NUMBER: S123DIP-S1000D365U850-4F0-1E-UDD-G4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	300.7	4.6
10°-20°	748.0	11.4
20°-30°	885.7	13.5
30°-40°	890.6	13.6
40°-50°	817.1	12.4
50°-60°	674.4	10.3
60°-70°	477.1	7.3
70°-80°	254.6	3.9
80°-90°	65.7	1.0
90°-100°	105.1	1.6
100°-110°	307.6	4.7
110°-120°	300.4	4.6
120°-130°	239.2	3.6
130°-140°	188.7	2.9
140°-150°	140.8	2.1
150°-160°	98.2	1.5
160°-170°	57.7	0.9
170°-180°	18.8	0.3
0°-30°	1934.4	29.4
0°-40°	2825.0	43.0
0°-60°	4316.4	65.7
0°-90°	5113.8	77.8
90°-120°	713.0	10.9
90°-150°	1281.7	19.5
90°-180°	1456.0	22.2
0°-180°	6570.1	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	3180	3180	3180	3180	3180	
5°	4007	3782	3197	2576	2367	382
15°	2955	3752	3058	1686	1471	816
25°	1473	2191	2770	1273	1176	695
35°	1068	1328	2310	1029	967	671
45°	844	952	1708	813	818	654
55°	648	687	1080	612	663	580
65°	432	451	592	418	471	430
75°	221	229	264	222	248	233
85°	49	55	52	55	56	54
90°	11	10	1	10	11	9
95°	46	232	13	232	46	74
105°	498	315	46	315	498	497
115°	606	241	80	241	606	591
125°	478	225	112	225	478	433
135°	388	222	131	222	388	301
145°	303	219	149	219	303	192
155°	251	212	170	212	251	117
165°	219	203	185	203	219	63
175°	197	195	193	195	197	19
180°	194	194	194	194	194	



TEST NUMBER: P831110

CATALOG NUMBER: S123DIP-S1000D365U850-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	3180.5	3180.5	3180.5	3180.5	3180.5	3180.5	3180.5	3180.5	3180.5	3180.5	3180.5
2.5°	3584.9	3581.2	3577.5	3559.1	3540.6	3531.8	3522.9	3496.4	3469.8	3440.3	3410.8
5°	4007.0	4017.3	4027.7	4015.9	4004.1	3967.9	3931.7	3883.8	3835.8	3781.9	3728.1
7.5°	4201.8	4207.7	4213.6	4206.2	4198.9	4189.3	4179.7	4136.9	4094.1	4038.7	3983.4
10°	3999.6	4012.9	4026.2	4055.0	4083.7	4116.2	4148.7	4142.8	4136.9	4120.6	4104.4
12.5°	3555.4	3571.6	3587.9	3645.4	3703.0	3776.8	3850.6	3914.0	3977.5	4021.8	4066.0
15°	2954.7	2999.7	3044.7	3097.1	3149.5	3258.0	3366.5	3500.0	3633.6	3752.4	3871.2
17.5°	2433.7	2450.7	2467.7	2523.7	2579.8	2716.4	2852.9	3007.1	3161.3	3358.4	3555.4
20°	2002.8	2018.3	2033.8	2107.6	2181.3	2288.3	2395.3	2568.8	2742.2	2954.0	3165.8
22.5°	1682.5	1706.9	1731.2	1772.5	1813.9	1916.4	2019.0	2173.2	2327.5	2561.4	2795.3
25°	1472.9	1490.6	1508.3	1533.4	1558.5	1640.4	1722.3	1849.3	1976.2	2190.9	2405.7
27.5°	1329.8	1337.1	1344.5	1369.6	1394.7	1447.8	1501.0	1610.2	1719.4	1901.7	2083.9
30°	1217.6	1222.8	1227.9	1250.1	1272.2	1308.4	1344.5	1423.5	1502.4	1663.3	1824.2
32.5°	1139.4	1143.1	1146.8	1163.7	1180.7	1206.5	1232.4	1289.9	1347.5	1480.3	1613.1
35°	1068.5	1070.7	1073.0	1085.5	1098.1	1117.2	1136.4	1180.0	1223.5	1328.3	1433.1
37.5°	1006.5	1009.5	1012.5	1019.8	1027.2	1044.2	1061.2	1095.8	1130.5	1211.0	1291.4
40°	946.0	951.2	956.4	961.5	966.7	980.7	994.7	1021.3	1047.9	1114.3	1180.7
42.5°	894.4	899.5	904.7	906.9	909.1	917.3	925.4	949.7	974.1	1023.5	1073.0
45°	844.2	846.4	848.6	850.8	853.1	859.7	866.3	887.7	909.1	951.9	994.7
47.5°	798.4	798.4	798.4	799.9	801.4	807.3	813.2	828.7	844.2	877.4	910.6
50°	754.2	754.2	754.2	752.0	749.7	753.4	757.1	768.9	780.7	810.3	839.8
52.5°	701.0	701.0	701.0	701.8	702.5	702.5	702.5	712.8	723.2	749.7	776.3
55°	647.9	650.9	653.8	651.6	649.4	650.9	652.3	659.0	665.6	687.0	708.4
57.5°	594.8	596.3	597.7	597.0	596.3	597.0	597.7	603.6	609.5	625.8	642.0
60°	544.6	544.6	544.6	543.1	541.6	543.1	544.6	547.6	550.5	565.3	580.0
62.5°	488.5	489.3	490.0	490.7	491.5	490.0	488.5	492.2	495.9	507.0	518.0
65°	432.4	433.2	433.9	436.1	438.3	436.9	435.4	439.1	442.8	450.9	459.0
67.5°	382.3	380.8	379.3	380.0	380.8	383.0	385.2	385.9	386.7	395.5	404.4
70°	323.2	324.7	326.2	325.4	324.7	325.4	326.2	328.4	330.6	337.2	343.9
72.5°	270.1	270.8	271.6	271.6	271.6	273.0	274.5	276.7	278.9	282.6	286.3
75°	221.4	221.4	221.4	222.9	224.3	225.1	225.8	225.8	225.8	228.8	231.7
77.5°	168.2	171.9	175.6	174.9	174.2	175.6	177.1	179.3	181.5	183.0	184.5
80°	122.5	122.5	122.5	123.2	124.0	126.2	128.4	129.9	131.4	134.3	137.3
82.5°	78.2	79.0	79.7	81.9	84.1	85.6	87.1	89.3	91.5	91.5	91.5
85°	48.7	47.2	45.8	47.2	48.7	50.2	51.7	52.4	53.1	54.6	56.1
87.5°	23.6	23.6	23.6	23.6	23.6	24.4	25.1	25.1	25.1	25.1	25.1
90°	11.4	11.8	11.4	11.0	11.4	10.6	10.2	9.8	9.4	9.8	8.6
92.5°	20.8	21.6	21.2	22.7	23.5	26.3	30.2	38.8	54.5	72.9	80.7
95°	45.5	47.0	49.8	53.3	60.7	74.9	95.6	141.1	188.5	232.4	206.9
97.5°	93.3	97.6	107.0	121.9	148.1	192.8	244.5	324.1	369.6	357.4	266.9
100°	245.7	245.3	260.6	289.2	328.8	384.5	430.3	462.0	448.3	371.1	250.8
102.5°	389.2	400.5	412.7	433.8	462.4	492.6	514.6	507.9	452.3	345.7	227.3
105°	498.5	500.5	513.0	527.9	545.9	556.1	548.7	509.5	427.6	315.1	208.9
107.5°	569.8	574.1	579.2	586.3	588.6	578.1	547.5	486.0	392.3	288.0	195.6
110°	610.6	611.4	612.1	609.0	598.0	570.6	521.2	449.1	359.4	265.7	188.5

TEST NUMBER: P831110

CATALOG NUMBER: S123DIP-S1000D365U850-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	618.8	618.4	614.5	603.1	580.8	543.6	486.7	412.7	330.8	250.8	184.6
115°	606.3	604.3	596.5	579.2	549.8	507.1	449.5	381.3	308.8	241.0	184.2
117.5°	578.8	576.1	564.3	545.1	514.6	470.3	417.4	357.0	294.3	234.4	184.6
120°	542.8	540.4	531.0	509.1	478.1	438.5	391.5	338.6	283.3	230.0	186.2
122.5°	509.1	505.9	495.4	476.2	449.5	413.5	370.7	324.1	274.3	227.3	188.9
125°	478.1	475.4	465.6	448.3	423.3	391.9	354.3	311.6	266.9	225.0	191.6
127.5°	451.5	449.1	440.1	425.2	402.5	373.5	339.0	300.2	259.8	223.8	194.8
130°	429.5	426.4	418.2	404.0	383.3	356.6	324.9	289.6	254.3	222.6	197.9
132.5°	408.0	406.0	399.0	384.8	365.6	340.6	311.6	279.8	249.2	222.2	200.3
135°	387.6	384.8	377.8	366.0	346.8	324.5	299.0	271.2	244.9	221.8	202.6
137.5°	366.0	363.7	357.8	345.7	329.2	309.2	286.5	263.0	241.0	221.0	204.2
140°	343.3	343.7	337.4	326.5	311.6	294.7	275.9	255.9	237.5	220.6	205.7
142.5°	322.1	322.5	317.0	307.6	295.5	281.4	265.7	249.2	234.4	219.9	206.9
145°	302.9	302.2	299.0	290.8	281.0	269.6	257.1	244.2	231.6	219.1	207.3
147.5°	286.5	286.1	283.0	277.1	269.2	261.0	250.4	239.8	228.9	217.9	207.3
150°	272.4	272.4	270.0	265.7	259.8	252.4	244.2	235.1	226.1	216.3	207.3
152.5°	260.6	260.6	259.4	255.5	251.2	245.3	238.3	230.8	223.0	214.4	206.1
155°	251.2	250.8	250.0	246.9	243.4	238.7	232.8	226.5	219.9	212.0	205.4
157.5°	242.2	242.2	241.4	239.1	235.9	232.0	227.3	221.8	216.3	210.1	204.2
160°	233.6	234.0	234.0	231.6	228.9	226.1	222.2	217.9	212.8	207.7	203.4
162.5°	225.7	226.1	226.1	224.2	222.6	220.2	216.7	213.2	209.3	205.4	201.8
165°	219.1	219.1	219.5	217.9	216.3	214.4	211.6	209.3	206.1	203.0	200.3
167.5°	212.4	212.4	212.8	211.6	210.8	209.3	207.7	205.7	203.0	200.7	198.7
170°	206.5	206.5	206.9	206.1	205.7	205.0	203.4	202.2	200.3	198.3	197.1
172.5°	201.0	201.4	202.2	201.4	201.4	201.0	199.9	199.1	197.5	196.3	195.9
175°	197.1	197.5	197.9	197.5	197.5	197.5	196.7	196.3	195.6	194.8	194.8
177.5°	194.4	194.4	195.2	194.8	195.2	195.2	194.8	194.4	194.0	193.6	194.0
180°	193.6	193.6	193.6	193.6	193.6	193.6	193.6	193.6	193.6	193.6	193.6



TEST NUMBER: P831110

CATALOG NUMBER: S123DIP-S1000D365U850-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	3180.5	3180.5	3180.5	3180.5	3180.5	3180.5	3180.5	3180.5	3180.5	3180.5	3180.5
2.5°	3401.9	3393.0	3360.6	3328.1	3291.2	3254.3	3227.0	3199.7	3159.1	3118.5	3085.3
5°	3686.7	3645.4	3576.8	3508.2	3415.2	3322.2	3259.5	3196.7	3112.6	3028.5	2961.3
7.5°	3912.5	3841.7	3745.8	3649.8	3528.1	3406.3	3291.2	3176.1	3047.7	2919.3	2814.5
10°	4056.4	4008.5	3897.8	3787.1	3624.0	3460.9	3300.1	3139.2	2973.9	2808.6	2669.9
12.5°	4070.5	4074.9	3973.1	3871.2	3686.7	3502.3	3306.7	3111.1	2903.0	2695.0	2533.3
15°	3947.2	4023.2	3967.2	3911.1	3725.1	3539.2	3298.6	3058.0	2818.2	2578.4	2391.7
17.5°	3718.5	3881.6	3889.7	3897.8	3711.8	3525.9	3259.5	2993.1	2721.5	2450.0	2253.7
20°	3406.3	3646.9	3729.5	3812.2	3660.9	3509.6	3223.3	2937.0	2633.0	2328.9	2123.0
22.5°	3087.5	3379.8	3531.0	3682.3	3570.1	3458.0	3153.2	2848.4	2527.4	2206.4	1997.6
25°	2724.5	3043.3	3275.7	3508.2	3439.5	3370.9	3070.6	2770.2	2428.6	2086.9	1873.6
27.5°	2407.9	2731.8	3012.3	3292.7	3277.9	3263.2	2965.0	2666.9	2317.1	1967.3	1761.5
30°	2126.0	2427.8	2741.4	3055.1	3091.2	3127.4	2839.6	2551.8	2201.3	1850.7	1652.2
32.5°	1876.6	2140.0	2476.5	2813.0	2883.9	2954.7	2695.0	2435.2	2088.4	1741.5	1550.4
35°	1672.2	1911.3	2247.8	2584.3	2672.8	2761.4	2535.6	2309.7	1971.8	1633.8	1451.5
37.5°	1491.4	1691.4	2019.7	2348.1	2456.6	2565.1	2362.9	2160.7	1844.1	1527.5	1360.0
40°	1341.6	1502.4	1804.3	2106.1	2231.5	2357.0	2190.2	2023.4	1723.1	1422.7	1268.5
42.5°	1216.1	1359.3	1633.1	1906.8	2027.1	2147.4	2006.5	1865.5	1598.4	1331.2	1190.3
45°	1109.1	1223.5	1472.2	1720.9	1835.3	1949.6	1828.6	1707.6	1472.2	1236.8	1105.4
47.5°	1008.8	1106.9	1319.4	1532.0	1633.8	1735.6	1641.2	1546.7	1347.5	1148.2	1029.4
50°	918.7	997.7	1183.7	1369.6	1458.2	1546.7	1463.3	1379.9	1216.1	1052.3	949.0
52.5°	840.5	904.7	1060.4	1216.1	1292.1	1368.1	1296.6	1225.0	1095.1	965.2	875.2
55°	763.0	817.6	952.7	1087.7	1139.4	1191.0	1135.7	1080.3	975.6	870.8	794.8
57.5°	690.7	739.4	850.1	960.8	1000.6	1040.5	990.3	940.1	861.2	782.2	718.8
60°	619.9	659.7	752.0	844.2	868.6	892.9	852.3	811.7	756.4	701.0	644.2
62.5°	554.2	590.4	659.0	727.6	743.8	760.1	729.1	698.1	656.0	614.0	569.7
65°	486.3	513.6	569.7	625.8	636.1	646.4	619.1	591.8	560.1	528.4	495.9
67.5°	423.6	442.8	488.5	534.3	535.0	535.7	513.6	491.5	473.8	456.0	430.2
70°	362.3	380.8	411.0	441.3	442.0	442.8	425.1	407.3	394.1	380.8	361.6
72.5°	299.6	312.9	335.8	358.6	357.2	355.7	344.6	333.5	323.2	312.9	298.9
75°	242.8	253.9	269.3	284.8	280.4	276.0	270.1	264.2	255.3	246.5	237.6
77.5°	191.1	197.8	206.6	215.5	212.5	209.6	204.4	199.2	192.6	186.0	182.3
80°	140.2	143.2	149.1	155.0	153.5	152.0	146.1	140.2	138.7	137.3	132.1
82.5°	95.2	98.9	100.4	101.8	101.1	100.4	95.9	91.5	90.0	88.6	87.8
85°	56.8	57.6	58.3	59.0	56.8	54.6	53.1	51.7	51.7	51.7	50.9
87.5°	25.8	26.6	26.6	26.6	25.8	25.1	23.6	22.1	22.9	23.6	23.6
90°	7.4	6.3	5.1	4.3	3.5	2.4	1.6	0.8	1.6	2.4	3.5
92.5°	60.4	39.6	27.0	20.0	16.1	12.5	8.6	5.9	8.6	12.5	16.1
95°	142.7	84.3	50.9	35.7	25.5	18.8	14.5	13.3	14.5	18.8	25.5
97.5°	158.7	90.9	58.0	41.1	31.0	25.1	21.6	21.2	21.6	25.1	31.0
100°	147.7	89.7	62.3	47.0	37.6	32.1	29.4	29.0	29.4	32.1	37.6
102.5°	138.3	91.3	67.4	53.7	45.5	40.4	38.0	37.2	38.0	40.4	45.5
105°	134.8	94.4	73.3	61.1	53.7	49.0	46.6	45.5	46.6	49.0	53.7
107.5°	134.0	99.5	80.7	69.4	62.3	57.6	55.3	54.1	55.3	57.6	62.3
110°	136.0	106.2	88.6	77.6	70.9	66.6	64.7	63.5	64.7	66.6	70.9



TEST NUMBER: P831110

CATALOG NUMBER: S123DIP-S1000D365U850-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	139.9	112.9	96.8	86.2	79.6	75.2	73.3	72.1	73.3	75.2	79.6
115°	144.2	120.3	105.4	94.8	88.2	84.3	81.9	80.3	81.9	84.3	88.2
117.5°	149.7	128.2	113.3	103.5	96.0	92.5	90.5	88.6	90.5	92.5	96.0
120°	156.0	135.6	121.5	111.7	104.2	100.3	98.4	97.2	98.4	100.3	104.2
122.5°	161.9	143.4	129.7	119.1	112.1	107.8	105.8	104.6	105.8	107.8	112.1
125°	168.1	150.9	137.2	126.6	119.1	114.8	112.5	111.7	112.5	114.8	119.1
127.5°	173.2	157.5	144.2	133.6	125.4	121.1	118.4	117.2	118.4	121.1	125.4
130°	178.3	163.4	150.5	139.9	131.7	127.0	123.4	122.3	123.4	127.0	131.7
132.5°	183.0	168.5	156.0	145.8	137.6	131.7	127.8	126.2	127.8	131.7	137.6
135°	186.9	173.6	161.5	150.9	142.7	136.8	132.5	130.9	132.5	136.8	142.7
137.5°	190.1	177.1	165.4	155.6	147.4	141.1	136.8	135.2	136.8	141.1	147.4
140°	192.4	180.7	169.3	159.5	151.7	145.4	141.5	139.5	141.5	145.4	151.7
142.5°	194.8	183.4	172.4	163.4	155.6	150.1	145.8	144.2	145.8	150.1	155.6
145°	196.3	185.8	175.6	166.6	159.9	154.0	150.5	149.3	150.5	154.0	159.9
147.5°	197.5	187.7	178.3	170.5	163.8	158.7	155.2	154.4	155.2	158.7	163.8
150°	197.9	189.7	180.7	173.6	168.1	163.0	159.9	159.5	159.9	163.0	168.1
152.5°	198.7	190.9	183.4	176.7	172.0	167.7	164.6	164.6	164.6	167.7	172.0
155°	198.7	192.4	185.8	180.3	176.0	172.0	169.7	169.7	169.7	172.0	176.0
157.5°	199.1	193.2	187.7	183.4	179.5	176.0	174.0	173.6	174.0	176.0	179.5
160°	199.1	194.4	189.7	185.8	183.0	179.9	178.3	178.3	178.3	179.9	183.0
162.5°	198.7	194.8	190.9	187.7	185.4	183.0	181.8	181.8	181.8	183.0	185.4
165°	197.9	195.2	192.0	189.3	187.7	185.8	185.0	185.4	185.0	185.8	187.7
167.5°	197.5	195.2	192.8	190.9	189.7	188.1	187.7	188.1	187.7	188.1	189.7
170°	196.3	194.8	192.8	192.0	191.2	190.1	189.7	190.5	189.7	190.1	191.2
172.5°	195.9	194.8	193.2	192.8	192.4	191.6	191.6	192.0	191.6	191.6	192.4
175°	195.2	194.4	193.6	193.2	193.2	192.4	192.8	193.2	192.8	192.4	193.2
177.5°	194.8	194.0	193.6	193.6	193.6	193.2	193.6	194.0	193.6	193.2	193.6
180°	193.6	193.6	193.6	193.6	193.6	193.6	193.6	193.6	193.6	193.6	193.6



TEST NUMBER: P831110

CATALOG NUMBER: S123DIP-S1000D365U850-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	3180.5	3180.5	3180.5	3180.5	3180.5	3180.5	3180.5	3180.5	3180.5	3180.5	3180.5
2.5°	3052.1	3023.3	2994.6	2972.4	2950.3	2912.6	2875.0	2866.2	2857.3	2844.8	2832.2
5°	2894.2	2823.4	2752.5	2689.0	2625.6	2576.1	2526.7	2494.2	2461.8	2438.1	2414.5
7.5°	2709.7	2603.4	2497.2	2421.9	2346.6	2275.1	2203.5	2180.6	2157.7	2126.7	2095.7
10°	2531.1	2413.8	2296.5	2198.3	2100.2	2030.1	1960.0	1931.9	1903.9	1864.8	1825.7
12.5°	2371.7	2243.3	2114.9	2016.0	1917.2	1849.3	1781.4	1740.8	1700.2	1678.1	1655.9
15°	2205.0	2067.7	1930.4	1838.9	1747.4	1686.2	1624.9	1589.5	1554.1	1532.7	1511.3
17.5°	2057.4	1921.6	1785.8	1698.0	1610.2	1554.1	1498.0	1467.0	1436.0	1419.8	1403.6
20°	1917.2	1784.3	1651.5	1565.9	1480.3	1434.6	1388.8	1368.9	1349.0	1335.7	1322.4
22.5°	1788.8	1658.1	1527.5	1454.5	1381.4	1344.5	1307.6	1293.6	1279.6	1268.5	1257.4
25°	1660.4	1543.8	1427.2	1365.2	1303.2	1272.9	1242.7	1228.7	1214.6	1203.6	1192.5
27.5°	1555.6	1444.1	1332.7	1279.6	1226.5	1202.8	1179.2	1168.2	1157.1	1146.8	1136.4
30°	1453.7	1354.1	1254.5	1208.7	1163.0	1141.6	1120.2	1109.1	1098.1	1088.5	1078.9
32.5°	1359.3	1273.7	1188.1	1146.0	1104.0	1086.2	1068.5	1055.3	1042.0	1034.6	1027.2
35°	1269.3	1192.5	1115.8	1081.1	1046.4	1028.7	1011.0	999.9	988.8	982.9	977.0
37.5°	1192.5	1123.9	1055.3	1022.0	988.8	971.9	954.9	945.3	935.7	933.5	931.3
40°	1114.3	1055.3	996.2	963.7	931.3	916.5	901.8	895.9	890.0	888.5	887.0
42.5°	1049.3	991.8	934.2	904.7	875.2	862.6	850.1	847.2	844.2	846.4	848.6
45°	974.1	926.1	878.1	850.8	823.5	813.2	802.9	800.7	798.4	802.9	807.3
47.5°	910.6	866.3	822.1	796.2	770.4	763.0	755.6	754.9	754.2	760.1	766.0
50°	845.7	802.9	760.1	739.4	718.8	712.1	705.5	707.7	709.9	719.5	729.1
52.5°	785.2	745.3	705.5	686.3	667.1	662.7	658.2	663.4	668.6	678.9	689.2
55°	718.8	682.6	646.4	631.7	616.9	612.5	608.1	618.4	628.7	638.3	647.9
57.5°	655.3	623.6	591.8	578.5	565.3	564.5	563.8	573.4	583.0	593.3	603.6
60°	587.4	560.8	534.3	523.9	513.6	515.1	516.6	527.6	538.7	546.8	554.9
62.5°	525.4	503.3	481.1	471.5	461.9	465.6	469.3	480.4	491.5	501.1	510.7
65°	463.4	445.0	426.5	419.9	413.2	418.4	423.6	433.2	442.8	449.4	456.0
67.5°	404.4	388.9	373.4	368.2	363.1	368.2	373.4	383.0	392.6	399.2	405.9
70°	342.4	329.9	317.3	313.6	309.9	315.8	321.7	329.9	338.0	344.6	351.3
72.5°	284.8	275.3	265.7	264.9	264.2	269.3	274.5	282.6	290.7	295.2	299.6
75°	228.8	223.6	218.4	217.7	217.0	222.1	227.3	231.7	236.1	239.8	243.5
77.5°	178.6	174.2	169.7	170.5	171.2	174.9	178.6	183.0	187.4	189.7	191.9
80°	126.9	125.4	124.0	125.4	126.9	129.9	132.8	135.8	138.7	140.2	141.7
82.5°	87.1	85.6	84.1	86.3	88.6	90.8	93.0	95.2	97.4	98.1	98.9
85°	50.2	52.4	54.6	54.6	54.6	55.3	56.1	56.8	57.6	56.8	56.1
87.5°	23.6	24.4	25.1	25.1	25.1	25.8	26.6	26.6	26.6	25.8	25.1
90°	4.3	5.1	6.3	7.4	8.6	9.8	9.4	9.8	10.2	10.6	11.4
92.5°	20.0	27.0	39.6	60.4	80.7	72.9	54.5	38.8	30.2	26.3	23.5
95°	35.7	50.9	84.3	142.7	206.9	232.4	188.5	141.1	95.6	74.9	60.7
97.5°	41.1	58.0	90.9	158.7	266.9	357.4	369.6	324.1	244.5	192.8	148.1
100°	47.0	62.3	89.7	147.7	250.8	371.1	448.3	462.0	430.3	384.5	328.8
102.5°	53.7	67.4	91.3	138.3	227.3	345.7	452.3	507.9	514.6	492.6	462.4
105°	61.1	73.3	94.4	134.8	208.9	315.1	427.6	509.5	548.7	556.1	545.9
107.5°	69.4	80.7	99.5	134.0	195.6	288.0	392.3	486.0	547.5	578.1	588.6
110°	77.6	88.6	106.2	136.0	188.5	265.7	359.4	449.1	521.2	570.6	598.0



TEST NUMBER: P831110

CATALOG NUMBER: S123DIP-S1000D365U850-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	86.2	96.8	112.9	139.9	184.6	250.8	330.8	412.7	486.7	543.6	580.8
115°	94.8	105.4	120.3	144.2	184.2	241.0	308.8	381.3	449.5	507.1	549.8
117.5°	103.5	113.3	128.2	149.7	184.6	234.4	294.3	357.0	417.4	470.3	514.6
120°	111.7	121.5	135.6	156.0	186.2	230.0	283.3	338.6	391.5	438.5	478.1
122.5°	119.1	129.7	143.4	161.9	188.9	227.3	274.3	324.1	370.7	413.5	449.5
125°	126.6	137.2	150.9	168.1	191.6	225.0	266.9	311.6	354.3	391.9	423.3
127.5°	133.6	144.2	157.5	173.2	194.8	223.8	259.8	300.2	339.0	373.5	402.5
130°	139.9	150.5	163.4	178.3	197.9	222.6	254.3	289.6	324.9	356.6	383.3
132.5°	145.8	156.0	168.5	183.0	200.3	222.2	249.2	279.8	311.6	340.6	365.6
135°	150.9	161.5	173.6	186.9	202.6	221.8	244.9	271.2	299.0	324.5	346.8
137.5°	155.6	165.4	177.1	190.1	204.2	221.0	241.0	263.0	286.5	309.2	329.2
140°	159.5	169.3	180.7	192.4	205.7	220.6	237.5	255.9	275.9	294.7	311.6
142.5°	163.4	172.4	183.4	194.8	206.9	219.9	234.4	249.2	265.7	281.4	295.5
145°	166.6	175.6	185.8	196.3	207.3	219.1	231.6	244.2	257.1	269.6	281.0
147.5°	170.5	178.3	187.7	197.5	207.3	217.9	228.9	239.8	250.4	261.0	269.2
150°	173.6	180.7	189.7	197.9	207.3	216.3	226.1	235.1	244.2	252.4	259.8
152.5°	176.7	183.4	190.9	198.7	206.1	214.4	223.0	230.8	238.3	245.3	251.2
155°	180.3	185.8	192.4	198.7	205.4	212.0	219.9	226.5	232.8	238.7	243.4
157.5°	183.4	187.7	193.2	199.1	204.2	210.1	216.3	221.8	227.3	232.0	235.9
160°	185.8	189.7	194.4	199.1	203.4	207.7	212.8	217.9	222.2	226.1	228.9
162.5°	187.7	190.9	194.8	198.7	201.8	205.4	209.3	213.2	216.7	220.2	222.6
165°	189.3	192.0	195.2	197.9	200.3	203.0	206.1	209.3	211.6	214.4	216.3
167.5°	190.9	192.8	195.2	197.5	198.7	200.7	203.0	205.7	207.7	209.3	210.8
170°	192.0	192.8	194.8	196.3	197.1	198.3	200.3	202.2	203.4	205.0	205.7
172.5°	192.8	193.2	194.8	195.9	195.9	196.3	197.5	199.1	199.9	201.0	201.4
175°	193.2	193.6	194.4	195.2	194.8	194.8	195.6	196.3	196.7	197.5	197.5
177.5°	193.6	193.6	194.0	194.8	194.0	193.6	194.0	194.4	194.8	195.2	195.2
180°	193.6	193.6	193.6	193.6	193.6	193.6	193.6	193.6	193.6	193.6	193.6



TEST NUMBER: P831110

CATALOG NUMBER: S123DIP-S1000D365U850-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	3180.5	3180.5	3180.5	3180.5
2.5°	2827.0	2821.9	2801.2	2780.6
5°	2396.8	2379.1	2373.2	2367.3
7.5°	2094.3	2092.8	2061.8	2030.8
10°	1827.9	1830.1	1802.0	1774.0
12.5°	1637.5	1619.0	1616.8	1614.6
15°	1494.3	1477.4	1474.4	1471.4
17.5°	1393.2	1382.9	1379.9	1377.0
20°	1316.5	1310.6	1305.4	1300.2
22.5°	1250.1	1242.7	1238.3	1233.8
25°	1185.9	1179.2	1177.7	1176.3
27.5°	1128.3	1120.2	1120.2	1120.2
30°	1073.7	1068.5	1066.3	1064.1
32.5°	1022.8	1018.4	1018.4	1018.4
35°	974.8	972.6	969.7	966.7
37.5°	931.3	931.3	929.8	928.3
40°	889.2	891.4	891.4	891.4
42.5°	850.8	853.1	853.1	853.1
45°	811.0	814.7	816.2	817.6
47.5°	771.9	777.8	779.3	780.7
50°	733.5	737.9	738.7	739.4
52.5°	694.4	699.6	703.3	706.9
55°	653.1	658.2	660.5	662.7
57.5°	608.8	614.0	614.7	615.4
60°	560.1	565.3	566.7	568.2
62.5°	513.6	516.6	518.0	519.5
65°	460.5	464.9	467.9	470.8
67.5°	409.6	413.2	413.2	413.2
70°	352.7	354.2	356.4	358.6
72.5°	300.3	301.1	301.1	301.1
75°	245.0	246.5	247.2	247.9
77.5°	192.6	193.3	193.3	193.3
80°	140.9	140.2	140.2	140.2
82.5°	96.7	94.5	94.5	94.5
85°	55.3	54.6	55.3	56.1
87.5°	25.1	25.1	25.1	25.1
90°	11.0	11.4	11.8	11.4
92.5°	22.7	21.2	21.6	20.8
95°	53.3	49.8	47.0	45.5
97.5°	121.9	107.0	97.6	93.3
100°	289.2	260.6	245.3	245.7
102.5°	433.8	412.7	400.5	389.2
105°	527.9	513.0	500.5	498.5
107.5°	586.3	579.2	574.1	569.8
110°	609.0	612.1	611.4	610.6



TEST NUMBER: P831110

CATALOG NUMBER: S123DIP-S1000D365U850-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
112.5°	603.1	614.5	618.4	618.8
115°	579.2	596.5	604.3	606.3
117.5°	545.1	564.3	576.1	578.8
120°	509.1	531.0	540.4	542.8
122.5°	476.2	495.4	505.9	509.1
125°	448.3	465.6	475.4	478.1
127.5°	425.2	440.1	449.1	451.5
130°	404.0	418.2	426.4	429.5
132.5°	384.8	399.0	406.0	408.0
135°	366.0	377.8	384.8	387.6
137.5°	345.7	357.8	363.7	366.0
140°	326.5	337.4	343.7	343.3
142.5°	307.6	317.0	322.5	322.1
145°	290.8	299.0	302.2	302.9
147.5°	277.1	283.0	286.1	286.5
150°	265.7	270.0	272.4	272.4
152.5°	255.5	259.4	260.6	260.6
155°	246.9	250.0	250.8	251.2
157.5°	239.1	241.4	242.2	242.2
160°	231.6	234.0	234.0	233.6
162.5°	224.2	226.1	226.1	225.7
165°	217.9	219.5	219.1	219.1
167.5°	211.6	212.8	212.4	212.4
170°	206.1	206.9	206.5	206.5
172.5°	201.4	202.2	201.4	201.0
175°	197.5	197.9	197.5	197.1
177.5°	194.8	195.2	194.4	194.4
180°	193.6	193.6	193.6	193.6



TEST NUMBER: P831110

CATALOG NUMBER: S123DIP-S1000D365U850-4F0-1E-UDD-G4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.14	19.25	18.82	19.95	20.76	20.37	21.49	21.06	22.18	23.00
	3H	19.80	20.80	20.50	21.51	22.35	21.82	22.82	22.51	23.52	24.37
	4H	20.39	21.33	21.11	22.05	22.91	22.28	23.22	22.99	23.94	24.80
	6H	20.77	21.64	21.50	22.37	23.24	22.57	23.44	23.30	24.16	25.03
	8H	20.88	21.70	21.62	22.45	23.32	22.64	23.46	23.38	24.21	25.08
	12H	20.93	21.72	21.68	22.46	23.36	22.66	23.45	23.41	24.19	25.09
4H	2H	18.74	19.68	19.46	20.40	21.26	20.57	21.51	21.29	22.22	23.08
	3H	20.59	21.38	21.32	22.13	23.00	22.21	22.99	22.94	23.74	24.62
	4H	21.30	22.01	22.05	22.76	23.67	22.80	23.51	23.55	24.27	25.17
	6H	21.79	22.40	22.55	23.18	24.10	23.22	23.83	23.98	24.61	25.53
	8H	21.93	22.50	22.70	23.28	24.20	23.34	23.91	24.10	24.68	25.61
	12H	22.01	22.52	22.80	23.32	24.25	23.39	23.91	24.18	24.71	25.64
8H	4H	21.58	22.16	22.35	22.93	23.86	22.93	23.50	23.69	24.27	25.20
	6H	22.18	22.66	22.98	23.47	24.40	23.44	23.91	24.24	24.73	25.66
	8H	22.39	22.81	23.20	23.63	24.57	23.62	24.04	24.43	24.86	25.80
	12H	22.53	22.90	23.34	23.70	24.71	23.73	24.10	24.54	24.91	25.91
12H	4H	21.60	22.11	22.39	22.91	23.84	22.91	23.43	23.70	24.22	25.16
	6H	22.23	22.66	23.04	23.47	24.42	23.45	23.87	24.26	24.69	25.63
	8H	22.48	22.85	23.29	23.66	24.66	23.66	24.03	24.48	24.84	25.84