

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831191

Luminaire Tested: S123DIP-S1165D1025U850-4F0-1E-UDD-G4

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P831191
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-1, G3-1807-864-17)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-S1165D1025U850-4F0-1E-UDD-G4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, GRAZE OPTIC
UPLIGHT 1025 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10021.4 lumens
Efficiency: N/A
Efficacy: 147.2 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 1.19 / 0.89
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 68.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P831191
CATALOG NUMBER: S123DIP-S1165D1025U850-4F0-1E-UDD-G4

Luminous Intensity Polar Plot





TEST NUMBER: P831191

CATALOG NUMBER: S123DIP-S1165D1025U850-4F0-1E-UDD-G4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59				
1	100	96	92	89	94	90	87	84	78	76	74	68	66	64	58	57	56	51				
2	92	85	79	74	86	79	74	70	69	66	62	60	57	55	52	50	48	44				
3	84	75	68	63	79	71	64	59	62	57	53	54	50	47	46	44	42	38				
4	78	67	60	54	72	63	56	51	56	50	46	49	45	41	42	39	36	33				
5	72	60	52	47	67	57	50	45	50	45	40	44	40	36	38	35	32	29				
6	66	55	47	41	62	52	44	39	46	40	36	40	36	32	35	32	29	26				
7	62	50	42	37	58	47	40	35	42	36	32	37	32	29	32	29	26	24				
8	58	45	38	33	54	43	36	31	38	33	29	34	30	26	30	27	24	22				
9	54	42	35	30	50	40	33	28	36	30	26	32	27	24	28	24	22	20				
10	50	39	32	27	47	37	30	26	33	28	24	30	25	22	26	23	20	18				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	39539	39539	39539	39539	39539
5°	50004	47195	39892	32148	29542
10°	50489	52017	39628	25626	22394
15°	38028	48294	39357	21701	18937
20°	26496	39079	38854	18978	17202
25°	20203	30053	37998	17461	16134
30°	17478	23876	36630	16388	15275
35°	16216	20159	35053	15612	14671
40°	15352	18083	32836	14873	14466
45°	14842	16736	30020	14297	14375
50°	14585	15671	26688	13772	14301
55°	14043	14891	23415	13275	14362
60°	13541	14053	20182	12807	14127
65°	12720	13262	17408	12307	13848
70°	11748	12258	14807	11481	13036
75°	10634	10988	12689	10667	11911
80°	8771	9614	10036	9298	10036
85°	6941	7793	7373	7892	8003

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 34276 cd/sqm



TEST NUMBER: P831191

CATALOG NUMBER: S123DIP-S1165D1025U850-4F0-1E-UDD-G4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	347.3	3.5
10°-20°	863.9	8.6
20°-30°	1022.9	10.2
30°-40°	1028.5	10.3
40°-50°	943.7	9.4
50°-60°	778.9	7.8
60°-70°	551.0	5.5
70°-80°	294.1	2.9
80°-90°	77.7	0.8
90°-100°	296.8	3.0
100°-110°	868.8	8.7
110°-120°	848.4	8.5
120°-130°	675.7	6.7
130°-140°	533.1	5.3
140°-150°	397.7	4.0
150°-160°	277.3	2.8
160°-170°	162.9	1.6
170°-180°	53.0	0.5
0°-30°	2234.1	22.3
0°-40°	3262.7	32.6
0°-60°	4985.2	49.7
0°-90°	5907.9	59.0
90°-120°	2013.9	20.1
90°-150°	3620.3	36.1
90°-180°	4113.0	41.0
0°-180°	10021.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	3673	3673	3673	3673	3673	
5°	4628	4368	3692	2975	2734	441
15°	3412	4334	3532	1947	1699	943
25°	1701	2530	3199	1470	1358	803
35°	1234	1534	2668	1188	1116	775
45°	975	1099	1972	939	944	755
55°	748	794	1248	707	765	670
65°	499	521	684	483	544	496
75°	256	264	305	256	286	269
85°	56	63	60	64	65	63
90°	32	28	2	28	32	21
95°	128	656	38	656	128	209
105°	1408	890	128	890	1408	1405
115°	1712	681	227	681	1712	1670
125°	1350	635	316	635	1350	1222
135°	1095	627	370	627	1095	849
145°	856	619	422	619	856	543
155°	710	599	479	599	710	331
165°	619	573	524	573	619	177
175°	557	550	546	550	557	54
180°	547	547	547	547	547	

TEST NUMBER: P831191

CATALOG NUMBER: S123DIP-S1165D1025U850-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	3673.3	3673.3	3673.3	3673.3	3673.3	3673.3	3673.3	3673.3	3673.3	3673.3	3673.3
2.5°	4140.3	4136.1	4131.8	4110.5	4089.2	4079.0	4068.7	4038.0	4007.4	3973.3	3939.2
5°	4627.8	4639.7	4651.7	4638.0	4624.4	4582.6	4540.9	4485.5	4430.1	4367.9	4305.7
7.5°	4852.8	4859.6	4866.5	4857.9	4849.4	4838.3	4827.2	4777.8	4728.4	4664.5	4600.5
10°	4619.3	4634.6	4650.0	4683.2	4716.5	4754.0	4791.5	4784.6	4777.8	4759.1	4740.3
12.5°	4106.2	4125.0	4143.7	4210.2	4276.7	4361.9	4447.1	4520.4	4593.7	4644.9	4696.0
15°	3412.5	3464.5	3516.5	3577.0	3637.5	3762.8	3888.0	4042.3	4196.6	4333.8	4471.0
17.5°	2810.8	2830.4	2850.0	2914.8	2979.5	3137.2	3294.9	3473.0	3651.1	3878.7	4106.2
20°	2313.1	2331.0	2348.9	2434.1	2519.3	2642.9	2766.5	2966.7	3167.0	3411.6	3656.2
22.5°	1943.2	1971.3	1999.4	2047.1	2094.9	2213.3	2331.8	2509.9	2688.1	2958.2	3228.4
25°	1701.1	1721.6	1742.0	1771.0	1800.0	1894.6	1989.2	2135.8	2282.4	2530.4	2778.4
27.5°	1535.8	1544.3	1552.8	1581.8	1610.8	1672.2	1733.5	1859.6	1985.8	2196.3	2406.8
30°	1406.2	1412.2	1418.2	1443.7	1469.3	1511.1	1552.8	1644.0	1735.2	1921.0	2106.8
32.5°	1315.9	1320.2	1324.4	1344.0	1363.6	1393.5	1423.3	1489.8	1556.2	1709.7	1863.1
35°	1234.1	1236.6	1239.2	1253.7	1268.2	1290.3	1312.5	1362.8	1413.1	1534.1	1655.1
37.5°	1162.5	1165.9	1169.3	1177.8	1186.4	1206.0	1225.6	1265.6	1305.7	1398.6	1491.5
40°	1092.6	1098.6	1104.5	1110.5	1116.5	1132.7	1148.9	1179.5	1210.2	1286.9	1363.6
42.5°	1032.9	1038.9	1044.9	1047.4	1050.0	1059.4	1068.7	1096.9	1125.0	1182.1	1239.2
45°	975.0	977.6	980.1	982.7	985.2	992.9	1000.6	1025.3	1050.0	1099.4	1148.9
47.5°	922.2	922.2	922.2	923.9	925.6	932.4	939.2	957.1	975.0	1013.3	1051.7
50°	871.0	871.0	871.0	868.5	865.9	870.2	874.4	888.1	901.7	935.8	969.9
52.5°	809.7	809.7	809.7	810.5	811.4	811.4	811.4	823.3	835.2	865.9	896.6
55°	748.3	751.7	755.1	752.6	750.0	751.7	753.4	761.1	768.7	793.5	818.2
57.5°	686.9	688.6	690.3	689.5	688.6	689.5	690.3	697.2	704.0	722.7	741.5
60°	629.0	629.0	629.0	627.3	625.6	627.3	629.0	632.4	635.8	652.8	669.9
62.5°	564.2	565.1	565.9	566.8	567.6	565.9	564.2	568.5	572.7	585.5	598.3
65°	499.4	500.3	501.1	503.7	506.2	504.5	502.8	507.1	511.4	520.7	530.1
67.5°	441.5	439.8	438.1	438.9	439.8	442.3	444.9	445.7	446.6	456.8	467.0
70°	373.3	375.0	376.7	375.9	375.0	375.9	376.7	379.3	381.8	389.5	397.2
72.5°	311.9	312.8	313.6	313.6	313.6	315.3	317.0	319.6	322.2	326.4	330.7
75°	255.7	255.7	255.7	257.4	259.1	259.9	260.8	260.8	260.8	264.2	267.6
77.5°	194.3	198.6	202.8	202.0	201.1	202.8	204.5	207.1	209.7	211.4	213.1
80°	141.5	141.5	141.5	142.3	143.2	145.7	148.3	150.0	151.7	155.1	158.5
82.5°	90.3	91.2	92.0	94.6	97.2	98.9	100.6	103.1	105.7	105.7	105.7
85°	56.2	54.5	52.8	54.5	56.2	58.0	59.7	60.5	61.4	63.1	64.8
87.5°	27.3	27.3	27.3	27.3	27.3	28.1	29.0	29.0	29.0	29.0	29.0
90°	32.1	33.2	32.1	31.0	32.1	29.9	28.8	27.7	26.6	27.7	24.4
92.5°	58.7	60.9	59.8	64.2	66.4	74.2	85.2	109.6	153.9	205.9	228.0
95°	128.4	132.8	140.6	150.5	171.6	211.4	270.1	398.5	532.5	656.4	584.5
97.5°	263.5	275.6	302.2	344.3	418.4	544.6	690.8	915.5	1043.9	1009.6	753.9
100°	694.1	693.0	736.1	817.0	928.8	1085.9	1215.5	1305.1	1266.4	1048.3	708.5
102.5°	1099.2	1131.3	1165.7	1225.4	1306.2	1391.5	1453.5	1434.6	1277.5	976.4	642.0
105°	1408.1	1413.6	1449.0	1491.1	1542.0	1570.8	1549.8	1439.1	1207.7	890.0	590.0
107.5°	1609.5	1621.7	1636.1	1656.0	1662.7	1632.8	1546.5	1372.7	1108.1	813.6	552.4
110°	1724.7	1726.9	1729.1	1720.2	1689.3	1611.8	1472.3	1268.6	1015.1	750.5	532.5



TEST NUMBER: P831191

CATALOG NUMBER: S123DIP-S1165D1025U850-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1747.9	1746.8	1735.7	1703.6	1640.5	1535.4	1374.9	1165.7	934.3	708.5	521.4
115°	1712.5	1707.0	1684.8	1636.1	1553.1	1432.4	1269.7	1077.1	872.3	680.8	520.3
117.5°	1635.0	1627.3	1594.1	1539.8	1453.5	1328.4	1178.9	1008.5	831.3	662.0	521.4
120°	1533.2	1526.5	1500.0	1438.0	1350.5	1238.7	1105.9	956.4	800.3	649.8	525.8
122.5°	1438.0	1429.1	1399.2	1345.0	1269.7	1167.9	1047.2	915.5	774.9	642.0	533.6
125°	1350.5	1342.8	1315.1	1266.4	1195.5	1107.0	1000.7	880.0	753.9	635.4	541.3
127.5°	1275.2	1268.6	1243.1	1201.1	1136.9	1055.0	957.5	847.9	733.9	632.1	550.2
130°	1213.3	1204.4	1181.1	1141.3	1082.6	1007.4	917.7	818.1	718.4	628.8	559.0
132.5°	1152.4	1146.8	1126.9	1087.1	1032.8	962.0	880.0	790.4	704.0	627.7	565.7
135°	1094.8	1087.1	1067.1	1033.9	979.7	916.6	844.6	766.0	691.9	626.6	572.3
137.5°	1033.9	1027.3	1010.7	976.4	929.9	873.4	809.2	742.8	680.8	624.3	576.7
140°	969.7	970.8	953.1	922.1	880.0	832.4	779.3	722.9	670.8	623.2	581.2
142.5°	909.9	911.0	895.5	869.0	834.7	794.8	750.5	704.0	662.0	621.0	584.5
145°	855.7	853.5	844.6	821.4	793.7	761.6	726.2	689.6	654.2	618.8	585.6
147.5°	809.2	808.1	799.2	782.6	760.5	737.2	707.4	677.5	646.5	615.5	585.6
150°	769.4	769.4	762.7	750.5	733.9	712.9	689.6	664.2	638.7	611.1	585.6
152.5°	736.1	736.1	732.8	721.8	709.6	693.0	673.0	652.0	629.9	605.5	582.3
155°	709.6	708.5	706.3	697.4	687.4	674.2	657.5	639.8	621.0	598.9	580.1
157.5°	684.1	684.1	681.9	675.3	666.4	655.3	642.0	626.6	611.1	593.3	576.7
160°	659.8	660.9	660.9	654.2	646.5	638.7	627.7	615.5	601.1	586.7	574.5
162.5°	637.6	638.7	638.7	633.2	628.8	622.1	612.2	602.2	591.1	580.1	570.1
165°	618.8	618.8	619.9	615.5	611.1	605.5	597.8	591.1	582.3	573.4	565.7
167.5°	600.0	600.0	601.1	597.8	595.6	591.1	586.7	581.2	573.4	566.8	561.2
170°	583.4	583.4	584.5	582.3	581.2	579.0	574.5	571.2	565.7	560.1	556.8
172.5°	567.9	569.0	571.2	569.0	569.0	567.9	564.6	562.3	557.9	554.6	553.5
175°	556.8	557.9	559.0	557.9	557.9	557.9	555.7	554.6	552.4	550.2	550.2
177.5°	549.1	549.1	551.3	550.2	551.3	551.3	550.2	549.1	548.0	546.8	548.0
180°	546.8	546.8	546.8	546.8	546.8	546.8	546.8	546.8	546.8	546.8	546.8



TEST NUMBER: P831191

CATALOG NUMBER: S123DIP-S1165D1025U850-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	3673.3	3673.3	3673.3	3673.3	3673.3	3673.3	3673.3	3673.3	3673.3	3673.3	3673.3
2.5°	3929.0	3918.7	3881.2	3843.7	3801.1	3758.5	3727.0	3695.4	3648.6	3601.7	3563.3
5°	4257.9	4210.2	4130.9	4051.7	3944.3	3836.9	3764.5	3692.0	3594.9	3497.7	3420.2
7.5°	4518.7	4436.9	4326.1	4215.3	4074.7	3934.1	3801.1	3668.2	3519.9	3371.6	3250.6
10°	4684.9	4629.5	4501.7	4373.8	4185.5	3997.1	3811.3	3625.6	3434.6	3243.7	3083.5
12.5°	4701.1	4706.2	4588.6	4471.0	4257.9	4044.9	3819.0	3593.2	3352.8	3112.5	2925.8
15°	4558.8	4646.6	4581.8	4517.0	4302.3	4087.5	3809.6	3531.8	3254.8	2977.8	2762.2
17.5°	4294.6	4482.9	4492.3	4501.7	4286.9	4072.1	3764.5	3456.8	3143.2	2829.5	2602.8
20°	3934.1	4211.9	4307.4	4402.8	4228.1	4053.4	3722.7	3392.0	3040.9	2689.8	2452.0
22.5°	3565.9	3903.4	4078.1	4252.8	4123.3	3993.7	3641.7	3289.8	2919.0	2548.3	2307.1
25°	3146.6	3514.8	3783.2	4051.7	3972.4	3893.2	3546.3	3199.4	2804.8	2410.2	2163.9
27.5°	2781.0	3155.1	3479.0	3802.8	3785.8	3768.7	3424.4	3080.1	2676.1	2272.1	2034.4
30°	2455.4	2804.0	3166.2	3528.4	3570.2	3611.9	3279.5	2947.1	2542.3	2137.5	1908.2
32.5°	2167.3	2471.6	2860.2	3248.8	3330.7	3412.5	3112.5	2812.5	2411.9	2011.4	1790.6
35°	1931.2	2207.4	2596.0	2984.6	3086.9	3189.2	2928.4	2667.6	2277.3	1886.9	1676.4
37.5°	1722.4	1953.4	2332.7	2711.9	2837.2	2962.5	2729.0	2495.4	2129.8	1764.2	1570.7
40°	1549.4	1735.2	2083.8	2432.4	2577.3	2722.1	2529.5	2336.9	1990.0	1643.2	1465.0
42.5°	1404.5	1569.9	1886.1	2202.3	2341.2	2480.1	2317.3	2154.5	1846.0	1537.5	1374.7
45°	1281.0	1413.1	1700.3	1987.5	2119.6	2251.7	2111.9	1972.1	1700.3	1428.4	1276.7
47.5°	1165.1	1278.4	1523.9	1769.3	1886.9	2004.5	1895.4	1786.4	1556.2	1326.1	1188.9
50°	1061.1	1152.3	1367.0	1581.8	1684.1	1786.4	1690.0	1593.7	1404.5	1215.3	1096.0
52.5°	970.7	1044.9	1224.7	1404.5	1492.3	1580.1	1497.4	1414.8	1264.8	1114.8	1010.8
55°	881.2	944.3	1100.3	1256.2	1315.9	1375.6	1311.6	1247.7	1126.7	1005.7	917.9
57.5°	797.7	854.0	981.8	1109.7	1155.7	1201.7	1143.7	1085.8	994.6	903.4	830.1
60°	715.9	761.9	868.5	975.0	1003.1	1031.2	984.4	937.5	873.6	809.7	744.0
62.5°	640.1	681.8	761.1	840.3	859.1	877.8	842.0	806.2	757.7	709.1	658.0
65°	561.6	593.2	658.0	722.7	734.7	746.6	715.1	683.5	646.9	610.2	572.7
67.5°	489.2	511.4	564.2	617.0	617.9	618.7	593.2	567.6	547.2	526.7	496.9
70°	418.5	439.8	474.7	509.7	510.5	511.4	490.9	470.5	455.1	439.8	417.6
72.5°	346.0	361.4	387.8	414.2	412.5	410.8	398.0	385.2	373.3	361.4	345.2
75°	280.4	293.2	311.1	329.0	323.9	318.7	311.9	305.1	294.9	284.7	274.4
77.5°	220.7	228.4	238.6	248.9	245.5	242.0	236.1	230.1	222.4	214.8	210.5
80°	161.9	165.3	172.2	179.0	177.3	175.6	168.7	161.9	160.2	158.5	152.6
82.5°	109.9	114.2	115.9	117.6	116.8	115.9	110.8	105.7	104.0	102.3	101.4
85°	65.6	66.5	67.3	68.2	65.6	63.1	61.4	59.7	59.7	59.7	58.8
87.5°	29.8	30.7	30.7	30.7	29.8	29.0	27.3	25.6	26.4	27.3	27.3
90°	21.0	17.7	14.4	12.2	10.0	6.6	4.4	2.2	4.4	6.6	10.0
92.5°	170.5	111.8	76.4	56.5	45.4	35.4	24.4	16.6	24.4	35.4	45.4
95°	402.9	238.0	143.9	100.7	72.0	53.1	41.0	37.6	41.0	53.1	72.0
97.5°	448.3	256.8	163.8	116.2	87.5	70.8	60.9	59.8	60.9	70.8	87.5
100°	417.3	253.5	176.0	132.8	106.3	90.8	83.0	81.9	83.0	90.8	106.3
102.5°	390.8	257.9	190.4	151.7	128.4	114.0	107.4	105.2	107.4	114.0	128.4
105°	380.8	266.8	207.0	172.7	151.7	138.4	131.7	128.4	131.7	138.4	151.7
107.5°	378.6	281.2	228.0	195.9	176.0	162.7	156.1	152.8	156.1	162.7	176.0
110°	384.1	300.0	250.2	219.2	200.4	188.2	182.7	179.3	182.7	188.2	200.4



TEST NUMBER: P831191

CATALOG NUMBER: S123DIP-S1165D1025U850-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	395.2	318.8	273.4	243.5	224.7	212.5	207.0	203.7	207.0	212.5	224.7
115°	407.4	339.8	297.8	267.9	249.1	238.0	231.4	226.9	231.4	238.0	249.1
117.5°	422.9	362.0	319.9	292.2	271.2	261.2	255.7	250.2	255.7	261.2	271.2
120°	440.6	383.0	343.2	315.5	294.5	283.4	277.9	274.5	277.9	283.4	294.5
122.5°	457.2	405.2	366.4	336.5	316.6	304.4	298.9	295.6	298.9	304.4	316.6
125°	474.9	426.2	387.4	357.6	336.5	324.3	317.7	315.5	317.7	324.3	336.5
127.5°	489.3	445.0	407.4	377.5	354.2	342.1	334.3	331.0	334.3	342.1	354.2
130°	503.7	461.6	425.1	395.2	371.9	358.7	348.7	345.4	348.7	358.7	371.9
132.5°	517.0	476.0	440.6	411.8	388.6	371.9	360.9	356.4	360.9	371.9	388.6
135°	528.0	490.4	456.1	426.2	402.9	386.3	374.2	369.7	374.2	386.3	402.9
137.5°	536.9	500.4	467.1	439.5	416.2	398.5	386.3	381.9	386.3	398.5	416.2
140°	543.5	510.3	478.2	450.5	428.4	410.7	399.6	394.1	399.6	410.7	428.4
142.5°	550.2	518.1	487.1	461.6	439.5	424.0	411.8	407.4	411.8	424.0	439.5
145°	554.6	524.7	495.9	470.5	451.6	435.0	425.1	421.8	425.1	435.0	451.6
147.5°	557.9	530.2	503.7	481.5	462.7	448.3	438.4	436.2	438.4	448.3	462.7
150°	559.0	535.8	510.3	490.4	474.9	460.5	451.6	450.5	451.6	460.5	474.9
152.5°	561.2	539.1	518.1	499.2	486.0	473.8	464.9	464.9	464.9	473.8	486.0
155°	561.2	543.5	524.7	509.2	497.0	486.0	479.3	479.3	479.3	486.0	497.0
157.5°	562.3	545.7	530.2	518.1	507.0	497.0	491.5	490.4	491.5	497.0	507.0
160°	562.3	549.1	535.8	524.7	517.0	508.1	503.7	503.7	503.7	508.1	517.0
162.5°	561.2	550.2	539.1	530.2	523.6	517.0	513.6	513.6	513.6	517.0	523.6
165°	559.0	551.3	542.4	534.7	530.2	524.7	522.5	523.6	522.5	524.7	530.2
167.5°	557.9	551.3	544.6	539.1	535.8	531.4	530.2	531.4	530.2	531.4	535.8
170°	554.6	550.2	544.6	542.4	540.2	536.9	535.8	538.0	535.8	536.9	540.2
172.5°	553.5	550.2	545.7	544.6	543.5	541.3	541.3	542.4	541.3	541.3	543.5
175°	551.3	549.1	546.8	545.7	545.7	543.5	544.6	545.7	544.6	543.5	545.7
177.5°	550.2	548.0	546.8	546.8	546.8	545.7	546.8	548.0	546.8	545.7	546.8
180°	546.8	546.8	546.8	546.8	546.8	546.8	546.8	546.8	546.8	546.8	546.8



TEST NUMBER: P831191

CATALOG NUMBER: S123DIP-S1165D1025U850-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	3673.3	3673.3	3673.3	3673.3	3673.3	3673.3	3673.3	3673.3	3673.3	3673.3	3673.3
2.5°	3525.0	3491.7	3458.5	3432.9	3407.4	3363.9	3320.4	3310.2	3300.0	3285.5	3271.0
5°	3342.6	3260.8	3179.0	3105.7	3032.4	2975.3	2918.2	2880.7	2843.2	2815.9	2788.6
7.5°	3129.5	3006.8	2884.1	2797.1	2710.2	2627.5	2544.9	2518.5	2492.0	2456.2	2420.4
10°	2923.3	2787.8	2652.3	2538.9	2425.6	2344.6	2263.6	2231.2	2198.9	2153.7	2108.5
12.5°	2739.2	2590.9	2442.6	2328.4	2214.2	2135.8	2057.4	2010.5	1963.6	1938.1	1912.5
15°	2546.6	2388.1	2229.5	2123.9	2018.2	1947.4	1876.7	1835.8	1794.9	1770.2	1745.4
17.5°	2376.1	2219.3	2062.5	1961.1	1859.6	1794.9	1730.1	1694.3	1658.5	1639.8	1621.0
20°	2214.2	2060.8	1907.4	1808.5	1709.7	1656.8	1604.0	1581.0	1557.9	1542.6	1527.3
22.5°	2065.9	1915.0	1764.2	1679.8	1595.4	1552.8	1510.2	1494.0	1477.8	1465.0	1452.3
25°	1917.6	1782.9	1648.3	1576.7	1505.1	1470.2	1435.2	1419.0	1402.8	1390.0	1377.3
27.5°	1796.6	1667.9	1539.2	1477.8	1416.5	1389.2	1361.9	1349.1	1336.4	1324.4	1312.5
30°	1679.0	1563.9	1448.9	1396.0	1343.2	1318.5	1293.7	1281.0	1268.2	1257.1	1246.0
32.5°	1569.9	1471.0	1372.2	1323.6	1275.0	1254.5	1234.1	1218.7	1203.4	1194.9	1186.4
35°	1465.9	1377.3	1288.6	1248.6	1208.5	1188.1	1167.6	1154.8	1142.0	1135.2	1128.4
37.5°	1377.3	1298.0	1218.7	1180.4	1142.0	1122.4	1102.8	1091.8	1080.7	1078.1	1075.6
40°	1286.9	1218.7	1150.6	1113.1	1075.6	1058.5	1041.5	1034.7	1027.8	1026.1	1024.4
42.5°	1211.9	1145.4	1079.0	1044.9	1010.8	996.3	981.8	978.4	975.0	977.6	980.1
45°	1125.0	1069.6	1014.2	982.7	951.1	939.2	927.3	924.7	922.2	927.3	932.4
47.5°	1051.7	1000.6	949.4	919.6	889.8	881.2	872.7	871.9	871.0	877.8	884.7
50°	976.7	927.3	877.8	854.0	830.1	822.4	814.8	817.3	819.9	831.0	842.0
52.5°	906.8	860.8	814.8	792.6	770.5	765.3	760.2	766.2	772.2	784.1	796.0
55°	830.1	788.3	746.6	729.5	712.5	707.4	702.3	714.2	726.1	737.2	748.3
57.5°	756.8	720.2	683.5	668.2	652.8	652.0	651.1	662.2	673.3	685.2	697.2
60°	678.4	647.7	617.0	605.1	593.2	594.9	596.6	609.4	622.2	631.5	640.9
62.5°	606.8	581.2	555.7	544.6	533.5	537.8	542.0	554.8	567.6	578.7	589.8
65°	535.2	513.9	492.6	484.9	477.3	483.2	489.2	500.3	511.4	519.0	526.7
67.5°	467.0	449.1	431.2	425.3	419.3	425.3	431.2	442.3	453.4	461.1	468.7
70°	395.5	381.0	366.5	362.2	358.0	364.8	371.6	381.0	390.3	398.0	405.7
72.5°	329.0	317.9	306.8	306.0	305.1	311.1	317.0	326.4	335.8	340.9	346.0
75°	264.2	258.2	252.3	251.4	250.6	256.5	262.5	267.6	272.7	277.0	281.2
77.5°	206.2	201.1	196.0	196.9	197.7	202.0	206.2	211.4	216.5	219.0	221.6
80°	146.6	144.9	143.2	144.9	146.6	150.0	153.4	156.8	160.2	161.9	163.6
82.5°	100.6	98.9	97.2	99.7	102.3	104.8	107.4	109.9	112.5	113.4	114.2
85°	58.0	60.5	63.1	63.1	63.1	63.9	64.8	65.6	66.5	65.6	64.8
87.5°	27.3	28.1	29.0	29.0	29.0	29.8	30.7	30.7	30.7	29.8	29.0
90°	12.2	14.4	17.7	21.0	24.4	27.7	26.6	27.7	28.8	29.9	32.1
92.5°	56.5	76.4	111.8	170.5	228.0	205.9	153.9	109.6	85.2	74.2	66.4
95°	100.7	143.9	238.0	402.9	584.5	656.4	532.5	398.5	270.1	211.4	171.6
97.5°	116.2	163.8	256.8	448.3	753.9	1009.6	1043.9	915.5	690.8	544.6	418.4
100°	132.8	176.0	253.5	417.3	708.5	1048.3	1266.4	1305.1	1215.5	1085.9	928.8
102.5°	151.7	190.4	257.9	390.8	642.0	976.4	1277.5	1434.6	1453.5	1391.5	1306.2
105°	172.7	207.0	266.8	380.8	590.0	890.0	1207.7	1439.1	1549.8	1570.8	1542.0
107.5°	195.9	228.0	281.2	378.6	552.4	813.6	1108.1	1372.7	1546.5	1632.8	1662.7
110°	219.2	250.2	300.0	384.1	532.5	750.5	1015.1	1268.6	1472.3	1611.8	1689.3



TEST NUMBER: P831191

CATALOG NUMBER: S123DIP-S1165D1025U850-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	243.5	273.4	318.8	395.2	521.4	708.5	934.3	1165.7	1374.9	1535.4	1640.5
115°	267.9	297.8	339.8	407.4	520.3	680.8	872.3	1077.1	1269.7	1432.4	1553.1
117.5°	292.2	319.9	362.0	422.9	521.4	662.0	831.3	1008.5	1178.9	1328.4	1453.5
120°	315.5	343.2	383.0	440.6	525.8	649.8	800.3	956.4	1105.9	1238.7	1350.5
122.5°	336.5	366.4	405.2	457.2	533.6	642.0	774.9	915.5	1047.2	1167.9	1269.7
125°	357.6	387.4	426.2	474.9	541.3	635.4	753.9	880.0	1000.7	1107.0	1195.5
127.5°	377.5	407.4	445.0	489.3	550.2	632.1	733.9	847.9	957.5	1055.0	1136.9
130°	395.2	425.1	461.6	503.7	559.0	628.8	718.4	818.1	917.7	1007.4	1082.6
132.5°	411.8	440.6	476.0	517.0	565.7	627.7	704.0	790.4	880.0	962.0	1032.8
135°	426.2	456.1	490.4	528.0	572.3	626.6	691.9	766.0	844.6	916.6	979.7
137.5°	439.5	467.1	500.4	536.9	576.7	624.3	680.8	742.8	809.2	873.4	929.9
140°	450.5	478.2	510.3	543.5	581.2	623.2	670.8	722.9	779.3	832.4	880.0
142.5°	461.6	487.1	518.1	550.2	584.5	621.0	662.0	704.0	750.5	794.8	834.7
145°	470.5	495.9	524.7	554.6	585.6	618.8	654.2	689.6	726.2	761.6	793.7
147.5°	481.5	503.7	530.2	557.9	585.6	615.5	646.5	677.5	707.4	737.2	760.5
150°	490.4	510.3	535.8	559.0	585.6	611.1	638.7	664.2	689.6	712.9	733.9
152.5°	499.2	518.1	539.1	561.2	582.3	605.5	629.9	652.0	673.0	693.0	709.6
155°	509.2	524.7	543.5	561.2	580.1	598.9	621.0	639.8	657.5	674.2	687.4
157.5°	518.1	530.2	545.7	562.3	576.7	593.3	611.1	626.6	642.0	655.3	666.4
160°	524.7	535.8	549.1	562.3	574.5	586.7	601.1	615.5	627.7	638.7	646.5
162.5°	530.2	539.1	550.2	561.2	570.1	580.1	591.1	602.2	612.2	622.1	628.8
165°	534.7	542.4	551.3	559.0	565.7	573.4	582.3	591.1	597.8	605.5	611.1
167.5°	539.1	544.6	551.3	557.9	561.2	566.8	573.4	581.2	586.7	591.1	595.6
170°	542.4	544.6	550.2	554.6	556.8	560.1	565.7	571.2	574.5	579.0	581.2
172.5°	544.6	545.7	550.2	553.5	553.5	554.6	557.9	562.3	564.6	567.9	569.0
175°	545.7	546.8	549.1	551.3	550.2	550.2	552.4	554.6	555.7	557.9	557.9
177.5°	546.8	546.8	548.0	550.2	548.0	546.8	548.0	549.1	550.2	551.3	551.3
180°	546.8	546.8	546.8	546.8	546.8	546.8	546.8	546.8	546.8	546.8	546.8



TEST NUMBER: P831191

CATALOG NUMBER: S123DIP-S1165D1025U850-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	3673.3	3673.3	3673.3	3673.3
2.5°	3265.0	3259.1	3235.2	3211.3
5°	2768.2	2747.7	2740.9	2734.1
7.5°	2418.7	2417.0	2381.2	2345.4
10°	2111.1	2113.6	2081.2	2048.9
12.5°	1891.2	1869.9	1867.3	1864.8
15°	1725.8	1706.2	1702.8	1699.4
17.5°	1609.1	1597.2	1593.7	1590.3
20°	1520.4	1513.6	1507.7	1501.7
22.5°	1443.7	1435.2	1430.1	1425.0
25°	1369.6	1361.9	1360.2	1358.5
27.5°	1303.1	1293.7	1293.7	1293.7
30°	1240.1	1234.1	1231.5	1229.0
32.5°	1181.2	1176.1	1176.1	1176.1
35°	1125.8	1123.3	1119.9	1116.5
37.5°	1075.6	1075.6	1073.9	1072.2
40°	1027.0	1029.5	1029.5	1029.5
42.5°	982.7	985.2	985.2	985.2
45°	936.6	940.9	942.6	944.3
47.5°	891.5	898.3	900.0	901.7
50°	847.2	852.3	853.1	854.0
52.5°	802.0	808.0	812.2	816.5
55°	754.3	760.2	762.8	765.3
57.5°	703.1	709.1	709.9	710.8
60°	646.9	652.8	654.5	656.2
62.5°	593.2	596.6	598.3	600.0
65°	531.8	536.9	540.3	543.7
67.5°	473.0	477.3	477.3	477.3
70°	407.4	409.1	411.6	414.2
72.5°	346.9	347.7	347.7	347.7
75°	283.0	284.7	285.5	286.4
77.5°	222.4	223.3	223.3	223.3
80°	162.8	161.9	161.9	161.9
82.5°	111.6	109.1	109.1	109.1
85°	63.9	63.1	63.9	64.8
87.5°	29.0	29.0	29.0	29.0
90°	31.0	32.1	33.2	32.1
92.5°	64.2	59.8	60.9	58.7
95°	150.5	140.6	132.8	128.4
97.5°	344.3	302.2	275.6	263.5
100°	817.0	736.1	693.0	694.1
102.5°	1225.4	1165.7	1131.3	1099.2
105°	1491.1	1449.0	1413.6	1408.1
107.5°	1656.0	1636.1	1621.7	1609.5
110°	1720.2	1729.1	1726.9	1724.7



TEST NUMBER: P831191

CATALOG NUMBER: S123DIP-S1165D1025U850-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
112.5°	1703.6	1735.7	1746.8	1747.9
115°	1636.1	1684.8	1707.0	1712.5
117.5°	1539.8	1594.1	1627.3	1635.0
120°	1438.0	1500.0	1526.5	1533.2
122.5°	1345.0	1399.2	1429.1	1438.0
125°	1266.4	1315.1	1342.8	1350.5
127.5°	1201.1	1243.1	1268.6	1275.2
130°	1141.3	1181.1	1204.4	1213.3
132.5°	1087.1	1126.9	1146.8	1152.4
135°	1033.9	1067.1	1087.1	1094.8
137.5°	976.4	1010.7	1027.3	1033.9
140°	922.1	953.1	970.8	969.7
142.5°	869.0	895.5	911.0	909.9
145°	821.4	844.6	853.5	855.7
147.5°	782.6	799.2	808.1	809.2
150°	750.5	762.7	769.4	769.4
152.5°	721.8	732.8	736.1	736.1
155°	697.4	706.3	708.5	709.6
157.5°	675.3	681.9	684.1	684.1
160°	654.2	660.9	660.9	659.8
162.5°	633.2	638.7	638.7	637.6
165°	615.5	619.9	618.8	618.8
167.5°	597.8	601.1	600.0	600.0
170°	582.3	584.5	583.4	583.4
172.5°	569.0	571.2	569.0	567.9
175°	557.9	559.0	557.9	556.8
177.5°	550.2	551.3	549.1	549.1
180°	546.8	546.8	546.8	546.8

TEST NUMBER: P831191

CATALOG NUMBER: S123DIP-S1165D1025U850-4F0-1E-UDD-G4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.14	18.05	18.03	18.94	20.09	19.38	20.28	20.26	21.18	22.32
	3H	18.79	19.60	19.69	20.51	21.68	20.81	21.62	21.70	22.52	23.69
	4H	19.37	20.14	20.28	21.05	22.23	21.26	22.02	22.17	22.94	24.11
	6H	19.74	20.45	20.67	21.37	22.56	21.54	22.24	22.46	23.16	24.35
	8H	19.84	20.51	20.77	21.45	22.64	21.60	22.27	22.53	23.21	24.39
	12H	19.89	20.53	20.82	21.46	22.67	21.62	22.26	22.56	23.19	24.40
4H	2H	17.72	18.49	18.64	19.40	20.58	19.55	20.31	20.46	21.23	22.40
	3H	19.55	20.19	20.48	21.14	22.33	21.17	21.81	22.10	22.75	23.94
	4H	20.25	20.83	21.19	21.77	22.99	21.76	22.33	22.69	23.28	24.49
	6H	20.73	21.23	21.68	22.20	23.41	22.16	22.66	23.11	23.63	24.84
	8H	20.87	21.34	21.82	22.29	23.52	22.27	22.74	23.23	23.70	24.93
	12H	20.94	21.36	21.91	22.33	23.57	22.32	22.74	23.29	23.72	24.95
8H	4H	20.52	20.99	21.48	21.95	23.18	21.86	22.33	22.82	23.29	24.52
	6H	21.11	21.50	22.09	22.50	23.73	22.37	22.75	23.35	23.75	24.98
	8H	21.32	21.66	22.31	22.65	23.90	22.55	22.89	23.54	23.88	25.12
	12H	21.45	21.75	22.44	22.73	24.02	22.65	22.95	23.64	23.93	25.23
12H	4H	20.53	20.95	21.50	21.92	23.16	21.84	22.26	22.81	23.24	24.47
	6H	21.16	21.50	22.15	22.49	23.74	22.38	22.72	23.37	23.71	24.96
	8H	21.40	21.70	22.39	22.68	23.98	22.58	22.88	23.57	23.86	25.16