

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332561-930

Luminaire Tested: **S124DIP-S575D810U930-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332561-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIP-S575D810U930-4F0-1E-UDD-F4  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4393.5 lumens  
Efficiency: N/A  
Efficacy: 114.4 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 38.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332561-930

CATALOG NUMBER: S124DIP-S575D810U930-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P332561-930

CATALOG NUMBER: S124DIP-S575D810U930-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	98	98	98	98	81	81	81	66	66	66	53	53	53	46				
1	97	93	89	85	89	85	82	79	71	69	67	58	57	55	47	45	44	39				
2	88	81	75	70	81	74	69	65	62	58	55	51	48	46	41	39	37	33				
3	80	71	64	58	74	65	59	54	55	50	46	45	42	39	36	34	32	28				
4	74	63	55	49	67	58	51	46	49	44	39	40	36	33	32	30	27	24				
5	68	56	48	42	62	52	45	39	44	38	34	36	32	29	29	26	24	21				
6	62	50	42	36	57	46	39	34	39	34	30	33	28	25	26	23	21	18				
7	57	45	37	32	53	42	35	30	36	30	26	30	25	22	24	21	19	16				
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	17	14				
9	50	37	30	25	46	35	28	24	30	24	21	25	21	18	20	17	15	13				
10	46	34	27	22	43	32	25	21	27	22	19	23	19	16	19	16	14	12				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6391	6391	6391
5°	6412	6334	6380
10°	6370	6283	6314
15°	6294	6193	6209
20°	6192	6082	6088
25°	6075	5956	5940
30°	5931	5808	5754
35°	5784	5653	5577
40°	5630	5476	5376
45°	5469	5302	5200
50°	5291	5148	4987
55°	5098	4947	4787
60°	4907	4721	4579
65°	4690	4508	4327
70°	4447	4223	4057
75°	4077	3877	3780
80°	3626	3477	3394
85°	3168	3057	3001



TEST NUMBER: P332561-930

CATALOG NUMBER: S124DIP-S575D810U930-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	74.6	1.7
10°-20°	210.1	4.8
20°-30°	309.2	7.0
30°-40°	359.5	8.2
40°-50°	359.5	8.2
50°-60°	314.5	7.2
60°-70°	233.5	5.3
70°-80°	132.7	3.0
80°-90°	40.1	0.9
90°-100°	234.4	5.3
100°-110°	487.8	11.1
110°-120°	436.9	9.9
120°-130°	367.5	8.4
130°-140°	306.4	7.0
140°-150°	234.1	5.3
150°-160°	164.6	3.7
160°-170°	96.8	2.2
170°-180°	31.5	0.7
0°-30°	593.9	13.5
0°-40°	953.4	21.7
0°-60°	1627.3	37.0
0°-90°	2033.6	46.3
90°-120°	1159.1	26.4
90°-150°	2067.1	47.0
90°-180°	2360.0	53.7
0°-180°	4393.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	792	792	792	792	792	
5°	791	788	782	788	787	75
15°	753	750	741	744	743	212
25°	682	677	669	669	667	314
35°	587	582	574	569	566	367
45°	479	474	464	458	456	369
55°	362	360	352	344	340	324
65°	246	242	236	230	226	243
75°	131	128	124	122	121	139
85°	34	34	33	33	32	38
90°	1	5	12	13	13	3
95°	21	66	520	257	156	24
105°	75	108	418	900	897	80
115°	131	165	373	716	861	130
125°	183	217	371	610	687	163
135°	217	259	368	541	615	168
145°	250	287	366	456	502	157
155°	285	308	356	403	420	131
165°	310	320	341	361	367	88
175°	324	324	327	332	330	31
180°	324	324	324	324	324	



TEST NUMBER: P332561-930

CATALOG NUMBER: S124DIP-S575D810U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	791.7	791.7	791.7	791.7	791.7	791.7	791.7	791.7	791.7	791.7	791.7
2.5°	793.8	793.4	793.1	792.8	792.5	791.7	790.4	789.2	787.9	786.7	787.8
5°	791.2	790.6	790.0	789.5	788.9	787.8	786.3	784.7	783.2	781.6	783.2
7.5°	783.7	783.2	782.7	782.1	781.5	780.4	778.7	777.0	775.2	773.5	774.8
10°	777.1	776.7	776.1	775.5	774.9	773.7	771.9	770.1	768.3	766.4	767.5
12.5°	768.6	768.0	767.4	766.9	766.3	765.1	763.1	761.2	759.2	757.2	758.5
15°	753.1	752.5	752.0	751.4	750.8	749.5	747.4	745.3	743.1	741.0	741.8
17.5°	734.4	733.7	733.0	732.3	731.6	730.3	728.2	726.3	724.2	722.3	722.8
20°	720.7	720.0	719.3	718.6	717.9	716.5	714.4	712.2	710.1	708.0	708.4
22.5°	706.0	705.1	704.2	703.2	702.3	700.7	698.6	696.5	694.4	692.3	693.1
25°	682.0	681.0	680.0	679.1	678.1	676.6	674.6	672.6	670.7	668.7	668.9
27.5°	654.6	653.6	652.6	651.6	650.5	649.1	647.3	645.5	643.6	641.8	641.5
30°	636.3	635.2	634.1	632.9	631.9	630.3	628.5	626.6	624.8	623.1	622.5
32.5°	617.0	616.0	615.0	614.0	613.0	611.5	609.6	607.6	605.7	603.7	603.1
35°	586.9	585.9	584.9	583.9	582.9	581.4	579.4	577.5	575.5	573.6	572.5
37.5°	555.0	554.1	553.2	552.3	551.4	549.9	547.8	545.7	543.6	541.4	540.4
40°	534.2	533.0	531.9	530.8	529.7	528.1	525.9	523.8	521.7	519.6	518.2
42.5°	511.8	511.2	510.5	509.8	509.2	507.6	505.3	503.0	500.6	498.3	496.7
45°	479.0	478.0	477.0	476.1	475.1	473.4	471.2	468.9	466.7	464.4	462.8
47.5°	444.6	443.9	443.3	442.5	441.9	440.5	438.5	436.3	434.2	432.2	430.4
50°	421.3	420.7	420.1	419.6	419.0	417.8	415.8	413.8	411.8	409.9	407.9
52.5°	398.4	397.8	397.1	396.4	395.7	394.4	392.2	390.2	388.1	386.0	384.3
55°	362.2	361.8	361.4	361.0	360.6	359.4	357.4	355.4	353.4	351.5	349.8
57.5°	327.8	327.3	326.8	326.3	325.8	324.7	322.7	320.7	318.8	316.8	315.2
60°	303.9	303.2	302.5	301.7	301.1	299.8	298.0	296.1	294.3	292.4	291.2
62.5°	280.5	280.0	279.3	278.8	278.2	276.9	275.0	273.0	271.1	269.1	268.0
65°	245.5	244.8	244.1	243.4	242.7	241.7	240.3	238.8	237.4	236.0	234.6
67.5°	210.3	209.6	209.0	208.3	207.7	206.7	205.3	204.0	202.6	201.2	199.9
70°	188.4	187.4	186.5	185.5	184.5	183.4	182.3	181.2	180.0	178.9	177.8
72.5°	165.1	164.1	163.1	162.1	161.1	160.2	159.3	158.4	157.5	156.5	155.6
75°	130.7	130.0	129.3	128.6	127.8	127.2	126.5	125.7	125.1	124.3	123.8
77.5°	97.8	97.5	97.2	96.9	96.6	96.1	95.5	94.9	94.2	93.7	93.4
80°	78.0	77.6	77.2	76.8	76.3	76.0	75.7	75.4	75.2	74.8	74.6
82.5°	58.8	58.5	58.4	58.1	58.0	57.8	57.8	57.7	57.6	57.6	57.4
85°	34.2	34.2	34.2	34.2	34.2	34.1	33.8	33.6	33.3	33.0	33.0
87.5°	13.3	13.5	13.7	13.8	13.8	13.6	14.3	14.2	14.3	14.5	14.3
90°	0.7	1.9	3.8	4.5	5.1	5.1	8.9	8.9	10.2	11.5	10.8
92.5°	7.3	10.6	16.6	24.4	33.7	46.9	79.3	128.7	177.0	202.2	168.4
95°	21.0	22.9	29.4	37.6	52.9	79.7	135.2	239.7	392.1	519.6	534.3
97.5°	37.7	37.7	43.2	50.9	64.0	86.4	129.1	215.5	367.0	547.2	671.2
100°	48.4	48.4	52.9	60.6	72.6	93.1	130.7	202.8	332.8	512.6	675.7
102.5°	58.6	59.7	63.6	70.8	82.3	101.7	135.7	199.2	309.8	469.2	637.5
105°	74.6	76.5	79.7	87.3	98.8	117.3	147.9	200.8	290.1	418.2	568.0
107.5°	92.2	93.4	96.6	104.8	115.8	134.0	162.1	210.3	286.5	389.6	511.9
110°	104.0	105.2	108.4	116.0	127.5	144.7	172.8	217.4	287.5	379.9	483.9



TEST NUMBER: P332561-930

CATALOG NUMBER: S124DIP-S575D810U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	115.1	116.4	120.1	127.3	138.7	156.0	183.0	225.0	290.6	375.4	468.1
115°	131.3	133.2	137.7	144.1	156.2	173.4	198.9	237.2	296.4	372.9	453.2
117.5°	148.1	149.9	153.9	160.9	172.3	190.1	214.3	249.5	302.7	372.3	446.6
120°	159.4	160.6	165.1	172.1	183.0	200.8	225.0	258.2	307.3	372.3	443.0
122.5°	169.6	170.9	175.3	181.8	193.6	211.0	235.2	266.4	311.9	371.8	439.0
125°	183.0	185.5	189.3	196.3	208.5	226.3	249.2	278.6	318.8	371.0	432.2
127.5°	194.9	196.9	201.5	209.5	222.1	240.1	262.3	289.2	324.2	369.7	423.1
130°	201.5	204.0	209.1	218.7	230.8	249.2	270.9	295.8	328.3	369.1	417.6
132.5°	208.1	210.1	216.8	225.8	239.0	256.4	278.1	302.4	331.9	368.6	412.5
135°	217.4	220.0	226.3	237.2	250.5	267.1	288.1	311.1	337.2	367.9	404.8
137.5°	226.7	229.1	236.1	246.5	260.3	276.1	295.8	317.2	340.4	367.7	398.2
140°	233.3	235.2	242.2	253.1	266.4	281.8	300.9	321.3	343.0	367.2	394.6
142.5°	240.4	242.4	248.9	259.2	272.1	286.9	305.5	324.3	345.0	367.2	391.6
145°	250.5	252.4	258.9	267.7	279.9	293.9	310.5	327.7	346.2	365.9	386.3
147.5°	261.9	262.5	268.2	277.3	287.4	300.0	315.6	330.6	346.8	363.6	381.6
150°	269.0	269.7	274.8	282.4	292.0	304.1	318.1	332.2	346.8	362.1	378.1
152.5°	275.7	275.8	280.9	288.0	296.6	307.7	320.2	333.1	345.8	359.5	374.0
155°	284.9	285.6	289.4	295.8	302.8	312.3	323.2	334.0	344.2	355.7	367.9
157.5°	294.0	294.0	297.6	302.6	308.7	316.2	325.4	334.0	342.6	351.8	361.6
160°	299.6	299.6	302.1	306.6	311.8	318.8	326.4	334.0	341.0	348.7	357.0
162.5°	304.8	304.2	306.2	310.2	314.8	320.2	327.4	334.0	339.6	345.7	352.9
165°	310.5	310.5	311.8	315.0	318.1	322.0	327.7	332.8	336.6	341.0	346.2
167.5°	316.2	315.6	316.2	318.6	320.4	323.3	327.6	331.3	333.5	336.5	340.1
170°	318.8	318.1	318.8	320.7	322.0	323.8	327.0	330.2	331.5	333.4	336.0
172.5°	321.3	320.7	320.8	322.2	322.9	324.3	326.5	329.2	329.5	330.4	332.4
175°	323.8	323.2	323.2	323.8	324.5	324.5	325.8	327.7	327.0	327.0	328.3
177.5°	325.0	324.5	324.0	324.5	324.5	324.5	325.0	326.0	325.0	325.0	325.5
180°	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5



TEST NUMBER: P332561-930

CATALOG NUMBER: S124DIP-S575D810U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	791.7	791.7	791.7	791.7	791.7	791.7	791.7	791.7
2.5°	789.0	790.1	791.2	791.7	791.6	791.5	791.4	791.2
5°	784.7	786.3	787.8	788.5	788.1	787.9	787.6	787.3
7.5°	776.0	777.2	778.4	779.0	778.9	778.7	778.5	778.3
10°	768.7	769.8	770.9	771.4	771.0	770.8	770.5	770.2
12.5°	759.8	761.0	762.2	762.6	762.2	761.8	761.5	761.1
15°	742.7	743.6	744.4	744.6	744.2	743.8	743.3	742.9
17.5°	723.3	723.8	724.4	724.5	724.2	723.9	723.7	723.4
20°	708.9	709.3	709.7	709.8	709.5	709.2	709.0	708.7
22.5°	693.8	694.6	695.4	695.5	695.0	694.5	694.0	693.4
25°	669.0	669.1	669.3	669.0	668.5	667.9	667.3	666.8
27.5°	641.2	640.7	640.4	639.9	639.2	638.5	637.8	637.1
30°	621.9	621.3	620.8	620.1	619.4	618.7	618.0	617.3
32.5°	602.3	601.7	601.0	600.3	599.7	598.9	598.2	597.5
35°	571.5	570.5	569.6	568.8	568.0	567.3	566.6	565.9
37.5°	539.3	538.2	537.1	536.1	535.2	534.3	533.4	532.4
40°	516.8	515.4	514.0	512.9	512.2	511.5	510.8	510.1
42.5°	495.0	493.3	491.7	490.6	490.2	489.8	489.3	488.8
45°	461.3	459.7	458.2	457.2	456.8	456.4	455.9	455.5
47.5°	428.7	426.9	425.2	423.8	422.7	421.6	420.5	419.5
50°	405.9	403.9	401.9	400.6	399.7	398.8	398.0	397.1
52.5°	382.5	380.7	379.0	377.6	376.5	375.4	374.4	373.3
55°	348.1	346.4	344.7	343.4	342.6	341.8	340.9	340.1
57.5°	313.6	312.0	310.4	309.2	308.3	307.5	306.7	305.9
60°	289.9	288.7	287.4	286.4	285.7	285.0	284.3	283.6
62.5°	266.8	265.6	264.5	263.6	262.9	262.2	261.5	260.7
65°	233.2	231.8	230.4	229.3	228.6	227.9	227.2	226.5
67.5°	198.5	197.2	195.8	195.0	194.9	194.7	194.4	194.3
70°	176.7	175.5	174.4	173.7	173.2	172.8	172.4	171.9
72.5°	154.7	153.8	153.0	152.3	151.9	151.5	151.1	150.6
75°	123.2	122.6	122.1	121.7	121.6	121.5	121.3	121.2
77.5°	93.3	93.1	92.9	92.7	92.3	92.0	91.6	91.2
80°	74.3	74.0	73.7	73.5	73.4	73.2	73.1	73.0
82.5°	57.2	57.1	56.9	56.7	56.7	56.5	56.3	56.2
85°	33.0	33.0	33.0	32.9	32.8	32.6	32.5	32.4
87.5°	14.5	14.6	14.8	14.8	14.8	15.0	14.8	14.8
90°	11.5	12.1	12.7	12.7	13.4	14.0	13.4	13.4
92.5°	125.2	94.2	75.0	62.2	54.7	51.3	49.1	49.1
95°	472.4	373.6	288.1	226.3	195.1	175.3	163.9	155.6
97.5°	697.9	661.2	598.8	532.3	486.6	448.2	429.0	415.8
100°	768.8	781.5	750.3	703.2	647.7	608.8	589.7	584.6
102.5°	765.2	828.5	837.6	817.9	783.9	755.7	735.6	731.5
105°	714.0	824.3	887.4	913.5	914.8	909.7	900.8	897.0
107.5°	641.2	758.6	847.5	904.3	935.9	950.4	956.8	958.4
110°	597.4	707.6	800.1	870.2	915.4	942.2	953.7	959.4





TEST NUMBER: P332561-930

CATALOG NUMBER: S124DIP-S575D810U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	565.2	662.8	750.1	820.2	871.6	904.0	920.1	929.4
115°	533.0	611.4	685.9	747.1	797.5	835.8	856.1	861.3
117.5°	517.1	582.0	640.7	692.6	735.6	767.7	788.3	792.3
120°	510.0	569.3	620.3	665.5	701.9	729.9	746.5	753.5
122.5°	503.9	561.1	607.6	647.2	677.9	701.9	715.9	722.9
125°	493.4	548.3	592.2	627.3	652.8	671.3	683.4	687.2
127.5°	480.7	533.0	576.9	610.3	635.9	652.3	662.5	666.3
130°	470.5	520.8	564.2	597.9	624.1	640.1	650.3	654.1
132.5°	459.7	507.0	549.4	583.2	608.8	626.8	636.5	640.3
135°	445.0	486.4	525.3	557.2	582.7	600.5	610.7	614.6
137.5°	431.6	466.7	499.5	528.2	552.0	569.6	578.0	582.7
140°	424.0	453.9	482.6	509.4	531.7	545.7	554.6	559.7
142.5°	416.8	443.2	467.8	491.0	510.8	523.7	531.7	535.2
145°	406.8	428.4	447.5	465.4	481.4	492.1	498.6	501.7
147.5°	398.4	415.6	431.0	445.0	456.7	466.0	470.8	472.0
150°	393.3	408.0	420.8	432.2	442.5	450.7	454.5	455.2
152.5°	387.8	400.3	412.1	421.5	430.2	436.9	439.2	439.9
155°	379.3	389.6	399.1	406.8	413.1	418.2	420.1	420.1
157.5°	370.2	378.8	386.9	393.0	397.8	401.6	402.8	402.8
160°	364.7	371.7	378.7	383.8	387.6	391.4	392.1	392.1
162.5°	359.1	365.0	370.6	375.1	377.9	381.7	382.4	381.9
165°	351.2	355.1	359.5	362.7	365.3	367.9	367.2	366.6
167.5°	343.7	346.7	350.3	352.1	353.4	355.1	355.0	354.4
170°	339.2	341.0	343.6	345.5	346.8	347.4	346.8	346.8
172.5°	335.1	336.5	338.0	339.4	340.1	340.8	340.1	339.2
175°	329.6	330.2	331.5	331.5	331.5	332.8	331.5	330.2
177.5°	326.0	326.5	326.5	327.0	326.5	327.0	326.0	325.0
180°	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5

(END OF REPORT)