

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831351

Luminaire Tested: S123DIP-S340D1195U850-4F0-1E-UDD-G

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P831351
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-1, G3-1807-864-5)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-S340D1195U850-4F0-1E-UDD-G
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, GRAZE OPTIC
UPLIGHT 1195 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7040.6 lumens
Efficiency: N/A
Efficacy: 162.2 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 1.19 / 0.89
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 43.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P831351

CATALOG NUMBER: S123DIP-S340D1195U850-4F0-1E-UDD-G

Luminous Intensity Polar Plot





TEST NUMBER: P831351

CATALOG NUMBER: S123DIP-S340D1195U850-4F0-1E-UDD-G

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	33	33	33	25
1	92	88	85	81	82	79	76	73	61	59	57	45	43	42	30	29	28	21
2	84	77	72	67	75	69	64	60	54	51	48	40	37	36	26	25	24	18
3	77	68	61	56	68	61	55	51	48	44	40	35	33	31	24	22	21	16
4	71	60	53	47	63	54	48	43	42	38	35	31	29	26	21	20	18	14
5	65	54	46	41	58	48	42	37	38	33	30	28	25	23	19	18	16	12
6	60	48	41	35	53	44	37	32	34	30	26	26	23	20	18	16	14	11
7	55	44	36	31	49	39	33	28	31	26	23	23	20	18	16	14	13	10
8	51	40	32	27	46	36	29	25	28	24	21	21	18	16	15	13	12	9
9	48	36	29	24	42	33	27	22	26	22	18	20	17	15	14	12	11	8
10	44	33	26	22	40	30	24	20	24	20	17	18	15	13	13	11	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	11720	11720	11720	11720	11720
5°	14822	13989	11825	9529	8756
10°	14966	15419	11746	7596	6638
15°	11272	14315	11666	6433	5613
20°	7853	11584	11518	5625	5098
25°	5989	8909	11264	5176	4783
30°	5180	7077	10858	4857	4528
35°	4807	5975	10390	4628	4348
40°	4551	5361	9733	4409	4288
45°	4399	4961	8899	4238	4261
50°	4324	4645	7911	4083	4238
55°	4162	4414	6942	3935	4258
60°	4013	4166	5983	3795	4187
65°	3769	3933	5160	3647	4106
70°	3484	3635	4390	3402	3865
75°	3152	3256	3760	3161	3531
80°	2597	2851	2975	2758	2975
85°	2062	2309	2186	2334	2371

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 10161 cd/sqm



TEST NUMBER: P831351

CATALOG NUMBER: S123DIP-S340D1195U850-4F0-1E-UDD-G

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.9	1.5
10°-20°	256.1	3.6
20°-30°	303.2	4.3
30°-40°	304.9	4.3
40°-50°	279.7	4.0
50°-60°	230.9	3.3
60°-70°	163.3	2.3
70°-80°	87.2	1.2
80°-90°	25.6	0.4
90°-100°	61.1	0.9
100°-110°	295.6	4.2
110°-120°	724.5	10.3
120°-130°	919.8	13.1
130°-140°	982.6	14.0
140°-150°	918.9	13.1
150°-160°	741.1	10.5
160°-170°	478.3	6.8
170°-180°	164.8	2.3
0°-30°	662.3	9.4
0°-40°	967.1	13.7
0°-60°	1477.7	21.0
0°-90°	1753.8	24.9
90°-120°	1081.2	15.4
90°-150°	3902.5	55.4
90°-180°	5287.0	75.1
0°-180°	7040.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1089	1089	1089	1089	1089	
5°	1372	1295	1094	882	810	131
15°	1012	1285	1047	577	504	279
25°	504	750	948	436	403	238
35°	366	455	791	352	331	230
45°	289	326	585	278	280	224
55°	222	235	370	210	227	198
65°	148	154	203	143	161	147
75°	76	78	90	76	85	80
85°	17	19	18	19	19	19
90°	39	31	1	31	39	18
95°	49	40	79	40	49	41
105°	57	282	384	282	57	118
115°	758	740	720	740	758	713
125°	1036	1031	1015	1031	1036	926
135°	1277	1277	1264	1277	1277	985
145°	1473	1470	1458	1470	1473	920
155°	1604	1605	1607	1605	1604	740
165°	1690	1689	1694	1689	1690	478
175°	1728	1729	1734	1729	1728	164
180°	1734	1734	1734	1734	1734	



TEST NUMBER: P831351

CATALOG NUMBER: S123DIP-S340D1195U850-4F0-1E-UDD-G

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1088.8	1088.8	1088.8	1088.8	1088.8	1088.8	1088.8	1088.8	1088.8	1088.8	1088.8
2.5°	1227.3	1226.0	1224.8	1218.4	1212.1	1209.1	1206.1	1197.0	1187.9	1177.8	1167.7
5°	1371.8	1375.3	1378.9	1374.8	1370.8	1358.4	1346.0	1329.6	1313.2	1294.7	1276.3
7.5°	1438.5	1440.5	1442.5	1440.0	1437.5	1434.2	1430.9	1416.3	1401.6	1382.7	1363.7
10°	1369.3	1373.8	1378.4	1388.2	1398.1	1409.2	1420.3	1418.3	1416.3	1410.7	1405.1
12.5°	1217.2	1222.7	1228.3	1248.0	1267.7	1293.0	1318.2	1340.0	1361.7	1376.8	1392.0
15°	1011.5	1026.9	1042.4	1060.3	1078.2	1115.4	1152.5	1198.2	1244.0	1284.6	1325.3
17.5°	833.2	839.0	844.8	864.0	883.2	929.9	976.7	1029.5	1082.3	1149.7	1217.2
20°	685.6	690.9	696.3	721.5	746.8	783.4	820.0	879.4	938.8	1011.3	1083.8
22.5°	576.0	584.3	592.7	606.8	621.0	656.1	691.2	744.0	796.8	876.9	957.0
25°	504.3	510.3	516.4	525.0	533.6	561.6	589.6	633.1	676.5	750.1	823.6
27.5°	455.2	457.8	460.3	468.9	477.5	495.7	513.9	551.2	588.6	651.0	713.4
30°	416.8	418.6	420.4	428.0	435.5	447.9	460.3	487.3	514.4	569.4	624.5
32.5°	390.1	391.3	392.6	398.4	404.2	413.1	421.9	441.6	461.3	506.8	552.3
35°	365.8	366.6	367.3	371.6	375.9	382.5	389.1	404.0	418.9	454.7	490.6
37.5°	344.6	345.6	346.6	349.1	351.7	357.5	363.3	375.2	387.0	414.6	442.1
40°	323.9	325.6	327.4	329.2	330.9	335.7	340.5	349.6	358.7	381.5	404.2
42.5°	306.2	308.0	309.7	310.5	311.2	314.0	316.8	325.1	333.5	350.4	367.3
45°	289.0	289.8	290.5	291.3	292.0	294.3	296.6	303.9	311.2	325.9	340.5
47.5°	273.3	273.3	273.3	273.9	274.4	276.4	278.4	283.7	289.0	300.4	311.7
50°	258.2	258.2	258.2	257.4	256.7	257.9	259.2	263.2	267.3	277.4	287.5
52.5°	240.0	240.0	240.0	240.3	240.5	240.5	240.5	244.0	247.6	256.7	265.8
55°	221.8	222.8	223.8	223.1	222.3	222.8	223.3	225.6	227.9	235.2	242.5
57.5°	203.6	204.1	204.6	204.4	204.1	204.4	204.6	206.7	208.7	214.2	219.8
60°	186.4	186.4	186.4	185.9	185.4	185.9	186.4	187.5	188.5	193.5	198.6
62.5°	167.2	167.5	167.7	168.0	168.3	167.7	167.2	168.5	169.8	173.6	177.3
65°	148.0	148.3	148.5	149.3	150.1	149.6	149.1	150.3	151.6	154.4	157.1
67.5°	130.9	130.4	129.9	130.1	130.4	131.1	131.9	132.1	132.4	135.4	138.4
70°	110.7	111.2	111.7	111.4	111.2	111.4	111.7	112.4	113.2	115.5	117.7
72.5°	92.5	92.7	93.0	93.0	93.0	93.5	94.0	94.7	95.5	96.8	98.0
75°	75.8	75.8	75.8	76.3	76.8	77.1	77.3	77.3	77.3	78.3	79.3
77.5°	57.6	58.9	60.1	59.9	59.6	60.1	60.6	61.4	62.1	62.7	63.2
80°	41.9	41.9	41.9	42.2	42.4	43.2	44.0	44.5	45.0	46.0	47.0
82.5°	26.8	27.0	27.3	28.0	28.8	29.3	29.8	30.6	31.3	31.3	31.3
85°	16.7	16.2	15.7	16.2	16.7	17.2	17.7	17.9	18.2	18.7	19.2
87.5°	8.1	8.1	8.1	8.1	8.1	8.3	8.6	8.6	8.6	8.6	8.6
90°	38.7	38.1	37.5	36.9	36.4	35.5	34.4	33.2	32.1	30.9	27.2
92.5°	43.8	43.5	43.2	42.9	42.7	41.5	39.5	37.5	35.5	33.5	30.9
95°	49.0	49.0	49.0	49.0	49.0	48.0	46.0	44.0	41.9	39.9	36.8
97.5°	52.8	52.5	52.3	52.0	51.7	50.4	48.1	45.8	43.5	41.2	55.8
100°	54.1	53.8	53.5	53.3	53.0	51.7	49.4	47.1	44.8	42.5	87.2
102.5°	55.4	54.8	54.3	53.7	53.1	57.6	67.0	76.4	85.9	95.3	145.2
105°	56.7	56.1	55.5	55.0	54.4	79.5	130.1	180.8	231.5	282.2	307.9
107.5°	134.0	171.5	209.0	246.5	284.0	324.8	368.9	413.0	457.1	501.2	496.9
110°	354.3	395.3	436.2	477.2	518.1	543.3	552.7	562.2	571.6	581.1	577.9



TEST NUMBER: P831351

CATALOG NUMBER: S123DIP-S340D1195U850-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	671.3	671.9	672.4	673.0	673.6	672.6	670.0	667.4	664.8	662.3	659.1
115°	757.6	756.5	755.3	754.2	753.0	751.0	748.2	745.3	742.4	739.6	737.0
117.5°	827.2	826.9	826.6	826.3	826.0	824.7	822.5	820.2	817.9	815.6	814.2
120°	899.3	899.3	899.3	899.3	899.3	898.2	895.9	893.6	891.3	889.0	888.2
122.5°	970.2	969.9	969.6	969.3	969.1	968.2	966.8	965.3	963.9	962.5	961.3
125°	1035.9	1035.3	1034.8	1034.2	1033.6	1033.0	1032.5	1031.9	1031.3	1030.8	1029.6
127.5°	1100.3	1100.9	1101.5	1102.1	1102.6	1102.5	1101.6	1100.8	1099.9	1099.0	1097.6
130°	1162.2	1162.8	1163.3	1163.9	1164.5	1164.2	1163.0	1161.9	1160.7	1159.6	1158.5
132.5°	1218.9	1219.7	1220.6	1221.4	1222.3	1222.2	1221.0	1219.9	1218.7	1217.6	1216.7
135°	1276.9	1277.7	1278.6	1279.4	1280.3	1280.3	1279.4	1278.6	1277.7	1276.9	1275.7
137.5°	1332.3	1332.8	1333.4	1334.0	1334.5	1334.1	1332.7	1331.3	1329.8	1328.4	1327.8
140°	1381.2	1381.8	1382.4	1382.9	1383.5	1383.2	1382.1	1380.9	1379.8	1378.6	1377.8
142.5°	1426.3	1427.2	1428.0	1428.9	1429.7	1429.7	1428.9	1428.0	1427.2	1426.3	1425.5
145°	1472.7	1472.7	1472.7	1472.7	1472.7	1472.4	1471.8	1471.3	1470.7	1470.1	1469.5
147.5°	1506.2	1507.6	1509.1	1510.5	1511.9	1512.4	1511.8	1511.2	1510.6	1510.1	1509.5
150°	1544.8	1545.7	1546.6	1547.4	1548.3	1548.4	1547.9	1547.3	1546.7	1546.1	1545.6
152.5°	1575.8	1577.2	1578.6	1580.1	1581.5	1581.6	1580.5	1579.3	1578.2	1577.1	1576.8
155°	1604.1	1605.8	1607.6	1609.3	1611.0	1611.1	1609.7	1608.3	1606.8	1605.4	1605.1
157.5°	1628.6	1630.9	1633.2	1635.5	1637.8	1638.0	1636.3	1634.6	1632.9	1631.2	1631.5
160°	1651.8	1653.8	1655.8	1657.8	1659.8	1659.9	1658.2	1656.5	1654.8	1653.1	1653.4
162.5°	1673.7	1675.4	1677.1	1678.8	1680.6	1680.4	1678.4	1676.4	1674.4	1672.4	1672.7
165°	1690.4	1692.4	1694.5	1696.5	1698.5	1698.3	1696.0	1693.7	1691.4	1689.2	1689.4
167.5°	1703.3	1705.6	1707.9	1710.2	1712.5	1712.5	1710.2	1707.9	1705.6	1703.3	1703.3
170°	1714.9	1717.2	1719.5	1721.8	1724.1	1724.1	1721.8	1719.5	1717.2	1714.9	1714.9
172.5°	1721.4	1723.9	1726.5	1729.1	1731.7	1731.8	1729.5	1727.2	1724.9	1722.7	1722.4
175°	1727.8	1730.1	1732.4	1734.7	1737.0	1737.1	1735.1	1733.1	1731.1	1729.1	1728.8
177.5°	1729.1	1732.0	1734.8	1737.7	1740.5	1740.8	1738.5	1736.3	1734.0	1731.7	1731.4
180°	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2



TEST NUMBER: P831351

CATALOG NUMBER: S123DIP-S340D1195U850-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1088.8	1088.8	1088.8	1088.8	1088.8	1088.8	1088.8	1088.8	1088.8	1088.8	1088.8
2.5°	1164.6	1161.6	1150.5	1139.4	1126.7	1114.1	1104.8	1095.4	1081.5	1067.6	1056.3
5°	1262.1	1248.0	1224.5	1201.0	1169.2	1137.3	1115.9	1094.4	1065.6	1036.8	1013.8
7.5°	1339.5	1315.2	1282.4	1249.5	1207.8	1166.1	1126.7	1087.3	1043.4	999.4	963.5
10°	1388.7	1372.3	1334.4	1296.5	1240.7	1184.8	1129.8	1074.7	1018.1	961.5	914.0
12.5°	1393.5	1395.0	1360.2	1325.3	1262.1	1199.0	1132.0	1065.1	993.9	922.6	867.3
15°	1351.3	1377.3	1358.1	1338.9	1275.3	1211.6	1129.3	1046.9	964.8	882.7	818.8
17.5°	1273.0	1328.8	1331.6	1334.4	1270.7	1207.1	1115.9	1024.7	931.7	838.7	771.5
20°	1166.1	1248.5	1276.8	1305.1	1253.3	1201.5	1103.5	1005.5	901.4	797.3	726.8
22.5°	1057.0	1157.1	1208.8	1260.6	1222.2	1183.8	1079.5	975.2	865.3	755.4	683.9
25°	932.7	1041.9	1121.4	1201.0	1177.5	1154.0	1051.2	948.4	831.4	714.4	641.4
27.5°	824.3	935.2	1031.2	1127.2	1122.2	1117.1	1015.1	913.0	793.3	673.5	603.0
30°	727.8	831.2	938.5	1045.9	1058.3	1070.7	972.1	873.6	753.6	633.6	565.6
32.5°	642.4	732.6	847.8	963.0	987.3	1011.5	922.6	833.7	714.9	596.2	530.8
35°	572.5	654.3	769.5	884.7	915.0	945.3	868.0	790.7	675.0	559.3	496.9
37.5°	510.6	579.0	691.5	803.9	841.0	878.1	808.9	739.7	631.3	522.9	465.6
40°	459.3	514.4	617.7	721.0	764.0	806.9	749.8	692.7	589.9	487.1	434.3
42.5°	416.3	465.3	559.1	652.8	694.0	735.2	686.9	638.7	547.2	455.7	407.5
45°	379.7	418.9	504.0	589.1	628.3	667.5	626.0	584.6	504.0	423.4	378.4
47.5°	345.3	378.9	451.7	524.5	559.3	594.2	561.9	529.5	461.3	393.1	352.4
50°	314.5	341.6	405.2	468.9	499.2	529.5	501.0	472.4	416.3	360.3	324.9
52.5°	287.7	309.7	363.0	416.3	442.4	468.4	443.9	419.4	374.9	330.4	299.6
55°	261.2	279.9	326.1	372.4	390.1	407.7	388.8	369.9	334.0	298.1	272.1
57.5°	236.5	253.1	291.0	328.9	342.6	356.2	339.0	321.9	294.8	267.8	246.1
60°	212.2	225.9	257.4	289.0	297.3	305.7	291.8	277.9	258.9	240.0	220.5
62.5°	189.7	202.1	225.6	249.1	254.7	260.2	249.6	239.0	224.6	210.2	195.0
65°	166.5	175.8	195.0	214.2	217.8	221.3	212.0	202.6	191.7	180.9	169.8
67.5°	145.0	151.6	167.2	182.9	183.2	183.4	175.8	168.3	162.2	156.1	147.3
70°	124.0	130.4	140.7	151.1	151.3	151.6	145.5	139.5	134.9	130.4	123.8
72.5°	102.6	107.1	114.9	122.8	122.3	121.8	118.0	114.2	110.7	107.1	102.3
75°	83.1	86.9	92.2	97.5	96.0	94.5	92.5	90.4	87.4	84.4	81.3
77.5°	65.4	67.7	70.7	73.8	72.8	71.7	70.0	68.2	65.9	63.7	62.4
80°	48.0	49.0	51.0	53.1	52.5	52.0	50.0	48.0	47.5	47.0	45.2
82.5°	32.6	33.9	34.4	34.9	34.6	34.4	32.8	31.3	30.8	30.3	30.1
85°	19.5	19.7	20.0	20.2	19.5	18.7	18.2	17.7	17.7	17.7	17.4
87.5°	8.8	9.1	9.1	9.1	8.8	8.6	8.1	7.6	7.8	8.1	8.1
90°	23.5	19.8	16.0	12.7	9.9	7.0	4.2	1.3	4.2	7.0	9.9
92.5°	28.3	25.8	23.2	22.8	24.5	26.2	27.9	29.6	27.9	26.2	24.5
95°	33.6	30.5	27.3	31.6	43.4	55.1	66.9	78.6	66.9	55.1	43.4
97.5°	70.4	85.0	99.6	110.9	119.0	127.0	135.0	143.0	135.0	127.0	119.0
100°	131.9	176.5	221.2	240.7	234.9	229.2	223.5	217.7	223.5	229.2	234.9
102.5°	195.0	244.8	294.6	317.7	314.0	310.2	306.5	302.8	306.5	310.2	314.0
105°	333.7	359.5	385.2	396.6	393.4	390.3	387.1	384.0	387.1	390.3	393.4
107.5°	492.6	488.3	484.0	480.6	478.0	475.4	472.9	470.3	472.9	475.4	478.0
110°	574.8	571.6	568.5	565.8	563.5	561.2	558.9	556.6	558.9	561.2	563.5



TEST NUMBER: P831351

CATALOG NUMBER: S123DIP-S340D1195U850-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	656.0	652.8	649.7	647.1	645.1	643.1	641.1	639.1	641.1	643.1	645.1
115°	734.4	731.8	729.3	727.1	725.4	723.7	722.0	720.2	722.0	723.7	725.4
117.5°	812.7	811.3	809.9	808.1	806.1	804.1	802.1	800.1	802.1	804.1	806.1
120°	887.3	886.5	885.6	883.9	881.3	878.7	876.1	873.6	876.1	878.7	881.3
122.5°	960.2	959.0	957.9	956.3	954.3	952.3	950.3	948.3	950.3	952.3	954.3
125°	1028.5	1027.3	1026.2	1024.5	1022.2	1019.9	1017.6	1015.3	1017.6	1019.9	1022.2
127.5°	1096.2	1094.8	1093.3	1091.5	1089.2	1086.9	1084.6	1082.3	1084.6	1086.9	1089.2
130°	1157.3	1156.2	1155.0	1153.3	1151.0	1148.7	1146.4	1144.1	1146.4	1148.7	1151.0
132.5°	1215.9	1215.0	1214.1	1212.6	1210.3	1208.0	1205.7	1203.4	1205.7	1208.0	1210.3
135°	1274.6	1273.4	1272.3	1270.8	1269.1	1267.4	1265.7	1264.0	1265.7	1267.4	1269.1
137.5°	1327.2	1326.7	1326.1	1324.7	1322.4	1320.1	1317.8	1315.5	1317.8	1320.1	1322.4
140°	1376.9	1376.1	1375.2	1373.9	1372.2	1370.5	1368.8	1367.0	1368.8	1370.5	1372.2
142.5°	1424.6	1423.7	1422.9	1421.6	1419.9	1418.2	1416.4	1414.7	1416.4	1418.2	1419.9
145°	1469.0	1468.4	1467.8	1466.5	1464.5	1462.5	1460.5	1458.5	1460.5	1462.5	1464.5
147.5°	1508.9	1508.3	1507.8	1506.8	1505.3	1503.9	1502.5	1501.0	1502.5	1503.9	1505.3
150°	1545.0	1544.4	1543.8	1543.1	1542.3	1541.4	1540.6	1539.7	1540.6	1541.4	1542.3
152.5°	1576.5	1576.2	1575.9	1575.6	1575.3	1575.1	1574.8	1574.5	1574.8	1575.1	1575.3
155°	1604.8	1604.5	1604.3	1604.4	1605.0	1605.5	1606.1	1606.7	1606.1	1605.5	1605.0
157.5°	1631.7	1632.0	1632.3	1632.5	1632.5	1632.5	1632.5	1632.5	1632.5	1632.5	1632.5
160°	1653.7	1653.9	1654.2	1654.5	1654.8	1655.1	1655.4	1655.7	1655.4	1655.1	1654.8
162.5°	1673.0	1673.3	1673.5	1674.1	1675.0	1675.8	1676.7	1677.6	1676.7	1675.8	1675.0
165°	1689.7	1690.0	1690.3	1690.9	1691.7	1692.6	1693.4	1694.3	1693.4	1692.6	1691.7
167.5°	1703.3	1703.3	1703.3	1703.9	1705.0	1706.2	1707.3	1708.5	1707.3	1706.2	1705.0
170°	1714.9	1714.9	1714.9	1715.5	1716.6	1717.8	1718.9	1720.1	1718.9	1717.8	1716.6
172.5°	1722.1	1721.8	1721.5	1722.1	1723.5	1724.9	1726.4	1727.8	1726.4	1724.9	1723.5
175°	1728.5	1728.2	1728.0	1728.5	1730.0	1731.4	1732.8	1734.2	1732.8	1731.4	1730.0
177.5°	1731.1	1730.8	1730.5	1731.1	1732.5	1734.0	1735.4	1736.8	1735.4	1734.0	1732.5
180°	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2



TEST NUMBER: P831351

CATALOG NUMBER: S123DIP-S340D1195U850-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1088.8	1088.8	1088.8	1088.8	1088.8	1088.8	1088.8	1088.8	1088.8	1088.8	1088.8
2.5°	1044.9	1035.0	1025.2	1017.6	1010.0	997.1	984.3	981.2	978.2	973.9	969.6
5°	990.8	966.6	942.3	920.6	898.9	881.9	865.0	853.9	842.8	834.7	826.6
7.5°	927.7	891.3	854.9	829.1	803.4	778.9	754.4	746.5	738.7	728.1	717.5
10°	866.5	826.4	786.2	752.6	719.0	695.0	671.0	661.4	651.8	638.4	625.0
12.5°	812.0	768.0	724.0	690.2	656.3	633.1	609.9	596.0	582.1	574.5	566.9
15°	754.9	707.9	660.9	629.6	598.2	577.3	556.3	544.2	532.0	524.7	517.4
17.5°	704.3	657.9	611.4	581.3	551.2	532.0	512.8	502.2	491.6	486.1	480.5
20°	656.3	610.9	565.4	536.1	506.8	491.1	475.5	468.6	461.8	457.3	452.7
22.5°	612.4	567.7	522.9	497.9	472.9	460.3	447.7	442.9	438.1	434.3	430.5
25°	568.4	528.5	488.6	467.4	446.1	435.8	425.4	420.6	415.8	412.0	408.3
27.5°	532.5	494.4	456.3	438.1	419.9	411.8	403.7	399.9	396.1	392.6	389.1
30°	497.7	463.6	429.5	413.8	398.1	390.8	383.5	379.7	375.9	372.6	369.3
32.5°	465.3	436.0	406.7	392.3	377.9	371.9	365.8	361.3	356.7	354.2	351.7
35°	434.5	408.3	382.0	370.1	358.2	352.2	346.1	342.3	338.5	336.5	334.5
37.5°	408.3	384.8	361.3	349.9	338.5	332.7	326.9	323.6	320.3	319.6	318.8
40°	381.5	361.3	341.1	329.9	318.8	313.8	308.7	306.7	304.7	304.2	303.7
42.5°	359.2	339.5	319.8	309.7	299.6	295.3	291.0	290.0	289.0	289.8	290.5
45°	333.5	317.1	300.6	291.3	281.9	278.4	274.9	274.1	273.3	274.9	276.4
47.5°	311.7	296.6	281.4	272.6	263.7	261.2	258.7	258.4	258.2	260.2	262.2
50°	289.5	274.9	260.2	253.1	246.1	243.8	241.5	242.3	243.0	246.3	249.6
52.5°	268.8	255.2	241.5	234.9	228.4	226.9	225.3	227.1	228.9	232.4	236.0
55°	246.1	233.7	221.3	216.3	211.2	209.7	208.2	211.7	215.2	218.5	221.8
57.5°	224.3	213.5	202.6	198.1	193.5	193.3	193.0	196.3	199.6	203.1	206.7
60°	201.1	192.0	182.9	179.4	175.8	176.3	176.8	180.6	184.4	187.2	190.0
62.5°	179.9	172.3	164.7	161.4	158.1	159.4	160.7	164.5	168.3	171.5	174.8
65°	158.7	152.3	146.0	143.7	141.5	143.2	145.0	148.3	151.6	153.9	156.1
67.5°	138.4	133.1	127.8	126.1	124.3	126.1	127.8	131.1	134.4	136.7	138.9
70°	117.2	112.9	108.6	107.4	106.1	108.1	110.1	112.9	115.7	118.0	120.3
72.5°	97.5	94.2	90.9	90.7	90.4	92.2	94.0	96.8	99.5	101.1	102.6
75°	78.3	76.5	74.8	74.5	74.3	76.0	77.8	79.3	80.8	82.1	83.4
77.5°	61.1	59.6	58.1	58.4	58.6	59.9	61.1	62.7	64.2	64.9	65.7
80°	43.5	42.9	42.4	42.9	43.5	44.5	45.5	46.5	47.5	48.0	48.5
82.5°	29.8	29.3	28.8	29.6	30.3	31.1	31.8	32.6	33.3	33.6	33.9
85°	17.2	17.9	18.7	18.7	18.7	18.9	19.2	19.5	19.7	19.5	19.2
87.5°	8.1	8.3	8.6	8.6	8.6	8.8	9.1	9.1	9.1	8.8	8.6
90°	12.7	16.0	19.8	23.5	27.2	30.9	32.1	33.2	34.4	35.5	36.4
92.5°	22.8	23.2	25.8	28.3	30.9	33.5	35.5	37.5	39.5	41.5	42.7
95°	31.6	27.3	30.5	33.6	36.8	39.9	41.9	44.0	46.0	48.0	49.0
97.5°	110.9	99.6	85.0	70.4	55.8	41.2	43.5	45.8	48.1	50.4	51.7
100°	240.7	221.2	176.5	131.9	87.2	42.5	44.8	47.1	49.4	51.7	53.0
102.5°	317.7	294.6	244.8	195.0	145.2	95.3	85.9	76.4	67.0	57.6	53.1
105°	396.6	385.2	359.5	333.7	307.9	282.2	231.5	180.8	130.1	79.5	54.4
107.5°	480.6	484.0	488.3	492.6	496.9	501.2	457.1	413.0	368.9	324.8	284.0
110°	565.8	568.5	571.6	574.8	577.9	581.1	571.6	562.2	552.7	543.3	518.1



TEST NUMBER: P831351

CATALOG NUMBER: S123DIP-S340D1195U850-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	647.1	649.7	652.8	656.0	659.1	662.3	664.8	667.4	670.0	672.6	673.6
115°	727.1	729.3	731.8	734.4	737.0	739.6	742.4	745.3	748.2	751.0	753.0
117.5°	808.1	809.9	811.3	812.7	814.2	815.6	817.9	820.2	822.5	824.7	826.0
120°	883.9	885.6	886.5	887.3	888.2	889.0	891.3	893.6	895.9	898.2	899.3
122.5°	956.3	957.9	959.0	960.2	961.3	962.5	963.9	965.3	966.8	968.2	969.1
125°	1024.5	1026.2	1027.3	1028.5	1029.6	1030.8	1031.3	1031.9	1032.5	1033.0	1033.6
127.5°	1091.5	1093.3	1094.8	1096.2	1097.6	1099.0	1099.9	1100.8	1101.6	1102.5	1102.6
130°	1153.3	1155.0	1156.2	1157.3	1158.5	1159.6	1160.7	1161.9	1163.0	1164.2	1164.5
132.5°	1212.6	1214.1	1215.0	1215.9	1216.7	1217.6	1218.7	1219.9	1221.0	1222.2	1222.3
135°	1270.8	1272.3	1273.4	1274.6	1275.7	1276.9	1277.7	1278.6	1279.4	1280.3	1280.3
137.5°	1324.7	1326.1	1326.7	1327.2	1327.8	1328.4	1329.8	1331.3	1332.7	1334.1	1334.5
140°	1373.9	1375.2	1376.1	1376.9	1377.8	1378.6	1379.8	1380.9	1382.1	1383.2	1383.5
142.5°	1421.6	1422.9	1423.7	1424.6	1425.5	1426.3	1427.2	1428.0	1428.9	1429.7	1429.7
145°	1466.5	1467.8	1468.4	1469.0	1469.5	1470.1	1470.7	1471.3	1471.8	1472.4	1472.7
147.5°	1506.8	1507.8	1508.3	1508.9	1509.5	1510.1	1510.6	1511.2	1511.8	1512.4	1511.9
150°	1543.1	1543.8	1544.4	1545.0	1545.6	1546.1	1546.7	1547.3	1547.9	1548.4	1548.3
152.5°	1575.6	1575.9	1576.2	1576.5	1576.8	1577.1	1578.2	1579.3	1580.5	1581.6	1581.5
155°	1604.4	1604.3	1604.5	1604.8	1605.1	1605.4	1606.8	1608.3	1609.7	1611.1	1611.0
157.5°	1632.5	1632.3	1632.0	1631.7	1631.5	1631.2	1632.9	1634.6	1636.3	1638.0	1637.8
160°	1654.5	1654.2	1653.9	1653.7	1653.4	1653.1	1654.8	1656.5	1658.2	1659.9	1659.8
162.5°	1674.1	1673.5	1673.3	1673.0	1672.7	1672.4	1674.4	1676.4	1678.4	1680.4	1680.6
165°	1690.9	1690.3	1690.0	1689.7	1689.4	1689.2	1691.4	1693.7	1696.0	1698.3	1698.5
167.5°	1703.9	1703.3	1703.3	1703.3	1703.3	1703.3	1705.6	1707.9	1710.2	1712.5	1712.5
170°	1715.5	1714.9	1714.9	1714.9	1714.9	1714.9	1717.2	1719.5	1721.8	1724.1	1724.1
172.5°	1722.1	1721.5	1721.8	1722.1	1722.4	1722.7	1724.9	1727.2	1729.5	1731.8	1731.7
175°	1728.5	1728.0	1728.2	1728.5	1728.8	1729.1	1731.1	1733.1	1735.1	1737.1	1737.0
177.5°	1731.1	1730.5	1730.8	1731.1	1731.4	1731.7	1734.0	1736.3	1738.5	1740.8	1740.5
180°	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2



TEST NUMBER: P831351

CATALOG NUMBER: S123DIP-S340D1195U850-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	1088.8	1088.8	1088.8	1088.8
2.5°	967.8	966.1	959.0	951.9
5°	820.5	814.5	812.5	810.4
7.5°	717.0	716.5	705.9	695.2
10°	625.8	626.5	616.9	607.3
12.5°	560.6	554.3	553.5	552.8
15°	511.6	505.8	504.8	503.7
17.5°	477.0	473.4	472.4	471.4
20°	450.7	448.7	446.9	445.1
22.5°	428.0	425.4	423.9	422.4
25°	406.0	403.7	403.2	402.7
27.5°	386.3	383.5	383.5	383.5
30°	367.6	365.8	365.1	364.3
32.5°	350.1	348.6	348.6	348.6
35°	333.7	333.0	332.0	330.9
37.5°	318.8	318.8	318.3	317.8
40°	304.4	305.2	305.2	305.2
42.5°	291.3	292.0	292.0	292.0
45°	277.6	278.9	279.4	279.9
47.5°	264.3	266.3	266.8	267.3
50°	251.1	252.6	252.9	253.1
52.5°	237.7	239.5	240.8	242.0
55°	223.6	225.3	226.1	226.9
57.5°	208.4	210.2	210.4	210.7
60°	191.7	193.5	194.0	194.5
62.5°	175.8	176.8	177.3	177.9
65°	157.6	159.2	160.2	161.2
67.5°	140.2	141.5	141.5	141.5
70°	120.8	121.3	122.0	122.8
72.5°	102.8	103.1	103.1	103.1
75°	83.9	84.4	84.6	84.9
77.5°	65.9	66.2	66.2	66.2
80°	48.3	48.0	48.0	48.0
82.5°	33.1	32.3	32.3	32.3
85°	18.9	18.7	18.9	19.2
87.5°	8.6	8.6	8.6	8.6
90°	36.9	37.5	38.1	38.7
92.5°	42.9	43.2	43.5	43.8
95°	49.0	49.0	49.0	49.0
97.5°	52.0	52.3	52.5	52.8
100°	53.3	53.5	53.8	54.1
102.5°	53.7	54.3	54.8	55.4
105°	55.0	55.5	56.1	56.7
107.5°	246.5	209.0	171.5	134.0
110°	477.2	436.2	395.3	354.3



TEST NUMBER: P831351

CATALOG NUMBER: S123DIP-S340D1195U850-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
112.5°	673.0	672.4	671.9	671.3
115°	754.2	755.3	756.5	757.6
117.5°	826.3	826.6	826.9	827.2
120°	899.3	899.3	899.3	899.3
122.5°	969.3	969.6	969.9	970.2
125°	1034.2	1034.8	1035.3	1035.9
127.5°	1102.1	1101.5	1100.9	1100.3
130°	1163.9	1163.3	1162.8	1162.2
132.5°	1221.4	1220.6	1219.7	1218.9
135°	1279.4	1278.6	1277.7	1276.9
137.5°	1334.0	1333.4	1332.8	1332.3
140°	1382.9	1382.4	1381.8	1381.2
142.5°	1428.9	1428.0	1427.2	1426.3
145°	1472.7	1472.7	1472.7	1472.7
147.5°	1510.5	1509.1	1507.6	1506.2
150°	1547.4	1546.6	1545.7	1544.8
152.5°	1580.1	1578.6	1577.2	1575.8
155°	1609.3	1607.6	1605.8	1604.1
157.5°	1635.5	1633.2	1630.9	1628.6
160°	1657.8	1655.8	1653.8	1651.8
162.5°	1678.8	1677.1	1675.4	1673.7
165°	1696.5	1694.5	1692.4	1690.4
167.5°	1710.2	1707.9	1705.6	1703.3
170°	1721.8	1719.5	1717.2	1714.9
172.5°	1729.1	1726.5	1723.9	1721.4
175°	1734.7	1732.4	1730.1	1727.8
177.5°	1737.7	1734.8	1732.0	1729.1
180°	1734.2	1734.2	1734.2	1734.2



TEST NUMBER: P831351

CATALOG NUMBER: S123DIP-S340D1195U850-4F0-1E-UDD-G

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.13	9.79	10.28	10.92	12.51	11.37	12.02	12.52	13.16	14.75
	3H	10.76	11.35	11.92	12.49	14.10	12.78	13.36	13.93	14.51	16.12
	4H	11.33	11.89	12.50	13.03	14.64	13.22	13.78	14.38	14.92	16.53
	6H	11.69	12.20	12.86	13.35	14.97	13.48	14.00	14.66	15.14	16.76
	8H	11.78	12.27	12.96	13.43	15.05	13.54	14.03	14.72	15.19	16.80
	12H	11.82	12.28	13.00	13.44	15.07	13.55	14.02	14.73	15.17	16.81
4H	2H	9.68	10.24	10.86	11.38	13.00	11.51	12.06	12.68	13.21	14.82
	3H	11.49	11.96	12.67	13.13	14.75	13.11	13.57	14.29	14.74	16.37
	4H	12.18	12.61	13.36	13.77	15.41	13.68	14.11	14.86	15.27	16.91
	6H	12.65	13.01	13.83	14.19	15.82	14.08	14.44	15.26	15.62	17.25
	8H	12.78	13.12	13.96	14.29	15.94	14.18	14.53	15.37	15.70	17.35
	12H	12.84	13.15	14.04	14.33	15.98	14.22	14.53	15.42	15.71	17.36
8H	4H	12.43	12.78	13.62	13.95	15.60	13.77	14.12	14.96	15.29	16.94
	6H	13.01	13.30	14.22	14.51	16.16	14.27	14.55	15.47	15.76	17.41
	8H	13.22	13.47	14.43	14.66	16.32	14.45	14.69	15.65	15.88	17.55
	12H	13.34	13.55	14.55	14.74	16.44	14.54	14.75	15.75	15.94	17.64
12H	4H	12.42	12.74	13.62	13.92	15.57	13.74	14.05	14.94	15.23	16.88
	6H	13.06	13.31	14.27	14.50	16.17	14.28	14.53	15.49	15.72	17.38
	8H	13.29	13.50	14.50	14.69	16.39	14.47	14.69	15.68	15.88	17.57