

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332624-930

Luminaire Tested: **S124DIP-S795D1205U930-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332624-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIP-S795D1205U930-4F0-1E-UDD-F4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6287.0 lumens
Efficiency: N/A
Efficacy: 110.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 56.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332624-930

CATALOG NUMBER: S124DIP-S795D1205U930-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332624-930

CATALOG NUMBER: S124DIP-S795D1205U930-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44
1	96	92	88	85	88	84	81	78	70	68	66	57	55	54	45	44	43	37
2	88	80	74	69	80	74	69	64	61	58	54	50	47	45	39	38	36	31
3	80	71	63	58	73	65	59	54	54	49	46	44	41	38	35	33	31	26
4	73	63	55	49	67	58	51	45	48	43	39	39	36	33	31	29	26	23
5	67	56	48	42	61	51	44	39	43	38	33	35	31	28	28	25	23	20
6	62	50	42	36	56	46	39	34	39	33	29	32	28	25	26	23	20	17
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15
8	53	41	33	28	48	38	31	26	32	27	23	27	22	19	21	18	16	14
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	20	17	15	12
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8737	8737	8737
5°	8763	8658	8721
10°	8708	8588	8630
15°	8603	8466	8487
20°	8463	8314	8322
25°	8304	8141	8118
30°	8108	7938	7866
35°	7906	7727	7624
40°	7695	7484	7347
45°	7476	7247	7108
50°	7232	7036	6818
55°	6970	6763	6542
60°	6707	6455	6260
65°	6411	6162	5914
70°	6080	5773	5549
75°	5571	5303	5168
80°	4956	4756	4635
85°	4335	4177	4094



TEST NUMBER: P332624-930

CATALOG NUMBER: S124DIP-S795D1205U930-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	101.9	1.6
10°-20°	287.2	4.6
20°-30°	422.7	6.7
30°-40°	491.4	7.8
40°-50°	491.4	7.8
50°-60°	429.8	6.8
60°-70°	319.2	5.1
70°-80°	181.4	2.9
80°-90°	55.0	0.9
90°-100°	348.3	5.5
100°-110°	724.9	11.5
110°-120°	649.3	10.3
120°-130°	546.2	8.7
130°-140°	455.4	7.2
140°-150°	347.9	5.5
150°-160°	244.5	3.9
160°-170°	143.8	2.3
170°-180°	46.8	0.7
0°-30°	811.8	12.9
0°-40°	1303.1	20.7
0°-60°	2224.4	35.4
0°-90°	2779.9	44.2
90°-120°	1722.5	27.4
90°-150°	3071.9	48.9
90°-180°	3507.0	55.8
0°-180°	6287.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1082	1082	1082	1082	1082	
5°	1081	1078	1068	1077	1076	103
15°	1029	1025	1013	1018	1016	290
25°	932	926	914	915	911	429
35°	802	796	784	778	774	501
45°	655	648	635	626	623	505
55°	495	492	480	470	465	443
65°	336	331	323	314	310	332
75°	179	174	170	167	166	190
85°	47	47	45	45	44	52
90°	1	8	17	19	20	4
95°	31	99	772	382	231	35
105°	111	161	622	1338	1333	118
115°	195	245	554	1065	1280	193
125°	272	323	551	906	1021	242
135°	323	385	547	804	913	250
145°	372	426	544	678	746	234
155°	424	457	529	599	624	195
165°	461	476	507	537	545	130
175°	481	482	486	493	491	46
180°	482	482	482	482	482	



TEST NUMBER: P332624-930

CATALOG NUMBER: S124DIP-S795D1205U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1082.3	1082.3	1082.3	1082.3	1082.3	1082.3	1082.3	1082.3	1082.3	1082.3	1082.3
2.5°	1085.1	1084.6	1084.1	1083.7	1083.2	1082.1	1080.4	1078.7	1077.0	1075.4	1076.8
5°	1081.4	1080.7	1079.9	1079.1	1078.3	1076.8	1074.7	1072.6	1070.5	1068.4	1070.5
7.5°	1071.4	1070.6	1069.8	1069.0	1068.3	1066.7	1064.4	1062.0	1059.6	1057.3	1059.0
10°	1062.3	1061.6	1060.8	1060.1	1059.2	1057.6	1055.1	1052.6	1050.1	1047.6	1049.1
12.5°	1050.5	1049.8	1049.0	1048.2	1047.5	1045.7	1043.1	1040.4	1037.8	1035.1	1036.8
15°	1029.4	1028.6	1027.8	1027.0	1026.3	1024.5	1021.6	1018.7	1015.8	1012.9	1014.1
17.5°	1003.9	1002.9	1001.9	1001.0	1000.0	998.2	995.5	992.7	989.9	987.2	988.0
20°	985.1	984.1	983.3	982.3	981.3	979.3	976.5	973.5	970.7	967.8	968.4
22.5°	965.1	963.8	962.5	961.2	959.9	957.9	955.0	952.1	949.2	946.3	947.4
25°	932.2	930.9	929.5	928.2	926.8	924.8	922.1	919.4	916.7	914.0	914.2
27.5°	894.8	893.4	892.0	890.6	889.2	887.3	884.8	882.3	879.8	877.3	876.8
30°	869.8	868.3	866.7	865.2	863.6	861.6	859.1	856.6	854.1	851.6	850.8
32.5°	843.4	842.0	840.7	839.3	837.9	835.8	833.2	830.5	827.9	825.2	824.3
35°	802.2	800.8	799.5	798.1	796.8	794.8	792.1	789.4	786.7	784.0	782.6
37.5°	758.6	757.4	756.2	755.0	753.7	751.6	748.8	745.8	743.0	740.0	738.6
40°	730.2	728.6	727.1	725.5	724.0	721.8	718.9	716.0	713.1	710.2	708.3
42.5°	699.7	698.7	697.8	696.9	695.9	693.9	690.7	687.5	684.3	681.1	678.9
45°	654.8	653.4	652.1	650.7	649.4	647.1	644.1	641.0	637.9	634.8	632.7
47.5°	607.7	606.8	605.9	605.0	604.1	602.2	599.3	596.5	593.6	590.8	588.3
50°	575.8	575.0	574.3	573.5	572.7	571.0	568.3	565.7	562.9	560.2	557.5
52.5°	544.6	543.7	542.7	541.8	540.9	539.0	536.1	533.3	530.4	527.6	525.2
55°	495.2	494.6	494.0	493.4	492.8	491.2	488.5	485.8	483.1	480.5	478.1
57.5°	448.0	447.4	446.7	446.1	445.4	443.7	441.1	438.4	435.8	433.1	430.9
60°	415.4	414.4	413.4	412.5	411.6	409.8	407.3	404.8	402.3	399.8	398.0
62.5°	383.5	382.7	381.9	381.1	380.3	378.5	375.9	373.2	370.6	367.9	366.3
65°	335.6	334.7	333.7	332.7	331.7	330.3	328.4	326.4	324.5	322.6	320.7
67.5°	287.4	286.5	285.6	284.7	283.9	282.5	280.6	278.8	277.0	275.1	273.2
70°	257.6	256.2	254.9	253.5	252.2	250.7	249.2	247.6	246.1	244.6	243.0
72.5°	225.7	224.3	223.0	221.6	220.2	219.0	217.8	216.5	215.2	214.0	212.8
75°	178.6	177.7	176.8	175.8	174.8	173.8	172.8	171.9	171.0	170.0	169.2
77.5°	133.7	133.3	132.9	132.5	132.0	131.4	130.5	129.7	128.8	128.0	127.8
80°	106.6	106.1	105.5	104.9	104.4	103.9	103.5	103.1	102.7	102.3	101.9
82.5°	80.3	80.1	79.7	79.5	79.2	79.1	79.0	78.9	78.8	78.8	78.5
85°	46.8	46.8	46.8	46.8	46.8	46.6	46.2	45.9	45.5	45.1	45.1
87.5°	18.3	18.4	18.8	18.9	18.9	18.8	19.7	19.6	19.8	20.1	19.9
90°	1.0	2.9	5.7	6.6	7.6	7.6	13.3	13.3	15.2	17.0	16.1
92.5°	10.8	15.7	24.6	36.2	50.1	69.7	117.9	191.4	263.0	300.5	250.3
95°	31.2	34.1	43.6	55.9	78.6	118.5	200.8	356.2	582.6	772.1	793.9
97.5°	56.1	56.1	64.2	75.6	95.1	128.5	191.9	320.2	545.3	813.3	997.4
100°	72.0	72.0	78.6	90.0	108.0	138.4	194.2	301.3	494.6	761.7	1004.2
102.5°	87.2	88.7	94.6	105.2	122.4	151.2	201.8	296.0	460.4	697.2	947.4
105°	110.9	113.7	118.5	129.8	146.8	174.3	219.8	298.4	431.0	621.5	844.1
107.5°	137.0	138.8	143.7	155.7	172.0	199.2	240.8	312.4	425.7	579.0	760.8
110°	154.4	156.3	161.0	172.4	189.5	215.1	256.7	323.0	427.3	564.7	719.1



TEST NUMBER: P332624-930

CATALOG NUMBER: S124DIP-S795D1205U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	171.1	173.0	178.5	189.1	206.2	231.7	271.9	334.4	431.8	557.8	695.5
115°	195.2	198.0	204.6	214.1	232.1	257.7	295.5	352.5	440.5	554.2	673.6
117.5°	220.1	222.8	228.7	239.1	256.0	282.5	318.5	370.8	449.8	553.3	663.7
120°	236.8	238.7	245.4	255.8	271.9	298.4	334.4	383.7	456.6	553.3	658.4
122.5°	252.0	253.9	260.6	270.2	287.8	313.6	349.6	395.8	463.5	552.5	652.4
125°	271.9	275.7	281.4	291.8	309.8	336.3	370.4	414.0	473.7	551.4	642.3
127.5°	289.5	292.5	299.4	311.3	330.0	356.8	389.7	429.7	481.8	549.3	628.8
130°	299.4	303.1	310.7	325.0	342.9	370.4	402.7	439.6	487.9	548.5	620.5
132.5°	309.2	312.3	322.1	335.6	355.1	381.1	413.3	449.5	493.2	547.8	612.9
135°	323.0	326.9	336.3	352.5	372.3	397.0	428.2	462.4	501.2	546.7	601.6
137.5°	336.9	340.5	350.9	366.2	386.9	410.4	439.6	471.4	505.9	546.4	591.7
140°	346.7	349.6	360.0	376.1	396.0	418.7	447.2	477.4	509.7	545.7	586.4
142.5°	357.3	360.2	369.8	385.2	404.3	426.3	454.0	482.0	512.7	545.7	581.9
145°	372.3	375.2	384.7	397.9	415.9	436.8	461.4	487.0	514.5	543.8	574.1
147.5°	389.1	390.1	398.4	412.1	427.1	445.8	469.0	491.3	515.4	540.4	567.1
150°	399.8	400.7	408.3	419.7	433.9	451.9	472.7	493.6	515.4	538.1	561.8
152.5°	409.6	409.9	417.4	428.0	440.8	457.2	475.8	495.1	513.9	534.3	555.7
155°	423.5	424.4	430.1	439.6	450.0	464.2	480.3	496.4	511.6	528.6	546.7
157.5°	436.9	436.9	442.2	449.6	458.7	469.9	483.6	496.4	509.2	522.8	537.4
160°	445.2	445.2	449.1	455.7	463.3	473.7	485.0	496.4	506.9	518.2	530.5
162.5°	452.8	452.1	455.1	461.0	467.8	476.0	486.6	496.4	504.6	513.6	524.5
165°	461.4	461.4	463.3	468.0	472.7	478.4	487.0	494.6	500.2	506.9	514.5
167.5°	469.9	469.0	469.9	473.5	476.1	480.5	486.7	492.3	495.7	500.0	505.3
170°	473.7	472.7	473.7	476.5	478.4	481.3	486.0	490.7	492.6	495.5	499.3
172.5°	477.4	476.5	476.7	478.8	480.0	482.0	485.3	489.3	489.6	490.9	494.0
175°	481.3	480.3	480.3	481.3	482.2	482.2	484.1	487.0	486.0	486.0	487.9
177.5°	483.0	482.2	481.4	482.2	482.2	482.2	483.0	484.5	483.0	483.0	483.7
180°	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2



TEST NUMBER: P332624-930

CATALOG NUMBER: S124DIP-S795D1205U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1082.3	1082.3	1082.3	1082.3	1082.3	1082.3	1082.3	1082.3
2.5°	1078.4	1079.9	1081.5	1082.2	1082.1	1081.9	1081.7	1081.6
5°	1072.6	1074.7	1076.8	1077.7	1077.3	1077.0	1076.6	1076.2
7.5°	1060.7	1062.4	1064.0	1064.8	1064.6	1064.4	1064.1	1063.9
10°	1050.7	1052.2	1053.8	1054.3	1053.9	1053.5	1053.2	1052.8
12.5°	1038.5	1040.2	1041.9	1042.4	1042.0	1041.4	1040.8	1040.3
15°	1015.2	1016.4	1017.5	1017.8	1017.2	1016.7	1016.1	1015.5
17.5°	988.7	989.4	990.2	990.3	989.9	989.5	989.2	988.8
20°	969.0	969.6	970.1	970.2	969.8	969.5	969.1	968.7
22.5°	948.4	949.4	950.5	950.6	949.9	949.3	948.5	947.9
25°	914.4	914.6	914.8	914.5	913.8	913.0	912.2	911.4
27.5°	876.4	875.9	875.4	874.7	873.8	872.8	871.8	870.8
30°	850.0	849.3	848.5	847.7	846.7	845.7	844.7	843.8
32.5°	823.4	822.5	821.6	820.6	819.6	818.6	817.7	816.8
35°	781.3	779.9	778.5	777.4	776.4	775.5	774.5	773.6
37.5°	737.1	735.6	734.3	732.9	731.6	730.3	729.0	727.7
40°	706.4	704.5	702.5	701.1	700.1	699.2	698.2	697.2
42.5°	676.6	674.4	672.1	670.7	670.1	669.4	668.8	668.1
45°	630.6	628.4	626.3	625.0	624.4	623.8	623.2	622.6
47.5°	586.0	583.6	581.1	579.3	577.8	576.3	574.9	573.4
50°	554.8	552.1	549.4	547.5	546.3	545.2	544.0	542.9
52.5°	522.9	520.4	518.0	516.2	514.7	513.2	511.8	510.3
55°	475.8	473.5	471.2	469.4	468.3	467.2	465.9	464.8
57.5°	428.7	426.5	424.3	422.7	421.5	420.4	419.3	418.2
60°	396.3	394.6	392.8	391.5	390.5	389.6	388.6	387.7
62.5°	364.7	363.1	361.6	360.3	359.3	358.3	357.4	356.4
65°	318.8	316.8	314.9	313.5	312.5	311.5	310.5	309.6
67.5°	271.4	269.5	267.7	266.6	266.4	266.1	265.8	265.5
70°	241.5	239.9	238.4	237.3	236.8	236.2	235.6	235.1
72.5°	211.6	210.3	209.1	208.2	207.6	207.0	206.4	205.9
75°	168.4	167.6	166.9	166.4	166.2	166.0	165.8	165.7
77.5°	127.5	127.3	127.1	126.7	126.2	125.7	125.2	124.7
80°	101.6	101.2	100.8	100.5	100.3	100.1	100.0	99.7
82.5°	78.3	78.0	77.8	77.6	77.5	77.2	77.0	76.8
85°	45.1	45.1	45.1	45.0	44.8	44.6	44.4	44.2
87.5°	20.1	20.2	20.5	20.5	20.6	20.8	20.6	20.6
90°	17.0	18.0	18.9	18.9	19.9	20.9	19.9	19.9
92.5°	186.1	140.0	111.5	92.5	81.3	76.1	73.0	73.0
95°	702.0	555.1	428.2	336.3	289.9	260.6	243.4	231.1
97.5°	1037.2	982.6	890.0	791.1	723.0	666.0	637.6	617.9
100°	1142.6	1161.5	1115.1	1045.0	962.5	904.7	876.4	868.8
102.5°	1137.3	1231.2	1244.6	1215.4	1164.9	1123.0	1093.1	1087.0
105°	1061.0	1225.0	1318.7	1357.6	1359.5	1351.9	1338.6	1332.9
107.5°	952.8	1127.4	1259.5	1343.9	1390.7	1412.3	1421.8	1424.3
110°	887.7	1051.6	1189.0	1293.1	1360.4	1400.2	1417.3	1425.8



TEST NUMBER: P332624-930

CATALOG NUMBER: S124DIP-S795D1205U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	839.9	984.9	1114.7	1218.9	1295.3	1343.4	1367.3	1381.1
115°	792.0	908.6	1019.4	1110.4	1185.2	1242.0	1272.4	1279.9
117.5°	768.5	865.0	952.1	1029.2	1093.1	1140.8	1171.5	1177.4
120°	757.9	846.0	921.8	989.0	1043.1	1084.8	1109.4	1119.8
122.5°	748.8	833.9	902.9	961.8	1007.5	1043.1	1063.9	1074.3
125°	733.3	814.7	880.1	932.2	970.1	997.6	1015.6	1021.2
127.5°	714.3	792.2	857.4	906.9	944.9	969.4	984.6	990.2
130°	699.2	774.0	838.5	888.7	927.5	951.1	966.3	972.0
132.5°	683.2	753.6	816.4	866.7	904.7	931.5	945.8	951.5
135°	661.3	722.8	780.6	828.0	865.9	892.4	907.6	913.3
137.5°	641.4	693.5	742.2	785.0	820.4	846.6	859.1	865.9
140°	630.0	674.5	717.1	756.9	790.1	811.0	824.2	831.8
142.5°	619.4	658.6	695.2	729.7	759.0	778.4	790.1	795.4
145°	604.5	636.7	665.0	691.6	715.3	731.4	740.9	745.6
147.5°	592.2	617.7	640.4	661.3	678.7	692.5	699.8	701.4
150°	584.6	606.3	625.3	642.3	657.5	669.8	675.5	676.5
152.5°	576.2	594.9	612.4	626.4	639.3	649.3	652.7	653.7
155°	563.7	578.9	593.0	604.5	613.9	621.5	624.4	624.4
157.5°	550.2	563.0	574.9	584.0	591.2	596.9	598.6	598.6
160°	541.9	552.3	562.7	570.3	576.0	581.7	582.6	582.6
162.5°	533.5	542.5	550.7	557.4	561.6	567.3	568.3	567.4
165°	522.0	527.7	534.3	539.1	542.8	546.7	545.7	544.8
167.5°	510.9	515.2	520.5	523.3	525.2	527.7	527.5	526.8
170°	504.0	506.9	510.6	513.5	515.4	516.3	515.4	515.4
172.5°	497.9	500.0	502.3	504.3	505.5	506.5	505.5	504.0
175°	489.8	490.7	492.6	492.6	492.6	494.6	492.6	490.7
177.5°	484.5	485.3	485.3	486.0	485.3	486.0	484.5	483.0
180°	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2

(END OF REPORT)