

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332588-930

Luminaire Tested: **S124DIP-S795D365U930-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332588-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIP-S795D365U930-4F0-1E-UDD-F4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3844.8 lumens
Efficiency: N/A
Efficacy: 109.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 35
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332588-930

CATALOG NUMBER: S124DIP-S795D365U930-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332588-930

CATALOG NUMBER: S124DIP-S795D365U930-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	107	107	107	107	96	96	96	86	86	86	77	77	77	72
1	103	98	94	91	97	93	90	86	84	81	79	75	73	71	68	66	65	61
2	94	86	79	74	88	82	76	71	74	69	65	66	63	60	60	57	54	51
3	85	75	68	62	81	72	65	59	65	59	55	59	54	51	53	49	46	43
4	78	67	59	52	74	64	56	50	58	52	47	52	47	43	47	43	40	37
5	72	60	51	45	68	57	49	44	52	45	41	47	42	38	43	38	35	32
6	66	54	45	39	63	51	44	38	47	40	36	43	37	33	39	34	31	28
7	61	49	40	35	58	47	39	34	43	36	31	39	33	29	35	31	27	25
8	57	44	36	31	54	42	35	30	39	33	28	36	30	26	32	28	25	22
9	53	41	33	28	51	39	32	27	36	30	25	33	28	24	30	25	22	20
10	50	37	30	25	47	36	29	24	33	27	23	30	25	22	28	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8737	8737	8737
5°	8763	8658	8721
10°	8708	8588	8630
15°	8603	8466	8487
20°	8463	8314	8322
25°	8304	8141	8118
30°	8108	7938	7866
35°	7906	7727	7624
40°	7695	7484	7347
45°	7476	7247	7108
50°	7232	7036	6818
55°	6970	6763	6542
60°	6707	6455	6260
65°	6411	6162	5914
70°	6080	5773	5549
75°	5571	5303	5168
80°	4956	4756	4635
85°	4335	4177	4094



TEST NUMBER: P332588-930

CATALOG NUMBER: S124DIP-S795D365U930-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	101.9	2.7
10°-20°	287.2	7.5
20°-30°	422.7	11.0
30°-40°	491.4	12.8
40°-50°	491.4	12.8
50°-60°	429.8	11.2
60°-70°	319.2	8.3
70°-80°	181.4	4.7
80°-90°	53.2	1.4
90°-100°	105.9	2.8
100°-110°	220.5	5.7
110°-120°	197.5	5.1
120°-130°	166.1	4.3
130°-140°	138.5	3.6
140°-150°	105.8	2.8
150°-160°	74.4	1.9
160°-170°	43.7	1.1
170°-180°	14.2	0.4
0°-30°	811.8	21.1
0°-40°	1303.1	33.9
0°-60°	2224.4	57.9
0°-90°	2778.1	72.3
90°-120°	523.9	13.6
90°-150°	934.3	24.3
90°-180°	1067.0	27.8
0°-180°	3844.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1082	1082	1082	1082	1082	
5°	1081	1078	1068	1077	1076	103
15°	1029	1025	1013	1018	1016	290
25°	932	926	914	915	911	429
35°	802	796	784	778	774	501
45°	655	648	635	626	623	505
55°	495	492	480	470	465	443
65°	336	331	323	314	310	332
75°	179	174	170	167	166	190
85°	47	47	45	45	44	52
90°	0	2	5	6	6	3
95°	10	30	235	116	70	11
105°	34	49	189	407	405	36
115°	59	74	169	324	389	59
125°	83	98	168	276	311	74
135°	98	117	166	245	278	76
145°	113	130	165	206	227	71
155°	129	139	161	182	190	59
165°	140	145	154	163	166	40
175°	146	147	148	150	149	14
180°	147	147	147	147	147	



TEST NUMBER: P332588-930

CATALOG NUMBER: S124DIP-S795D365U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1082.3	1082.3	1082.3	1082.3	1082.3	1082.3	1082.3	1082.3	1082.3	1082.3	1082.3
2.5°	1085.1	1084.6	1084.1	1083.7	1083.2	1082.1	1080.4	1078.7	1077.0	1075.4	1076.8
5°	1081.4	1080.7	1079.9	1079.1	1078.3	1076.8	1074.7	1072.6	1070.5	1068.4	1070.5
7.5°	1071.4	1070.6	1069.8	1069.0	1068.3	1066.7	1064.4	1062.0	1059.6	1057.3	1059.0
10°	1062.3	1061.6	1060.8	1060.1	1059.2	1057.6	1055.1	1052.6	1050.1	1047.6	1049.1
12.5°	1050.5	1049.8	1049.0	1048.2	1047.5	1045.7	1043.1	1040.4	1037.8	1035.1	1036.8
15°	1029.4	1028.6	1027.8	1027.0	1026.3	1024.5	1021.6	1018.7	1015.8	1012.9	1014.1
17.5°	1003.9	1002.9	1001.9	1001.0	1000.0	998.2	995.5	992.7	989.9	987.2	988.0
20°	985.1	984.1	983.3	982.3	981.3	979.3	976.5	973.5	970.7	967.8	968.4
22.5°	965.1	963.8	962.5	961.2	959.9	957.9	955.0	952.1	949.2	946.3	947.4
25°	932.2	930.9	929.5	928.2	926.8	924.8	922.1	919.4	916.7	914.0	914.2
27.5°	894.8	893.4	892.0	890.6	889.2	887.3	884.8	882.3	879.8	877.3	876.8
30°	869.8	868.3	866.7	865.2	863.6	861.6	859.1	856.6	854.1	851.6	850.8
32.5°	843.4	842.0	840.7	839.3	837.9	835.8	833.2	830.5	827.9	825.2	824.3
35°	802.2	800.8	799.5	798.1	796.8	794.8	792.1	789.4	786.7	784.0	782.6
37.5°	758.6	757.4	756.2	755.0	753.7	751.6	748.8	745.8	743.0	740.0	738.6
40°	730.2	728.6	727.1	725.5	724.0	721.8	718.9	716.0	713.1	710.2	708.3
42.5°	699.7	698.7	697.8	696.9	695.9	693.9	690.7	687.5	684.3	681.1	678.9
45°	654.8	653.4	652.1	650.7	649.4	647.1	644.1	641.0	637.9	634.8	632.7
47.5°	607.7	606.8	605.9	605.0	604.1	602.2	599.3	596.5	593.6	590.8	588.3
50°	575.8	575.0	574.3	573.5	572.7	571.0	568.3	565.7	562.9	560.2	557.5
52.5°	544.6	543.7	542.7	541.8	540.9	539.0	536.1	533.3	530.4	527.6	525.2
55°	495.2	494.6	494.0	493.4	492.8	491.2	488.5	485.8	483.1	480.5	478.1
57.5°	448.0	447.4	446.7	446.1	445.4	443.7	441.1	438.4	435.8	433.1	430.9
60°	415.4	414.4	413.4	412.5	411.6	409.8	407.3	404.8	402.3	399.8	398.0
62.5°	383.5	382.7	381.9	381.1	380.3	378.5	375.9	373.2	370.6	367.9	366.3
65°	335.6	334.7	333.7	332.7	331.7	330.3	328.4	326.4	324.5	322.6	320.7
67.5°	287.4	286.5	285.6	284.7	283.9	282.5	280.6	278.8	277.0	275.1	273.2
70°	257.6	256.2	254.9	253.5	252.2	250.7	249.2	247.6	246.1	244.6	243.0
72.5°	225.7	224.3	223.0	221.6	220.2	219.0	217.8	216.5	215.2	214.0	212.8
75°	178.6	177.7	176.8	175.8	174.8	173.8	172.8	171.9	171.0	170.0	169.2
77.5°	133.7	133.3	132.9	132.5	132.0	131.4	130.5	129.7	128.8	128.0	127.8
80°	106.6	106.1	105.5	104.9	104.4	103.9	103.5	103.1	102.7	102.3	101.9
82.5°	80.3	80.1	79.7	79.5	79.2	79.1	79.0	78.9	78.8	78.8	78.5
85°	46.8	46.8	46.8	46.8	46.8	46.6	46.2	45.9	45.5	45.1	45.1
87.5°	18.1	18.0	18.1	18.0	17.9	17.7	17.9	17.8	17.7	17.7	17.6
90°	0.3	0.9	1.7	2.0	2.3	2.3	4.0	4.0	4.6	5.2	4.9
92.5°	3.3	4.8	7.5	11.0	15.2	21.2	35.9	58.2	80.0	91.4	76.1
95°	9.5	10.4	13.3	17.0	23.9	36.0	61.1	108.4	177.2	234.8	241.5
97.5°	17.0	17.0	19.6	23.0	28.9	39.1	58.4	97.4	165.8	247.4	303.4
100°	21.9	21.9	23.9	27.4	32.9	42.1	59.1	91.6	150.4	231.7	305.4
102.5°	26.5	27.0	28.8	32.0	37.3	46.0	61.4	90.0	140.1	212.1	288.1
105°	33.8	34.6	36.0	39.5	44.7	53.0	66.9	90.7	131.1	189.0	256.7
107.5°	41.7	42.2	43.7	47.4	52.3	60.6	73.2	95.1	129.5	176.1	231.4
110°	47.0	47.5	49.0	52.4	57.6	65.4	78.1	98.2	130.0	171.7	218.7



TEST NUMBER: P332588-930

CATALOG NUMBER: S124DIP-S795D365U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	52.0	52.6	54.3	57.5	62.7	70.4	82.7	101.7	131.3	169.7	211.6
115°	59.4	60.3	62.2	65.1	70.6	78.4	89.9	107.2	134.0	168.6	204.9
117.5°	66.9	67.8	69.5	72.7	77.9	85.9	96.9	112.8	136.8	168.3	201.9
120°	72.1	72.6	74.6	77.8	82.7	90.7	101.7	116.7	138.9	168.3	200.2
122.5°	76.6	77.2	79.2	82.2	87.6	95.4	106.3	120.4	141.0	168.0	198.4
125°	82.7	83.8	85.6	88.8	94.2	102.3	112.7	125.9	144.1	167.7	195.3
127.5°	88.1	88.9	91.1	94.7	100.4	108.5	118.5	130.7	146.6	167.1	191.3
130°	91.1	92.2	94.5	98.8	104.3	112.7	122.5	133.7	148.4	166.8	188.7
132.5°	94.1	95.0	98.0	102.1	108.0	115.9	125.7	136.7	150.0	166.6	186.5
135°	98.2	99.4	102.3	107.2	113.2	120.7	130.2	140.6	152.5	166.2	183.0
137.5°	102.5	103.5	106.7	111.4	117.6	124.8	133.7	143.4	153.8	166.2	180.0
140°	105.5	106.3	109.5	114.4	120.4	127.3	136.0	145.2	155.0	166.0	178.4
142.5°	108.7	109.6	112.5	117.2	122.9	129.6	138.1	146.6	156.0	166.0	177.0
145°	113.2	114.1	117.0	121.0	126.5	132.8	140.3	148.1	156.5	165.4	174.6
147.5°	118.4	118.6	121.2	125.3	129.9	135.6	142.6	149.4	156.8	164.4	172.5
150°	121.6	121.9	124.2	127.7	132.0	137.5	143.8	150.1	156.8	163.6	170.9
152.5°	124.6	124.7	126.9	130.2	134.0	139.1	144.7	150.6	156.3	162.5	169.0
155°	128.8	129.1	130.9	133.7	136.9	141.2	146.1	151.0	155.6	160.8	166.2
157.5°	132.9	132.9	134.5	136.7	139.5	142.9	147.1	151.0	154.8	159.0	163.5
160°	135.4	135.4	136.6	138.6	140.9	144.1	147.6	151.0	154.2	157.6	161.3
162.5°	137.7	137.5	138.4	140.2	142.3	144.8	148.0	151.0	153.4	156.2	159.6
165°	140.3	140.3	140.9	142.4	143.8	145.5	148.1	150.4	152.1	154.2	156.5
167.5°	142.9	142.6	142.9	144.0	144.8	146.2	148.1	149.7	150.7	152.1	153.7
170°	144.1	143.8	144.1	145.0	145.5	146.3	147.8	149.3	149.9	150.7	151.9
172.5°	145.2	145.0	145.0	145.6	145.9	146.6	147.6	148.8	149.0	149.3	150.3
175°	146.3	146.1	146.1	146.3	146.7	146.7	147.2	148.1	147.8	147.8	148.4
177.5°	146.9	146.7	146.4	146.7	146.7	146.7	146.9	147.3	146.9	146.9	147.2
180°	146.7	146.7	146.7	146.7	146.7	146.7	146.7	146.7	146.7	146.7	146.7



TEST NUMBER: P332588-930

CATALOG NUMBER: S124DIP-S795D365U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1082.3	1082.3	1082.3	1082.3	1082.3	1082.3	1082.3	1082.3
2.5°	1078.4	1079.9	1081.5	1082.2	1082.1	1081.9	1081.7	1081.6
5°	1072.6	1074.7	1076.8	1077.7	1077.3	1077.0	1076.6	1076.2
7.5°	1060.7	1062.4	1064.0	1064.8	1064.6	1064.4	1064.1	1063.9
10°	1050.7	1052.2	1053.8	1054.3	1053.9	1053.5	1053.2	1052.8
12.5°	1038.5	1040.2	1041.9	1042.4	1042.0	1041.4	1040.8	1040.3
15°	1015.2	1016.4	1017.5	1017.8	1017.2	1016.7	1016.1	1015.5
17.5°	988.7	989.4	990.2	990.3	989.9	989.5	989.2	988.8
20°	969.0	969.6	970.1	970.2	969.8	969.5	969.1	968.7
22.5°	948.4	949.4	950.5	950.6	949.9	949.3	948.5	947.9
25°	914.4	914.6	914.8	914.5	913.8	913.0	912.2	911.4
27.5°	876.4	875.9	875.4	874.7	873.8	872.8	871.8	870.8
30°	850.0	849.3	848.5	847.7	846.7	845.7	844.7	843.8
32.5°	823.4	822.5	821.6	820.6	819.6	818.6	817.7	816.8
35°	781.3	779.9	778.5	777.4	776.4	775.5	774.5	773.6
37.5°	737.1	735.6	734.3	732.9	731.6	730.3	729.0	727.7
40°	706.4	704.5	702.5	701.1	700.1	699.2	698.2	697.2
42.5°	676.6	674.4	672.1	670.7	670.1	669.4	668.8	668.1
45°	630.6	628.4	626.3	625.0	624.4	623.8	623.2	622.6
47.5°	586.0	583.6	581.1	579.3	577.8	576.3	574.9	573.4
50°	554.8	552.1	549.4	547.5	546.3	545.2	544.0	542.9
52.5°	522.9	520.4	518.0	516.2	514.7	513.2	511.8	510.3
55°	475.8	473.5	471.2	469.4	468.3	467.2	465.9	464.8
57.5°	428.7	426.5	424.3	422.7	421.5	420.4	419.3	418.2
60°	396.3	394.6	392.8	391.5	390.5	389.6	388.6	387.7
62.5°	364.7	363.1	361.6	360.3	359.3	358.3	357.4	356.4
65°	318.8	316.8	314.9	313.5	312.5	311.5	310.5	309.6
67.5°	271.4	269.5	267.7	266.6	266.4	266.1	265.8	265.5
70°	241.5	239.9	238.4	237.3	236.8	236.2	235.6	235.1
72.5°	211.6	210.3	209.1	208.2	207.6	207.0	206.4	205.9
75°	168.4	167.6	166.9	166.4	166.2	166.0	165.8	165.7
77.5°	127.5	127.3	127.1	126.7	126.2	125.7	125.2	124.7
80°	101.6	101.2	100.8	100.5	100.3	100.1	100.0	99.7
82.5°	78.3	78.0	77.8	77.6	77.5	77.2	77.0	76.8
85°	45.1	45.1	45.1	45.0	44.8	44.6	44.4	44.2
87.5°	17.7	17.8	17.8	17.8	17.9	17.9	17.9	17.9
90°	5.2	5.5	5.8	5.8	6.0	6.4	6.0	6.0
92.5°	56.6	42.6	33.9	28.1	24.7	23.2	22.2	22.2
95°	213.5	168.8	130.2	102.3	88.1	79.2	74.0	70.3
97.5°	315.4	298.9	270.7	240.6	219.9	202.6	194.0	187.9
100°	347.5	353.3	339.2	317.8	292.8	275.2	266.5	264.2
102.5°	345.9	374.5	378.5	369.7	354.3	341.6	332.5	330.6
105°	322.7	372.6	401.1	412.9	413.5	411.2	407.2	405.4
107.5°	289.8	342.9	383.0	408.8	423.0	429.6	432.4	433.2
110°	270.0	319.8	361.7	393.3	413.8	425.9	431.0	433.7



TEST NUMBER: P332588-930

CATALOG NUMBER: S124DIP-S795D365U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	255.4	299.5	339.0	370.7	394.0	408.6	415.9	420.0
115°	240.9	276.3	310.1	337.7	360.4	377.7	387.0	389.3
117.5°	233.7	263.1	289.6	313.1	332.5	347.0	356.3	358.1
120°	230.5	257.3	280.4	300.8	317.2	330.0	337.5	340.6
122.5°	227.7	253.6	274.6	292.5	306.4	317.2	323.6	326.8
125°	223.1	247.8	267.7	283.6	295.1	303.5	308.9	310.6
127.5°	217.3	240.9	260.8	275.8	287.4	294.8	299.5	301.2
130°	212.6	235.5	255.0	270.3	282.1	289.3	293.9	295.6
132.5°	207.8	229.2	248.3	263.6	275.2	283.3	287.7	289.4
135°	201.1	219.9	237.4	251.8	263.3	271.4	276.1	277.8
137.5°	195.1	210.9	225.8	238.7	249.6	257.5	261.3	263.3
140°	191.6	205.1	218.1	230.2	240.4	246.6	250.7	253.0
142.5°	188.4	200.3	211.4	221.9	230.9	236.8	240.4	241.9
145°	183.8	193.6	202.3	210.3	217.5	222.4	225.3	226.7
147.5°	180.1	187.8	194.8	201.1	206.4	210.7	212.8	213.4
150°	177.8	184.4	190.2	195.3	200.0	203.7	205.5	205.7
152.5°	175.3	181.0	186.3	190.5	194.4	197.5	198.5	198.9
155°	171.5	176.0	180.3	183.8	186.7	189.0	189.9	189.9
157.5°	167.4	171.2	174.9	177.7	179.8	181.6	182.1	182.1
160°	164.9	168.0	171.1	173.5	175.2	176.9	177.2	177.2
162.5°	162.3	165.0	167.5	169.6	170.8	172.5	172.8	172.6
165°	158.7	160.5	162.5	164.0	165.1	166.2	166.0	165.7
167.5°	155.4	156.7	158.3	159.1	159.7	160.5	160.5	160.2
170°	153.3	154.2	155.3	156.2	156.8	157.0	156.8	156.8
172.5°	151.5	152.1	152.8	153.4	153.8	154.0	153.8	153.3
175°	149.0	149.3	149.9	149.9	149.9	150.4	149.9	149.3
177.5°	147.3	147.6	147.6	147.8	147.6	147.8	147.3	146.9
180°	146.7	146.7	146.7	146.7	146.7	146.7	146.7	146.7

(END OF REPORT)