

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831650

Luminaire Tested: S123DIP-S775D365U850-4F0-1E-UDD-G4

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P831650
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-1, G3-1807-864-17)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-S775D365U850-4F0-1E-UDD-G4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, GRAZE OPTIC
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5390.7 lumens
Efficiency: N/A
Efficacy: 150.2 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 1.19 / 0.89
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 35.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P831650
CATALOG NUMBER: S123DIP-S775D365U850-4F0-1E-UDD-G4

Luminous Intensity Polar Plot





TEST NUMBER: P831650

CATALOG NUMBER: S123DIP-S775D365U850-4F0-1E-UDD-G4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	113	113	113	113	107	107	107	107	96	96	96	86	86	86	77	77	77	77	77	77	73	
1	104	99	96	92	98	95	91	88	86	83	81	77	75	73	69	68	67	67	67	67	63	
2	95	88	82	77	90	84	78	74	76	72	68	69	66	63	62	60	57	57	57	57	54	
3	87	78	71	65	83	75	68	63	68	63	58	62	58	54	56	53	50	50	50	50	47	
4	81	70	62	56	76	67	60	54	61	55	51	56	51	47	51	47	44	44	44	44	41	
5	74	63	55	49	71	60	53	48	55	49	45	51	46	42	46	42	39	39	39	39	36	
6	69	57	49	43	66	55	48	42	50	44	40	46	41	37	42	38	35	35	35	35	33	
7	64	52	44	39	61	50	43	38	46	40	36	43	38	34	39	35	32	32	32	32	29	
8	60	48	40	35	57	46	39	34	43	37	32	39	34	31	36	32	29	29	29	29	27	
9	56	44	37	32	54	43	36	31	40	34	29	37	32	28	34	30	27	27	27	27	25	
10	53	41	34	29	50	40	33	28	37	31	27	34	29	26	32	27	24	24	24	24	23	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	26337	26337	26337	26337	26337
5°	33309	31437	26573	21414	19678
10°	33632	34649	26397	17070	14917
15°	25331	32169	26216	14456	12615
20°	17649	26032	25882	12641	11458
25°	13459	20018	25312	11631	10747
30°	11642	15904	24401	10916	10174
35°	10801	13428	23349	10399	9772
40°	10227	12045	21874	9908	9636
45°	9887	11149	19998	9523	9575
50°	9716	10438	17777	9173	9525
55°	9355	9918	15597	8843	9567
60°	9020	9362	13444	8531	9410
65°	8474	8835	11596	8199	9225
70°	7827	8164	9863	7648	8683
75°	7083	7320	8451	7107	7935
80°	5839	6403	6688	6192	6688
85°	4631	5187	4903	5261	5323

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 22832 cd/sqm



TEST NUMBER: P831650

CATALOG NUMBER: S123DIP-S775D365U850-4F0-1E-UDD-G4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	231.3	4.3
10°-20°	575.5	10.7
20°-30°	681.4	12.6
30°-40°	685.1	12.7
40°-50°	628.6	11.7
50°-60°	518.8	9.6
60°-70°	367.0	6.8
70°-80°	195.9	3.6
80°-90°	50.8	0.9
90°-100°	105.1	1.9
100°-110°	307.6	5.7
110°-120°	300.4	5.6
120°-130°	239.2	4.4
130°-140°	188.7	3.5
140°-150°	140.8	2.6
150°-160°	98.2	1.8
160°-170°	57.7	1.1
170°-180°	18.8	0.3
0°-30°	1488.2	27.6
0°-40°	2173.3	40.3
0°-60°	3320.7	61.6
0°-90°	3934.4	73.0
90°-120°	713.0	13.2
90°-150°	1281.7	23.8
90°-180°	1456.0	27.0
0°-180°	5390.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2447	2447	2447	2447	2447	
5°	3083	2910	2459	1982	1821	294
15°	2273	2887	2353	1297	1132	628
25°	1133	1686	2131	979	905	535
35°	822	1022	1777	791	744	517
45°	650	732	1314	626	629	503
55°	498	528	831	471	510	446
65°	333	347	455	322	362	331
75°	170	176	203	171	191	179
85°	38	42	40	43	43	42
90°	11	10	1	10	11	8
95°	46	232	13	232	46	74
105°	498	315	46	315	498	497
115°	606	241	80	241	606	591
125°	478	225	112	225	478	433
135°	388	222	131	222	388	301
145°	303	219	149	219	303	192
155°	251	212	170	212	251	117
165°	219	203	185	203	219	63
175°	197	195	193	195	197	19
180°	194	194	194	194	194	



TEST NUMBER: P831650

CATALOG NUMBER: S123DIP-S775D365U850-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2446.8	2446.8	2446.8	2446.8	2446.8	2446.8	2446.8	2446.8	2446.8	2446.8	2446.8
2.5°	2758.0	2755.1	2752.3	2738.1	2723.9	2717.1	2710.3	2689.8	2669.4	2646.7	2624.0
5°	3082.7	3090.6	3098.6	3089.5	3080.4	3052.6	3024.8	2987.9	2951.0	2909.5	2868.1
7.5°	3232.6	3237.1	3241.6	3236.0	3230.3	3222.9	3215.5	3182.6	3149.7	3107.1	3064.5
10°	3077.0	3087.2	3097.4	3119.6	3141.7	3166.7	3191.7	3187.1	3182.6	3170.1	3157.6
12.5°	2735.2	2747.7	2760.2	2804.5	2848.8	2905.6	2962.3	3011.2	3060.0	3094.0	3128.1
15°	2273.1	2307.8	2342.4	2382.7	2423.0	2506.5	2589.9	2692.7	2795.4	2886.8	2978.2
17.5°	1872.3	1885.4	1898.4	1941.6	1984.7	2089.8	2194.8	2313.4	2432.1	2583.7	2735.2
20°	1540.8	1552.7	1564.6	1621.4	1678.2	1760.5	1842.8	1976.2	2109.6	2272.6	2435.5
22.5°	1294.4	1313.1	1331.9	1363.6	1395.4	1474.4	1553.3	1671.9	1790.6	1970.5	2150.5
25°	1133.2	1146.8	1160.4	1179.7	1199.0	1262.0	1325.0	1422.7	1520.3	1685.5	1850.7
27.5°	1023.0	1028.7	1034.4	1053.7	1073.0	1113.9	1154.7	1238.8	1322.8	1463.0	1603.2
30°	936.7	940.7	944.7	961.7	978.7	1006.6	1034.4	1095.1	1155.9	1279.6	1403.4
32.5°	876.5	879.4	882.2	895.3	908.3	928.2	948.1	992.4	1036.6	1138.8	1241.0
35°	822.0	823.8	825.5	835.1	844.8	859.5	874.3	907.8	941.3	1021.9	1102.5
37.5°	774.4	776.6	778.9	784.6	790.3	803.3	816.4	843.1	869.7	931.6	993.5
40°	727.8	731.8	735.8	739.7	743.7	754.5	765.3	785.7	806.2	857.2	908.3
42.5°	688.1	692.0	696.0	697.7	699.4	705.7	711.9	730.6	749.4	787.4	825.5
45°	649.5	651.2	652.9	654.6	656.3	661.4	666.5	683.0	699.4	732.4	765.3
47.5°	614.3	614.3	614.3	615.4	616.5	621.1	625.6	637.5	649.5	675.0	700.6
50°	580.2	580.2	580.2	578.5	576.8	579.6	582.5	591.6	600.6	623.3	646.1
52.5°	539.3	539.3	539.3	539.9	540.5	540.5	540.5	548.4	556.4	576.8	597.2
55°	498.5	500.7	503.0	501.3	499.6	500.7	501.9	507.0	512.1	528.5	545.0
57.5°	457.6	458.7	459.8	459.3	458.7	459.3	459.8	464.4	468.9	481.4	493.9
60°	419.0	419.0	419.0	417.8	416.7	417.8	419.0	421.2	423.5	434.9	446.2
62.5°	375.8	376.4	377.0	377.5	378.1	377.0	375.8	378.7	381.5	390.0	398.5
65°	332.7	333.2	333.8	335.5	337.2	336.1	335.0	337.8	340.6	346.9	353.1
67.5°	294.1	292.9	291.8	292.4	292.9	294.6	296.3	296.9	297.5	304.3	311.1
70°	248.7	249.8	250.9	250.4	249.8	250.4	250.9	252.6	254.3	259.4	264.6
72.5°	207.8	208.4	208.9	208.9	208.9	210.1	211.2	212.9	214.6	217.4	220.3
75°	170.3	170.3	170.3	171.4	172.6	173.2	173.7	173.7	173.7	176.0	178.3
77.5°	129.4	132.3	135.1	134.5	134.0	135.1	136.3	138.0	139.7	140.8	141.9
80°	94.2	94.2	94.2	94.8	95.4	97.1	98.8	99.9	101.1	103.3	105.6
82.5°	60.2	60.7	61.3	63.0	64.7	65.9	67.0	68.7	70.4	70.4	70.4
85°	37.5	36.3	35.2	36.3	37.5	38.6	39.7	40.3	40.9	42.0	43.1
87.5°	18.2	18.2	18.2	18.2	18.2	18.7	19.3	19.3	19.3	19.3	19.3
90°	11.4	11.8	11.4	11.0	11.4	10.6	10.2	9.8	9.4	9.8	8.6
92.5°	20.8	21.6	21.2	22.7	23.5	26.3	30.2	38.8	54.5	72.9	80.7
95°	45.5	47.0	49.8	53.3	60.7	74.9	95.6	141.1	188.5	232.4	206.9
97.5°	93.3	97.6	107.0	121.9	148.1	192.8	244.5	324.1	369.6	357.4	266.9
100°	245.7	245.3	260.6	289.2	328.8	384.5	430.3	462.0	448.3	371.1	250.8
102.5°	389.2	400.5	412.7	433.8	462.4	492.6	514.6	507.9	452.3	345.7	227.3
105°	498.5	500.5	513.0	527.9	545.9	556.1	548.7	509.5	427.6	315.1	208.9
107.5°	569.8	574.1	579.2	586.3	588.6	578.1	547.5	486.0	392.3	288.0	195.6
110°	610.6	611.4	612.1	609.0	598.0	570.6	521.2	449.1	359.4	265.7	188.5



TEST NUMBER: P831650

CATALOG NUMBER: S123DIP-S775D365U850-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	618.8	618.4	614.5	603.1	580.8	543.6	486.7	412.7	330.8	250.8	184.6
115°	606.3	604.3	596.5	579.2	549.8	507.1	449.5	381.3	308.8	241.0	184.2
117.5°	578.8	576.1	564.3	545.1	514.6	470.3	417.4	357.0	294.3	234.4	184.6
120°	542.8	540.4	531.0	509.1	478.1	438.5	391.5	338.6	283.3	230.0	186.2
122.5°	509.1	505.9	495.4	476.2	449.5	413.5	370.7	324.1	274.3	227.3	188.9
125°	478.1	475.4	465.6	448.3	423.3	391.9	354.3	311.6	266.9	225.0	191.6
127.5°	451.5	449.1	440.1	425.2	402.5	373.5	339.0	300.2	259.8	223.8	194.8
130°	429.5	426.4	418.2	404.0	383.3	356.6	324.9	289.6	254.3	222.6	197.9
132.5°	408.0	406.0	399.0	384.8	365.6	340.6	311.6	279.8	249.2	222.2	200.3
135°	387.6	384.8	377.8	366.0	346.8	324.5	299.0	271.2	244.9	221.8	202.6
137.5°	366.0	363.7	357.8	345.7	329.2	309.2	286.5	263.0	241.0	221.0	204.2
140°	343.3	343.7	337.4	326.5	311.6	294.7	275.9	255.9	237.5	220.6	205.7
142.5°	322.1	322.5	317.0	307.6	295.5	281.4	265.7	249.2	234.4	219.9	206.9
145°	302.9	302.2	299.0	290.8	281.0	269.6	257.1	244.2	231.6	219.1	207.3
147.5°	286.5	286.1	283.0	277.1	269.2	261.0	250.4	239.8	228.9	217.9	207.3
150°	272.4	272.4	270.0	265.7	259.8	252.4	244.2	235.1	226.1	216.3	207.3
152.5°	260.6	260.6	259.4	255.5	251.2	245.3	238.3	230.8	223.0	214.4	206.1
155°	251.2	250.8	250.0	246.9	243.4	238.7	232.8	226.5	219.9	212.0	205.4
157.5°	242.2	242.2	241.4	239.1	235.9	232.0	227.3	221.8	216.3	210.1	204.2
160°	233.6	234.0	234.0	231.6	228.9	226.1	222.2	217.9	212.8	207.7	203.4
162.5°	225.7	226.1	226.1	224.2	222.6	220.2	216.7	213.2	209.3	205.4	201.8
165°	219.1	219.1	219.5	217.9	216.3	214.4	211.6	209.3	206.1	203.0	200.3
167.5°	212.4	212.4	212.8	211.6	210.8	209.3	207.7	205.7	203.0	200.7	198.7
170°	206.5	206.5	206.9	206.1	205.7	205.0	203.4	202.2	200.3	198.3	197.1
172.5°	201.0	201.4	202.2	201.4	201.4	201.0	199.9	199.1	197.5	196.3	195.9
175°	197.1	197.5	197.9	197.5	197.5	197.5	196.7	196.3	195.6	194.8	194.8
177.5°	194.4	194.4	195.2	194.8	195.2	195.2	194.8	194.4	194.0	193.6	194.0
180°	193.6	193.6	193.6	193.6	193.6	193.6	193.6	193.6	193.6	193.6	193.6



TEST NUMBER: P831650

CATALOG NUMBER: S123DIP-S775D365U850-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2446.8	2446.8	2446.8	2446.8	2446.8	2446.8	2446.8	2446.8	2446.8	2446.8	2446.8
2.5°	2617.2	2610.3	2585.4	2560.4	2532.0	2503.6	2482.6	2461.6	2430.4	2399.2	2373.6
5°	2836.3	2804.5	2751.7	2698.9	2627.4	2555.8	2507.6	2459.3	2394.6	2329.9	2278.2
7.5°	3010.0	2955.5	2881.7	2807.9	2714.2	2620.6	2532.0	2443.4	2344.7	2245.9	2165.3
10°	3120.7	3083.8	2998.7	2913.5	2788.0	2662.6	2538.8	2415.1	2287.9	2160.7	2054.0
12.5°	3131.5	3134.9	3056.6	2978.2	2836.3	2694.4	2543.9	2393.5	2233.4	2073.3	1949.0
15°	3036.7	3095.2	3052.0	3008.9	2865.8	2722.8	2537.7	2352.6	2168.1	1983.6	1840.0
17.5°	2860.7	2986.2	2992.4	2998.7	2855.6	2712.5	2507.6	2302.6	2093.7	1884.8	1733.8
20°	2620.6	2805.6	2869.2	2932.8	2816.4	2700.0	2479.8	2259.5	2025.6	1791.7	1633.3
22.5°	2375.3	2600.1	2716.5	2832.9	2746.6	2660.3	2425.8	2191.4	1944.4	1697.5	1536.8
25°	2096.0	2341.3	2520.1	2698.9	2646.1	2593.3	2362.3	2131.2	1868.3	1605.5	1441.4
27.5°	1852.4	2101.7	2317.4	2533.1	2521.8	2510.4	2281.1	2051.7	1782.6	1513.5	1355.1
30°	1635.6	1867.8	2109.1	2350.3	2378.2	2406.0	2184.6	1963.2	1693.5	1423.8	1271.1
32.5°	1443.7	1646.4	1905.2	2164.1	2218.6	2273.1	2073.3	1873.5	1606.6	1339.8	1192.8
35°	1286.4	1470.4	1729.3	1988.1	2056.3	2124.4	1950.7	1776.9	1516.9	1256.9	1116.7
37.5°	1147.3	1301.2	1553.8	1806.5	1889.9	1973.4	1817.8	1662.3	1418.7	1175.2	1046.3
40°	1032.1	1155.9	1388.1	1620.3	1716.8	1813.3	1685.0	1556.7	1325.6	1094.6	975.9
42.5°	935.6	1045.7	1256.4	1467.0	1559.5	1652.0	1543.6	1435.2	1229.7	1024.2	915.7
45°	853.3	941.3	1132.6	1323.9	1411.9	1499.9	1406.8	1313.7	1132.6	951.5	850.4
47.5°	776.1	851.6	1015.1	1178.6	1256.9	1335.3	1262.6	1189.9	1036.6	883.4	792.0
50°	706.8	767.5	910.6	1053.7	1121.8	1189.9	1125.8	1061.6	935.6	809.6	730.1
52.5°	646.6	696.0	815.8	935.6	994.1	1052.5	997.5	942.4	842.5	742.6	673.3
55°	587.0	629.0	732.9	836.8	876.5	916.3	873.7	831.1	750.5	669.9	611.4
57.5°	531.4	568.8	654.0	739.2	769.8	800.5	761.9	723.3	662.5	601.8	553.0
60°	476.9	507.5	578.5	649.5	668.2	686.9	655.7	624.5	581.9	539.3	495.6
62.5°	426.4	454.2	507.0	559.8	572.3	584.7	560.9	537.1	504.7	472.3	438.3
65°	374.1	395.1	438.3	481.4	489.4	497.3	476.3	455.3	430.9	406.5	381.5
67.5°	325.9	340.6	375.8	411.0	411.6	412.2	395.1	378.1	364.5	350.8	331.0
70°	278.7	292.9	316.2	339.5	340.1	340.6	327.0	313.4	303.2	292.9	278.2
72.5°	230.5	240.7	258.3	275.9	274.8	273.6	265.1	256.6	248.7	240.7	229.9
75°	186.8	195.3	207.2	219.1	215.7	212.3	207.8	203.2	196.4	189.6	182.8
77.5°	147.0	152.1	159.0	165.8	163.5	161.2	157.3	153.3	148.2	143.1	140.2
80°	107.9	110.1	114.7	119.2	118.1	116.9	112.4	107.9	106.7	105.6	101.6
82.5°	73.2	76.1	77.2	78.3	77.8	77.2	73.8	70.4	69.3	68.1	67.6
85°	43.7	44.3	44.8	45.4	43.7	42.0	40.9	39.7	39.7	39.7	39.2
87.5°	19.9	20.4	20.4	20.4	19.9	19.3	18.2	17.0	17.6	18.2	18.2
90°	7.4	6.3	5.1	4.3	3.5	2.4	1.6	0.8	1.6	2.4	3.5
92.5°	60.4	39.6	27.0	20.0	16.1	12.5	8.6	5.9	8.6	12.5	16.1
95°	142.7	84.3	50.9	35.7	25.5	18.8	14.5	13.3	14.5	18.8	25.5
97.5°	158.7	90.9	58.0	41.1	31.0	25.1	21.6	21.2	21.6	25.1	31.0
100°	147.7	89.7	62.3	47.0	37.6	32.1	29.4	29.0	29.4	32.1	37.6
102.5°	138.3	91.3	67.4	53.7	45.5	40.4	38.0	37.2	38.0	40.4	45.5
105°	134.8	94.4	73.3	61.1	53.7	49.0	46.6	45.5	46.6	49.0	53.7
107.5°	134.0	99.5	80.7	69.4	62.3	57.6	55.3	54.1	55.3	57.6	62.3
110°	136.0	106.2	88.6	77.6	70.9	66.6	64.7	63.5	64.7	66.6	70.9



TEST NUMBER: P831650

CATALOG NUMBER: S123DIP-S775D365U850-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	139.9	112.9	96.8	86.2	79.6	75.2	73.3	72.1	73.3	75.2	79.6
115°	144.2	120.3	105.4	94.8	88.2	84.3	81.9	80.3	81.9	84.3	88.2
117.5°	149.7	128.2	113.3	103.5	96.0	92.5	90.5	88.6	90.5	92.5	96.0
120°	156.0	135.6	121.5	111.7	104.2	100.3	98.4	97.2	98.4	100.3	104.2
122.5°	161.9	143.4	129.7	119.1	112.1	107.8	105.8	104.6	105.8	107.8	112.1
125°	168.1	150.9	137.2	126.6	119.1	114.8	112.5	111.7	112.5	114.8	119.1
127.5°	173.2	157.5	144.2	133.6	125.4	121.1	118.4	117.2	118.4	121.1	125.4
130°	178.3	163.4	150.5	139.9	131.7	127.0	123.4	122.3	123.4	127.0	131.7
132.5°	183.0	168.5	156.0	145.8	137.6	131.7	127.8	126.2	127.8	131.7	137.6
135°	186.9	173.6	161.5	150.9	142.7	136.8	132.5	130.9	132.5	136.8	142.7
137.5°	190.1	177.1	165.4	155.6	147.4	141.1	136.8	135.2	136.8	141.1	147.4
140°	192.4	180.7	169.3	159.5	151.7	145.4	141.5	139.5	141.5	145.4	151.7
142.5°	194.8	183.4	172.4	163.4	155.6	150.1	145.8	144.2	145.8	150.1	155.6
145°	196.3	185.8	175.6	166.6	159.9	154.0	150.5	149.3	150.5	154.0	159.9
147.5°	197.5	187.7	178.3	170.5	163.8	158.7	155.2	154.4	155.2	158.7	163.8
150°	197.9	189.7	180.7	173.6	168.1	163.0	159.9	159.5	159.9	163.0	168.1
152.5°	198.7	190.9	183.4	176.7	172.0	167.7	164.6	164.6	164.6	167.7	172.0
155°	198.7	192.4	185.8	180.3	176.0	172.0	169.7	169.7	169.7	172.0	176.0
157.5°	199.1	193.2	187.7	183.4	179.5	176.0	174.0	173.6	174.0	176.0	179.5
160°	199.1	194.4	189.7	185.8	183.0	179.9	178.3	178.3	178.3	179.9	183.0
162.5°	198.7	194.8	190.9	187.7	185.4	183.0	181.8	181.8	181.8	183.0	185.4
165°	197.9	195.2	192.0	189.3	187.7	185.8	185.0	185.4	185.0	185.8	187.7
167.5°	197.5	195.2	192.8	190.9	189.7	188.1	187.7	188.1	187.7	188.1	189.7
170°	196.3	194.8	192.8	192.0	191.2	190.1	189.7	190.5	189.7	190.1	191.2
172.5°	195.9	194.8	193.2	192.8	192.4	191.6	191.6	192.0	191.6	191.6	192.4
175°	195.2	194.4	193.6	193.2	193.2	192.4	192.8	193.2	192.8	192.4	193.2
177.5°	194.8	194.0	193.6	193.6	193.6	193.2	193.6	194.0	193.6	193.2	193.6
180°	193.6	193.6	193.6	193.6	193.6	193.6	193.6	193.6	193.6	193.6	193.6



TEST NUMBER: P831650

CATALOG NUMBER: S123DIP-S775D365U850-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2446.8	2446.8	2446.8	2446.8	2446.8	2446.8	2446.8	2446.8	2446.8	2446.8	2446.8
2.5°	2348.1	2325.9	2303.8	2286.8	2269.7	2240.8	2211.8	2205.0	2198.2	2188.5	2178.9
5°	2226.6	2172.1	2117.6	2068.7	2019.9	1981.9	1943.9	1918.9	1893.9	1875.7	1857.6
7.5°	2084.6	2002.9	1921.1	1863.2	1805.3	1750.3	1695.2	1677.6	1660.0	1636.2	1612.3
10°	1947.3	1857.0	1766.7	1691.2	1615.7	1561.8	1507.8	1486.3	1464.7	1434.6	1404.5
12.5°	1824.6	1725.8	1627.1	1551.0	1474.9	1422.7	1370.5	1339.2	1308.0	1291.0	1273.9
15°	1696.3	1590.7	1485.1	1414.7	1344.3	1297.2	1250.1	1222.9	1195.6	1179.1	1162.7
17.5°	1582.8	1478.3	1373.9	1306.3	1238.8	1195.6	1152.5	1128.6	1104.8	1092.3	1079.8
20°	1474.9	1372.7	1270.5	1204.7	1138.8	1103.6	1068.4	1053.1	1037.8	1027.6	1017.3
22.5°	1376.1	1275.7	1175.2	1119.0	1062.8	1034.4	1006.0	995.2	984.4	975.9	967.4
25°	1277.4	1187.7	1098.0	1050.3	1002.6	979.3	956.0	945.2	934.5	925.9	917.4
27.5°	1196.7	1111.0	1025.3	984.4	943.5	925.4	907.2	898.7	890.2	882.2	874.3
30°	1118.4	1041.8	965.1	929.9	894.7	878.3	861.8	853.3	844.8	837.4	830.0
32.5°	1045.7	979.9	914.0	881.7	849.3	835.7	822.0	811.8	801.6	795.9	790.3
35°	976.5	917.4	858.4	831.7	805.0	791.4	777.8	769.3	760.7	756.2	751.7
37.5°	917.4	864.6	811.8	786.3	760.7	747.7	734.6	727.2	719.9	718.2	716.5
40°	857.2	811.8	766.4	741.4	716.5	705.1	693.7	689.2	684.7	683.5	682.4
42.5°	807.3	763.0	718.7	696.0	673.3	663.7	654.0	651.7	649.5	651.2	652.9
45°	749.4	712.5	675.6	654.6	633.6	625.6	617.7	616.0	614.3	617.7	621.1
47.5°	700.6	666.5	632.4	612.6	592.7	587.0	581.3	580.8	580.2	584.7	589.3
50°	650.6	617.7	584.7	568.8	553.0	547.8	542.7	544.4	546.1	553.5	560.9
52.5°	604.0	573.4	542.7	528.0	513.2	509.8	506.4	510.4	514.3	522.3	530.2
55°	553.0	525.1	497.3	486.0	474.6	471.2	467.8	475.7	483.7	491.1	498.5
57.5°	504.1	479.7	455.3	445.1	434.9	434.3	433.7	441.1	448.5	456.4	464.4
60°	451.9	431.5	411.0	403.1	395.1	396.3	397.4	405.9	414.4	420.7	426.9
62.5°	404.2	387.2	370.1	362.8	355.4	358.2	361.1	369.6	378.1	385.5	392.9
65°	356.5	342.3	328.1	323.0	317.9	321.9	325.9	333.2	340.6	345.7	350.8
67.5°	311.1	299.2	287.3	283.3	279.3	283.3	287.3	294.6	302.0	307.1	312.2
70°	263.4	253.8	244.1	241.3	238.4	243.0	247.5	253.8	260.0	265.1	270.2
72.5°	219.1	211.8	204.4	203.8	203.2	207.2	211.2	217.4	223.7	227.1	230.5
75°	176.0	172.0	168.0	167.5	166.9	170.9	174.9	178.3	181.7	184.5	187.3
77.5°	137.4	134.0	130.6	131.1	131.7	134.5	137.4	140.8	144.2	145.9	147.6
80°	97.6	96.5	95.4	96.5	97.6	99.9	102.2	104.5	106.7	107.9	109.0
82.5°	67.0	65.9	64.7	66.4	68.1	69.8	71.5	73.2	74.9	75.5	76.1
85°	38.6	40.3	42.0	42.0	42.0	42.6	43.1	43.7	44.3	43.7	43.1
87.5°	18.2	18.7	19.3	19.3	19.3	19.9	20.4	20.4	20.4	19.9	19.3
90°	4.3	5.1	6.3	7.4	8.6	9.8	9.4	9.8	10.2	10.6	11.4
92.5°	20.0	27.0	39.6	60.4	80.7	72.9	54.5	38.8	30.2	26.3	23.5
95°	35.7	50.9	84.3	142.7	206.9	232.4	188.5	141.1	95.6	74.9	60.7
97.5°	41.1	58.0	90.9	158.7	266.9	357.4	369.6	324.1	244.5	192.8	148.1
100°	47.0	62.3	89.7	147.7	250.8	371.1	448.3	462.0	430.3	384.5	328.8
102.5°	53.7	67.4	91.3	138.3	227.3	345.7	452.3	507.9	514.6	492.6	462.4
105°	61.1	73.3	94.4	134.8	208.9	315.1	427.6	509.5	548.7	556.1	545.9
107.5°	69.4	80.7	99.5	134.0	195.6	288.0	392.3	486.0	547.5	578.1	588.6
110°	77.6	88.6	106.2	136.0	188.5	265.7	359.4	449.1	521.2	570.6	598.0



TEST NUMBER: P831650

CATALOG NUMBER: S123DIP-S775D365U850-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	86.2	96.8	112.9	139.9	184.6	250.8	330.8	412.7	486.7	543.6	580.8
115°	94.8	105.4	120.3	144.2	184.2	241.0	308.8	381.3	449.5	507.1	549.8
117.5°	103.5	113.3	128.2	149.7	184.6	234.4	294.3	357.0	417.4	470.3	514.6
120°	111.7	121.5	135.6	156.0	186.2	230.0	283.3	338.6	391.5	438.5	478.1
122.5°	119.1	129.7	143.4	161.9	188.9	227.3	274.3	324.1	370.7	413.5	449.5
125°	126.6	137.2	150.9	168.1	191.6	225.0	266.9	311.6	354.3	391.9	423.3
127.5°	133.6	144.2	157.5	173.2	194.8	223.8	259.8	300.2	339.0	373.5	402.5
130°	139.9	150.5	163.4	178.3	197.9	222.6	254.3	289.6	324.9	356.6	383.3
132.5°	145.8	156.0	168.5	183.0	200.3	222.2	249.2	279.8	311.6	340.6	365.6
135°	150.9	161.5	173.6	186.9	202.6	221.8	244.9	271.2	299.0	324.5	346.8
137.5°	155.6	165.4	177.1	190.1	204.2	221.0	241.0	263.0	286.5	309.2	329.2
140°	159.5	169.3	180.7	192.4	205.7	220.6	237.5	255.9	275.9	294.7	311.6
142.5°	163.4	172.4	183.4	194.8	206.9	219.9	234.4	249.2	265.7	281.4	295.5
145°	166.6	175.6	185.8	196.3	207.3	219.1	231.6	244.2	257.1	269.6	281.0
147.5°	170.5	178.3	187.7	197.5	207.3	217.9	228.9	239.8	250.4	261.0	269.2
150°	173.6	180.7	189.7	197.9	207.3	216.3	226.1	235.1	244.2	252.4	259.8
152.5°	176.7	183.4	190.9	198.7	206.1	214.4	223.0	230.8	238.3	245.3	251.2
155°	180.3	185.8	192.4	198.7	205.4	212.0	219.9	226.5	232.8	238.7	243.4
157.5°	183.4	187.7	193.2	199.1	204.2	210.1	216.3	221.8	227.3	232.0	235.9
160°	185.8	189.7	194.4	199.1	203.4	207.7	212.8	217.9	222.2	226.1	228.9
162.5°	187.7	190.9	194.8	198.7	201.8	205.4	209.3	213.2	216.7	220.2	222.6
165°	189.3	192.0	195.2	197.9	200.3	203.0	206.1	209.3	211.6	214.4	216.3
167.5°	190.9	192.8	195.2	197.5	198.7	200.7	203.0	205.7	207.7	209.3	210.8
170°	192.0	192.8	194.8	196.3	197.1	198.3	200.3	202.2	203.4	205.0	205.7
172.5°	192.8	193.2	194.8	195.9	195.9	196.3	197.5	199.1	199.9	201.0	201.4
175°	193.2	193.6	194.4	195.2	194.8	194.8	195.6	196.3	196.7	197.5	197.5
177.5°	193.6	193.6	194.0	194.8	194.0	193.6	194.0	194.4	194.8	195.2	195.2
180°	193.6	193.6	193.6	193.6	193.6	193.6	193.6	193.6	193.6	193.6	193.6



TEST NUMBER: P831650

CATALOG NUMBER: S123DIP-S775D365U850-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	2446.8	2446.8	2446.8	2446.8
2.5°	2174.9	2170.9	2155.0	2139.1
5°	1843.9	1830.3	1825.8	1821.2
7.5°	1611.2	1610.0	1586.2	1562.3
10°	1406.2	1407.9	1386.4	1364.8
12.5°	1259.8	1245.6	1243.9	1242.2
15°	1149.6	1136.6	1134.3	1132.0
17.5°	1071.8	1063.9	1061.6	1059.4
20°	1012.8	1008.3	1004.3	1000.3
22.5°	961.7	956.0	952.6	949.2
25°	912.3	907.2	906.1	904.9
27.5°	868.0	861.8	861.8	861.8
30°	826.0	822.0	820.3	818.6
32.5°	786.9	783.4	783.4	783.4
35°	749.9	748.2	746.0	743.7
37.5°	716.5	716.5	715.3	714.2
40°	684.1	685.8	685.8	685.8
42.5°	654.6	656.3	656.3	656.3
45°	623.9	626.8	627.9	629.0
47.5°	593.8	598.4	599.5	600.6
50°	564.3	567.7	568.3	568.8
52.5°	534.2	538.2	541.0	543.9
55°	502.4	506.4	508.1	509.8
57.5°	468.4	472.3	472.9	473.5
60°	430.9	434.9	436.0	437.1
62.5°	395.1	397.4	398.5	399.7
65°	354.3	357.7	359.9	362.2
67.5°	315.1	317.9	317.9	317.9
70°	271.4	272.5	274.2	275.9
72.5°	231.1	231.6	231.6	231.6
75°	188.5	189.6	190.2	190.8
77.5°	148.2	148.7	148.7	148.7
80°	108.4	107.9	107.9	107.9
82.5°	74.4	72.7	72.7	72.7
85°	42.6	42.0	42.6	43.1
87.5°	19.3	19.3	19.3	19.3
90°	11.0	11.4	11.8	11.4
92.5°	22.7	21.2	21.6	20.8
95°	53.3	49.8	47.0	45.5
97.5°	121.9	107.0	97.6	93.3
100°	289.2	260.6	245.3	245.7
102.5°	433.8	412.7	400.5	389.2
105°	527.9	513.0	500.5	498.5
107.5°	586.3	579.2	574.1	569.8
110°	609.0	612.1	611.4	610.6



TEST NUMBER: P831650

CATALOG NUMBER: S123DIP-S775D365U850-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
112.5°	603.1	614.5	618.4	618.8
115°	579.2	596.5	604.3	606.3
117.5°	545.1	564.3	576.1	578.8
120°	509.1	531.0	540.4	542.8
122.5°	476.2	495.4	505.9	509.1
125°	448.3	465.6	475.4	478.1
127.5°	425.2	440.1	449.1	451.5
130°	404.0	418.2	426.4	429.5
132.5°	384.8	399.0	406.0	408.0
135°	366.0	377.8	384.8	387.6
137.5°	345.7	357.8	363.7	366.0
140°	326.5	337.4	343.7	343.3
142.5°	307.6	317.0	322.5	322.1
145°	290.8	299.0	302.2	302.9
147.5°	277.1	283.0	286.1	286.5
150°	265.7	270.0	272.4	272.4
152.5°	255.5	259.4	260.6	260.6
155°	246.9	250.0	250.8	251.2
157.5°	239.1	241.4	242.2	242.2
160°	231.6	234.0	234.0	233.6
162.5°	224.2	226.1	226.1	225.7
165°	217.9	219.5	219.1	219.1
167.5°	211.6	212.8	212.4	212.4
170°	206.1	206.9	206.5	206.5
172.5°	201.4	202.2	201.4	201.0
175°	197.5	197.9	197.5	197.1
177.5°	194.8	195.2	194.4	194.4
180°	193.6	193.6	193.6	193.6



TEST NUMBER: P831650

CATALOG NUMBER: S123DIP-S775D365U850-4F0-1E-UDD-G4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.86	17.91	17.60	18.67	19.57	19.10	20.15	19.84	20.90	21.81
	3H	18.52	19.46	19.27	20.23	21.16	20.53	21.48	21.29	22.24	23.18
	4H	19.11	20.00	19.88	20.77	21.72	20.99	21.88	21.76	22.66	23.60
	6H	19.49	20.31	20.27	21.09	22.05	21.28	22.10	22.06	22.88	23.84
	8H	19.59	20.37	20.38	21.17	22.13	21.35	22.13	22.14	22.93	23.89
	12H	19.64	20.38	20.44	21.18	22.17	21.37	22.11	22.17	22.91	23.90
4H	2H	17.46	18.35	18.23	19.12	20.07	19.28	20.17	20.06	20.94	21.89
	3H	19.30	20.04	20.09	20.85	21.81	20.92	21.66	21.70	22.47	23.43
	4H	20.01	20.68	20.81	21.49	22.48	21.51	22.18	22.31	22.99	23.98
	6H	20.49	21.07	21.31	21.91	22.90	21.92	22.50	22.74	23.34	24.33
	8H	20.63	21.17	21.45	22.00	23.01	22.04	22.58	22.86	23.41	24.42
	12H	20.71	21.19	21.55	22.04	23.06	22.09	22.58	22.93	23.43	24.44
8H	4H	20.29	20.83	21.11	21.66	22.67	21.63	22.17	22.45	23.00	24.01
	6H	20.88	21.33	21.73	22.20	23.21	22.14	22.58	22.99	23.46	24.47
	8H	21.09	21.49	21.95	22.36	23.38	22.32	22.71	23.18	23.58	24.61
	12H	21.22	21.57	22.09	22.43	23.51	22.43	22.78	23.29	23.63	24.72
12H	4H	20.30	20.78	21.14	21.63	22.65	21.61	22.10	22.45	22.95	23.96
	6H	20.93	21.33	21.80	22.20	23.23	22.15	22.55	23.01	23.42	24.44
	8H	21.18	21.53	22.04	22.38	23.47	22.36	22.71	23.22	23.57	24.65