

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831675

Luminaire Tested: S123DIP-S775D585U850-4F0-1E-UDD-G

Issue Date: 05/03/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P831675  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-1, G3-1807-864-5)  
Test Lab: INNOVATION CENTER  
Issue Date: 05/03/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S775D585U850-4F0-1E-UDD-G  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 775 LUMENS PER FOOT, GRAZE OPTIC  
UPLIGHT 585 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6530.4 lumens  
Efficiency: N/A  
Efficacy: 158.9 lumens/watt  
Spacing Criteria (0/90/45): 0.65 / 1.19 / 0.89  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Direct  
  
Input Watts (W): 41.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P831675

CATALOG NUMBER: S123DIP-S775D585U850-4F0-1E-UDD-G

### Luminous Intensity Polar Plot





TEST NUMBER: P831675

CATALOG NUMBER: S123DIP-S775D585U850-4F0-1E-UDD-G

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	66	66	66	66	66	66	60	
1	101	97	93	89	94	90	87	84	79	77	74	69	67	65	59	58	57	57	57	57	52	
2	92	85	79	74	86	80	75	70	70	66	63	61	58	56	53	51	49	49	49	49	45	
3	85	76	68	63	79	71	65	60	63	58	54	55	51	48	47	45	42	42	42	42	39	
4	78	67	60	54	73	64	57	51	56	51	47	49	45	42	43	40	37	37	37	37	34	
5	72	61	53	47	67	57	50	45	51	45	41	45	40	37	39	36	33	33	33	33	30	
6	67	55	47	41	62	52	45	40	46	40	36	41	36	33	36	32	30	30	30	30	27	
7	62	50	42	37	58	47	40	35	42	37	32	38	33	30	33	30	27	27	27	27	24	
8	58	46	38	33	54	43	36	32	39	33	29	35	30	27	31	27	24	24	24	24	22	
9	54	42	35	30	51	40	33	29	36	30	27	32	28	24	29	25	22	22	22	22	20	
10	51	39	32	27	48	37	31	26	33	28	24	30	26	22	27	23	21	21	21	21	19	

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°	135°	180°
0°	26337	26337	26337	26337	26337
5°	33309	31437	26573	21414	19678
10°	33632	34649	26397	17070	14917
15°	25331	32169	26216	14456	12615
20°	17649	26032	25882	12641	11458
25°	13459	20018	25312	11631	10747
30°	11642	15904	24401	10916	10174
35°	10801	13428	23349	10399	9772
40°	10227	12045	21874	9908	9636
45°	9887	11149	19998	9523	9575
50°	9716	10438	17777	9173	9525
55°	9355	9918	15597	8843	9567
60°	9020	9362	13444	8531	9410
65°	8474	8835	11596	8199	9225
70°	7827	8164	9863	7648	8683
75°	7083	7320	8451	7107	7935
80°	5839	6403	6688	6192	6688
85°	4631	5187	4903	5261	5323

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 80°  
 Vertical Angle: 45°  
 Luminance: 22832 cd/sqm



TEST NUMBER: P831675

CATALOG NUMBER: S123DIP-S775D585U850-4F0-1E-UDD-G

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	231.3	3.5
10°-20°	575.5	8.8
20°-30°	681.4	10.4
30°-40°	685.1	10.5
40°-50°	628.6	9.6
50°-60°	518.8	7.9
60°-70°	367.0	5.6
70°-80°	195.9	3.0
80°-90°	51.4	0.8
90°-100°	30.0	0.5
100°-110°	145.1	2.2
110°-120°	355.7	5.4
120°-130°	451.5	6.9
130°-140°	482.4	7.4
140°-150°	451.1	6.9
150°-160°	363.8	5.6
160°-170°	234.8	3.6
170°-180°	80.9	1.2
0°-30°	1488.2	22.8
0°-40°	2173.3	33.3
0°-60°	3320.7	50.9
0°-90°	3935.1	60.3
90°-120°	530.8	8.1
90°-150°	1915.8	29.3
90°-180°	2595.0	39.7
0°-180°	6530.4	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	2447	2447	2447	2447	2447	
5°	3083	2910	2459	1982	1821	294
15°	2273	2887	2353	1297	1132	628
25°	1133	1686	2131	979	905	535
35°	822	1022	1777	791	744	517
45°	650	732	1314	626	629	503
55°	498	528	831	471	510	446
65°	333	347	455	322	362	331
75°	170	176	203	171	191	179
85°	38	42	40	43	43	42
90°	19	15	1	15	19	11
95°	24	20	39	20	24	20
105°	28	138	188	138	28	58
115°	372	363	354	363	372	350
125°	508	506	498	506	508	454
135°	627	627	620	627	627	484
145°	723	722	716	722	723	451
155°	788	788	789	788	788	363
165°	830	829	832	829	830	234
175°	848	849	851	849	848	81
180°	851	851	851	851	851	



TEST NUMBER: P831675

CATALOG NUMBER: S123DIP-S775D585U850-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2446.8	2446.8	2446.8	2446.8	2446.8	2446.8	2446.8	2446.8	2446.8	2446.8	2446.8
2.5°	2758.0	2755.1	2752.3	2738.1	2723.9	2717.1	2710.3	2689.8	2669.4	2646.7	2624.0
5°	3082.7	3090.6	3098.6	3089.5	3080.4	3052.6	3024.8	2987.9	2951.0	2909.5	2868.1
7.5°	3232.6	3237.1	3241.6	3236.0	3230.3	3222.9	3215.5	3182.6	3149.7	3107.1	3064.5
10°	3077.0	3087.2	3097.4	3119.6	3141.7	3166.7	3191.7	3187.1	3182.6	3170.1	3157.6
12.5°	2735.2	2747.7	2760.2	2804.5	2848.8	2905.6	2962.3	3011.2	3060.0	3094.0	3128.1
15°	2273.1	2307.8	2342.4	2382.7	2423.0	2506.5	2589.9	2692.7	2795.4	2886.8	2978.2
17.5°	1872.3	1885.4	1898.4	1941.6	1984.7	2089.8	2194.8	2313.4	2432.1	2583.7	2735.2
20°	1540.8	1552.7	1564.6	1621.4	1678.2	1760.5	1842.8	1976.2	2109.6	2272.6	2435.5
22.5°	1294.4	1313.1	1331.9	1363.6	1395.4	1474.4	1553.3	1671.9	1790.6	1970.5	2150.5
25°	1133.2	1146.8	1160.4	1179.7	1199.0	1262.0	1325.0	1422.7	1520.3	1685.5	1850.7
27.5°	1023.0	1028.7	1034.4	1053.7	1073.0	1113.9	1154.7	1238.8	1322.8	1463.0	1603.2
30°	936.7	940.7	944.7	961.7	978.7	1006.6	1034.4	1095.1	1155.9	1279.6	1403.4
32.5°	876.5	879.4	882.2	895.3	908.3	928.2	948.1	992.4	1036.6	1138.8	1241.0
35°	822.0	823.8	825.5	835.1	844.8	859.5	874.3	907.8	941.3	1021.9	1102.5
37.5°	774.4	776.6	778.9	784.6	790.3	803.3	816.4	843.1	869.7	931.6	993.5
40°	727.8	731.8	735.8	739.7	743.7	754.5	765.3	785.7	806.2	857.2	908.3
42.5°	688.1	692.0	696.0	697.7	699.4	705.7	711.9	730.6	749.4	787.4	825.5
45°	649.5	651.2	652.9	654.6	656.3	661.4	666.5	683.0	699.4	732.4	765.3
47.5°	614.3	614.3	614.3	615.4	616.5	621.1	625.6	637.5	649.5	675.0	700.6
50°	580.2	580.2	580.2	578.5	576.8	579.6	582.5	591.6	600.6	623.3	646.1
52.5°	539.3	539.3	539.3	539.9	540.5	540.5	540.5	548.4	556.4	576.8	597.2
55°	498.5	500.7	503.0	501.3	499.6	500.7	501.9	507.0	512.1	528.5	545.0
57.5°	457.6	458.7	459.8	459.3	458.7	459.3	459.8	464.4	468.9	481.4	493.9
60°	419.0	419.0	419.0	417.8	416.7	417.8	419.0	421.2	423.5	434.9	446.2
62.5°	375.8	376.4	377.0	377.5	378.1	377.0	375.8	378.7	381.5	390.0	398.5
65°	332.7	333.2	333.8	335.5	337.2	336.1	335.0	337.8	340.6	346.9	353.1
67.5°	294.1	292.9	291.8	292.4	292.9	294.6	296.3	296.9	297.5	304.3	311.1
70°	248.7	249.8	250.9	250.4	249.8	250.4	250.9	252.6	254.3	259.4	264.6
72.5°	207.8	208.4	208.9	208.9	208.9	210.1	211.2	212.9	214.6	217.4	220.3
75°	170.3	170.3	170.3	171.4	172.6	173.2	173.7	173.7	173.7	176.0	178.3
77.5°	129.4	132.3	135.1	134.5	134.0	135.1	136.3	138.0	139.7	140.8	141.9
80°	94.2	94.2	94.2	94.8	95.4	97.1	98.8	99.9	101.1	103.3	105.6
82.5°	60.2	60.7	61.3	63.0	64.7	65.9	67.0	68.7	70.4	70.4	70.4
85°	37.5	36.3	35.2	36.3	37.5	38.6	39.7	40.3	40.9	42.0	43.1
87.5°	18.2	18.2	18.2	18.2	18.2	18.7	19.3	19.3	19.3	19.3	19.3
90°	19.0	18.7	18.4	18.1	17.9	17.4	16.9	16.3	15.7	15.2	13.4
92.5°	21.5	21.4	21.2	21.1	20.9	20.4	19.4	18.4	17.4	16.4	15.2
95°	24.0	24.0	24.0	24.0	24.0	23.5	22.6	21.6	20.6	19.6	18.1
97.5°	25.9	25.8	25.7	25.5	25.4	24.7	23.6	22.5	21.4	20.2	27.4
100°	26.6	26.4	26.3	26.1	26.0	25.4	24.2	23.1	22.0	20.9	42.8
102.5°	27.2	26.9	26.6	26.4	26.1	28.3	32.9	37.5	42.2	46.8	71.3
105°	27.8	27.5	27.3	27.0	26.7	39.0	63.9	88.8	113.6	138.5	151.2
107.5°	65.8	84.2	102.6	121.0	139.4	159.5	181.1	202.8	224.4	246.1	243.9
110°	173.9	194.0	214.1	234.2	254.3	266.7	271.4	276.0	280.6	285.3	283.7



TEST NUMBER: P831675

CATALOG NUMBER: S123DIP-S775D585U850-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	329.5	329.8	330.1	330.4	330.7	330.2	328.9	327.6	326.4	325.1	323.6
115°	371.9	371.4	370.8	370.2	369.7	368.7	367.3	365.9	364.5	363.1	361.8
117.5°	406.1	405.9	405.8	405.7	405.5	404.9	403.8	402.6	401.5	400.4	399.7
120°	441.5	441.5	441.5	441.5	441.5	440.9	439.8	438.7	437.6	436.4	436.0
122.5°	476.3	476.2	476.0	475.9	475.7	475.3	474.6	473.9	473.2	472.5	471.9
125°	508.5	508.3	508.0	507.7	507.4	507.1	506.9	506.6	506.3	506.0	505.5
127.5°	540.2	540.5	540.7	541.0	541.3	541.2	540.8	540.4	540.0	539.5	538.8
130°	570.5	570.8	571.1	571.4	571.7	571.5	571.0	570.4	569.8	569.3	568.7
132.5°	598.4	598.8	599.2	599.6	600.1	600.0	599.4	598.9	598.3	597.7	597.3
135°	626.8	627.3	627.7	628.1	628.5	628.5	628.1	627.7	627.3	626.8	626.3
137.5°	654.0	654.3	654.6	654.9	655.2	654.9	654.2	653.5	652.8	652.1	651.9
140°	678.1	678.3	678.6	678.9	679.2	679.1	678.5	677.9	677.4	676.8	676.4
142.5°	700.2	700.6	701.0	701.5	701.9	701.9	701.5	701.0	700.6	700.2	699.8
145°	723.0	723.0	723.0	723.0	723.0	722.8	722.6	722.3	722.0	721.7	721.4
147.5°	739.4	740.1	740.8	741.5	742.2	742.4	742.2	741.9	741.6	741.3	741.0
150°	758.4	758.8	759.2	759.7	760.1	760.2	759.9	759.6	759.3	759.0	758.7
152.5°	773.6	774.3	775.0	775.7	776.4	776.5	775.9	775.3	774.8	774.2	774.1
155°	787.5	788.3	789.2	790.0	790.9	790.9	790.2	789.5	788.8	788.1	788.0
157.5°	799.5	800.6	801.8	802.9	804.0	804.1	803.3	802.5	801.6	800.8	800.9
160°	810.9	811.9	812.9	813.8	814.8	814.9	814.1	813.2	812.4	811.5	811.7
162.5°	821.6	822.5	823.3	824.2	825.0	825.0	824.0	823.0	822.0	821.0	821.2
165°	829.9	830.9	831.8	832.8	833.8	833.7	832.6	831.5	830.4	829.2	829.4
167.5°	836.2	837.3	838.4	839.6	840.7	840.7	839.6	838.4	837.3	836.2	836.2
170°	841.9	843.0	844.1	845.3	846.4	846.4	845.3	844.1	843.0	841.9	841.9
172.5°	845.1	846.3	847.6	848.8	850.1	850.2	849.1	847.9	846.8	845.7	845.5
175°	848.2	849.3	850.5	851.6	852.7	852.8	851.8	850.8	849.8	848.8	848.7
177.5°	848.8	850.3	851.7	853.1	854.5	854.6	853.5	852.4	851.2	850.1	850.0
180°	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4

TEST NUMBER: P831675

CATALOG NUMBER: S123DIP-S775D585U850-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2446.8	2446.8	2446.8	2446.8	2446.8	2446.8	2446.8	2446.8	2446.8	2446.8	2446.8
2.5°	2617.2	2610.3	2585.4	2560.4	2532.0	2503.6	2482.6	2461.6	2430.4	2399.2	2373.6
5°	2836.3	2804.5	2751.7	2698.9	2627.4	2555.8	2507.6	2459.3	2394.6	2329.9	2278.2
7.5°	3010.0	2955.5	2881.7	2807.9	2714.2	2620.6	2532.0	2443.4	2344.7	2245.9	2165.3
10°	3120.7	3083.8	2998.7	2913.5	2788.0	2662.6	2538.8	2415.1	2287.9	2160.7	2054.0
12.5°	3131.5	3134.9	3056.6	2978.2	2836.3	2694.4	2543.9	2393.5	2233.4	2073.3	1949.0
15°	3036.7	3095.2	3052.0	3008.9	2865.8	2722.8	2537.7	2352.6	2168.1	1983.6	1840.0
17.5°	2860.7	2986.2	2992.4	2998.7	2855.6	2712.5	2507.6	2302.6	2093.7	1884.8	1733.8
20°	2620.6	2805.6	2869.2	2932.8	2816.4	2700.0	2479.8	2259.5	2025.6	1791.7	1633.3
22.5°	2375.3	2600.1	2716.5	2832.9	2746.6	2660.3	2425.8	2191.4	1944.4	1697.5	1536.8
25°	2096.0	2341.3	2520.1	2698.9	2646.1	2593.3	2362.3	2131.2	1868.3	1605.5	1441.4
27.5°	1852.4	2101.7	2317.4	2533.1	2521.8	2510.4	2281.1	2051.7	1782.6	1513.5	1355.1
30°	1635.6	1867.8	2109.1	2350.3	2378.2	2406.0	2184.6	1963.2	1693.5	1423.8	1271.1
32.5°	1443.7	1646.4	1905.2	2164.1	2218.6	2273.1	2073.3	1873.5	1606.6	1339.8	1192.8
35°	1286.4	1470.4	1729.3	1988.1	2056.3	2124.4	1950.7	1776.9	1516.9	1256.9	1116.7
37.5°	1147.3	1301.2	1553.8	1806.5	1889.9	1973.4	1817.8	1662.3	1418.7	1175.2	1046.3
40°	1032.1	1155.9	1388.1	1620.3	1716.8	1813.3	1685.0	1556.7	1325.6	1094.6	975.9
42.5°	935.6	1045.7	1256.4	1467.0	1559.5	1652.0	1543.6	1435.2	1229.7	1024.2	915.7
45°	853.3	941.3	1132.6	1323.9	1411.9	1499.9	1406.8	1313.7	1132.6	951.5	850.4
47.5°	776.1	851.6	1015.1	1178.6	1256.9	1335.3	1262.6	1189.9	1036.6	883.4	792.0
50°	706.8	767.5	910.6	1053.7	1121.8	1189.9	1125.8	1061.6	935.6	809.6	730.1
52.5°	646.6	696.0	815.8	935.6	994.1	1052.5	997.5	942.4	842.5	742.6	673.3
55°	587.0	629.0	732.9	836.8	876.5	916.3	873.7	831.1	750.5	669.9	611.4
57.5°	531.4	568.8	654.0	739.2	769.8	800.5	761.9	723.3	662.5	601.8	553.0
60°	476.9	507.5	578.5	649.5	668.2	686.9	655.7	624.5	581.9	539.3	495.6
62.5°	426.4	454.2	507.0	559.8	572.3	584.7	560.9	537.1	504.7	472.3	438.3
65°	374.1	395.1	438.3	481.4	489.4	497.3	476.3	455.3	430.9	406.5	381.5
67.5°	325.9	340.6	375.8	411.0	411.6	412.2	395.1	378.1	364.5	350.8	331.0
70°	278.7	292.9	316.2	339.5	340.1	340.6	327.0	313.4	303.2	292.9	278.2
72.5°	230.5	240.7	258.3	275.9	274.8	273.6	265.1	256.6	248.7	240.7	229.9
75°	186.8	195.3	207.2	219.1	215.7	212.3	207.8	203.2	196.4	189.6	182.8
77.5°	147.0	152.1	159.0	165.8	163.5	161.2	157.3	153.3	148.2	143.1	140.2
80°	107.9	110.1	114.7	119.2	118.1	116.9	112.4	107.9	106.7	105.6	101.6
82.5°	73.2	76.1	77.2	78.3	77.8	77.2	73.8	70.4	69.3	68.1	67.6
85°	43.7	44.3	44.8	45.4	43.7	42.0	40.9	39.7	39.7	39.7	39.2
87.5°	19.9	20.4	20.4	20.4	19.9	19.3	18.2	17.0	17.6	18.2	18.2
90°	11.5	9.7	7.9	6.3	4.8	3.4	2.0	0.6	2.0	3.4	4.8
92.5°	13.9	12.7	11.4	11.2	12.0	12.9	13.7	14.5	13.7	12.9	12.0
95°	16.5	15.0	13.4	15.5	21.3	27.1	32.8	38.6	32.8	27.1	21.3
97.5°	34.6	41.7	48.9	54.5	58.4	62.3	66.3	70.2	66.3	62.3	58.4
100°	64.7	86.7	108.6	118.1	115.3	112.5	109.7	106.9	109.7	112.5	115.3
102.5°	95.7	120.2	144.6	156.0	154.1	152.3	150.5	148.6	150.5	152.3	154.1
105°	163.8	176.5	189.1	194.7	193.1	191.6	190.0	188.5	190.0	191.6	193.1
107.5°	241.8	239.7	237.6	235.9	234.7	233.4	232.1	230.9	232.1	233.4	234.7
110°	282.2	280.6	279.1	277.7	276.6	275.5	274.4	273.3	274.4	275.5	276.6





TEST NUMBER: P831675

CATALOG NUMBER: S123DIP-S775D585U850-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	322.0	320.5	318.9	317.7	316.7	315.7	314.7	313.7	314.7	315.7	316.7
115°	360.5	359.3	358.0	357.0	356.1	355.3	354.4	353.6	354.4	355.3	356.1
117.5°	399.0	398.3	397.6	396.7	395.7	394.8	393.8	392.8	393.8	394.8	395.7
120°	435.6	435.2	434.8	433.9	432.6	431.4	430.1	428.9	430.1	431.4	432.6
122.5°	471.4	470.8	470.2	469.5	468.5	467.5	466.5	465.5	466.5	467.5	468.5
125°	504.9	504.3	503.8	502.9	501.8	500.7	499.6	498.4	499.6	500.7	501.8
127.5°	538.1	537.4	536.7	535.8	534.7	533.6	532.4	531.3	532.4	533.6	534.7
130°	568.1	567.6	567.0	566.2	565.1	563.9	562.8	561.7	562.8	563.9	565.1
132.5°	596.9	596.5	596.0	595.3	594.2	593.0	591.9	590.8	591.9	593.0	594.2
135°	625.7	625.1	624.6	623.9	623.0	622.2	621.3	620.5	621.3	622.2	623.0
137.5°	651.6	651.3	651.0	650.3	649.2	648.1	646.9	645.8	646.9	648.1	649.2
140°	676.0	675.5	675.1	674.5	673.6	672.8	672.0	671.1	672.0	672.8	673.6
142.5°	699.4	698.9	698.5	697.9	697.0	696.2	695.4	694.5	695.4	696.2	697.0
145°	721.1	720.9	720.6	720.0	719.0	718.0	717.0	716.0	717.0	718.0	719.0
147.5°	740.8	740.5	740.2	739.7	739.0	738.3	737.6	736.9	737.6	738.3	739.0
150°	758.5	758.2	757.9	757.6	757.1	756.7	756.3	755.9	756.3	756.7	757.1
152.5°	773.9	773.8	773.6	773.5	773.4	773.2	773.1	772.9	773.1	773.2	773.4
155°	787.8	787.7	787.6	787.6	787.9	788.2	788.5	788.8	788.5	788.2	787.9
157.5°	801.1	801.2	801.3	801.4	801.4	801.4	801.4	801.4	801.4	801.4	801.4
160°	811.8	812.0	812.1	812.2	812.4	812.5	812.7	812.8	812.7	812.5	812.4
162.5°	821.3	821.4	821.6	821.9	822.3	822.7	823.1	823.5	823.1	822.7	822.3
165°	829.5	829.7	829.8	830.1	830.5	830.9	831.3	831.8	831.3	830.9	830.5
167.5°	836.2	836.2	836.2	836.5	837.0	837.6	838.2	838.7	838.2	837.6	837.0
170°	841.9	841.9	841.9	842.2	842.7	843.3	843.9	844.4	843.9	843.3	842.7
172.5°	845.4	845.3	845.1	845.4	846.1	846.8	847.5	848.2	847.5	846.8	846.1
175°	848.6	848.4	848.3	848.6	849.3	850.0	850.7	851.4	850.7	850.0	849.3
177.5°	849.8	849.7	849.6	849.8	850.5	851.2	851.9	852.6	851.9	851.2	850.5
180°	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4



TEST NUMBER: P831675

CATALOG NUMBER: S123DIP-S775D585U850-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2446.8	2446.8	2446.8	2446.8	2446.8	2446.8	2446.8	2446.8	2446.8	2446.8	2446.8
2.5°	2348.1	2325.9	2303.8	2286.8	2269.7	2240.8	2211.8	2205.0	2198.2	2188.5	2178.9
5°	2226.6	2172.1	2117.6	2068.7	2019.9	1981.9	1943.9	1918.9	1893.9	1875.7	1857.6
7.5°	2084.6	2002.9	1921.1	1863.2	1805.3	1750.3	1695.2	1677.6	1660.0	1636.2	1612.3
10°	1947.3	1857.0	1766.7	1691.2	1615.7	1561.8	1507.8	1486.3	1464.7	1434.6	1404.5
12.5°	1824.6	1725.8	1627.1	1551.0	1474.9	1422.7	1370.5	1339.2	1308.0	1291.0	1273.9
15°	1696.3	1590.7	1485.1	1414.7	1344.3	1297.2	1250.1	1222.9	1195.6	1179.1	1162.7
17.5°	1582.8	1478.3	1373.9	1306.3	1238.8	1195.6	1152.5	1128.6	1104.8	1092.3	1079.8
20°	1474.9	1372.7	1270.5	1204.7	1138.8	1103.6	1068.4	1053.1	1037.8	1027.6	1017.3
22.5°	1376.1	1275.7	1175.2	1119.0	1062.8	1034.4	1006.0	995.2	984.4	975.9	967.4
25°	1277.4	1187.7	1098.0	1050.3	1002.6	979.3	956.0	945.2	934.5	925.9	917.4
27.5°	1196.7	1111.0	1025.3	984.4	943.5	925.4	907.2	898.7	890.2	882.2	874.3
30°	1118.4	1041.8	965.1	929.9	894.7	878.3	861.8	853.3	844.8	837.4	830.0
32.5°	1045.7	979.9	914.0	881.7	849.3	835.7	822.0	811.8	801.6	795.9	790.3
35°	976.5	917.4	858.4	831.7	805.0	791.4	777.8	769.3	760.7	756.2	751.7
37.5°	917.4	864.6	811.8	786.3	760.7	747.7	734.6	727.2	719.9	718.2	716.5
40°	857.2	811.8	766.4	741.4	716.5	705.1	693.7	689.2	684.7	683.5	682.4
42.5°	807.3	763.0	718.7	696.0	673.3	663.7	654.0	651.7	649.5	651.2	652.9
45°	749.4	712.5	675.6	654.6	633.6	625.6	617.7	616.0	614.3	617.7	621.1
47.5°	700.6	666.5	632.4	612.6	592.7	587.0	581.3	580.8	580.2	584.7	589.3
50°	650.6	617.7	584.7	568.8	553.0	547.8	542.7	544.4	546.1	553.5	560.9
52.5°	604.0	573.4	542.7	528.0	513.2	509.8	506.4	510.4	514.3	522.3	530.2
55°	553.0	525.1	497.3	486.0	474.6	471.2	467.8	475.7	483.7	491.1	498.5
57.5°	504.1	479.7	455.3	445.1	434.9	434.3	433.7	441.1	448.5	456.4	464.4
60°	451.9	431.5	411.0	403.1	395.1	396.3	397.4	405.9	414.4	420.7	426.9
62.5°	404.2	387.2	370.1	362.8	355.4	358.2	361.1	369.6	378.1	385.5	392.9
65°	356.5	342.3	328.1	323.0	317.9	321.9	325.9	333.2	340.6	345.7	350.8
67.5°	311.1	299.2	287.3	283.3	279.3	283.3	287.3	294.6	302.0	307.1	312.2
70°	263.4	253.8	244.1	241.3	238.4	243.0	247.5	253.8	260.0	265.1	270.2
72.5°	219.1	211.8	204.4	203.8	203.2	207.2	211.2	217.4	223.7	227.1	230.5
75°	176.0	172.0	168.0	167.5	166.9	170.9	174.9	178.3	181.7	184.5	187.3
77.5°	137.4	134.0	130.6	131.1	131.7	134.5	137.4	140.8	144.2	145.9	147.6
80°	97.6	96.5	95.4	96.5	97.6	99.9	102.2	104.5	106.7	107.9	109.0
82.5°	67.0	65.9	64.7	66.4	68.1	69.8	71.5	73.2	74.9	75.5	76.1
85°	38.6	40.3	42.0	42.0	42.0	42.6	43.1	43.7	44.3	43.7	43.1
87.5°	18.2	18.7	19.3	19.3	19.3	19.9	20.4	20.4	20.4	19.9	19.3
90°	6.3	7.9	9.7	11.5	13.4	15.2	15.7	16.3	16.9	17.4	17.9
92.5°	11.2	11.4	12.7	13.9	15.2	16.4	17.4	18.4	19.4	20.4	20.9
95°	15.5	13.4	15.0	16.5	18.1	19.6	20.6	21.6	22.6	23.5	24.0
97.5°	54.5	48.9	41.7	34.6	27.4	20.2	21.4	22.5	23.6	24.7	25.4
100°	118.1	108.6	86.7	64.7	42.8	20.9	22.0	23.1	24.2	25.4	26.0
102.5°	156.0	144.6	120.2	95.7	71.3	46.8	42.2	37.5	32.9	28.3	26.1
105°	194.7	189.1	176.5	163.8	151.2	138.5	113.6	88.8	63.9	39.0	26.7
107.5°	235.9	237.6	239.7	241.8	243.9	246.1	224.4	202.8	181.1	159.5	139.4
110°	277.7	279.1	280.6	282.2	283.7	285.3	280.6	276.0	271.4	266.7	254.3



TEST NUMBER: P831675

CATALOG NUMBER: S123DIP-S775D585U850-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	317.7	318.9	320.5	322.0	323.6	325.1	326.4	327.6	328.9	330.2	330.7
115°	357.0	358.0	359.3	360.5	361.8	363.1	364.5	365.9	367.3	368.7	369.7
117.5°	396.7	397.6	398.3	399.0	399.7	400.4	401.5	402.6	403.8	404.9	405.5
120°	433.9	434.8	435.2	435.6	436.0	436.4	437.6	438.7	439.8	440.9	441.5
122.5°	469.5	470.2	470.8	471.4	471.9	472.5	473.2	473.9	474.6	475.3	475.7
125°	502.9	503.8	504.3	504.9	505.5	506.0	506.3	506.6	506.9	507.1	507.4
127.5°	535.8	536.7	537.4	538.1	538.8	539.5	540.0	540.4	540.8	541.2	541.3
130°	566.2	567.0	567.6	568.1	568.7	569.3	569.8	570.4	571.0	571.5	571.7
132.5°	595.3	596.0	596.5	596.9	597.3	597.7	598.3	598.9	599.4	600.0	600.1
135°	623.9	624.6	625.1	625.7	626.3	626.8	627.3	627.7	628.1	628.5	628.5
137.5°	650.3	651.0	651.3	651.6	651.9	652.1	652.8	653.5	654.2	654.9	655.2
140°	674.5	675.1	675.5	676.0	676.4	676.8	677.4	677.9	678.5	679.1	679.2
142.5°	697.9	698.5	698.9	699.4	699.8	700.2	700.6	701.0	701.5	701.9	701.9
145°	720.0	720.6	720.9	721.1	721.4	721.7	722.0	722.3	722.6	722.8	723.0
147.5°	739.7	740.2	740.5	740.8	741.0	741.3	741.6	741.9	742.2	742.4	742.2
150°	757.6	757.9	758.2	758.5	758.7	759.0	759.3	759.6	759.9	760.2	760.1
152.5°	773.5	773.6	773.8	773.9	774.1	774.2	774.8	775.3	775.9	776.5	776.4
155°	787.6	787.6	787.7	787.8	788.0	788.1	788.8	789.5	790.2	790.9	790.9
157.5°	801.4	801.3	801.2	801.1	800.9	800.8	801.6	802.5	803.3	804.1	804.0
160°	812.2	812.1	812.0	811.8	811.7	811.5	812.4	813.2	814.1	814.9	814.8
162.5°	821.9	821.6	821.4	821.3	821.2	821.0	822.0	823.0	824.0	825.0	825.0
165°	830.1	829.8	829.7	829.5	829.4	829.2	830.4	831.5	832.6	833.7	833.8
167.5°	836.5	836.2	836.2	836.2	836.2	836.2	837.3	838.4	839.6	840.7	840.7
170°	842.2	841.9	841.9	841.9	841.9	841.9	843.0	844.1	845.3	846.4	846.4
172.5°	845.4	845.1	845.3	845.4	845.5	845.7	846.8	847.9	849.1	850.2	850.1
175°	848.6	848.3	848.4	848.6	848.7	848.8	849.8	850.8	851.8	852.8	852.7
177.5°	849.8	849.6	849.7	849.8	850.0	850.1	851.2	852.4	853.5	854.6	854.5
180°	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4	851.4

TEST NUMBER: P831675

CATALOG NUMBER: S123DIP-S775D585U850-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
0°	2446.8	2446.8	2446.8	2446.8
2.5°	2174.9	2170.9	2155.0	2139.1
5°	1843.9	1830.3	1825.8	1821.2
7.5°	1611.2	1610.0	1586.2	1562.3
10°	1406.2	1407.9	1386.4	1364.8
12.5°	1259.8	1245.6	1243.9	1242.2
15°	1149.6	1136.6	1134.3	1132.0
17.5°	1071.8	1063.9	1061.6	1059.4
20°	1012.8	1008.3	1004.3	1000.3
22.5°	961.7	956.0	952.6	949.2
25°	912.3	907.2	906.1	904.9
27.5°	868.0	861.8	861.8	861.8
30°	826.0	822.0	820.3	818.6
32.5°	786.9	783.4	783.4	783.4
35°	749.9	748.2	746.0	743.7
37.5°	716.5	716.5	715.3	714.2
40°	684.1	685.8	685.8	685.8
42.5°	654.6	656.3	656.3	656.3
45°	623.9	626.8	627.9	629.0
47.5°	593.8	598.4	599.5	600.6
50°	564.3	567.7	568.3	568.8
52.5°	534.2	538.2	541.0	543.9
55°	502.4	506.4	508.1	509.8
57.5°	468.4	472.3	472.9	473.5
60°	430.9	434.9	436.0	437.1
62.5°	395.1	397.4	398.5	399.7
65°	354.3	357.7	359.9	362.2
67.5°	315.1	317.9	317.9	317.9
70°	271.4	272.5	274.2	275.9
72.5°	231.1	231.6	231.6	231.6
75°	188.5	189.6	190.2	190.8
77.5°	148.2	148.7	148.7	148.7
80°	108.4	107.9	107.9	107.9
82.5°	74.4	72.7	72.7	72.7
85°	42.6	42.0	42.6	43.1
87.5°	19.3	19.3	19.3	19.3
90°	18.1	18.4	18.7	19.0
92.5°	21.1	21.2	21.4	21.5
95°	24.0	24.0	24.0	24.0
97.5°	25.5	25.7	25.8	25.9
100°	26.1	26.3	26.4	26.6
102.5°	26.4	26.6	26.9	27.2
105°	27.0	27.3	27.5	27.8
107.5°	121.0	102.6	84.2	65.8
110°	234.2	214.1	194.0	173.9



TEST NUMBER: P831675

CATALOG NUMBER: S123DIP-S775D585U850-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
112.5°	330.4	330.1	329.8	329.5
115°	370.2	370.8	371.4	371.9
117.5°	405.7	405.8	405.9	406.1
120°	441.5	441.5	441.5	441.5
122.5°	475.9	476.0	476.2	476.3
125°	507.7	508.0	508.3	508.5
127.5°	541.0	540.7	540.5	540.2
130°	571.4	571.1	570.8	570.5
132.5°	599.6	599.2	598.8	598.4
135°	628.1	627.7	627.3	626.8
137.5°	654.9	654.6	654.3	654.0
140°	678.9	678.6	678.3	678.1
142.5°	701.5	701.0	700.6	700.2
145°	723.0	723.0	723.0	723.0
147.5°	741.5	740.8	740.1	739.4
150°	759.7	759.2	758.8	758.4
152.5°	775.7	775.0	774.3	773.6
155°	790.0	789.2	788.3	787.5
157.5°	802.9	801.8	800.6	799.5
160°	813.8	812.9	811.9	810.9
162.5°	824.2	823.3	822.5	821.6
165°	832.8	831.8	830.9	829.9
167.5°	839.6	838.4	837.3	836.2
170°	845.3	844.1	843.0	841.9
172.5°	848.8	847.6	846.3	845.1
175°	851.6	850.5	849.3	848.2
177.5°	853.1	851.7	850.3	848.8
180°	851.4	851.4	851.4	851.4



TEST NUMBER: P831675

CATALOG NUMBER: S123DIP-S775D585U850-4F0-1E-UDD-G

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.84	16.76	16.71	17.64	18.76	18.08	18.99	18.95	19.88	21.00
	3H	17.49	18.31	18.38	19.21	20.36	19.51	20.33	20.39	21.22	22.37
	4H	18.07	18.85	18.97	19.75	20.91	19.96	20.73	20.86	21.64	22.79
	6H	18.45	19.16	19.36	20.07	21.24	20.24	20.95	21.15	21.86	23.03
	8H	18.54	19.22	19.46	20.15	21.32	20.30	20.98	21.22	21.91	23.07
	12H	18.59	19.24	19.51	20.16	21.35	20.32	20.97	21.25	21.89	23.08
4H	2H	16.42	17.20	17.33	18.10	19.26	18.25	19.02	19.15	19.92	21.08
	3H	18.26	18.90	19.17	19.83	21.01	19.87	20.52	20.79	21.45	22.62
	4H	18.96	19.54	19.88	20.47	21.67	20.46	21.04	21.38	21.97	23.17
	6H	19.43	19.94	20.37	20.89	22.09	20.86	21.37	21.80	22.32	23.52
	8H	19.57	20.04	20.51	20.99	22.20	20.98	21.45	21.92	22.40	23.61
	12H	19.64	20.07	20.60	21.03	22.25	21.02	21.45	21.99	22.41	23.63
8H	4H	19.23	19.70	20.17	20.65	21.86	20.57	21.04	21.51	21.99	23.20
	6H	19.82	20.21	20.78	21.20	22.41	21.07	21.46	22.04	22.45	23.66
	8H	20.02	20.37	21.00	21.35	22.58	21.25	21.59	22.23	22.57	23.80
	12H	20.15	20.45	21.13	21.42	22.70	21.36	21.66	22.34	22.63	23.91
12H	4H	19.23	19.65	20.19	20.62	21.84	20.54	20.97	21.50	21.93	23.15
	6H	19.87	20.21	20.84	21.19	22.42	21.09	21.43	22.06	22.41	23.64
	8H	20.10	20.41	21.08	21.38	22.65	21.29	21.59	22.27	22.56	23.84