

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831704

Luminaire Tested: S123DIP-S775D805U850-4F0-1E-UDD-G4

Issue Date: 05/03/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P831704  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-1, G3-1807-864-17)  
Test Lab: INNOVATION CENTER  
Issue Date: 05/03/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S775D805U850-4F0-1E-UDD-G4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 775 LUMENS PER FOOT, GRAZE OPTIC  
UPLIGHT 805 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7157.6 lumens  
Efficiency: N/A  
Efficacy: 153.9 lumens/watt  
Spacing Criteria (0/90/45): 0.65 / 1.19 / 0.89  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 46.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P831704

CATALOG NUMBER: S123DIP-S775D805U850-4F0-1E-UDD-G4

### Luminous Intensity Polar Plot





TEST NUMBER: P831704

CATALOG NUMBER: S123DIP-S775D805U850-4F0-1E-UDD-G4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55				
1	99	95	92	88	92	89	86	83	76	74	72	65	63	62	55	53	52	47				
2	91	84	78	73	84	78	73	69	68	64	61	58	55	53	49	47	45	41				
3	84	74	67	62	77	70	63	58	60	56	52	52	48	45	44	41	39	35				
4	77	66	59	53	71	62	55	50	54	49	45	47	43	39	40	37	34	31				
5	71	60	52	46	66	56	49	44	49	43	39	42	38	35	36	33	31	27				
6	66	54	46	40	61	51	44	38	44	39	35	39	34	31	33	30	27	25				
7	61	49	41	36	57	46	39	34	41	35	31	35	31	28	31	27	25	22				
8	57	45	37	32	53	42	35	31	37	32	28	33	28	25	28	25	22	20				
9	53	41	34	29	49	39	32	28	34	29	25	30	26	23	26	23	21	19				
10	50	38	31	26	46	36	30	25	32	27	23	28	24	21	25	21	19	17				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°	135°	180°
0°	26337	26337	26337	26337	26337
5°	33309	31437	26573	21414	19678
10°	33632	34649	26397	17070	14917
15°	25331	32169	26216	14456	12615
20°	17649	26032	25882	12641	11458
25°	13459	20018	25312	11631	10747
30°	11642	15904	24401	10916	10174
35°	10801	13428	23349	10399	9772
40°	10227	12045	21874	9908	9636
45°	9887	11149	19998	9523	9575
50°	9716	10438	17777	9173	9525
55°	9355	9918	15597	8843	9567
60°	9020	9362	13444	8531	9410
65°	8474	8835	11596	8199	9225
70°	7827	8164	9863	7648	8683
75°	7083	7320	8451	7107	7935
80°	5839	6403	6688	6192	6688
85°	4631	5187	4903	5261	5323

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 80°  
 Vertical Angle: 45°  
 Luminance: 22832 cd/sqm



TEST NUMBER: P831704

CATALOG NUMBER: S123DIP-S775D805U850-4F0-1E-UDD-G4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	231.3	3.2
10°-20°	575.5	8.0
20°-30°	681.4	9.5
30°-40°	685.1	9.6
40°-50°	628.6	8.8
50°-60°	518.8	7.2
60°-70°	367.0	5.1
70°-80°	195.9	2.7
80°-90°	52.1	0.7
90°-100°	232.4	3.2
100°-110°	680.5	9.5
110°-120°	664.5	9.3
120°-130°	529.2	7.4
130°-140°	417.5	5.8
140°-150°	311.5	4.4
150°-160°	217.2	3.0
160°-170°	127.6	1.8
170°-180°	41.5	0.6
0°-30°	1488.2	20.8
0°-40°	2173.3	30.4
0°-60°	3320.7	46.4
0°-90°	3935.7	55.0
90°-120°	1577.4	22.0
90°-150°	2835.6	39.6
90°-180°	3222.0	45.0
0°-180°	7157.6	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	2447	2447	2447	2447	2447	
5°	3083	2910	2459	1982	1821	294
15°	2273	2887	2353	1297	1132	628
25°	1133	1686	2131	979	905	535
35°	822	1022	1777	791	744	517
45°	650	732	1314	626	629	503
55°	498	528	831	471	510	446
65°	333	347	455	322	362	331
75°	170	176	203	171	191	179
85°	38	42	40	43	43	42
90°	25	22	2	22	25	16
95°	101	514	30	514	101	163
105°	1103	697	101	697	1103	1100
115°	1341	533	178	533	1341	1308
125°	1058	498	247	498	1058	957
135°	858	491	290	491	858	665
145°	670	485	330	485	670	426
155°	556	469	375	469	556	259
165°	485	449	410	449	485	138
175°	436	431	427	431	436	42
180°	428	428	428	428	428	



TEST NUMBER: P831704

CATALOG NUMBER: S123DIP-S775D805U850-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2446.8	2446.8	2446.8	2446.8	2446.8	2446.8	2446.8	2446.8	2446.8	2446.8	2446.8
2.5°	2758.0	2755.1	2752.3	2738.1	2723.9	2717.1	2710.3	2689.8	2669.4	2646.7	2624.0
5°	3082.7	3090.6	3098.6	3089.5	3080.4	3052.6	3024.8	2987.9	2951.0	2909.5	2868.1
7.5°	3232.6	3237.1	3241.6	3236.0	3230.3	3222.9	3215.5	3182.6	3149.7	3107.1	3064.5
10°	3077.0	3087.2	3097.4	3119.6	3141.7	3166.7	3191.7	3187.1	3182.6	3170.1	3157.6
12.5°	2735.2	2747.7	2760.2	2804.5	2848.8	2905.6	2962.3	3011.2	3060.0	3094.0	3128.1
15°	2273.1	2307.8	2342.4	2382.7	2423.0	2506.5	2589.9	2692.7	2795.4	2886.8	2978.2
17.5°	1872.3	1885.4	1898.4	1941.6	1984.7	2089.8	2194.8	2313.4	2432.1	2583.7	2735.2
20°	1540.8	1552.7	1564.6	1621.4	1678.2	1760.5	1842.8	1976.2	2109.6	2272.6	2435.5
22.5°	1294.4	1313.1	1331.9	1363.6	1395.4	1474.4	1553.3	1671.9	1790.6	1970.5	2150.5
25°	1133.2	1146.8	1160.4	1179.7	1199.0	1262.0	1325.0	1422.7	1520.3	1685.5	1850.7
27.5°	1023.0	1028.7	1034.4	1053.7	1073.0	1113.9	1154.7	1238.8	1322.8	1463.0	1603.2
30°	936.7	940.7	944.7	961.7	978.7	1006.6	1034.4	1095.1	1155.9	1279.6	1403.4
32.5°	876.5	879.4	882.2	895.3	908.3	928.2	948.1	992.4	1036.6	1138.8	1241.0
35°	822.0	823.8	825.5	835.1	844.8	859.5	874.3	907.8	941.3	1021.9	1102.5
37.5°	774.4	776.6	778.9	784.6	790.3	803.3	816.4	843.1	869.7	931.6	993.5
40°	727.8	731.8	735.8	739.7	743.7	754.5	765.3	785.7	806.2	857.2	908.3
42.5°	688.1	692.0	696.0	697.7	699.4	705.7	711.9	730.6	749.4	787.4	825.5
45°	649.5	651.2	652.9	654.6	656.3	661.4	666.5	683.0	699.4	732.4	765.3
47.5°	614.3	614.3	614.3	615.4	616.5	621.1	625.6	637.5	649.5	675.0	700.6
50°	580.2	580.2	580.2	578.5	576.8	579.6	582.5	591.6	600.6	623.3	646.1
52.5°	539.3	539.3	539.3	539.9	540.5	540.5	540.5	548.4	556.4	576.8	597.2
55°	498.5	500.7	503.0	501.3	499.6	500.7	501.9	507.0	512.1	528.5	545.0
57.5°	457.6	458.7	459.8	459.3	458.7	459.3	459.8	464.4	468.9	481.4	493.9
60°	419.0	419.0	419.0	417.8	416.7	417.8	419.0	421.2	423.5	434.9	446.2
62.5°	375.8	376.4	377.0	377.5	378.1	377.0	375.8	378.7	381.5	390.0	398.5
65°	332.7	333.2	333.8	335.5	337.2	336.1	335.0	337.8	340.6	346.9	353.1
67.5°	294.1	292.9	291.8	292.4	292.9	294.6	296.3	296.9	297.5	304.3	311.1
70°	248.7	249.8	250.9	250.4	249.8	250.4	250.9	252.6	254.3	259.4	264.6
72.5°	207.8	208.4	208.9	208.9	208.9	210.1	211.2	212.9	214.6	217.4	220.3
75°	170.3	170.3	170.3	171.4	172.6	173.2	173.7	173.7	173.7	176.0	178.3
77.5°	129.4	132.3	135.1	134.5	134.0	135.1	136.3	138.0	139.7	140.8	141.9
80°	94.2	94.2	94.2	94.8	95.4	97.1	98.8	99.9	101.1	103.3	105.6
82.5°	60.2	60.7	61.3	63.0	64.7	65.9	67.0	68.7	70.4	70.4	70.4
85°	37.5	36.3	35.2	36.3	37.5	38.6	39.7	40.3	40.9	42.0	43.1
87.5°	18.2	18.2	18.2	18.2	18.2	18.7	19.3	19.3	19.3	19.3	19.3
90°	25.1	26.0	25.1	24.3	25.1	23.4	22.5	21.7	20.8	21.7	19.1
92.5°	46.0	47.7	46.8	50.3	52.0	58.1	66.8	85.8	120.5	161.3	178.6
95°	100.6	104.0	110.1	117.9	134.4	165.6	211.6	312.1	417.0	514.2	457.8
97.5°	206.4	215.9	236.7	269.6	327.7	426.6	541.0	717.0	817.6	790.7	590.5
100°	543.6	542.8	576.6	639.9	727.4	850.6	952.0	1022.2	991.9	821.1	554.9
102.5°	861.0	886.1	913.0	959.8	1023.1	1089.9	1138.4	1123.7	1000.6	764.7	502.9
105°	1102.9	1107.2	1135.0	1167.9	1207.8	1230.3	1213.9	1127.1	945.9	697.1	462.1
107.5°	1260.7	1270.2	1281.5	1297.1	1302.3	1278.9	1211.3	1075.1	867.9	637.3	432.7
110°	1350.8	1352.6	1354.3	1347.4	1323.1	1262.4	1153.2	993.6	795.1	587.9	417.0



TEST NUMBER: P831704

CATALOG NUMBER: S123DIP-S775D805U850-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1369.1	1368.2	1359.5	1334.4	1285.0	1202.6	1076.9	913.0	731.8	554.9	408.4
115°	1341.3	1337.0	1319.6	1281.5	1216.5	1121.9	994.5	843.6	683.2	533.2	407.5
117.5°	1280.6	1274.5	1248.5	1206.1	1138.4	1040.4	923.4	789.9	651.1	518.5	408.4
120°	1200.8	1195.6	1174.8	1126.3	1057.8	970.2	866.2	749.1	626.9	509.0	411.8
122.5°	1126.3	1119.3	1095.9	1053.5	994.5	914.7	820.2	717.0	606.9	502.9	417.9
125°	1057.8	1051.7	1030.0	991.9	936.4	867.0	783.8	689.3	590.5	497.7	424.0
127.5°	998.8	993.6	973.7	940.7	890.4	826.3	750.0	664.2	574.8	495.1	430.9
130°	950.3	943.3	925.1	893.9	848.0	789.0	718.8	640.7	562.7	492.5	437.9
132.5°	902.6	898.3	882.6	851.4	808.9	753.5	689.3	619.1	551.4	491.6	443.1
135°	857.5	851.4	835.8	809.8	767.3	717.9	661.6	600.0	541.9	490.7	448.3
137.5°	809.8	804.6	791.6	764.7	728.3	684.1	633.8	581.8	533.2	489.0	451.7
140°	759.5	760.4	746.5	722.2	689.3	652.0	610.4	566.2	525.4	488.1	455.2
142.5°	712.7	713.6	701.4	680.6	653.7	622.5	587.9	551.4	518.5	486.4	457.8
145°	670.2	668.5	661.6	643.3	621.7	596.5	568.8	540.2	512.4	484.7	458.7
147.5°	633.8	632.9	626.0	613.0	595.7	577.4	554.0	530.6	506.4	482.1	458.7
150°	602.6	602.6	597.4	587.9	574.8	558.4	540.2	520.2	500.3	478.6	458.7
152.5°	576.6	576.6	574.0	565.3	555.8	542.8	527.2	510.7	493.3	474.3	456.1
155°	555.8	554.9	553.2	546.2	538.4	528.0	515.0	501.1	486.4	469.1	454.3
157.5°	535.8	535.8	534.1	528.9	522.0	513.3	502.9	490.7	478.6	464.7	451.7
160°	516.8	517.6	517.6	512.4	506.4	500.3	491.6	482.1	470.8	459.5	450.0
162.5°	499.4	500.3	500.3	495.9	492.5	487.3	479.5	471.7	463.0	454.3	446.5
165°	484.7	484.7	485.5	482.1	478.6	474.3	468.2	463.0	456.1	449.1	443.1
167.5°	469.9	469.9	470.8	468.2	466.5	463.0	459.5	455.2	449.1	443.9	439.6
170°	456.9	456.9	457.8	456.1	455.2	453.5	450.0	447.4	443.1	438.7	436.1
172.5°	444.8	445.7	447.4	445.7	445.7	444.8	442.2	440.5	437.0	434.4	433.5
175°	436.1	437.0	437.9	437.0	437.0	437.0	435.3	434.4	432.7	430.9	430.9
177.5°	430.1	430.1	431.8	430.9	431.8	431.8	430.9	430.1	429.2	428.3	429.2
180°	428.3	428.3	428.3	428.3	428.3	428.3	428.3	428.3	428.3	428.3	428.3



TEST NUMBER: P831704

CATALOG NUMBER: S123DIP-S775D805U850-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2446.8	2446.8	2446.8	2446.8	2446.8	2446.8	2446.8	2446.8	2446.8	2446.8	2446.8
2.5°	2617.2	2610.3	2585.4	2560.4	2532.0	2503.6	2482.6	2461.6	2430.4	2399.2	2373.6
5°	2836.3	2804.5	2751.7	2698.9	2627.4	2555.8	2507.6	2459.3	2394.6	2329.9	2278.2
7.5°	3010.0	2955.5	2881.7	2807.9	2714.2	2620.6	2532.0	2443.4	2344.7	2245.9	2165.3
10°	3120.7	3083.8	2998.7	2913.5	2788.0	2662.6	2538.8	2415.1	2287.9	2160.7	2054.0
12.5°	3131.5	3134.9	3056.6	2978.2	2836.3	2694.4	2543.9	2393.5	2233.4	2073.3	1949.0
15°	3036.7	3095.2	3052.0	3008.9	2865.8	2722.8	2537.7	2352.6	2168.1	1983.6	1840.0
17.5°	2860.7	2986.2	2992.4	2998.7	2855.6	2712.5	2507.6	2302.6	2093.7	1884.8	1733.8
20°	2620.6	2805.6	2869.2	2932.8	2816.4	2700.0	2479.8	2259.5	2025.6	1791.7	1633.3
22.5°	2375.3	2600.1	2716.5	2832.9	2746.6	2660.3	2425.8	2191.4	1944.4	1697.5	1536.8
25°	2096.0	2341.3	2520.1	2698.9	2646.1	2593.3	2362.3	2131.2	1868.3	1605.5	1441.4
27.5°	1852.4	2101.7	2317.4	2533.1	2521.8	2510.4	2281.1	2051.7	1782.6	1513.5	1355.1
30°	1635.6	1867.8	2109.1	2350.3	2378.2	2406.0	2184.6	1963.2	1693.5	1423.8	1271.1
32.5°	1443.7	1646.4	1905.2	2164.1	2218.6	2273.1	2073.3	1873.5	1606.6	1339.8	1192.8
35°	1286.4	1470.4	1729.3	1988.1	2056.3	2124.4	1950.7	1776.9	1516.9	1256.9	1116.7
37.5°	1147.3	1301.2	1553.8	1806.5	1889.9	1973.4	1817.8	1662.3	1418.7	1175.2	1046.3
40°	1032.1	1155.9	1388.1	1620.3	1716.8	1813.3	1685.0	1556.7	1325.6	1094.6	975.9
42.5°	935.6	1045.7	1256.4	1467.0	1559.5	1652.0	1543.6	1435.2	1229.7	1024.2	915.7
45°	853.3	941.3	1132.6	1323.9	1411.9	1499.9	1406.8	1313.7	1132.6	951.5	850.4
47.5°	776.1	851.6	1015.1	1178.6	1256.9	1335.3	1262.6	1189.9	1036.6	883.4	792.0
50°	706.8	767.5	910.6	1053.7	1121.8	1189.9	1125.8	1061.6	935.6	809.6	730.1
52.5°	646.6	696.0	815.8	935.6	994.1	1052.5	997.5	942.4	842.5	742.6	673.3
55°	587.0	629.0	732.9	836.8	876.5	916.3	873.7	831.1	750.5	669.9	611.4
57.5°	531.4	568.8	654.0	739.2	769.8	800.5	761.9	723.3	662.5	601.8	553.0
60°	476.9	507.5	578.5	649.5	668.2	686.9	655.7	624.5	581.9	539.3	495.6
62.5°	426.4	454.2	507.0	559.8	572.3	584.7	560.9	537.1	504.7	472.3	438.3
65°	374.1	395.1	438.3	481.4	489.4	497.3	476.3	455.3	430.9	406.5	381.5
67.5°	325.9	340.6	375.8	411.0	411.6	412.2	395.1	378.1	364.5	350.8	331.0
70°	278.7	292.9	316.2	339.5	340.1	340.6	327.0	313.4	303.2	292.9	278.2
72.5°	230.5	240.7	258.3	275.9	274.8	273.6	265.1	256.6	248.7	240.7	229.9
75°	186.8	195.3	207.2	219.1	215.7	212.3	207.8	203.2	196.4	189.6	182.8
77.5°	147.0	152.1	159.0	165.8	163.5	161.2	157.3	153.3	148.2	143.1	140.2
80°	107.9	110.1	114.7	119.2	118.1	116.9	112.4	107.9	106.7	105.6	101.6
82.5°	73.2	76.1	77.2	78.3	77.8	77.2	73.8	70.4	69.3	68.1	67.6
85°	43.7	44.3	44.8	45.4	43.7	42.0	40.9	39.7	39.7	39.7	39.2
87.5°	19.9	20.4	20.4	20.4	19.9	19.3	18.2	17.0	17.6	18.2	18.2
90°	16.5	13.9	11.3	9.5	7.8	5.2	3.5	1.7	3.5	5.2	7.8
92.5°	133.5	87.6	59.8	44.2	35.5	27.7	19.1	13.0	19.1	27.7	35.5
95°	315.6	186.4	112.7	78.9	56.4	41.6	32.1	29.5	32.1	41.6	56.4
97.5°	351.2	201.2	128.3	91.0	68.5	55.5	47.7	46.8	47.7	55.5	68.5
100°	326.9	198.6	137.9	104.0	83.2	71.1	65.0	64.2	65.0	71.1	83.2
102.5°	306.1	202.0	149.1	118.8	100.6	89.3	84.1	82.4	84.1	89.3	100.6
105°	298.3	209.0	162.1	135.3	118.8	108.4	103.2	100.6	103.2	108.4	118.8
107.5°	296.5	220.2	178.6	153.5	137.9	127.5	122.3	119.7	122.3	127.5	137.9
110°	300.9	235.0	196.0	171.7	156.9	147.4	143.1	140.5	143.1	147.4	156.9





TEST NUMBER: P831704

CATALOG NUMBER: S123DIP-S775D805U850-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	309.5	249.7	214.2	190.7	176.0	166.5	162.1	159.5	162.1	166.5	176.0
115°	319.1	266.2	233.2	209.8	195.1	186.4	181.2	177.7	181.2	186.4	195.1
117.5°	331.2	283.5	250.6	228.9	212.4	204.6	200.3	196.0	200.3	204.6	212.4
120°	345.1	300.0	268.8	247.1	230.6	222.0	217.6	215.0	217.6	222.0	230.6
122.5°	358.1	317.3	287.0	263.6	248.0	238.4	234.1	231.5	234.1	238.4	248.0
125°	372.0	333.8	303.5	280.1	263.6	254.0	248.8	247.1	248.8	254.0	263.6
127.5°	383.2	348.5	319.1	295.7	277.5	267.9	261.8	259.2	261.8	267.9	277.5
130°	394.5	361.6	332.9	309.5	291.3	280.9	273.1	270.5	273.1	280.9	291.3
132.5°	404.9	372.8	345.1	322.5	304.3	291.3	282.7	279.2	282.7	291.3	304.3
135°	413.6	384.1	357.2	333.8	315.6	302.6	293.1	289.6	293.1	302.6	315.6
137.5°	420.5	391.9	365.9	344.2	326.0	312.1	302.6	299.1	302.6	312.1	326.0
140°	425.7	399.7	374.6	352.9	335.5	321.7	313.0	308.7	313.0	321.7	335.5
142.5°	430.9	405.8	381.5	361.6	344.2	332.1	322.5	319.1	322.5	332.1	344.2
145°	434.4	411.0	388.4	368.5	353.8	340.7	332.9	330.3	332.9	340.7	353.8
147.5°	437.0	415.3	394.5	377.2	362.4	351.2	343.3	341.6	343.3	351.2	362.4
150°	437.9	419.6	399.7	384.1	372.0	360.7	353.8	352.9	353.8	360.7	372.0
152.5°	439.6	422.2	405.8	391.0	380.6	371.1	364.2	364.2	364.2	371.1	380.6
155°	439.6	425.7	411.0	398.8	389.3	380.6	375.4	375.4	375.4	380.6	389.3
157.5°	440.5	427.4	415.3	405.8	397.1	389.3	385.0	384.1	385.0	389.3	397.1
160°	440.5	430.1	419.6	411.0	404.9	398.0	394.5	394.5	394.5	398.0	404.9
162.5°	439.6	430.9	422.2	415.3	410.1	404.9	402.3	402.3	402.3	404.9	410.1
165°	437.9	431.8	424.8	418.8	415.3	411.0	409.2	410.1	409.2	411.0	415.3
167.5°	437.0	431.8	426.6	422.2	419.6	416.2	415.3	416.2	415.3	416.2	419.6
170°	434.4	430.9	426.6	424.8	423.1	420.5	419.6	421.4	419.6	420.5	423.1
172.5°	433.5	430.9	427.4	426.6	425.7	424.0	424.0	424.8	424.0	424.0	425.7
175°	431.8	430.1	428.3	427.4	427.4	425.7	426.6	427.4	426.6	425.7	427.4
177.5°	430.9	429.2	428.3	428.3	428.3	427.4	428.3	429.2	428.3	427.4	428.3
180°	428.3	428.3	428.3	428.3	428.3	428.3	428.3	428.3	428.3	428.3	428.3



TEST NUMBER: P831704

CATALOG NUMBER: S123DIP-S775D805U850-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2446.8	2446.8	2446.8	2446.8	2446.8	2446.8	2446.8	2446.8	2446.8	2446.8	2446.8
2.5°	2348.1	2325.9	2303.8	2286.8	2269.7	2240.8	2211.8	2205.0	2198.2	2188.5	2178.9
5°	2226.6	2172.1	2117.6	2068.7	2019.9	1981.9	1943.9	1918.9	1893.9	1875.7	1857.6
7.5°	2084.6	2002.9	1921.1	1863.2	1805.3	1750.3	1695.2	1677.6	1660.0	1636.2	1612.3
10°	1947.3	1857.0	1766.7	1691.2	1615.7	1561.8	1507.8	1486.3	1464.7	1434.6	1404.5
12.5°	1824.6	1725.8	1627.1	1551.0	1474.9	1422.7	1370.5	1339.2	1308.0	1291.0	1273.9
15°	1696.3	1590.7	1485.1	1414.7	1344.3	1297.2	1250.1	1222.9	1195.6	1179.1	1162.7
17.5°	1582.8	1478.3	1373.9	1306.3	1238.8	1195.6	1152.5	1128.6	1104.8	1092.3	1079.8
20°	1474.9	1372.7	1270.5	1204.7	1138.8	1103.6	1068.4	1053.1	1037.8	1027.6	1017.3
22.5°	1376.1	1275.7	1175.2	1119.0	1062.8	1034.4	1006.0	995.2	984.4	975.9	967.4
25°	1277.4	1187.7	1098.0	1050.3	1002.6	979.3	956.0	945.2	934.5	925.9	917.4
27.5°	1196.7	1111.0	1025.3	984.4	943.5	925.4	907.2	898.7	890.2	882.2	874.3
30°	1118.4	1041.8	965.1	929.9	894.7	878.3	861.8	853.3	844.8	837.4	830.0
32.5°	1045.7	979.9	914.0	881.7	849.3	835.7	822.0	811.8	801.6	795.9	790.3
35°	976.5	917.4	858.4	831.7	805.0	791.4	777.8	769.3	760.7	756.2	751.7
37.5°	917.4	864.6	811.8	786.3	760.7	747.7	734.6	727.2	719.9	718.2	716.5
40°	857.2	811.8	766.4	741.4	716.5	705.1	693.7	689.2	684.7	683.5	682.4
42.5°	807.3	763.0	718.7	696.0	673.3	663.7	654.0	651.7	649.5	651.2	652.9
45°	749.4	712.5	675.6	654.6	633.6	625.6	617.7	616.0	614.3	617.7	621.1
47.5°	700.6	666.5	632.4	612.6	592.7	587.0	581.3	580.8	580.2	584.7	589.3
50°	650.6	617.7	584.7	568.8	553.0	547.8	542.7	544.4	546.1	553.5	560.9
52.5°	604.0	573.4	542.7	528.0	513.2	509.8	506.4	510.4	514.3	522.3	530.2
55°	553.0	525.1	497.3	486.0	474.6	471.2	467.8	475.7	483.7	491.1	498.5
57.5°	504.1	479.7	455.3	445.1	434.9	434.3	433.7	441.1	448.5	456.4	464.4
60°	451.9	431.5	411.0	403.1	395.1	396.3	397.4	405.9	414.4	420.7	426.9
62.5°	404.2	387.2	370.1	362.8	355.4	358.2	361.1	369.6	378.1	385.5	392.9
65°	356.5	342.3	328.1	323.0	317.9	321.9	325.9	333.2	340.6	345.7	350.8
67.5°	311.1	299.2	287.3	283.3	279.3	283.3	287.3	294.6	302.0	307.1	312.2
70°	263.4	253.8	244.1	241.3	238.4	243.0	247.5	253.8	260.0	265.1	270.2
72.5°	219.1	211.8	204.4	203.8	203.2	207.2	211.2	217.4	223.7	227.1	230.5
75°	176.0	172.0	168.0	167.5	166.9	170.9	174.9	178.3	181.7	184.5	187.3
77.5°	137.4	134.0	130.6	131.1	131.7	134.5	137.4	140.8	144.2	145.9	147.6
80°	97.6	96.5	95.4	96.5	97.6	99.9	102.2	104.5	106.7	107.9	109.0
82.5°	67.0	65.9	64.7	66.4	68.1	69.8	71.5	73.2	74.9	75.5	76.1
85°	38.6	40.3	42.0	42.0	42.0	42.6	43.1	43.7	44.3	43.7	43.1
87.5°	18.2	18.7	19.3	19.3	19.3	19.9	20.4	20.4	20.4	19.9	19.3
90°	9.5	11.3	13.9	16.5	19.1	21.7	20.8	21.7	22.5	23.4	25.1
92.5°	44.2	59.8	87.6	133.5	178.6	161.3	120.5	85.8	66.8	58.1	52.0
95°	78.9	112.7	186.4	315.6	457.8	514.2	417.0	312.1	211.6	165.6	134.4
97.5°	91.0	128.3	201.2	351.2	590.5	790.7	817.6	717.0	541.0	426.6	327.7
100°	104.0	137.9	198.6	326.9	554.9	821.1	991.9	1022.2	952.0	850.6	727.4
102.5°	118.8	149.1	202.0	306.1	502.9	764.7	1000.6	1123.7	1138.4	1089.9	1023.1
105°	135.3	162.1	209.0	298.3	462.1	697.1	945.9	1127.1	1213.9	1230.3	1207.8
107.5°	153.5	178.6	220.2	296.5	432.7	637.3	867.9	1075.1	1211.3	1278.9	1302.3
110°	171.7	196.0	235.0	300.9	417.0	587.9	795.1	993.6	1153.2	1262.4	1323.1



TEST NUMBER: P831704

CATALOG NUMBER: S123DIP-S775D805U850-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	190.7	214.2	249.7	309.5	408.4	554.9	731.8	913.0	1076.9	1202.6	1285.0
115°	209.8	233.2	266.2	319.1	407.5	533.2	683.2	843.6	994.5	1121.9	1216.5
117.5°	228.9	250.6	283.5	331.2	408.4	518.5	651.1	789.9	923.4	1040.4	1138.4
120°	247.1	268.8	300.0	345.1	411.8	509.0	626.9	749.1	866.2	970.2	1057.8
122.5°	263.6	287.0	317.3	358.1	417.9	502.9	606.9	717.0	820.2	914.7	994.5
125°	280.1	303.5	333.8	372.0	424.0	497.7	590.5	689.3	783.8	867.0	936.4
127.5°	295.7	319.1	348.5	383.2	430.9	495.1	574.8	664.2	750.0	826.3	890.4
130°	309.5	332.9	361.6	394.5	437.9	492.5	562.7	640.7	718.8	789.0	848.0
132.5°	322.5	345.1	372.8	404.9	443.1	491.6	551.4	619.1	689.3	753.5	808.9
135°	333.8	357.2	384.1	413.6	448.3	490.7	541.9	600.0	661.6	717.9	767.3
137.5°	344.2	365.9	391.9	420.5	451.7	489.0	533.2	581.8	633.8	684.1	728.3
140°	352.9	374.6	399.7	425.7	455.2	488.1	525.4	566.2	610.4	652.0	689.3
142.5°	361.6	381.5	405.8	430.9	457.8	486.4	518.5	551.4	587.9	622.5	653.7
145°	368.5	388.4	411.0	434.4	458.7	484.7	512.4	540.2	568.8	596.5	621.7
147.5°	377.2	394.5	415.3	437.0	458.7	482.1	506.4	530.6	554.0	577.4	595.7
150°	384.1	399.7	419.6	437.9	458.7	478.6	500.3	520.2	540.2	558.4	574.8
152.5°	391.0	405.8	422.2	439.6	456.1	474.3	493.3	510.7	527.2	542.8	555.8
155°	398.8	411.0	425.7	439.6	454.3	469.1	486.4	501.1	515.0	528.0	538.4
157.5°	405.8	415.3	427.4	440.5	451.7	464.7	478.6	490.7	502.9	513.3	522.0
160°	411.0	419.6	430.1	440.5	450.0	459.5	470.8	482.1	491.6	500.3	506.4
162.5°	415.3	422.2	430.9	439.6	446.5	454.3	463.0	471.7	479.5	487.3	492.5
165°	418.8	424.8	431.8	437.9	443.1	449.1	456.1	463.0	468.2	474.3	478.6
167.5°	422.2	426.6	431.8	437.0	439.6	443.9	449.1	455.2	459.5	463.0	466.5
170°	424.8	426.6	430.9	434.4	436.1	438.7	443.1	447.4	450.0	453.5	455.2
172.5°	426.6	427.4	430.9	433.5	433.5	434.4	437.0	440.5	442.2	444.8	445.7
175°	427.4	428.3	430.1	431.8	430.9	430.9	432.7	434.4	435.3	437.0	437.0
177.5°	428.3	428.3	429.2	430.9	429.2	428.3	429.2	430.1	430.9	431.8	431.8
180°	428.3	428.3	428.3	428.3	428.3	428.3	428.3	428.3	428.3	428.3	428.3



TEST NUMBER: P831704

CATALOG NUMBER: S123DIP-S775D805U850-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
0°	2446.8	2446.8	2446.8	2446.8
2.5°	2174.9	2170.9	2155.0	2139.1
5°	1843.9	1830.3	1825.8	1821.2
7.5°	1611.2	1610.0	1586.2	1562.3
10°	1406.2	1407.9	1386.4	1364.8
12.5°	1259.8	1245.6	1243.9	1242.2
15°	1149.6	1136.6	1134.3	1132.0
17.5°	1071.8	1063.9	1061.6	1059.4
20°	1012.8	1008.3	1004.3	1000.3
22.5°	961.7	956.0	952.6	949.2
25°	912.3	907.2	906.1	904.9
27.5°	868.0	861.8	861.8	861.8
30°	826.0	822.0	820.3	818.6
32.5°	786.9	783.4	783.4	783.4
35°	749.9	748.2	746.0	743.7
37.5°	716.5	716.5	715.3	714.2
40°	684.1	685.8	685.8	685.8
42.5°	654.6	656.3	656.3	656.3
45°	623.9	626.8	627.9	629.0
47.5°	593.8	598.4	599.5	600.6
50°	564.3	567.7	568.3	568.8
52.5°	534.2	538.2	541.0	543.9
55°	502.4	506.4	508.1	509.8
57.5°	468.4	472.3	472.9	473.5
60°	430.9	434.9	436.0	437.1
62.5°	395.1	397.4	398.5	399.7
65°	354.3	357.7	359.9	362.2
67.5°	315.1	317.9	317.9	317.9
70°	271.4	272.5	274.2	275.9
72.5°	231.1	231.6	231.6	231.6
75°	188.5	189.6	190.2	190.8
77.5°	148.2	148.7	148.7	148.7
80°	108.4	107.9	107.9	107.9
82.5°	74.4	72.7	72.7	72.7
85°	42.6	42.0	42.6	43.1
87.5°	19.3	19.3	19.3	19.3
90°	24.3	25.1	26.0	25.1
92.5°	50.3	46.8	47.7	46.0
95°	117.9	110.1	104.0	100.6
97.5°	269.6	236.7	215.9	206.4
100°	639.9	576.6	542.8	543.6
102.5°	959.8	913.0	886.1	861.0
105°	1167.9	1135.0	1107.2	1102.9
107.5°	1297.1	1281.5	1270.2	1260.7
110°	1347.4	1354.3	1352.6	1350.8



TEST NUMBER: P831704

CATALOG NUMBER: S123DIP-S775D805U850-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
112.5°	1334.4	1359.5	1368.2	1369.1
115°	1281.5	1319.6	1337.0	1341.3
117.5°	1206.1	1248.5	1274.5	1280.6
120°	1126.3	1174.8	1195.6	1200.8
122.5°	1053.5	1095.9	1119.3	1126.3
125°	991.9	1030.0	1051.7	1057.8
127.5°	940.7	973.7	993.6	998.8
130°	893.9	925.1	943.3	950.3
132.5°	851.4	882.6	898.3	902.6
135°	809.8	835.8	851.4	857.5
137.5°	764.7	791.6	804.6	809.8
140°	722.2	746.5	760.4	759.5
142.5°	680.6	701.4	713.6	712.7
145°	643.3	661.6	668.5	670.2
147.5°	613.0	626.0	632.9	633.8
150°	587.9	597.4	602.6	602.6
152.5°	565.3	574.0	576.6	576.6
155°	546.2	553.2	554.9	555.8
157.5°	528.9	534.1	535.8	535.8
160°	512.4	517.6	517.6	516.8
162.5°	495.9	500.3	500.3	499.4
165°	482.1	485.5	484.7	484.7
167.5°	468.2	470.8	469.9	469.9
170°	456.1	457.8	456.9	456.9
172.5°	445.7	447.4	445.7	444.8
175°	437.0	437.9	437.0	436.1
177.5°	430.9	431.8	430.1	430.1
180°	428.3	428.3	428.3	428.3



TEST NUMBER: P831704

CATALOG NUMBER: S123DIP-S775D805U850-4F0-1E-UDD-G4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.39	16.25	16.31	17.19	18.39	17.62	18.49	18.54	19.42	20.63
	3H	17.03	17.81	17.97	18.75	19.98	19.05	19.82	19.98	20.77	21.99
	4H	17.61	18.35	18.56	19.29	20.53	19.50	20.23	20.45	21.18	22.42
	6H	17.98	18.66	18.94	19.61	20.86	19.77	20.45	20.73	21.40	22.65
	8H	18.08	18.72	19.04	19.69	20.94	19.84	20.48	20.80	21.45	22.70
	12H	18.12	18.74	19.09	19.70	20.97	19.86	20.47	20.83	21.43	22.70
4H	2H	15.96	16.70	16.92	17.64	18.88	17.79	18.52	18.74	19.47	20.70
	3H	17.79	18.40	18.75	19.38	20.63	19.41	20.02	20.37	21.00	22.24
	4H	18.49	19.05	19.46	20.02	21.29	19.99	20.55	20.96	21.52	22.79
	6H	18.97	19.45	19.95	20.44	21.71	20.40	20.88	21.38	21.87	23.14
	8H	19.10	19.55	20.09	20.54	21.82	20.51	20.96	21.49	21.94	23.23
	12H	19.17	19.57	20.17	20.58	21.87	20.55	20.96	21.56	21.96	23.25
8H	4H	18.76	19.20	19.74	20.19	21.48	20.10	20.54	21.08	21.53	22.82
	6H	19.35	19.71	20.36	20.75	22.03	20.60	20.97	21.61	22.00	23.28
	8H	19.55	19.88	20.57	20.90	22.20	20.78	21.10	21.80	22.12	23.43
	12H	19.68	19.96	20.70	20.97	22.32	20.88	21.17	21.90	22.18	23.53
12H	4H	18.76	19.16	19.76	20.17	21.46	20.07	20.48	21.08	21.48	22.77
	6H	19.40	19.72	20.41	20.74	22.04	20.61	20.94	21.63	21.96	23.26
	8H	19.63	19.92	20.65	20.93	22.28	20.81	21.10	21.84	22.11	23.46