

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831857

Luminaire Tested: S123RDIP-S1000D585U850-4F0-1E-UDD-G4

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P831857
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-2, G3-1807-864-17)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1000D585U850-4F0-1E-UDD-G4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, GRAZE OPTIC
UPLIGHT 585 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7123.6 lumens
Efficiency: N/A
Efficacy: 141.6 lumens/watt
Spacing Criteria (0/90/45): 0.55 / 1.17 / 0.8
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 50.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P831857

CATALOG NUMBER: S123RDIP-S1000D585U850-4F0-1E-UDD-G4

Luminous Intensity Polar Plot





TEST NUMBER: P831857

CATALOG NUMBER: S123RDIP-S1000D585U850-4F0-1E-UDD-G4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	67				
1	103	99	95	92	97	93	90	87	83	81	79	74	72	70	65	64	63	59				
2	94	87	82	77	89	83	78	73	74	70	67	66	63	61	59	56	55	51				
3	87	78	71	66	82	74	68	63	67	62	58	60	56	53	53	50	48	45				
4	80	70	63	57	76	67	60	55	60	55	50	54	50	46	48	45	42	39				
5	74	63	56	50	70	60	53	48	55	49	45	49	45	41	44	41	38	35				
6	69	57	50	44	65	55	48	43	50	44	40	45	41	37	41	37	34	32				
7	64	53	45	40	61	50	43	38	46	40	36	42	37	33	38	34	31	29				
8	60	48	41	36	57	46	39	35	42	37	33	39	34	30	35	31	28	26				
9	56	45	37	32	53	43	36	32	39	34	30	36	31	28	33	29	26	24				
10	53	41	34	30	50	40	33	29	37	31	27	34	29	26	31	27	24	22				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	38736	38736	38736	38736	38736
5°	45995	44529	38980	31511	29255
10°	41673	45228	38786	25247	21659
15°	28691	38780	38376	20635	17133
20°	19961	29857	37606	17400	15060
25°	15210	22755	36485	15465	13879
30°	13241	18192	35082	14359	12855
35°	12156	15347	33097	13427	11924
40°	11092	13704	30498	12513	11071
45°	10018	12533	27694	11645	10219
50°	9093	11563	24387	10798	9167
55°	8223	10620	21210	9969	7863
60°	7369	9655	18424	9052	7434
65°	6803	8568	15860	8135	7027
70°	5526	7405	13838	7361	5712
75°	4849	5889	11720	6105	5032
80°	4389	4984	9602	5120	4754
85°	4014	4372	7287	4644	4372

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 29221 cd/sqm



TEST NUMBER: P831857

CATALOG NUMBER: S123RDIP-S1000D585U850-4F0-1E-UDD-G4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	328.0	4.6
10°-20°	759.0	10.7
20°-30°	870.9	12.2
30°-40°	858.4	12.0
40°-50°	757.0	10.6
50°-60°	582.4	8.2
60°-70°	382.9	5.4
70°-80°	185.9	2.6
80°-90°	48.6	0.7
90°-100°	169.6	2.4
100°-110°	496.4	7.0
110°-120°	484.8	6.8
120°-130°	386.1	5.4
130°-140°	304.6	4.3
140°-150°	227.2	3.2
150°-160°	158.4	2.2
160°-170°	93.1	1.3
170°-180°	30.3	0.4
0°-30°	1957.9	27.5
0°-40°	2816.3	39.5
0°-60°	4155.7	58.3
0°-90°	4773.1	67.0
90°-120°	1150.8	16.2
90°-150°	2068.7	29.0
90°-180°	2350.0	33.0
0°-180°	7123.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	3599	3599	3599	3599	3599	
5°	4257	4121	3608	2916	2708	389
15°	2575	3480	3444	1852	1538	727
25°	1281	1916	3072	1302	1169	605
35°	925	1168	2519	1022	907	577
45°	658	823	1819	765	671	511
55°	438	566	1130	531	419	393
65°	267	336	623	319	276	262
75°	117	142	282	147	121	125
85°	32	35	59	38	35	35
90°	18	16	1	16	18	12
95°	73	375	22	375	73	119
105°	805	509	73	509	805	803
115°	978	389	130	389	978	954
125°	772	363	180	363	772	698
135°	626	358	211	358	626	485
145°	489	354	241	354	489	311
155°	406	342	274	342	406	189
165°	354	328	299	328	354	101
175°	318	314	312	314	318	31
180°	312	312	312	312	312	



TEST NUMBER: P831857

CATALOG NUMBER: S123RDIP-S1000D585U850-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	3598.7	3598.7	3598.7	3598.7	3598.7	3598.7	3598.7	3598.7	3598.7	3598.7	3598.7
2.5°	3988.3	3975.7	3963.2	3959.5	3955.8	3944.0	3932.2	3905.6	3879.1	3851.8	3824.5
5°	4256.8	4258.3	4259.7	4256.1	4252.4	4236.9	4221.4	4188.9	4156.5	4121.1	4085.6
7.5°	4174.2	4197.8	4221.4	4225.8	4230.2	4242.0	4253.8	4246.5	4239.1	4225.8	4212.5
10°	3812.7	3811.2	3809.7	3836.3	3862.8	3941.8	4020.7	4061.3	4101.9	4138.0	4174.2
12.5°	3222.5	3224.7	3226.9	3314.0	3401.0	3475.5	3550.0	3653.3	3756.6	3868.0	3979.4
15°	2574.7	2610.9	2647.0	2724.5	2802.0	2914.1	3026.2	3164.9	3303.6	3480.0	3656.3
17.5°	2114.4	2129.9	2145.4	2219.9	2294.4	2400.6	2506.9	2664.0	2821.1	3048.4	3275.6
20°	1742.6	1756.6	1770.6	1824.4	1878.3	1980.1	2081.9	2231.7	2381.4	2606.5	2831.5
22.5°	1454.8	1482.1	1509.4	1545.6	1581.7	1655.5	1729.3	1882.0	2034.7	2239.8	2444.9
25°	1280.7	1293.3	1305.8	1336.8	1367.8	1438.6	1509.4	1610.5	1711.6	1915.9	2120.3
27.5°	1162.7	1166.4	1170.1	1192.9	1215.8	1261.5	1307.3	1401.0	1494.7	1662.9	1831.1
30°	1065.3	1071.9	1078.6	1096.3	1114.0	1147.2	1180.4	1246.8	1313.2	1463.7	1614.2
32.5°	990.1	993.7	997.4	1012.2	1026.9	1051.3	1075.6	1128.0	1180.4	1295.5	1410.6
35°	925.1	925.9	926.6	937.7	948.7	972.4	996.0	1039.5	1083.0	1167.9	1252.7
37.5°	851.4	856.5	861.7	869.8	877.9	898.6	919.2	954.6	990.1	1060.1	1130.2
40°	789.4	793.8	798.2	807.8	817.4	833.7	849.9	882.3	914.8	975.3	1035.8
42.5°	727.4	730.4	733.3	742.9	752.5	772.4	792.3	818.2	844.0	894.1	944.3
45°	658.1	665.4	672.8	683.2	693.5	710.4	727.4	754.0	780.5	823.3	866.1
47.5°	600.5	604.2	607.9	616.8	625.6	646.3	666.9	690.5	714.1	754.0	793.8
50°	543.0	544.5	545.9	554.0	562.2	580.6	599.1	626.3	653.6	690.5	727.4
52.5°	488.4	492.1	495.8	503.9	512.0	524.5	537.1	565.1	593.1	629.3	665.4
55°	438.2	440.4	442.6	448.5	454.5	469.2	484.0	508.3	532.7	565.9	599.1
57.5°	391.0	394.0	396.9	401.3	405.8	419.0	432.3	453.7	475.1	508.3	541.5
60°	342.3	346.0	349.7	354.9	360.0	370.3	380.7	399.9	419.0	448.5	478.1
62.5°	306.9	307.6	308.4	312.8	317.2	324.6	332.0	347.5	363.0	392.5	422.0
65°	267.1	269.3	271.5	273.7	275.9	281.8	287.7	301.0	314.3	336.4	358.5
67.5°	225.8	228.0	230.2	233.9	237.6	242.7	247.9	256.7	265.6	286.2	306.9
70°	175.6	175.6	175.6	181.5	187.4	196.2	205.1	211.7	218.4	235.3	252.3
72.5°	143.1	143.9	144.6	145.3	146.1	151.2	156.4	167.5	178.5	188.9	199.2
75°	116.6	117.3	118.0	118.8	119.5	121.0	122.5	126.2	129.8	141.6	153.5
77.5°	93.0	93.7	94.4	95.2	95.9	97.4	98.9	100.3	101.8	106.2	110.7
80°	70.8	71.6	72.3	73.0	73.8	74.5	75.3	76.7	78.2	80.4	82.6
82.5°	51.6	51.6	51.6	51.6	51.6	53.1	54.6	54.6	54.6	56.1	57.5
85°	32.5	32.5	32.5	33.2	33.9	33.9	33.9	34.7	35.4	35.4	35.4
87.5°	14.8	14.0	13.3	14.0	14.8	14.8	14.8	15.5	16.2	16.2	16.2
90°	18.3	19.0	18.3	17.7	18.3	17.1	16.4	15.8	15.2	15.8	13.9
92.5°	33.5	34.8	34.2	36.7	38.0	42.4	48.7	62.6	87.9	117.7	130.3
95°	73.4	75.9	80.3	86.0	98.0	120.8	154.3	227.7	304.3	375.1	334.0
97.5°	150.5	157.5	172.7	196.7	239.1	311.2	394.7	523.1	596.5	576.9	430.8
100°	396.6	396.0	420.6	466.8	530.7	620.5	694.5	745.8	723.6	599.0	404.8
102.5°	628.1	646.5	666.1	700.2	746.4	795.1	830.5	819.8	730.0	557.9	366.9
105°	804.6	807.8	828.0	852.0	881.1	897.6	885.6	822.3	690.1	508.6	337.1
107.5°	919.7	926.7	934.9	946.3	950.1	933.0	883.7	784.4	633.2	464.9	315.6
110°	985.5	986.8	988.0	983.0	965.3	921.0	841.3	724.9	580.0	428.9	304.3



TEST NUMBER: P831857

CATALOG NUMBER: S123RDIP-S1000D585U850-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	998.8	998.2	991.8	973.5	937.4	877.3	785.6	666.1	533.9	404.8	297.9
115°	978.5	975.4	962.7	934.9	887.5	818.5	725.5	615.5	498.4	389.0	297.3
117.5°	934.3	929.8	910.9	879.9	830.5	759.1	673.7	576.2	475.0	378.3	297.9
120°	876.1	872.3	857.1	821.7	771.7	707.8	631.9	546.5	457.3	371.3	300.5
122.5°	821.7	816.6	799.5	768.5	725.5	667.3	598.4	523.1	442.8	366.9	304.9
125°	771.7	767.3	751.5	723.6	683.1	632.5	571.8	502.9	430.8	363.1	309.3
127.5°	728.7	724.9	710.3	686.3	649.6	602.8	547.2	484.5	419.4	361.2	314.4
130°	693.3	688.2	674.9	652.2	618.6	575.6	524.4	467.5	410.5	359.3	319.4
132.5°	658.5	655.3	643.9	621.2	590.2	549.7	502.9	451.6	402.3	358.7	323.2
135°	625.6	621.2	609.8	590.8	559.8	523.7	482.6	437.7	395.3	358.0	327.0
137.5°	590.8	587.0	577.5	557.9	531.3	499.1	462.4	424.4	389.0	356.8	329.6
140°	554.1	554.7	544.6	526.9	502.9	475.7	445.3	413.1	383.3	356.1	332.1
142.5°	520.0	520.6	511.7	496.5	476.9	454.2	428.9	402.3	378.3	354.9	334.0
145°	489.0	487.7	482.6	469.3	453.5	435.2	414.9	394.1	373.8	353.6	334.6
147.5°	462.4	461.8	456.7	447.2	434.6	421.3	404.2	387.1	369.4	351.7	334.6
150°	439.6	439.6	435.8	428.9	419.4	407.4	394.1	379.5	365.0	349.2	334.6
152.5°	420.6	420.6	418.7	412.4	405.5	396.0	384.6	372.6	359.9	346.0	332.7
155°	405.5	404.8	403.6	398.5	392.8	385.2	375.7	365.6	354.9	342.2	331.5
157.5°	390.9	390.9	389.6	385.9	380.8	374.5	366.9	358.0	349.2	339.0	329.6
160°	377.0	377.6	377.6	373.8	369.4	365.0	358.7	351.7	343.5	335.2	328.3
162.5°	364.3	365.0	365.0	361.8	359.3	355.5	349.8	344.1	337.8	331.5	325.8
165°	353.6	353.6	354.2	351.7	349.2	346.0	341.6	337.8	332.7	327.7	323.2
167.5°	342.8	342.8	343.5	341.6	340.3	337.8	335.2	332.1	327.7	323.9	320.7
170°	333.4	333.4	334.0	332.7	332.1	330.8	328.3	326.4	323.2	320.1	318.2
172.5°	324.5	325.1	326.4	325.1	325.1	324.5	322.6	321.3	318.8	316.9	316.3
175°	318.2	318.8	319.4	318.8	318.8	318.8	317.5	316.9	315.6	314.4	314.4
177.5°	313.7	313.7	315.0	314.4	315.0	315.0	314.4	313.7	313.1	312.5	313.1
180°	312.5	312.5	312.5	312.5	312.5	312.5	312.5	312.5	312.5	312.5	312.5



TEST NUMBER: P831857

CATALOG NUMBER: S123RDIP-S1000D585U850-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	3598.7	3598.7	3598.7	3598.7	3598.7	3598.7	3598.7	3598.7	3598.7	3598.7	3598.7
2.5°	3820.8	3817.1	3781.7	3746.3	3711.6	3676.9	3651.1	3625.3	3581.8	3538.2	3510.9
5°	4057.6	4029.6	3973.5	3917.4	3833.3	3749.2	3678.4	3607.6	3517.6	3427.6	3352.3
7.5°	4189.7	4166.8	4098.9	4031.0	3919.6	3808.2	3697.6	3586.9	3454.1	3321.3	3207.7
10°	4193.4	4212.5	4156.5	4100.4	3975.0	3849.6	3699.1	3548.6	3370.0	3191.5	3044.7
12.5°	4062.0	4144.7	4132.9	4121.1	3993.4	3865.8	3682.8	3499.9	3280.8	3061.6	2877.9
15°	3816.4	3976.5	4023.7	4070.9	3965.4	3859.9	3651.8	3443.8	3186.3	2928.9	2717.9
17.5°	3499.9	3724.1	3848.8	3973.5	3896.8	3820.1	3592.1	3364.1	3074.2	2784.3	2554.8
20°	3125.1	3418.7	3614.2	3809.7	3781.7	3753.7	3518.3	3283.0	2970.2	2657.4	2408.7
22.5°	2754.7	3064.6	3334.6	3604.6	3633.4	3662.2	3424.6	3187.1	2844.8	2502.4	2249.4
25°	2435.3	2750.3	3072.0	3393.6	3458.6	3523.5	3297.7	3072.0	2717.1	2362.3	2110.7
27.5°	2130.6	2430.1	2784.3	3138.4	3256.4	3374.5	3167.9	2961.3	2591.7	2222.1	1971.3
30°	1882.0	2149.8	2511.3	2872.8	3037.3	3201.8	3012.2	2822.6	2456.0	2089.3	1843.6
32.5°	1650.3	1890.1	2253.1	2616.0	2807.1	2998.2	2834.4	2670.6	2318.0	1965.4	1722.6
35°	1467.4	1682.1	2020.7	2359.3	2573.3	2787.2	2652.9	2518.7	2174.1	1829.6	1600.2
37.5°	1310.2	1490.2	1808.2	2126.2	2353.4	2580.6	2468.5	2356.4	2032.5	1708.6	1491.7
40°	1180.4	1325.0	1620.8	1916.7	2139.5	2362.3	2266.4	2170.5	1880.5	1590.6	1387.7
42.5°	1069.0	1193.7	1459.3	1724.9	1929.2	2133.6	2070.1	2006.7	1744.0	1481.4	1293.3
45°	970.9	1075.6	1309.5	1543.4	1731.5	1919.6	1869.4	1819.3	1592.8	1366.3	1193.7
47.5°	883.8	973.8	1182.6	1391.4	1560.3	1729.3	1682.8	1636.3	1448.9	1261.5	1104.4
50°	804.1	880.9	1055.0	1229.1	1381.1	1533.0	1494.7	1456.3	1301.4	1146.5	1010.7
52.5°	728.9	792.3	948.7	1105.1	1227.6	1350.1	1320.6	1291.1	1171.5	1052.0	928.8
55°	657.3	715.6	847.7	979.7	1084.5	1189.2	1159.7	1130.2	1037.3	944.3	835.9
57.5°	592.4	643.3	750.3	857.3	940.6	1024.0	1010.0	996.0	918.5	841.0	751.8
60°	523.8	569.5	661.8	754.0	821.1	888.2	872.0	855.8	800.5	745.1	668.4
62.5°	462.6	503.1	576.9	650.7	705.3	759.9	748.1	736.3	694.2	652.2	588.7
65°	398.4	438.2	498.0	557.7	600.5	643.3	633.0	622.7	590.9	559.2	508.3
67.5°	340.1	373.3	424.9	476.6	505.4	534.1	528.2	522.3	498.0	473.6	433.8
70°	281.1	309.9	352.6	395.4	415.4	435.3	437.5	439.7	417.6	395.4	365.9
72.5°	222.1	244.9	284.8	324.6	340.1	355.6	354.9	354.1	340.8	327.6	301.0
75°	170.4	187.4	218.4	249.4	262.6	275.9	278.9	281.8	269.3	256.7	242.0
77.5°	122.5	134.3	157.9	181.5	196.2	211.0	212.5	213.9	208.0	202.1	188.1
80°	86.3	90.0	104.8	119.5	135.0	150.5	152.7	154.9	149.0	143.1	134.3
82.5°	59.8	62.0	67.1	72.3	84.8	97.4	100.3	103.3	100.3	97.4	87.8
85°	36.1	36.9	39.1	41.3	47.2	53.1	56.1	59.0	57.5	56.1	50.9
87.5°	16.2	16.2	17.0	17.7	19.2	20.7	24.3	28.0	25.8	23.6	21.4
90°	12.0	10.1	8.2	7.0	5.7	3.8	2.5	1.3	2.5	3.8	5.7
92.5°	97.4	63.9	43.6	32.3	25.9	20.2	13.9	9.5	13.9	20.2	25.9
95°	230.2	136.0	82.2	57.6	41.1	30.4	23.4	21.5	23.4	30.4	41.1
97.5°	256.2	146.8	93.6	66.4	50.0	40.5	34.8	34.2	34.8	40.5	50.0
100°	238.5	144.9	100.6	75.9	60.7	51.9	47.4	46.8	47.4	51.9	60.7
102.5°	223.3	147.4	108.8	86.7	73.4	65.2	61.4	60.1	61.4	65.2	73.4
105°	217.6	152.4	118.3	98.7	86.7	79.1	75.3	73.4	75.3	79.1	86.7
107.5°	216.3	160.7	130.3	112.0	100.6	93.0	89.2	87.3	89.2	93.0	100.6
110°	219.5	171.4	143.0	125.2	114.5	107.5	104.4	102.5	104.4	107.5	114.5



TEST NUMBER: P831857

CATALOG NUMBER: S123RDIP-S1000D585U850-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	225.8	182.2	156.2	139.2	128.4	121.4	118.3	116.4	118.3	121.4	128.4
115°	232.8	194.2	170.2	153.1	142.3	136.0	132.2	129.7	132.2	136.0	142.3
117.5°	241.6	206.8	182.8	167.0	155.0	149.3	146.1	143.0	146.1	149.3	155.0
120°	251.8	218.9	196.1	180.3	168.3	161.9	158.8	156.9	158.8	161.9	168.3
122.5°	261.2	231.5	209.4	192.3	180.9	173.9	170.8	168.9	170.8	173.9	180.9
125°	271.4	243.5	221.4	204.3	192.3	185.3	181.5	180.3	181.5	185.3	192.3
127.5°	279.6	254.3	232.8	215.7	202.4	195.5	191.0	189.1	191.0	195.5	202.4
130°	287.8	263.8	242.9	225.8	212.5	204.9	199.3	197.4	199.3	204.9	212.5
132.5°	295.4	272.0	251.8	235.3	222.0	212.5	206.2	203.7	206.2	212.5	222.0
135°	301.7	280.2	260.6	243.5	230.2	220.8	213.8	211.3	213.8	220.8	230.2
137.5°	306.8	285.9	266.9	251.1	237.8	227.7	220.8	218.2	220.8	227.7	237.8
140°	310.6	291.6	273.3	257.4	244.8	234.7	228.3	225.2	228.3	234.7	244.8
142.5°	314.4	296.0	278.3	263.8	251.1	242.3	235.3	232.8	235.3	242.3	251.1
145°	316.9	299.8	283.4	268.8	258.1	248.6	242.9	241.0	242.9	248.6	258.1
147.5°	318.8	303.0	287.8	275.2	264.4	256.2	250.5	249.2	250.5	256.2	264.4
150°	319.4	306.2	291.6	280.2	271.4	263.1	258.1	257.4	258.1	263.1	271.4
152.5°	320.7	308.0	296.0	285.3	277.7	270.7	265.7	265.7	265.7	270.7	277.7
155°	320.7	310.6	299.8	291.0	284.0	277.7	273.9	273.9	273.9	277.7	284.0
157.5°	321.3	311.8	303.0	296.0	289.7	284.0	280.8	280.2	280.8	284.0	289.7
160°	321.3	313.7	306.2	299.8	295.4	290.3	287.8	287.8	287.8	290.3	295.4
162.5°	320.7	314.4	308.0	303.0	299.2	295.4	293.5	293.5	293.5	295.4	299.2
165°	319.4	315.0	309.9	305.5	303.0	299.8	298.6	299.2	298.6	299.8	303.0
167.5°	318.8	315.0	311.2	308.0	306.2	303.6	303.0	303.6	303.0	303.6	306.2
170°	316.9	314.4	311.2	309.9	308.7	306.8	306.2	307.4	306.2	306.8	308.7
172.5°	316.3	314.4	311.8	311.2	310.6	309.3	309.3	309.9	309.3	309.3	310.6
175°	315.0	313.7	312.5	311.8	311.8	310.6	311.2	311.8	311.2	310.6	311.8
177.5°	314.4	313.1	312.5	312.5	312.5	311.8	312.5	313.1	312.5	311.8	312.5
180°	312.5	312.5	312.5	312.5	312.5	312.5	312.5	312.5	312.5	312.5	312.5



TEST NUMBER: P831857

CATALOG NUMBER: S123RDIP-S1000D585U850-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	3598.7	3598.7	3598.7	3598.7	3598.7	3598.7	3598.7	3598.7	3598.7	3598.7	3598.7
2.5°	3483.6	3441.6	3399.5	3369.3	3339.0	3301.4	3263.8	3262.3	3260.8	3232.8	3204.8
5°	3277.1	3204.0	3131.0	3059.4	2987.9	2916.3	2844.8	2828.5	2812.3	2787.9	2763.6
7.5°	3094.1	2977.5	2861.0	2769.5	2678.0	2606.5	2534.9	2486.2	2437.5	2399.9	2362.3
10°	2897.9	2753.3	2608.7	2498.0	2387.3	2309.9	2232.4	2176.4	2120.3	2093.7	2067.2
12.5°	2694.3	2537.1	2380.0	2271.5	2163.1	2070.1	1977.2	1926.3	1875.4	1838.5	1801.6
15°	2506.9	2337.9	2169.0	2053.9	1938.8	1851.7	1764.7	1713.8	1662.9	1626.0	1589.1
17.5°	2325.4	2155.0	1984.5	1868.0	1751.4	1672.5	1593.5	1544.1	1494.7	1471.8	1448.9
20°	2160.1	1988.2	1816.3	1706.4	1596.5	1519.0	1441.6	1415.0	1388.4	1367.0	1345.6
22.5°	1996.3	1831.1	1665.8	1560.3	1454.8	1398.8	1342.7	1321.3	1299.9	1283.7	1267.4
25°	1859.1	1694.6	1530.1	1437.9	1345.6	1302.1	1258.6	1244.6	1230.6	1214.3	1198.1
27.5°	1720.4	1564.0	1407.6	1333.8	1260.1	1224.7	1189.2	1171.5	1153.8	1140.6	1127.3
30°	1598.0	1453.4	1308.8	1247.5	1186.3	1155.3	1124.3	1105.1	1086.0	1073.4	1060.9
32.5°	1479.9	1351.6	1223.2	1170.8	1118.4	1088.2	1057.9	1039.5	1021.0	1006.3	991.5
35°	1370.7	1259.3	1147.9	1100.0	1052.0	1021.8	991.5	973.1	954.6	939.9	925.1
37.5°	1274.8	1173.8	1072.7	1027.7	982.7	956.1	929.6	910.4	891.2	875.7	860.2
40°	1184.8	1095.6	1006.3	962.8	919.2	890.5	861.7	844.7	827.8	813.7	799.7
42.5°	1105.1	1023.3	941.4	898.6	855.8	828.5	801.2	781.3	761.4	753.2	745.1
45°	1021.0	948.7	876.4	835.1	793.8	765.0	736.3	719.3	702.3	695.0	687.6
47.5°	947.3	880.1	813.0	772.4	731.8	706.0	680.2	666.9	653.6	643.3	633.0
50°	875.0	810.0	745.1	706.0	666.9	644.8	622.7	606.4	590.2	582.8	575.4
52.5°	805.6	746.6	687.6	647.7	607.9	586.5	565.1	551.1	537.1	521.6	506.1
55°	727.4	675.8	624.1	588.7	553.3	531.2	509.0	492.8	476.6	460.4	444.1
57.5°	662.5	611.6	560.7	529.0	497.2	475.8	454.5	436.7	419.0	405.8	392.5
60°	591.7	547.4	503.1	472.2	441.2	420.5	399.9	382.9	365.9	359.3	352.6
62.5°	525.3	484.0	442.6	415.4	388.1	368.1	348.2	337.2	326.1	321.7	317.2
65°	457.4	422.0	386.6	361.5	336.4	319.4	302.5	297.3	292.1	288.5	284.8
67.5°	394.0	363.7	333.5	311.3	289.2	277.4	265.6	259.7	253.8	249.4	244.9
70°	336.4	309.9	283.3	264.1	244.9	233.9	222.8	217.6	212.5	204.4	196.2
72.5°	274.4	253.8	233.1	218.4	203.6	194.0	184.4	174.1	163.8	156.4	149.0
75°	227.2	206.6	185.9	171.9	157.9	146.8	135.7	132.1	128.4	126.2	123.9
77.5°	174.1	156.4	138.7	127.6	116.6	111.4	106.2	104.0	101.8	101.1	100.3
80°	125.4	110.7	95.9	90.0	84.1	82.6	81.2	79.7	78.2	77.5	76.7
82.5°	78.2	70.8	63.4	62.0	60.5	59.8	59.0	58.3	57.5	56.8	56.1
85°	45.7	42.8	39.8	39.1	38.4	37.6	36.9	36.9	36.9	36.9	36.9
87.5°	19.2	19.2	19.2	19.2	19.2	19.2	19.2	19.2	19.2	18.4	17.7
90°	7.0	8.2	10.1	12.0	13.9	15.8	15.2	15.8	16.4	17.1	18.3
92.5°	32.3	43.6	63.9	97.4	130.3	117.7	87.9	62.6	48.7	42.4	38.0
95°	57.6	82.2	136.0	230.2	334.0	375.1	304.3	227.7	154.3	120.8	98.0
97.5°	66.4	93.6	146.8	256.2	430.8	576.9	596.5	523.1	394.7	311.2	239.1
100°	75.9	100.6	144.9	238.5	404.8	599.0	723.6	745.8	694.5	620.5	530.7
102.5°	86.7	108.8	147.4	223.3	366.9	557.9	730.0	819.8	830.5	795.1	746.4
105°	98.7	118.3	152.4	217.6	337.1	508.6	690.1	822.3	885.6	897.6	881.1
107.5°	112.0	130.3	160.7	216.3	315.6	464.9	633.2	784.4	883.7	933.0	950.1
110°	125.2	143.0	171.4	219.5	304.3	428.9	580.0	724.9	841.3	921.0	965.3



TEST NUMBER: P831857

CATALOG NUMBER: S123RDIP-S1000D585U850-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	139.2	156.2	182.2	225.8	297.9	404.8	533.9	666.1	785.6	877.3	937.4
115°	153.1	170.2	194.2	232.8	297.3	389.0	498.4	615.5	725.5	818.5	887.5
117.5°	167.0	182.8	206.8	241.6	297.9	378.3	475.0	576.2	673.7	759.1	830.5
120°	180.3	196.1	218.9	251.8	300.5	371.3	457.3	546.5	631.9	707.8	771.7
122.5°	192.3	209.4	231.5	261.2	304.9	366.9	442.8	523.1	598.4	667.3	725.5
125°	204.3	221.4	243.5	271.4	309.3	363.1	430.8	502.9	571.8	632.5	683.1
127.5°	215.7	232.8	254.3	279.6	314.4	361.2	419.4	484.5	547.2	602.8	649.6
130°	225.8	242.9	263.8	287.8	319.4	359.3	410.5	467.5	524.4	575.6	618.6
132.5°	235.3	251.8	272.0	295.4	323.2	358.7	402.3	451.6	502.9	549.7	590.2
135°	243.5	260.6	280.2	301.7	327.0	358.0	395.3	437.7	482.6	523.7	559.8
137.5°	251.1	266.9	285.9	306.8	329.6	356.8	389.0	424.4	462.4	499.1	531.3
140°	257.4	273.3	291.6	310.6	332.1	356.1	383.3	413.1	445.3	475.7	502.9
142.5°	263.8	278.3	296.0	314.4	334.0	354.9	378.3	402.3	428.9	454.2	476.9
145°	268.8	283.4	299.8	316.9	334.6	353.6	373.8	394.1	414.9	435.2	453.5
147.5°	275.2	287.8	303.0	318.8	334.6	351.7	369.4	387.1	404.2	421.3	434.6
150°	280.2	291.6	306.2	319.4	334.6	349.2	365.0	379.5	394.1	407.4	419.4
152.5°	285.3	296.0	308.0	320.7	332.7	346.0	359.9	372.6	384.6	396.0	405.5
155°	291.0	299.8	310.6	320.7	331.5	342.2	354.9	365.6	375.7	385.2	392.8
157.5°	296.0	303.0	311.8	321.3	329.6	339.0	349.2	358.0	366.9	374.5	380.8
160°	299.8	306.2	313.7	321.3	328.3	335.2	343.5	351.7	358.7	365.0	369.4
162.5°	303.0	308.0	314.4	320.7	325.8	331.5	337.8	344.1	349.8	355.5	359.3
165°	305.5	309.9	315.0	319.4	323.2	327.7	332.7	337.8	341.6	346.0	349.2
167.5°	308.0	311.2	315.0	318.8	320.7	323.9	327.7	332.1	335.2	337.8	340.3
170°	309.9	311.2	314.4	316.9	318.2	320.1	323.2	326.4	328.3	330.8	332.1
172.5°	311.2	311.8	314.4	316.3	316.3	316.9	318.8	321.3	322.6	324.5	325.1
175°	311.8	312.5	313.7	315.0	314.4	314.4	315.6	316.9	317.5	318.8	318.8
177.5°	312.5	312.5	313.1	314.4	313.1	312.5	313.1	313.7	314.4	315.0	315.0
180°	312.5	312.5	312.5	312.5	312.5	312.5	312.5	312.5	312.5	312.5	312.5



TEST NUMBER: P831857

CATALOG NUMBER: S123RDIP-S1000D585U850-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	3598.7	3598.7	3598.7	3598.7
2.5°	3197.4	3190.0	3187.1	3184.1
5°	2740.7	2717.9	2712.7	2707.5
7.5°	2352.7	2343.1	2311.4	2279.6
10°	2037.7	2008.1	1994.9	1981.6
12.5°	1774.3	1747.0	1742.6	1738.1
15°	1569.9	1550.7	1544.1	1537.5
17.5°	1435.7	1422.4	1414.3	1406.1
20°	1336.1	1326.5	1320.6	1314.7
22.5°	1260.1	1252.7	1248.3	1243.8
25°	1187.0	1176.0	1172.3	1168.6
27.5°	1117.7	1108.1	1104.4	1100.7
30°	1052.8	1044.6	1039.5	1034.3
32.5°	981.9	972.4	969.4	966.4
35°	919.2	913.3	910.4	907.4
37.5°	852.8	845.5	841.0	836.6
40°	796.0	792.3	790.1	787.9
42.5°	738.5	731.8	731.1	730.4
45°	680.9	674.3	672.8	671.3
47.5°	627.1	621.2	620.4	619.7
50°	567.3	559.2	553.3	547.4
52.5°	498.7	491.3	486.2	481.0
55°	436.0	427.9	423.5	419.0
57.5°	388.8	385.1	382.9	380.7
60°	350.4	348.2	346.7	345.3
62.5°	315.0	312.8	312.8	312.8
65°	282.6	280.3	278.1	275.9
67.5°	240.5	236.1	235.3	234.6
70°	189.6	183.0	182.2	181.5
72.5°	148.3	147.5	146.1	144.6
75°	122.5	121.0	121.0	121.0
77.5°	98.9	97.4	97.4	97.4
80°	76.0	75.3	76.0	76.7
82.5°	56.1	56.1	55.3	54.6
85°	36.1	35.4	35.4	35.4
87.5°	17.7	17.7	17.7	17.7
90°	17.7	18.3	19.0	18.3
92.5°	36.7	34.2	34.8	33.5
95°	86.0	80.3	75.9	73.4
97.5°	196.7	172.7	157.5	150.5
100°	466.8	420.6	396.0	396.6
102.5°	700.2	666.1	646.5	628.1
105°	852.0	828.0	807.8	804.6
107.5°	946.3	934.9	926.7	919.7
110°	983.0	988.0	986.8	985.5



TEST NUMBER: P831857

CATALOG NUMBER: S123RDIP-S1000D585U850-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
112.5°	973.5	991.8	998.2	998.8
115°	934.9	962.7	975.4	978.5
117.5°	879.9	910.9	929.8	934.3
120°	821.7	857.1	872.3	876.1
122.5°	768.5	799.5	816.6	821.7
125°	723.6	751.5	767.3	771.7
127.5°	686.3	710.3	724.9	728.7
130°	652.2	674.9	688.2	693.3
132.5°	621.2	643.9	655.3	658.5
135°	590.8	609.8	621.2	625.6
137.5°	557.9	577.5	587.0	590.8
140°	526.9	544.6	554.7	554.1
142.5°	496.5	511.7	520.6	520.0
145°	469.3	482.6	487.7	489.0
147.5°	447.2	456.7	461.8	462.4
150°	428.9	435.8	439.6	439.6
152.5°	412.4	418.7	420.6	420.6
155°	398.5	403.6	404.8	405.5
157.5°	385.9	389.6	390.9	390.9
160°	373.8	377.6	377.6	377.0
162.5°	361.8	365.0	365.0	364.3
165°	351.7	354.2	353.6	353.6
167.5°	341.6	343.5	342.8	342.8
170°	332.7	334.0	333.4	333.4
172.5°	325.1	326.4	325.1	324.5
175°	318.8	319.4	318.8	318.2
177.5°	314.4	315.0	313.7	313.7
180°	312.5	312.5	312.5	312.5



TEST NUMBER: P831857

CATALOG NUMBER: S123RDIP-S1000D585U850-4F0-1E-UDD-G4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.92	15.88	15.73	16.70	17.71	19.59	20.54	20.40	21.37	22.38
	3H	16.15	17.01	16.97	17.84	18.88	21.09	21.95	21.92	22.78	23.82
	4H	16.54	17.35	17.38	18.19	19.24	21.59	22.40	22.43	23.24	24.29
	6H	16.83	17.57	17.68	18.42	19.48	21.91	22.65	22.76	23.50	24.56
	8H	16.92	17.62	17.78	18.49	19.55	21.99	22.70	22.85	23.56	24.62
	12H	16.97	17.65	17.84	18.50	19.59	22.03	22.70	22.89	23.56	24.64
4H	2H	15.66	16.47	16.50	17.31	18.36	19.60	20.40	20.44	21.24	22.29
	3H	17.04	17.71	17.89	18.58	19.65	21.27	21.93	22.12	22.81	23.87
	4H	17.50	18.11	18.37	18.98	20.07	21.88	22.48	22.74	23.35	24.45
	6H	17.87	18.40	18.76	19.29	20.39	22.32	22.84	23.20	23.74	24.84
	8H	18.00	18.49	18.89	19.38	20.49	22.45	22.94	23.34	23.83	24.94
	12H	18.08	18.52	18.99	19.43	20.54	22.52	22.96	23.42	23.87	24.98
8H	4H	17.82	18.31	18.71	19.20	20.31	21.85	22.34	22.74	23.23	24.34
	6H	18.29	18.69	19.20	19.62	20.73	22.35	22.75	23.26	23.69	24.79
	8H	18.48	18.84	19.41	19.76	20.89	22.54	22.89	23.46	23.82	24.94
	12H	18.63	18.94	19.55	19.86	21.04	22.66	22.97	23.58	23.89	25.07
12H	4H	17.84	18.28	18.74	19.19	20.30	21.81	22.25	22.71	23.15	24.27
	6H	18.35	18.71	19.27	19.63	20.76	22.33	22.68	23.25	23.61	24.73
	8H	18.57	18.89	19.50	19.80	20.98	22.53	22.84	23.45	23.75	24.93