

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332988-930

Luminaire Tested: **S124RDIP-S1195D365U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332988-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIP-S1195D365U930-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 365 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5121.1 lumens
Efficiency: N/A
Efficacy: 102.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 49.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332988-930

CATALOG NUMBER: S124RDIP-S1195D365U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332988-930

CATALOG NUMBER: S124RDIP-S1195D365U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	114	114	114	114	108	108	108	108	98	98	98	89	89	89	81	81	81	77
1	104	100	96	92	99	95	92	89	87	84	82	79	77	75	72	70	69	66
2	95	88	82	76	91	84	78	74	77	72	68	70	67	63	64	61	59	56
3	87	78	70	64	83	74	67	62	68	63	58	62	58	54	57	53	50	47
4	80	69	61	55	76	66	59	53	61	55	50	56	51	47	51	47	44	41
5	74	62	53	47	70	59	52	46	55	48	43	50	45	41	46	42	38	36
6	68	56	47	41	65	54	46	40	50	43	38	46	40	36	42	38	34	32
7	63	51	42	37	60	49	41	36	45	39	34	42	36	32	39	34	30	28
8	59	46	38	33	56	45	37	32	41	35	30	38	33	29	36	31	27	25
9	55	42	35	29	52	41	34	29	38	32	27	35	30	26	33	28	25	23
10	52	39	32	27	49	38	31	26	35	29	25	33	28	24	31	26	23	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13726	13726	13726
5°	13757	13588	13674
10°	13671	13426	13426
15°	13514	13143	13046
20°	13298	12773	12538
25°	13023	12339	12026
30°	12755	11882	11384
35°	12458	11406	10738
40°	12101	10866	10043
45°	11772	10330	9334
50°	11396	9712	8584
55°	10994	9070	7769
60°	10551	8365	6936
65°	10147	7484	6117
70°	9557	6515	5193
75°	8812	5402	4223
80°	7685	4114	3873
85°	6512	3742	3492



TEST NUMBER: P332988-930

CATALOG NUMBER: S124RDIP-S1195D365U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.7	3.1
10°-20°	445.4	8.7
20°-30°	643.1	12.6
30°-40°	729.0	14.2
40°-50°	704.0	13.7
50°-60°	585.4	11.4
60°-70°	404.2	7.9
70°-80°	204.9	4.0
80°-90°	53.7	1.0
90°-100°	13.2	0.3
100°-110°	84.0	1.6
110°-120°	160.7	3.1
120°-130°	204.0	4.0
130°-140°	218.3	4.3
140°-150°	204.1	4.0
150°-160°	164.6	3.2
160°-170°	106.2	2.1
170°-180°	36.6	0.7
0°-30°	1248.2	24.4
0°-40°	1977.3	38.6
0°-60°	3266.6	63.8
0°-90°	3929.4	76.7
90°-120°	257.9	5.0
90°-150°	884.3	17.3
90°-180°	1192.0	23.3
0°-180°	5121.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1700	1700	1700	1700	1700	
5°	1698	1692	1677	1689	1687	161
15°	1617	1604	1573	1570	1561	455
25°	1462	1437	1385	1364	1350	673
35°	1264	1221	1157	1114	1090	790
45°	1031	981	905	843	818	795
55°	781	727	644	579	552	698
65°	531	474	392	338	320	524
75°	282	234	173	144	135	298
85°	70	46	40	38	38	79
90°	1	4	6	8	9	4
95°	16	7	6	8	8	20
105°	87	88	90	92	82	91
115°	162	163	162	163	163	159
125°	228	229	228	229	229	203
135°	282	282	283	284	284	217
145°	326	326	326	327	327	203
155°	357	357	356	357	357	165
165°	377	375	375	377	375	106
175°	385	384	384	386	383	37
180°	385	385	385	385	385	



TEST NUMBER: P332988-930

CATALOG NUMBER: S124RDIP-S1195D365U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2
2.5°	1704.4	1703.5	1702.6	1701.6	1700.7	1699.0	1696.5	1693.9	1691.3	1688.8	1691.3
5°	1697.6	1696.5	1695.3	1694.2	1693.1	1690.7	1687.3	1683.8	1680.3	1676.8	1679.7
7.5°	1682.3	1681.1	1679.8	1678.6	1677.4	1674.5	1670.1	1665.6	1661.0	1656.5	1658.4
10°	1667.7	1666.2	1664.8	1663.4	1661.9	1658.6	1653.4	1648.2	1643.0	1637.8	1638.9
12.5°	1648.9	1647.3	1645.6	1643.9	1642.3	1638.3	1632.2	1626.1	1619.9	1613.8	1614.5
15°	1616.9	1614.3	1611.8	1609.2	1606.5	1601.6	1594.4	1587.1	1579.9	1572.6	1572.1
17.5°	1578.2	1574.3	1570.6	1566.8	1563.1	1556.9	1548.2	1539.5	1530.8	1522.2	1520.5
20°	1547.9	1544.2	1540.4	1536.7	1532.9	1526.1	1516.3	1506.4	1496.6	1486.8	1484.4
22.5°	1514.6	1510.4	1506.2	1501.9	1497.7	1490.4	1479.8	1469.3	1458.7	1448.2	1444.7
25°	1462.0	1456.8	1451.6	1446.4	1441.2	1432.6	1420.8	1408.9	1397.1	1385.2	1380.3
27.5°	1406.8	1400.3	1393.8	1387.2	1380.6	1371.1	1358.4	1345.7	1333.0	1320.4	1314.3
30°	1368.3	1361.1	1353.8	1346.5	1339.4	1328.9	1315.3	1301.7	1288.2	1274.6	1267.3
32.5°	1327.6	1319.5	1311.3	1303.2	1295.0	1283.9	1269.8	1255.8	1241.7	1227.7	1219.3
35°	1264.1	1254.8	1245.6	1236.3	1227.1	1215.2	1200.8	1186.3	1171.8	1157.4	1147.5
37.5°	1196.2	1186.6	1177.0	1167.5	1158.0	1145.2	1129.2	1113.1	1097.1	1081.1	1070.1
40°	1148.3	1138.7	1129.2	1119.7	1110.0	1097.1	1080.6	1064.0	1047.6	1031.1	1019.0
42.5°	1102.4	1092.4	1082.4	1072.4	1062.4	1048.8	1031.6	1014.4	997.3	980.1	967.7
45°	1031.1	1020.3	1009.7	999.0	988.3	974.2	956.9	939.6	922.2	904.8	890.6
47.5°	957.4	946.3	935.3	924.2	913.2	898.6	880.6	862.5	844.5	826.5	811.7
50°	907.4	896.1	884.8	873.6	862.3	847.3	828.8	810.3	791.8	773.3	758.9
52.5°	856.4	845.3	834.3	823.2	812.2	797.1	778.2	759.2	740.2	721.2	706.5
55°	781.1	769.6	758.0	746.4	734.8	719.7	700.8	682.1	663.2	644.4	629.4
57.5°	706.6	694.6	682.6	670.6	658.5	643.3	624.8	606.2	587.7	569.2	553.9
60°	653.5	642.0	630.4	618.8	607.2	592.2	573.7	555.2	536.6	518.1	503.1
62.5°	605.6	593.6	581.6	569.6	557.5	542.0	523.0	504.0	485.0	466.1	452.2
65°	531.2	518.7	506.3	493.8	481.4	465.9	447.4	428.9	410.4	391.8	379.4
67.5°	453.8	441.9	430.0	418.1	406.2	391.6	374.4	357.3	340.1	322.9	312.2
70°	404.9	392.7	380.6	368.4	356.3	341.9	325.5	309.0	292.5	276.0	266.4
72.5°	352.8	341.9	330.8	319.8	308.8	295.5	280.0	264.4	248.8	233.3	225.1
75°	282.5	271.8	261.1	250.4	239.7	227.6	213.9	200.3	186.8	173.2	166.5
77.5°	211.2	202.1	193.0	183.9	174.8	164.8	153.8	142.8	131.8	120.8	116.9
80°	165.3	156.9	148.5	140.1	131.8	123.3	114.5	105.9	97.2	88.5	87.6
82.5°	125.8	118.1	110.4	102.6	95.0	88.6	83.6	78.7	73.7	68.7	68.1
85°	70.3	64.5	58.7	52.9	47.1	43.9	43.0	42.1	41.3	40.4	39.8
87.5°	24.1	22.4	20.7	19.0	17.3	16.4	16.2	16.1	16.0	15.8	15.7
90°	0.9	1.5	2.3	3.0	3.7	4.3	4.8	5.3	5.8	6.4	6.7
92.5°	3.7	3.7	3.7	3.8	3.8	4.1	4.6	5.1	5.6	6.1	6.5
95°	15.8	13.7	11.5	9.3	7.2	6.1	6.1	6.2	6.3	6.4	6.7
97.5°	33.7	35.0	36.4	37.7	39.1	36.2	29.0	21.9	14.8	7.6	7.7
100°	47.3	48.4	49.6	50.7	51.9	48.0	39.2	30.3	21.5	12.7	11.6
102.5°	62.5	63.3	64.2	65.0	65.9	65.7	64.6	63.4	62.2	61.1	49.3
105°	86.7	87.1	87.5	87.9	88.3	88.6	88.9	89.3	89.6	89.9	90.5
107.5°	109.3	109.4	109.7	109.8	110.1	110.3	110.8	111.2	111.6	112.1	112.3
110°	124.5	124.7	124.8	125.1	125.2	125.6	125.9	126.3	126.7	127.1	127.2



TEST NUMBER: P332988-930

CATALOG NUMBER: S124RDIP-S1195D365U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	139.3	139.6	139.9	140.2	140.6	140.9	141.0	141.2	141.4	141.6	141.5
115°	161.9	162.2	162.3	162.5	162.7	162.7	162.7	162.7	162.6	162.5	162.7
117.5°	182.4	182.6	182.9	183.2	183.4	183.6	183.8	183.9	184.0	184.2	184.2
120°	196.2	196.5	196.7	197.0	197.2	197.3	197.3	197.2	197.1	197.1	197.2
122.5°	209.1	209.3	209.5	209.6	209.8	209.9	209.9	210.0	210.1	210.3	210.3
125°	227.6	227.9	228.1	228.4	228.7	228.7	228.6	228.4	228.4	228.2	228.4
127.5°	245.2	245.2	245.2	245.3	245.4	245.6	245.9	246.1	246.5	246.8	246.7
130°	256.4	256.5	256.6	256.7	256.7	256.8	257.0	257.2	257.4	257.6	257.6
132.5°	266.8	266.9	267.0	267.2	267.3	267.4	267.7	267.9	268.2	268.4	268.5
135°	282.3	282.3	282.3	282.2	282.1	282.2	282.5	282.7	283.0	283.2	283.4
137.5°	296.1	296.2	296.2	296.2	296.3	296.4	296.7	296.9	297.3	297.5	297.7
140°	305.2	305.2	305.4	305.5	305.7	305.7	305.9	306.1	306.1	306.3	306.5
142.5°	313.2	313.4	313.6	313.9	314.1	314.3	314.4	314.5	314.5	314.6	314.7
145°	325.6	325.8	326.0	326.2	326.4	326.4	326.4	326.4	326.4	326.4	326.5
147.5°	335.4	335.8	336.1	336.6	336.9	337.0	337.0	336.9	336.8	336.8	336.8
150°	342.6	342.8	343.1	343.4	343.6	343.7	343.6	343.6	343.5	343.5	343.5
152.5°	348.6	348.8	349.0	349.2	349.4	349.4	349.4	349.2	349.1	349.0	349.1
155°	357.0	357.1	357.1	357.2	357.3	357.2	357.0	356.8	356.6	356.4	356.7
157.5°	364.1	364.0	364.0	363.9	363.9	363.8	363.6	363.4	363.1	363.0	363.3
160°	368.3	368.0	367.9	367.7	367.5	367.4	367.3	367.2	367.1	367.0	367.5
162.5°	371.9	371.7	371.5	371.2	371.0	370.8	370.7	370.6	370.6	370.6	371.0
165°	376.6	376.3	375.9	375.6	375.3	375.1	375.1	375.1	375.1	375.1	375.7
167.5°	380.3	379.9	379.6	379.3	379.0	378.8	378.7	378.7	378.6	378.6	379.2
170°	382.4	382.0	381.6	381.2	380.8	380.7	380.7	380.8	380.8	380.9	381.4
172.5°	383.8	383.4	382.9	382.6	382.2	382.0	382.1	382.2	382.2	382.3	382.8
175°	385.2	384.8	384.5	384.1	383.7	383.5	383.6	383.7	383.8	383.8	384.4
177.5°	386.0	385.6	385.2	384.8	384.5	384.3	384.5	384.6	384.7	384.7	385.2
180°	385.2	385.2	385.2	385.2	385.2	385.2	385.2	385.2	385.2	385.2	385.2



TEST NUMBER: P332988-930

CATALOG NUMBER: S124RDIP-S1195D365U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2
2.5°	1693.9	1696.5	1699.0	1700.1	1699.9	1699.7	1699.4	1699.2
5°	1682.6	1685.5	1688.4	1689.5	1689.0	1688.4	1687.8	1687.3
7.5°	1660.2	1662.1	1663.9	1664.4	1663.5	1662.6	1661.6	1660.7
10°	1640.1	1641.2	1642.4	1642.4	1641.2	1640.1	1638.9	1637.8
12.5°	1615.2	1615.9	1616.6	1616.1	1614.5	1612.9	1611.3	1609.6
15°	1571.5	1570.9	1570.3	1569.0	1567.0	1565.0	1563.0	1561.0
17.5°	1518.9	1517.3	1515.6	1513.4	1510.3	1507.2	1504.1	1501.0
20°	1482.1	1479.8	1477.5	1474.5	1470.7	1467.0	1463.1	1459.4
22.5°	1441.3	1437.8	1434.4	1431.1	1428.0	1424.9	1421.9	1418.8
25°	1375.3	1370.4	1365.5	1361.6	1358.7	1355.8	1352.9	1350.1
27.5°	1308.2	1302.1	1296.1	1290.9	1286.8	1282.6	1278.5	1274.3
30°	1260.0	1252.9	1245.6	1239.7	1235.0	1230.4	1225.8	1221.2
32.5°	1210.9	1202.5	1194.1	1187.7	1183.3	1178.9	1174.5	1170.1
35°	1137.7	1127.9	1118.0	1110.5	1105.3	1100.1	1094.9	1089.6
37.5°	1059.1	1048.1	1037.1	1029.0	1023.8	1018.6	1013.4	1008.2
40°	1006.8	994.7	982.5	973.8	968.6	963.4	958.2	953.0
42.5°	955.3	942.9	930.5	921.6	916.2	910.8	905.3	899.8
45°	876.4	862.3	848.1	838.4	833.2	828.0	822.8	817.6
47.5°	797.0	782.4	767.7	757.4	751.7	746.0	740.2	734.5
50°	744.4	729.9	715.4	705.5	700.0	694.5	689.0	683.5
52.5°	691.9	677.2	662.4	652.2	646.5	640.8	635.0	629.3
55°	614.3	599.3	584.2	574.0	568.5	563.0	557.5	552.0
57.5°	538.7	523.3	508.1	498.4	494.2	490.0	485.8	481.7
60°	488.0	473.0	458.0	448.2	443.5	438.9	434.2	429.6
62.5°	438.3	424.4	410.5	401.7	398.0	394.4	390.6	386.9
65°	367.0	354.6	342.1	334.1	330.7	327.2	323.8	320.2
67.5°	301.5	290.7	280.1	272.8	269.0	265.1	261.3	257.5
70°	256.9	247.4	237.8	231.6	228.7	225.8	222.9	220.0
72.5°	217.0	208.8	200.6	195.3	192.6	190.0	187.3	184.6
75°	159.9	153.2	146.5	142.4	140.6	138.8	137.1	135.4
77.5°	113.1	109.2	105.3	103.1	102.6	102.1	101.6	101.0
80°	86.8	85.9	85.0	84.5	84.2	83.9	83.6	83.3
82.5°	67.5	66.9	66.2	65.7	65.5	65.1	64.9	64.6
85°	39.2	38.6	38.1	37.7	37.7	37.7	37.7	37.7
87.5°	15.6	15.4	15.2	15.2	15.6	15.8	16.1	16.3
90°	7.1	7.5	7.9	8.2	8.2	8.4	8.5	8.6
92.5°	6.8	7.3	7.7	7.8	7.9	7.9	7.9	8.0
95°	7.1	7.5	7.9	8.1	8.2	8.2	8.3	8.3
97.5°	7.7	7.7	7.7	7.8	7.9	7.9	8.0	8.1
100°	10.5	9.4	8.3	7.8	7.9	7.9	8.0	8.1
102.5°	37.6	25.8	14.1	8.2	8.2	8.2	8.3	8.3
105°	91.1	91.6	92.2	91.3	89.0	86.7	84.4	82.1
107.5°	112.7	112.9	113.2	113.5	113.7	114.0	114.2	114.5
110°	127.3	127.4	127.6	127.8	127.9	128.2	128.3	128.5



TEST NUMBER: P332988-930

CATALOG NUMBER: S124RDIP-S1195D365U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	141.5	141.5	141.5	141.6	141.9	142.1	142.4	142.6
115°	162.7	162.9	163.1	163.1	163.1	163.1	163.1	163.1
117.5°	184.1	184.1	184.1	184.0	184.0	184.0	184.0	183.9
120°	197.3	197.5	197.6	197.6	197.5	197.3	197.2	197.1
122.5°	210.3	210.4	210.5	210.5	210.3	210.3	210.1	210.0
125°	228.6	228.8	228.9	229.1	229.2	229.3	229.3	229.3
127.5°	246.7	246.6	246.6	246.5	246.5	246.5	246.4	246.4
130°	257.7	257.8	257.9	257.9	257.9	257.9	257.9	257.9
132.5°	268.6	268.6	268.7	268.7	268.6	268.6	268.6	268.5
135°	283.5	283.6	283.7	283.9	284.0	284.1	284.3	284.4
137.5°	297.8	298.0	298.1	298.2	298.1	298.1	298.0	298.0
140°	306.6	306.9	307.0	307.2	307.3	307.3	307.4	307.4
142.5°	314.9	315.0	315.1	315.2	315.3	315.3	315.3	315.3
145°	326.6	326.7	326.7	326.8	326.9	327.1	327.2	327.3
147.5°	336.9	337.0	337.0	337.0	337.1	337.1	337.2	337.3
150°	343.5	343.5	343.5	343.5	343.6	343.6	343.6	343.7
152.5°	349.2	349.3	349.4	349.4	349.4	349.4	349.4	349.3
155°	356.9	357.2	357.4	357.5	357.3	357.1	356.9	356.7
157.5°	363.6	363.9	364.3	364.3	363.9	363.6	363.3	363.0
160°	367.9	368.3	368.6	368.6	368.3	367.9	367.5	367.0
162.5°	371.3	371.7	372.1	372.0	371.6	371.2	370.7	370.3
165°	376.2	376.7	377.2	377.2	376.6	376.0	375.4	374.9
167.5°	379.8	380.3	380.8	380.8	380.2	379.5	378.9	378.3
170°	382.0	382.5	382.9	382.9	382.3	381.6	381.0	380.3
172.5°	383.4	383.8	384.3	384.3	383.6	382.9	382.2	381.5
175°	385.0	385.6	386.1	386.0	385.2	384.5	383.7	382.9
177.5°	385.6	386.0	386.5	386.3	385.7	385.1	384.5	383.8
180°	385.2	385.2	385.2	385.2	385.2	385.2	385.2	385.2

(END OF REPORT)