

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P832289

Luminaire Tested: S123RDIP-S560D805U850-4F0-1E-UDD-G4

Issue Date: 05/03/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P832289  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-2, G3-1807-864-17)  
Test Lab: INNOVATION CENTER  
Issue Date: 05/03/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S560D805U850-4F0-1E-UDD-G4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 560 LUMENS PER FOOT, GRAZE OPTIC  
UPLIGHT 805 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5909.7 lumens  
Efficiency: N/A  
Efficacy: 147.0 lumens/watt  
Spacing Criteria (0/90/45): 0.55 / 1.17 / 0.8  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 40.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P832289

CATALOG NUMBER: S123RDIP-S560D805U850-4F0-1E-UDD-G4

### Luminous Intensity Polar Plot





TEST NUMBER: P832289

CATALOG NUMBER: S123RDIP-S560D805U850-4F0-1E-UDD-G4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	45				45
1	97	93	90	87	89	86	83	80	72	70	68	59	57	56	47	46	45				40	
2	89	82	77	72	82	76	71	67	64	60	57	53	50	48	42	41	39				35	
3	82	73	66	61	75	68	62	57	57	53	49	47	44	42	38	36	34				30	
4	76	65	58	52	69	61	54	49	51	46	43	43	39	36	35	32	30				27	
5	70	59	51	45	64	54	48	43	46	41	37	39	35	32	32	29	27				24	
6	64	53	45	40	59	49	43	38	42	37	33	36	32	29	29	27	24				22	
7	60	48	41	35	55	45	38	34	39	33	30	33	29	26	27	24	22				20	
8	56	44	37	32	51	41	35	30	35	30	27	30	26	23	25	22	20				18	
9	52	41	33	29	48	38	31	27	33	28	24	28	24	21	23	21	19				16	
10	49	37	30	26	45	35	29	25	30	25	22	26	22	20	22	19	17				15	

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°	135°	180°
0°	21801	21801	21801	21801	21801
5°	25887	25061	21939	17735	16466
10°	23455	25456	21829	14210	12190
15°	16148	21826	21599	11614	9643
20°	11234	16804	21165	9793	8475
25°	8561	12807	20535	8704	7811
30°	7452	10239	19745	8081	7235
35°	6842	8637	18628	7557	6711
40°	6243	7713	17165	7043	6232
45°	5638	7054	15586	6555	5751
50°	5117	6507	13725	6077	5159
55°	4628	5977	11937	5611	4425
60°	4148	5436	10370	5096	4183
65°	3828	4821	8925	4579	3955
70°	3109	4170	7789	4142	3213
75°	2728	3315	6596	3435	2832
80°	2473	2808	5405	2882	2678
85°	2260	2458	4100	2618	2458

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 80°  
 Vertical Angle: 45°  
 Luminance: 16446 cd/sqm



TEST NUMBER: P832289

CATALOG NUMBER: S123RDIP-S560D805U850-4F0-1E-UDD-G4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	184.6	3.1
10°-20°	427.2	7.2
20°-30°	490.1	8.3
30°-40°	483.1	8.2
40°-50°	426.0	7.2
50°-60°	327.8	5.5
60°-70°	215.5	3.6
70°-80°	104.7	1.8
80°-90°	28.8	0.5
90°-100°	232.4	3.9
100°-110°	680.5	11.5
110°-120°	664.5	11.2
120°-130°	529.2	9.0
130°-140°	417.5	7.1
140°-150°	311.5	5.3
150°-160°	217.2	3.7
160°-170°	127.6	2.2
170°-180°	41.5	0.7
0°-30°	1102.0	18.6
0°-40°	1585.1	26.8
0°-60°	2338.9	39.6
0°-90°	2687.8	45.5
90°-120°	1577.4	26.7
90°-150°	2835.6	48.0
90°-180°	3222.0	54.5
0°-180°	5909.7	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	2025	2025	2025	2025	2025	
5°	2396	2319	2030	1641	1524	219
15°	1449	1959	1938	1042	865	409
25°	721	1078	1729	733	658	340
35°	521	657	1418	575	511	325
45°	370	463	1024	431	378	288
55°	247	318	636	299	236	221
65°	150	189	350	180	155	147
75°	66	80	159	83	68	71
85°	18	20	33	21	20	19
90°	25	22	2	22	25	14
95°	101	514	30	514	101	163
105°	1103	697	101	697	1103	1100
115°	1341	533	178	533	1341	1308
125°	1058	498	247	498	1058	957
135°	858	491	290	491	858	665
145°	670	485	330	485	670	426
155°	556	469	375	469	556	259
165°	485	449	410	449	485	138
175°	436	431	427	431	436	42
180°	428	428	428	428	428	



TEST NUMBER: P832289

CATALOG NUMBER: S123RDIP-S560D805U850-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2025.4	2025.4	2025.4	2025.4	2025.4	2025.4	2025.4	2025.4	2025.4	2025.4	2025.4
2.5°	2244.7	2237.6	2230.6	2228.5	2226.4	2219.8	2213.1	2198.2	2183.2	2167.9	2152.5
5°	2395.8	2396.6	2397.5	2395.4	2393.3	2384.6	2375.9	2357.6	2339.3	2319.4	2299.5
7.5°	2349.3	2362.6	2375.9	2378.4	2380.9	2387.5	2394.2	2390.0	2385.8	2378.4	2370.9
10°	2145.9	2145.0	2144.2	2159.1	2174.1	2218.5	2262.9	2285.8	2308.6	2329.0	2349.3
12.5°	1813.7	1814.9	1816.2	1865.2	1914.2	1956.1	1998.0	2056.2	2114.3	2177.0	2239.7
15°	1449.1	1469.5	1489.8	1533.4	1577.0	1640.1	1703.2	1781.3	1859.4	1958.6	2057.8
17.5°	1190.0	1198.7	1207.5	1249.4	1291.3	1351.1	1410.9	1499.4	1587.8	1715.7	1843.6
20°	980.7	988.6	996.5	1026.8	1057.1	1114.4	1171.7	1256.0	1340.3	1467.0	1593.6
22.5°	818.8	834.2	849.5	869.9	890.2	931.8	973.3	1059.2	1145.2	1260.6	1376.0
25°	720.8	727.9	734.9	752.4	769.8	809.7	849.5	906.4	963.3	1078.3	1193.3
27.5°	654.4	656.5	658.5	671.4	684.3	710.0	735.8	788.5	841.2	935.9	1030.6
30°	599.6	603.3	607.1	617.0	627.0	645.7	664.4	701.7	739.1	823.8	908.5
32.5°	557.2	559.3	561.4	569.7	578.0	591.7	605.4	634.9	664.4	729.1	793.9
35°	520.7	521.1	521.5	527.7	534.0	547.3	560.5	585.0	609.5	657.3	705.0
37.5°	479.2	482.1	485.0	489.5	494.1	505.7	517.4	537.3	557.2	596.7	636.1
40°	444.3	446.8	449.3	454.7	460.1	469.2	478.3	496.6	514.9	548.9	583.0
42.5°	409.4	411.1	412.7	418.1	423.5	434.7	445.9	460.5	475.0	503.2	531.5
45°	370.4	374.5	378.7	384.5	390.3	399.9	409.4	424.4	439.3	463.4	487.5
47.5°	338.0	340.1	342.1	347.1	352.1	363.7	375.4	388.6	401.9	424.4	446.8
50°	305.6	306.4	307.3	311.8	316.4	326.8	337.2	352.5	367.9	388.6	409.4
52.5°	274.9	277.0	279.0	283.6	288.2	295.2	302.3	318.1	333.8	354.2	374.5
55°	246.6	247.9	249.1	252.5	255.8	264.1	272.4	286.1	299.8	318.5	337.2
57.5°	220.1	221.7	223.4	225.9	228.4	235.8	243.3	255.4	267.4	286.1	304.8
60°	192.7	194.7	196.8	199.7	202.6	208.4	214.3	225.0	235.8	252.5	269.1
62.5°	172.7	173.1	173.6	176.1	178.5	182.7	186.8	195.6	204.3	220.9	237.5
65°	150.3	151.6	152.8	154.0	155.3	158.6	161.9	169.4	176.9	189.3	201.8
67.5°	127.1	128.3	129.5	131.6	133.7	136.6	139.5	144.5	149.5	161.1	172.7
70°	98.8	98.8	98.8	102.1	105.5	110.4	115.4	119.2	122.9	132.5	142.0
72.5°	80.6	81.0	81.4	81.8	82.2	85.1	88.0	94.3	100.5	106.3	112.1
75°	65.6	66.0	66.4	66.9	67.3	68.1	68.9	71.0	73.1	79.7	86.4
77.5°	52.3	52.7	53.1	53.6	54.0	54.8	55.6	56.5	57.3	59.8	62.3
80°	39.9	40.3	40.7	41.1	41.5	41.9	42.4	43.2	44.0	45.3	46.5
82.5°	29.1	29.1	29.1	29.1	29.1	29.9	30.7	30.7	30.7	31.6	32.4
85°	18.3	18.3	18.3	18.7	19.1	19.1	19.1	19.5	19.9	19.9	19.9
87.5°	8.3	7.9	7.5	7.9	8.3	8.3	8.3	8.7	9.1	9.1	9.1
90°	25.1	26.0	25.1	24.3	25.1	23.4	22.5	21.7	20.8	21.7	19.1
92.5°	46.0	47.7	46.8	50.3	52.0	58.1	66.8	85.8	120.5	161.3	178.6
95°	100.6	104.0	110.1	117.9	134.4	165.6	211.6	312.1	417.0	514.2	457.8
97.5°	206.4	215.9	236.7	269.6	327.7	426.6	541.0	717.0	817.6	790.7	590.5
100°	543.6	542.8	576.6	639.9	727.4	850.6	952.0	1022.2	991.9	821.1	554.9
102.5°	861.0	886.1	913.0	959.8	1023.1	1089.9	1138.4	1123.7	1000.6	764.7	502.9
105°	1102.9	1107.2	1135.0	1167.9	1207.8	1230.3	1213.9	1127.1	945.9	697.1	462.1
107.5°	1260.7	1270.2	1281.5	1297.1	1302.3	1278.9	1211.3	1075.1	867.9	637.3	432.7
110°	1350.8	1352.6	1354.3	1347.4	1323.1	1262.4	1153.2	993.6	795.1	587.9	417.0



TEST NUMBER: P832289

CATALOG NUMBER: S123RDIP-S560D805U850-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1369.1	1368.2	1359.5	1334.4	1285.0	1202.6	1076.9	913.0	731.8	554.9	408.4
115°	1341.3	1337.0	1319.6	1281.5	1216.5	1121.9	994.5	843.6	683.2	533.2	407.5
117.5°	1280.6	1274.5	1248.5	1206.1	1138.4	1040.4	923.4	789.9	651.1	518.5	408.4
120°	1200.8	1195.6	1174.8	1126.3	1057.8	970.2	866.2	749.1	626.9	509.0	411.8
122.5°	1126.3	1119.3	1095.9	1053.5	994.5	914.7	820.2	717.0	606.9	502.9	417.9
125°	1057.8	1051.7	1030.0	991.9	936.4	867.0	783.8	689.3	590.5	497.7	424.0
127.5°	998.8	993.6	973.7	940.7	890.4	826.3	750.0	664.2	574.8	495.1	430.9
130°	950.3	943.3	925.1	893.9	848.0	789.0	718.8	640.7	562.7	492.5	437.9
132.5°	902.6	898.3	882.6	851.4	808.9	753.5	689.3	619.1	551.4	491.6	443.1
135°	857.5	851.4	835.8	809.8	767.3	717.9	661.6	600.0	541.9	490.7	448.3
137.5°	809.8	804.6	791.6	764.7	728.3	684.1	633.8	581.8	533.2	489.0	451.7
140°	759.5	760.4	746.5	722.2	689.3	652.0	610.4	566.2	525.4	488.1	455.2
142.5°	712.7	713.6	701.4	680.6	653.7	622.5	587.9	551.4	518.5	486.4	457.8
145°	670.2	668.5	661.6	643.3	621.7	596.5	568.8	540.2	512.4	484.7	458.7
147.5°	633.8	632.9	626.0	613.0	595.7	577.4	554.0	530.6	506.4	482.1	458.7
150°	602.6	602.6	597.4	587.9	574.8	558.4	540.2	520.2	500.3	478.6	458.7
152.5°	576.6	576.6	574.0	565.3	555.8	542.8	527.2	510.7	493.3	474.3	456.1
155°	555.8	554.9	553.2	546.2	538.4	528.0	515.0	501.1	486.4	469.1	454.3
157.5°	535.8	535.8	534.1	528.9	522.0	513.3	502.9	490.7	478.6	464.7	451.7
160°	516.8	517.6	517.6	512.4	506.4	500.3	491.6	482.1	470.8	459.5	450.0
162.5°	499.4	500.3	500.3	495.9	492.5	487.3	479.5	471.7	463.0	454.3	446.5
165°	484.7	484.7	485.5	482.1	478.6	474.3	468.2	463.0	456.1	449.1	443.1
167.5°	469.9	469.9	470.8	468.2	466.5	463.0	459.5	455.2	449.1	443.9	439.6
170°	456.9	456.9	457.8	456.1	455.2	453.5	450.0	447.4	443.1	438.7	436.1
172.5°	444.8	445.7	447.4	445.7	445.7	444.8	442.2	440.5	437.0	434.4	433.5
175°	436.1	437.0	437.9	437.0	437.0	437.0	435.3	434.4	432.7	430.9	430.9
177.5°	430.1	430.1	431.8	430.9	431.8	431.8	430.9	430.1	429.2	428.3	429.2
180°	428.3	428.3	428.3	428.3	428.3	428.3	428.3	428.3	428.3	428.3	428.3



TEST NUMBER: P832289

CATALOG NUMBER: S123RDIP-S560D805U850-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2025.4	2025.4	2025.4	2025.4	2025.4	2025.4	2025.4	2025.4	2025.4	2025.4	2025.4
2.5°	2150.4	2148.3	2128.4	2108.5	2089.0	2069.5	2054.9	2040.4	2015.9	1991.4	1976.0
5°	2283.7	2267.9	2236.4	2204.8	2157.5	2110.1	2070.3	2030.4	1979.8	1929.1	1886.8
7.5°	2358.0	2345.2	2307.0	2268.8	2206.1	2143.4	2081.1	2018.8	1944.1	1869.3	1805.4
10°	2360.1	2370.9	2339.3	2307.8	2237.2	2166.6	2081.9	1997.2	1896.7	1796.2	1713.6
12.5°	2286.2	2332.7	2326.1	2319.4	2247.6	2175.7	2072.8	1969.8	1846.5	1723.2	1619.8
15°	2147.9	2238.0	2264.6	2291.2	2231.8	2172.4	2055.3	1938.2	1793.3	1648.4	1529.7
17.5°	1969.8	2096.0	2166.2	2236.4	2193.2	2150.0	2021.7	1893.4	1730.2	1567.0	1437.9
20°	1758.9	1924.1	2034.2	2144.2	2128.4	2112.6	1980.2	1847.7	1671.7	1495.6	1355.7
22.5°	1550.4	1724.8	1876.8	2028.8	2045.0	2061.1	1927.4	1793.7	1601.1	1408.4	1266.0
25°	1370.6	1547.9	1729.0	1910.0	1946.5	1983.1	1856.0	1729.0	1529.3	1329.5	1187.9
27.5°	1199.2	1367.7	1567.0	1766.3	1832.8	1899.2	1783.0	1666.7	1458.7	1250.6	1109.5
30°	1059.2	1209.9	1413.4	1616.9	1709.5	1802.1	1695.3	1588.6	1382.3	1175.9	1037.6
32.5°	928.8	1063.8	1268.1	1472.4	1579.9	1687.5	1595.3	1503.1	1304.6	1106.1	969.5
35°	825.9	946.7	1137.3	1327.9	1448.3	1568.7	1493.1	1417.6	1223.7	1029.7	900.6
37.5°	737.4	838.7	1017.7	1196.7	1324.5	1452.4	1389.3	1326.2	1143.9	961.6	839.6
40°	664.4	745.7	912.2	1078.7	1204.1	1329.5	1275.6	1221.6	1058.4	895.2	781.0
42.5°	601.7	671.8	821.3	970.8	1085.8	1200.8	1165.1	1129.4	981.6	833.8	727.9
45°	546.4	605.4	737.0	868.6	974.5	1080.4	1052.2	1023.9	896.5	769.0	671.8
47.5°	497.4	548.1	665.6	783.1	878.2	973.3	947.1	921.0	815.5	710.0	621.6
50°	452.6	495.8	593.8	691.8	777.3	862.8	841.2	819.6	732.4	645.3	568.9
52.5°	410.2	445.9	534.0	622.0	690.9	759.9	743.2	726.6	659.4	592.1	522.8
55°	370.0	402.8	477.1	551.4	610.4	669.3	652.7	636.1	583.8	531.5	470.4
57.5°	333.4	362.1	422.3	482.5	529.4	576.3	568.4	560.5	516.9	473.3	423.1
60°	294.8	320.5	372.5	424.4	462.1	499.9	490.8	481.7	450.5	419.4	376.2
62.5°	260.3	283.2	324.7	366.2	396.9	427.7	421.0	414.4	390.7	367.1	331.3
65°	224.2	246.6	280.3	313.9	338.0	362.1	356.3	350.4	332.6	314.7	286.1
67.5°	191.4	210.1	239.2	268.2	284.4	300.6	297.3	294.0	280.3	266.6	244.1
70°	158.2	174.4	198.5	222.6	233.8	245.0	246.2	247.5	235.0	222.6	205.9
72.5°	125.0	137.9	160.3	182.7	191.4	200.1	199.7	199.3	191.8	184.4	169.4
75°	95.9	105.5	122.9	140.3	147.8	155.3	157.0	158.6	151.6	144.5	136.2
77.5°	68.9	75.6	88.9	102.1	110.4	118.8	119.6	120.4	117.1	113.8	105.9
80°	48.6	50.7	59.0	67.3	76.0	84.7	86.0	87.2	83.9	80.6	75.6
82.5°	33.6	34.9	37.8	40.7	47.8	54.8	56.5	58.1	56.5	54.8	49.4
85°	20.3	20.8	22.0	23.3	26.6	29.9	31.6	33.2	32.4	31.6	28.7
87.5°	9.1	9.1	9.6	10.0	10.8	11.6	13.7	15.8	14.5	13.3	12.0
90°	16.5	13.9	11.3	9.5	7.8	5.2	3.5	1.7	3.5	5.2	7.8
92.5°	133.5	87.6	59.8	44.2	35.5	27.7	19.1	13.0	19.1	27.7	35.5
95°	315.6	186.4	112.7	78.9	56.4	41.6	32.1	29.5	32.1	41.6	56.4
97.5°	351.2	201.2	128.3	91.0	68.5	55.5	47.7	46.8	47.7	55.5	68.5
100°	326.9	198.6	137.9	104.0	83.2	71.1	65.0	64.2	65.0	71.1	83.2
102.5°	306.1	202.0	149.1	118.8	100.6	89.3	84.1	82.4	84.1	89.3	100.6
105°	298.3	209.0	162.1	135.3	118.8	108.4	103.2	100.6	103.2	108.4	118.8
107.5°	296.5	220.2	178.6	153.5	137.9	127.5	122.3	119.7	122.3	127.5	137.9
110°	300.9	235.0	196.0	171.7	156.9	147.4	143.1	140.5	143.1	147.4	156.9





TEST NUMBER: P832289

CATALOG NUMBER: S123RDIP-S560D805U850-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	309.5	249.7	214.2	190.7	176.0	166.5	162.1	159.5	162.1	166.5	176.0
115°	319.1	266.2	233.2	209.8	195.1	186.4	181.2	177.7	181.2	186.4	195.1
117.5°	331.2	283.5	250.6	228.9	212.4	204.6	200.3	196.0	200.3	204.6	212.4
120°	345.1	300.0	268.8	247.1	230.6	222.0	217.6	215.0	217.6	222.0	230.6
122.5°	358.1	317.3	287.0	263.6	248.0	238.4	234.1	231.5	234.1	238.4	248.0
125°	372.0	333.8	303.5	280.1	263.6	254.0	248.8	247.1	248.8	254.0	263.6
127.5°	383.2	348.5	319.1	295.7	277.5	267.9	261.8	259.2	261.8	267.9	277.5
130°	394.5	361.6	332.9	309.5	291.3	280.9	273.1	270.5	273.1	280.9	291.3
132.5°	404.9	372.8	345.1	322.5	304.3	291.3	282.7	279.2	282.7	291.3	304.3
135°	413.6	384.1	357.2	333.8	315.6	302.6	293.1	289.6	293.1	302.6	315.6
137.5°	420.5	391.9	365.9	344.2	326.0	312.1	302.6	299.1	302.6	312.1	326.0
140°	425.7	399.7	374.6	352.9	335.5	321.7	313.0	308.7	313.0	321.7	335.5
142.5°	430.9	405.8	381.5	361.6	344.2	332.1	322.5	319.1	322.5	332.1	344.2
145°	434.4	411.0	388.4	368.5	353.8	340.7	332.9	330.3	332.9	340.7	353.8
147.5°	437.0	415.3	394.5	377.2	362.4	351.2	343.3	341.6	343.3	351.2	362.4
150°	437.9	419.6	399.7	384.1	372.0	360.7	353.8	352.9	353.8	360.7	372.0
152.5°	439.6	422.2	405.8	391.0	380.6	371.1	364.2	364.2	364.2	371.1	380.6
155°	439.6	425.7	411.0	398.8	389.3	380.6	375.4	375.4	375.4	380.6	389.3
157.5°	440.5	427.4	415.3	405.8	397.1	389.3	385.0	384.1	385.0	389.3	397.1
160°	440.5	430.1	419.6	411.0	404.9	398.0	394.5	394.5	394.5	398.0	404.9
162.5°	439.6	430.9	422.2	415.3	410.1	404.9	402.3	402.3	402.3	404.9	410.1
165°	437.9	431.8	424.8	418.8	415.3	411.0	409.2	410.1	409.2	411.0	415.3
167.5°	437.0	431.8	426.6	422.2	419.6	416.2	415.3	416.2	415.3	416.2	419.6
170°	434.4	430.9	426.6	424.8	423.1	420.5	419.6	421.4	419.6	420.5	423.1
172.5°	433.5	430.9	427.4	426.6	425.7	424.0	424.0	424.8	424.0	424.0	425.7
175°	431.8	430.1	428.3	427.4	427.4	425.7	426.6	427.4	426.6	425.7	427.4
177.5°	430.9	429.2	428.3	428.3	428.3	427.4	428.3	429.2	428.3	427.4	428.3
180°	428.3	428.3	428.3	428.3	428.3	428.3	428.3	428.3	428.3	428.3	428.3



TEST NUMBER: P832289

CATALOG NUMBER: S123RDIP-S560D805U850-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2025.4	2025.4	2025.4	2025.4	2025.4	2025.4	2025.4	2025.4	2025.4	2025.4	2025.4
2.5°	1960.7	1937.0	1913.3	1896.3	1879.3	1858.1	1836.9	1836.1	1835.3	1819.5	1803.7
5°	1844.4	1803.3	1762.2	1721.9	1681.6	1641.4	1601.1	1592.0	1582.8	1569.1	1555.4
7.5°	1741.4	1675.8	1610.2	1558.7	1507.2	1467.0	1426.7	1399.3	1371.9	1350.7	1329.5
10°	1631.0	1549.6	1468.2	1405.9	1343.6	1300.1	1256.5	1224.9	1193.3	1178.4	1163.4
12.5°	1516.4	1427.9	1339.5	1278.5	1217.4	1165.1	1112.8	1084.1	1055.5	1034.7	1014.0
15°	1410.9	1315.8	1220.7	1156.0	1091.2	1042.2	993.2	964.6	935.9	915.1	894.4
17.5°	1308.8	1212.9	1116.9	1051.3	985.7	941.3	896.9	869.1	841.2	828.4	815.5
20°	1215.8	1119.0	1022.3	960.4	898.5	854.9	811.3	796.4	781.4	769.4	757.4
22.5°	1123.6	1030.6	937.6	878.2	818.8	787.3	755.7	743.7	731.6	722.5	713.3
25°	1046.4	953.8	861.2	809.3	757.4	732.9	708.4	700.5	692.6	683.5	674.3
27.5°	968.3	880.3	792.2	750.7	709.2	689.3	669.3	659.4	649.4	641.9	634.5
30°	899.4	818.0	736.6	702.1	667.7	650.2	632.8	622.0	611.2	604.1	597.1
32.5°	832.9	760.7	688.4	659.0	629.5	612.4	595.4	585.0	574.7	566.4	558.1
35°	771.5	708.8	646.1	619.1	592.1	575.1	558.1	547.7	537.3	529.0	520.7
37.5°	717.5	660.6	603.7	578.4	553.1	538.1	523.2	512.4	501.6	492.9	484.1
40°	666.8	616.6	566.4	541.9	517.4	501.2	485.0	475.4	465.9	458.0	450.1
42.5°	622.0	575.9	529.8	505.7	481.7	466.3	450.9	439.7	428.5	423.9	419.4
45°	574.7	534.0	493.3	470.0	446.8	430.6	414.4	404.8	395.3	391.1	387.0
47.5°	533.1	495.4	457.6	434.7	411.9	397.4	382.8	375.4	367.9	362.1	356.3
50°	492.5	455.9	419.4	397.4	375.4	362.9	350.4	341.3	332.2	328.0	323.9
52.5°	453.4	420.2	387.0	364.6	342.1	330.1	318.1	310.2	302.3	293.6	284.8
55°	409.4	380.3	351.3	331.3	311.4	299.0	286.5	277.4	268.2	259.1	250.0
57.5°	372.9	344.2	315.6	297.7	279.9	267.8	255.8	245.8	235.8	228.4	220.9
60°	333.0	308.1	283.2	265.7	248.3	236.7	225.0	215.5	205.9	202.2	198.5
62.5°	295.6	272.4	249.1	233.8	218.4	207.2	196.0	189.8	183.5	181.0	178.5
65°	257.4	237.5	217.6	203.5	189.3	179.8	170.2	167.3	164.4	162.4	160.3
67.5°	221.7	204.7	187.7	175.2	162.8	156.1	149.5	146.2	142.8	140.3	137.9
70°	189.3	174.4	159.4	148.6	137.9	131.6	125.4	122.5	119.6	115.0	110.4
72.5°	154.5	142.8	131.2	122.9	114.6	109.2	103.8	98.0	92.2	88.0	83.9
75°	127.9	116.3	104.6	96.7	88.9	82.6	76.4	74.3	72.2	71.0	69.8
77.5°	98.0	88.0	78.1	71.8	65.6	62.7	59.8	58.5	57.3	56.9	56.5
80°	70.6	62.3	54.0	50.7	47.3	46.5	45.7	44.8	44.0	43.6	43.2
82.5°	44.0	39.9	35.7	34.9	34.0	33.6	33.2	32.8	32.4	32.0	31.6
85°	25.7	24.1	22.4	22.0	21.6	21.2	20.8	20.8	20.8	20.8	20.8
87.5°	10.8	10.8	10.8	10.8	10.8	10.8	10.8	10.8	10.8	10.4	10.0
90°	9.5	11.3	13.9	16.5	19.1	21.7	20.8	21.7	22.5	23.4	25.1
92.5°	44.2	59.8	87.6	133.5	178.6	161.3	120.5	85.8	66.8	58.1	52.0
95°	78.9	112.7	186.4	315.6	457.8	514.2	417.0	312.1	211.6	165.6	134.4
97.5°	91.0	128.3	201.2	351.2	590.5	790.7	817.6	717.0	541.0	426.6	327.7
100°	104.0	137.9	198.6	326.9	554.9	821.1	991.9	1022.2	952.0	850.6	727.4
102.5°	118.8	149.1	202.0	306.1	502.9	764.7	1000.6	1123.7	1138.4	1089.9	1023.1
105°	135.3	162.1	209.0	298.3	462.1	697.1	945.9	1127.1	1213.9	1230.3	1207.8
107.5°	153.5	178.6	220.2	296.5	432.7	637.3	867.9	1075.1	1211.3	1278.9	1302.3
110°	171.7	196.0	235.0	300.9	417.0	587.9	795.1	993.6	1153.2	1262.4	1323.1



TEST NUMBER: P832289

CATALOG NUMBER: S123RDIP-S560D805U850-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	190.7	214.2	249.7	309.5	408.4	554.9	731.8	913.0	1076.9	1202.6	1285.0
115°	209.8	233.2	266.2	319.1	407.5	533.2	683.2	843.6	994.5	1121.9	1216.5
117.5°	228.9	250.6	283.5	331.2	408.4	518.5	651.1	789.9	923.4	1040.4	1138.4
120°	247.1	268.8	300.0	345.1	411.8	509.0	626.9	749.1	866.2	970.2	1057.8
122.5°	263.6	287.0	317.3	358.1	417.9	502.9	606.9	717.0	820.2	914.7	994.5
125°	280.1	303.5	333.8	372.0	424.0	497.7	590.5	689.3	783.8	867.0	936.4
127.5°	295.7	319.1	348.5	383.2	430.9	495.1	574.8	664.2	750.0	826.3	890.4
130°	309.5	332.9	361.6	394.5	437.9	492.5	562.7	640.7	718.8	789.0	848.0
132.5°	322.5	345.1	372.8	404.9	443.1	491.6	551.4	619.1	689.3	753.5	808.9
135°	333.8	357.2	384.1	413.6	448.3	490.7	541.9	600.0	661.6	717.9	767.3
137.5°	344.2	365.9	391.9	420.5	451.7	489.0	533.2	581.8	633.8	684.1	728.3
140°	352.9	374.6	399.7	425.7	455.2	488.1	525.4	566.2	610.4	652.0	689.3
142.5°	361.6	381.5	405.8	430.9	457.8	486.4	518.5	551.4	587.9	622.5	653.7
145°	368.5	388.4	411.0	434.4	458.7	484.7	512.4	540.2	568.8	596.5	621.7
147.5°	377.2	394.5	415.3	437.0	458.7	482.1	506.4	530.6	554.0	577.4	595.7
150°	384.1	399.7	419.6	437.9	458.7	478.6	500.3	520.2	540.2	558.4	574.8
152.5°	391.0	405.8	422.2	439.6	456.1	474.3	493.3	510.7	527.2	542.8	555.8
155°	398.8	411.0	425.7	439.6	454.3	469.1	486.4	501.1	515.0	528.0	538.4
157.5°	405.8	415.3	427.4	440.5	451.7	464.7	478.6	490.7	502.9	513.3	522.0
160°	411.0	419.6	430.1	440.5	450.0	459.5	470.8	482.1	491.6	500.3	506.4
162.5°	415.3	422.2	430.9	439.6	446.5	454.3	463.0	471.7	479.5	487.3	492.5
165°	418.8	424.8	431.8	437.9	443.1	449.1	456.1	463.0	468.2	474.3	478.6
167.5°	422.2	426.6	431.8	437.0	439.6	443.9	449.1	455.2	459.5	463.0	466.5
170°	424.8	426.6	430.9	434.4	436.1	438.7	443.1	447.4	450.0	453.5	455.2
172.5°	426.6	427.4	430.9	433.5	433.5	434.4	437.0	440.5	442.2	444.8	445.7
175°	427.4	428.3	430.1	431.8	430.9	430.9	432.7	434.4	435.3	437.0	437.0
177.5°	428.3	428.3	429.2	430.9	429.2	428.3	429.2	430.1	430.9	431.8	431.8
180°	428.3	428.3	428.3	428.3	428.3	428.3	428.3	428.3	428.3	428.3	428.3



TEST NUMBER: P832289

CATALOG NUMBER: S123RDIP-S560D805U850-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
0°	2025.4	2025.4	2025.4	2025.4
2.5°	1799.6	1795.4	1793.7	1792.1
5°	1542.5	1529.7	1526.8	1523.9
7.5°	1324.1	1318.7	1300.9	1283.0
10°	1146.8	1130.2	1122.8	1115.3
12.5°	998.6	983.2	980.7	978.3
15°	883.6	872.8	869.1	865.3
17.5°	808.0	800.5	796.0	791.4
20°	752.0	746.6	743.2	739.9
22.5°	709.2	705.0	702.6	700.1
25°	668.1	661.9	659.8	657.7
27.5°	629.1	623.7	621.6	619.5
30°	592.5	588.0	585.0	582.1
32.5°	552.7	547.3	545.6	543.9
35°	517.4	514.0	512.4	510.7
37.5°	480.0	475.8	473.3	470.9
40°	448.0	445.9	444.7	443.5
42.5°	415.6	411.9	411.5	411.1
45°	383.2	379.5	378.7	377.8
47.5°	352.9	349.6	349.2	348.8
50°	319.3	314.7	311.4	308.1
52.5°	280.7	276.5	273.6	270.7
55°	245.4	240.8	238.3	235.8
57.5°	218.8	216.7	215.5	214.3
60°	197.2	196.0	195.2	194.3
62.5°	177.3	176.1	176.1	176.1
65°	159.0	157.8	156.5	155.3
67.5°	135.4	132.9	132.5	132.0
70°	106.7	103.0	102.6	102.1
72.5°	83.5	83.0	82.2	81.4
75°	68.9	68.1	68.1	68.1
77.5°	55.6	54.8	54.8	54.8
80°	42.8	42.4	42.8	43.2
82.5°	31.6	31.6	31.1	30.7
85°	20.3	19.9	19.9	19.9
87.5°	10.0	10.0	10.0	10.0
90°	24.3	25.1	26.0	25.1
92.5°	50.3	46.8	47.7	46.0
95°	117.9	110.1	104.0	100.6
97.5°	269.6	236.7	215.9	206.4
100°	639.9	576.6	542.8	543.6
102.5°	959.8	913.0	886.1	861.0
105°	1167.9	1135.0	1107.2	1102.9
107.5°	1297.1	1281.5	1270.2	1260.7
110°	1347.4	1354.3	1352.6	1350.8



TEST NUMBER: P832289

CATALOG NUMBER: S123RDIP-S560D805U850-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
112.5°	1334.4	1359.5	1368.2	1369.1
115°	1281.5	1319.6	1337.0	1341.3
117.5°	1206.1	1248.5	1274.5	1280.6
120°	1126.3	1174.8	1195.6	1200.8
122.5°	1053.5	1095.9	1119.3	1126.3
125°	991.9	1030.0	1051.7	1057.8
127.5°	940.7	973.7	993.6	998.8
130°	893.9	925.1	943.3	950.3
132.5°	851.4	882.6	898.3	902.6
135°	809.8	835.8	851.4	857.5
137.5°	764.7	791.6	804.6	809.8
140°	722.2	746.5	760.4	759.5
142.5°	680.6	701.4	713.6	712.7
145°	643.3	661.6	668.5	670.2
147.5°	613.0	626.0	632.9	633.8
150°	587.9	597.4	602.6	602.6
152.5°	565.3	574.0	576.6	576.6
155°	546.2	553.2	554.9	555.8
157.5°	528.9	534.1	535.8	535.8
160°	512.4	517.6	517.6	516.8
162.5°	495.9	500.3	500.3	499.4
165°	482.1	485.5	484.7	484.7
167.5°	468.2	470.8	469.9	469.9
170°	456.1	457.8	456.9	456.9
172.5°	445.7	447.4	445.7	444.8
175°	437.0	437.9	437.0	436.1
177.5°	430.9	431.8	430.1	430.1
180°	428.3	428.3	428.3	428.3



TEST NUMBER: P832289

CATALOG NUMBER: S123RDIP-S560D805U850-4F0-1E-UDD-G4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.01	11.79	12.02	12.80	14.14	15.68	16.45	16.68	17.46	18.80
	3H	12.23	12.92	13.25	13.94	15.30	17.17	17.86	18.19	18.88	20.24
	4H	12.61	13.26	13.64	14.28	15.65	17.66	18.31	18.69	19.33	20.70
	6H	12.89	13.49	13.93	14.52	15.89	17.97	18.57	19.01	19.60	20.97
	8H	12.97	13.55	14.02	14.59	15.96	18.05	18.62	19.09	19.66	21.03
	12H	13.02	13.57	14.07	14.60	16.00	18.08	18.62	19.12	19.65	21.05
4H	2H	11.73	12.38	12.76	13.40	14.77	15.66	16.32	16.70	17.34	18.71
	3H	13.09	13.64	14.14	14.69	16.07	17.32	17.86	18.36	18.91	20.29
	4H	13.55	14.04	14.60	15.08	16.49	17.92	18.42	18.97	19.46	20.86
	6H	13.91	14.34	14.97	15.40	16.80	18.36	18.78	19.42	19.85	21.25
	8H	14.04	14.43	15.10	15.49	16.90	18.49	18.89	19.55	19.94	21.36
	12H	14.11	14.47	15.19	15.54	16.96	18.55	18.91	19.62	19.98	21.40
8H	4H	13.86	14.26	14.92	15.31	16.72	17.89	18.28	18.95	19.34	20.75
	6H	14.32	14.65	15.40	15.75	17.16	18.38	18.71	19.46	19.81	21.22
	8H	14.51	14.80	15.60	15.88	17.31	18.57	18.85	19.66	19.94	21.37
	12H	14.65	14.90	15.74	15.98	17.45	18.68	18.93	19.77	20.01	21.48
12H	4H	13.87	14.22	14.94	15.30	16.71	17.83	18.19	18.91	19.26	20.68
	6H	14.38	14.67	15.47	15.75	17.18	18.36	18.64	19.44	19.73	21.16
	8H	14.59	14.85	15.69	15.92	17.39	18.55	18.80	19.64	19.88	21.35