

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332948-930

Luminaire Tested: **S124RDIP-S795D1035U930-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332948-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIP-S795D1035U930-4F0-1E-UDD-F4  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5632.0 lumens  
Efficiency: N/A  
Efficacy: 108.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 52  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332948-930

CATALOG NUMBER: S124RDIP-S795D1035U930-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P332948-930

CATALOG NUMBER: S124RDIP-S795D1035U930-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	98	98	98	98	81	81	81	67	67	67	53	53	53	47				47
1	97	93	89	86	89	86	82	79	72	69	67	59	57	56	47	46	45				40	
2	89	82	76	71	81	75	70	66	63	59	56	52	49	47	42	40	38				34	
3	81	72	65	59	74	66	60	55	56	51	47	46	43	40	37	35	33				29	
4	74	64	56	50	68	59	52	47	50	45	41	41	38	34	33	31	29				25	
5	68	57	49	43	62	53	46	40	45	39	35	37	33	30	30	27	25				22	
6	63	51	43	37	58	47	40	35	40	35	31	34	30	26	27	24	22				19	
7	58	46	38	33	53	43	36	31	37	31	27	31	26	23	25	22	20				17	
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	23	20	18				15	
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	21	18	16				14	
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15				13	

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	9143	9143	9143
5°	9164	9052	9108
10°	9107	8943	8943
15°	9002	8756	8690
20°	8858	8508	8352
25°	8675	8219	8011
30°	8496	7914	7582
35°	8298	7597	7154
40°	8061	7238	6690
45°	7841	6882	6218
50°	7592	6469	5718
55°	7323	6042	5175
60°	7030	5572	4621
65°	6758	4988	4076
70°	6366	4338	3460
75°	5870	3599	2813
80°	5119	2738	2580
85°	4335	2492	2325



TEST NUMBER: P332948-930

CATALOG NUMBER: S124RDIP-S795D1035U930-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	106.4	1.9
10°-20°	296.7	5.3
20°-30°	428.4	7.6
30°-40°	485.6	8.6
40°-50°	468.9	8.3
50°-60°	389.9	6.9
60°-70°	269.3	4.8
70°-80°	136.5	2.4
80°-90°	37.3	0.7
90°-100°	299.2	5.3
100°-110°	622.8	11.1
110°-120°	557.8	9.9
120°-130°	469.2	8.3
130°-140°	391.2	6.9
140°-150°	298.9	5.3
150°-160°	210.1	3.7
160°-170°	123.6	2.2
170°-180°	40.2	0.7
0°-30°	831.5	14.8
0°-40°	1317.1	23.4
0°-60°	2176.0	38.6
0°-90°	2619.0	46.5
90°-120°	1479.8	26.3
90°-150°	2639.2	46.9
90°-180°	3013.0	53.5
0°-180°	5632.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1133	1133	1133	1133	1133	
5°	1131	1127	1117	1125	1124	107
15°	1077	1069	1048	1046	1040	303
25°	974	957	923	908	899	449
35°	842	813	771	742	726	526
45°	687	654	603	562	545	529
55°	520	484	429	386	368	465
65°	354	316	261	225	213	349
75°	188	156	115	96	90	199
85°	47	30	27	25	25	53
90°	1	6	15	16	17	4
95°	27	85	663	328	199	30
105°	95	138	534	1150	1145	102
115°	168	210	476	915	1100	166
125°	234	278	474	778	877	208
135°	278	330	470	691	785	214
145°	320	366	467	583	641	201
155°	364	393	454	514	536	168
165°	396	409	436	461	468	112
175°	413	414	418	423	422	39
180°	414	414	414	414	414	



TEST NUMBER: P332948-930

CATALOG NUMBER: S124RDIP-S795D1035U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1132.6	1132.6	1132.6	1132.6	1132.6	1132.6	1132.6	1132.6	1132.6	1132.6	1132.6
2.5°	1135.4	1134.7	1134.1	1133.5	1132.9	1131.7	1130.0	1128.4	1126.7	1124.9	1126.7
5°	1130.8	1130.1	1129.3	1128.5	1127.7	1126.3	1123.9	1121.6	1119.2	1117.0	1118.9
7.5°	1120.6	1119.8	1119.0	1118.2	1117.4	1115.5	1112.5	1109.5	1106.4	1103.4	1104.6
10°	1110.9	1109.9	1109.0	1108.0	1107.0	1104.8	1101.4	1097.9	1094.5	1091.0	1091.7
12.5°	1098.4	1097.3	1096.2	1095.0	1094.0	1091.4	1087.3	1083.1	1079.0	1075.0	1075.5
15°	1077.1	1075.4	1073.6	1071.9	1070.2	1066.9	1062.0	1057.2	1052.4	1047.6	1047.2
17.5°	1051.2	1048.7	1046.2	1043.7	1041.2	1037.1	1031.3	1025.5	1019.7	1013.9	1012.8
20°	1031.1	1028.6	1026.1	1023.6	1021.1	1016.6	1010.0	1003.5	996.9	990.3	988.8
22.5°	1008.9	1006.1	1003.3	1000.5	997.7	992.7	985.7	978.7	971.7	964.7	962.4
25°	973.9	970.4	966.9	963.4	960.0	954.3	946.4	938.5	930.6	922.7	919.4
27.5°	937.1	932.8	928.4	924.1	919.7	913.3	904.8	896.4	887.9	879.5	875.5
30°	911.4	906.6	901.8	897.0	892.2	885.3	876.2	867.2	858.0	849.0	844.2
32.5°	884.4	879.0	873.5	868.0	862.7	855.2	845.9	836.5	827.1	817.7	812.2
35°	842.0	835.9	829.7	823.5	817.4	809.5	799.9	790.2	780.6	770.9	764.4
37.5°	796.8	790.4	784.1	777.7	771.4	762.9	752.2	741.5	730.8	720.2	712.8
40°	764.9	758.6	752.2	745.8	739.5	730.8	719.7	708.8	697.8	686.8	678.7
42.5°	734.3	727.7	721.1	714.4	707.7	698.6	687.2	675.7	664.3	652.8	644.6
45°	686.8	679.7	672.5	665.4	658.3	649.0	637.4	625.8	614.2	602.8	593.3
47.5°	637.7	630.4	623.1	615.6	608.3	598.6	586.6	574.5	562.6	550.5	540.7
50°	604.5	597.0	589.4	581.9	574.4	564.4	552.1	539.8	527.4	515.1	505.5
52.5°	570.5	563.1	555.7	548.4	541.0	531.0	518.4	505.7	493.1	480.5	470.7
55°	520.3	512.6	504.9	497.2	489.5	479.4	466.8	454.3	441.8	429.3	419.2
57.5°	470.8	462.7	454.7	446.7	438.6	428.4	416.1	403.8	391.5	379.1	369.0
60°	435.4	427.6	420.0	412.2	404.5	394.5	382.1	369.8	357.5	345.1	335.1
62.5°	403.4	395.4	387.4	379.4	371.4	361.0	348.4	335.7	323.1	310.5	301.2
65°	353.8	345.5	337.2	329.0	320.7	310.4	298.0	285.7	273.4	261.1	252.7
67.5°	302.3	294.4	286.4	278.5	270.5	260.9	249.4	238.0	226.5	215.1	207.9
70°	269.7	261.6	253.5	245.4	237.3	227.8	216.8	205.8	194.9	183.8	177.5
72.5°	235.1	227.7	220.4	213.0	205.7	196.9	186.5	176.1	165.8	155.4	149.9
75°	188.2	181.1	173.9	166.8	159.6	151.6	142.5	133.5	124.4	115.4	110.9
77.5°	140.6	134.6	128.6	122.5	116.4	109.7	102.5	95.1	87.8	80.5	77.9
80°	110.1	104.5	99.0	93.4	87.8	82.1	76.3	70.5	64.7	58.9	58.4
82.5°	83.8	78.7	73.5	68.4	63.3	59.0	55.8	52.4	49.1	45.8	45.3
85°	46.8	43.0	39.1	35.3	31.4	29.2	28.6	28.0	27.5	26.9	26.5
87.5°	16.1	15.2	14.4	13.4	12.3	11.7	12.5	12.3	12.5	12.6	12.3
90°	0.8	2.4	4.9	5.7	6.5	6.5	11.4	11.4	13.0	14.7	13.9
92.5°	9.3	13.5	21.2	31.1	43.0	59.9	101.3	164.4	225.9	258.2	215.1
95°	26.8	29.3	37.4	48.0	67.6	101.7	172.5	306.1	500.6	663.3	682.1
97.5°	48.2	48.2	55.2	65.0	81.7	110.4	164.9	275.1	468.5	698.6	856.9
100°	61.9	61.9	67.6	77.3	92.8	118.9	166.9	258.9	424.9	654.4	862.7
102.5°	74.8	76.1	81.2	90.3	105.2	129.9	173.3	254.3	395.6	599.1	813.9
105°	95.2	97.7	101.7	111.5	126.1	149.8	188.8	256.4	370.3	533.9	725.2
107.5°	117.7	119.4	123.4	133.8	147.8	171.0	206.9	268.4	365.7	497.5	653.5
110°	132.6	134.3	138.4	148.1	162.8	184.7	220.5	277.5	367.0	485.1	617.8



TEST NUMBER: P332948-930

CATALOG NUMBER: S124RDIP-S795D1035U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	147.0	148.6	153.4	162.5	177.1	199.1	233.6	287.3	371.0	479.2	597.6
115°	167.7	170.1	175.8	183.9	199.4	221.4	254.0	302.8	378.5	476.1	578.7
117.5°	189.1	191.4	196.5	205.5	219.9	242.7	273.6	318.5	386.5	475.3	570.2
120°	203.5	205.1	210.8	219.7	233.6	256.4	287.3	329.6	392.3	475.3	565.7
122.5°	216.5	218.1	223.8	232.1	247.3	269.4	300.4	340.1	398.2	474.7	560.4
125°	233.6	236.8	241.7	250.7	266.1	288.9	318.2	355.7	407.0	473.7	551.9
127.5°	248.7	251.4	257.2	267.4	283.6	306.6	334.8	369.2	413.9	471.9	540.3
130°	257.2	260.5	266.9	279.2	294.6	318.2	345.9	377.6	419.1	471.2	533.1
132.5°	265.6	268.2	276.7	288.3	305.1	327.3	355.1	386.1	423.7	470.6	526.6
135°	277.5	280.8	288.9	302.8	319.8	341.0	367.9	397.2	430.6	469.6	516.8
137.5°	289.4	292.5	301.5	314.6	332.4	352.6	377.6	405.0	434.6	469.4	508.3
140°	297.9	300.4	309.3	323.1	340.2	359.8	384.2	410.2	437.9	468.8	503.9
142.5°	307.0	309.5	317.7	330.9	347.4	366.2	390.0	414.1	440.5	468.8	499.9
145°	319.8	322.3	330.4	341.9	357.3	375.2	396.4	418.3	442.0	467.2	493.3
147.5°	334.4	335.2	342.3	354.1	366.9	383.0	402.9	422.1	442.8	464.2	487.2
150°	343.5	344.3	350.8	360.6	372.8	388.2	406.2	424.0	442.8	462.3	482.7
152.5°	352.0	352.1	358.7	367.7	378.6	392.8	408.8	425.3	441.5	459.0	477.4
155°	363.8	364.6	369.5	377.6	386.6	398.8	412.6	426.5	439.5	454.2	469.6
157.5°	375.4	375.4	379.9	386.3	394.1	403.7	415.4	426.5	437.4	449.1	461.6
160°	382.5	382.5	385.8	391.5	398.0	407.0	416.7	426.5	435.5	445.2	455.8
162.5°	389.1	388.4	391.0	396.1	401.9	409.0	418.0	426.5	433.5	441.3	450.6
165°	396.4	396.4	398.0	402.1	406.2	411.0	418.3	424.9	429.7	435.5	442.0
167.5°	403.7	402.9	403.7	406.8	409.1	412.8	418.2	422.9	425.8	429.6	434.1
170°	407.0	406.2	407.0	409.4	411.0	413.4	417.5	421.6	423.2	425.7	428.9
172.5°	410.2	409.4	409.5	411.3	412.3	414.1	416.9	420.3	420.6	421.8	424.4
175°	413.4	412.6	412.6	413.4	414.3	414.3	415.9	418.3	417.5	417.5	419.1
177.5°	414.9	414.3	413.6	414.3	414.3	414.3	414.9	416.2	414.9	414.9	415.6
180°	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3



TEST NUMBER: P332948-930

CATALOG NUMBER: S124RDIP-S795D1035U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1132.6	1132.6	1132.6	1132.6	1132.6	1132.6	1132.6	1132.6
2.5°	1128.4	1130.0	1131.7	1132.5	1132.4	1132.2	1132.0	1131.9
5°	1120.8	1122.7	1124.7	1125.4	1125.0	1124.7	1124.3	1123.9
7.5°	1105.9	1107.2	1108.4	1108.6	1108.1	1107.4	1106.9	1106.2
10°	1092.5	1093.2	1094.1	1094.1	1093.2	1092.5	1091.7	1091.0
12.5°	1076.0	1076.4	1076.8	1076.5	1075.5	1074.4	1073.3	1072.2
15°	1046.8	1046.4	1046.0	1045.2	1043.8	1042.4	1041.1	1039.8
17.5°	1011.8	1010.7	1009.6	1008.0	1006.0	1004.0	1001.9	999.9
20°	987.2	985.7	984.1	982.2	979.7	977.1	974.6	972.2
22.5°	960.1	957.7	955.4	953.2	951.2	949.2	947.1	945.1
25°	916.2	912.9	909.6	907.0	905.1	903.2	901.2	899.3
27.5°	871.4	867.4	863.3	859.9	857.1	854.4	851.6	848.8
30°	839.4	834.5	829.7	825.7	822.7	819.6	816.5	813.4
32.5°	806.6	801.0	795.4	791.2	788.2	785.3	782.4	779.4
35°	757.8	751.3	744.8	739.7	736.3	732.8	729.3	725.9
37.5°	705.5	698.1	690.8	685.4	682.0	678.5	675.1	671.6
40°	670.7	662.5	654.4	648.7	645.2	641.7	638.3	634.8
42.5°	636.3	628.1	619.9	613.9	610.3	606.7	603.1	599.4
45°	583.8	574.4	564.9	558.5	555.0	551.5	548.0	544.6
47.5°	530.9	521.1	511.4	504.5	500.8	496.9	493.1	489.3
50°	495.9	486.2	476.5	469.9	466.3	462.6	458.9	455.3
52.5°	460.9	451.1	441.2	434.5	430.6	426.8	423.1	419.2
55°	409.2	399.2	389.2	382.4	378.7	375.0	371.4	367.7
57.5°	358.8	348.6	338.4	332.0	329.2	326.4	323.7	320.9
60°	325.1	315.1	305.1	298.5	295.5	292.4	289.3	286.2
62.5°	292.0	282.7	273.5	267.6	265.1	262.7	260.2	257.7
65°	244.4	236.2	227.9	222.6	220.3	217.9	215.6	213.4
67.5°	200.8	193.7	186.5	181.7	179.2	176.6	174.1	171.5
70°	171.1	164.8	158.4	154.3	152.4	150.4	148.5	146.6
72.5°	144.6	139.1	133.6	130.0	128.3	126.5	124.7	122.9
75°	106.5	102.1	97.6	94.8	93.7	92.5	91.3	90.2
77.5°	75.3	72.7	70.1	68.6	68.3	68.0	67.7	67.3
80°	57.8	57.2	56.7	56.3	56.1	55.8	55.7	55.5
82.5°	44.9	44.5	44.1	43.8	43.6	43.4	43.2	43.0
85°	26.1	25.8	25.4	25.1	25.1	25.1	25.1	25.1
87.5°	12.3	12.3	12.3	12.3	12.6	13.0	13.0	13.1
90°	14.7	15.5	16.3	16.3	17.1	17.9	17.1	17.1
92.5°	159.9	120.3	95.7	79.4	69.9	65.5	62.7	62.7
95°	603.1	477.0	367.9	288.9	249.1	223.8	209.2	198.6
97.5°	891.1	844.2	764.6	679.6	621.2	572.2	547.8	530.8
100°	981.6	997.8	958.0	897.7	827.0	777.3	752.8	746.4
102.5°	977.1	1057.8	1069.3	1044.2	1000.8	964.8	939.1	933.9
105°	911.6	1052.4	1132.9	1166.4	1168.0	1161.5	1150.1	1145.2
107.5°	818.6	968.6	1082.1	1154.6	1194.8	1213.4	1221.6	1223.7
110°	762.6	903.4	1021.5	1111.0	1168.8	1203.0	1217.6	1225.0





TEST NUMBER: P332948-930

CATALOG NUMBER: S124RDIP-S795D1035U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	721.6	846.1	957.7	1047.2	1112.8	1154.1	1174.7	1186.5
115°	680.4	780.6	875.8	953.9	1018.2	1067.1	1093.1	1099.6
117.5°	660.2	743.1	818.0	884.3	939.1	980.2	1006.5	1011.5
120°	651.1	726.8	792.0	849.7	896.1	932.0	953.1	962.1
122.5°	643.4	716.4	775.7	826.3	865.5	896.1	914.0	923.0
125°	630.0	699.9	756.1	800.9	833.5	857.0	872.5	877.4
127.5°	613.7	680.6	736.6	779.1	811.8	832.8	845.8	850.7
130°	600.7	665.0	720.3	763.4	796.8	817.2	830.2	835.1
132.5°	587.0	647.4	701.4	744.6	777.3	800.2	812.6	817.5
135°	568.1	621.0	670.7	711.3	744.0	766.7	779.8	784.6
137.5°	551.1	595.8	637.6	674.4	704.8	727.3	738.1	744.0
140°	541.3	579.5	616.1	650.3	678.8	696.8	708.1	714.6
142.5°	532.1	565.8	597.3	626.9	652.1	668.7	678.8	683.4
145°	519.3	547.0	571.4	594.2	614.5	628.4	636.5	640.6
147.5°	508.7	530.7	550.2	568.1	583.1	595.0	601.2	602.6
150°	502.2	520.9	537.2	551.9	564.8	575.4	580.3	581.1
152.5°	495.0	511.1	526.1	538.2	549.3	557.8	560.8	561.6
155°	484.3	497.3	509.5	519.3	527.4	533.9	536.4	536.4
157.5°	472.7	483.6	493.9	501.7	507.8	512.7	514.2	514.2
160°	465.5	474.5	483.5	490.0	494.9	499.8	500.6	500.6
162.5°	458.4	466.0	473.0	478.9	482.5	487.4	488.2	487.5
165°	448.5	453.4	459.0	463.1	466.4	469.6	468.8	468.0
167.5°	438.9	442.6	447.2	449.6	451.3	453.4	453.2	452.6
170°	433.0	435.5	438.7	441.2	442.8	443.6	442.8	442.8
172.5°	427.8	429.6	431.5	433.3	434.3	435.1	434.3	433.0
175°	420.8	421.6	423.2	423.2	423.2	424.9	423.2	421.6
177.5°	416.2	416.9	416.9	417.5	416.9	417.5	416.2	414.9
180°	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3

(END OF REPORT)