

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332934-930

Luminaire Tested: **S124RDIP-S795D590U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332934-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIP-S795D590U930-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 590 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4541.9 lumens
Efficiency: N/A
Efficacy: 112.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 40.3
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332934-930

CATALOG NUMBER: S124RDIP-S795D590U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332934-930

CATALOG NUMBER: S124RDIP-S795D590U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	63	63	63
1	100	96	92	88	93	89	86	83	77	75	73	66	65	63	56	55	54
2	91	84	78	73	85	78	73	69	68	64	61	59	56	53	50	48	46
3	83	74	67	61	77	69	63	58	60	55	51	52	48	45	44	42	39
4	76	66	58	52	71	62	55	49	54	48	44	47	42	39	40	37	34
5	70	59	51	45	65	55	48	42	48	43	38	42	38	34	36	33	30
6	65	53	45	39	60	50	42	37	44	38	33	38	33	30	33	29	27
7	60	48	40	34	56	45	38	33	40	34	30	35	30	27	30	26	24
8	56	43	36	30	52	41	34	29	36	31	26	32	27	24	28	24	21
9	52	40	32	27	49	38	31	26	33	28	24	29	25	22	26	22	19
10	49	37	29	25	45	35	28	24	31	25	22	27	23	20	24	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9143	9143	9143
5°	9164	9052	9108
10°	9107	8943	8943
15°	9002	8756	8690
20°	8858	8508	8352
25°	8675	8219	8011
30°	8496	7914	7582
35°	8298	7597	7154
40°	8061	7238	6690
45°	7841	6882	6218
50°	7592	6469	5718
55°	7323	6042	5175
60°	7030	5572	4621
65°	6758	4988	4076
70°	6366	4338	3460
75°	5870	3599	2813
80°	5119	2738	2580
85°	4335	2492	2325



TEST NUMBER: P332934-930

CATALOG NUMBER: S124RDIP-S795D590U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	106.4	2.3
10°-20°	296.7	6.5
20°-30°	428.4	9.4
30°-40°	485.6	10.7
40°-50°	468.9	10.3
50°-60°	389.9	8.6
60°-70°	269.3	5.9
70°-80°	136.5	3.0
80°-90°	36.8	0.8
90°-100°	21.3	0.5
100°-110°	135.6	3.0
110°-120°	259.4	5.7
120°-130°	329.3	7.3
130°-140°	352.3	7.8
140°-150°	329.4	7.3
150°-160°	265.7	5.8
160°-170°	171.4	3.8
170°-180°	59.1	1.3
0°-30°	831.5	18.3
0°-40°	1317.1	29.0
0°-60°	2176.0	47.9
0°-90°	2618.5	57.7
90°-120°	416.3	9.2
90°-150°	1427.3	31.4
90°-180°	1923.0	42.3
0°-180°	4541.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1133	1133	1133	1133	1133	
5°	1131	1127	1117	1125	1124	107
15°	1077	1069	1048	1046	1040	303
25°	974	957	923	908	899	449
35°	842	813	771	742	726	526
45°	687	654	603	562	545	529
55°	520	484	429	386	368	465
65°	354	316	261	225	213	349
75°	188	156	115	96	90	199
85°	47	30	27	25	25	53
90°	1	6	10	13	14	3
95°	26	11	10	13	14	33
105°	140	143	145	148	133	146
115°	261	263	262	263	263	257
125°	367	369	368	370	370	328
135°	456	455	457	458	459	351
145°	526	527	527	527	528	328
155°	576	577	575	577	576	266
165°	608	606	606	609	605	172
175°	622	619	620	623	618	59
180°	622	622	622	622	622	



TEST NUMBER: P332934-930

CATALOG NUMBER: S124RDIP-S795D590U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1132.6	1132.6	1132.6	1132.6	1132.6	1132.6	1132.6	1132.6	1132.6	1132.6	1132.6
2.5°	1135.4	1134.7	1134.1	1133.5	1132.9	1131.7	1130.0	1128.4	1126.7	1124.9	1126.7
5°	1130.8	1130.1	1129.3	1128.5	1127.7	1126.3	1123.9	1121.6	1119.2	1117.0	1118.9
7.5°	1120.6	1119.8	1119.0	1118.2	1117.4	1115.5	1112.5	1109.5	1106.4	1103.4	1104.6
10°	1110.9	1109.9	1109.0	1108.0	1107.0	1104.8	1101.4	1097.9	1094.5	1091.0	1091.7
12.5°	1098.4	1097.3	1096.2	1095.0	1094.0	1091.4	1087.3	1083.1	1079.0	1075.0	1075.5
15°	1077.1	1075.4	1073.6	1071.9	1070.2	1066.9	1062.0	1057.2	1052.4	1047.6	1047.2
17.5°	1051.2	1048.7	1046.2	1043.7	1041.2	1037.1	1031.3	1025.5	1019.7	1013.9	1012.8
20°	1031.1	1028.6	1026.1	1023.6	1021.1	1016.6	1010.0	1003.5	996.9	990.3	988.8
22.5°	1008.9	1006.1	1003.3	1000.5	997.7	992.7	985.7	978.7	971.7	964.7	962.4
25°	973.9	970.4	966.9	963.4	960.0	954.3	946.4	938.5	930.6	922.7	919.4
27.5°	937.1	932.8	928.4	924.1	919.7	913.3	904.8	896.4	887.9	879.5	875.5
30°	911.4	906.6	901.8	897.0	892.2	885.3	876.2	867.2	858.0	849.0	844.2
32.5°	884.4	879.0	873.5	868.0	862.7	855.2	845.9	836.5	827.1	817.7	812.2
35°	842.0	835.9	829.7	823.5	817.4	809.5	799.9	790.2	780.6	770.9	764.4
37.5°	796.8	790.4	784.1	777.7	771.4	762.9	752.2	741.5	730.8	720.2	712.8
40°	764.9	758.6	752.2	745.8	739.5	730.8	719.7	708.8	697.8	686.8	678.7
42.5°	734.3	727.7	721.1	714.4	707.7	698.6	687.2	675.7	664.3	652.8	644.6
45°	686.8	679.7	672.5	665.4	658.3	649.0	637.4	625.8	614.2	602.8	593.3
47.5°	637.7	630.4	623.1	615.6	608.3	598.6	586.6	574.5	562.6	550.5	540.7
50°	604.5	597.0	589.4	581.9	574.4	564.4	552.1	539.8	527.4	515.1	505.5
52.5°	570.5	563.1	555.7	548.4	541.0	531.0	518.4	505.7	493.1	480.5	470.7
55°	520.3	512.6	504.9	497.2	489.5	479.4	466.8	454.3	441.8	429.3	419.2
57.5°	470.8	462.7	454.7	446.7	438.6	428.4	416.1	403.8	391.5	379.1	369.0
60°	435.4	427.6	420.0	412.2	404.5	394.5	382.1	369.8	357.5	345.1	335.1
62.5°	403.4	395.4	387.4	379.4	371.4	361.0	348.4	335.7	323.1	310.5	301.2
65°	353.8	345.5	337.2	329.0	320.7	310.4	298.0	285.7	273.4	261.1	252.7
67.5°	302.3	294.4	286.4	278.5	270.5	260.9	249.4	238.0	226.5	215.1	207.9
70°	269.7	261.6	253.5	245.4	237.3	227.8	216.8	205.8	194.9	183.8	177.5
72.5°	235.1	227.7	220.4	213.0	205.7	196.9	186.5	176.1	165.8	155.4	149.9
75°	188.2	181.1	173.9	166.8	159.6	151.6	142.5	133.5	124.4	115.4	110.9
77.5°	140.6	134.6	128.6	122.5	116.4	109.7	102.5	95.1	87.8	80.5	77.9
80°	110.1	104.5	99.0	93.4	87.8	82.1	76.3	70.5	64.7	58.9	58.4
82.5°	83.8	78.7	73.5	68.4	63.3	59.0	55.8	52.4	49.1	45.8	45.3
85°	46.8	43.0	39.1	35.3	31.4	29.2	28.6	28.0	27.5	26.9	26.5
87.5°	16.2	15.2	14.2	13.2	12.2	11.7	11.7	11.7	11.7	11.7	11.7
90°	1.4	2.5	3.7	4.8	6.0	6.9	7.7	8.6	9.4	10.2	10.8
92.5°	5.9	6.0	6.0	6.0	6.1	6.5	7.4	8.2	9.0	9.9	10.5
95°	25.6	22.1	18.6	15.0	11.5	9.8	9.9	10.0	10.1	10.2	10.8
97.5°	54.3	56.5	58.7	60.9	63.1	58.4	46.9	35.4	23.8	12.3	12.3
100°	76.2	78.1	80.0	81.9	83.7	77.5	63.3	49.0	34.7	20.5	18.7
102.5°	100.9	102.2	103.5	104.9	106.3	106.1	104.2	102.3	100.4	98.6	79.7
105°	140.0	140.6	141.2	141.9	142.4	143.0	143.6	144.1	144.6	145.1	146.0
107.5°	176.3	176.7	177.0	177.2	177.6	178.1	178.8	179.5	180.2	180.9	181.4
110°	200.9	201.2	201.5	201.9	202.1	202.6	203.3	203.8	204.5	205.1	205.3



TEST NUMBER: P332934-930

CATALOG NUMBER: S124RDIP-S795D590U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	224.7	225.3	225.8	226.4	227.0	227.4	227.6	228.0	228.3	228.5	228.5
115°	261.4	261.7	262.0	262.3	262.6	262.7	262.6	262.5	262.4	262.3	262.5
117.5°	294.4	294.8	295.2	295.6	296.0	296.4	296.6	296.9	297.0	297.3	297.3
120°	316.7	317.2	317.6	318.0	318.4	318.5	318.5	318.3	318.2	318.1	318.3
122.5°	337.5	337.8	338.0	338.3	338.5	338.8	338.9	339.0	339.2	339.3	339.4
125°	367.4	367.8	368.3	368.7	369.1	369.2	368.9	368.8	368.5	368.4	368.7
127.5°	395.7	395.7	395.9	396.0	396.1	396.4	396.9	397.3	397.8	398.3	398.2
130°	413.9	414.0	414.1	414.3	414.3	414.5	414.8	415.2	415.5	415.8	415.9
132.5°	430.6	430.8	431.0	431.2	431.4	431.7	432.1	432.4	432.8	433.3	433.3
135°	455.8	455.7	455.6	455.4	455.3	455.5	455.9	456.3	456.7	457.1	457.4
137.5°	478.0	478.0	478.1	478.1	478.2	478.4	478.8	479.3	479.8	480.2	480.5
140°	492.5	492.7	492.9	493.1	493.3	493.5	493.7	494.0	494.2	494.4	494.6
142.5°	505.6	505.9	506.3	506.6	507.0	507.3	507.4	507.5	507.6	507.8	508.0
145°	525.5	525.9	526.1	526.4	526.8	526.9	526.9	526.9	526.9	526.9	527.0
147.5°	541.4	542.0	542.6	543.2	543.7	544.0	543.9	543.8	543.6	543.6	543.6
150°	552.9	553.3	553.8	554.2	554.6	554.8	554.6	554.6	554.5	554.3	554.3
152.5°	562.6	563.0	563.3	563.6	563.9	564.0	563.9	563.7	563.5	563.3	563.5
155°	576.3	576.3	576.4	576.5	576.7	576.5	576.3	575.9	575.6	575.3	575.7
157.5°	587.7	587.6	587.5	587.5	587.4	587.2	586.9	586.5	586.1	585.8	586.4
160°	594.4	594.0	593.7	593.5	593.1	592.9	592.8	592.7	592.6	592.5	593.1
162.5°	600.3	599.9	599.5	599.2	598.8	598.5	598.3	598.3	598.2	598.1	598.7
165°	607.8	607.3	606.8	606.3	605.8	605.5	605.5	605.5	605.5	605.5	606.3
167.5°	613.8	613.3	612.7	612.2	611.6	611.3	611.3	611.2	611.1	611.1	612.0
170°	617.2	616.5	615.9	615.3	614.7	614.4	614.5	614.6	614.7	614.8	615.6
172.5°	619.4	618.7	618.2	617.5	616.9	616.6	616.8	616.9	616.9	617.0	617.9
175°	621.8	621.2	620.5	620.0	619.3	619.1	619.1	619.3	619.4	619.5	620.4
177.5°	622.9	622.3	621.7	621.2	620.6	620.4	620.5	620.7	620.9	621.0	621.7
180°	621.8	621.8	621.8	621.8	621.8	621.8	621.8	621.8	621.8	621.8	621.8



TEST NUMBER: P332934-930

CATALOG NUMBER: S124RDIP-S795D590U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1132.6	1132.6	1132.6	1132.6	1132.6	1132.6	1132.6	1132.6
2.5°	1128.4	1130.0	1131.7	1132.5	1132.4	1132.2	1132.0	1131.9
5°	1120.8	1122.7	1124.7	1125.4	1125.0	1124.7	1124.3	1123.9
7.5°	1105.9	1107.2	1108.4	1108.6	1108.1	1107.4	1106.9	1106.2
10°	1092.5	1093.2	1094.1	1094.1	1093.2	1092.5	1091.7	1091.0
12.5°	1076.0	1076.4	1076.8	1076.5	1075.5	1074.4	1073.3	1072.2
15°	1046.8	1046.4	1046.0	1045.2	1043.8	1042.4	1041.1	1039.8
17.5°	1011.8	1010.7	1009.6	1008.0	1006.0	1004.0	1001.9	999.9
20°	987.2	985.7	984.1	982.2	979.7	977.1	974.6	972.2
22.5°	960.1	957.7	955.4	953.2	951.2	949.2	947.1	945.1
25°	916.2	912.9	909.6	907.0	905.1	903.2	901.2	899.3
27.5°	871.4	867.4	863.3	859.9	857.1	854.4	851.6	848.8
30°	839.4	834.5	829.7	825.7	822.7	819.6	816.5	813.4
32.5°	806.6	801.0	795.4	791.2	788.2	785.3	782.4	779.4
35°	757.8	751.3	744.8	739.7	736.3	732.8	729.3	725.9
37.5°	705.5	698.1	690.8	685.4	682.0	678.5	675.1	671.6
40°	670.7	662.5	654.4	648.7	645.2	641.7	638.3	634.8
42.5°	636.3	628.1	619.9	613.9	610.3	606.7	603.1	599.4
45°	583.8	574.4	564.9	558.5	555.0	551.5	548.0	544.6
47.5°	530.9	521.1	511.4	504.5	500.8	496.9	493.1	489.3
50°	495.9	486.2	476.5	469.9	466.3	462.6	458.9	455.3
52.5°	460.9	451.1	441.2	434.5	430.6	426.8	423.1	419.2
55°	409.2	399.2	389.2	382.4	378.7	375.0	371.4	367.7
57.5°	358.8	348.6	338.4	332.0	329.2	326.4	323.7	320.9
60°	325.1	315.1	305.1	298.5	295.5	292.4	289.3	286.2
62.5°	292.0	282.7	273.5	267.6	265.1	262.7	260.2	257.7
65°	244.4	236.2	227.9	222.6	220.3	217.9	215.6	213.4
67.5°	200.8	193.7	186.5	181.7	179.2	176.6	174.1	171.5
70°	171.1	164.8	158.4	154.3	152.4	150.4	148.5	146.6
72.5°	144.6	139.1	133.6	130.0	128.3	126.5	124.7	122.9
75°	106.5	102.1	97.6	94.8	93.7	92.5	91.3	90.2
77.5°	75.3	72.7	70.1	68.6	68.3	68.0	67.7	67.3
80°	57.8	57.2	56.7	56.3	56.1	55.8	55.7	55.5
82.5°	44.9	44.5	44.1	43.8	43.6	43.4	43.2	43.0
85°	26.1	25.8	25.4	25.1	25.1	25.1	25.1	25.1
87.5°	11.7	11.7	11.7	11.7	11.9	12.1	12.3	12.5
90°	11.5	12.1	12.7	13.1	13.4	13.5	13.8	13.9
92.5°	11.1	11.7	12.3	12.6	12.7	12.7	12.8	12.8
95°	11.5	12.1	12.7	13.0	13.2	13.3	13.4	13.5
97.5°	12.4	12.5	12.6	12.6	12.7	12.8	12.9	13.0
100°	17.0	15.2	13.5	12.6	12.7	12.8	12.9	13.0
102.5°	60.7	41.7	22.7	13.3	13.4	13.4	13.4	13.4
105°	147.0	147.9	148.8	147.4	143.7	140.0	136.2	132.6
107.5°	181.8	182.3	182.7	183.1	183.5	183.9	184.3	184.7
110°	205.5	205.7	205.9	206.2	206.5	206.8	207.1	207.4



TEST NUMBER: P332934-930

CATALOG NUMBER: S124RDIP-S795D590U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	228.4	228.4	228.4	228.5	228.9	229.3	229.8	230.1
115°	262.7	262.9	263.1	263.3	263.3	263.3	263.3	263.3
117.5°	297.2	297.2	297.1	297.1	297.0	297.0	296.9	296.9
120°	318.5	318.7	318.9	318.9	318.7	318.5	318.3	318.1
122.5°	339.6	339.7	339.8	339.7	339.6	339.3	339.2	338.9
125°	368.9	369.2	369.6	369.8	369.9	370.0	370.1	370.2
127.5°	398.2	398.1	398.0	397.9	397.9	397.8	397.7	397.6
130°	416.0	416.0	416.2	416.2	416.2	416.2	416.2	416.2
132.5°	433.5	433.6	433.7	433.7	433.6	433.5	433.4	433.3
135°	457.5	457.8	458.0	458.2	458.4	458.6	458.9	459.0
137.5°	480.7	480.9	481.1	481.2	481.2	481.1	481.0	480.9
140°	495.0	495.3	495.6	495.8	495.9	496.0	496.1	496.2
142.5°	508.2	508.4	508.7	508.8	508.8	508.8	508.8	508.9
145°	527.1	527.3	527.3	527.5	527.7	527.9	528.2	528.3
147.5°	543.7	543.8	543.9	544.0	544.1	544.2	544.3	544.4
150°	554.3	554.3	554.3	554.4	554.5	554.6	554.7	554.8
152.5°	563.6	563.8	563.9	564.0	563.9	563.9	563.8	563.8
155°	576.1	576.5	576.9	577.0	576.7	576.3	576.1	575.8
157.5°	586.9	587.4	587.9	587.9	587.4	586.9	586.4	585.8
160°	593.7	594.4	595.0	595.0	594.4	593.7	593.1	592.5
162.5°	599.3	599.9	600.5	600.5	599.8	599.1	598.4	597.7
165°	607.2	608.0	608.9	608.8	607.8	606.9	606.0	605.0
167.5°	612.9	613.8	614.7	614.7	613.7	612.6	611.6	610.6
170°	616.4	617.3	618.2	618.0	617.0	616.0	614.9	613.9
172.5°	618.7	619.5	620.4	620.2	619.1	618.0	616.9	615.7
175°	621.3	622.2	623.2	623.1	621.8	620.5	619.3	618.1
177.5°	622.4	623.1	623.7	623.5	622.6	621.6	620.5	619.5
180°	621.8	621.8	621.8	621.8	621.8	621.8	621.8	621.8

(END OF REPORT)