

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332936-930

Luminaire Tested: **S124RDIP-S795D590U930-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332936-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIP-S795D590U930-4F0-1E-UDD-F4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4339.7 lumens
Efficiency: N/A
Efficacy: 107.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 40.3
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332936-930

CATALOG NUMBER: S124RDIP-S795D590U930-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332936-930

CATALOG NUMBER: S124RDIP-S795D590U930-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	66	66	66
1	100	96	92	89	94	90	87	84	79	76	74	68	66	65	59	57	56
2	92	84	78	73	86	79	74	69	69	65	62	60	57	55	52	50	48
3	84	74	67	61	78	70	63	58	61	56	52	54	50	47	46	43	41
4	77	66	58	52	72	62	55	50	55	49	45	48	44	40	42	38	36
5	71	59	51	45	66	56	48	43	49	43	39	43	39	35	38	34	31
6	65	53	45	39	61	50	43	38	44	39	34	39	34	31	34	30	28
7	60	48	40	35	56	46	38	33	40	35	30	36	31	27	31	28	25
8	56	44	36	31	53	41	34	29	37	31	27	33	28	25	29	25	22
9	52	40	33	28	49	38	31	26	34	28	24	30	26	22	27	23	20
10	49	37	30	25	46	35	28	24	31	26	22	28	23	20	25	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9143	9143	9143
5°	9164	9052	9108
10°	9107	8943	8943
15°	9002	8756	8690
20°	8858	8508	8352
25°	8675	8219	8011
30°	8496	7914	7582
35°	8298	7597	7154
40°	8061	7238	6690
45°	7841	6882	6218
50°	7592	6469	5718
55°	7323	6042	5175
60°	7030	5572	4621
65°	6758	4988	4076
70°	6366	4338	3460
75°	5870	3599	2813
80°	5119	2738	2580
85°	4335	2492	2325



TEST NUMBER: P332936-930

CATALOG NUMBER: S124RDIP-S795D590U930-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	106.4	2.5
10°-20°	296.7	6.8
20°-30°	428.4	9.9
30°-40°	485.6	11.2
40°-50°	468.9	10.8
50°-60°	389.9	9.0
60°-70°	269.3	6.2
70°-80°	136.5	3.1
80°-90°	36.3	0.8
90°-100°	171.0	3.9
100°-110°	355.9	8.2
110°-120°	318.7	7.3
120°-130°	268.1	6.2
130°-140°	223.6	5.2
140°-150°	170.8	3.9
150°-160°	120.0	2.8
160°-170°	70.6	1.6
170°-180°	23.0	0.5
0°-30°	831.5	19.2
0°-40°	1317.1	30.3
0°-60°	2176.0	50.1
0°-90°	2618.0	60.3
90°-120°	845.6	19.5
90°-150°	1508.1	34.8
90°-180°	1722.0	39.7
0°-180°	4339.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1133	1133	1133	1133	1133	
5°	1131	1127	1117	1125	1124	107
15°	1077	1069	1048	1046	1040	303
25°	974	957	923	908	899	449
35°	842	813	771	742	726	526
45°	687	654	603	562	545	529
55°	520	484	429	386	368	465
65°	354	316	261	225	213	349
75°	188	156	115	96	90	199
85°	47	30	27	25	25	53
90°	0	4	8	9	10	3
95°	15	48	379	188	114	17
105°	54	79	305	657	654	58
115°	96	120	272	523	628	95
125°	134	159	271	445	501	119
135°	159	189	268	395	448	123
145°	183	209	267	333	366	115
155°	208	224	260	294	306	96
165°	226	234	249	263	267	64
175°	236	237	239	242	241	22
180°	237	237	237	237	237	



TEST NUMBER: P332936-930

CATALOG NUMBER: S124RDIP-S795D590U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1132.6	1132.6	1132.6	1132.6	1132.6	1132.6	1132.6	1132.6	1132.6	1132.6	1132.6
2.5°	1135.4	1134.7	1134.1	1133.5	1132.9	1131.7	1130.0	1128.4	1126.7	1124.9	1126.7
5°	1130.8	1130.1	1129.3	1128.5	1127.7	1126.3	1123.9	1121.6	1119.2	1117.0	1118.9
7.5°	1120.6	1119.8	1119.0	1118.2	1117.4	1115.5	1112.5	1109.5	1106.4	1103.4	1104.6
10°	1110.9	1109.9	1109.0	1108.0	1107.0	1104.8	1101.4	1097.9	1094.5	1091.0	1091.7
12.5°	1098.4	1097.3	1096.2	1095.0	1094.0	1091.4	1087.3	1083.1	1079.0	1075.0	1075.5
15°	1077.1	1075.4	1073.6	1071.9	1070.2	1066.9	1062.0	1057.2	1052.4	1047.6	1047.2
17.5°	1051.2	1048.7	1046.2	1043.7	1041.2	1037.1	1031.3	1025.5	1019.7	1013.9	1012.8
20°	1031.1	1028.6	1026.1	1023.6	1021.1	1016.6	1010.0	1003.5	996.9	990.3	988.8
22.5°	1008.9	1006.1	1003.3	1000.5	997.7	992.7	985.7	978.7	971.7	964.7	962.4
25°	973.9	970.4	966.9	963.4	960.0	954.3	946.4	938.5	930.6	922.7	919.4
27.5°	937.1	932.8	928.4	924.1	919.7	913.3	904.8	896.4	887.9	879.5	875.5
30°	911.4	906.6	901.8	897.0	892.2	885.3	876.2	867.2	858.0	849.0	844.2
32.5°	884.4	879.0	873.5	868.0	862.7	855.2	845.9	836.5	827.1	817.7	812.2
35°	842.0	835.9	829.7	823.5	817.4	809.5	799.9	790.2	780.6	770.9	764.4
37.5°	796.8	790.4	784.1	777.7	771.4	762.9	752.2	741.5	730.8	720.2	712.8
40°	764.9	758.6	752.2	745.8	739.5	730.8	719.7	708.8	697.8	686.8	678.7
42.5°	734.3	727.7	721.1	714.4	707.7	698.6	687.2	675.7	664.3	652.8	644.6
45°	686.8	679.7	672.5	665.4	658.3	649.0	637.4	625.8	614.2	602.8	593.3
47.5°	637.7	630.4	623.1	615.6	608.3	598.6	586.6	574.5	562.6	550.5	540.7
50°	604.5	597.0	589.4	581.9	574.4	564.4	552.1	539.8	527.4	515.1	505.5
52.5°	570.5	563.1	555.7	548.4	541.0	531.0	518.4	505.7	493.1	480.5	470.7
55°	520.3	512.6	504.9	497.2	489.5	479.4	466.8	454.3	441.8	429.3	419.2
57.5°	470.8	462.7	454.7	446.7	438.6	428.4	416.1	403.8	391.5	379.1	369.0
60°	435.4	427.6	420.0	412.2	404.5	394.5	382.1	369.8	357.5	345.1	335.1
62.5°	403.4	395.4	387.4	379.4	371.4	361.0	348.4	335.7	323.1	310.5	301.2
65°	353.8	345.5	337.2	329.0	320.7	310.4	298.0	285.7	273.4	261.1	252.7
67.5°	302.3	294.4	286.4	278.5	270.5	260.9	249.4	238.0	226.5	215.1	207.9
70°	269.7	261.6	253.5	245.4	237.3	227.8	216.8	205.8	194.9	183.8	177.5
72.5°	235.1	227.7	220.4	213.0	205.7	196.9	186.5	176.1	165.8	155.4	149.9
75°	188.2	181.1	173.9	166.8	159.6	151.6	142.5	133.5	124.4	115.4	110.9
77.5°	140.6	134.6	128.6	122.5	116.4	109.7	102.5	95.1	87.8	80.5	77.9
80°	110.1	104.5	99.0	93.4	87.8	82.1	76.3	70.5	64.7	58.9	58.4
82.5°	83.8	78.7	73.5	68.4	63.3	59.0	55.8	52.4	49.1	45.8	45.3
85°	46.8	43.0	39.1	35.3	31.4	29.2	28.6	28.0	27.5	26.9	26.5
87.5°	16.1	15.0	14.0	12.9	11.7	11.1	11.5	11.3	11.3	11.4	11.2
90°	0.5	1.4	2.8	3.3	3.8	3.8	6.5	6.5	7.4	8.4	7.9
92.5°	5.3	7.7	12.1	17.8	24.5	34.2	57.9	93.9	129.1	147.5	122.9
95°	15.3	16.7	21.4	27.5	38.6	58.1	98.6	174.9	286.0	379.0	389.7
97.5°	27.6	27.6	31.6	37.1	46.7	63.1	94.2	157.2	267.7	399.3	489.7
100°	35.4	35.4	38.6	44.2	53.0	67.9	95.3	147.9	242.8	373.9	493.0
102.5°	42.8	43.5	46.4	51.6	60.1	74.2	99.1	145.3	226.0	342.3	465.0
105°	54.4	55.8	58.1	63.8	72.1	85.6	107.9	146.5	211.7	305.1	414.4
107.5°	67.3	68.2	70.5	76.5	84.5	97.8	118.2	153.4	209.0	284.3	373.5
110°	75.8	76.7	79.1	84.6	93.0	105.6	126.0	158.6	209.8	277.2	353.0



TEST NUMBER: P332936-930

CATALOG NUMBER: S124RDIP-S795D590U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	84.0	85.0	87.6	92.9	101.2	113.7	133.5	164.2	212.0	273.9	341.4
115°	95.8	97.2	100.4	105.1	114.0	126.5	145.1	173.0	216.3	272.1	330.7
117.5°	108.1	109.4	112.3	117.4	125.6	138.7	156.4	182.1	220.8	271.6	325.9
120°	116.3	117.2	120.4	125.6	133.5	146.5	164.2	188.3	224.2	271.6	323.3
122.5°	123.7	124.7	127.9	132.6	141.3	153.9	171.6	194.3	227.6	271.3	320.2
125°	133.5	135.3	138.1	143.2	152.1	165.1	181.8	203.3	232.5	270.7	315.4
127.5°	142.1	143.7	147.0	152.8	162.0	175.1	191.4	211.0	236.5	269.6	308.8
130°	147.0	148.8	152.5	159.6	168.4	181.8	197.6	215.8	239.5	269.3	304.6
132.5°	151.8	153.3	158.2	164.8	174.3	187.0	202.8	220.6	242.1	268.9	300.9
135°	158.6	160.5	165.1	173.0	182.8	194.9	210.2	227.0	246.1	268.3	295.3
137.5°	165.4	167.1	172.3	179.8	190.0	201.5	215.8	231.5	248.3	268.2	290.5
140°	170.2	171.6	176.8	184.7	194.4	205.5	219.6	234.4	250.2	267.9	287.9
142.5°	175.5	176.8	181.6	189.1	198.5	209.3	222.9	236.6	251.7	267.9	285.7
145°	182.8	184.2	188.8	195.3	204.2	214.4	226.5	239.0	252.6	266.9	281.8
147.5°	191.0	191.5	195.6	202.3	209.7	218.9	230.2	241.2	253.0	265.3	278.4
150°	196.2	196.7	200.5	206.0	213.0	221.8	232.1	242.3	253.0	264.2	275.8
152.5°	201.1	201.2	204.9	210.1	216.4	224.5	233.6	243.0	252.3	262.3	272.8
155°	207.9	208.4	211.2	215.8	220.9	227.9	235.8	243.7	251.1	259.5	268.3
157.5°	214.5	214.5	217.1	220.7	225.2	230.6	237.4	243.7	250.0	256.7	263.8
160°	218.6	218.6	220.5	223.7	227.4	232.5	238.1	243.7	248.8	254.4	260.5
162.5°	222.3	221.9	223.4	226.3	229.7	233.7	238.9	243.7	247.7	252.2	257.5
165°	226.5	226.5	227.4	229.8	232.1	234.9	239.0	242.8	245.6	248.8	252.6
167.5°	230.6	230.2	230.6	232.4	233.7	235.9	239.0	241.7	243.4	245.5	248.1
170°	232.5	232.1	232.5	233.9	234.9	236.3	238.6	240.9	241.8	243.2	245.1
172.5°	234.4	233.9	234.0	235.1	235.6	236.6	238.2	240.2	240.4	241.0	242.5
175°	236.3	235.8	235.8	236.3	236.8	236.8	237.7	239.0	238.6	238.6	239.5
177.5°	237.1	236.8	236.4	236.8	236.8	236.8	237.1	237.8	237.1	237.1	237.5
180°	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8



TEST NUMBER: P332936-930

CATALOG NUMBER: S124RDIP-S795D590U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1132.6	1132.6	1132.6	1132.6	1132.6	1132.6	1132.6	1132.6
2.5°	1128.4	1130.0	1131.7	1132.5	1132.4	1132.2	1132.0	1131.9
5°	1120.8	1122.7	1124.7	1125.4	1125.0	1124.7	1124.3	1123.9
7.5°	1105.9	1107.2	1108.4	1108.6	1108.1	1107.4	1106.9	1106.2
10°	1092.5	1093.2	1094.1	1094.1	1093.2	1092.5	1091.7	1091.0
12.5°	1076.0	1076.4	1076.8	1076.5	1075.5	1074.4	1073.3	1072.2
15°	1046.8	1046.4	1046.0	1045.2	1043.8	1042.4	1041.1	1039.8
17.5°	1011.8	1010.7	1009.6	1008.0	1006.0	1004.0	1001.9	999.9
20°	987.2	985.7	984.1	982.2	979.7	977.1	974.6	972.2
22.5°	960.1	957.7	955.4	953.2	951.2	949.2	947.1	945.1
25°	916.2	912.9	909.6	907.0	905.1	903.2	901.2	899.3
27.5°	871.4	867.4	863.3	859.9	857.1	854.4	851.6	848.8
30°	839.4	834.5	829.7	825.7	822.7	819.6	816.5	813.4
32.5°	806.6	801.0	795.4	791.2	788.2	785.3	782.4	779.4
35°	757.8	751.3	744.8	739.7	736.3	732.8	729.3	725.9
37.5°	705.5	698.1	690.8	685.4	682.0	678.5	675.1	671.6
40°	670.7	662.5	654.4	648.7	645.2	641.7	638.3	634.8
42.5°	636.3	628.1	619.9	613.9	610.3	606.7	603.1	599.4
45°	583.8	574.4	564.9	558.5	555.0	551.5	548.0	544.6
47.5°	530.9	521.1	511.4	504.5	500.8	496.9	493.1	489.3
50°	495.9	486.2	476.5	469.9	466.3	462.6	458.9	455.3
52.5°	460.9	451.1	441.2	434.5	430.6	426.8	423.1	419.2
55°	409.2	399.2	389.2	382.4	378.7	375.0	371.4	367.7
57.5°	358.8	348.6	338.4	332.0	329.2	326.4	323.7	320.9
60°	325.1	315.1	305.1	298.5	295.5	292.4	289.3	286.2
62.5°	292.0	282.7	273.5	267.6	265.1	262.7	260.2	257.7
65°	244.4	236.2	227.9	222.6	220.3	217.9	215.6	213.4
67.5°	200.8	193.7	186.5	181.7	179.2	176.6	174.1	171.5
70°	171.1	164.8	158.4	154.3	152.4	150.4	148.5	146.6
72.5°	144.6	139.1	133.6	130.0	128.3	126.5	124.7	122.9
75°	106.5	102.1	97.6	94.8	93.7	92.5	91.3	90.2
77.5°	75.3	72.7	70.1	68.6	68.3	68.0	67.7	67.3
80°	57.8	57.2	56.7	56.3	56.1	55.8	55.7	55.5
82.5°	44.9	44.5	44.1	43.8	43.6	43.4	43.2	43.0
85°	26.1	25.8	25.4	25.1	25.1	25.1	25.1	25.1
87.5°	11.1	11.0	10.9	10.9	11.2	11.4	11.5	11.7
90°	8.4	8.8	9.3	9.3	9.8	10.2	9.8	9.8
92.5°	91.3	68.7	54.7	45.4	39.9	37.4	35.8	35.8
95°	344.6	272.6	210.2	165.1	142.4	127.9	119.5	113.5
97.5°	509.2	482.4	436.9	388.3	355.0	326.9	313.0	303.3
100°	560.9	570.2	547.4	513.0	472.5	444.2	430.2	426.5
102.5°	558.3	604.5	611.1	596.7	571.9	551.3	536.6	533.6
105°	520.9	601.4	647.4	666.5	667.4	663.7	657.1	654.4
107.5°	467.8	553.4	618.3	659.7	682.7	693.3	698.0	699.2
110°	435.8	516.2	583.7	634.9	667.9	687.4	695.8	699.9



TEST NUMBER: P332936-930

CATALOG NUMBER: S124RDIP-S795D590U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	412.4	483.5	547.2	598.3	635.9	659.5	671.2	678.0
115°	388.8	446.1	500.4	545.1	581.8	609.8	624.6	628.4
117.5°	377.2	424.6	467.4	505.2	536.6	560.0	575.1	578.0
120°	372.1	415.3	452.5	485.5	512.1	532.6	544.6	549.8
122.5°	367.6	409.4	443.2	472.1	494.6	512.1	522.3	527.4
125°	360.0	400.0	432.0	457.6	476.2	489.8	498.6	501.3
127.5°	350.7	388.9	420.9	445.2	463.9	475.9	483.3	486.1
130°	343.2	380.0	411.6	436.3	455.3	466.9	474.4	477.2
132.5°	335.4	369.9	400.8	425.4	444.2	457.3	464.3	467.2
135°	324.7	354.9	383.2	406.5	425.1	438.1	445.6	448.3
137.5°	314.9	340.5	364.4	385.4	402.8	415.6	421.8	425.1
140°	309.2	331.2	352.0	371.6	387.9	398.1	404.6	408.4
142.5°	304.1	323.3	341.3	358.2	372.6	382.1	387.9	390.4
145°	296.7	312.5	326.5	339.5	351.1	359.1	363.7	366.0
147.5°	290.7	303.2	314.4	324.7	333.2	340.0	343.5	344.4
150°	287.0	297.7	307.0	315.4	322.8	328.8	331.6	332.1
152.5°	282.8	292.0	300.6	307.5	313.8	318.8	320.4	320.9
155°	276.7	284.1	291.1	296.7	301.4	305.1	306.5	306.5
157.5°	270.1	276.4	282.2	286.7	290.2	293.0	293.8	293.8
160°	266.0	271.2	276.2	280.0	282.7	285.6	286.0	286.0
162.5°	262.0	266.3	270.3	273.7	275.7	278.5	279.0	278.6
165°	256.2	259.0	262.3	264.6	266.5	268.3	267.9	267.4
167.5°	250.8	252.9	255.5	256.9	257.9	259.0	258.9	258.6
170°	247.4	248.8	250.7	252.1	253.0	253.5	253.0	253.0
172.5°	244.4	245.5	246.6	247.6	248.2	248.7	248.2	247.4
175°	240.4	240.9	241.8	241.8	241.8	242.8	241.8	240.9
177.5°	237.8	238.2	238.2	238.6	238.2	238.6	237.8	237.1
180°	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8

(END OF REPORT)