

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332659

Luminaire Tested: **S124DIP-S1020D1035U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332659  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIP-S1020D1035U835-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1035 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 8012.4 lumens  
Efficiency: N/A  
Efficacy: 132.4 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 60.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332659

CATALOG NUMBER: S124DIP-S1020D1035U835-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332659

CATALOG NUMBER: S124DIP-S1020D1035U835-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55																				
1	99	95	91	87	92	88	85	81	76	73	71	64	62	61	54	53	51	46																				
2	90	83	76	71	83	77	71	67	66	62	59	56	53	51	47	45	43	39																				
3	82	73	65	59	76	68	61	56	58	53	49	50	46	43	42	39	37	33																				
4	75	64	56	50	70	60	53	47	52	46	42	44	40	37	38	34	32	28																				
5	69	57	49	43	64	54	46	41	47	41	36	40	35	32	34	30	28	25																				
6	64	51	43	37	59	48	41	35	42	36	32	36	32	28	31	27	24	22																				
7	59	46	38	33	55	44	36	31	38	32	28	33	28	25	28	24	22	19																				
8	55	42	34	29	51	40	33	28	35	29	25	30	25	22	26	22	19	17																				
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	20	18	15																				
10	48	35	28	23	44	33	27	22	29	24	20	26	21	18	22	19	16	14																				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13930	13930	13930
5°	13972	13804	13904
10°	13884	13691	13759
15°	13717	13497	13531
20°	13493	13256	13268
25°	13239	12981	12944
30°	12928	12656	12541
35°	12604	12318	12154
40°	12269	11934	11715
45°	11918	11555	11334
50°	11531	11218	10870
55°	11112	10781	10431
60°	10693	10291	9978
65°	10222	9824	9429
70°	9692	9203	8844
75°	8883	8453	8238
80°	7908	7583	7392
85°	6919	6660	6530



TEST NUMBER: P332659

CATALOG NUMBER: S124DIP-S1020D1035U835-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	162.5	2.0
10°-20°	457.8	5.7
20°-30°	673.9	8.4
30°-40°	783.4	9.8
40°-50°	783.4	9.8
50°-60°	685.3	8.6
60°-70°	508.9	6.4
70°-80°	289.1	3.6
80°-90°	87.3	1.1
90°-100°	85.1	1.1
100°-110°	252.2	3.1
110°-120°	428.0	5.3
120°-130°	564.3	7.0
130°-140°	633.8	7.9
140°-150°	622.8	7.8
150°-160°	523.8	6.5
160°-170°	348.5	4.3
170°-180°	122.0	1.5
0°-30°	1294.2	16.2
0°-40°	2077.6	25.9
0°-60°	3546.4	44.3
0°-90°	4431.7	55.3
90°-120°	765.3	9.6
90°-150°	2586.3	32.3
90°-180°	3581.0	44.7
0°-180°	8012.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1726	1726	1726	1726	1726	
5°	1724	1718	1703	1718	1716	163
15°	1641	1635	1615	1622	1619	462
25°	1486	1476	1457	1458	1453	684
35°	1279	1269	1250	1240	1233	799
45°	1044	1034	1012	997	993	804
55°	790	784	766	750	741	707
65°	535	528	514	501	494	530
75°	285	278	271	266	264	303
85°	75	75	72	72	70	82
90°	3	14	22	28	30	8
95°	60	69	76	79	79	67
105°	233	234	238	241	244	247
115°	435	435	433	432	431	429
125°	634	634	633	631	629	565
135°	818	823	824	821	818	632
145°	993	997	998	997	994	621
155°	1138	1138	1137	1140	1137	523
165°	1239	1236	1234	1239	1236	349
175°	1289	1284	1283	1289	1283	122
180°	1291	1291	1291	1291	1291	



TEST NUMBER: P332659

CATALOG NUMBER: S124DIP-S1020D1035U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5
2.5°	1729.9	1729.2	1728.4	1727.7	1727.0	1725.2	1722.5	1719.8	1717.1	1714.4	1716.9
5°	1724.1	1722.9	1721.7	1720.4	1719.2	1716.9	1713.5	1710.1	1706.8	1703.4	1706.8
7.5°	1708.1	1706.8	1705.6	1704.4	1703.2	1700.7	1696.9	1693.2	1689.4	1685.7	1688.4
10°	1693.7	1692.5	1691.2	1690.0	1688.8	1686.2	1682.2	1678.2	1674.2	1670.2	1672.6
12.5°	1674.9	1673.7	1672.4	1671.2	1670.0	1667.2	1663.0	1658.8	1654.5	1650.3	1653.0
15°	1641.2	1639.9	1638.7	1637.5	1636.2	1633.3	1628.7	1624.1	1619.5	1614.9	1616.7
17.5°	1600.5	1599.0	1597.4	1595.9	1594.4	1591.4	1587.0	1582.7	1578.3	1574.0	1575.1
20°	1570.6	1569.1	1567.6	1566.0	1564.5	1561.4	1556.8	1552.2	1547.6	1543.0	1543.9
22.5°	1538.6	1536.5	1534.5	1532.5	1530.5	1527.1	1522.5	1517.9	1513.3	1508.7	1510.4
25°	1486.3	1484.2	1482.0	1479.8	1477.7	1474.5	1470.2	1465.9	1461.6	1457.3	1457.6
27.5°	1426.6	1424.4	1422.1	1419.9	1417.7	1414.6	1410.6	1406.6	1402.6	1398.6	1397.9
30°	1386.8	1384.3	1381.8	1379.4	1376.9	1373.7	1369.7	1365.7	1361.7	1357.7	1356.5
32.5°	1344.7	1342.5	1340.3	1338.1	1335.9	1332.6	1328.4	1324.2	1319.9	1315.7	1314.2
35°	1278.9	1276.8	1274.6	1272.5	1270.3	1267.1	1262.8	1258.5	1254.2	1249.9	1247.7
37.5°	1209.5	1207.5	1205.6	1203.6	1201.6	1198.4	1193.7	1189.1	1184.5	1179.9	1177.6
40°	1164.2	1161.7	1159.2	1156.8	1154.3	1150.8	1146.2	1141.6	1137.0	1132.4	1129.3
42.5°	1115.5	1114.0	1112.5	1111.1	1109.6	1106.3	1101.2	1096.1	1091.0	1085.9	1082.3
45°	1043.9	1041.7	1039.6	1037.4	1035.3	1031.7	1026.8	1021.9	1017.0	1012.1	1008.7
47.5°	968.9	967.5	966.0	964.5	963.0	960.0	955.5	950.9	946.4	941.8	938.0
50°	918.1	916.8	915.6	914.4	913.1	910.4	906.1	901.8	897.5	893.2	888.9
52.5°	868.3	866.8	865.3	863.9	862.4	859.4	854.8	850.3	845.7	841.2	837.4
55°	789.5	788.5	787.6	786.7	785.8	783.2	778.9	774.6	770.3	766.0	762.3
57.5°	714.3	713.2	712.2	711.1	710.1	707.4	703.2	699.0	694.7	690.5	687.0
60°	662.3	660.7	659.2	657.7	656.1	653.4	649.4	645.4	641.4	637.4	634.6
62.5°	611.4	610.1	608.8	607.5	606.2	603.5	599.2	595.0	590.7	586.5	584.0
65°	535.1	533.5	532.0	530.5	528.9	526.6	523.5	520.5	517.4	514.3	511.3
67.5°	458.2	456.8	455.4	454.0	452.5	450.4	447.4	444.5	441.5	438.6	435.6
70°	410.6	408.5	406.3	404.2	402.0	399.7	397.3	394.8	392.4	389.9	387.4
72.5°	359.8	357.6	355.5	353.3	351.2	349.1	347.1	345.2	343.2	341.2	339.3
75°	284.8	283.3	281.7	280.2	278.7	277.1	275.6	274.1	272.5	271.0	269.8
77.5°	213.2	212.5	211.8	211.2	210.5	209.5	208.1	206.8	205.4	204.1	203.7
80°	170.1	169.1	168.2	167.3	166.4	165.6	165.0	164.4	163.8	163.1	162.5
82.5°	128.0	127.6	127.2	126.7	126.3	126.0	125.9	125.8	125.7	125.5	125.2
85°	74.7	74.7	74.7	74.7	74.7	74.4	73.7	73.1	72.5	71.9	71.9
87.5°	29.4	29.6	29.8	30.1	30.3	30.5	30.6	30.7	30.8	30.9	31.2
90°	3.0	5.4	7.9	10.3	12.8	14.9	16.6	18.4	20.2	22.0	23.3
92.5°	21.4	24.2	26.9	29.7	32.5	34.6	35.8	37.0	38.3	39.5	40.3
95°	59.9	61.9	63.9	65.9	67.9	69.6	71.2	72.8	74.3	75.9	76.5
97.5°	104.6	106.2	107.8	109.4	111.0	112.7	114.5	116.3	118.2	120.0	120.8
100°	139.7	140.6	141.5	142.4	143.3	144.7	146.7	148.7	150.7	152.7	153.2
102.5°	176.5	176.8	177.2	177.5	177.9	179.0	180.8	182.6	184.4	186.3	186.9
105°	232.6	232.8	233.0	233.2	233.5	234.0	234.9	235.8	236.7	237.6	238.2
107.5°	291.5	291.7	292.0	292.3	292.5	292.7	292.9	293.0	293.1	293.3	293.9
110°	331.4	331.8	332.3	332.7	333.2	333.3	333.0	332.8	332.6	332.4	331.9



TEST NUMBER: P332659

CATALOG NUMBER: S124DIP-S1020D1035U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	372.9	373.0	373.1	373.2	373.3	373.1	372.7	372.3	371.9	371.5	371.4
115°	435.2	435.2	435.2	435.2	435.2	435.0	434.5	434.1	433.6	433.2	433.0
117.5°	493.9	494.1	494.2	494.4	494.6	494.5	494.2	493.9	493.6	493.3	492.5
120°	533.0	533.9	534.8	535.7	536.6	536.7	536.0	535.3	534.7	534.0	532.9
122.5°	573.7	574.1	574.4	574.8	575.1	575.2	574.9	574.5	574.2	573.9	573.2
125°	633.8	633.8	633.8	633.8	633.8	633.7	633.5	633.3	633.0	632.8	632.4
127.5°	688.3	689.0	689.6	690.3	691.0	691.1	690.8	690.4	690.1	689.7	689.3
130°	726.6	727.3	728.0	728.6	729.3	729.6	729.6	729.6	729.6	729.6	729.2
132.5°	765.8	766.3	766.7	767.2	767.7	767.9	767.7	767.5	767.3	767.2	766.7
135°	817.5	818.8	820.1	821.5	822.8	823.5	823.5	823.5	823.5	823.5	823.0
137.5°	873.8	874.4	875.0	875.6	876.3	876.7	877.1	877.5	877.8	878.2	877.6
140°	911.3	911.7	912.2	912.6	913.1	913.3	913.3	913.3	913.3	913.3	913.1
142.5°	945.6	946.1	946.5	947.0	947.4	947.5	947.4	947.2	947.0	946.8	946.8
145°	993.1	994.0	994.9	995.8	996.7	997.2	997.5	997.7	997.9	998.1	997.9
147.5°	1040.3	1041.3	1042.4	1043.5	1044.5	1045.0	1044.8	1044.6	1044.4	1044.3	1044.1
150°	1069.0	1069.9	1070.8	1071.7	1072.6	1073.0	1073.0	1073.0	1073.0	1073.0	1073.0
152.5°	1096.2	1096.7	1097.2	1097.8	1098.3	1098.6	1098.8	1099.0	1099.2	1099.3	1099.9
155°	1137.9	1137.9	1137.9	1137.9	1137.9	1137.8	1137.5	1137.3	1137.1	1136.9	1137.8
157.5°	1173.0	1172.6	1172.2	1171.8	1171.4	1171.2	1171.1	1171.1	1171.1	1171.0	1171.7
160°	1193.8	1193.5	1193.3	1193.1	1192.9	1192.7	1192.4	1192.2	1192.0	1191.8	1192.4
162.5°	1212.9	1212.4	1211.8	1211.2	1210.6	1210.2	1210.0	1209.8	1209.6	1209.3	1210.5
165°	1238.7	1238.0	1237.4	1236.7	1236.0	1235.5	1235.0	1234.6	1234.1	1233.7	1235.0
167.5°	1258.5	1257.5	1256.6	1255.7	1254.7	1254.3	1254.3	1254.4	1254.4	1254.5	1255.8
170°	1269.6	1268.5	1267.4	1266.3	1265.2	1264.7	1265.0	1265.2	1265.4	1265.6	1267.0
172.5°	1277.6	1276.7	1275.8	1274.8	1273.9	1273.4	1273.5	1273.5	1273.6	1273.6	1275.1
175°	1288.6	1287.5	1286.4	1285.3	1284.2	1283.5	1283.3	1283.0	1282.8	1282.6	1284.2
177.5°	1292.2	1291.3	1290.4	1289.5	1288.6	1288.2	1288.2	1288.2	1288.2	1288.2	1289.4
180°	1290.6	1290.6	1290.6	1290.6	1290.6	1290.6	1290.6	1290.6	1290.6	1290.6	1290.6



TEST NUMBER: P332659

CATALOG NUMBER: S124DIP-S1020D1035U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5
2.5°	1719.3	1721.8	1724.3	1725.4	1725.1	1724.9	1724.6	1724.4
5°	1710.1	1713.5	1716.9	1718.3	1717.7	1717.0	1716.4	1715.8
7.5°	1691.1	1693.8	1696.5	1697.7	1697.3	1696.9	1696.5	1696.2
10°	1675.1	1677.6	1680.0	1680.9	1680.3	1679.7	1679.1	1678.5
12.5°	1655.7	1658.4	1661.1	1662.0	1661.2	1660.3	1659.4	1658.6
15°	1618.6	1620.4	1622.3	1622.7	1621.8	1620.9	1620.0	1619.0
17.5°	1576.3	1577.5	1578.6	1578.9	1578.3	1577.7	1577.1	1576.4
20°	1544.8	1545.8	1546.7	1546.8	1546.2	1545.6	1545.0	1544.4
22.5°	1512.0	1513.7	1515.3	1515.6	1514.5	1513.4	1512.3	1511.2
25°	1457.9	1458.2	1458.5	1458.0	1456.8	1455.6	1454.3	1453.1
27.5°	1397.2	1396.4	1395.7	1394.6	1393.0	1391.5	1389.9	1388.4
30°	1355.3	1354.0	1352.8	1351.4	1349.9	1348.3	1346.8	1345.3
32.5°	1312.7	1311.3	1309.8	1308.3	1306.7	1305.2	1303.7	1302.1
35°	1245.6	1243.4	1241.3	1239.4	1237.9	1236.4	1234.8	1233.3
37.5°	1175.2	1172.9	1170.6	1168.4	1166.4	1164.3	1162.3	1160.3
40°	1126.2	1123.1	1120.1	1117.8	1116.2	1114.7	1113.2	1111.6
42.5°	1078.8	1075.2	1071.6	1069.3	1068.3	1067.2	1066.2	1065.2
45°	1005.3	1001.9	998.5	996.4	995.5	994.6	993.6	992.7
47.5°	934.2	930.4	926.6	923.5	921.2	918.8	916.5	914.2
50°	884.6	880.3	876.0	872.9	871.0	869.2	867.4	865.5
52.5°	833.6	829.7	825.9	822.9	820.5	818.2	815.9	813.5
55°	758.6	754.9	751.2	748.5	746.6	744.8	742.9	741.1
57.5°	683.5	680.0	676.5	673.8	672.0	670.3	668.5	666.7
60°	631.9	629.1	626.3	624.2	622.6	621.1	619.6	618.0
62.5°	581.5	578.9	576.4	574.4	572.9	571.3	569.8	568.3
65°	508.2	505.1	502.0	499.7	498.2	496.7	495.1	493.6
67.5°	432.7	429.7	426.8	425.1	424.6	424.2	423.8	423.4
70°	385.0	382.5	380.1	378.4	377.5	376.5	375.6	374.7
72.5°	337.3	335.3	333.4	331.9	331.0	330.1	329.2	328.2
75°	268.5	267.3	266.1	265.3	265.0	264.7	264.4	264.1
77.5°	203.3	203.0	202.6	202.0	201.2	200.4	199.6	198.8
80°	161.9	161.3	160.7	160.2	159.9	159.6	159.3	159.0
82.5°	124.8	124.4	124.1	123.7	123.4	123.1	122.8	122.5
85°	71.9	71.9	71.9	71.7	71.4	71.1	70.8	70.5
87.5°	31.5	31.7	32.0	32.2	32.3	32.4	32.4	32.5
90°	24.6	26.0	27.3	28.2	28.6	29.1	29.5	29.9
92.5°	41.1	41.9	42.7	43.3	43.5	43.8	44.1	44.3
95°	77.2	77.9	78.5	78.9	78.9	78.9	78.9	78.9
97.5°	121.6	122.4	123.2	123.6	123.6	123.6	123.6	123.6
100°	153.6	154.0	154.5	154.7	154.7	154.7	154.7	154.7
102.5°	187.5	188.1	188.7	189.1	189.3	189.5	189.7	189.8
105°	238.9	239.6	240.2	240.9	241.5	242.2	242.9	243.5
107.5°	294.5	295.1	295.7	296.0	296.0	295.9	295.9	295.8
110°	331.5	331.0	330.6	330.7	331.4	332.0	332.7	333.4





TEST NUMBER: P332659

CATALOG NUMBER: S124DIP-S1020D1035U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	371.3	371.2	371.2	371.2	371.3	371.4	371.6	371.7
115°	432.7	432.5	432.3	432.1	431.9	431.6	431.4	431.2
117.5°	491.8	491.0	490.3	489.7	489.2	488.8	488.3	487.9
120°	531.8	530.7	529.6	529.2	529.7	530.1	530.6	531.0
122.5°	572.4	571.7	570.9	570.1	569.3	568.5	567.7	566.9
125°	631.9	631.5	631.0	630.6	630.2	629.7	629.3	628.8
127.5°	688.8	688.4	687.9	687.5	687.2	686.8	686.5	686.1
130°	728.8	728.3	727.9	727.2	726.3	725.4	724.5	723.6
132.5°	766.3	765.8	765.4	765.0	764.6	764.3	763.9	763.6
135°	822.6	822.1	821.7	821.1	820.5	819.8	819.1	818.5
137.5°	877.0	876.4	875.9	875.6	875.8	875.9	876.0	876.2
140°	912.9	912.6	912.4	912.2	912.0	911.7	911.5	911.3
142.5°	946.7	946.7	946.7	946.6	946.6	946.5	946.5	946.4
145°	997.7	997.5	997.2	996.8	996.1	995.5	994.8	994.1
147.5°	1043.9	1043.7	1043.5	1043.3	1043.1	1042.9	1042.7	1042.5
150°	1073.0	1073.0	1073.0	1072.9	1072.7	1072.4	1072.2	1072.0
152.5°	1100.4	1100.9	1101.5	1101.5	1100.9	1100.3	1099.7	1099.1
155°	1138.7	1139.5	1140.4	1140.4	1139.5	1138.7	1137.8	1136.9
157.5°	1172.3	1173.0	1173.7	1173.6	1172.9	1172.1	1171.4	1170.6
160°	1193.1	1193.8	1194.4	1194.2	1193.1	1192.0	1190.9	1189.8
162.5°	1211.7	1212.9	1214.1	1214.2	1213.1	1212.0	1210.9	1209.7
165°	1236.4	1237.7	1239.0	1239.2	1238.4	1237.5	1236.6	1235.7
167.5°	1257.1	1258.5	1259.8	1259.8	1258.4	1257.0	1255.6	1254.3
170°	1268.3	1269.6	1271.0	1270.8	1269.3	1267.7	1266.2	1264.6
172.5°	1276.6	1278.1	1279.7	1279.6	1278.1	1276.5	1275.0	1273.4
175°	1285.7	1287.3	1288.8	1288.8	1287.3	1285.7	1284.2	1282.6
177.5°	1290.7	1291.9	1293.2	1293.1	1291.7	1290.2	1288.8	1287.4
180°	1290.6	1290.6	1290.6	1290.6	1290.6	1290.6	1290.6	1290.6

(END OF REPORT)