

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831232

Luminaire Tested: S123DIP-S1165D1195U950-4F0-1E-UDD-G1

Issue Date: 05/03/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P831232  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-1, G3-1807-864-9)  
Test Lab: INNOVATION CENTER  
Issue Date: 05/03/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S1165D1195U950-4F0-1E-UDD-G1  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1165 LUMENS PER FOOT, GRAZE OPTIC  
UPLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8992.3 lumens  
Efficiency: N/A  
Efficacy: 122.8 lumens/watt  
Spacing Criteria (0/90/45): 0.65 / 1.19 / 0.89  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 73.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P831232  
CATALOG NUMBER: S123DIP-S1165D1195U950-4F0-1E-UDD-G1

### Luminous Intensity Polar Plot





TEST NUMBER: P831232

CATALOG NUMBER: S123DIP-S1165D1195U950-4F0-1E-UDD-G1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	57				
1	100	96	92	89	93	89	86	83	77	75	73	66	64	63	56	55	54	49				
2	91	84	78	73	85	79	74	69	68	64	61	59	56	53	50	48	46	42				
3	84	75	68	62	78	70	64	59	61	56	52	53	49	46	45	42	40	36				
4	77	67	59	53	72	63	56	51	55	49	45	47	43	40	41	38	35	32				
5	71	60	52	46	66	56	49	44	49	44	40	43	39	35	37	34	31	28				
6	66	54	46	41	61	51	44	39	45	39	35	39	35	32	34	31	28	25				
7	61	49	42	36	57	46	39	35	41	35	31	36	32	28	31	28	25	23				
8	57	45	38	32	53	43	36	31	38	32	28	33	29	26	29	26	23	21				
9	53	41	34	29	50	39	33	28	35	29	26	31	26	23	27	24	21	19				
10	50	38	31	27	47	36	30	26	32	27	23	29	24	21	25	22	19	18				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°	135°	180°
0°	34013	34013	34013	34013	34013
5°	43015	40599	34317	27654	25412
10°	43432	44746	34088	22045	19264
15°	32712	41545	33857	18668	16291
20°	22793	33617	33424	16325	14797
25°	17380	25852	32687	15020	13879
30°	15035	20539	31510	14097	13140
35°	13950	17341	30154	13429	12620
40°	13207	15556	28247	12795	12444
45°	12767	14397	25825	12298	12365
50°	12548	13480	22958	11848	12301
55°	12080	12810	20142	11419	12356
60°	11649	12090	17362	11016	12152
65°	10942	11410	14976	10588	11915
70°	10106	10543	12737	9876	11213
75°	9145	9453	10917	9179	10243
80°	7544	8269	8635	7996	8635
85°	5978	6706	6336	6793	6879

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 80°  
 Vertical Angle: 45°  
 Luminance: 29486 cd/sqm



TEST NUMBER: P831232

CATALOG NUMBER: S123DIP-S1165D1195U950-4F0-1E-UDD-G1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	298.7	3.3
10°-20°	743.2	8.3
20°-30°	880.0	9.8
30°-40°	884.8	9.8
40°-50°	811.8	9.0
50°-60°	670.0	7.5
60°-70°	474.0	5.3
70°-80°	253.0	2.8
80°-90°	67.2	0.7
90°-100°	90.8	1.0
100°-110°	274.9	3.1
110°-120°	468.0	5.2
120°-130°	615.7	6.8
130°-140°	692.1	7.7
140°-150°	680.4	7.6
150°-160°	572.8	6.4
160°-170°	381.4	4.2
170°-180°	133.5	1.5
0°-30°	1921.9	21.4
0°-40°	2806.7	31.2
0°-60°	4288.4	47.7
0°-90°	5082.6	56.5
90°-120°	833.8	9.3
90°-150°	2822.0	31.4
90°-180°	3910.0	43.5
0°-180°	8992.3	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	3160	3160	3160	3160	3160	
5°	3981	3757	3176	2559	2352	379
15°	2936	3728	3038	1675	1462	811
25°	1463	2177	2752	1265	1169	691
35°	1062	1320	2295	1022	960	667
45°	839	946	1696	808	812	650
55°	644	683	1073	608	658	576
65°	430	448	588	416	468	427
75°	220	227	262	221	246	231
85°	48	54	51	55	56	54
90°	33	27	1	27	33	19
95°	86	82	65	82	86	87
105°	264	262	249	262	264	280
115°	472	472	471	472	472	468
125°	682	691	689	691	682	610
135°	893	900	894	900	893	687
145°	1085	1091	1085	1091	1085	678
155°	1240	1244	1243	1244	1240	571
165°	1349	1350	1353	1350	1349	381
175°	1402	1403	1408	1403	1402	133
180°	1411	1411	1411	1411	1411	



TEST NUMBER: P831232

CATALOG NUMBER: S123DIP-S1165D1195U950-4F0-1E-UDD-G1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	3159.9	3159.9	3159.9	3159.9	3159.9	3159.9	3159.9	3159.9	3159.9	3159.9	3159.9
2.5°	3561.6	3558.0	3554.3	3536.0	3517.7	3508.9	3500.1	3473.7	3447.3	3417.9	3388.6
5°	3981.0	3991.3	4001.5	3989.8	3978.1	3942.2	3906.2	3858.6	3810.9	3757.4	3703.9
7.5°	4174.6	4180.4	4186.3	4179.0	4171.6	4162.1	4152.6	4110.0	4067.5	4012.5	3957.5
10°	3973.7	3986.9	4000.1	4028.7	4057.3	4089.5	4121.8	4115.9	4110.0	4093.9	4077.8
12.5°	3532.3	3548.4	3564.6	3621.8	3679.0	3752.3	3825.6	3888.6	3951.7	3995.7	4039.7
15°	2935.5	2980.3	3025.0	3077.0	3129.1	3236.9	3344.6	3477.3	3610.0	3728.1	3846.1
17.5°	2417.9	2434.8	2451.7	2507.4	2563.1	2698.7	2834.4	2987.6	3140.8	3336.6	3532.3
20°	1989.8	2005.2	2020.6	2093.9	2167.2	2273.5	2379.8	2552.1	2724.4	2934.8	3145.2
22.5°	1671.6	1695.8	1720.0	1761.0	1802.1	1904.0	2005.9	2159.1	2312.4	2544.8	2777.2
25°	1463.4	1481.0	1498.6	1523.5	1548.4	1629.8	1711.2	1837.3	1963.4	2176.7	2390.1
27.5°	1321.1	1328.5	1335.8	1360.7	1385.7	1438.4	1491.2	1599.7	1708.2	1889.3	2070.4
30°	1209.7	1214.8	1220.0	1242.0	1264.0	1299.9	1335.8	1414.2	1492.7	1652.5	1812.3
32.5°	1132.0	1135.7	1139.3	1156.2	1173.0	1198.7	1224.4	1281.5	1338.7	1470.7	1602.7
35°	1061.6	1063.8	1066.0	1078.5	1090.9	1110.0	1129.1	1172.3	1215.6	1319.7	1423.8
37.5°	1000.0	1003.0	1005.9	1013.2	1020.5	1037.4	1054.3	1088.7	1123.2	1203.1	1283.0
40°	939.9	945.0	950.2	955.3	960.4	974.4	988.3	1014.7	1041.1	1107.1	1173.0
42.5°	888.6	893.7	898.8	901.0	903.2	911.3	919.4	943.6	967.8	1016.9	1066.0
45°	838.7	840.9	843.1	845.3	847.5	854.1	860.7	882.0	903.2	945.8	988.3
47.5°	793.3	793.3	793.3	794.7	796.2	802.1	807.9	823.3	838.7	871.7	904.7
50°	749.3	749.3	749.3	747.1	744.9	748.5	752.2	763.9	775.7	805.0	834.3
52.5°	696.5	696.5	696.5	697.2	698.0	698.0	698.0	708.2	718.5	744.9	771.3
55°	643.7	646.6	649.6	647.4	645.2	646.6	648.1	654.7	661.3	682.6	703.8
57.5°	590.9	592.4	593.9	593.1	592.4	593.1	593.9	599.7	605.6	621.7	637.8
60°	541.1	541.1	541.1	539.6	538.1	539.6	541.1	544.0	546.9	561.6	576.3
62.5°	485.3	486.1	486.8	487.5	488.3	486.8	485.3	489.0	492.7	503.7	514.7
65°	429.6	430.4	431.1	433.3	435.5	434.0	432.6	436.2	439.9	448.0	456.0
67.5°	379.8	378.3	376.8	377.6	378.3	380.5	382.7	383.4	384.2	393.0	401.8
70°	321.1	322.6	324.1	323.3	322.6	323.3	324.1	326.3	328.5	335.0	341.6
72.5°	268.3	269.1	269.8	269.8	269.8	271.3	272.7	274.9	277.1	280.8	284.5
75°	219.9	219.9	219.9	221.4	222.9	223.6	224.3	224.3	224.3	227.3	230.2
77.5°	167.2	170.8	174.5	173.8	173.0	174.5	176.0	178.2	180.4	181.8	183.3
80°	121.7	121.7	121.7	122.4	123.2	125.4	127.6	129.0	130.5	133.4	136.4
82.5°	77.7	78.4	79.2	81.4	83.6	85.0	86.5	88.7	90.9	90.9	90.9
85°	48.4	46.9	45.5	46.9	48.4	49.9	51.3	52.1	52.8	54.3	55.7
87.5°	23.5	23.5	23.5	23.5	23.5	24.2	24.9	24.9	24.9	24.9	24.9
90°	33.3	32.8	32.3	31.8	31.3	30.5	29.6	28.6	27.6	26.6	23.4
92.5°	47.7	48.2	48.6	49.1	49.6	49.5	48.8	48.0	47.3	46.6	45.1
95°	86.5	86.5	86.5	86.5	86.5	86.0	85.0	84.0	83.0	82.0	80.1
97.5°	124.1	124.4	124.6	124.9	125.1	124.6	123.4	122.2	120.9	119.7	118.2
100°	168.5	168.0	167.5	167.0	166.5	165.9	165.2	164.4	163.7	162.9	161.7
102.5°	213.9	214.2	214.4	214.7	214.9	214.7	213.9	213.2	212.5	211.7	210.0
105°	263.8	263.3	262.8	262.3	261.8	261.6	261.6	261.6	261.6	261.6	259.4
107.5°	314.8	315.0	315.3	315.5	315.8	315.5	314.8	314.1	313.3	312.6	311.6
110°	366.9	367.4	367.9	368.4	368.9	368.6	367.6	366.6	365.7	364.7	364.2



TEST NUMBER: P831232

CATALOG NUMBER: S123DIP-S1165D1195U950-4F0-1E-UDD-G1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	422.3	422.3	422.3	422.3	422.3	421.7	420.5	419.2	418.0	416.8	416.8
115°	472.2	472.4	472.7	472.9	473.2	473.2	472.9	472.7	472.4	472.2	472.7
117.5°	523.2	523.9	524.7	525.4	526.1	526.5	526.5	526.5	526.5	526.5	527.0
120°	577.5	578.0	578.5	579.0	579.5	579.8	580.1	580.3	580.6	580.8	582.1
122.5°	629.6	630.3	631.1	631.8	632.5	633.3	634.0	634.8	635.5	636.2	636.7
125°	681.7	682.7	683.7	684.6	685.6	686.6	687.6	688.6	689.6	690.6	691.0
127.5°	733.8	734.8	735.8	736.7	737.7	739.0	740.4	741.9	743.4	744.9	745.4
130°	784.8	786.5	788.2	789.9	791.7	793.0	794.0	795.0	796.0	797.0	797.7
132.5°	838.0	839.2	840.4	841.7	842.9	844.1	845.4	846.6	847.8	849.1	849.6
135°	893.4	893.9	894.4	894.9	895.4	896.1	897.1	898.1	899.1	900.0	900.3
137.5°	942.2	942.9	943.6	944.4	945.1	946.1	947.3	948.6	949.8	951.0	950.3
140°	989.8	991.6	993.3	995.0	996.7	997.7	998.0	998.2	998.5	998.7	998.5
142.5°	1038.6	1039.8	1041.1	1042.3	1043.5	1044.3	1044.5	1044.8	1045.0	1045.3	1044.8
145°	1085.2	1086.1	1087.1	1088.1	1089.1	1089.7	1090.0	1090.2	1090.5	1090.7	1090.0
147.5°	1127.3	1128.8	1130.2	1131.7	1133.2	1133.9	1133.9	1133.9	1133.9	1133.9	1133.2
150°	1167.2	1168.7	1170.1	1171.6	1173.1	1173.8	1173.8	1173.8	1173.8	1173.8	1173.3
152.5°	1206.0	1207.2	1208.4	1209.7	1210.9	1211.3	1210.8	1210.3	1209.8	1209.3	1209.1
155°	1240.3	1242.1	1243.8	1245.5	1247.2	1247.6	1246.6	1245.6	1244.6	1243.7	1243.4
157.5°	1272.5	1274.0	1275.4	1276.9	1278.4	1278.6	1277.7	1276.7	1275.7	1274.7	1274.5
160°	1303.5	1304.5	1305.5	1306.5	1307.5	1307.3	1306.1	1304.9	1303.6	1302.4	1302.4
162.5°	1326.8	1328.5	1330.2	1332.0	1333.7	1333.9	1332.7	1331.5	1330.2	1329.0	1328.8
165°	1349.0	1350.7	1352.4	1354.1	1355.9	1356.0	1354.5	1353.0	1351.6	1350.1	1350.1
167.5°	1368.9	1370.4	1371.9	1373.4	1374.8	1374.8	1373.4	1371.9	1370.4	1368.9	1368.7
170°	1383.3	1385.1	1386.8	1388.5	1390.2	1390.2	1388.5	1386.8	1385.1	1383.3	1383.3
172.5°	1394.4	1396.1	1397.9	1399.6	1401.3	1401.4	1400.0	1398.5	1397.0	1395.5	1395.5
175°	1402.2	1403.9	1405.6	1407.3	1409.1	1409.2	1407.7	1406.2	1404.8	1403.3	1403.3
177.5°	1406.6	1408.3	1410.1	1411.8	1413.5	1413.6	1412.1	1410.7	1409.2	1407.7	1407.7
180°	1411.0	1411.0	1411.0	1411.0	1411.0	1411.0	1411.0	1411.0	1411.0	1411.0	1411.0



TEST NUMBER: P831232

CATALOG NUMBER: S123DIP-S1165D1195U950-4F0-1E-UDD-G1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	3159.9	3159.9	3159.9	3159.9	3159.9	3159.9	3159.9	3159.9	3159.9	3159.9	3159.9
2.5°	3379.8	3371.0	3338.8	3306.5	3269.9	3233.2	3206.1	3178.9	3138.6	3098.3	3065.3
5°	3662.8	3621.8	3553.6	3485.4	3393.0	3300.6	3238.3	3176.0	3092.4	3008.9	2942.1
7.5°	3887.2	3816.8	3721.5	3626.2	3505.2	3384.2	3269.9	3155.5	3027.9	2900.3	2796.2
10°	4030.1	3982.5	3872.5	3762.5	3600.5	3438.5	3278.6	3118.8	2954.6	2790.4	2652.5
12.5°	4044.1	4048.5	3947.3	3846.1	3662.8	3479.5	3285.2	3091.0	2884.2	2677.5	2516.9
15°	3921.6	3997.1	3941.4	3885.7	3700.9	3516.2	3277.2	3038.2	2799.9	2561.6	2376.1
17.5°	3694.3	3856.4	3864.4	3872.5	3687.7	3503.0	3238.3	2973.7	2703.9	2434.1	2239.0
20°	3384.2	3623.2	3705.3	3787.5	3637.2	3486.9	3202.4	2917.9	2615.9	2313.8	2109.3
22.5°	3067.5	3357.8	3508.1	3658.4	3547.0	3435.5	3132.8	2830.0	2511.0	2192.1	1984.6
25°	2706.8	3023.5	3254.5	3485.4	3417.2	3349.0	3050.6	2752.2	2412.8	2073.4	1861.5
27.5°	2392.3	2714.1	2992.7	3271.3	3256.7	3242.0	2945.8	2649.6	2302.1	1954.6	1750.0
30°	2112.2	2412.1	2723.7	3035.2	3071.2	3107.1	2821.2	2535.2	2187.0	1838.7	1641.5
32.5°	1864.4	2126.1	2460.5	2794.8	2865.2	2935.5	2677.5	2419.4	2074.8	1730.2	1540.3
35°	1661.3	1898.9	2233.2	2567.5	2655.5	2743.4	2519.1	2294.8	1959.0	1623.2	1442.1
37.5°	1481.7	1680.4	2006.6	2332.9	2440.7	2548.4	2347.5	2146.7	1832.1	1517.6	1351.2
40°	1332.9	1492.7	1792.6	2092.4	2217.0	2341.7	2176.0	2010.3	1711.9	1413.5	1260.3
42.5°	1208.2	1350.5	1622.5	1894.5	2014.0	2133.5	1993.4	1853.4	1588.0	1322.6	1182.6
45°	1101.9	1215.6	1462.6	1709.7	1823.3	1937.0	1816.7	1696.5	1462.6	1228.8	1098.3
47.5°	1002.2	1099.7	1310.9	1522.0	1623.2	1724.4	1630.5	1536.7	1338.7	1140.8	1022.7
50°	912.8	991.2	1176.0	1360.7	1448.7	1536.7	1453.8	1371.0	1208.2	1045.5	942.8
52.5°	835.1	898.8	1053.5	1208.2	1283.7	1359.3	1288.1	1217.0	1088.0	959.0	869.5
55°	758.1	812.3	946.5	1080.7	1132.0	1183.3	1128.3	1073.3	969.2	865.1	789.6
57.5°	686.2	734.6	844.6	954.6	994.2	1033.7	983.9	934.0	855.6	777.1	714.1
60°	615.8	655.4	747.1	838.7	862.9	887.1	846.8	806.5	751.5	696.5	640.0
62.5°	550.6	586.5	654.7	722.9	739.0	755.1	724.4	693.6	651.8	610.0	566.0
65°	483.1	510.3	566.0	621.7	632.0	642.2	615.1	588.0	556.5	524.9	492.7
67.5°	420.8	439.9	485.3	530.8	531.5	532.3	510.3	488.3	470.7	453.1	427.4
70°	360.0	378.3	408.4	438.4	439.2	439.9	422.3	404.7	391.5	378.3	359.2
72.5°	297.7	310.9	333.6	356.3	354.8	353.4	342.4	331.4	321.1	310.9	296.9
75°	241.2	252.2	267.6	283.0	278.6	274.2	268.3	262.5	253.7	244.9	236.1
77.5°	189.9	196.5	205.3	214.1	211.1	208.2	203.1	198.0	191.4	184.8	181.1
80°	139.3	142.2	148.1	154.0	152.5	151.0	145.2	139.3	137.8	136.4	131.2
82.5°	94.6	98.2	99.7	101.2	100.4	99.7	95.3	90.9	89.4	88.0	87.2
85°	56.5	57.2	57.9	58.7	56.5	54.3	52.8	51.3	51.3	51.3	50.6
87.5°	25.7	26.4	26.4	26.4	25.7	24.9	23.5	22.0	22.7	23.5	23.5
90°	20.2	17.0	13.8	11.0	8.5	6.0	3.6	1.1	3.6	6.0	8.5
92.5°	43.6	42.1	40.6	39.2	37.7	36.2	34.7	33.3	34.7	36.2	37.7
95°	78.1	76.1	74.1	72.3	70.6	68.8	67.1	65.4	67.1	68.8	70.6
97.5°	116.8	115.3	113.8	112.4	111.2	110.0	108.7	107.5	108.7	110.0	111.2
100°	160.5	159.2	158.0	156.7	155.2	153.7	152.2	150.7	152.2	153.7	155.2
102.5°	208.3	206.5	204.8	203.6	202.8	202.1	201.4	200.6	201.4	202.1	202.8
105°	257.2	254.9	252.7	251.4	250.9	250.4	249.9	249.4	249.9	250.4	250.9
107.5°	310.6	309.6	308.6	308.0	307.8	307.5	307.3	307.0	307.3	307.5	307.8
110°	363.7	363.2	362.7	362.2	361.7	361.2	360.7	360.2	360.7	361.2	361.7





TEST NUMBER: P831232

CATALOG NUMBER: S123DIP-S1165D1195U950-4F0-1E-UDD-G1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	416.8	416.8	416.8	416.6	416.4	416.2	415.9	415.7	415.9	416.2	416.4
115°	473.2	473.7	474.2	474.0	473.3	472.6	471.8	471.1	471.8	472.6	473.3
117.5°	527.5	528.0	528.5	528.6	528.4	528.1	527.9	527.6	527.9	528.1	528.4
120°	583.3	584.5	585.7	585.6	584.1	582.7	581.2	579.7	581.2	582.7	584.1
122.5°	637.2	637.7	638.2	638.0	637.0	636.0	635.0	634.0	635.0	636.0	637.0
125°	691.5	692.0	692.5	692.4	691.7	690.9	690.2	689.4	690.2	690.9	691.7
127.5°	745.9	746.3	746.8	746.3	744.9	743.4	741.9	740.4	741.9	743.4	744.9
130°	798.4	799.2	799.9	799.3	797.3	795.4	793.4	791.4	793.4	795.4	797.3
132.5°	850.0	850.5	851.0	850.3	848.3	846.4	844.4	842.4	844.4	846.4	848.3
135°	900.5	900.8	901.0	900.4	898.9	897.5	896.0	894.5	896.0	897.5	898.9
137.5°	949.6	948.8	948.1	947.1	945.9	944.6	943.4	942.2	943.4	944.6	945.9
140°	998.2	998.0	997.7	997.0	995.7	994.5	993.3	992.0	993.3	994.5	995.7
142.5°	1044.3	1043.8	1043.3	1042.4	1041.2	1040.0	1038.7	1037.5	1038.7	1040.0	1041.2
145°	1089.2	1088.5	1087.7	1087.1	1086.6	1086.1	1085.7	1085.2	1085.7	1086.1	1086.6
147.5°	1132.5	1131.7	1131.0	1130.1	1129.1	1128.1	1127.2	1126.2	1127.2	1128.1	1129.1
150°	1172.8	1172.4	1171.9	1171.4	1170.9	1170.4	1169.9	1169.4	1169.9	1170.4	1170.9
152.5°	1208.8	1208.6	1208.3	1207.8	1207.1	1206.3	1205.6	1204.9	1205.6	1206.3	1207.1
155°	1243.2	1242.9	1242.7	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6	1242.6
157.5°	1274.2	1274.0	1273.7	1273.7	1274.0	1274.2	1274.5	1274.7	1274.5	1274.2	1274.0
160°	1302.4	1302.4	1302.4	1302.7	1303.2	1303.6	1304.1	1304.6	1304.1	1303.6	1303.2
162.5°	1328.5	1328.3	1328.0	1328.3	1329.0	1329.8	1330.5	1331.2	1330.5	1329.8	1329.0
165°	1350.1	1350.1	1350.1	1350.4	1351.2	1351.9	1352.7	1353.4	1352.7	1351.9	1351.2
167.5°	1368.4	1368.2	1367.9	1368.3	1369.3	1370.3	1371.3	1372.2	1371.3	1370.3	1369.3
170°	1383.3	1383.3	1383.3	1383.8	1384.8	1385.8	1386.8	1387.8	1386.8	1385.8	1384.8
172.5°	1395.5	1395.5	1395.5	1396.0	1397.0	1398.0	1399.0	1400.0	1399.0	1398.0	1397.0
175°	1403.3	1403.3	1403.3	1403.8	1404.8	1405.7	1406.7	1407.7	1406.7	1405.7	1404.8
177.5°	1407.7	1407.7	1407.7	1408.2	1409.2	1410.2	1411.2	1412.1	1411.2	1410.2	1409.2
180°	1411.0	1411.0	1411.0	1411.0	1411.0	1411.0	1411.0	1411.0	1411.0	1411.0	1411.0



TEST NUMBER: P831232

CATALOG NUMBER: S123DIP-S1165D1195U950-4F0-1E-UDD-G1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	3159.9	3159.9	3159.9	3159.9	3159.9	3159.9	3159.9	3159.9	3159.9	3159.9	3159.9
2.5°	3032.3	3003.7	2975.1	2953.1	2931.1	2893.7	2856.4	2847.6	2838.8	2826.3	2813.8
5°	2875.4	2805.0	2734.7	2671.6	2608.6	2559.4	2510.3	2478.0	2445.8	2422.3	2398.9
7.5°	2692.1	2586.6	2481.0	2406.2	2331.4	2260.3	2189.2	2166.5	2143.7	2112.9	2082.1
10°	2514.7	2398.1	2281.6	2184.1	2086.5	2016.9	1947.2	1919.4	1891.5	1852.7	1813.8
12.5°	2356.3	2228.8	2101.2	2003.0	1904.7	1837.3	1769.8	1729.5	1689.2	1667.2	1645.2
15°	2190.7	2054.3	1917.9	1827.0	1736.1	1675.2	1614.4	1579.2	1544.0	1522.8	1501.5
17.5°	2044.0	1909.1	1774.2	1687.0	1599.7	1544.0	1488.3	1457.5	1426.7	1410.6	1394.5
20°	1904.7	1772.8	1640.8	1555.7	1470.7	1425.2	1379.8	1360.0	1340.2	1327.0	1313.8
22.5°	1777.2	1647.4	1517.6	1445.0	1372.5	1335.8	1299.1	1285.2	1271.3	1260.3	1249.3
25°	1649.6	1533.8	1417.9	1356.3	1294.7	1264.7	1234.6	1220.7	1206.8	1195.8	1184.8
27.5°	1545.5	1434.8	1324.1	1271.3	1218.5	1195.0	1171.6	1160.6	1149.6	1139.3	1129.1
30°	1444.3	1345.3	1246.4	1200.9	1155.4	1134.2	1112.9	1101.9	1090.9	1081.4	1071.9
32.5°	1350.5	1265.4	1180.4	1138.6	1096.8	1079.2	1061.6	1048.4	1035.2	1027.9	1020.5
35°	1261.0	1184.8	1108.5	1074.1	1039.6	1022.0	1004.4	993.4	982.4	976.6	970.7
37.5°	1184.8	1116.6	1048.4	1015.4	982.4	965.6	948.7	939.2	929.6	927.4	925.2
40°	1107.1	1048.4	989.8	957.5	925.2	910.6	895.9	890.0	884.2	882.7	881.2
42.5°	1042.5	985.4	928.2	898.8	869.5	857.1	844.6	841.7	838.7	840.9	843.1
45°	967.8	920.1	872.4	845.3	818.2	807.9	797.7	795.5	793.3	797.7	802.1
47.5°	904.7	860.7	816.7	791.1	765.4	758.1	750.7	750.0	749.3	755.1	761.0
50°	840.2	797.7	755.1	734.6	714.1	707.5	700.9	703.1	705.3	714.8	724.4
52.5°	780.1	740.5	700.9	681.8	662.8	658.4	654.0	659.1	664.2	674.5	684.8
55°	714.1	678.2	642.2	627.6	612.9	608.5	604.1	614.4	624.6	634.2	643.7
57.5°	651.0	619.5	588.0	574.8	561.6	560.9	560.1	569.7	579.2	589.5	599.7
60°	583.6	557.2	530.8	520.5	510.3	511.7	513.2	524.2	535.2	543.3	551.3
62.5°	522.0	500.0	478.0	468.5	459.0	462.6	466.3	477.3	488.3	497.8	507.3
65°	460.4	442.1	423.8	417.2	410.6	415.7	420.8	430.4	439.9	446.5	453.1
67.5°	401.8	386.4	371.0	365.8	360.7	365.8	371.0	380.5	390.0	396.6	403.2
70°	340.2	327.7	315.3	311.6	307.9	313.8	319.7	327.7	335.8	342.4	349.0
72.5°	283.0	273.5	263.9	263.2	262.5	267.6	272.7	280.8	288.9	293.3	297.7
75°	227.3	222.1	217.0	216.3	215.5	220.7	225.8	230.2	234.6	238.3	241.9
77.5°	177.4	173.0	168.6	169.4	170.1	173.8	177.4	181.8	186.2	188.4	190.6
80°	126.1	124.6	123.2	124.6	126.1	129.0	132.0	134.9	137.8	139.3	140.8
82.5°	86.5	85.0	83.6	85.8	88.0	90.2	92.4	94.6	96.8	97.5	98.2
85°	49.9	52.1	54.3	54.3	54.3	55.0	55.7	56.5	57.2	56.5	55.7
87.5°	23.5	24.2	24.9	24.9	24.9	25.7	26.4	26.4	26.4	25.7	24.9
90°	11.0	13.8	17.0	20.2	23.4	26.6	27.6	28.6	29.6	30.5	31.3
92.5°	39.2	40.6	42.1	43.6	45.1	46.6	47.3	48.0	48.8	49.5	49.6
95°	72.3	74.1	76.1	78.1	80.1	82.0	83.0	84.0	85.0	86.0	86.5
97.5°	112.4	113.8	115.3	116.8	118.2	119.7	120.9	122.2	123.4	124.6	125.1
100°	156.7	158.0	159.2	160.5	161.7	162.9	163.7	164.4	165.2	165.9	166.5
102.5°	203.6	204.8	206.5	208.3	210.0	211.7	212.5	213.2	213.9	214.7	214.9
105°	251.4	252.7	254.9	257.2	259.4	261.6	261.6	261.6	261.6	261.6	261.8
107.5°	308.0	308.6	309.6	310.6	311.6	312.6	313.3	314.1	314.8	315.5	315.8
110°	362.2	362.7	363.2	363.7	364.2	364.7	365.7	366.6	367.6	368.6	368.9



TEST NUMBER: P831232

CATALOG NUMBER: S123DIP-S1165D1195U950-4F0-1E-UDD-G1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	416.6	416.8	416.8	416.8	416.8	416.8	418.0	419.2	420.5	421.7	422.3
115°	474.0	474.2	473.7	473.2	472.7	472.2	472.4	472.7	472.9	473.2	473.2
117.5°	528.6	528.5	528.0	527.5	527.0	526.5	526.5	526.5	526.5	526.5	526.1
120°	585.6	585.7	584.5	583.3	582.1	580.8	580.6	580.3	580.1	579.8	579.5
122.5°	638.0	638.2	637.7	637.2	636.7	636.2	635.5	634.8	634.0	633.3	632.5
125°	692.4	692.5	692.0	691.5	691.0	690.6	689.6	688.6	687.6	686.6	685.6
127.5°	746.3	746.8	746.3	745.9	745.4	744.9	743.4	741.9	740.4	739.0	737.7
130°	799.3	799.9	799.2	798.4	797.7	797.0	796.0	795.0	794.0	793.0	791.7
132.5°	850.3	851.0	850.5	850.0	849.6	849.1	847.8	846.6	845.4	844.1	842.9
135°	900.4	901.0	900.8	900.5	900.3	900.0	899.1	898.1	897.1	896.1	895.4
137.5°	947.1	948.1	948.8	949.6	950.3	951.0	949.8	948.6	947.3	946.1	945.1
140°	997.0	997.7	998.0	998.2	998.5	998.7	998.5	998.2	998.0	997.7	996.7
142.5°	1042.4	1043.3	1043.8	1044.3	1044.8	1045.3	1045.0	1044.8	1044.5	1044.3	1043.5
145°	1087.1	1087.7	1088.5	1089.2	1090.0	1090.7	1090.5	1090.2	1090.0	1089.7	1089.1
147.5°	1130.1	1131.0	1131.7	1132.5	1133.2	1133.9	1133.9	1133.9	1133.9	1133.9	1133.2
150°	1171.4	1171.9	1172.4	1172.8	1173.3	1173.8	1173.8	1173.8	1173.8	1173.8	1173.1
152.5°	1207.8	1208.3	1208.6	1208.8	1209.1	1209.3	1209.8	1210.3	1210.8	1211.3	1210.9
155°	1242.6	1242.7	1242.9	1243.2	1243.4	1243.7	1244.6	1245.6	1246.6	1247.6	1247.2
157.5°	1273.7	1273.7	1274.0	1274.2	1274.5	1274.7	1275.7	1276.7	1277.7	1278.6	1278.4
160°	1302.7	1302.4	1302.4	1302.4	1302.4	1302.4	1303.6	1304.9	1306.1	1307.3	1307.5
162.5°	1328.3	1328.0	1328.3	1328.5	1328.8	1329.0	1330.2	1331.5	1332.7	1333.9	1333.7
165°	1350.4	1350.1	1350.1	1350.1	1350.1	1350.1	1351.6	1353.0	1354.5	1356.0	1355.9
167.5°	1368.3	1367.9	1368.2	1368.4	1368.7	1368.9	1370.4	1371.9	1373.4	1374.8	1374.8
170°	1383.8	1383.3	1383.3	1383.3	1383.3	1383.3	1385.1	1386.8	1388.5	1390.2	1390.2
172.5°	1396.0	1395.5	1395.5	1395.5	1395.5	1395.5	1397.0	1398.5	1400.0	1401.4	1401.3
175°	1403.8	1403.3	1403.3	1403.3	1403.3	1403.3	1404.8	1406.2	1407.7	1409.2	1409.1
177.5°	1408.2	1407.7	1407.7	1407.7	1407.7	1407.7	1409.2	1410.7	1412.1	1413.6	1413.5
180°	1411.0	1411.0	1411.0	1411.0	1411.0	1411.0	1411.0	1411.0	1411.0	1411.0	1411.0



TEST NUMBER: P831232

CATALOG NUMBER: S123DIP-S1165D1195U950-4F0-1E-UDD-G1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
0°	3159.9	3159.9	3159.9	3159.9
2.5°	2808.7	2803.6	2783.0	2762.5
5°	2381.3	2363.7	2357.8	2351.9
7.5°	2080.7	2079.2	2048.4	2017.6
10°	1816.0	1818.2	1790.4	1762.5
12.5°	1626.9	1608.5	1606.3	1604.1
15°	1484.6	1467.8	1464.8	1461.9
17.5°	1384.2	1373.9	1371.0	1368.1
20°	1307.9	1302.1	1296.9	1291.8
22.5°	1242.0	1234.6	1230.2	1225.8
25°	1178.2	1171.6	1170.1	1168.6
27.5°	1121.0	1112.9	1112.9	1112.9
30°	1066.7	1061.6	1059.4	1057.2
32.5°	1016.1	1011.7	1011.7	1011.7
35°	968.5	966.3	963.4	960.4
37.5°	925.2	925.2	923.8	922.3
40°	883.4	885.6	885.6	885.6
42.5°	845.3	847.5	847.5	847.5
45°	805.7	809.4	810.9	812.3
47.5°	766.9	772.7	774.2	775.7
50°	728.8	733.2	733.9	734.6
52.5°	689.9	695.0	698.7	702.4
55°	648.8	654.0	656.2	658.4
57.5°	604.8	610.0	610.7	611.4
60°	556.5	561.6	563.1	564.5
62.5°	510.3	513.2	514.7	516.1
65°	457.5	461.9	464.8	467.8
67.5°	406.9	410.6	410.6	410.6
70°	350.4	351.9	354.1	356.3
72.5°	298.4	299.1	299.1	299.1
75°	243.4	244.9	245.6	246.3
77.5°	191.4	192.1	192.1	192.1
80°	140.0	139.3	139.3	139.3
82.5°	96.0	93.8	93.8	93.8
85°	55.0	54.3	55.0	55.7
87.5°	24.9	24.9	24.9	24.9
90°	31.8	32.3	32.8	33.3
92.5°	49.1	48.6	48.2	47.7
95°	86.5	86.5	86.5	86.5
97.5°	124.9	124.6	124.4	124.1
100°	167.0	167.5	168.0	168.5
102.5°	214.7	214.4	214.2	213.9
105°	262.3	262.8	263.3	263.8
107.5°	315.5	315.3	315.0	314.8
110°	368.4	367.9	367.4	366.9



TEST NUMBER: P831232

CATALOG NUMBER: S123DIP-S1165D1195U950-4F0-1E-UDD-G1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
112.5°	422.3	422.3	422.3	422.3
115°	472.9	472.7	472.4	472.2
117.5°	525.4	524.7	523.9	523.2
120°	579.0	578.5	578.0	577.5
122.5°	631.8	631.1	630.3	629.6
125°	684.6	683.7	682.7	681.7
127.5°	736.7	735.8	734.8	733.8
130°	789.9	788.2	786.5	784.8
132.5°	841.7	840.4	839.2	838.0
135°	894.9	894.4	893.9	893.4
137.5°	944.4	943.6	942.9	942.2
140°	995.0	993.3	991.6	989.8
142.5°	1042.3	1041.1	1039.8	1038.6
145°	1088.1	1087.1	1086.1	1085.2
147.5°	1131.7	1130.2	1128.8	1127.3
150°	1171.6	1170.1	1168.7	1167.2
152.5°	1209.7	1208.4	1207.2	1206.0
155°	1245.5	1243.8	1242.1	1240.3
157.5°	1276.9	1275.4	1274.0	1272.5
160°	1306.5	1305.5	1304.5	1303.5
162.5°	1332.0	1330.2	1328.5	1326.8
165°	1354.1	1352.4	1350.7	1349.0
167.5°	1373.4	1371.9	1370.4	1368.9
170°	1388.5	1386.8	1385.1	1383.3
172.5°	1399.6	1397.9	1396.1	1394.4
175°	1407.3	1405.6	1403.9	1402.2
177.5°	1411.8	1410.1	1408.3	1406.6
180°	1411.0	1411.0	1411.0	1411.0



TEST NUMBER: P831232

CATALOG NUMBER: S123DIP-S1165D1195U950-4F0-1E-UDD-G1

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.41	17.29	17.32	18.21	19.39	18.65	19.53	19.55	20.45	21.63
	3H	18.06	18.85	18.98	19.78	20.98	20.07	20.86	20.99	21.79	22.99
	4H	18.64	19.38	19.57	20.32	21.53	20.52	21.27	21.46	22.20	23.42
	6H	19.01	19.69	19.95	20.64	21.86	20.80	21.49	21.75	22.43	23.65
	8H	19.11	19.76	20.06	20.72	21.94	20.86	21.52	21.82	22.47	23.70
	12H	19.15	19.77	20.11	20.72	21.97	20.88	21.50	21.84	22.46	23.70
4H	2H	16.99	17.73	17.93	18.67	19.88	18.81	19.56	19.75	20.49	21.71
	3H	18.82	19.44	19.77	20.40	21.63	20.43	21.05	21.38	22.02	23.25
	4H	19.52	20.08	20.47	21.04	22.29	21.02	21.58	21.98	22.54	23.79
	6H	19.99	20.48	20.96	21.46	22.71	21.42	21.91	22.39	22.89	24.15
	8H	20.13	20.58	21.10	21.56	22.83	21.54	21.99	22.51	22.97	24.23
	12H	20.20	20.61	21.19	21.60	22.87	21.58	21.99	22.57	22.98	24.25
8H	4H	19.78	20.24	20.76	21.22	22.48	21.12	21.58	22.10	22.56	23.82
	6H	20.37	20.75	21.37	21.77	23.03	21.63	22.00	22.63	23.02	24.29
	8H	20.58	20.91	21.59	21.92	23.20	21.81	22.14	22.81	23.15	24.43
	12H	20.71	21.00	21.72	22.00	23.32	21.91	22.20	22.92	23.20	24.53
12H	4H	19.79	20.20	20.78	21.19	22.46	21.10	21.51	22.09	22.50	23.77
	6H	20.42	20.76	21.43	21.76	23.04	21.64	21.97	22.65	22.98	24.26
	8H	20.66	20.95	21.67	21.95	23.28	21.84	22.13	22.85	23.13	24.46