

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831447

Luminaire Tested: S123DIP-S340D805U950-4F0-1E-UDD-G

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P831447
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-1, G3-1807-864-5)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-S340D805U950-4F0-1E-UDD-G
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, GRAZE OPTIC
UPLIGHT 805 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4568.0 lumens
Efficiency: N/A
Efficacy: 138.4 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 1.19 / 0.89
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 33
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P831447

CATALOG NUMBER: S123DIP-S340D805U950-4F0-1E-UDD-G

Luminous Intensity Polar Plot





TEST NUMBER: P831447

CATALOG NUMBER: S123DIP-S340D805U950-4F0-1E-UDD-G

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	41	41	41	33				
1	94	90	87	83	85	81	78	76	65	63	61	50	49	48	36	36	35	28				
2	86	79	73	69	77	72	67	63	57	54	51	44	42	40	32	31	30	24				
3	79	70	63	58	71	63	57	53	51	47	43	40	37	35	29	27	26	21				
4	72	62	55	49	65	56	50	45	46	41	37	36	32	30	26	24	23	19				
5	66	55	48	42	60	50	44	39	41	36	32	32	29	26	24	22	20	16				
6	61	50	42	37	55	45	39	34	37	32	28	29	26	23	22	20	18	15				
7	57	45	38	32	51	41	35	30	34	29	25	27	23	21	20	18	16	13				
8	53	41	34	29	48	37	31	27	31	26	23	25	21	19	19	16	15	12				
9	49	37	30	26	44	34	28	24	28	24	20	23	19	17	17	15	13	11				
10	46	34	28	23	41	32	25	21	26	22	18	21	18	15	16	14	12	10				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	10083	10083	10083	10083	10083
5°	12751	12035	10172	8198	7533
10°	12874	13264	10105	6535	5710
15°	9697	12315	10036	5534	4829
20°	6756	9964	9907	4840	4386
25°	5152	7663	9689	4453	4114
30°	4457	6088	9340	4179	3895
35°	4135	5140	8938	3980	3741
40°	3915	4612	8373	3792	3688
45°	3784	4267	7655	3646	3666
50°	3719	3996	6805	3512	3647
55°	3581	3796	5971	3385	3663
60°	3453	3584	5147	3266	3602
65°	3245	3382	4439	3138	3533
70°	2996	3125	3777	2927	3323
75°	2712	2803	3236	2720	3036
80°	2238	2455	2560	2368	2560
85°	1766	1988	1877	2013	2038

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 8741 cd/sqm



TEST NUMBER: P831447

CATALOG NUMBER: S123DIP-S340D805U950-4F0-1E-UDD-G

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.6	1.9
10°-20°	220.3	4.8
20°-30°	260.8	5.7
30°-40°	262.3	5.7
40°-50°	240.6	5.3
50°-60°	198.6	4.3
60°-70°	140.5	3.1
70°-80°	75.0	1.6
80°-90°	21.0	0.5
90°-100°	35.4	0.8
100°-110°	171.1	3.7
110°-120°	419.4	9.2
120°-130°	532.4	11.7
130°-140°	568.8	12.5
140°-150°	531.9	11.6
150°-160°	429.0	9.4
160°-170°	276.9	6.1
170°-180°	95.4	2.1
0°-30°	569.7	12.5
0°-40°	832.0	18.2
0°-60°	1271.2	27.8
0°-90°	1507.7	33.0
90°-120°	625.9	13.7
90°-150°	2259.0	49.5
90°-180°	3060.0	67.0
0°-180°	4568.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	937	937	937	937	937	
5°	1180	1114	941	759	697	112
15°	870	1105	901	497	433	240
25°	434	645	816	375	346	205
35°	315	391	680	303	285	198
45°	249	280	503	240	241	193
55°	191	202	318	180	195	171
65°	127	133	174	123	139	127
75°	65	67	78	65	73	68
85°	14	16	15	16	16	16
90°	22	18	1	18	22	11
95°	28	23	46	23	28	24
105°	33	163	222	163	33	68
115°	438	428	417	428	438	412
125°	600	597	588	597	600	536
135°	739	739	732	739	739	570
145°	852	851	844	851	852	532
155°	929	929	930	929	929	428
165°	978	978	981	978	978	276
175°	1000	1001	1004	1001	1000	95
180°	1004	1004	1004	1004	1004	



TEST NUMBER: P831447

CATALOG NUMBER: S123DIP-S340D805U950-4F0-1E-UDD-G

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	936.7	936.7	936.7	936.7	936.7	936.7	936.7	936.7	936.7	936.7	936.7
2.5°	1055.8	1054.7	1053.6	1048.1	1042.7	1040.1	1037.5	1029.7	1021.9	1013.2	1004.5
5°	1180.1	1183.1	1186.1	1182.7	1179.2	1168.5	1157.9	1143.8	1129.6	1113.8	1097.9
7.5°	1237.4	1239.2	1240.9	1238.7	1236.6	1233.7	1230.9	1218.3	1205.7	1189.4	1173.1
10°	1177.9	1181.8	1185.7	1194.2	1202.7	1212.2	1221.8	1220.1	1218.3	1213.5	1208.7
12.5°	1047.1	1051.8	1056.6	1073.6	1090.5	1112.3	1134.0	1152.7	1171.4	1184.4	1197.4
15°	870.2	883.4	896.7	912.1	927.5	959.5	991.4	1030.8	1070.1	1105.1	1140.1
17.5°	716.7	721.7	726.7	743.2	759.8	800.0	840.2	885.6	931.0	989.0	1047.1
20°	589.8	594.4	598.9	620.7	642.4	673.9	705.4	756.5	807.6	869.9	932.3
22.5°	495.5	502.7	509.8	522.0	534.2	564.4	594.6	640.0	685.4	754.3	823.2
25°	433.8	439.0	444.2	451.6	459.0	483.1	507.2	544.6	582.0	645.2	708.5
27.5°	391.6	393.8	396.0	403.4	410.7	426.4	442.0	474.2	506.4	560.0	613.7
30°	358.6	360.1	361.6	368.1	374.7	385.3	396.0	419.2	442.5	489.8	537.2
32.5°	335.5	336.6	337.7	342.7	347.7	355.3	362.9	379.9	396.8	435.9	475.1
35°	314.7	315.3	316.0	319.7	323.4	329.0	334.7	347.5	360.3	391.2	422.0
37.5°	296.4	297.3	298.2	300.3	302.5	307.5	312.5	322.7	332.9	356.6	380.3
40°	278.6	280.1	281.7	283.2	284.7	288.8	293.0	300.8	308.6	328.2	347.7
42.5°	263.4	264.9	266.4	267.1	267.7	270.1	272.5	279.7	286.9	301.4	316.0
45°	248.6	249.3	249.9	250.6	251.2	253.2	255.1	261.4	267.7	280.3	293.0
47.5°	235.1	235.1	235.1	235.6	236.0	237.8	239.5	244.1	248.6	258.4	268.2
50°	222.1	222.1	222.1	221.5	220.8	221.9	223.0	226.5	229.9	238.6	247.3
52.5°	206.5	206.5	206.5	206.7	206.9	206.9	206.9	209.9	213.0	220.8	228.6
55°	190.8	191.7	192.5	191.9	191.2	191.7	192.1	194.1	196.0	202.3	208.6
57.5°	175.2	175.6	176.0	175.8	175.6	175.8	176.0	177.8	179.5	184.3	189.1
60°	160.4	160.4	160.4	159.9	159.5	159.9	160.4	161.3	162.1	166.5	170.8
62.5°	143.9	144.1	144.3	144.5	144.7	144.3	143.9	145.0	146.0	149.3	152.6
65°	127.4	127.6	127.8	128.4	129.1	128.7	128.2	129.3	130.4	132.8	135.2
67.5°	112.6	112.1	111.7	111.9	112.1	112.8	113.4	113.7	113.9	116.5	119.1
70°	95.2	95.6	96.1	95.8	95.6	95.8	96.1	96.7	97.4	99.3	101.3
72.5°	79.5	79.8	80.0	80.0	80.0	80.4	80.8	81.5	82.1	83.2	84.3
75°	65.2	65.2	65.2	65.6	66.1	66.3	66.5	66.5	66.5	67.4	68.2
77.5°	49.5	50.6	51.7	51.5	51.3	51.7	52.2	52.8	53.5	53.9	54.3
80°	36.1	36.1	36.1	36.3	36.5	37.2	37.8	38.2	38.7	39.6	40.4
82.5°	23.0	23.3	23.5	24.1	24.8	25.2	25.6	26.3	26.9	26.9	26.9
85°	14.3	13.9	13.5	13.9	14.3	14.8	15.2	15.4	15.6	16.1	16.5
87.5°	7.0	7.0	7.0	7.0	7.0	7.2	7.4	7.4	7.4	7.4	7.4
90°	22.4	22.0	21.7	21.4	21.0	20.6	19.9	19.2	18.6	17.9	15.7
92.5°	25.4	25.2	25.0	24.9	24.7	24.0	22.9	21.7	20.6	19.4	17.9
95°	28.3	28.3	28.3	28.3	28.3	27.8	26.6	25.4	24.3	23.1	21.3
97.5°	30.6	30.4	30.2	30.1	29.9	29.2	27.8	26.5	25.2	23.9	32.3
100°	31.3	31.2	31.0	30.8	30.7	29.9	28.6	27.3	25.9	24.6	50.5
102.5°	32.1	31.7	31.4	31.1	30.7	33.3	38.8	44.3	49.7	55.2	84.0
105°	32.8	32.5	32.2	31.8	31.5	46.0	75.3	104.7	134.0	163.3	178.3
107.5°	77.6	99.3	121.0	142.7	164.4	188.0	213.6	239.1	264.6	290.1	287.6
110°	205.1	228.8	252.5	276.2	299.9	314.5	320.0	325.4	330.9	336.4	334.5



TEST NUMBER: P831447

CATALOG NUMBER: S123DIP-S340D805U950-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	388.6	388.9	389.2	389.6	389.9	389.3	387.8	386.3	384.8	383.4	381.5
115°	438.5	437.9	437.2	436.6	435.9	434.7	433.1	431.4	429.8	428.1	426.6
117.5°	478.8	478.7	478.5	478.3	478.2	477.4	476.1	474.8	473.4	472.1	471.3
120°	520.6	520.6	520.6	520.6	520.6	519.9	518.6	517.3	515.9	514.6	514.1
122.5°	561.6	561.4	561.3	561.1	560.9	560.5	559.6	558.8	558.0	557.1	556.5
125°	599.6	599.3	599.0	598.7	598.3	598.0	597.7	597.3	597.0	596.7	596.0
127.5°	636.9	637.3	637.6	637.9	638.3	638.2	637.7	637.2	636.7	636.2	635.4
130°	672.7	673.1	673.4	673.7	674.1	673.9	673.2	672.6	671.9	671.2	670.6
132.5°	705.6	706.1	706.6	707.0	707.5	707.5	706.8	706.1	705.5	704.8	704.3
135°	739.1	739.6	740.1	740.6	741.1	741.1	740.6	740.1	739.6	739.1	738.5
137.5°	771.2	771.5	771.9	772.2	772.5	772.3	771.4	770.6	769.8	769.0	768.6
140°	799.5	799.9	800.2	800.5	800.9	800.7	800.0	799.4	798.7	798.0	797.5
142.5°	825.6	826.1	826.6	827.1	827.6	827.6	827.1	826.6	826.1	825.6	825.1
145°	852.5	852.5	852.5	852.5	852.5	852.3	852.0	851.7	851.3	851.0	850.7
147.5°	871.9	872.7	873.5	874.4	875.2	875.4	875.1	874.8	874.4	874.1	873.8
150°	894.3	894.7	895.2	895.7	896.2	896.3	896.0	895.7	895.3	895.0	894.7
152.5°	912.2	913.0	913.8	914.6	915.5	915.6	914.9	914.2	913.6	912.9	912.7
155°	928.6	929.6	930.5	931.5	932.5	932.6	931.8	931.0	930.1	929.3	929.1
157.5°	942.7	944.1	945.4	946.7	948.0	948.2	947.2	946.2	945.2	944.2	944.4
160°	956.2	957.3	958.5	959.6	960.8	960.9	959.9	958.9	957.9	956.9	957.1
162.5°	968.8	969.8	970.8	971.8	972.8	972.7	971.6	970.4	969.3	968.1	968.3
165°	978.5	979.7	980.9	982.0	983.2	983.1	981.8	980.4	979.1	977.8	978.0
167.5°	986.0	987.3	988.6	990.0	991.3	991.3	990.0	988.6	987.3	986.0	986.0
170°	992.7	994.0	995.4	996.7	998.0	998.0	996.7	995.4	994.0	992.7	992.7
172.5°	996.4	997.9	999.4	1000.9	1002.4	1002.5	1001.2	999.8	998.5	997.2	997.0
175°	1000.2	1001.5	1002.8	1004.1	1005.5	1005.5	1004.4	1003.2	1002.1	1000.9	1000.7
177.5°	1000.9	1002.6	1004.2	1005.9	1007.5	1007.7	1006.4	1005.0	1003.7	1002.4	1002.2
180°	1003.9	1003.9	1003.9	1003.9	1003.9	1003.9	1003.9	1003.9	1003.9	1003.9	1003.9



TEST NUMBER: P831447

CATALOG NUMBER: S123DIP-S340D805U950-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	936.7	936.7	936.7	936.7	936.7	936.7	936.7	936.7	936.7	936.7	936.7
2.5°	1001.9	999.3	989.7	980.1	969.3	958.4	950.4	942.3	930.4	918.4	908.6
5°	1085.7	1073.6	1053.4	1033.2	1005.8	978.4	959.9	941.4	916.7	891.9	872.1
7.5°	1152.2	1131.4	1103.1	1074.9	1039.0	1003.2	969.3	935.4	897.5	859.7	828.9
10°	1194.6	1180.5	1147.9	1115.3	1067.3	1019.2	971.9	924.5	875.8	827.1	786.3
12.5°	1198.8	1200.1	1170.1	1140.1	1085.7	1031.4	973.8	916.2	854.9	793.7	746.1
15°	1162.5	1184.8	1168.3	1151.8	1097.0	1042.3	971.4	900.6	830.0	759.3	704.3
17.5°	1095.1	1143.1	1145.5	1147.9	1093.1	1038.4	959.9	881.5	801.5	721.5	663.7
20°	1003.2	1074.0	1098.3	1122.7	1078.1	1033.6	949.3	864.9	775.4	685.9	625.2
22.5°	909.3	995.3	1039.9	1084.4	1051.4	1018.4	928.6	838.9	744.3	649.8	588.3
25°	802.4	896.2	964.7	1033.2	1012.9	992.7	904.3	815.8	715.2	614.6	551.8
27.5°	709.1	804.5	887.1	969.7	965.3	961.0	873.2	785.4	682.4	579.4	518.7
30°	626.1	715.0	807.4	899.7	910.4	921.0	836.3	751.5	648.3	545.0	486.6
32.5°	552.7	630.2	729.3	828.4	849.3	870.2	793.7	717.2	615.0	512.9	456.6
35°	492.5	562.9	662.0	761.1	787.1	813.2	746.7	680.2	580.7	481.2	427.5
37.5°	439.2	498.1	594.8	691.5	723.5	755.4	695.9	636.3	543.1	449.9	400.5
40°	395.1	442.5	531.4	620.2	657.2	694.1	645.0	595.9	507.4	419.0	373.6
42.5°	358.1	400.3	480.9	561.6	597.0	632.4	590.9	549.4	470.7	392.1	350.5
45°	326.6	360.3	433.6	506.8	540.5	574.2	538.5	502.9	433.6	364.2	325.5
47.5°	297.1	326.0	388.6	451.2	481.2	511.1	483.3	455.5	396.8	338.2	303.2
50°	270.6	293.8	348.6	403.4	429.4	455.5	431.0	406.4	358.1	309.9	279.5
52.5°	247.5	266.4	312.3	358.1	380.5	402.9	381.8	360.8	322.5	284.3	257.7
55°	224.7	240.8	280.6	320.3	335.5	350.8	334.5	318.2	287.3	256.4	234.1
57.5°	203.4	217.8	250.4	283.0	294.7	306.4	291.6	276.9	253.6	230.4	211.7
60°	182.6	194.3	221.5	248.6	255.8	263.0	251.0	239.1	222.8	206.5	189.7
62.5°	163.2	173.9	194.1	214.3	219.1	223.8	214.7	205.6	193.2	180.8	167.8
65°	143.2	151.3	167.8	184.3	187.3	190.4	182.3	174.3	164.9	155.6	146.0
67.5°	124.7	130.4	143.9	157.3	157.6	157.8	151.3	144.7	139.5	134.3	126.7
70°	106.7	112.1	121.0	130.0	130.2	130.4	125.2	120.0	116.1	112.1	106.5
72.5°	88.2	92.1	98.9	105.6	105.2	104.7	101.5	98.2	95.2	92.1	88.0
75°	71.5	74.8	79.3	83.9	82.6	81.3	79.5	77.8	75.2	72.6	70.0
77.5°	56.3	58.2	60.9	63.5	62.6	61.7	60.2	58.7	56.7	54.8	53.7
80°	41.3	42.2	43.9	45.6	45.2	44.8	43.0	41.3	40.9	40.4	38.9
82.5°	28.0	29.1	29.6	30.0	29.8	29.6	28.3	26.9	26.5	26.1	25.9
85°	16.7	17.0	17.2	17.4	16.7	16.1	15.6	15.2	15.2	15.2	15.0
87.5°	7.6	7.8	7.8	7.8	7.6	7.4	7.0	6.5	6.7	7.0	7.0
90°	13.6	11.4	9.3	7.4	5.7	4.1	2.4	0.7	2.4	4.1	5.7
92.5°	16.4	14.9	13.4	13.2	14.2	15.2	16.2	17.2	16.2	15.2	14.2
95°	19.5	17.7	15.8	18.3	25.1	31.9	38.7	45.5	38.7	31.9	25.1
97.5°	40.8	49.2	57.7	64.2	68.9	73.5	78.1	82.8	78.1	73.5	68.9
100°	76.3	102.2	128.0	139.3	136.0	132.7	129.4	126.0	129.4	132.7	136.0
102.5°	112.9	141.7	170.5	183.9	181.7	179.6	177.4	175.3	177.4	179.6	181.7
105°	193.2	208.1	223.0	229.6	227.7	225.9	224.1	222.3	224.1	225.9	227.7
107.5°	285.2	282.7	280.2	278.2	276.7	275.2	273.7	272.2	273.7	275.2	276.7
110°	332.7	330.9	329.1	327.5	326.2	324.9	323.5	322.2	323.5	324.9	326.2



TEST NUMBER: P831447

CATALOG NUMBER: S123DIP-S340D805U950-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	379.7	377.9	376.1	374.6	373.4	372.3	371.1	369.9	371.1	372.3	373.4
115°	425.1	423.6	422.1	420.9	419.9	418.9	417.9	416.9	417.9	418.9	419.9
117.5°	470.5	469.6	468.8	467.8	466.6	465.5	464.3	463.2	464.3	465.5	466.6
120°	513.6	513.1	512.6	511.6	510.1	508.7	507.2	505.7	507.2	508.7	510.1
122.5°	555.8	555.1	554.5	553.6	552.4	551.3	550.1	548.9	550.1	551.3	552.4
125°	595.3	594.7	594.0	593.0	591.7	590.4	589.0	587.7	589.0	590.4	591.7
127.5°	634.5	633.7	632.9	631.8	630.5	629.2	627.8	626.5	627.8	629.2	630.5
130°	669.9	669.3	668.6	667.6	666.3	665.0	663.6	662.3	663.6	665.0	666.3
132.5°	703.8	703.3	702.8	701.9	700.6	699.3	697.9	696.6	697.9	699.3	700.6
135°	737.8	737.1	736.5	735.6	734.6	733.7	732.7	731.7	732.7	733.7	734.6
137.5°	768.3	768.0	767.6	766.8	765.5	764.1	762.8	761.5	762.8	764.1	765.5
140°	797.0	796.5	796.1	795.3	794.3	793.3	792.3	791.3	792.3	793.3	794.3
142.5°	824.6	824.1	823.6	822.9	821.9	820.9	819.9	818.9	819.9	820.9	821.9
145°	850.3	850.0	849.7	848.9	847.8	846.6	845.4	844.3	845.4	846.6	847.8
147.5°	873.5	873.1	872.8	872.2	871.4	870.6	869.7	868.9	869.7	870.6	871.4
150°	894.3	894.0	893.7	893.3	892.8	892.3	891.8	891.3	891.8	892.3	892.8
152.5°	912.6	912.4	912.2	912.1	911.9	911.7	911.6	911.4	911.6	911.7	911.9
155°	929.0	928.8	928.6	928.7	929.1	929.4	929.7	930.1	929.7	929.4	929.1
157.5°	944.6	944.7	944.9	945.0	945.0	945.0	945.0	945.0	945.0	945.0	945.0
160°	957.2	957.4	957.6	957.7	957.9	958.1	958.2	958.4	958.2	958.1	957.9
162.5°	968.4	968.6	968.8	969.1	969.6	970.1	970.6	971.1	970.6	970.1	969.6
165°	978.1	978.3	978.4	978.8	979.3	979.8	980.3	980.8	980.3	979.8	979.3
167.5°	986.0	986.0	986.0	986.3	987.0	987.6	988.3	989.0	988.3	987.6	987.0
170°	992.7	992.7	992.7	993.0	993.7	994.4	995.0	995.7	995.0	994.4	993.7
172.5°	996.8	996.7	996.5	996.8	997.7	998.5	999.3	1000.2	999.3	998.5	997.7
175°	1000.6	1000.4	1000.2	1000.6	1001.4	1002.2	1003.1	1003.9	1003.1	1002.2	1001.4
177.5°	1002.1	1001.9	1001.7	1002.1	1002.9	1003.7	1004.6	1005.4	1004.6	1003.7	1002.9
180°	1003.9	1003.9	1003.9	1003.9	1003.9	1003.9	1003.9	1003.9	1003.9	1003.9	1003.9



TEST NUMBER: P831447

CATALOG NUMBER: S123DIP-S340D805U950-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	936.7	936.7	936.7	936.7	936.7	936.7	936.7	936.7	936.7	936.7	936.7
2.5°	898.8	890.4	881.9	875.4	868.9	857.8	846.7	844.1	841.5	837.8	834.1
5°	852.3	831.5	810.6	791.9	773.2	758.7	744.1	734.6	725.0	718.0	711.1
7.5°	798.0	766.7	735.4	713.3	691.1	670.0	648.9	642.2	635.5	626.3	617.2
10°	745.4	710.9	676.3	647.4	618.5	597.9	577.2	569.0	560.7	549.2	537.7
12.5°	698.5	660.7	622.8	593.7	564.6	544.6	524.6	512.7	500.7	494.2	487.7
15°	649.4	608.9	568.5	541.6	514.6	496.6	478.5	468.1	457.7	451.4	445.1
17.5°	605.9	565.9	525.9	500.1	474.2	457.7	441.2	432.0	422.9	418.1	413.3
20°	564.6	525.5	486.4	461.2	435.9	422.5	409.0	403.1	397.3	393.4	389.4
22.5°	526.8	488.3	449.9	428.3	406.8	396.0	385.1	381.0	376.8	373.6	370.3
25°	489.0	454.6	420.3	402.0	383.8	374.9	366.0	361.8	357.7	354.5	351.2
27.5°	458.1	425.3	392.5	376.8	361.2	354.2	347.3	344.0	340.8	337.7	334.7
30°	428.1	398.8	369.4	356.0	342.5	336.2	329.9	326.6	323.4	320.6	317.7
32.5°	400.3	375.1	349.9	337.5	325.1	319.9	314.7	310.8	306.9	304.7	302.5
35°	373.8	351.2	328.6	318.4	308.2	302.9	297.7	294.5	291.2	289.5	287.7
37.5°	351.2	331.0	310.8	301.0	291.2	286.2	281.2	278.4	275.6	274.9	274.3
40°	328.2	310.8	293.4	283.8	274.3	269.9	265.6	263.8	262.1	261.7	261.2
42.5°	309.0	292.1	275.1	266.4	257.7	254.1	250.4	249.5	248.6	249.3	249.9
45°	286.9	272.7	258.6	250.6	242.5	239.5	236.4	235.8	235.1	236.4	237.8
47.5°	268.2	255.1	242.1	234.5	226.9	224.7	222.5	222.3	222.1	223.8	225.6
50°	249.1	236.4	223.8	217.8	211.7	209.7	207.8	208.4	209.1	211.9	214.7
52.5°	231.2	219.5	207.8	202.1	196.5	195.2	193.9	195.4	196.9	199.9	203.0
55°	211.7	201.0	190.4	186.0	181.7	180.4	179.1	182.1	185.2	188.0	190.8
57.5°	193.0	183.6	174.3	170.4	166.5	166.3	166.0	168.9	171.7	174.7	177.8
60°	173.0	165.2	157.3	154.3	151.3	151.7	152.1	155.4	158.6	161.0	163.4
62.5°	154.7	148.2	141.7	138.9	136.0	137.1	138.2	141.5	144.7	147.6	150.4
65°	136.5	131.0	125.6	123.7	121.7	123.2	124.7	127.6	130.4	132.3	134.3
67.5°	119.1	114.5	110.0	108.4	106.9	108.4	110.0	112.8	115.6	117.6	119.5
70°	100.8	97.1	93.4	92.4	91.3	93.0	94.8	97.1	99.5	101.5	103.4
72.5°	83.9	81.1	78.2	78.0	77.8	79.3	80.8	83.2	85.6	86.9	88.2
75°	67.4	65.8	64.3	64.1	63.9	65.4	66.9	68.2	69.5	70.6	71.7
77.5°	52.6	51.3	50.0	50.2	50.4	51.5	52.6	53.9	55.2	55.9	56.5
80°	37.4	36.9	36.5	36.9	37.4	38.2	39.1	40.0	40.9	41.3	41.7
82.5°	25.6	25.2	24.8	25.4	26.1	26.7	27.4	28.0	28.7	28.9	29.1
85°	14.8	15.4	16.1	16.1	16.1	16.3	16.5	16.7	17.0	16.7	16.5
87.5°	7.0	7.2	7.4	7.4	7.4	7.6	7.8	7.8	7.8	7.6	7.4
90°	7.4	9.3	11.4	13.6	15.7	17.9	18.6	19.2	19.9	20.6	21.0
92.5°	13.2	13.4	14.9	16.4	17.9	19.4	20.6	21.7	22.9	24.0	24.7
95°	18.3	15.8	17.7	19.5	21.3	23.1	24.3	25.4	26.6	27.8	28.3
97.5°	64.2	57.7	49.2	40.8	32.3	23.9	25.2	26.5	27.8	29.2	29.9
100°	139.3	128.0	102.2	76.3	50.5	24.6	25.9	27.3	28.6	29.9	30.7
102.5°	183.9	170.5	141.7	112.9	84.0	55.2	49.7	44.3	38.8	33.3	30.7
105°	229.6	223.0	208.1	193.2	178.3	163.3	134.0	104.7	75.3	46.0	31.5
107.5°	278.2	280.2	282.7	285.2	287.6	290.1	264.6	239.1	213.6	188.0	164.4
110°	327.5	329.1	330.9	332.7	334.5	336.4	330.9	325.4	320.0	314.5	299.9



TEST NUMBER: P831447

CATALOG NUMBER: S123DIP-S340D805U950-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	374.6	376.1	377.9	379.7	381.5	383.4	384.8	386.3	387.8	389.3	389.9
115°	420.9	422.1	423.6	425.1	426.6	428.1	429.8	431.4	433.1	434.7	435.9
117.5°	467.8	468.8	469.6	470.5	471.3	472.1	473.4	474.8	476.1	477.4	478.2
120°	511.6	512.6	513.1	513.6	514.1	514.6	515.9	517.3	518.6	519.9	520.6
122.5°	553.6	554.5	555.1	555.8	556.5	557.1	558.0	558.8	559.6	560.5	560.9
125°	593.0	594.0	594.7	595.3	596.0	596.7	597.0	597.3	597.7	598.0	598.3
127.5°	631.8	632.9	633.7	634.5	635.4	636.2	636.7	637.2	637.7	638.2	638.3
130°	667.6	668.6	669.3	669.9	670.6	671.2	671.9	672.6	673.2	673.9	674.1
132.5°	701.9	702.8	703.3	703.8	704.3	704.8	705.5	706.1	706.8	707.5	707.5
135°	735.6	736.5	737.1	737.8	738.5	739.1	739.6	740.1	740.6	741.1	741.1
137.5°	766.8	767.6	768.0	768.3	768.6	769.0	769.8	770.6	771.4	772.3	772.5
140°	795.3	796.1	796.5	797.0	797.5	798.0	798.7	799.4	800.0	800.7	800.9
142.5°	822.9	823.6	824.1	824.6	825.1	825.6	826.1	826.6	827.1	827.6	827.6
145°	848.9	849.7	850.0	850.3	850.7	851.0	851.3	851.7	852.0	852.3	852.5
147.5°	872.2	872.8	873.1	873.5	873.8	874.1	874.4	874.8	875.1	875.4	875.2
150°	893.3	893.7	894.0	894.3	894.7	895.0	895.3	895.7	896.0	896.3	896.2
152.5°	912.1	912.2	912.4	912.6	912.7	912.9	913.6	914.2	914.9	915.6	915.5
155°	928.7	928.6	928.8	929.0	929.1	929.3	930.1	931.0	931.8	932.6	932.5
157.5°	945.0	944.9	944.7	944.6	944.4	944.2	945.2	946.2	947.2	948.2	948.0
160°	957.7	957.6	957.4	957.2	957.1	956.9	957.9	958.9	959.9	960.9	960.8
162.5°	969.1	968.8	968.6	968.4	968.3	968.1	969.3	970.4	971.6	972.7	972.8
165°	978.8	978.4	978.3	978.1	978.0	977.8	979.1	980.4	981.8	983.1	983.2
167.5°	986.3	986.0	986.0	986.0	986.0	986.0	987.3	988.6	990.0	991.3	991.3
170°	993.0	992.7	992.7	992.7	992.7	992.7	994.0	995.4	996.7	998.0	998.0
172.5°	996.8	996.5	996.7	996.8	997.0	997.2	998.5	999.8	1001.2	1002.5	1002.4
175°	1000.6	1000.2	1000.4	1000.6	1000.7	1000.9	1002.1	1003.2	1004.4	1005.5	1005.5
177.5°	1002.1	1001.7	1001.9	1002.1	1002.2	1002.4	1003.7	1005.0	1006.4	1007.7	1007.5
180°	1003.9	1003.9	1003.9	1003.9	1003.9	1003.9	1003.9	1003.9	1003.9	1003.9	1003.9



TEST NUMBER: P831447

CATALOG NUMBER: S123DIP-S340D805U950-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	936.7	936.7	936.7	936.7
2.5°	832.6	831.0	825.0	818.9
5°	705.9	700.6	698.9	697.2
7.5°	616.8	616.3	607.2	598.1
10°	538.3	539.0	530.7	522.4
12.5°	482.2	476.8	476.2	475.5
15°	440.1	435.1	434.2	433.3
17.5°	410.3	407.3	406.4	405.5
20°	387.7	386.0	384.4	382.9
22.5°	368.1	366.0	364.7	363.4
25°	349.2	347.3	346.8	346.4
27.5°	332.3	329.9	329.9	329.9
30°	316.2	314.7	314.0	313.4
32.5°	301.2	299.9	299.9	299.9
35°	287.1	286.4	285.6	284.7
37.5°	274.3	274.3	273.8	273.4
40°	261.9	262.5	262.5	262.5
42.5°	250.6	251.2	251.2	251.2
45°	238.8	239.9	240.4	240.8
47.5°	227.3	229.1	229.5	229.9
50°	216.0	217.3	217.5	217.8
52.5°	204.5	206.0	207.1	208.2
55°	192.3	193.9	194.5	195.2
57.5°	179.3	180.8	181.0	181.2
60°	164.9	166.5	166.9	167.3
62.5°	151.3	152.1	152.6	153.0
65°	135.6	136.9	137.8	138.7
67.5°	120.6	121.7	121.7	121.7
70°	103.9	104.3	105.0	105.6
72.5°	88.5	88.7	88.7	88.7
75°	72.2	72.6	72.8	73.0
77.5°	56.7	56.9	56.9	56.9
80°	41.5	41.3	41.3	41.3
82.5°	28.5	27.8	27.8	27.8
85°	16.3	16.1	16.3	16.5
87.5°	7.4	7.4	7.4	7.4
90°	21.4	21.7	22.0	22.4
92.5°	24.9	25.0	25.2	25.4
95°	28.3	28.3	28.3	28.3
97.5°	30.1	30.2	30.4	30.6
100°	30.8	31.0	31.2	31.3
102.5°	31.1	31.4	31.7	32.1
105°	31.8	32.2	32.5	32.8
107.5°	142.7	121.0	99.3	77.6
110°	276.2	252.5	228.8	205.1



TEST NUMBER: P831447

CATALOG NUMBER: S123DIP-S340D805U950-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
112.5°	389.6	389.2	388.9	388.6
115°	436.6	437.2	437.9	438.5
117.5°	478.3	478.5	478.7	478.8
120°	520.6	520.6	520.6	520.6
122.5°	561.1	561.3	561.4	561.6
125°	598.7	599.0	599.3	599.6
127.5°	637.9	637.6	637.3	636.9
130°	673.7	673.4	673.1	672.7
132.5°	707.0	706.6	706.1	705.6
135°	740.6	740.1	739.6	739.1
137.5°	772.2	771.9	771.5	771.2
140°	800.5	800.2	799.9	799.5
142.5°	827.1	826.6	826.1	825.6
145°	852.5	852.5	852.5	852.5
147.5°	874.4	873.5	872.7	871.9
150°	895.7	895.2	894.7	894.3
152.5°	914.6	913.8	913.0	912.2
155°	931.5	930.5	929.6	928.6
157.5°	946.7	945.4	944.1	942.7
160°	959.6	958.5	957.3	956.2
162.5°	971.8	970.8	969.8	968.8
165°	982.0	980.9	979.7	978.5
167.5°	990.0	988.6	987.3	986.0
170°	996.7	995.4	994.0	992.7
172.5°	1000.9	999.4	997.9	996.4
175°	1004.1	1002.8	1001.5	1000.2
177.5°	1005.9	1004.2	1002.6	1000.9
180°	1003.9	1003.9	1003.9	1003.9



TEST NUMBER: P831447

CATALOG NUMBER: S123DIP-S340D805U950-4F0-1E-UDD-G

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.76	10.46	10.85	11.55	13.05	11.99	12.70	13.09	13.79	15.29
	3H	11.39	12.02	12.50	13.12	14.64	13.41	14.04	14.51	15.14	16.65
	4H	11.96	12.56	13.08	13.66	15.18	13.85	14.45	14.97	15.55	17.07
	6H	12.33	12.88	13.45	13.98	15.51	14.12	14.67	15.24	15.77	17.31
	8H	12.42	12.94	13.55	14.06	15.59	14.18	14.70	15.31	15.82	17.34
	12H	12.46	12.96	13.59	14.07	15.62	14.19	14.69	15.32	15.80	17.35
4H	2H	10.31	10.91	11.44	12.01	13.53	12.14	12.74	13.26	13.84	15.36
	3H	12.13	12.63	13.26	13.76	15.29	13.75	14.24	14.87	15.37	16.90
	4H	12.82	13.28	13.95	14.40	15.95	14.32	14.78	15.46	15.90	17.45
	6H	13.29	13.68	14.43	14.82	16.36	14.72	15.11	15.86	16.25	17.80
	8H	13.42	13.79	14.56	14.92	16.48	14.83	15.19	15.97	16.32	17.89
	12H	13.48	13.81	14.64	14.96	16.52	14.87	15.20	16.02	16.34	17.90
8H	4H	13.08	13.44	14.21	14.57	16.13	14.42	14.78	15.56	15.91	17.47
	6H	13.66	13.96	14.82	15.13	16.69	14.91	15.22	16.07	16.39	17.95
	8H	13.87	14.13	15.03	15.28	16.86	15.09	15.36	16.26	16.51	18.09
	12H	13.98	14.22	15.15	15.36	16.98	15.19	15.42	16.36	16.57	18.18
12H	4H	13.07	13.40	14.22	14.54	16.11	14.39	14.72	15.54	15.86	17.42
	6H	13.71	13.97	14.87	15.13	16.70	14.93	15.19	16.09	16.34	17.92
	8H	13.94	14.17	15.10	15.32	16.93	15.12	15.35	16.29	16.50	18.11