

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332632

Luminaire Tested: **S124DIP-S1020D365U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332632
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIP-S1020D365U835-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5696.9 lumens
Efficiency: N/A
Efficacy: 131.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 43.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332632

CATALOG NUMBER: S124DIP-S1020D365U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332632

CATALOG NUMBER: S124DIP-S1020D365U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																		
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	114	114	114	114	109	109	109	109	99	99	99	90	90	90	82	82	82	82	82	82	82	82	82	82	82	82	82	82	82	78																
1	104	99	95	92	99	95	91	88	87	84	81	79	77	75	72	70	69	69	69	69	69	69	69	69	69	69	69	69	69	65																
2	95	87	80	75	90	83	77	72	76	71	67	69	66	63	63	61	58	63	61	58	63	61	58	63	61	58	63	61	58	55																
3	86	76	69	63	82	73	66	61	67	61	57	61	57	53	56	53	49	56	53	49	56	53	49	56	53	49	56	53	49	46																
4	79	68	59	53	75	65	57	51	60	53	48	55	50	45	50	46	43	50	46	43	50	46	43	50	46	43	50	46	43	40																
5	73	61	52	46	69	58	50	44	54	47	42	49	44	40	45	41	37	45	41	37	45	41	37	45	41	37	45	41	37	35																
6	67	55	46	40	64	52	45	39	48	42	37	45	39	35	41	36	33	41	36	33	41	36	33	41	36	33	41	36	33	30																
7	62	49	41	35	59	48	40	34	44	37	33	41	35	31	38	33	29	41	35	31	38	33	29	41	35	31	38	33	29	27																
8	58	45	37	31	55	43	36	31	40	34	29	37	32	28	35	30	26	37	32	28	35	30	26	37	32	28	35	30	26	24																
9	54	41	33	28	52	40	32	27	37	31	26	34	29	25	32	27	24	34	29	25	32	27	24	32	27	24	32	27	24	22																
10	51	38	30	25	48	37	30	25	34	28	24	32	26	23	30	25	22	32	26	23	30	25	22	30	25	22	30	25	22	20																

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13930	13930	13930
5°	13972	13804	13904
10°	13884	13691	13759
15°	13717	13497	13531
20°	13493	13256	13268
25°	13239	12981	12944
30°	12928	12656	12541
35°	12604	12318	12154
40°	12269	11934	11715
45°	11918	11555	11334
50°	11531	11218	10870
55°	11112	10781	10431
60°	10693	10291	9978
65°	10222	9824	9429
70°	9692	9203	8844
75°	8883	8453	8238
80°	7908	7583	7392
85°	6919	6660	6530



TEST NUMBER: P332632

CATALOG NUMBER: S124DIP-S1020D365U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	162.5	2.9
10°-20°	457.8	8.0
20°-30°	673.9	11.8
30°-40°	783.4	13.8
40°-50°	783.4	13.8
50°-60°	685.3	12.0
60°-70°	508.9	8.9
70°-80°	289.1	5.1
80°-90°	84.8	1.5
90°-100°	30.1	0.5
100°-110°	89.3	1.6
110°-120°	151.5	2.7
120°-130°	199.8	3.5
130°-140°	224.4	3.9
140°-150°	220.5	3.9
150°-160°	185.4	3.3
160°-170°	123.4	2.2
170°-180°	43.2	0.8
0°-30°	1294.2	22.7
0°-40°	2077.6	36.5
0°-60°	3546.4	62.3
0°-90°	4429.3	77.7
90°-120°	270.9	4.8
90°-150°	915.6	16.1
90°-180°	1268.0	22.3
0°-180°	5696.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1726	1726	1726	1726	1726	
5°	1724	1718	1703	1718	1716	163
15°	1641	1635	1615	1622	1619	462
25°	1486	1476	1457	1458	1453	684
35°	1279	1269	1250	1240	1233	799
45°	1044	1034	1012	997	993	804
55°	790	784	766	750	741	707
65°	535	528	514	501	494	530
75°	285	278	271	266	264	303
85°	75	75	72	72	70	82
90°	1	5	8	10	11	5
95°	21	24	27	28	28	24
105°	82	83	84	85	86	87
115°	154	154	153	153	153	152
125°	224	224	224	223	223	200
135°	289	291	292	291	290	224
145°	352	353	353	353	352	220
155°	403	403	402	404	402	185
165°	438	438	437	439	438	124
175°	456	454	454	456	454	43
180°	457	457	457	457	457	



TEST NUMBER: P332632

CATALOG NUMBER: S124DIP-S1020D365U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5
2.5°	1729.9	1729.2	1728.4	1727.7	1727.0	1725.2	1722.5	1719.8	1717.1	1714.4	1716.9
5°	1724.1	1722.9	1721.7	1720.4	1719.2	1716.9	1713.5	1710.1	1706.8	1703.4	1706.8
7.5°	1708.1	1706.8	1705.6	1704.4	1703.2	1700.7	1696.9	1693.2	1689.4	1685.7	1688.4
10°	1693.7	1692.5	1691.2	1690.0	1688.8	1686.2	1682.2	1678.2	1674.2	1670.2	1672.6
12.5°	1674.9	1673.7	1672.4	1671.2	1670.0	1667.2	1663.0	1658.8	1654.5	1650.3	1653.0
15°	1641.2	1639.9	1638.7	1637.5	1636.2	1633.3	1628.7	1624.1	1619.5	1614.9	1616.7
17.5°	1600.5	1599.0	1597.4	1595.9	1594.4	1591.4	1587.0	1582.7	1578.3	1574.0	1575.1
20°	1570.6	1569.1	1567.6	1566.0	1564.5	1561.4	1556.8	1552.2	1547.6	1543.0	1543.9
22.5°	1538.6	1536.5	1534.5	1532.5	1530.5	1527.1	1522.5	1517.9	1513.3	1508.7	1510.4
25°	1486.3	1484.2	1482.0	1479.8	1477.7	1474.5	1470.2	1465.9	1461.6	1457.3	1457.6
27.5°	1426.6	1424.4	1422.1	1419.9	1417.7	1414.6	1410.6	1406.6	1402.6	1398.6	1397.9
30°	1386.8	1384.3	1381.8	1379.4	1376.9	1373.7	1369.7	1365.7	1361.7	1357.7	1356.5
32.5°	1344.7	1342.5	1340.3	1338.1	1335.9	1332.6	1328.4	1324.2	1319.9	1315.7	1314.2
35°	1278.9	1276.8	1274.6	1272.5	1270.3	1267.1	1262.8	1258.5	1254.2	1249.9	1247.7
37.5°	1209.5	1207.5	1205.6	1203.6	1201.6	1198.4	1193.7	1189.1	1184.5	1179.9	1177.6
40°	1164.2	1161.7	1159.2	1156.8	1154.3	1150.8	1146.2	1141.6	1137.0	1132.4	1129.3
42.5°	1115.5	1114.0	1112.5	1111.1	1109.6	1106.3	1101.2	1096.1	1091.0	1085.9	1082.3
45°	1043.9	1041.7	1039.6	1037.4	1035.3	1031.7	1026.8	1021.9	1017.0	1012.1	1008.7
47.5°	968.9	967.5	966.0	964.5	963.0	960.0	955.5	950.9	946.4	941.8	938.0
50°	918.1	916.8	915.6	914.4	913.1	910.4	906.1	901.8	897.5	893.2	888.9
52.5°	868.3	866.8	865.3	863.9	862.4	859.4	854.8	850.3	845.7	841.2	837.4
55°	789.5	788.5	787.6	786.7	785.8	783.2	778.9	774.6	770.3	766.0	762.3
57.5°	714.3	713.2	712.2	711.1	710.1	707.4	703.2	699.0	694.7	690.5	687.0
60°	662.3	660.7	659.2	657.7	656.1	653.4	649.4	645.4	641.4	637.4	634.6
62.5°	611.4	610.1	608.8	607.5	606.2	603.5	599.2	595.0	590.7	586.5	584.0
65°	535.1	533.5	532.0	530.5	528.9	526.6	523.5	520.5	517.4	514.3	511.3
67.5°	458.2	456.8	455.4	454.0	452.5	450.4	447.4	444.5	441.5	438.6	435.6
70°	410.6	408.5	406.3	404.2	402.0	399.7	397.3	394.8	392.4	389.9	387.4
72.5°	359.8	357.6	355.5	353.3	351.2	349.1	347.1	345.2	343.2	341.2	339.3
75°	284.8	283.3	281.7	280.2	278.7	277.1	275.6	274.1	272.5	271.0	269.8
77.5°	213.2	212.5	211.8	211.2	210.5	209.5	208.1	206.8	205.4	204.1	203.7
80°	170.1	169.1	168.2	167.3	166.4	165.6	165.0	164.4	163.8	163.1	162.5
82.5°	128.0	127.6	127.2	126.7	126.3	126.0	125.9	125.8	125.7	125.5	125.2
85°	74.7	74.7	74.7	74.7	74.7	74.4	73.7	73.1	72.5	71.9	71.9
87.5°	29.0	28.9	28.8	28.8	28.7	28.6	28.5	28.3	28.2	28.1	28.2
90°	1.1	1.9	2.8	3.7	4.5	5.3	5.9	6.5	7.1	7.8	8.2
92.5°	7.6	8.6	9.5	10.5	11.5	12.2	12.7	13.1	13.6	14.0	14.3
95°	21.2	21.9	22.6	23.3	24.0	24.7	25.2	25.8	26.3	26.9	27.1
97.5°	37.0	37.6	38.2	38.7	39.3	39.9	40.5	41.2	41.8	42.5	42.8
100°	49.5	49.8	50.1	50.4	50.7	51.2	51.9	52.7	53.4	54.1	54.2
102.5°	62.5	62.6	62.7	62.9	63.0	63.4	64.0	64.7	65.3	65.9	66.2
105°	82.3	82.4	82.5	82.6	82.6	82.8	83.2	83.5	83.8	84.1	84.3
107.5°	103.2	103.3	103.4	103.5	103.6	103.6	103.7	103.7	103.8	103.8	104.0
110°	117.3	117.5	117.6	117.8	117.9	118.0	117.9	117.8	117.7	117.7	117.5



TEST NUMBER: P332632

CATALOG NUMBER: S124DIP-S1020D365U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	132.0	132.0	132.1	132.1	132.1	132.1	131.9	131.8	131.7	131.5	131.5
115°	154.1	154.1	154.1	154.1	154.1	154.0	153.8	153.7	153.5	153.4	153.3
117.5°	174.8	174.9	175.0	175.0	175.1	175.1	175.0	174.9	174.7	174.6	174.4
120°	188.7	189.0	189.3	189.6	190.0	190.0	189.8	189.5	189.3	189.1	188.7
122.5°	203.1	203.2	203.4	203.5	203.6	203.6	203.5	203.4	203.3	203.2	202.9
125°	224.4	224.4	224.4	224.4	224.4	224.3	224.3	224.2	224.1	224.0	223.9
127.5°	243.7	243.9	244.2	244.4	244.6	244.7	244.6	244.4	244.3	244.2	244.0
130°	257.3	257.5	257.7	258.0	258.2	258.3	258.3	258.3	258.3	258.3	258.2
132.5°	271.1	271.3	271.4	271.6	271.8	271.8	271.8	271.7	271.7	271.6	271.4
135°	289.4	289.9	290.3	290.8	291.3	291.5	291.5	291.5	291.5	291.5	291.4
137.5°	309.3	309.6	309.8	310.0	310.2	310.4	310.5	310.6	310.8	310.9	310.7
140°	322.6	322.8	322.9	323.1	323.3	323.3	323.3	323.3	323.3	323.3	323.3
142.5°	334.8	334.9	335.1	335.2	335.4	335.5	335.4	335.3	335.3	335.2	335.2
145°	351.6	351.9	352.2	352.5	352.9	353.1	353.1	353.2	353.3	353.4	353.3
147.5°	368.3	368.7	369.0	369.4	369.8	369.9	369.9	369.8	369.8	369.7	369.6
150°	378.5	378.8	379.1	379.4	379.7	379.9	379.9	379.9	379.9	379.9	379.9
152.5°	388.1	388.3	388.4	388.6	388.8	388.9	389.0	389.1	389.1	389.2	389.4
155°	402.8	402.8	402.8	402.8	402.8	402.8	402.7	402.6	402.6	402.5	402.8
157.5°	415.3	415.1	415.0	414.9	414.7	414.6	414.6	414.6	414.6	414.6	414.8
160°	422.6	422.5	422.5	422.4	422.3	422.2	422.2	422.1	422.0	421.9	422.2
162.5°	429.4	429.2	429.0	428.8	428.6	428.5	428.4	428.3	428.2	428.1	428.6
165°	438.5	438.3	438.1	437.8	437.6	437.4	437.2	437.1	436.9	436.8	437.2
167.5°	445.5	445.2	444.9	444.5	444.2	444.0	444.1	444.1	444.1	444.1	444.6
170°	449.5	449.1	448.7	448.3	447.9	447.8	447.8	447.9	448.0	448.1	448.5
172.5°	452.3	452.0	451.6	451.3	451.0	450.8	450.8	450.9	450.9	450.9	451.4
175°	456.2	455.8	455.4	455.0	454.6	454.4	454.3	454.2	454.2	454.1	454.6
177.5°	457.5	457.2	456.8	456.5	456.2	456.1	456.1	456.1	456.1	456.1	456.5
180°	456.9	456.9	456.9	456.9	456.9	456.9	456.9	456.9	456.9	456.9	456.9



TEST NUMBER: P332632

CATALOG NUMBER: S124DIP-S1020D365U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5
2.5°	1719.3	1721.8	1724.3	1725.4	1725.1	1724.9	1724.6	1724.4
5°	1710.1	1713.5	1716.9	1718.3	1717.7	1717.0	1716.4	1715.8
7.5°	1691.1	1693.8	1696.5	1697.7	1697.3	1696.9	1696.5	1696.2
10°	1675.1	1677.6	1680.0	1680.9	1680.3	1679.7	1679.1	1678.5
12.5°	1655.7	1658.4	1661.1	1662.0	1661.2	1660.3	1659.4	1658.6
15°	1618.6	1620.4	1622.3	1622.7	1621.8	1620.9	1620.0	1619.0
17.5°	1576.3	1577.5	1578.6	1578.9	1578.3	1577.7	1577.1	1576.4
20°	1544.8	1545.8	1546.7	1546.8	1546.2	1545.6	1545.0	1544.4
22.5°	1512.0	1513.7	1515.3	1515.6	1514.5	1513.4	1512.3	1511.2
25°	1457.9	1458.2	1458.5	1458.0	1456.8	1455.6	1454.3	1453.1
27.5°	1397.2	1396.4	1395.7	1394.6	1393.0	1391.5	1389.9	1388.4
30°	1355.3	1354.0	1352.8	1351.4	1349.9	1348.3	1346.8	1345.3
32.5°	1312.7	1311.3	1309.8	1308.3	1306.7	1305.2	1303.7	1302.1
35°	1245.6	1243.4	1241.3	1239.4	1237.9	1236.4	1234.8	1233.3
37.5°	1175.2	1172.9	1170.6	1168.4	1166.4	1164.3	1162.3	1160.3
40°	1126.2	1123.1	1120.1	1117.8	1116.2	1114.7	1113.2	1111.6
42.5°	1078.8	1075.2	1071.6	1069.3	1068.3	1067.2	1066.2	1065.2
45°	1005.3	1001.9	998.5	996.4	995.5	994.6	993.6	992.7
47.5°	934.2	930.4	926.6	923.5	921.2	918.8	916.5	914.2
50°	884.6	880.3	876.0	872.9	871.0	869.2	867.4	865.5
52.5°	833.6	829.7	825.9	822.9	820.5	818.2	815.9	813.5
55°	758.6	754.9	751.2	748.5	746.6	744.8	742.9	741.1
57.5°	683.5	680.0	676.5	673.8	672.0	670.3	668.5	666.7
60°	631.9	629.1	626.3	624.2	622.6	621.1	619.6	618.0
62.5°	581.5	578.9	576.4	574.4	572.9	571.3	569.8	568.3
65°	508.2	505.1	502.0	499.7	498.2	496.7	495.1	493.6
67.5°	432.7	429.7	426.8	425.1	424.6	424.2	423.8	423.4
70°	385.0	382.5	380.1	378.4	377.5	376.5	375.6	374.7
72.5°	337.3	335.3	333.4	331.9	331.0	330.1	329.2	328.2
75°	268.5	267.3	266.1	265.3	265.0	264.7	264.4	264.1
77.5°	203.3	203.0	202.6	202.0	201.2	200.4	199.6	198.8
80°	161.9	161.3	160.7	160.2	159.9	159.6	159.3	159.0
82.5°	124.8	124.4	124.1	123.7	123.4	123.1	122.8	122.5
85°	71.9	71.9	71.9	71.7	71.4	71.1	70.8	70.5
87.5°	28.3	28.4	28.5	28.5	28.6	28.6	28.6	28.7
90°	8.7	9.2	9.7	10.0	10.1	10.3	10.4	10.6
92.5°	14.6	14.8	15.1	15.3	15.4	15.5	15.6	15.7
95°	27.3	27.6	27.8	27.9	27.9	27.9	27.9	27.9
97.5°	43.0	43.3	43.6	43.7	43.7	43.7	43.7	43.7
100°	54.4	54.5	54.7	54.8	54.8	54.8	54.8	54.8
102.5°	66.4	66.6	66.8	67.0	67.0	67.1	67.1	67.2
105°	84.6	84.8	85.0	85.3	85.5	85.8	86.0	86.2
107.5°	104.3	104.5	104.7	104.8	104.8	104.8	104.8	104.7
110°	117.4	117.2	117.0	117.1	117.3	117.6	117.8	118.0



TEST NUMBER: P332632

CATALOG NUMBER: S124DIP-S1020D365U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	131.5	131.4	131.4	131.4	131.5	131.5	131.5	131.6
115°	153.2	153.1	153.0	153.0	152.9	152.8	152.7	152.7
117.5°	174.1	173.8	173.6	173.4	173.2	173.0	172.9	172.7
120°	188.3	187.9	187.5	187.4	187.5	187.7	187.8	188.0
122.5°	202.7	202.4	202.1	201.8	201.6	201.3	201.0	200.7
125°	223.7	223.6	223.4	223.2	223.1	222.9	222.8	222.6
127.5°	243.9	243.7	243.5	243.4	243.3	243.2	243.0	242.9
130°	258.0	257.8	257.7	257.4	257.1	256.8	256.5	256.2
132.5°	271.3	271.1	271.0	270.8	270.7	270.6	270.5	270.3
135°	291.2	291.1	290.9	290.7	290.5	290.2	290.0	289.8
137.5°	310.5	310.3	310.1	310.0	310.0	310.1	310.1	310.2
140°	323.2	323.1	323.0	322.9	322.9	322.8	322.7	322.6
142.5°	335.2	335.2	335.1	335.1	335.1	335.1	335.1	335.1
145°	353.2	353.1	353.1	352.9	352.7	352.4	352.2	352.0
147.5°	369.6	369.5	369.4	369.4	369.3	369.2	369.1	369.1
150°	379.9	379.9	379.9	379.8	379.8	379.7	379.6	379.5
152.5°	389.6	389.8	390.0	389.9	389.7	389.5	389.3	389.1
155°	403.1	403.4	403.7	403.7	403.4	403.1	402.8	402.5
157.5°	415.0	415.3	415.5	415.5	415.2	415.0	414.7	414.4
160°	422.4	422.6	422.9	422.8	422.4	422.0	421.6	421.2
162.5°	429.0	429.4	429.8	429.8	429.5	429.1	428.7	428.3
165°	437.7	438.2	438.6	438.7	438.4	438.1	437.8	437.5
167.5°	445.1	445.5	446.0	446.0	445.5	445.0	444.5	444.0
170°	449.0	449.5	450.0	449.9	449.4	448.8	448.3	447.7
172.5°	452.0	452.5	453.0	453.0	452.5	451.9	451.4	450.8
175°	455.2	455.7	456.3	456.3	455.7	455.2	454.6	454.1
177.5°	456.9	457.4	457.8	457.8	457.3	456.8	456.3	455.8
180°	456.9	456.9	456.9	456.9	456.9	456.9	456.9	456.9

(END OF REPORT)