

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831791

Luminaire Tested: S123RDIP-S1000D1025U950-4F0-1E-UDD-G4

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P831791
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-2, G3-1807-864-17)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1000D1025U950-4F0-1E-UDD-G4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, GRAZE OPTIC
UPLIGHT 1025 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7645.6 lumens
Efficiency: N/A
Efficacy: 125.3 lumens/watt
Spacing Criteria (0/90/45): 0.55 / 1.17 / 0.8
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 61
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P831791

CATALOG NUMBER: S123RDIP-S1000D1025U950-4F0-1E-UDD-G4

Luminous Intensity Polar Plot





TEST NUMBER: P831791

CATALOG NUMBER: S123RDIP-S1000D1025U950-4F0-1E-UDD-G4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	60	60	60	54	54	54	54	
1	99	95	92	89	92	89	86	83	76	74	72	65	63	62	54	53	52	47	47	47	47	
2	91	84	79	74	85	79	74	69	68	64	61	58	55	53	49	47	45	41	41	41	41	
3	84	75	68	63	78	70	64	59	61	56	52	52	49	46	44	42	40	36	36	36	36	
4	77	67	60	54	72	63	56	51	55	50	46	47	43	40	40	37	35	32	32	32	32	
5	71	60	53	47	66	57	50	45	50	44	40	43	39	36	37	34	31	28	28	28	28	
6	66	55	47	42	61	51	45	40	45	40	36	39	35	32	34	31	28	25	25	25	25	
7	62	50	42	37	57	47	40	35	41	36	32	36	32	29	31	28	26	23	23	23	23	
8	57	46	38	33	53	43	36	32	38	33	29	33	29	26	29	26	23	21	21	21	21	
9	54	42	35	30	50	40	33	29	35	30	26	31	27	24	27	24	21	19	19	19	19	
10	50	39	32	27	47	37	31	26	33	28	24	29	25	22	25	22	20	18	18	18	18	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	33322	33322	33322	33322	33322
5°	39566	38305	33532	27107	25166
10°	35848	38907	33365	21718	18631
15°	24682	33360	33013	17751	14739
20°	17171	25684	32349	14968	12954
25°	13085	19574	31385	13303	11940
30°	11390	15649	30179	12352	11059
35°	10457	13201	28470	11550	10257
40°	9542	11789	26235	10763	9524
45°	8617	10782	23823	10018	8791
50°	7822	9947	20979	9289	7886
55°	7075	9135	18246	8574	6765
60°	6340	8308	15849	7787	6394
65°	5850	7371	13642	6999	6046
70°	4752	6370	11903	6332	4913
75°	4171	5065	10081	5253	4329
80°	3775	4289	8263	4407	4091
85°	3446	3767	6274	4001	3767

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 25137 cd/sqm



TEST NUMBER: P831791

CATALOG NUMBER: S123RDIP-S1000D1025U950-4F0-1E-UDD-G4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	282.2	3.7
10°-20°	652.9	8.5
20°-30°	749.2	9.8
30°-40°	738.4	9.7
40°-50°	651.2	8.5
50°-60°	501.0	6.6
60°-70°	329.4	4.3
70°-80°	160.0	2.1
80°-90°	42.9	0.6
90°-100°	255.3	3.3
100°-110°	747.4	9.8
110°-120°	729.8	9.5
120°-130°	581.2	7.6
130°-140°	458.6	6.0
140°-150°	342.1	4.5
150°-160°	238.5	3.1
160°-170°	140.1	1.8
170°-180°	45.6	0.6
0°-30°	1684.3	22.0
0°-40°	2422.7	31.7
0°-60°	3574.9	46.8
0°-90°	4107.1	53.7
90°-120°	1732.4	22.7
90°-150°	3114.3	40.7
90°-180°	3539.0	46.3
0°-180°	7645.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	3096	3096	3096	3096	3096	
5°	3662	3545	3103	2509	2329	335
15°	2215	2994	2962	1593	1323	625
25°	1102	1648	2643	1120	1005	520
35°	796	1005	2167	879	781	496
45°	566	708	1565	658	578	439
55°	377	487	972	457	360	338
65°	230	289	536	275	237	225
75°	100	122	242	126	104	108
85°	28	30	51	32	30	30
90°	28	24	2	24	28	16
95°	110	565	32	565	110	180
105°	1211	766	110	766	1211	1208
115°	1473	586	195	586	1473	1437
125°	1162	547	271	547	1162	1051
135°	942	539	318	539	942	730
145°	736	532	363	532	736	467
155°	610	515	412	515	610	284
165°	532	493	450	493	532	152
175°	479	473	470	473	479	46
180°	470	470	470	470	470	



TEST NUMBER: P831791

CATALOG NUMBER: S123RDIP-S1000D1025U950-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	3095.7	3095.7	3095.7	3095.7	3095.7	3095.7	3095.7	3095.7	3095.7	3095.7	3095.7
2.5°	3430.8	3420.0	3409.3	3406.1	3402.9	3392.8	3382.6	3359.8	3336.9	3313.4	3289.9
5°	3661.8	3663.1	3664.4	3661.2	3658.0	3644.7	3631.4	3603.5	3575.5	3545.1	3514.6
7.5°	3590.8	3611.1	3631.4	3635.2	3639.0	3649.2	3659.3	3653.0	3646.6	3635.2	3623.8
10°	3279.8	3278.5	3277.3	3300.1	3322.9	3390.9	3458.8	3493.7	3528.6	3559.7	3590.8
12.5°	2772.1	2774.0	2775.9	2850.8	2925.7	2989.8	3053.9	3142.7	3231.6	3327.4	3423.2
15°	2214.9	2246.0	2277.1	2343.7	2410.3	2506.8	2603.3	2722.6	2841.9	2993.6	3145.3
17.5°	1818.9	1832.2	1845.5	1909.6	1973.7	2065.1	2156.5	2291.7	2426.8	2622.3	2817.8
20°	1499.0	1511.1	1523.1	1569.5	1615.8	1703.4	1790.9	1919.8	2048.6	2242.2	2435.7
22.5°	1251.5	1275.0	1298.5	1329.6	1360.7	1424.1	1487.6	1619.0	1750.3	1926.8	2103.2
25°	1101.7	1112.5	1123.3	1150.0	1176.6	1237.5	1298.5	1385.4	1472.4	1648.1	1823.9
27.5°	1000.2	1003.4	1006.5	1026.2	1045.9	1085.2	1124.6	1205.2	1285.8	1430.5	1575.2
30°	916.4	922.1	927.8	943.1	958.3	986.9	1015.4	1072.5	1129.7	1259.1	1388.6
32.5°	851.7	854.9	858.0	870.7	883.4	904.4	925.3	970.4	1015.4	1114.4	1213.4
35°	795.8	796.5	797.1	806.6	816.1	836.4	856.8	894.2	931.6	1004.6	1077.6
37.5°	732.4	736.8	741.3	748.2	755.2	773.0	790.8	821.2	851.7	912.0	972.3
40°	679.1	682.9	686.7	694.9	703.2	717.1	731.1	759.0	786.9	839.0	891.0
42.5°	625.8	628.3	630.8	639.1	647.3	664.5	681.6	703.8	726.0	769.2	812.3
45°	566.1	572.4	578.8	587.7	596.6	611.2	625.8	648.6	671.4	708.3	745.1
47.5°	516.6	519.8	522.9	530.6	538.2	555.9	573.7	594.0	614.3	648.6	682.9
50°	467.1	468.4	469.6	476.6	483.6	499.5	515.3	538.8	562.3	594.0	625.8
52.5°	420.1	423.3	426.5	433.5	440.4	451.2	462.0	486.1	510.2	541.3	572.4
55°	377.0	378.9	380.8	385.9	390.9	403.6	416.3	437.3	458.2	486.8	515.3
57.5°	336.4	338.9	341.4	345.2	349.0	360.5	371.9	390.3	408.7	437.3	465.8
60°	294.5	297.6	300.8	305.3	309.7	318.6	327.5	344.0	360.5	385.9	411.2
62.5°	264.0	264.6	265.3	269.1	272.9	279.2	285.6	298.9	312.2	337.6	363.0
65°	229.7	231.6	233.5	235.4	237.4	242.4	247.5	258.9	270.4	289.4	308.4
67.5°	194.2	196.1	198.0	201.2	204.4	208.8	213.2	220.9	228.5	246.2	264.0
70°	151.0	151.0	151.0	156.1	161.2	168.8	176.4	182.1	187.9	202.4	217.0
72.5°	123.1	123.8	124.4	125.0	125.7	130.1	134.5	144.1	153.6	162.5	171.4
75°	100.3	100.9	101.5	102.2	102.8	104.1	105.3	108.5	111.7	121.8	132.0
77.5°	80.0	80.6	81.2	81.9	82.5	83.8	85.0	86.3	87.6	91.4	95.2
80°	60.9	61.6	62.2	62.8	63.5	64.1	64.7	66.0	67.3	69.2	71.1
82.5°	44.4	44.4	44.4	44.4	44.4	45.7	47.0	47.0	47.0	48.2	49.5
85°	27.9	27.9	27.9	28.6	29.2	29.2	29.2	29.8	30.5	30.5	30.5
87.5°	12.7	12.1	11.4	12.1	12.7	12.7	12.7	13.3	14.0	14.0	14.0
90°	27.6	28.6	27.6	26.7	27.6	25.7	24.8	23.8	22.9	23.8	20.9
92.5°	50.5	52.4	51.4	55.2	57.1	63.8	73.3	94.3	132.4	177.1	196.2
95°	110.5	114.3	120.9	129.5	147.6	181.9	232.4	342.8	458.0	564.7	502.8
97.5°	226.6	237.1	260.0	296.2	360.0	468.5	594.2	787.5	898.0	868.5	648.5
100°	597.1	596.1	633.3	702.8	798.9	934.2	1045.6	1122.7	1089.4	901.8	609.4
102.5°	945.6	973.2	1002.7	1054.2	1123.7	1197.0	1250.3	1234.1	1098.9	839.9	552.3
105°	1211.3	1216.0	1246.5	1282.7	1326.5	1351.3	1333.2	1237.9	1038.9	765.6	507.6
107.5°	1384.6	1395.1	1407.4	1424.6	1430.3	1404.6	1330.3	1180.8	953.2	699.9	475.2
110°	1483.6	1485.5	1487.4	1479.8	1453.2	1386.5	1266.5	1091.3	873.2	645.6	458.0



TEST NUMBER: P831791

CATALOG NUMBER: S123RDIP-S1000D1025U950-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1503.6	1502.7	1493.1	1465.5	1411.3	1320.8	1182.7	1002.7	803.7	609.4	448.5
115°	1473.2	1468.4	1449.3	1407.4	1336.0	1232.2	1092.2	926.6	750.4	585.6	447.6
117.5°	1406.5	1399.8	1371.3	1324.6	1250.3	1142.7	1014.2	867.5	715.1	569.5	448.5
120°	1318.9	1313.2	1290.3	1237.0	1161.8	1065.6	951.3	822.8	688.5	559.0	452.3
122.5°	1237.0	1229.4	1203.7	1157.0	1092.2	1004.6	900.8	787.5	666.6	552.3	459.0
125°	1161.8	1155.1	1131.3	1089.4	1028.4	952.3	860.8	757.0	648.5	546.6	465.7
127.5°	1097.0	1091.3	1069.4	1033.2	978.0	907.5	823.7	729.4	631.4	543.7	473.3
130°	1043.7	1036.1	1016.1	981.8	931.3	866.6	789.4	703.7	618.0	540.9	480.9
132.5°	991.3	986.5	969.4	935.1	888.5	827.5	757.0	679.9	605.6	539.9	486.6
135°	941.8	935.1	918.0	889.4	842.8	788.5	726.6	659.0	595.2	539.0	492.3
137.5°	889.4	883.7	869.4	839.9	799.9	751.3	696.1	639.0	585.6	537.1	496.1
140°	834.2	835.1	819.9	793.2	757.0	716.1	670.4	621.8	577.1	536.1	499.9
142.5°	782.8	783.7	770.4	747.5	718.0	683.7	645.6	605.6	569.5	534.2	502.8
145°	736.1	734.2	726.6	706.6	682.8	655.2	624.7	593.3	562.8	532.3	503.7
147.5°	696.1	695.2	687.5	673.2	654.2	634.2	608.5	582.8	556.1	529.5	503.7
150°	661.8	661.8	656.1	645.6	631.4	613.3	593.3	571.4	549.5	525.6	503.7
152.5°	633.3	633.3	630.4	620.9	610.4	596.1	579.0	560.9	541.8	520.9	500.9
155°	610.4	609.4	607.5	599.9	591.4	579.9	565.6	550.4	534.2	515.2	499.0
157.5°	588.5	588.5	586.6	580.9	573.3	563.7	552.3	539.0	525.6	510.4	496.1
160°	567.5	568.5	568.5	562.8	556.1	549.5	539.9	529.5	517.1	504.7	494.2
162.5°	548.5	549.5	549.5	544.7	540.9	535.2	526.6	518.0	508.5	499.0	490.4
165°	532.3	532.3	533.3	529.5	525.6	520.9	514.2	508.5	500.9	493.3	486.6
167.5°	516.1	516.1	517.1	514.2	512.3	508.5	504.7	499.9	493.3	487.6	482.8
170°	501.8	501.8	502.8	500.9	499.9	498.0	494.2	491.4	486.6	481.8	479.0
172.5°	488.5	489.5	491.4	489.5	489.5	488.5	485.7	483.7	479.9	477.1	476.1
175°	479.0	479.9	480.9	479.9	479.9	479.9	478.0	477.1	475.2	473.3	473.3
177.5°	472.3	472.3	474.2	473.3	474.2	474.2	473.3	472.3	471.4	470.4	471.4
180°	470.4	470.4	470.4	470.4	470.4	470.4	470.4	470.4	470.4	470.4	470.4

TEST NUMBER: P831791

CATALOG NUMBER: S123RDIP-S1000D1025U950-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	3095.7	3095.7	3095.7	3095.7	3095.7	3095.7	3095.7	3095.7	3095.7	3095.7	3095.7
2.5°	3286.8	3283.6	3253.1	3222.7	3192.8	3163.0	3140.8	3118.6	3081.2	3043.7	3020.2
5°	3490.5	3466.4	3418.1	3369.9	3297.6	3225.2	3164.3	3103.4	3025.9	2948.5	2883.8
7.5°	3604.1	3584.4	3526.0	3467.6	3371.8	3276.0	3180.8	3085.6	2971.4	2857.1	2759.4
10°	3607.3	3623.8	3575.5	3527.3	3419.4	3311.5	3182.1	3052.6	2899.0	2745.4	2619.1
12.5°	3494.3	3565.4	3555.2	3545.1	3435.3	3325.5	3168.1	3010.7	2822.2	2633.7	2475.7
15°	3283.0	3420.7	3461.3	3501.9	3411.2	3320.4	3141.4	2962.5	2741.0	2519.5	2338.0
17.5°	3010.7	3203.6	3310.9	3418.1	3352.1	3286.1	3090.0	2893.9	2644.5	2395.1	2197.7
20°	2688.3	2940.9	3109.1	3277.3	3253.1	3229.0	3026.6	2824.1	2555.0	2286.0	2072.1
22.5°	2369.7	2636.3	2868.6	3100.8	3125.6	3150.3	2946.0	2741.6	2447.2	2152.7	1935.0
25°	2094.9	2365.9	2642.6	2919.3	2975.2	3031.0	2836.8	2642.6	2337.4	2032.1	1815.7
27.5°	1832.8	2090.5	2395.1	2699.7	2801.3	2902.8	2725.1	2547.4	2229.5	1911.5	1695.7
30°	1619.0	1849.3	2160.3	2471.3	2612.8	2754.3	2591.2	2428.1	2112.7	1797.3	1586.0
32.5°	1419.7	1625.9	1938.2	2250.4	2414.8	2579.2	2438.3	2297.4	1994.0	1690.7	1481.9
35°	1262.3	1447.0	1738.3	2029.6	2213.6	2397.7	2282.1	2166.6	1870.3	1573.9	1376.5
37.5°	1127.1	1282.0	1555.5	1829.0	2024.5	2220.0	2123.5	2027.0	1748.4	1469.8	1283.2
40°	1015.4	1139.8	1394.3	1648.8	1840.4	2032.1	1949.6	1867.1	1617.7	1368.3	1193.7
42.5°	919.6	1026.8	1255.3	1483.8	1659.6	1835.4	1780.8	1726.2	1500.3	1274.3	1112.5
45°	835.2	925.3	1126.5	1327.7	1489.5	1651.3	1608.2	1565.0	1370.2	1175.3	1026.8
47.5°	760.3	837.7	1017.3	1196.9	1342.3	1487.6	1447.6	1407.6	1246.4	1085.2	950.0
50°	691.8	757.8	907.5	1057.3	1188.0	1318.8	1285.8	1252.8	1119.5	986.2	869.4
52.5°	627.0	681.6	816.1	950.7	1056.0	1161.4	1136.0	1110.6	1007.8	905.0	799.0
55°	565.5	615.6	729.2	842.8	932.9	1023.0	997.6	972.3	892.3	812.3	719.0
57.5°	509.6	553.4	645.4	737.4	809.2	880.9	868.8	856.8	790.1	723.5	646.7
60°	450.6	489.9	569.3	648.6	706.3	764.1	750.1	736.2	688.6	641.0	575.0
62.5°	397.9	432.8	496.3	559.7	606.7	653.7	643.5	633.4	597.2	561.0	506.4
65°	342.7	377.0	428.4	479.8	516.6	553.4	544.5	535.6	508.3	481.1	437.3
67.5°	292.6	321.1	365.5	410.0	434.7	459.5	454.4	449.3	428.4	407.4	373.2
70°	241.8	266.5	303.4	340.2	357.3	374.4	376.3	378.2	359.2	340.2	314.8
72.5°	191.0	210.7	245.0	279.2	292.6	305.9	305.3	304.6	293.2	281.8	258.9
75°	146.6	161.2	187.9	214.5	225.9	237.4	239.9	242.4	231.6	220.9	208.2
77.5°	105.3	115.5	135.8	156.1	168.8	181.5	182.8	184.0	179.0	173.9	161.8
80°	74.3	77.4	90.1	102.8	116.1	129.5	131.4	133.3	128.2	123.1	115.5
82.5°	51.4	53.3	57.8	62.2	73.0	83.8	86.3	88.8	86.3	83.8	75.5
85°	31.1	31.7	33.6	35.5	40.6	45.7	48.2	50.8	49.5	48.2	43.8
87.5°	14.0	14.0	14.6	15.2	16.5	17.8	20.9	24.1	22.2	20.3	18.4
90°	18.1	15.2	12.4	10.5	8.6	5.7	3.8	1.9	3.8	5.7	8.6
92.5°	146.6	96.2	65.7	48.6	39.0	30.5	20.9	14.3	20.9	30.5	39.0
95°	346.6	204.7	123.8	86.7	61.9	45.7	35.2	32.4	35.2	45.7	61.9
97.5°	385.7	220.9	140.9	100.0	75.2	60.9	52.4	51.4	52.4	60.9	75.2
100°	359.0	218.1	151.4	114.3	91.4	78.1	71.4	70.5	71.4	78.1	91.4
102.5°	336.1	221.9	163.8	130.5	110.5	98.1	92.4	90.5	92.4	98.1	110.5
105°	327.6	229.5	178.1	148.6	130.5	119.0	113.3	110.5	113.3	119.0	130.5
107.5°	325.7	241.9	196.2	168.6	151.4	140.0	134.3	131.4	134.3	140.0	151.4
110°	330.4	258.1	215.2	188.5	172.4	161.9	157.1	154.3	157.1	161.9	172.4

TEST NUMBER: P831791

CATALOG NUMBER: S123RDIP-S1000D1025U950-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	340.0	274.3	235.2	209.5	193.3	182.8	178.1	175.2	178.1	182.8	193.3
115°	350.4	292.3	256.2	230.4	214.3	204.7	199.0	195.2	199.0	204.7	214.3
117.5°	363.8	311.4	275.2	251.4	233.3	224.7	220.0	215.2	220.0	224.7	233.3
120°	379.0	329.5	295.2	271.4	253.3	243.8	239.0	236.2	239.0	243.8	253.3
122.5°	393.3	348.5	315.2	289.5	272.3	261.9	257.1	254.3	257.1	261.9	272.3
125°	408.5	366.6	333.3	307.6	289.5	279.0	273.3	271.4	273.3	279.0	289.5
127.5°	420.9	382.8	350.4	324.7	304.7	294.2	287.6	284.7	287.6	294.2	304.7
130°	433.3	397.1	365.7	340.0	320.0	308.5	300.0	297.1	300.0	308.5	320.0
132.5°	444.7	409.5	379.0	354.2	334.2	320.0	310.4	306.6	310.4	320.0	334.2
135°	454.2	421.9	392.3	366.6	346.6	332.3	321.9	318.1	321.9	332.3	346.6
137.5°	461.8	430.4	401.9	378.0	358.1	342.8	332.3	328.5	332.3	342.8	358.1
140°	467.6	439.0	411.4	387.6	368.5	353.3	343.8	339.0	343.8	353.3	368.5
142.5°	473.3	445.7	419.0	397.1	378.0	364.7	354.2	350.4	354.2	364.7	378.0
145°	477.1	451.4	426.6	404.7	388.5	374.2	365.7	362.8	365.7	374.2	388.5
147.5°	479.9	456.1	433.3	414.2	398.0	385.7	377.1	375.2	377.1	385.7	398.0
150°	480.9	460.9	439.0	421.9	408.5	396.1	388.5	387.6	388.5	396.1	408.5
152.5°	482.8	463.8	445.7	429.5	418.0	407.6	400.0	400.0	400.0	407.6	418.0
155°	482.8	467.6	451.4	438.0	427.6	418.0	412.3	412.3	412.3	418.0	427.6
157.5°	483.7	469.5	456.1	445.7	436.1	427.6	422.8	421.9	422.8	427.6	436.1
160°	483.7	472.3	460.9	451.4	444.7	437.1	433.3	433.3	433.3	437.1	444.7
162.5°	482.8	473.3	463.8	456.1	450.4	444.7	441.8	441.8	441.8	444.7	450.4
165°	480.9	474.2	466.6	459.9	456.1	451.4	449.5	450.4	449.5	451.4	456.1
167.5°	479.9	474.2	468.5	463.8	460.9	457.1	456.1	457.1	456.1	457.1	460.9
170°	477.1	473.3	468.5	466.6	464.7	461.8	460.9	462.8	460.9	461.8	464.7
172.5°	476.1	473.3	469.5	468.5	467.6	465.7	465.7	466.6	465.7	465.7	467.6
175°	474.2	472.3	470.4	469.5	469.5	467.6	468.5	469.5	468.5	467.6	469.5
177.5°	473.3	471.4	470.4	470.4	470.4	469.5	470.4	471.4	470.4	469.5	470.4
180°	470.4	470.4	470.4	470.4	470.4	470.4	470.4	470.4	470.4	470.4	470.4



TEST NUMBER: P831791

CATALOG NUMBER: S123RDIP-S1000D1025U950-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	3095.7	3095.7	3095.7	3095.7	3095.7	3095.7	3095.7	3095.7	3095.7	3095.7	3095.7
2.5°	2996.7	2960.6	2924.4	2898.4	2872.4	2840.0	2807.6	2806.4	2805.1	2781.0	2756.9
5°	2819.0	2756.2	2693.4	2631.8	2570.3	2508.7	2447.2	2433.2	2419.2	2398.3	2377.3
7.5°	2661.7	2561.4	2461.1	2382.4	2303.7	2242.2	2180.6	2138.7	2096.8	2064.5	2032.1
10°	2492.8	2368.5	2244.1	2148.9	2053.7	1987.0	1920.4	1872.2	1823.9	1801.1	1778.2
12.5°	2317.7	2182.5	2047.3	1954.0	1860.7	1780.8	1700.8	1657.0	1613.2	1581.5	1549.8
15°	2156.5	2011.2	1865.8	1766.8	1667.8	1592.9	1518.0	1474.3	1430.5	1398.7	1367.0
17.5°	2000.4	1853.8	1707.2	1606.9	1506.6	1438.7	1370.8	1328.3	1285.8	1266.1	1246.4
20°	1858.2	1710.3	1562.5	1467.9	1373.4	1306.7	1240.1	1217.2	1194.4	1176.0	1157.6
22.5°	1717.3	1575.2	1433.0	1342.3	1251.5	1203.3	1155.0	1136.6	1118.2	1104.3	1090.3
25°	1599.3	1457.8	1316.2	1236.9	1157.6	1120.1	1082.7	1070.6	1058.6	1044.6	1030.6
27.5°	1480.0	1345.4	1210.9	1147.4	1084.0	1053.5	1023.0	1007.8	992.6	981.1	969.7
30°	1374.6	1250.2	1125.8	1073.2	1020.5	993.8	967.2	950.7	934.2	923.4	912.6
32.5°	1273.1	1162.7	1052.2	1007.2	962.1	936.1	910.1	894.2	878.3	865.6	852.9
35°	1179.2	1083.3	987.5	946.2	905.0	879.0	852.9	837.1	821.2	808.5	795.8
37.5°	1096.6	1009.7	922.8	884.0	845.3	822.5	799.6	783.1	766.6	753.3	740.0
40°	1019.2	942.4	865.6	828.2	790.8	766.0	741.3	726.7	712.1	700.0	687.9
42.5°	950.7	880.2	809.8	773.0	736.2	712.7	689.2	672.1	654.9	648.0	641.0
45°	878.3	816.1	753.9	718.4	682.9	658.1	633.4	618.8	604.2	597.8	591.5
47.5°	814.9	757.1	699.4	664.5	629.6	607.3	585.1	573.7	562.3	553.4	544.5
50°	752.7	696.8	641.0	607.3	573.7	554.7	535.6	521.7	507.7	501.4	495.0
52.5°	693.0	642.3	591.5	557.2	522.9	504.5	486.1	474.1	462.0	448.7	435.4
55°	625.8	581.3	536.9	506.4	476.0	456.9	437.9	423.9	410.0	396.0	382.1
57.5°	569.9	526.1	482.3	455.0	427.7	409.3	390.9	375.7	360.5	349.0	337.6
60°	509.0	470.9	432.8	406.2	379.5	361.7	344.0	329.4	314.8	309.1	303.4
62.5°	451.9	416.3	380.8	357.3	333.8	316.7	299.5	290.0	280.5	276.7	272.9
65°	393.5	363.0	332.5	311.0	289.4	274.8	260.2	255.8	251.3	248.1	245.0
67.5°	338.9	312.9	286.9	267.8	248.8	238.6	228.5	223.4	218.3	214.5	210.7
70°	289.4	266.5	243.7	227.2	210.7	201.2	191.7	187.2	182.8	175.8	168.8
72.5°	236.1	218.3	200.5	187.9	175.2	166.9	158.7	149.8	140.9	134.5	128.2
75°	195.5	177.7	159.9	147.9	135.8	126.3	116.8	113.6	110.4	108.5	106.6
77.5°	149.8	134.5	119.3	109.8	100.3	95.8	91.4	89.5	87.6	86.9	86.3
80°	107.9	95.2	82.5	77.4	72.3	71.1	69.8	68.5	67.3	66.6	66.0
82.5°	67.3	60.9	54.6	53.3	52.0	51.4	50.8	50.1	49.5	48.9	48.2
85°	39.3	36.8	34.3	33.6	33.0	32.4	31.7	31.7	31.7	31.7	31.7
87.5°	16.5	16.5	16.5	16.5	16.5	16.5	16.5	16.5	16.5	15.9	15.2
90°	10.5	12.4	15.2	18.1	20.9	23.8	22.9	23.8	24.8	25.7	27.6
92.5°	48.6	65.7	96.2	146.6	196.2	177.1	132.4	94.3	73.3	63.8	57.1
95°	86.7	123.8	204.7	346.6	502.8	564.7	458.0	342.8	232.4	181.9	147.6
97.5°	100.0	140.9	220.9	385.7	648.5	868.5	898.0	787.5	594.2	468.5	360.0
100°	114.3	151.4	218.1	359.0	609.4	901.8	1089.4	1122.7	1045.6	934.2	798.9
102.5°	130.5	163.8	221.9	336.1	552.3	839.9	1098.9	1234.1	1250.3	1197.0	1123.7
105°	148.6	178.1	229.5	327.6	507.6	765.6	1038.9	1237.9	1333.2	1351.3	1326.5
107.5°	168.6	196.2	241.9	325.7	475.2	699.9	953.2	1180.8	1330.3	1404.6	1430.3
110°	188.5	215.2	258.1	330.4	458.0	645.6	873.2	1091.3	1266.5	1386.5	1453.2



TEST NUMBER: P831791

CATALOG NUMBER: S123RDIP-S1000D1025U950-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	209.5	235.2	274.3	340.0	448.5	609.4	803.7	1002.7	1182.7	1320.8	1411.3
115°	230.4	256.2	292.3	350.4	447.6	585.6	750.4	926.6	1092.2	1232.2	1336.0
117.5°	251.4	275.2	311.4	363.8	448.5	569.5	715.1	867.5	1014.2	1142.7	1250.3
120°	271.4	295.2	329.5	379.0	452.3	559.0	688.5	822.8	951.3	1065.6	1161.8
122.5°	289.5	315.2	348.5	393.3	459.0	552.3	666.6	787.5	900.8	1004.6	1092.2
125°	307.6	333.3	366.6	408.5	465.7	546.6	648.5	757.0	860.8	952.3	1028.4
127.5°	324.7	350.4	382.8	420.9	473.3	543.7	631.4	729.4	823.7	907.5	978.0
130°	340.0	365.7	397.1	433.3	480.9	540.9	618.0	703.7	789.4	866.6	931.3
132.5°	354.2	379.0	409.5	444.7	486.6	539.9	605.6	679.9	757.0	827.5	888.5
135°	366.6	392.3	421.9	454.2	492.3	539.0	595.2	659.0	726.6	788.5	842.8
137.5°	378.0	401.9	430.4	461.8	496.1	537.1	585.6	639.0	696.1	751.3	799.9
140°	387.6	411.4	439.0	467.6	499.9	536.1	577.1	621.8	670.4	716.1	757.0
142.5°	397.1	419.0	445.7	473.3	502.8	534.2	569.5	605.6	645.6	683.7	718.0
145°	404.7	426.6	451.4	477.1	503.7	532.3	562.8	593.3	624.7	655.2	682.8
147.5°	414.2	433.3	456.1	479.9	503.7	529.5	556.1	582.8	608.5	634.2	654.2
150°	421.9	439.0	460.9	480.9	503.7	525.6	549.5	571.4	593.3	613.3	631.4
152.5°	429.5	445.7	463.8	482.8	500.9	520.9	541.8	560.9	579.0	596.1	610.4
155°	438.0	451.4	467.6	482.8	499.0	515.2	534.2	550.4	565.6	579.9	591.4
157.5°	445.7	456.1	469.5	483.7	496.1	510.4	525.6	539.0	552.3	563.7	573.3
160°	451.4	460.9	472.3	483.7	494.2	504.7	517.1	529.5	539.9	549.5	556.1
162.5°	456.1	463.8	473.3	482.8	490.4	499.0	508.5	518.0	526.6	535.2	540.9
165°	459.9	466.6	474.2	480.9	486.6	493.3	500.9	508.5	514.2	520.9	525.6
167.5°	463.8	468.5	474.2	479.9	482.8	487.6	493.3	499.9	504.7	508.5	512.3
170°	466.6	468.5	473.3	477.1	479.0	481.8	486.6	491.4	494.2	498.0	499.9
172.5°	468.5	469.5	473.3	476.1	476.1	477.1	479.9	483.7	485.7	488.5	489.5
175°	469.5	470.4	472.3	474.2	473.3	473.3	475.2	477.1	478.0	479.9	479.9
177.5°	470.4	470.4	471.4	473.3	471.4	470.4	471.4	472.3	473.3	474.2	474.2
180°	470.4	470.4	470.4	470.4	470.4	470.4	470.4	470.4	470.4	470.4	470.4



TEST NUMBER: P831791

CATALOG NUMBER: S123RDIP-S1000D1025U950-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	3095.7	3095.7	3095.7	3095.7
2.5°	2750.5	2744.2	2741.6	2739.1
5°	2357.7	2338.0	2333.6	2329.1
7.5°	2023.9	2015.6	1988.3	1961.0
10°	1752.9	1727.5	1716.1	1704.6
12.5°	1526.3	1502.8	1499.0	1495.2
15°	1350.5	1334.0	1328.3	1322.6
17.5°	1235.0	1223.6	1216.6	1209.6
20°	1149.3	1141.1	1136.0	1130.9
22.5°	1084.0	1077.6	1073.8	1070.0
25°	1021.1	1011.6	1008.4	1005.3
27.5°	961.5	953.2	950.0	946.9
30°	905.6	898.6	894.2	889.8
32.5°	844.7	836.4	833.9	831.4
35°	790.8	785.7	783.1	780.6
37.5°	733.6	727.3	723.5	719.7
40°	684.8	681.6	679.7	677.8
42.5°	635.3	629.6	628.9	628.3
45°	585.8	580.1	578.8	577.5
47.5°	539.4	534.4	533.7	533.1
50°	488.0	481.1	476.0	470.9
52.5°	429.0	422.7	418.2	413.8
55°	375.1	368.1	364.3	360.5
57.5°	334.5	331.3	329.4	327.5
60°	301.5	299.5	298.3	297.0
62.5°	271.0	269.1	269.1	269.1
65°	243.1	241.2	239.3	237.4
67.5°	206.9	203.1	202.4	201.8
70°	163.1	157.4	156.8	156.1
72.5°	127.6	126.9	125.7	124.4
75°	105.3	104.1	104.1	104.1
77.5°	85.0	83.8	83.8	83.8
80°	65.4	64.7	65.4	66.0
82.5°	48.2	48.2	47.6	47.0
85°	31.1	30.5	30.5	30.5
87.5°	15.2	15.2	15.2	15.2
90°	26.7	27.6	28.6	27.6
92.5°	55.2	51.4	52.4	50.5
95°	129.5	120.9	114.3	110.5
97.5°	296.2	260.0	237.1	226.6
100°	702.8	633.3	596.1	597.1
102.5°	1054.2	1002.7	973.2	945.6
105°	1282.7	1246.5	1216.0	1211.3
107.5°	1424.6	1407.4	1395.1	1384.6
110°	1479.8	1487.4	1485.5	1483.6



TEST NUMBER: P831791

CATALOG NUMBER: S123RDIP-S1000D1025U950-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
112.5°	1465.5	1493.1	1502.7	1503.6
115°	1407.4	1449.3	1468.4	1473.2
117.5°	1324.6	1371.3	1399.8	1406.5
120°	1237.0	1290.3	1313.2	1318.9
122.5°	1157.0	1203.7	1229.4	1237.0
125°	1089.4	1131.3	1155.1	1161.8
127.5°	1033.2	1069.4	1091.3	1097.0
130°	981.8	1016.1	1036.1	1043.7
132.5°	935.1	969.4	986.5	991.3
135°	889.4	918.0	935.1	941.8
137.5°	839.9	869.4	883.7	889.4
140°	793.2	819.9	835.1	834.2
142.5°	747.5	770.4	783.7	782.8
145°	706.6	726.6	734.2	736.1
147.5°	673.2	687.5	695.2	696.1
150°	645.6	656.1	661.8	661.8
152.5°	620.9	630.4	633.3	633.3
155°	599.9	607.5	609.4	610.4
157.5°	580.9	586.6	588.5	588.5
160°	562.8	568.5	568.5	567.5
162.5°	544.7	549.5	549.5	548.5
165°	529.5	533.3	532.3	532.3
167.5°	514.2	517.1	516.1	516.1
170°	500.9	502.8	501.8	501.8
172.5°	489.5	491.4	489.5	488.5
175°	479.9	480.9	479.9	479.0
177.5°	473.3	474.2	472.3	472.3
180°	470.4	470.4	470.4	470.4

TEST NUMBER: P831791

CATALOG NUMBER: S123RDIP-S1000D1025U950-4F0-1E-UDD-G4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.27	14.11	14.21	15.05	16.28	17.93	18.77	18.87	19.72	20.94
	3H	14.49	15.24	15.44	16.19	17.44	19.43	20.18	20.38	21.14	22.38
	4H	14.88	15.58	15.84	16.54	17.80	19.92	20.63	20.89	21.59	22.84
	6H	15.16	15.81	16.13	16.77	18.04	20.24	20.89	21.21	21.85	23.12
	8H	15.24	15.86	16.22	16.84	18.11	20.32	20.93	21.30	21.91	23.18
	12H	15.30	15.88	16.28	16.86	18.15	20.35	20.94	21.33	21.91	23.20
4H	2H	14.00	14.70	14.96	15.66	16.92	17.93	18.64	18.90	19.60	20.85
	3H	15.36	15.95	16.34	16.94	18.21	19.59	20.18	20.57	21.16	22.43
	4H	15.82	16.36	16.81	17.34	18.63	20.20	20.73	21.18	21.71	23.01
	6H	16.19	16.65	17.19	17.65	18.94	20.63	21.09	21.63	22.10	23.39
	8H	16.31	16.74	17.31	17.74	19.05	20.77	21.19	21.76	22.19	23.50
	12H	16.39	16.78	17.41	17.79	19.10	20.83	21.21	21.84	22.23	23.54
8H	4H	16.13	16.56	17.13	17.56	18.87	20.16	20.59	21.16	21.59	22.90
	6H	16.60	16.95	17.62	17.99	19.30	20.66	21.01	21.68	22.05	23.36
	8H	16.79	17.10	17.82	18.13	19.45	20.85	21.16	21.88	22.19	23.51
	12H	16.93	17.21	17.97	18.23	19.59	20.96	21.24	22.00	22.26	23.62
12H	4H	16.15	16.53	17.16	17.55	18.86	20.11	20.50	21.13	21.52	22.83
	6H	16.66	16.97	17.69	18.00	19.32	20.64	20.95	21.67	21.97	23.30
	8H	16.88	17.15	17.91	18.17	19.54	20.83	21.10	21.86	22.12	23.49