

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831871

Luminaire Tested: S123RDIP-S1000D585U950-4F0-1E-UDD-G1

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P831871
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-2, G3-1807-864-9)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1000D585U950-4F0-1E-UDD-G1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, GRAZE OPTIC
UPLIGHT 585 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6025.3 lumens
Efficiency: N/A
Efficacy: 119.8 lumens/watt
Spacing Criteria (0/90/45): 0.55 / 1.17 / 0.8
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 50.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P831871

CATALOG NUMBER: S123RDIP-S1000D585U950-4F0-1E-UDD-G1

Luminous Intensity Polar Plot





TEST NUMBER: P831871

CATALOG NUMBER: S123RDIP-S1000D585U950-4F0-1E-UDD-G1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20				
RC	80					70					50					30				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	111	111	111	111	105	105	105	105	93	93	93	83	83	83	73	73	73	68		
1	103	99	95	92	97	94	90	88	84	81	79	74	73	71	66	65	64	60		
2	95	88	82	77	89	83	78	74	75	71	67	67	64	61	60	57	55	52		
3	87	78	71	66	82	74	68	63	67	62	58	60	56	53	54	51	49	45		
4	81	70	63	57	76	67	60	55	61	55	51	55	50	47	49	46	43	40		
5	75	63	56	50	70	61	54	48	55	49	45	50	45	42	45	41	38	36		
6	69	58	50	44	65	55	48	43	50	44	40	46	41	37	41	38	35	32		
7	65	53	45	40	61	51	44	39	46	40	36	42	37	34	38	34	32	29		
8	60	49	41	36	57	46	40	35	43	37	33	39	34	31	36	32	29	27		
9	57	45	38	33	54	43	36	32	40	34	30	36	32	28	33	29	27	25		
10	53	42	35	30	51	40	33	29	37	31	28	34	29	26	31	27	25	23		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	33322	33322	33322	33322	33322
5°	39566	38305	33532	27107	25166
10°	35848	38907	33365	21718	18631
15°	24682	33360	33013	17751	14739
20°	17171	25684	32349	14968	12954
25°	13085	19574	31385	13303	11940
30°	11390	15649	30179	12352	11059
35°	10457	13201	28470	11550	10257
40°	9542	11789	26235	10763	9524
45°	8617	10782	23823	10018	8791
50°	7822	9947	20979	9289	7886
55°	7075	9135	18246	8574	6765
60°	6340	8308	15849	7787	6394
65°	5850	7371	13642	6999	6046
70°	4752	6370	11903	6332	4913
75°	4171	5065	10081	5253	4329
80°	3775	4289	8263	4407	4091
85°	3446	3767	6274	4001	3767

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 25137 cd/sqm



TEST NUMBER: P831871

CATALOG NUMBER: S123RDIP-S1000D585U950-4F0-1E-UDD-G1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	282.2	4.7
10°-20°	652.9	10.8
20°-30°	749.2	12.4
30°-40°	738.4	12.3
40°-50°	651.2	10.8
50°-60°	501.0	8.3
60°-70°	329.4	5.5
70°-80°	160.0	2.7
80°-90°	41.8	0.7
90°-100°	44.6	0.7
100°-110°	135.0	2.2
110°-120°	229.8	3.8
120°-130°	302.3	5.0
130°-140°	339.8	5.6
140°-150°	334.0	5.5
150°-160°	281.2	4.7
160°-170°	187.2	3.1
170°-180°	65.6	1.1
0°-30°	1684.3	28.0
0°-40°	2422.7	40.2
0°-60°	3574.9	59.3
0°-90°	4106.0	68.1
90°-120°	409.3	6.8
90°-150°	1385.4	23.0
90°-180°	1919.0	31.8
0°-180°	6025.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	3096	3096	3096	3096	3096	
5°	3662	3545	3103	2509	2329	335
15°	2215	2994	2962	1593	1323	625
25°	1102	1648	2643	1120	1005	520
35°	796	1005	2167	879	781	496
45°	566	708	1565	658	578	439
55°	377	487	972	457	360	338
65°	230	289	536	275	237	225
75°	100	122	242	126	104	108
85°	28	30	51	32	30	30
90°	16	13	0	13	16	9
95°	42	40	32	40	42	43
105°	130	128	122	128	130	137
115°	232	232	231	232	232	230
125°	335	339	338	339	335	299
135°	439	442	439	442	439	337
145°	533	535	533	535	533	333
155°	609	610	610	610	609	281
165°	662	663	664	663	662	187
175°	688	689	691	689	688	65
180°	693	693	693	693	693	



TEST NUMBER: P831871

CATALOG NUMBER: S123RDIP-S1000D585U950-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	3095.7	3095.7	3095.7	3095.7	3095.7	3095.7	3095.7	3095.7	3095.7	3095.7	3095.7
2.5°	3430.8	3420.0	3409.3	3406.1	3402.9	3392.8	3382.6	3359.8	3336.9	3313.4	3289.9
5°	3661.8	3663.1	3664.4	3661.2	3658.0	3644.7	3631.4	3603.5	3575.5	3545.1	3514.6
7.5°	3590.8	3611.1	3631.4	3635.2	3639.0	3649.2	3659.3	3653.0	3646.6	3635.2	3623.8
10°	3279.8	3278.5	3277.3	3300.1	3322.9	3390.9	3458.8	3493.7	3528.6	3559.7	3590.8
12.5°	2772.1	2774.0	2775.9	2850.8	2925.7	2989.8	3053.9	3142.7	3231.6	3327.4	3423.2
15°	2214.9	2246.0	2277.1	2343.7	2410.3	2506.8	2603.3	2722.6	2841.9	2993.6	3145.3
17.5°	1818.9	1832.2	1845.5	1909.6	1973.7	2065.1	2156.5	2291.7	2426.8	2622.3	2817.8
20°	1499.0	1511.1	1523.1	1569.5	1615.8	1703.4	1790.9	1919.8	2048.6	2242.2	2435.7
22.5°	1251.5	1275.0	1298.5	1329.6	1360.7	1424.1	1487.6	1619.0	1750.3	1926.8	2103.2
25°	1101.7	1112.5	1123.3	1150.0	1176.6	1237.5	1298.5	1385.4	1472.4	1648.1	1823.9
27.5°	1000.2	1003.4	1006.5	1026.2	1045.9	1085.2	1124.6	1205.2	1285.8	1430.5	1575.2
30°	916.4	922.1	927.8	943.1	958.3	986.9	1015.4	1072.5	1129.7	1259.1	1388.6
32.5°	851.7	854.9	858.0	870.7	883.4	904.4	925.3	970.4	1015.4	1114.4	1213.4
35°	795.8	796.5	797.1	806.6	816.1	836.4	856.8	894.2	931.6	1004.6	1077.6
37.5°	732.4	736.8	741.3	748.2	755.2	773.0	790.8	821.2	851.7	912.0	972.3
40°	679.1	682.9	686.7	694.9	703.2	717.1	731.1	759.0	786.9	839.0	891.0
42.5°	625.8	628.3	630.8	639.1	647.3	664.5	681.6	703.8	726.0	769.2	812.3
45°	566.1	572.4	578.8	587.7	596.6	611.2	625.8	648.6	671.4	708.3	745.1
47.5°	516.6	519.8	522.9	530.6	538.2	555.9	573.7	594.0	614.3	648.6	682.9
50°	467.1	468.4	469.6	476.6	483.6	499.5	515.3	538.8	562.3	594.0	625.8
52.5°	420.1	423.3	426.5	433.5	440.4	451.2	462.0	486.1	510.2	541.3	572.4
55°	377.0	378.9	380.8	385.9	390.9	403.6	416.3	437.3	458.2	486.8	515.3
57.5°	336.4	338.9	341.4	345.2	349.0	360.5	371.9	390.3	408.7	437.3	465.8
60°	294.5	297.6	300.8	305.3	309.7	318.6	327.5	344.0	360.5	385.9	411.2
62.5°	264.0	264.6	265.3	269.1	272.9	279.2	285.6	298.9	312.2	337.6	363.0
65°	229.7	231.6	233.5	235.4	237.4	242.4	247.5	258.9	270.4	289.4	308.4
67.5°	194.2	196.1	198.0	201.2	204.4	208.8	213.2	220.9	228.5	246.2	264.0
70°	151.0	151.0	151.0	156.1	161.2	168.8	176.4	182.1	187.9	202.4	217.0
72.5°	123.1	123.8	124.4	125.0	125.7	130.1	134.5	144.1	153.6	162.5	171.4
75°	100.3	100.9	101.5	102.2	102.8	104.1	105.3	108.5	111.7	121.8	132.0
77.5°	80.0	80.6	81.2	81.9	82.5	83.8	85.0	86.3	87.6	91.4	95.2
80°	60.9	61.6	62.2	62.8	63.5	64.1	64.7	66.0	67.3	69.2	71.1
82.5°	44.4	44.4	44.4	44.4	44.4	45.7	47.0	47.0	47.0	48.2	49.5
85°	27.9	27.9	27.9	28.6	29.2	29.2	29.2	29.8	30.5	30.5	30.5
87.5°	12.7	12.1	11.4	12.1	12.7	12.7	12.7	13.3	14.0	14.0	14.0
90°	16.3	16.1	15.8	15.6	15.4	15.0	14.5	14.0	13.5	13.1	11.5
92.5°	23.4	23.6	23.9	24.1	24.4	24.3	23.9	23.6	23.2	22.9	22.1
95°	42.4	42.4	42.4	42.4	42.4	42.2	41.7	41.2	40.8	40.3	39.3
97.5°	60.9	61.1	61.2	61.3	61.4	61.2	60.6	60.0	59.4	58.8	58.0
100°	82.7	82.5	82.2	82.0	81.7	81.4	81.1	80.7	80.4	80.0	79.4
102.5°	105.0	105.1	105.3	105.4	105.5	105.4	105.0	104.7	104.3	103.9	103.1
105°	129.5	129.3	129.0	128.8	128.5	128.4	128.4	128.4	128.4	128.4	127.3
107.5°	154.5	154.7	154.8	154.9	155.0	154.9	154.5	154.2	153.8	153.5	153.0
110°	180.1	180.4	180.6	180.8	181.1	181.0	180.5	180.0	179.5	179.0	178.8



TEST NUMBER: P831871

CATALOG NUMBER: S123RDIP-S1000D585U950-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	207.3	207.3	207.3	207.3	207.3	207.0	206.4	205.8	205.2	204.6	204.6
115°	231.8	231.9	232.1	232.2	232.3	232.3	232.2	232.1	231.9	231.8	232.1
117.5°	256.8	257.2	257.6	257.9	258.3	258.5	258.5	258.5	258.5	258.5	258.7
120°	283.5	283.7	284.0	284.2	284.5	284.7	284.8	284.9	285.0	285.1	285.7
122.5°	309.1	309.4	309.8	310.2	310.5	310.9	311.3	311.6	312.0	312.3	312.6
125°	334.7	335.1	335.6	336.1	336.6	337.1	337.6	338.0	338.5	339.0	339.2
127.5°	360.2	360.7	361.2	361.7	362.2	362.8	363.5	364.2	364.9	365.7	365.9
130°	385.3	386.1	387.0	387.8	388.6	389.3	389.8	390.3	390.8	391.2	391.6
132.5°	411.4	412.0	412.6	413.2	413.8	414.4	415.0	415.6	416.2	416.8	417.1
135°	438.6	438.8	439.1	439.3	439.6	439.9	440.4	440.9	441.4	441.9	442.0
137.5°	462.5	462.9	463.3	463.6	464.0	464.5	465.1	465.7	466.3	466.9	466.5
140°	485.9	486.8	487.6	488.5	489.3	489.8	489.9	490.0	490.2	490.3	490.2
142.5°	509.9	510.5	511.1	511.7	512.3	512.7	512.8	512.9	513.0	513.1	512.9
145°	532.7	533.2	533.7	534.2	534.7	535.0	535.1	535.2	535.3	535.4	535.1
147.5°	553.4	554.1	554.9	555.6	556.3	556.7	556.7	556.7	556.7	556.7	556.3
150°	573.0	573.7	574.4	575.2	575.9	576.3	576.3	576.3	576.3	576.3	576.0
152.5°	592.0	592.6	593.2	593.9	594.5	594.6	594.4	594.2	593.9	593.7	593.5
155°	608.9	609.8	610.6	611.4	612.3	612.5	612.0	611.5	611.0	610.5	610.4
157.5°	624.7	625.4	626.1	626.9	627.6	627.7	627.2	626.7	626.3	625.8	625.7
160°	639.9	640.4	640.9	641.4	641.9	641.8	641.2	640.6	640.0	639.4	639.4
162.5°	651.4	652.2	653.0	653.9	654.7	654.9	654.3	653.6	653.0	652.4	652.3
165°	662.2	663.1	663.9	664.8	665.6	665.7	665.0	664.2	663.5	662.8	662.8
167.5°	672.0	672.8	673.5	674.2	674.9	674.9	674.2	673.5	672.8	672.0	671.9
170°	679.1	679.9	680.8	681.6	682.5	682.5	681.6	680.8	679.9	679.1	679.1
172.5°	684.5	685.4	686.2	687.1	687.9	688.0	687.3	686.5	685.8	685.1	685.1
175°	688.4	689.2	690.0	690.9	691.7	691.8	691.1	690.3	689.6	688.9	688.9
177.5°	690.5	691.4	692.2	693.1	693.9	694.0	693.3	692.5	691.8	691.1	691.1
180°	692.7	692.7	692.7	692.7	692.7	692.7	692.7	692.7	692.7	692.7	692.7



TEST NUMBER: P831871

CATALOG NUMBER: S123RDIP-S1000D585U950-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	3095.7	3095.7	3095.7	3095.7	3095.7	3095.7	3095.7	3095.7	3095.7	3095.7	3095.7
2.5°	3286.8	3283.6	3253.1	3222.7	3192.8	3163.0	3140.8	3118.6	3081.2	3043.7	3020.2
5°	3490.5	3466.4	3418.1	3369.9	3297.6	3225.2	3164.3	3103.4	3025.9	2948.5	2883.8
7.5°	3604.1	3584.4	3526.0	3467.6	3371.8	3276.0	3180.8	3085.6	2971.4	2857.1	2759.4
10°	3607.3	3623.8	3575.5	3527.3	3419.4	3311.5	3182.1	3052.6	2899.0	2745.4	2619.1
12.5°	3494.3	3565.4	3555.2	3545.1	3435.3	3325.5	3168.1	3010.7	2822.2	2633.7	2475.7
15°	3283.0	3420.7	3461.3	3501.9	3411.2	3320.4	3141.4	2962.5	2741.0	2519.5	2338.0
17.5°	3010.7	3203.6	3310.9	3418.1	3352.1	3286.1	3090.0	2893.9	2644.5	2395.1	2197.7
20°	2688.3	2940.9	3109.1	3277.3	3253.1	3229.0	3026.6	2824.1	2555.0	2286.0	2072.1
22.5°	2369.7	2636.3	2868.6	3100.8	3125.6	3150.3	2946.0	2741.6	2447.2	2152.7	1935.0
25°	2094.9	2365.9	2642.6	2919.3	2975.2	3031.0	2836.8	2642.6	2337.4	2032.1	1815.7
27.5°	1832.8	2090.5	2395.1	2699.7	2801.3	2902.8	2725.1	2547.4	2229.5	1911.5	1695.7
30°	1619.0	1849.3	2160.3	2471.3	2612.8	2754.3	2591.2	2428.1	2112.7	1797.3	1586.0
32.5°	1419.7	1625.9	1938.2	2250.4	2414.8	2579.2	2438.3	2297.4	1994.0	1690.7	1481.9
35°	1262.3	1447.0	1738.3	2029.6	2213.6	2397.7	2282.1	2166.6	1870.3	1573.9	1376.5
37.5°	1127.1	1282.0	1555.5	1829.0	2024.5	2220.0	2123.5	2027.0	1748.4	1469.8	1283.2
40°	1015.4	1139.8	1394.3	1648.8	1840.4	2032.1	1949.6	1867.1	1617.7	1368.3	1193.7
42.5°	919.6	1026.8	1255.3	1483.8	1659.6	1835.4	1780.8	1726.2	1500.3	1274.3	1112.5
45°	835.2	925.3	1126.5	1327.7	1489.5	1651.3	1608.2	1565.0	1370.2	1175.3	1026.8
47.5°	760.3	837.7	1017.3	1196.9	1342.3	1487.6	1447.6	1407.6	1246.4	1085.2	950.0
50°	691.8	757.8	907.5	1057.3	1188.0	1318.8	1285.8	1252.8	1119.5	986.2	869.4
52.5°	627.0	681.6	816.1	950.7	1056.0	1161.4	1136.0	1110.6	1007.8	905.0	799.0
55°	565.5	615.6	729.2	842.8	932.9	1023.0	997.6	972.3	892.3	812.3	719.0
57.5°	509.6	553.4	645.4	737.4	809.2	880.9	868.8	856.8	790.1	723.5	646.7
60°	450.6	489.9	569.3	648.6	706.3	764.1	750.1	736.2	688.6	641.0	575.0
62.5°	397.9	432.8	496.3	559.7	606.7	653.7	643.5	633.4	597.2	561.0	506.4
65°	342.7	377.0	428.4	479.8	516.6	553.4	544.5	535.6	508.3	481.1	437.3
67.5°	292.6	321.1	365.5	410.0	434.7	459.5	454.4	449.3	428.4	407.4	373.2
70°	241.8	266.5	303.4	340.2	357.3	374.4	376.3	378.2	359.2	340.2	314.8
72.5°	191.0	210.7	245.0	279.2	292.6	305.9	305.3	304.6	293.2	281.8	258.9
75°	146.6	161.2	187.9	214.5	225.9	237.4	239.9	242.4	231.6	220.9	208.2
77.5°	105.3	115.5	135.8	156.1	168.8	181.5	182.8	184.0	179.0	173.9	161.8
80°	74.3	77.4	90.1	102.8	116.1	129.5	131.4	133.3	128.2	123.1	115.5
82.5°	51.4	53.3	57.8	62.2	73.0	83.8	86.3	88.8	86.3	83.8	75.5
85°	31.1	31.7	33.6	35.5	40.6	45.7	48.2	50.8	49.5	48.2	43.8
87.5°	14.0	14.0	14.6	15.2	16.5	17.8	20.9	24.1	22.2	20.3	18.4
90°	9.9	8.3	6.8	5.4	4.2	3.0	1.8	0.5	1.8	3.0	4.2
92.5°	21.4	20.7	20.0	19.2	18.5	17.8	17.1	16.3	17.1	17.8	18.5
95°	38.3	37.4	36.4	35.5	34.6	33.8	33.0	32.1	33.0	33.8	34.6
97.5°	57.3	56.6	55.9	55.2	54.6	54.0	53.4	52.8	53.4	54.0	54.6
100°	78.8	78.2	77.6	76.9	76.2	75.5	74.7	74.0	74.7	75.5	76.2
102.5°	102.2	101.4	100.5	99.9	99.6	99.2	98.9	98.5	98.9	99.2	99.6
105°	126.2	125.2	124.1	123.4	123.2	122.9	122.7	122.4	122.7	122.9	123.2
107.5°	152.5	152.0	151.5	151.2	151.1	151.0	150.9	150.7	150.9	151.0	151.1
110°	178.5	178.3	178.1	177.8	177.6	177.3	177.1	176.8	177.1	177.3	177.6



TEST NUMBER: P831871

CATALOG NUMBER: S123RDIP-S1000D585U950-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	204.6	204.6	204.6	204.5	204.4	204.3	204.2	204.1	204.2	204.3	204.4
115°	232.3	232.5	232.8	232.7	232.4	232.0	231.6	231.3	231.6	232.0	232.4
117.5°	259.0	259.2	259.4	259.5	259.4	259.3	259.1	259.0	259.1	259.3	259.4
120°	286.3	286.9	287.6	287.5	286.8	286.0	285.3	284.6	285.3	286.0	286.8
122.5°	312.8	313.1	313.3	313.2	312.7	312.2	311.7	311.3	311.7	312.2	312.7
125°	339.5	339.7	340.0	339.9	339.6	339.2	338.8	338.5	338.8	339.2	339.6
127.5°	366.2	366.4	366.6	366.4	365.7	364.9	364.2	363.5	364.2	364.9	365.7
130°	392.0	392.3	392.7	392.4	391.4	390.5	389.5	388.5	389.5	390.5	391.4
132.5°	417.3	417.5	417.8	417.4	416.5	415.5	414.5	413.6	414.5	415.5	416.5
135°	442.1	442.2	442.3	442.0	441.3	440.6	439.9	439.1	439.9	440.6	441.3
137.5°	466.2	465.8	465.4	464.9	464.3	463.7	463.1	462.5	463.1	463.7	464.3
140°	490.0	489.9	489.8	489.4	488.8	488.2	487.6	487.0	487.6	488.2	488.8
142.5°	512.7	512.4	512.2	511.7	511.1	510.5	509.9	509.3	509.9	510.5	511.1
145°	534.7	534.4	534.0	533.7	533.5	533.2	533.0	532.7	533.0	533.2	533.5
147.5°	555.9	555.6	555.2	554.8	554.3	553.8	553.3	552.9	553.3	553.8	554.3
150°	575.8	575.5	575.3	575.0	574.8	574.6	574.3	574.1	574.3	574.6	574.8
152.5°	593.4	593.3	593.2	592.9	592.6	592.2	591.9	591.5	591.9	592.2	592.6
155°	610.3	610.2	610.1	610.0	610.0	610.0	610.0	610.0	610.0	610.0	610.0
157.5°	625.5	625.4	625.3	625.3	625.4	625.5	625.7	625.8	625.7	625.5	625.4
160°	639.4	639.4	639.4	639.5	639.7	640.0	640.2	640.5	640.2	640.0	639.7
162.5°	652.2	652.1	652.0	652.1	652.4	652.8	653.2	653.5	653.2	652.8	652.4
165°	662.8	662.8	662.8	663.0	663.3	663.7	664.0	664.4	664.0	663.7	663.3
167.5°	671.8	671.7	671.5	671.7	672.2	672.7	673.2	673.7	673.2	672.7	672.2
170°	679.1	679.1	679.1	679.3	679.8	680.3	680.8	681.3	680.8	680.3	679.8
172.5°	685.1	685.1	685.1	685.3	685.8	686.3	686.8	687.3	686.8	686.3	685.8
175°	688.9	688.9	688.9	689.1	689.6	690.1	690.6	691.1	690.6	690.1	689.6
177.5°	691.1	691.1	691.1	691.3	691.8	692.3	692.8	693.3	692.8	692.3	691.8
180°	692.7	692.7	692.7	692.7	692.7	692.7	692.7	692.7	692.7	692.7	692.7



TEST NUMBER: P831871

CATALOG NUMBER: S123RDIP-S1000D585U950-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	3095.7	3095.7	3095.7	3095.7	3095.7	3095.7	3095.7	3095.7	3095.7	3095.7	3095.7
2.5°	2996.7	2960.6	2924.4	2898.4	2872.4	2840.0	2807.6	2806.4	2805.1	2781.0	2756.9
5°	2819.0	2756.2	2693.4	2631.8	2570.3	2508.7	2447.2	2433.2	2419.2	2398.3	2377.3
7.5°	2661.7	2561.4	2461.1	2382.4	2303.7	2242.2	2180.6	2138.7	2096.8	2064.5	2032.1
10°	2492.8	2368.5	2244.1	2148.9	2053.7	1987.0	1920.4	1872.2	1823.9	1801.1	1778.2
12.5°	2317.7	2182.5	2047.3	1954.0	1860.7	1780.8	1700.8	1657.0	1613.2	1581.5	1549.8
15°	2156.5	2011.2	1865.8	1766.8	1667.8	1592.9	1518.0	1474.3	1430.5	1398.7	1367.0
17.5°	2000.4	1853.8	1707.2	1606.9	1506.6	1438.7	1370.8	1328.3	1285.8	1266.1	1246.4
20°	1858.2	1710.3	1562.5	1467.9	1373.4	1306.7	1240.1	1217.2	1194.4	1176.0	1157.6
22.5°	1717.3	1575.2	1433.0	1342.3	1251.5	1203.3	1155.0	1136.6	1118.2	1104.3	1090.3
25°	1599.3	1457.8	1316.2	1236.9	1157.6	1120.1	1082.7	1070.6	1058.6	1044.6	1030.6
27.5°	1480.0	1345.4	1210.9	1147.4	1084.0	1053.5	1023.0	1007.8	992.6	981.1	969.7
30°	1374.6	1250.2	1125.8	1073.2	1020.5	993.8	967.2	950.7	934.2	923.4	912.6
32.5°	1273.1	1162.7	1052.2	1007.2	962.1	936.1	910.1	894.2	878.3	865.6	852.9
35°	1179.2	1083.3	987.5	946.2	905.0	879.0	852.9	837.1	821.2	808.5	795.8
37.5°	1096.6	1009.7	922.8	884.0	845.3	822.5	799.6	783.1	766.6	753.3	740.0
40°	1019.2	942.4	865.6	828.2	790.8	766.0	741.3	726.7	712.1	700.0	687.9
42.5°	950.7	880.2	809.8	773.0	736.2	712.7	689.2	672.1	654.9	648.0	641.0
45°	878.3	816.1	753.9	718.4	682.9	658.1	633.4	618.8	604.2	597.8	591.5
47.5°	814.9	757.1	699.4	664.5	629.6	607.3	585.1	573.7	562.3	553.4	544.5
50°	752.7	696.8	641.0	607.3	573.7	554.7	535.6	521.7	507.7	501.4	495.0
52.5°	693.0	642.3	591.5	557.2	522.9	504.5	486.1	474.1	462.0	448.7	435.4
55°	625.8	581.3	536.9	506.4	476.0	456.9	437.9	423.9	410.0	396.0	382.1
57.5°	569.9	526.1	482.3	455.0	427.7	409.3	390.9	375.7	360.5	349.0	337.6
60°	509.0	470.9	432.8	406.2	379.5	361.7	344.0	329.4	314.8	309.1	303.4
62.5°	451.9	416.3	380.8	357.3	333.8	316.7	299.5	290.0	280.5	276.7	272.9
65°	393.5	363.0	332.5	311.0	289.4	274.8	260.2	255.8	251.3	248.1	245.0
67.5°	338.9	312.9	286.9	267.8	248.8	238.6	228.5	223.4	218.3	214.5	210.7
70°	289.4	266.5	243.7	227.2	210.7	201.2	191.7	187.2	182.8	175.8	168.8
72.5°	236.1	218.3	200.5	187.9	175.2	166.9	158.7	149.8	140.9	134.5	128.2
75°	195.5	177.7	159.9	147.9	135.8	126.3	116.8	113.6	110.4	108.5	106.6
77.5°	149.8	134.5	119.3	109.8	100.3	95.8	91.4	89.5	87.6	86.9	86.3
80°	107.9	95.2	82.5	77.4	72.3	71.1	69.8	68.5	67.3	66.6	66.0
82.5°	67.3	60.9	54.6	53.3	52.0	51.4	50.8	50.1	49.5	48.9	48.2
85°	39.3	36.8	34.3	33.6	33.0	32.4	31.7	31.7	31.7	31.7	31.7
87.5°	16.5	16.5	16.5	16.5	16.5	16.5	16.5	16.5	16.5	15.9	15.2
90°	5.4	6.8	8.3	9.9	11.5	13.1	13.5	14.0	14.5	15.0	15.4
92.5°	19.2	20.0	20.7	21.4	22.1	22.9	23.2	23.6	23.9	24.3	24.4
95°	35.5	36.4	37.4	38.3	39.3	40.3	40.8	41.2	41.7	42.2	42.4
97.5°	55.2	55.9	56.6	57.3	58.0	58.8	59.4	60.0	60.6	61.2	61.4
100°	76.9	77.6	78.2	78.8	79.4	80.0	80.4	80.7	81.1	81.4	81.7
102.5°	99.9	100.5	101.4	102.2	103.1	103.9	104.3	104.7	105.0	105.4	105.5
105°	123.4	124.1	125.2	126.2	127.3	128.4	128.4	128.4	128.4	128.4	128.5
107.5°	151.2	151.5	152.0	152.5	153.0	153.5	153.8	154.2	154.5	154.9	155.0
110°	177.8	178.1	178.3	178.5	178.8	179.0	179.5	180.0	180.5	181.0	181.1



TEST NUMBER: P831871

CATALOG NUMBER: S123RDIP-S1000D585U950-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	204.5	204.6	204.6	204.6	204.6	204.6	205.2	205.8	206.4	207.0	207.3
115°	232.7	232.8	232.5	232.3	232.1	231.8	231.9	232.1	232.2	232.3	232.3
117.5°	259.5	259.4	259.2	259.0	258.7	258.5	258.5	258.5	258.5	258.5	258.3
120°	287.5	287.6	286.9	286.3	285.7	285.1	285.0	284.9	284.8	284.7	284.5
122.5°	313.2	313.3	313.1	312.8	312.6	312.3	312.0	311.6	311.3	310.9	310.5
125°	339.9	340.0	339.7	339.5	339.2	339.0	338.5	338.0	337.6	337.1	336.6
127.5°	366.4	366.6	366.4	366.2	365.9	365.7	364.9	364.2	363.5	362.8	362.2
130°	392.4	392.7	392.3	392.0	391.6	391.2	390.8	390.3	389.8	389.3	388.6
132.5°	417.4	417.8	417.5	417.3	417.1	416.8	416.2	415.6	415.0	414.4	413.8
135°	442.0	442.3	442.2	442.1	442.0	441.9	441.4	440.9	440.4	439.9	439.6
137.5°	464.9	465.4	465.8	466.2	466.5	466.9	466.3	465.7	465.1	464.5	464.0
140°	489.4	489.8	489.9	490.0	490.2	490.3	490.2	490.0	489.9	489.8	489.3
142.5°	511.7	512.2	512.4	512.7	512.9	513.1	513.0	512.9	512.8	512.7	512.3
145°	533.7	534.0	534.4	534.7	535.1	535.4	535.3	535.2	535.1	535.0	534.7
147.5°	554.8	555.2	555.6	555.9	556.3	556.7	556.7	556.7	556.7	556.7	556.3
150°	575.0	575.3	575.5	575.8	576.0	576.3	576.3	576.3	576.3	576.3	575.9
152.5°	592.9	593.2	593.3	593.4	593.5	593.7	593.9	594.2	594.4	594.6	594.5
155°	610.0	610.1	610.2	610.3	610.4	610.5	611.0	611.5	612.0	612.5	612.3
157.5°	625.3	625.3	625.4	625.5	625.7	625.8	626.3	626.7	627.2	627.7	627.6
160°	639.5	639.4	639.4	639.4	639.4	639.4	640.0	640.6	641.2	641.8	641.9
162.5°	652.1	652.0	652.1	652.2	652.3	652.4	653.0	653.6	654.3	654.9	654.7
165°	663.0	662.8	662.8	662.8	662.8	662.8	663.5	664.2	665.0	665.7	665.6
167.5°	671.7	671.5	671.7	671.8	671.9	672.0	672.8	673.5	674.2	674.9	674.9
170°	679.3	679.1	679.1	679.1	679.1	679.1	679.9	680.8	681.6	682.5	682.5
172.5°	685.3	685.1	685.1	685.1	685.1	685.1	685.8	686.5	687.3	688.0	687.9
175°	689.1	688.9	688.9	688.9	688.9	688.9	689.6	690.3	691.1	691.8	691.7
177.5°	691.3	691.1	691.1	691.1	691.1	691.1	691.8	692.5	693.3	694.0	693.9
180°	692.7	692.7	692.7	692.7	692.7	692.7	692.7	692.7	692.7	692.7	692.7



TEST NUMBER: P831871

CATALOG NUMBER: S123RDIP-S1000D585U950-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	3095.7	3095.7	3095.7	3095.7
2.5°	2750.5	2744.2	2741.6	2739.1
5°	2357.7	2338.0	2333.6	2329.1
7.5°	2023.9	2015.6	1988.3	1961.0
10°	1752.9	1727.5	1716.1	1704.6
12.5°	1526.3	1502.8	1499.0	1495.2
15°	1350.5	1334.0	1328.3	1322.6
17.5°	1235.0	1223.6	1216.6	1209.6
20°	1149.3	1141.1	1136.0	1130.9
22.5°	1084.0	1077.6	1073.8	1070.0
25°	1021.1	1011.6	1008.4	1005.3
27.5°	961.5	953.2	950.0	946.9
30°	905.6	898.6	894.2	889.8
32.5°	844.7	836.4	833.9	831.4
35°	790.8	785.7	783.1	780.6
37.5°	733.6	727.3	723.5	719.7
40°	684.8	681.6	679.7	677.8
42.5°	635.3	629.6	628.9	628.3
45°	585.8	580.1	578.8	577.5
47.5°	539.4	534.4	533.7	533.1
50°	488.0	481.1	476.0	470.9
52.5°	429.0	422.7	418.2	413.8
55°	375.1	368.1	364.3	360.5
57.5°	334.5	331.3	329.4	327.5
60°	301.5	299.5	298.3	297.0
62.5°	271.0	269.1	269.1	269.1
65°	243.1	241.2	239.3	237.4
67.5°	206.9	203.1	202.4	201.8
70°	163.1	157.4	156.8	156.1
72.5°	127.6	126.9	125.7	124.4
75°	105.3	104.1	104.1	104.1
77.5°	85.0	83.8	83.8	83.8
80°	65.4	64.7	65.4	66.0
82.5°	48.2	48.2	47.6	47.0
85°	31.1	30.5	30.5	30.5
87.5°	15.2	15.2	15.2	15.2
90°	15.6	15.8	16.1	16.3
92.5°	24.1	23.9	23.6	23.4
95°	42.4	42.4	42.4	42.4
97.5°	61.3	61.2	61.1	60.9
100°	82.0	82.2	82.5	82.7
102.5°	105.4	105.3	105.1	105.0
105°	128.8	129.0	129.3	129.5
107.5°	154.9	154.8	154.7	154.5
110°	180.8	180.6	180.4	180.1



TEST NUMBER: P831871

CATALOG NUMBER: S123RDIP-S1000D585U950-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
112.5°	207.3	207.3	207.3	207.3
115°	232.2	232.1	231.9	231.8
117.5°	257.9	257.6	257.2	256.8
120°	284.2	284.0	283.7	283.5
122.5°	310.2	309.8	309.4	309.1
125°	336.1	335.6	335.1	334.7
127.5°	361.7	361.2	360.7	360.2
130°	387.8	387.0	386.1	385.3
132.5°	413.2	412.6	412.0	411.4
135°	439.3	439.1	438.8	438.6
137.5°	463.6	463.3	462.9	462.5
140°	488.5	487.6	486.8	485.9
142.5°	511.7	511.1	510.5	509.9
145°	534.2	533.7	533.2	532.7
147.5°	555.6	554.9	554.1	553.4
150°	575.2	574.4	573.7	573.0
152.5°	593.9	593.2	592.6	592.0
155°	611.4	610.6	609.8	608.9
157.5°	626.9	626.1	625.4	624.7
160°	641.4	640.9	640.4	639.9
162.5°	653.9	653.0	652.2	651.4
165°	664.8	663.9	663.1	662.2
167.5°	674.2	673.5	672.8	672.0
170°	681.6	680.8	679.9	679.1
172.5°	687.1	686.2	685.4	684.5
175°	690.9	690.0	689.2	688.4
177.5°	693.1	692.2	691.4	690.5
180°	692.7	692.7	692.7	692.7



TEST NUMBER: P831871

CATALOG NUMBER: S123RDIP-S1000D585U950-4F0-1E-UDD-G1

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.49	15.46	15.29	16.27	17.26	19.15	20.12	19.95	20.93	21.92
	3H	15.72	16.59	16.53	17.41	18.43	20.66	21.53	21.47	22.35	23.37
	4H	16.11	16.93	16.94	17.75	18.79	21.16	21.98	21.99	22.80	23.84
	6H	16.40	17.15	17.24	17.98	19.03	21.48	22.23	22.32	23.06	24.11
	8H	16.49	17.20	17.34	18.06	19.10	21.56	22.27	22.41	23.13	24.17
	12H	16.54	17.22	17.40	18.07	19.14	21.60	22.28	22.45	23.12	24.19
4H	2H	15.23	16.05	16.06	16.87	17.91	19.17	19.98	20.00	20.81	21.84
	3H	16.61	17.29	17.45	18.15	19.20	20.84	21.51	21.68	22.37	23.42
	4H	17.07	17.69	17.93	18.54	19.62	21.45	22.06	22.30	22.92	24.00
	6H	17.45	17.97	18.32	18.86	19.94	21.89	22.42	22.76	23.30	24.38
	8H	17.57	18.07	18.45	18.94	20.04	22.03	22.52	22.90	23.40	24.49
	12H	17.66	18.10	18.55	19.00	20.09	22.09	22.54	22.99	23.43	24.53
8H	4H	17.39	17.89	18.27	18.77	19.86	21.42	21.92	22.30	22.80	23.89
	6H	17.86	18.27	18.76	19.19	20.28	21.92	22.33	22.83	23.25	24.34
	8H	18.06	18.42	18.97	19.33	20.44	22.11	22.47	23.02	23.38	24.49
	12H	18.20	18.52	19.11	19.42	20.59	22.23	22.55	23.15	23.45	24.62
12H	4H	17.41	17.85	18.30	18.75	19.85	21.38	21.82	22.27	22.72	23.82
	6H	17.92	18.28	18.83	19.20	20.30	21.90	22.26	22.81	23.17	24.28
	8H	18.15	18.46	19.06	19.37	20.53	22.10	22.42	23.01	23.32	24.48