

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P332694

Luminaire Tested: **S124DIP-S1195D810U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332694
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIP-S1195D810U835-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 810 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8350.6 lumens
Efficiency: N/A
Efficacy: 137.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 60.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332694

CATALOG NUMBER: S124DIP-S1195D810U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332694

CATALOG NUMBER: S124DIP-S1195D810U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	66	66	66	61
1	100	96	92	88	94	90	86	83	79	76	74	68	66	65	59	57	56	52
2	91	84	77	72	85	79	73	68	69	65	61	60	57	54	52	49	47	43
3	83	74	66	60	78	69	62	57	61	56	51	53	49	46	46	43	40	37
4	76	65	57	51	71	61	54	48	54	48	44	47	43	39	41	37	35	31
5	70	58	50	44	65	55	47	42	48	42	38	42	38	34	37	33	30	27
6	65	52	44	38	60	49	42	36	44	38	33	38	34	30	33	30	27	24
7	60	47	39	33	56	45	37	32	40	34	29	35	30	26	31	27	24	21
8	56	43	35	30	52	41	33	28	36	30	26	32	27	24	28	24	21	19
9	52	39	32	26	48	37	30	25	33	27	23	29	25	21	26	22	19	17
10	48	36	29	24	45	34	27	23	31	25	21	27	23	19	24	20	17	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16088	16088	16088
5°	16136	15943	16058
10°	16035	15813	15891
15°	15841	15588	15628
20°	15584	15309	15323
25°	15291	14991	14949
30°	14930	14618	14483
35°	14557	14226	14038
40°	14169	13782	13529
45°	13764	13345	13089
50°	13317	12955	12554
55°	12833	12451	12047
60°	12350	11885	11525
65°	11805	11347	10890
70°	11195	10629	10213
75°	10259	9763	9513
80°	9131	8759	8536
85°	7984	7688	7540



TEST NUMBER: P332694

CATALOG NUMBER: S124DIP-S1195D810U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	187.7	2.2
10°-20°	528.8	6.3
20°-30°	778.3	9.3
30°-40°	904.8	10.8
40°-50°	904.8	10.8
50°-60°	791.5	9.5
60°-70°	587.8	7.0
70°-80°	333.9	4.0
80°-90°	99.4	1.2
90°-100°	35.8	0.4
100°-110°	228.0	2.7
110°-120°	436.1	5.2
120°-130°	553.6	6.6
130°-140°	592.3	7.1
140°-150°	553.9	6.6
150°-160°	446.7	5.3
160°-170°	288.1	3.4
170°-180°	99.3	1.2
0°-30°	1494.7	17.9
0°-40°	2399.5	28.7
0°-60°	4095.8	49.0
0°-90°	5116.9	61.3
90°-120°	699.8	8.4
90°-150°	2399.6	28.7
90°-180°	3234.0	38.7
0°-180°	8350.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1993	1993	1993	1993	1993	
5°	1991	1984	1967	1984	1982	189
15°	1895	1888	1865	1874	1870	534
25°	1717	1705	1683	1684	1678	789
35°	1477	1465	1444	1433	1424	923
45°	1206	1194	1169	1152	1146	929
55°	912	906	885	866	856	816
65°	618	610	594	578	570	612
75°	329	321	313	307	305	350
85°	86	86	83	83	81	95
90°	2	11	17	22	24	7
95°	43	18	17	22	23	55
105°	235	240	244	249	223	246
115°	439	442	441	442	443	432
125°	618	621	619	622	622	551
135°	766	766	769	770	772	590
145°	884	886	886	887	888	552
155°	969	969	967	970	968	446
165°	1022	1018	1018	1024	1017	289
175°	1045	1041	1042	1048	1039	100
180°	1045	1045	1045	1045	1045	



TEST NUMBER: P332694

CATALOG NUMBER: S124DIP-S1195D810U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8
2.5°	1997.9	1997.1	1996.2	1995.4	1994.5	1992.5	1989.4	1986.3	1983.2	1980.1	1982.9
5°	1991.2	1989.8	1988.4	1987.0	1985.6	1982.9	1979.0	1975.1	1971.2	1967.3	1971.2
7.5°	1972.7	1971.3	1969.9	1968.4	1967.0	1964.2	1959.8	1955.5	1951.2	1946.8	1950.0
10°	1956.1	1954.7	1953.3	1951.8	1950.4	1947.4	1942.8	1938.2	1933.6	1929.0	1931.8
12.5°	1934.4	1933.0	1931.5	1930.1	1928.7	1925.5	1920.7	1915.8	1910.9	1906.0	1909.1
15°	1895.4	1894.0	1892.6	1891.2	1889.7	1886.4	1881.0	1875.7	1870.4	1865.1	1867.2
17.5°	1848.5	1846.7	1844.9	1843.2	1841.4	1838.0	1832.9	1827.9	1822.9	1817.8	1819.2
20°	1814.0	1812.2	1810.4	1808.7	1806.9	1803.3	1798.0	1792.7	1787.4	1782.0	1783.1
22.5°	1776.9	1774.6	1772.3	1769.9	1767.6	1763.7	1758.4	1753.1	1747.8	1742.4	1744.4
25°	1716.6	1714.1	1711.6	1709.1	1706.6	1702.9	1697.9	1693.0	1688.0	1683.0	1683.4
27.5°	1647.6	1645.0	1642.5	1639.9	1637.4	1633.8	1629.2	1624.6	1620.0	1615.3	1614.5
30°	1601.6	1598.8	1595.9	1593.1	1590.3	1586.5	1581.9	1577.3	1572.7	1568.1	1566.7
32.5°	1553.1	1550.5	1548.0	1545.4	1542.8	1539.1	1534.2	1529.3	1524.4	1519.5	1517.8
35°	1477.1	1474.6	1472.1	1469.6	1467.1	1463.4	1458.4	1453.5	1448.5	1443.5	1441.0
37.5°	1396.9	1394.6	1392.4	1390.1	1387.8	1384.0	1378.7	1373.4	1368.0	1362.7	1360.0
40°	1344.5	1341.7	1338.8	1336.0	1333.2	1329.1	1323.8	1318.4	1313.1	1307.8	1304.2
42.5°	1288.3	1286.6	1284.9	1283.2	1281.5	1277.7	1271.8	1265.9	1260.0	1254.1	1250.0
45°	1205.6	1203.1	1200.6	1198.1	1195.7	1191.6	1185.9	1180.2	1174.5	1168.9	1165.0
47.5°	1119.0	1117.3	1115.6	1113.9	1112.2	1108.8	1103.5	1098.3	1093.0	1087.8	1083.4
50°	1060.3	1058.9	1057.4	1056.0	1054.6	1051.4	1046.4	1041.5	1036.5	1031.5	1026.6
52.5°	1002.8	1001.1	999.4	997.7	996.0	992.5	987.3	982.0	976.8	971.5	967.1
55°	911.8	910.7	909.7	908.6	907.5	904.5	899.5	894.6	889.6	884.6	880.4
57.5°	824.9	823.7	822.5	821.3	820.1	817.0	812.1	807.2	802.3	797.4	793.4
60°	764.9	763.1	761.3	759.6	757.8	754.6	750.0	745.4	740.7	736.1	732.9
62.5°	706.1	704.6	703.1	701.6	700.2	697.0	692.1	687.2	682.3	677.4	674.5
65°	618.0	616.2	614.4	612.6	610.9	608.2	604.7	601.1	597.6	594.0	590.5
67.5°	529.2	527.6	525.9	524.3	522.7	520.1	516.7	513.3	509.9	506.5	503.1
70°	474.3	471.8	469.3	466.8	464.3	461.7	458.8	456.0	453.1	450.3	447.5
72.5°	415.5	413.0	410.5	408.0	405.6	403.2	400.9	398.6	396.4	394.1	391.8
75°	328.9	327.2	325.4	323.6	321.8	320.1	318.3	316.5	314.8	313.0	311.6
77.5°	246.2	245.4	244.7	243.9	243.1	241.9	240.4	238.8	237.3	235.7	235.3
80°	196.4	195.3	194.3	193.2	192.2	191.3	190.6	189.8	189.1	188.4	187.7
82.5°	147.9	147.4	146.9	146.4	145.9	145.6	145.4	145.3	145.1	145.0	144.6
85°	86.2	86.2	86.2	86.2	86.2	85.9	85.2	84.5	83.7	83.0	83.0
87.5°	33.7	33.8	33.9	34.0	34.1	34.1	34.1	34.1	34.1	34.1	34.3
90°	2.3	4.3	6.2	8.1	10.0	11.6	13.0	14.4	15.8	17.2	18.2
92.5°	9.9	10.0	10.1	10.2	10.3	11.0	12.4	13.8	15.2	16.6	17.6
95°	43.0	37.1	31.2	25.3	19.4	16.5	16.7	16.9	17.0	17.2	18.2
97.5°	91.3	95.0	98.7	102.4	106.1	98.2	78.8	59.4	40.0	20.6	20.7
100°	128.2	131.4	134.5	137.6	140.7	130.3	106.3	82.4	58.4	34.4	31.4
102.5°	169.5	171.8	174.1	176.4	178.7	178.3	175.1	172.0	168.9	165.8	133.9
105°	235.3	236.4	237.4	238.5	239.5	240.5	241.3	242.2	243.1	243.9	245.5
107.5°	296.5	297.0	297.5	298.1	298.6	299.4	300.6	301.8	303.0	304.2	304.9
110°	337.8	338.3	338.8	339.3	339.9	340.6	341.7	342.7	343.8	344.8	345.2



TEST NUMBER: P332694

CATALOG NUMBER: S124DIP-S1195D810U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	377.8	378.7	379.7	380.6	381.6	382.3	382.8	383.2	383.7	384.2	384.2
115°	439.4	439.9	440.5	441.0	441.5	441.7	441.5	441.3	441.2	441.0	441.3
117.5°	494.9	495.6	496.3	497.0	497.7	498.3	498.6	499.0	499.4	499.8	499.7
120°	532.5	533.2	533.9	534.6	535.2	535.5	535.3	535.2	535.0	534.8	535.2
122.5°	567.5	567.9	568.3	568.7	569.2	569.5	569.7	570.0	570.2	570.5	570.7
125°	617.7	618.4	619.1	619.8	620.5	620.6	620.3	620.0	619.6	619.3	619.8
127.5°	665.2	665.4	665.6	665.8	665.9	666.4	667.2	668.0	668.8	669.6	669.5
130°	695.9	696.1	696.2	696.4	696.6	696.9	697.4	698.0	698.5	699.0	699.2
132.5°	724.0	724.3	724.7	725.0	725.3	725.8	726.4	727.1	727.7	728.4	728.6
135°	766.3	766.1	765.9	765.7	765.6	765.8	766.5	767.2	767.9	768.6	768.9
137.5°	803.6	803.7	803.8	803.8	803.9	804.3	805.1	805.9	806.6	807.4	807.8
140°	828.0	828.4	828.7	829.1	829.4	829.8	830.1	830.5	830.8	831.1	831.7
142.5°	849.9	850.5	851.2	851.8	852.4	852.8	853.0	853.3	853.5	853.7	854.1
145°	883.5	884.1	884.6	885.1	885.6	885.9	885.9	885.9	885.9	885.9	886.1
147.5°	910.3	911.3	912.2	913.2	914.2	914.6	914.4	914.2	914.0	913.9	914.0
150°	929.7	930.4	931.1	931.8	932.4	932.7	932.5	932.4	932.2	932.0	932.0
152.5°	945.9	946.5	947.0	947.6	948.2	948.3	948.0	947.7	947.3	947.0	947.3
155°	968.8	968.9	969.1	969.3	969.5	969.3	968.8	968.2	967.7	967.2	967.9
157.5°	988.0	987.9	987.8	987.7	987.6	987.2	986.6	986.1	985.5	984.9	985.8
160°	999.3	998.7	998.2	997.7	997.2	996.8	996.7	996.5	996.3	996.1	997.2
162.5°	1009.3	1008.6	1007.9	1007.3	1006.6	1006.2	1006.0	1005.9	1005.7	1005.5	1006.6
165°	1021.9	1021.1	1020.2	1019.3	1018.5	1018.0	1018.0	1018.0	1018.0	1018.0	1019.4
167.5°	1031.9	1031.0	1030.1	1029.2	1028.3	1027.8	1027.7	1027.6	1027.5	1027.4	1028.9
170°	1037.6	1036.5	1035.5	1034.4	1033.4	1033.0	1033.1	1033.3	1033.5	1033.7	1035.0
172.5°	1041.3	1040.3	1039.2	1038.2	1037.2	1036.7	1036.9	1037.1	1037.2	1037.4	1038.8
175°	1045.4	1044.3	1043.3	1042.3	1041.2	1040.8	1041.0	1041.1	1041.3	1041.5	1043.0
177.5°	1047.3	1046.3	1045.3	1044.3	1043.4	1043.0	1043.3	1043.6	1043.9	1044.1	1045.2
180°	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4



TEST NUMBER: P332694

CATALOG NUMBER: S124DIP-S1195D810U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8
2.5°	1985.7	1988.6	1991.4	1992.7	1992.4	1992.1	1991.8	1991.5
5°	1975.1	1979.0	1982.9	1984.5	1983.8	1983.1	1982.4	1981.6
7.5°	1953.1	1956.2	1959.3	1960.7	1960.3	1959.8	1959.4	1959.0
10°	1934.6	1937.5	1940.3	1941.4	1940.7	1940.0	1939.2	1938.5
12.5°	1912.2	1915.3	1918.5	1919.5	1918.5	1917.5	1916.5	1915.5
15°	1869.3	1871.5	1873.6	1874.1	1873.1	1872.0	1870.9	1869.9
17.5°	1820.5	1821.9	1823.2	1823.5	1822.8	1822.1	1821.4	1820.7
20°	1784.2	1785.2	1786.3	1786.5	1785.8	1785.1	1784.4	1783.6
22.5°	1746.3	1748.2	1750.1	1750.4	1749.2	1747.9	1746.6	1745.3
25°	1683.8	1684.1	1684.5	1683.9	1682.5	1681.1	1679.7	1678.3
27.5°	1613.6	1612.8	1611.9	1610.6	1608.8	1607.1	1605.3	1603.5
30°	1565.2	1563.8	1562.4	1560.8	1559.0	1557.3	1555.5	1553.7
32.5°	1516.1	1514.4	1512.7	1511.0	1509.2	1507.4	1505.7	1503.9
35°	1438.6	1436.1	1433.6	1431.5	1429.7	1427.9	1426.1	1424.4
37.5°	1357.3	1354.6	1351.9	1349.4	1347.1	1344.7	1342.4	1340.0
40°	1300.7	1297.1	1293.6	1290.9	1289.2	1287.4	1285.6	1283.8
42.5°	1245.9	1241.8	1237.7	1235.0	1233.8	1232.6	1231.4	1230.2
45°	1161.1	1157.2	1153.3	1150.8	1149.7	1148.6	1147.6	1146.5
47.5°	1079.0	1074.6	1070.2	1066.6	1063.9	1061.2	1058.5	1055.8
50°	1021.6	1016.6	1011.7	1008.1	1006.0	1003.9	1001.7	999.6
52.5°	962.7	958.3	953.9	950.4	947.7	945.0	942.3	939.6
55°	876.1	871.9	867.6	864.4	862.3	860.2	858.0	855.9
57.5°	789.4	785.3	781.3	778.2	776.2	774.1	772.0	770.0
60°	729.7	726.6	723.4	720.9	719.1	717.3	715.6	713.8
62.5°	671.5	668.6	665.7	663.4	661.6	659.8	658.1	656.3
65°	586.9	583.4	579.8	577.2	575.4	573.6	571.8	570.1
67.5°	499.7	496.3	492.9	490.9	490.4	489.9	489.4	488.9
70°	444.6	441.8	438.9	437.0	435.9	434.9	433.8	432.7
72.5°	389.6	387.3	385.0	383.3	382.3	381.2	380.1	379.1
75°	310.1	308.7	307.3	306.4	306.1	305.7	305.3	305.0
77.5°	234.8	234.4	234.0	233.3	232.4	231.5	230.5	229.6
80°	187.0	186.3	185.6	185.1	184.7	184.3	184.0	183.6
82.5°	144.1	143.7	143.3	142.9	142.5	142.2	141.8	141.5
85°	83.0	83.0	83.0	82.9	82.5	82.1	81.8	81.4
87.5°	34.5	34.7	34.9	35.1	35.1	35.2	35.3	35.4
90°	19.3	20.3	21.4	22.1	22.4	22.8	23.1	23.5
92.5°	18.7	19.7	20.7	21.3	21.4	21.4	21.5	21.6
95°	19.3	20.3	21.4	22.0	22.2	22.3	22.5	22.7
97.5°	20.9	21.0	21.1	21.2	21.4	21.5	21.7	21.9
100°	28.5	25.5	22.6	21.2	21.4	21.5	21.7	21.9
102.5°	102.0	70.2	38.3	22.4	22.4	22.4	22.5	22.5
105°	247.1	248.6	250.2	247.9	241.6	235.3	229.1	222.8
107.5°	305.7	306.4	307.2	307.9	308.6	309.2	309.9	310.6
110°	345.5	345.9	346.2	346.6	347.2	347.7	348.2	348.7



TEST NUMBER: P332694

CATALOG NUMBER: S124DIP-S1195D810U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	384.1	384.0	383.9	384.2	384.9	385.6	386.2	386.9
115°	441.7	442.0	442.4	442.6	442.6	442.6	442.6	442.6
117.5°	499.6	499.6	499.5	499.4	499.4	499.3	499.2	499.2
120°	535.5	535.9	536.2	536.2	535.9	535.5	535.2	534.8
122.5°	570.9	571.1	571.3	571.2	570.9	570.5	570.2	569.8
125°	620.3	620.8	621.3	621.7	621.9	622.0	622.2	622.4
127.5°	669.4	669.3	669.2	669.1	668.9	668.8	668.7	668.5
130°	699.4	699.5	699.7	699.8	699.8	699.8	699.8	699.8
132.5°	728.8	728.9	729.1	729.1	729.0	728.8	728.7	728.6
135°	769.3	769.6	770.0	770.3	770.7	771.0	771.4	771.7
137.5°	808.1	808.5	808.9	809.0	808.9	808.8	808.7	808.6
140°	832.2	832.7	833.2	833.6	833.8	833.9	834.1	834.3
142.5°	854.4	854.8	855.2	855.4	855.4	855.5	855.5	855.5
145°	886.2	886.4	886.6	886.8	887.2	887.5	887.9	888.2
147.5°	914.2	914.3	914.4	914.6	914.8	914.9	915.1	915.3
150°	932.0	932.0	932.0	932.1	932.3	932.4	932.6	932.8
152.5°	947.6	947.9	948.1	948.2	948.1	948.0	947.9	947.8
155°	968.6	969.3	970.0	970.1	969.5	969.0	968.5	968.0
157.5°	986.7	987.6	988.5	988.5	987.6	986.7	985.8	984.9
160°	998.2	999.3	1000.3	1000.3	999.3	998.2	997.2	996.1
162.5°	1007.6	1008.6	1009.7	1009.6	1008.4	1007.2	1006.1	1004.9
165°	1020.8	1022.2	1023.6	1023.5	1021.9	1020.4	1018.8	1017.2
167.5°	1030.5	1032.0	1033.5	1033.4	1031.7	1029.9	1028.2	1026.5
170°	1036.4	1037.8	1039.2	1039.0	1037.3	1035.6	1033.8	1032.1
172.5°	1040.2	1041.6	1043.0	1042.7	1040.9	1039.0	1037.1	1035.2
175°	1044.6	1046.2	1047.7	1047.5	1045.4	1043.3	1041.2	1039.1
177.5°	1046.4	1047.5	1048.6	1048.3	1046.6	1045.0	1043.3	1041.6
180°	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4

(END OF REPORT)