

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P832115

Luminaire Tested: S123RDIP-S340D365U950-4F0-1E-UDD-G4

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P832115
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-2, G3-1807-864-17)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-S340D365U950-4F0-1E-UDD-G4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, GRAZE OPTIC
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2658.8 lumens
Efficiency: N/A
Efficacy: 118.7 lumens/watt
Spacing Criteria (0/90/45): 0.55 / 1.17 / 0.8
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 22.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P832115

CATALOG NUMBER: S123RDIP-S340D365U950-4F0-1E-UDD-G4

Luminous Intensity Polar Plot



TEST NUMBER: P832115

CATALOG NUMBER: S123RDIP-S340D365U950-4F0-1E-UDD-G4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	
RCR																					
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53	53	53	
1	99	95	92	88	92	88	85	83	76	73	71	64	62	61	53	52	51	46	46	46	
2	91	84	78	74	84	78	73	69	67	64	61	57	55	52	48	46	45	40	40	40	
3	84	75	68	63	77	70	64	59	60	56	52	52	48	45	43	41	39	35	35	35	
4	77	67	60	54	71	63	56	51	54	49	45	47	43	40	39	37	35	31	31	31	
5	71	60	53	47	66	56	50	45	49	44	40	42	38	35	36	33	31	28	28	28	
6	66	55	47	41	61	51	44	39	45	39	35	39	35	32	33	30	28	25	25	25	
7	61	50	42	37	57	47	40	35	41	36	32	36	32	28	31	28	25	23	23	23	
8	57	46	38	33	53	43	36	32	38	32	29	33	29	26	29	25	23	21	21	21	
9	54	42	35	30	50	40	33	29	35	30	26	31	27	24	27	23	21	19	19	19	
10	50	39	32	27	47	37	30	26	33	27	24	29	25	22	25	22	20	18	18	18	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	11408	11408	11408	11408	11408
5°	13545	13113	11479	9280	8616
10°	12272	13319	11423	7436	6379
15°	8450	11420	11302	6077	5046
20°	5879	8793	11074	5125	4435
25°	4480	6701	10745	4555	4087
30°	3899	5358	10332	4228	3786
35°	3581	4519	9746	3954	3511
40°	3267	4036	8982	3684	3260
45°	2950	3691	8156	3430	3009
50°	2678	3406	7182	3180	2699
55°	2423	3126	6247	2935	2316
60°	2170	2844	5425	2665	2189
65°	2004	2524	4671	2397	2071
70°	1627	2181	4076	2168	1681
75°	1426	1734	3452	1797	1481
80°	1296	1469	2827	1506	1401
85°	1186	1284	2149	1371	1284

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 8605 cd/sqm



TEST NUMBER: P832115

CATALOG NUMBER: S123RDIP-S340D365U950-4F0-1E-UDD-G4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.6	3.6
10°-20°	223.5	8.4
20°-30°	256.5	9.6
30°-40°	252.8	9.5
40°-50°	222.9	8.4
50°-60°	171.5	6.5
60°-70°	112.8	4.2
70°-80°	54.8	2.1
80°-90°	14.7	0.6
90°-100°	90.4	3.4
100°-110°	264.6	10.0
110°-120°	258.4	9.7
120°-130°	205.8	7.7
130°-140°	162.3	6.1
140°-150°	121.1	4.6
150°-160°	84.4	3.2
160°-170°	49.6	1.9
170°-180°	16.1	0.6
0°-30°	576.6	21.7
0°-40°	829.4	31.2
0°-60°	1223.8	46.0
0°-90°	1406.1	52.9
90°-120°	613.3	23.1
90°-150°	1102.5	41.5
90°-180°	1253.0	47.1
0°-180°	2658.8	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1060	1060	1060	1060	1060	
5°	1254	1214	1062	859	797	115
15°	758	1025	1014	545	453	214
25°	377	564	905	384	344	178
35°	272	344	742	301	267	170
45°	194	242	536	225	198	150
55°	129	167	333	156	123	116
65°	79	99	183	94	81	77
75°	34	42	83	43	36	37
85°	10	10	17	11	10	10
90°	10	8	1	8	10	6
95°	39	200	12	200	39	64
105°	429	271	39	271	429	428
115°	522	207	69	207	522	509
125°	411	194	96	194	411	372
135°	333	191	113	191	333	259
145°	261	188	128	188	261	165
155°	216	182	146	182	216	101
165°	188	175	160	175	188	54
175°	170	168	166	168	170	16
180°	166	166	166	166	166	

TEST NUMBER: P832115

CATALOG NUMBER: S123RDIP-S340D365U950-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8
2.5°	1174.5	1170.8	1167.2	1166.1	1165.0	1161.5	1158.0	1150.2	1142.4	1134.3	1126.3
5°	1253.6	1254.1	1254.5	1253.4	1252.3	1247.8	1243.2	1233.6	1224.1	1213.6	1203.2
7.5°	1229.3	1236.2	1243.2	1244.5	1245.8	1249.3	1252.8	1250.6	1248.4	1244.5	1240.6
10°	1122.8	1122.4	1122.0	1129.8	1137.6	1160.9	1184.1	1196.1	1208.0	1218.6	1229.3
12.5°	949.0	949.7	950.3	976.0	1001.6	1023.5	1045.5	1075.9	1106.3	1139.1	1171.9
15°	758.3	768.9	779.6	802.4	825.2	858.2	891.2	932.1	972.9	1024.8	1076.8
17.5°	622.7	627.2	631.8	653.8	675.7	707.0	738.3	784.5	830.8	897.7	964.7
20°	513.2	517.3	521.4	537.3	553.2	583.1	613.1	657.2	701.3	767.6	833.9
22.5°	428.4	436.5	444.5	455.2	465.8	487.5	509.3	554.2	599.2	659.6	720.0
25°	377.2	380.9	384.6	393.7	402.8	423.7	444.5	474.3	504.1	564.2	624.4
27.5°	342.4	343.5	344.6	351.3	358.1	371.5	385.0	412.6	440.2	489.7	539.3
30°	313.7	315.7	317.6	322.9	328.1	337.8	347.6	367.2	386.7	431.1	475.4
32.5°	291.6	292.7	293.7	298.1	302.4	309.6	316.8	332.2	347.6	381.5	415.4
35°	272.5	272.7	272.9	276.1	279.4	286.4	293.3	306.1	318.9	343.9	368.9
37.5°	250.7	252.2	253.8	256.2	258.5	264.6	270.7	281.1	291.6	312.2	332.9
40°	232.5	233.8	235.1	237.9	240.7	245.5	250.3	259.9	269.4	287.2	305.0
42.5°	214.2	215.1	216.0	218.8	221.6	227.5	233.3	240.9	248.6	263.3	278.1
45°	193.8	196.0	198.1	201.2	204.2	209.2	214.2	222.0	229.9	242.5	255.1
47.5°	176.9	177.9	179.0	181.6	184.2	190.3	196.4	203.4	210.3	222.0	233.8
50°	159.9	160.3	160.8	163.2	165.6	171.0	176.4	184.5	192.5	203.4	214.2
52.5°	143.8	144.9	146.0	148.4	150.8	154.5	158.2	166.4	174.7	185.3	196.0
55°	129.1	129.7	130.4	132.1	133.8	138.2	142.5	149.7	156.9	166.6	176.4
57.5°	115.2	116.0	116.9	118.2	119.5	123.4	127.3	133.6	139.9	149.7	159.5
60°	100.8	101.9	103.0	104.5	106.0	109.1	112.1	117.8	123.4	132.1	140.8
62.5°	90.4	90.6	90.8	92.1	93.4	95.6	97.8	102.3	106.9	115.6	124.3
65°	78.7	79.3	80.0	80.6	81.3	83.0	84.7	88.6	92.6	99.1	105.6
67.5°	66.5	67.1	67.8	68.9	70.0	71.5	73.0	75.6	78.2	84.3	90.4
70°	51.7	51.7	51.7	53.4	55.2	57.8	60.4	62.4	64.3	69.3	74.3
72.5°	42.1	42.4	42.6	42.8	43.0	44.5	46.1	49.3	52.6	55.6	58.7
75°	34.3	34.5	34.8	35.0	35.2	35.6	36.1	37.2	38.2	41.7	45.2
77.5°	27.4	27.6	27.8	28.0	28.2	28.7	29.1	29.5	30.0	31.3	32.6
80°	20.9	21.1	21.3	21.5	21.7	21.9	22.2	22.6	23.0	23.7	24.3
82.5°	15.2	15.2	15.2	15.2	15.2	15.6	16.1	16.1	16.1	16.5	16.9
85°	9.6	9.6	9.6	9.8	10.0	10.0	10.0	10.2	10.4	10.4	10.4
87.5°	4.3	4.1	3.9	4.1	4.3	4.3	4.3	4.6	4.8	4.8	4.8
90°	9.8	10.1	9.8	9.4	9.8	9.1	8.8	8.4	8.1	8.4	7.4
92.5°	17.9	18.5	18.2	19.6	20.2	22.6	26.0	33.4	46.9	62.7	69.4
95°	39.1	40.5	42.8	45.8	52.3	64.4	82.3	121.4	162.2	199.9	178.0
97.5°	80.2	83.9	92.0	104.8	127.4	165.9	210.4	278.8	317.9	307.5	229.6
100°	211.4	211.0	224.2	248.8	282.8	330.7	370.2	397.5	385.7	319.3	215.8
102.5°	334.8	344.5	355.0	373.2	397.8	423.8	442.6	436.9	389.0	297.3	195.5
105°	428.8	430.5	441.3	454.1	469.6	478.4	472.0	438.3	367.8	271.0	179.7
107.5°	490.2	493.9	498.3	504.3	506.4	497.3	471.0	418.0	337.5	247.8	168.2
110°	525.2	525.9	526.6	523.9	514.5	490.9	448.4	386.3	309.1	228.6	162.2

TEST NUMBER: P832115

CATALOG NUMBER: S123RDIP-S340D365U950-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	532.3	532.0	528.6	518.8	499.6	467.6	418.7	355.0	284.5	215.8	158.8
115°	521.5	519.8	513.1	498.3	473.0	436.2	386.7	328.0	265.7	207.3	158.4
117.5°	497.9	495.6	485.5	468.9	442.6	404.6	359.0	307.1	253.2	201.6	158.8
120°	466.9	464.9	456.8	437.9	411.3	377.2	336.8	291.3	243.7	197.9	160.1
122.5°	437.9	435.2	426.1	409.6	386.7	355.7	318.9	278.8	236.0	195.5	162.5
125°	411.3	408.9	400.5	385.7	364.1	337.1	304.8	268.0	229.6	193.5	164.9
127.5°	388.4	386.3	378.6	365.8	346.2	321.3	291.6	258.2	223.5	192.5	167.6
130°	369.5	366.8	359.7	347.6	329.7	306.8	279.5	249.1	218.8	191.5	170.2
132.5°	350.9	349.3	343.2	331.1	314.5	293.0	268.0	240.7	214.4	191.2	172.3
135°	333.4	331.1	325.0	314.9	298.4	279.1	257.2	233.3	210.7	190.8	174.3
137.5°	314.9	312.9	307.8	297.3	283.2	266.0	246.4	226.2	207.3	190.1	175.6
140°	295.3	295.7	290.3	280.8	268.0	253.5	237.3	220.1	204.3	189.8	177.0
142.5°	277.1	277.5	272.7	264.6	254.2	242.1	228.6	214.4	201.6	189.1	178.0
145°	260.6	259.9	257.2	250.1	241.7	231.9	221.2	210.0	199.2	188.5	178.3
147.5°	246.4	246.1	243.4	238.3	231.6	224.5	215.4	206.3	196.9	187.4	178.3
150°	234.3	234.3	232.3	228.6	223.5	217.1	210.0	202.3	194.5	186.1	178.3
152.5°	224.2	224.2	223.2	219.8	216.1	211.0	205.0	198.6	191.8	184.4	177.3
155°	216.1	215.8	215.1	212.4	209.4	205.3	200.3	194.9	189.1	182.4	176.7
157.5°	208.3	208.3	207.7	205.6	202.9	199.6	195.5	190.8	186.1	180.7	175.6
160°	200.9	201.3	201.3	199.2	196.9	194.5	191.2	187.4	183.1	178.7	175.0
162.5°	194.2	194.5	194.5	192.8	191.5	189.5	186.4	183.4	180.0	176.7	173.6
165°	188.5	188.5	188.8	187.4	186.1	184.4	182.0	180.0	177.3	174.6	172.3
167.5°	182.7	182.7	183.1	182.0	181.4	180.0	178.7	177.0	174.6	172.6	170.9
170°	177.7	177.7	178.0	177.3	177.0	176.3	175.0	174.0	172.3	170.6	169.6
172.5°	172.9	173.3	174.0	173.3	173.3	172.9	171.9	171.3	169.9	168.9	168.6
175°	169.6	169.9	170.2	169.9	169.9	169.9	169.2	168.9	168.2	167.6	167.6
177.5°	167.2	167.2	167.9	167.6	167.9	167.9	167.6	167.2	166.9	166.5	166.9
180°	166.5	166.5	166.5	166.5	166.5	166.5	166.5	166.5	166.5	166.5	166.5

TEST NUMBER: P832115

CATALOG NUMBER: S123RDIP-S340D365U950-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8
2.5°	1125.2	1124.1	1113.7	1103.3	1093.1	1082.9	1075.3	1067.6	1054.8	1042.0	1034.0
5°	1195.0	1186.7	1170.2	1153.7	1128.9	1104.1	1083.3	1062.4	1035.9	1009.4	987.3
7.5°	1233.9	1227.1	1207.1	1187.1	1154.3	1121.5	1088.9	1056.3	1017.2	978.1	944.7
10°	1234.9	1240.6	1224.1	1207.6	1170.6	1133.7	1089.4	1045.1	992.5	939.9	896.7
12.5°	1196.3	1220.6	1217.1	1213.6	1176.1	1138.5	1084.6	1030.7	966.2	901.7	847.6
15°	1123.9	1171.1	1185.0	1198.9	1167.8	1136.7	1075.5	1014.2	938.4	862.5	800.4
17.5°	1030.7	1096.8	1133.5	1170.2	1147.6	1125.0	1057.9	990.7	905.3	820.0	752.4
20°	920.3	1006.8	1064.4	1122.0	1113.7	1105.5	1036.1	966.8	874.7	782.6	709.4
22.5°	811.3	902.5	982.0	1061.6	1070.0	1078.5	1008.6	938.6	837.8	737.0	662.4
25°	717.2	810.0	904.7	999.4	1018.5	1037.7	971.2	904.7	800.2	695.7	621.6
27.5°	627.5	715.7	820.0	924.3	959.0	993.8	932.9	872.1	763.3	654.4	580.5
30°	554.2	633.1	739.6	846.0	894.5	942.9	887.1	831.3	723.3	615.3	542.9
32.5°	486.0	556.6	663.5	770.4	826.7	883.0	834.7	786.5	682.7	578.8	507.3
35°	432.1	495.4	595.1	694.8	757.8	820.8	781.3	741.7	640.3	538.8	471.3
37.5°	385.9	438.9	532.5	626.2	693.1	760.0	727.0	693.9	598.6	503.2	439.3
40°	347.6	390.2	477.3	564.5	630.1	695.7	667.4	639.2	553.8	468.4	408.7
42.5°	314.8	351.5	429.8	508.0	568.2	628.3	609.6	591.0	513.6	436.3	380.9
45°	285.9	316.8	385.6	454.5	509.9	565.3	550.6	535.8	469.1	402.4	351.5
47.5°	260.3	286.8	348.3	409.8	459.5	509.3	495.6	481.9	426.7	371.5	325.2
50°	236.8	259.4	310.7	362.0	406.7	451.5	440.2	428.9	383.3	337.6	297.7
52.5°	214.7	233.3	279.4	325.5	361.5	397.6	388.9	380.2	345.0	309.8	273.5
55°	193.6	210.7	249.6	288.5	319.4	350.2	341.5	332.9	305.5	278.1	246.2
57.5°	174.5	189.5	221.0	252.5	277.0	301.6	297.4	293.3	270.5	247.7	221.4
60°	154.3	167.7	194.9	222.0	241.8	261.6	256.8	252.0	235.7	219.4	196.8
62.5°	136.2	148.2	169.9	191.6	207.7	223.8	220.3	216.8	204.4	192.1	173.4
65°	117.3	129.1	146.7	164.3	176.9	189.5	186.4	183.4	174.0	164.7	149.7
67.5°	100.2	109.9	125.1	140.4	148.8	157.3	155.6	153.8	146.7	139.5	127.8
70°	82.8	91.3	103.9	116.5	122.3	128.2	128.8	129.5	123.0	116.5	107.8
72.5°	65.4	72.1	83.9	95.6	100.2	104.7	104.5	104.3	100.4	96.5	88.6
75°	50.2	55.2	64.3	73.4	77.3	81.3	82.1	83.0	79.3	75.6	71.3
77.5°	36.1	39.5	46.5	53.4	57.8	62.1	62.6	63.0	61.3	59.5	55.4
80°	25.4	26.5	30.9	35.2	39.8	44.3	45.0	45.6	43.9	42.1	39.5
82.5°	17.6	18.3	19.8	21.3	25.0	28.7	29.5	30.4	29.5	28.7	25.9
85°	10.6	10.9	11.5	12.2	13.9	15.6	16.5	17.4	16.9	16.5	15.0
87.5°	4.8	4.8	5.0	5.2	5.6	6.1	7.2	8.3	7.6	7.0	6.3
90°	6.4	5.4	4.4	3.7	3.0	2.0	1.3	0.7	1.3	2.0	3.0
92.5°	51.9	34.0	23.3	17.2	13.8	10.8	7.4	5.1	7.4	10.8	13.8
95°	122.7	72.5	43.8	30.7	21.9	16.2	12.5	11.5	12.5	16.2	21.9
97.5°	136.5	78.2	49.9	35.4	26.6	21.6	18.5	18.2	18.5	21.6	26.6
100°	127.1	77.2	53.6	40.5	32.4	27.6	25.3	24.9	25.3	27.6	32.4
102.5°	119.0	78.6	58.0	46.2	39.1	34.7	32.7	32.0	32.7	34.7	39.1
105°	116.0	81.2	63.0	52.6	46.2	42.1	40.1	39.1	40.1	42.1	46.2
107.5°	115.3	85.6	69.4	59.7	53.6	49.6	47.5	46.5	47.5	49.6	53.6
110°	117.0	91.4	76.2	66.8	61.0	57.3	55.6	54.6	55.6	57.3	61.0



TEST NUMBER: P832115

CATALOG NUMBER: S123RDIP-S340D365U950-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	120.4	97.1	83.3	74.2	68.4	64.7	63.0	62.0	63.0	64.7	68.4
115°	124.1	103.5	90.7	81.6	75.9	72.5	70.5	69.1	70.5	72.5	75.9
117.5°	128.8	110.2	97.4	89.0	82.6	79.6	77.9	76.2	77.9	79.6	82.6
120°	134.2	116.6	104.5	96.1	89.7	86.3	84.6	83.6	84.6	86.3	89.7
122.5°	139.2	123.4	111.6	102.5	96.4	92.7	91.0	90.0	91.0	92.7	96.4
125°	144.6	129.8	118.0	108.9	102.5	98.8	96.8	96.1	96.8	98.8	102.5
127.5°	149.0	135.5	124.1	115.0	107.9	104.2	101.8	100.8	101.8	104.2	107.9
130°	153.4	140.6	129.5	120.4	113.3	109.2	106.2	105.2	106.2	109.2	113.3
132.5°	157.4	145.0	134.2	125.4	118.3	113.3	109.9	108.6	109.9	113.3	118.3
135°	160.8	149.3	138.9	129.8	122.7	117.7	113.9	112.6	113.9	117.7	122.7
137.5°	163.5	152.4	142.3	133.8	126.8	121.4	117.7	116.3	117.7	121.4	126.8
140°	165.5	155.4	145.6	137.2	130.5	125.1	121.7	120.0	121.7	125.1	130.5
142.5°	167.6	157.8	148.3	140.6	133.8	129.1	125.4	124.1	125.4	129.1	133.8
145°	168.9	159.8	151.0	143.3	137.5	132.5	129.5	128.4	129.5	132.5	137.5
147.5°	169.9	161.5	153.4	146.6	140.9	136.5	133.5	132.8	133.5	136.5	140.9
150°	170.2	163.2	155.4	149.3	144.6	140.2	137.5	137.2	137.5	140.2	144.6
152.5°	170.9	164.2	157.8	152.0	148.0	144.3	141.6	141.6	141.6	144.3	148.0
155°	170.9	165.5	159.8	155.1	151.4	148.0	146.0	146.0	146.0	148.0	151.4
157.5°	171.3	166.2	161.5	157.8	154.4	151.4	149.7	149.3	149.7	151.4	154.4
160°	171.3	167.2	163.2	159.8	157.4	154.7	153.4	153.4	153.4	154.7	157.4
162.5°	170.9	167.6	164.2	161.5	159.5	157.4	156.4	156.4	156.4	157.4	159.5
165°	170.2	167.9	165.2	162.8	161.5	159.8	159.1	159.5	159.1	159.8	161.5
167.5°	169.9	167.9	165.9	164.2	163.2	161.8	161.5	161.8	161.5	161.8	163.2
170°	168.9	167.6	165.9	165.2	164.5	163.5	163.2	163.8	163.2	163.5	164.5
172.5°	168.6	167.6	166.2	165.9	165.5	164.9	164.9	165.2	164.9	164.9	165.5
175°	167.9	167.2	166.5	166.2	166.2	165.5	165.9	166.2	165.9	165.5	166.2
177.5°	167.6	166.9	166.5	166.5	166.5	166.2	166.5	166.9	166.5	166.2	166.5
180°	166.5	166.5	166.5	166.5	166.5	166.5	166.5	166.5	166.5	166.5	166.5



TEST NUMBER: P832115

CATALOG NUMBER: S123RDIP-S340D365U950-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8
2.5°	1025.9	1013.5	1001.2	992.3	983.3	972.3	961.2	960.8	960.3	952.1	943.8
5°	965.1	943.6	922.1	901.0	879.9	858.9	837.8	833.0	828.2	821.0	813.9
7.5°	911.2	876.9	842.6	815.6	788.7	767.6	746.5	732.2	717.8	706.8	695.7
10°	853.4	810.8	768.3	735.7	703.1	680.3	657.4	640.9	624.4	616.6	608.8
12.5°	793.5	747.2	700.9	669.0	637.0	609.6	582.3	567.3	552.3	541.4	530.6
15°	738.3	688.5	638.8	604.9	571.0	545.3	519.7	504.7	489.7	478.9	468.0
17.5°	684.8	634.6	584.4	550.1	515.8	492.5	469.3	454.7	440.2	433.4	426.7
20°	636.2	585.5	534.9	502.5	470.2	447.4	424.5	416.7	408.9	402.6	396.3
22.5°	587.9	539.3	490.6	459.5	428.4	411.9	395.4	389.1	382.8	378.0	373.3
25°	547.5	499.1	450.6	423.5	396.3	383.5	370.7	366.5	362.4	357.6	352.8
27.5°	506.7	460.6	414.5	392.8	371.1	360.7	350.2	345.0	339.8	335.9	332.0
30°	470.6	428.0	385.4	367.4	349.4	340.2	331.1	325.5	319.8	316.1	312.4
32.5°	435.8	398.0	360.2	344.8	329.4	320.5	311.6	306.1	300.7	296.4	292.0
35°	403.7	370.9	338.1	323.9	309.8	300.9	292.0	286.6	281.1	276.8	272.5
37.5°	375.4	345.7	315.9	302.7	289.4	281.6	273.8	268.1	262.5	257.9	253.3
40°	348.9	322.6	296.4	283.5	270.7	262.2	253.8	248.8	243.8	239.6	235.5
42.5°	325.5	301.3	277.2	264.6	252.0	244.0	236.0	230.1	224.2	221.8	219.4
45°	300.7	279.4	258.1	245.9	233.8	225.3	216.8	211.8	206.8	204.7	202.5
47.5°	279.0	259.2	239.4	227.5	215.5	207.9	200.3	196.4	192.5	189.5	186.4
50°	257.7	238.6	219.4	207.9	196.4	189.9	183.4	178.6	173.8	171.6	169.5
52.5°	237.3	219.9	202.5	190.8	179.0	172.7	166.4	162.3	158.2	153.6	149.0
55°	214.2	199.0	183.8	173.4	162.9	156.4	149.9	145.1	140.4	135.6	130.8
57.5°	195.1	180.1	165.1	155.8	146.4	140.1	133.8	128.6	123.4	119.5	115.6
60°	174.2	161.2	148.2	139.1	129.9	123.8	117.8	112.8	107.8	105.8	103.9
62.5°	154.7	142.5	130.4	122.3	114.3	108.4	102.5	99.3	96.0	94.7	93.4
65°	134.7	124.3	113.8	106.5	99.1	94.1	89.1	87.6	86.0	85.0	83.9
67.5°	116.0	107.1	98.2	91.7	85.2	81.7	78.2	76.5	74.7	73.4	72.1
70°	99.1	91.3	83.4	77.8	72.1	68.9	65.6	64.1	62.6	60.2	57.8
72.5°	80.8	74.7	68.7	64.3	60.0	57.1	54.3	51.3	48.2	46.1	43.9
75°	66.9	60.8	54.8	50.6	46.5	43.2	40.0	38.9	37.8	37.2	36.5
77.5°	51.3	46.1	40.8	37.6	34.3	32.8	31.3	30.6	30.0	29.8	29.5
80°	36.9	32.6	28.2	26.5	24.8	24.3	23.9	23.5	23.0	22.8	22.6
82.5°	23.0	20.9	18.7	18.3	17.8	17.6	17.4	17.2	16.9	16.7	16.5
85°	13.5	12.6	11.7	11.5	11.3	11.1	10.9	10.9	10.9	10.9	10.9
87.5°	5.6	5.6	5.6	5.6	5.6	5.6	5.6	5.6	5.6	5.4	5.2
90°	3.7	4.4	5.4	6.4	7.4	8.4	8.1	8.4	8.8	9.1	9.8
92.5°	17.2	23.3	34.0	51.9	69.4	62.7	46.9	33.4	26.0	22.6	20.2
95°	30.7	43.8	72.5	122.7	178.0	199.9	162.2	121.4	82.3	64.4	52.3
97.5°	35.4	49.9	78.2	136.5	229.6	307.5	317.9	278.8	210.4	165.9	127.4
100°	40.5	53.6	77.2	127.1	215.8	319.3	385.7	397.5	370.2	330.7	282.8
102.5°	46.2	58.0	78.6	119.0	195.5	297.3	389.0	436.9	442.6	423.8	397.8
105°	52.6	63.0	81.2	116.0	179.7	271.0	367.8	438.3	472.0	478.4	469.6
107.5°	59.7	69.4	85.6	115.3	168.2	247.8	337.5	418.0	471.0	497.3	506.4
110°	66.8	76.2	91.4	117.0	162.2	228.6	309.1	386.3	448.4	490.9	514.5



TEST NUMBER: P832115

CATALOG NUMBER: S123RDIP-S340D365U950-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	74.2	83.3	97.1	120.4	158.8	215.8	284.5	355.0	418.7	467.6	499.6
115°	81.6	90.7	103.5	124.1	158.4	207.3	265.7	328.0	386.7	436.2	473.0
117.5°	89.0	97.4	110.2	128.8	158.8	201.6	253.2	307.1	359.0	404.6	442.6
120°	96.1	104.5	116.6	134.2	160.1	197.9	243.7	291.3	336.8	377.2	411.3
122.5°	102.5	111.6	123.4	139.2	162.5	195.5	236.0	278.8	318.9	355.7	386.7
125°	108.9	118.0	129.8	144.6	164.9	193.5	229.6	268.0	304.8	337.1	364.1
127.5°	115.0	124.1	135.5	149.0	167.6	192.5	223.5	258.2	291.6	321.3	346.2
130°	120.4	129.5	140.6	153.4	170.2	191.5	218.8	249.1	279.5	306.8	329.7
132.5°	125.4	134.2	145.0	157.4	172.3	191.2	214.4	240.7	268.0	293.0	314.5
135°	129.8	138.9	149.3	160.8	174.3	190.8	210.7	233.3	257.2	279.1	298.4
137.5°	133.8	142.3	152.4	163.5	175.6	190.1	207.3	226.2	246.4	266.0	283.2
140°	137.2	145.6	155.4	165.5	177.0	189.8	204.3	220.1	237.3	253.5	268.0
142.5°	140.6	148.3	157.8	167.6	178.0	189.1	201.6	214.4	228.6	242.1	254.2
145°	143.3	151.0	159.8	168.9	178.3	188.5	199.2	210.0	221.2	231.9	241.7
147.5°	146.6	153.4	161.5	169.9	178.3	187.4	196.9	206.3	215.4	224.5	231.6
150°	149.3	155.4	163.2	170.2	178.3	186.1	194.5	202.3	210.0	217.1	223.5
152.5°	152.0	157.8	164.2	170.9	177.3	184.4	191.8	198.6	205.0	211.0	216.1
155°	155.1	159.8	165.5	170.9	176.7	182.4	189.1	194.9	200.3	205.3	209.4
157.5°	157.8	161.5	166.2	171.3	175.6	180.7	186.1	190.8	195.5	199.6	202.9
160°	159.8	163.2	167.2	171.3	175.0	178.7	183.1	187.4	191.2	194.5	196.9
162.5°	161.5	164.2	167.6	170.9	173.6	176.7	180.0	183.4	186.4	189.5	191.5
165°	162.8	165.2	167.9	170.2	172.3	174.6	177.3	180.0	182.0	184.4	186.1
167.5°	164.2	165.9	167.9	169.9	170.9	172.6	174.6	177.0	178.7	180.0	181.4
170°	165.2	165.9	167.6	168.9	169.6	170.6	172.3	174.0	175.0	176.3	177.0
172.5°	165.9	166.2	167.6	168.6	168.6	168.9	169.9	171.3	171.9	172.9	173.3
175°	166.2	166.5	167.2	167.9	167.6	167.6	168.2	168.9	169.2	169.9	169.9
177.5°	166.5	166.5	166.9	167.6	166.9	166.5	166.9	167.2	167.6	167.9	167.9
180°	166.5	166.5	166.5	166.5	166.5	166.5	166.5	166.5	166.5	166.5	166.5



TEST NUMBER: P832115

CATALOG NUMBER: S123RDIP-S340D365U950-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	1059.8	1059.8	1059.8	1059.8
2.5°	941.6	939.5	938.6	937.7
5°	807.1	800.4	798.9	797.4
7.5°	692.9	690.0	680.7	671.4
10°	600.1	591.4	587.5	583.6
12.5°	522.5	514.5	513.2	511.9
15°	462.3	456.7	454.7	452.8
17.5°	422.8	418.9	416.5	414.1
20°	393.5	390.6	388.9	387.2
22.5°	371.1	368.9	367.6	366.3
25°	349.6	346.3	345.2	344.1
27.5°	329.2	326.3	325.2	324.2
30°	310.0	307.6	306.1	304.6
32.5°	289.2	286.4	285.5	284.6
35°	270.7	269.0	268.1	267.2
37.5°	251.2	249.0	247.7	246.4
40°	234.4	233.3	232.7	232.0
42.5°	217.5	215.5	215.3	215.1
45°	200.5	198.6	198.1	197.7
47.5°	184.7	182.9	182.7	182.5
50°	167.1	164.7	162.9	161.2
52.5°	146.9	144.7	143.2	141.7
55°	128.4	126.0	124.7	123.4
57.5°	114.5	113.4	112.8	112.1
60°	103.2	102.5	102.1	101.7
62.5°	92.8	92.1	92.1	92.1
65°	83.2	82.6	81.9	81.3
67.5°	70.8	69.5	69.3	69.1
70°	55.8	53.9	53.7	53.4
72.5°	43.7	43.5	43.0	42.6
75°	36.1	35.6	35.6	35.6
77.5°	29.1	28.7	28.7	28.7
80°	22.4	22.2	22.4	22.6
82.5°	16.5	16.5	16.3	16.1
85°	10.6	10.4	10.4	10.4
87.5°	5.2	5.2	5.2	5.2
90°	9.4	9.8	10.1	9.8
92.5°	19.6	18.2	18.5	17.9
95°	45.8	42.8	40.5	39.1
97.5°	104.8	92.0	83.9	80.2
100°	248.8	224.2	211.0	211.4
102.5°	373.2	355.0	344.5	334.8
105°	454.1	441.3	430.5	428.8
107.5°	504.3	498.3	493.9	490.2
110°	523.9	526.6	525.9	525.2



TEST NUMBER: P832115

CATALOG NUMBER: S123RDIP-S340D365U950-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
112.5°	518.8	528.6	532.0	532.3
115°	498.3	513.1	519.8	521.5
117.5°	468.9	485.5	495.6	497.9
120°	437.9	456.8	464.9	466.9
122.5°	409.6	426.1	435.2	437.9
125°	385.7	400.5	408.9	411.3
127.5°	365.8	378.6	386.3	388.4
130°	347.6	359.7	366.8	369.5
132.5°	331.1	343.2	349.3	350.9
135°	314.9	325.0	331.1	333.4
137.5°	297.3	307.8	312.9	314.9
140°	280.8	290.3	295.7	295.3
142.5°	264.6	272.7	277.5	277.1
145°	250.1	257.2	259.9	260.6
147.5°	238.3	243.4	246.1	246.4
150°	228.6	232.3	234.3	234.3
152.5°	219.8	223.2	224.2	224.2
155°	212.4	215.1	215.8	216.1
157.5°	205.6	207.7	208.3	208.3
160°	199.2	201.3	201.3	200.9
162.5°	192.8	194.5	194.5	194.2
165°	187.4	188.8	188.5	188.5
167.5°	182.0	183.1	182.7	182.7
170°	177.3	178.0	177.7	177.7
172.5°	173.3	174.0	173.3	172.9
175°	169.9	170.2	169.9	169.6
177.5°	167.6	167.9	167.2	167.2
180°	166.5	166.5	166.5	166.5



TEST NUMBER: P832115

CATALOG NUMBER: S123RDIP-S340D365U950-4F0-1E-UDD-G4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.47	10.30	10.41	11.25	12.49	14.13	14.96	15.08	15.92	17.15
	3H	10.69	11.43	11.65	12.39	13.65	15.63	16.38	16.59	17.34	18.60
	4H	11.07	11.77	12.04	12.74	14.01	16.12	16.82	17.09	17.79	19.06
	6H	11.35	12.00	12.33	12.97	14.25	16.44	17.08	17.42	18.05	19.33
	8H	11.44	12.06	12.43	13.04	14.32	16.51	17.13	17.50	18.11	19.39
	12H	11.49	12.08	12.49	13.06	14.36	16.55	17.13	17.54	18.11	19.41
4H	2H	10.19	10.89	11.17	11.86	13.13	14.13	14.83	15.11	15.80	17.06
	3H	11.56	12.14	12.55	13.14	14.42	15.79	16.37	16.77	17.37	18.65
	4H	12.02	12.55	13.01	13.54	14.84	16.40	16.93	17.39	17.91	19.22
	6H	12.39	12.84	13.39	13.85	15.16	16.83	17.29	17.84	18.30	19.60
	8H	12.51	12.94	13.52	13.94	15.26	16.96	17.39	17.97	18.39	19.71
	12H	12.59	12.97	13.61	13.99	15.31	17.03	17.41	18.05	18.43	19.75
8H	4H	12.33	12.76	13.34	13.76	15.08	16.36	16.79	17.37	17.79	19.11
	6H	12.80	13.15	13.83	14.20	15.51	16.86	17.21	17.89	18.26	19.57
	8H	12.99	13.30	14.03	14.33	15.67	17.04	17.35	18.08	18.39	19.72
	12H	13.13	13.40	14.17	14.43	15.81	17.16	17.43	18.20	18.46	19.84
12H	4H	12.34	12.73	13.37	13.75	15.07	16.31	16.70	17.34	17.72	19.04
	6H	12.86	13.16	13.89	14.20	15.53	16.83	17.14	17.87	18.18	19.51
	8H	13.08	13.35	14.11	14.37	15.75	17.03	17.30	18.07	18.32	19.70