

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P832169

Luminaire Tested: S123RDIP-S340D805U950-4F0-1E-UDD-G4

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P832169
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-2, G3-1807-864-17)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-S340D805U950-4F0-1E-UDD-G4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, GRAZE OPTIC
UPLIGHT 805 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4178.8 lumens
Efficiency: N/A
Efficacy: 126.6 lumens/watt
Spacing Criteria (0/90/45): 0.55 / 1.17 / 0.8
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 33
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P832169

CATALOG NUMBER: S123RDIP-S340D805U950-4F0-1E-UDD-G4

Luminous Intensity Polar Plot





TEST NUMBER: P832169

CATALOG NUMBER: S123RDIP-S340D805U950-4F0-1E-UDD-G4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	34				
1	95	91	87	84	85	82	79	76	66	64	62	51	50	48	37	36	36	29				
2	87	80	74	69	78	72	68	63	58	55	52	45	43	41	33	32	31	26				
3	79	71	64	58	71	64	58	54	52	48	44	41	38	36	30	28	27	22				
4	73	63	56	50	66	57	51	46	46	42	38	37	34	31	27	25	24	20				
5	67	56	49	43	60	51	45	40	42	37	34	33	30	27	25	23	21	18				
6	62	51	43	38	56	46	40	35	38	33	30	30	27	24	23	21	19	16				
7	57	46	38	33	52	42	36	31	35	30	26	28	24	22	21	19	17	14				
8	53	42	35	30	48	38	32	28	32	27	24	25	22	20	20	17	16	13				
9	50	38	31	26	45	35	29	25	29	25	21	24	20	18	18	16	14	12				
10	47	35	28	24	42	32	26	22	27	22	19	22	19	16	17	15	13	11				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	11408	11408	11408	11408	11408
5°	13545	13113	11479	9280	8616
10°	12272	13319	11423	7436	6379
15°	8450	11420	11302	6077	5046
20°	5879	8793	11074	5125	4435
25°	4480	6701	10745	4555	4087
30°	3899	5358	10332	4228	3786
35°	3581	4519	9746	3954	3511
40°	3267	4036	8982	3684	3260
45°	2950	3691	8156	3430	3009
50°	2678	3406	7182	3180	2699
55°	2423	3126	6247	2935	2316
60°	2170	2844	5425	2665	2189
65°	2004	2524	4671	2397	2071
70°	1627	2181	4076	2168	1681
75°	1426	1734	3452	1797	1481
80°	1296	1469	2827	1506	1401
85°	1186	1284	2149	1371	1284

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 8605 cd/sqm



TEST NUMBER: P832169

CATALOG NUMBER: S123RDIP-S340D805U950-4F0-1E-UDD-G4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.6	2.3
10°-20°	223.5	5.3
20°-30°	256.5	6.1
30°-40°	252.8	6.0
40°-50°	222.9	5.3
50°-60°	171.5	4.1
60°-70°	112.8	2.7
70°-80°	54.8	1.3
80°-90°	15.8	0.4
90°-100°	199.9	4.8
100°-110°	585.4	14.0
110°-120°	571.6	13.7
120°-130°	455.2	10.9
130°-140°	359.2	8.6
140°-150°	267.9	6.4
150°-160°	186.8	4.5
160°-170°	109.7	2.6
170°-180°	35.7	0.9
0°-30°	576.6	13.8
0°-40°	829.4	19.8
0°-60°	1223.8	29.3
0°-90°	1407.2	33.7
90°-120°	1356.9	32.5
90°-150°	2439.3	58.4
90°-180°	2772.0	66.3
0°-180°	4178.8	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1060	1060	1060	1060	1060	
5°	1254	1214	1062	859	797	115
15°	758	1025	1014	545	453	214
25°	377	564	905	384	344	178
35°	272	344	742	301	267	170
45°	194	242	536	225	198	150
55°	129	167	333	156	123	116
65°	79	99	183	94	81	77
75°	34	42	83	43	36	37
85°	10	10	17	11	10	10
90°	22	19	2	19	22	12
95°	86	442	25	442	86	141
105°	949	600	86	600	949	946
115°	1154	459	153	459	1154	1125
125°	910	428	213	428	910	823
135°	738	422	249	422	738	572
145°	576	417	284	417	576	366
155°	478	404	323	404	478	223
165°	417	386	353	386	417	119
175°	375	371	368	371	375	36
180°	368	368	368	368	368	



TEST NUMBER: P832169

CATALOG NUMBER: S123RDIP-S340D805U950-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8
2.5°	1174.5	1170.8	1167.2	1166.1	1165.0	1161.5	1158.0	1150.2	1142.4	1134.3	1126.3
5°	1253.6	1254.1	1254.5	1253.4	1252.3	1247.8	1243.2	1233.6	1224.1	1213.6	1203.2
7.5°	1229.3	1236.2	1243.2	1244.5	1245.8	1249.3	1252.8	1250.6	1248.4	1244.5	1240.6
10°	1122.8	1122.4	1122.0	1129.8	1137.6	1160.9	1184.1	1196.1	1208.0	1218.6	1229.3
12.5°	949.0	949.7	950.3	976.0	1001.6	1023.5	1045.5	1075.9	1106.3	1139.1	1171.9
15°	758.3	768.9	779.6	802.4	825.2	858.2	891.2	932.1	972.9	1024.8	1076.8
17.5°	622.7	627.2	631.8	653.8	675.7	707.0	738.3	784.5	830.8	897.7	964.7
20°	513.2	517.3	521.4	537.3	553.2	583.1	613.1	657.2	701.3	767.6	833.9
22.5°	428.4	436.5	444.5	455.2	465.8	487.5	509.3	554.2	599.2	659.6	720.0
25°	377.2	380.9	384.6	393.7	402.8	423.7	444.5	474.3	504.1	564.2	624.4
27.5°	342.4	343.5	344.6	351.3	358.1	371.5	385.0	412.6	440.2	489.7	539.3
30°	313.7	315.7	317.6	322.9	328.1	337.8	347.6	367.2	386.7	431.1	475.4
32.5°	291.6	292.7	293.7	298.1	302.4	309.6	316.8	332.2	347.6	381.5	415.4
35°	272.5	272.7	272.9	276.1	279.4	286.4	293.3	306.1	318.9	343.9	368.9
37.5°	250.7	252.2	253.8	256.2	258.5	264.6	270.7	281.1	291.6	312.2	332.9
40°	232.5	233.8	235.1	237.9	240.7	245.5	250.3	259.9	269.4	287.2	305.0
42.5°	214.2	215.1	216.0	218.8	221.6	227.5	233.3	240.9	248.6	263.3	278.1
45°	193.8	196.0	198.1	201.2	204.2	209.2	214.2	222.0	229.9	242.5	255.1
47.5°	176.9	177.9	179.0	181.6	184.2	190.3	196.4	203.4	210.3	222.0	233.8
50°	159.9	160.3	160.8	163.2	165.6	171.0	176.4	184.5	192.5	203.4	214.2
52.5°	143.8	144.9	146.0	148.4	150.8	154.5	158.2	166.4	174.7	185.3	196.0
55°	129.1	129.7	130.4	132.1	133.8	138.2	142.5	149.7	156.9	166.6	176.4
57.5°	115.2	116.0	116.9	118.2	119.5	123.4	127.3	133.6	139.9	149.7	159.5
60°	100.8	101.9	103.0	104.5	106.0	109.1	112.1	117.8	123.4	132.1	140.8
62.5°	90.4	90.6	90.8	92.1	93.4	95.6	97.8	102.3	106.9	115.6	124.3
65°	78.7	79.3	80.0	80.6	81.3	83.0	84.7	88.6	92.6	99.1	105.6
67.5°	66.5	67.1	67.8	68.9	70.0	71.5	73.0	75.6	78.2	84.3	90.4
70°	51.7	51.7	51.7	53.4	55.2	57.8	60.4	62.4	64.3	69.3	74.3
72.5°	42.1	42.4	42.6	42.8	43.0	44.5	46.1	49.3	52.6	55.6	58.7
75°	34.3	34.5	34.8	35.0	35.2	35.6	36.1	37.2	38.2	41.7	45.2
77.5°	27.4	27.6	27.8	28.0	28.2	28.7	29.1	29.5	30.0	31.3	32.6
80°	20.9	21.1	21.3	21.5	21.7	21.9	22.2	22.6	23.0	23.7	24.3
82.5°	15.2	15.2	15.2	15.2	15.2	15.6	16.1	16.1	16.1	16.5	16.9
85°	9.6	9.6	9.6	9.8	10.0	10.0	10.0	10.2	10.4	10.4	10.4
87.5°	4.3	4.1	3.9	4.1	4.3	4.3	4.3	4.6	4.8	4.8	4.8
90°	21.6	22.4	21.6	20.9	21.6	20.1	19.4	18.6	17.9	18.6	16.4
92.5°	39.5	41.0	40.3	43.3	44.8	50.0	57.4	73.8	103.7	138.7	153.6
95°	86.5	89.5	94.7	101.4	115.6	142.5	182.0	268.5	358.8	442.3	393.8
97.5°	177.5	185.7	203.6	232.0	281.9	367.0	465.4	616.8	703.3	680.2	507.9
100°	467.7	466.9	496.0	550.4	625.8	731.7	819.0	879.4	853.3	706.3	477.3
102.5°	740.6	762.3	785.4	825.7	880.1	937.5	979.3	966.6	860.7	657.8	432.6
105°	948.7	952.5	976.3	1004.7	1039.0	1058.4	1044.2	969.6	813.7	599.7	397.5
107.5°	1084.5	1092.7	1102.4	1115.8	1120.3	1100.1	1042.0	924.9	746.6	548.2	372.2
110°	1162.0	1163.5	1165.0	1159.1	1138.2	1086.0	992.0	854.8	684.0	505.7	358.8



TEST NUMBER: P832169

CATALOG NUMBER: S123RDIP-S340D805U950-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1177.7	1177.0	1169.5	1147.9	1105.4	1034.5	926.4	785.4	629.5	477.3	351.3
115°	1153.8	1150.1	1135.2	1102.4	1046.4	965.1	855.5	725.7	587.7	458.7	350.6
117.5°	1101.6	1096.4	1074.0	1037.5	979.3	895.0	794.3	679.5	560.1	446.0	351.3
120°	1033.0	1028.5	1010.6	968.9	909.9	834.6	745.1	644.4	539.3	437.8	354.3
122.5°	968.9	962.9	942.8	906.2	855.5	786.9	705.6	616.8	522.1	432.6	359.5
125°	909.9	904.7	886.1	853.3	805.5	745.9	674.3	593.0	507.9	428.1	364.7
127.5°	859.2	854.8	837.6	809.3	766.0	710.8	645.2	571.3	494.5	425.9	370.7
130°	817.5	811.5	795.8	769.0	729.4	678.7	618.3	551.2	484.1	423.6	376.7
132.5°	776.4	772.7	759.3	732.4	695.9	648.1	593.0	532.5	474.4	422.9	381.1
135°	737.7	732.4	719.0	696.6	660.1	617.6	569.1	516.1	466.2	422.2	385.6
137.5°	696.6	692.2	681.0	657.8	626.5	588.5	545.2	500.5	458.7	420.7	388.6
140°	653.4	654.1	642.2	621.3	593.0	560.9	525.1	487.0	452.0	419.9	391.6
142.5°	613.1	613.8	603.4	585.5	562.4	535.5	505.7	474.4	446.0	418.4	393.8
145°	576.5	575.1	569.1	553.4	534.8	513.1	489.3	464.7	440.8	416.9	394.6
147.5°	545.2	544.5	538.5	527.3	512.4	496.7	476.6	456.5	435.6	414.7	394.6
150°	518.4	518.4	513.9	505.7	494.5	480.3	464.7	447.5	430.4	411.7	394.6
152.5°	496.0	496.0	493.8	486.3	478.1	466.9	453.5	439.3	424.4	408.0	392.3
155°	478.1	477.3	475.9	469.9	463.2	454.2	443.0	431.1	418.4	403.5	390.8
157.5°	460.9	460.9	459.4	455.0	449.0	441.5	432.6	422.2	411.7	399.8	388.6
160°	444.5	445.3	445.3	440.8	435.6	430.4	422.9	414.7	405.0	395.3	387.1
162.5°	429.6	430.4	430.4	426.6	423.6	419.2	412.5	405.7	398.3	390.8	384.1
165°	416.9	416.9	417.7	414.7	411.7	408.0	402.8	398.3	392.3	386.4	381.1
167.5°	404.3	404.3	405.0	402.8	401.3	398.3	395.3	391.6	386.4	381.9	378.1
170°	393.1	393.1	393.8	392.3	391.6	390.1	387.1	384.9	381.1	377.4	375.2
172.5°	382.6	383.4	384.9	383.4	383.4	382.6	380.4	378.9	375.9	373.7	372.9
175°	375.2	375.9	376.7	375.9	375.9	375.9	374.4	373.7	372.2	370.7	370.7
177.5°	369.9	369.9	371.4	370.7	371.4	371.4	370.7	369.9	369.2	368.5	369.2
180°	368.5	368.5	368.5	368.5	368.5	368.5	368.5	368.5	368.5	368.5	368.5



TEST NUMBER: P832169

CATALOG NUMBER: S123RDIP-S340D805U950-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8
2.5°	1125.2	1124.1	1113.7	1103.3	1093.1	1082.9	1075.3	1067.6	1054.8	1042.0	1034.0
5°	1195.0	1186.7	1170.2	1153.7	1128.9	1104.1	1083.3	1062.4	1035.9	1009.4	987.3
7.5°	1233.9	1227.1	1207.1	1187.1	1154.3	1121.5	1088.9	1056.3	1017.2	978.1	944.7
10°	1234.9	1240.6	1224.1	1207.6	1170.6	1133.7	1089.4	1045.1	992.5	939.9	896.7
12.5°	1196.3	1220.6	1217.1	1213.6	1176.1	1138.5	1084.6	1030.7	966.2	901.7	847.6
15°	1123.9	1171.1	1185.0	1198.9	1167.8	1136.7	1075.5	1014.2	938.4	862.5	800.4
17.5°	1030.7	1096.8	1133.5	1170.2	1147.6	1125.0	1057.9	990.7	905.3	820.0	752.4
20°	920.3	1006.8	1064.4	1122.0	1113.7	1105.5	1036.1	966.8	874.7	782.6	709.4
22.5°	811.3	902.5	982.0	1061.6	1070.0	1078.5	1008.6	938.6	837.8	737.0	662.4
25°	717.2	810.0	904.7	999.4	1018.5	1037.7	971.2	904.7	800.2	695.7	621.6
27.5°	627.5	715.7	820.0	924.3	959.0	993.8	932.9	872.1	763.3	654.4	580.5
30°	554.2	633.1	739.6	846.0	894.5	942.9	887.1	831.3	723.3	615.3	542.9
32.5°	486.0	556.6	663.5	770.4	826.7	883.0	834.7	786.5	682.7	578.8	507.3
35°	432.1	495.4	595.1	694.8	757.8	820.8	781.3	741.7	640.3	538.8	471.3
37.5°	385.9	438.9	532.5	626.2	693.1	760.0	727.0	693.9	598.6	503.2	439.3
40°	347.6	390.2	477.3	564.5	630.1	695.7	667.4	639.2	553.8	468.4	408.7
42.5°	314.8	351.5	429.8	508.0	568.2	628.3	609.6	591.0	513.6	436.3	380.9
45°	285.9	316.8	385.6	454.5	509.9	565.3	550.6	535.8	469.1	402.4	351.5
47.5°	260.3	286.8	348.3	409.8	459.5	509.3	495.6	481.9	426.7	371.5	325.2
50°	236.8	259.4	310.7	362.0	406.7	451.5	440.2	428.9	383.3	337.6	297.7
52.5°	214.7	233.3	279.4	325.5	361.5	397.6	388.9	380.2	345.0	309.8	273.5
55°	193.6	210.7	249.6	288.5	319.4	350.2	341.5	332.9	305.5	278.1	246.2
57.5°	174.5	189.5	221.0	252.5	277.0	301.6	297.4	293.3	270.5	247.7	221.4
60°	154.3	167.7	194.9	222.0	241.8	261.6	256.8	252.0	235.7	219.4	196.8
62.5°	136.2	148.2	169.9	191.6	207.7	223.8	220.3	216.8	204.4	192.1	173.4
65°	117.3	129.1	146.7	164.3	176.9	189.5	186.4	183.4	174.0	164.7	149.7
67.5°	100.2	109.9	125.1	140.4	148.8	157.3	155.6	153.8	146.7	139.5	127.8
70°	82.8	91.3	103.9	116.5	122.3	128.2	128.8	129.5	123.0	116.5	107.8
72.5°	65.4	72.1	83.9	95.6	100.2	104.7	104.5	104.3	100.4	96.5	88.6
75°	50.2	55.2	64.3	73.4	77.3	81.3	82.1	83.0	79.3	75.6	71.3
77.5°	36.1	39.5	46.5	53.4	57.8	62.1	62.6	63.0	61.3	59.5	55.4
80°	25.4	26.5	30.9	35.2	39.8	44.3	45.0	45.6	43.9	42.1	39.5
82.5°	17.6	18.3	19.8	21.3	25.0	28.7	29.5	30.4	29.5	28.7	25.9
85°	10.6	10.9	11.5	12.2	13.9	15.6	16.5	17.4	16.9	16.5	15.0
87.5°	4.8	4.8	5.0	5.2	5.6	6.1	7.2	8.3	7.6	7.0	6.3
90°	14.2	11.9	9.7	8.2	6.7	4.5	3.0	1.5	3.0	4.5	6.7
92.5°	114.9	75.3	51.5	38.0	30.6	23.9	16.4	11.2	16.4	23.9	30.6
95°	271.5	160.4	97.0	67.9	48.5	35.8	27.6	25.4	27.6	35.8	48.5
97.5°	302.1	173.0	110.4	78.3	58.9	47.7	41.0	40.3	41.0	47.7	58.9
100°	281.2	170.8	118.6	89.5	71.6	61.2	55.9	55.2	55.9	61.2	71.6
102.5°	263.3	173.8	128.3	102.2	86.5	76.8	72.3	70.9	72.3	76.8	86.5
105°	256.6	179.8	139.5	116.4	102.2	93.2	88.8	86.5	88.8	93.2	102.2
107.5°	255.1	189.4	153.6	132.0	118.6	109.6	105.2	102.9	105.2	109.6	118.6
110°	258.8	202.1	168.6	147.7	135.0	126.8	123.1	120.8	123.1	126.8	135.0



TEST NUMBER: P832169

CATALOG NUMBER: S123RDIP-S340D805U950-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	266.3	214.8	184.2	164.1	151.4	143.2	139.5	137.2	139.5	143.2	151.4
115°	274.5	229.0	200.6	180.5	167.8	160.4	155.9	152.9	155.9	160.4	167.8
117.5°	284.9	243.9	215.6	196.9	182.7	176.0	172.3	168.6	172.3	176.0	182.7
120°	296.9	258.1	231.2	212.6	198.4	190.9	187.2	185.0	187.2	190.9	198.4
122.5°	308.0	273.0	246.9	226.7	213.3	205.1	201.4	199.1	201.4	205.1	213.3
125°	320.0	287.2	261.0	240.9	226.7	218.5	214.1	212.6	214.1	218.5	226.7
127.5°	329.7	299.8	274.5	254.3	238.7	230.5	225.2	223.0	225.2	230.5	238.7
130°	339.4	311.0	286.4	266.3	250.6	241.7	234.9	232.7	234.9	241.7	250.6
132.5°	348.3	320.7	296.9	277.5	261.8	250.6	243.1	240.2	243.1	250.6	261.8
135°	355.8	330.4	307.3	287.2	271.5	260.3	252.1	249.1	252.1	260.3	271.5
137.5°	361.7	337.1	314.8	296.1	280.4	268.5	260.3	257.3	260.3	268.5	280.4
140°	366.2	343.8	322.2	303.6	288.6	276.7	269.3	265.5	269.3	276.7	288.6
142.5°	370.7	349.1	328.2	311.0	296.1	285.7	277.5	274.5	277.5	285.7	296.1
145°	373.7	353.5	334.1	317.0	304.3	293.1	286.4	284.2	286.4	293.1	304.3
147.5°	375.9	357.3	339.4	324.4	311.8	302.1	295.4	293.9	295.4	302.1	311.8
150°	376.7	361.0	343.8	330.4	320.0	310.3	304.3	303.6	304.3	310.3	320.0
152.5°	378.1	363.2	349.1	336.4	327.4	319.2	313.3	313.3	313.3	319.2	327.4
155°	378.1	366.2	353.5	343.1	334.9	327.4	323.0	323.0	323.0	327.4	334.9
157.5°	378.9	367.7	357.3	349.1	341.6	334.9	331.2	330.4	331.2	334.9	341.6
160°	378.9	369.9	361.0	353.5	348.3	342.3	339.4	339.4	339.4	342.3	348.3
162.5°	378.1	370.7	363.2	357.3	352.8	348.3	346.1	346.1	346.1	348.3	352.8
165°	376.7	371.4	365.5	360.2	357.3	353.5	352.0	352.8	352.0	353.5	357.3
167.5°	375.9	371.4	367.0	363.2	361.0	358.0	357.3	358.0	357.3	358.0	361.0
170°	373.7	370.7	367.0	365.5	364.0	361.7	361.0	362.5	361.0	361.7	364.0
172.5°	372.9	370.7	367.7	367.0	366.2	364.7	364.7	365.5	364.7	364.7	366.2
175°	371.4	369.9	368.5	367.7	367.7	366.2	367.0	367.7	367.0	366.2	367.7
177.5°	370.7	369.2	368.5	368.5	368.5	367.7	368.5	369.2	368.5	367.7	368.5
180°	368.5	368.5	368.5	368.5	368.5	368.5	368.5	368.5	368.5	368.5	368.5



TEST NUMBER: P832169

CATALOG NUMBER: S123RDIP-S340D805U950-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8	1059.8
2.5°	1025.9	1013.5	1001.2	992.3	983.3	972.3	961.2	960.8	960.3	952.1	943.8
5°	965.1	943.6	922.1	901.0	879.9	858.9	837.8	833.0	828.2	821.0	813.9
7.5°	911.2	876.9	842.6	815.6	788.7	767.6	746.5	732.2	717.8	706.8	695.7
10°	853.4	810.8	768.3	735.7	703.1	680.3	657.4	640.9	624.4	616.6	608.8
12.5°	793.5	747.2	700.9	669.0	637.0	609.6	582.3	567.3	552.3	541.4	530.6
15°	738.3	688.5	638.8	604.9	571.0	545.3	519.7	504.7	489.7	478.9	468.0
17.5°	684.8	634.6	584.4	550.1	515.8	492.5	469.3	454.7	440.2	433.4	426.7
20°	636.2	585.5	534.9	502.5	470.2	447.4	424.5	416.7	408.9	402.6	396.3
22.5°	587.9	539.3	490.6	459.5	428.4	411.9	395.4	389.1	382.8	378.0	373.3
25°	547.5	499.1	450.6	423.5	396.3	383.5	370.7	366.5	362.4	357.6	352.8
27.5°	506.7	460.6	414.5	392.8	371.1	360.7	350.2	345.0	339.8	335.9	332.0
30°	470.6	428.0	385.4	367.4	349.4	340.2	331.1	325.5	319.8	316.1	312.4
32.5°	435.8	398.0	360.2	344.8	329.4	320.5	311.6	306.1	300.7	296.4	292.0
35°	403.7	370.9	338.1	323.9	309.8	300.9	292.0	286.6	281.1	276.8	272.5
37.5°	375.4	345.7	315.9	302.7	289.4	281.6	273.8	268.1	262.5	257.9	253.3
40°	348.9	322.6	296.4	283.5	270.7	262.2	253.8	248.8	243.8	239.6	235.5
42.5°	325.5	301.3	277.2	264.6	252.0	244.0	236.0	230.1	224.2	221.8	219.4
45°	300.7	279.4	258.1	245.9	233.8	225.3	216.8	211.8	206.8	204.7	202.5
47.5°	279.0	259.2	239.4	227.5	215.5	207.9	200.3	196.4	192.5	189.5	186.4
50°	257.7	238.6	219.4	207.9	196.4	189.9	183.4	178.6	173.8	171.6	169.5
52.5°	237.3	219.9	202.5	190.8	179.0	172.7	166.4	162.3	158.2	153.6	149.0
55°	214.2	199.0	183.8	173.4	162.9	156.4	149.9	145.1	140.4	135.6	130.8
57.5°	195.1	180.1	165.1	155.8	146.4	140.1	133.8	128.6	123.4	119.5	115.6
60°	174.2	161.2	148.2	139.1	129.9	123.8	117.8	112.8	107.8	105.8	103.9
62.5°	154.7	142.5	130.4	122.3	114.3	108.4	102.5	99.3	96.0	94.7	93.4
65°	134.7	124.3	113.8	106.5	99.1	94.1	89.1	87.6	86.0	85.0	83.9
67.5°	116.0	107.1	98.2	91.7	85.2	81.7	78.2	76.5	74.7	73.4	72.1
70°	99.1	91.3	83.4	77.8	72.1	68.9	65.6	64.1	62.6	60.2	57.8
72.5°	80.8	74.7	68.7	64.3	60.0	57.1	54.3	51.3	48.2	46.1	43.9
75°	66.9	60.8	54.8	50.6	46.5	43.2	40.0	38.9	37.8	37.2	36.5
77.5°	51.3	46.1	40.8	37.6	34.3	32.8	31.3	30.6	30.0	29.8	29.5
80°	36.9	32.6	28.2	26.5	24.8	24.3	23.9	23.5	23.0	22.8	22.6
82.5°	23.0	20.9	18.7	18.3	17.8	17.6	17.4	17.2	16.9	16.7	16.5
85°	13.5	12.6	11.7	11.5	11.3	11.1	10.9	10.9	10.9	10.9	10.9
87.5°	5.6	5.6	5.6	5.6	5.6	5.6	5.6	5.6	5.6	5.4	5.2
90°	8.2	9.7	11.9	14.2	16.4	18.6	17.9	18.6	19.4	20.1	21.6
92.5°	38.0	51.5	75.3	114.9	153.6	138.7	103.7	73.8	57.4	50.0	44.8
95°	67.9	97.0	160.4	271.5	393.8	442.3	358.8	268.5	182.0	142.5	115.6
97.5°	78.3	110.4	173.0	302.1	507.9	680.2	703.3	616.8	465.4	367.0	281.9
100°	89.5	118.6	170.8	281.2	477.3	706.3	853.3	879.4	819.0	731.7	625.8
102.5°	102.2	128.3	173.8	263.3	432.6	657.8	860.7	966.6	979.3	937.5	880.1
105°	116.4	139.5	179.8	256.6	397.5	599.7	813.7	969.6	1044.2	1058.4	1039.0
107.5°	132.0	153.6	189.4	255.1	372.2	548.2	746.6	924.9	1042.0	1100.1	1120.3
110°	147.7	168.6	202.1	258.8	358.8	505.7	684.0	854.8	992.0	1086.0	1138.2



TEST NUMBER: P832169

CATALOG NUMBER: S123RDIP-S340D805U950-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	164.1	184.2	214.8	266.3	351.3	477.3	629.5	785.4	926.4	1034.5	1105.4
115°	180.5	200.6	229.0	274.5	350.6	458.7	587.7	725.7	855.5	965.1	1046.4
117.5°	196.9	215.6	243.9	284.9	351.3	446.0	560.1	679.5	794.3	895.0	979.3
120°	212.6	231.2	258.1	296.9	354.3	437.8	539.3	644.4	745.1	834.6	909.9
122.5°	226.7	246.9	273.0	308.0	359.5	432.6	522.1	616.8	705.6	786.9	855.5
125°	240.9	261.0	287.2	320.0	364.7	428.1	507.9	593.0	674.3	745.9	805.5
127.5°	254.3	274.5	299.8	329.7	370.7	425.9	494.5	571.3	645.2	710.8	766.0
130°	266.3	286.4	311.0	339.4	376.7	423.6	484.1	551.2	618.3	678.7	729.4
132.5°	277.5	296.9	320.7	348.3	381.1	422.9	474.4	532.5	593.0	648.1	695.9
135°	287.2	307.3	330.4	355.8	385.6	422.2	466.2	516.1	569.1	617.6	660.1
137.5°	296.1	314.8	337.1	361.7	388.6	420.7	458.7	500.5	545.2	588.5	626.5
140°	303.6	322.2	343.8	366.2	391.6	419.9	452.0	487.0	525.1	560.9	593.0
142.5°	311.0	328.2	349.1	370.7	393.8	418.4	446.0	474.4	505.7	535.5	562.4
145°	317.0	334.1	353.5	373.7	394.6	416.9	440.8	464.7	489.3	513.1	534.8
147.5°	324.4	339.4	357.3	375.9	394.6	414.7	435.6	456.5	476.6	496.7	512.4
150°	330.4	343.8	361.0	376.7	394.6	411.7	430.4	447.5	464.7	480.3	494.5
152.5°	336.4	349.1	363.2	378.1	392.3	408.0	424.4	439.3	453.5	466.9	478.1
155°	343.1	353.5	366.2	378.1	390.8	403.5	418.4	431.1	443.0	454.2	463.2
157.5°	349.1	357.3	367.7	378.9	388.6	399.8	411.7	422.2	432.6	441.5	449.0
160°	353.5	361.0	369.9	378.9	387.1	395.3	405.0	414.7	422.9	430.4	435.6
162.5°	357.3	363.2	370.7	378.1	384.1	390.8	398.3	405.7	412.5	419.2	423.6
165°	360.2	365.5	371.4	376.7	381.1	386.4	392.3	398.3	402.8	408.0	411.7
167.5°	363.2	367.0	371.4	375.9	378.1	381.9	386.4	391.6	395.3	398.3	401.3
170°	365.5	367.0	370.7	373.7	375.2	377.4	381.1	384.9	387.1	390.1	391.6
172.5°	367.0	367.7	370.7	372.9	372.9	373.7	375.9	378.9	380.4	382.6	383.4
175°	367.7	368.5	369.9	371.4	370.7	370.7	372.2	373.7	374.4	375.9	375.9
177.5°	368.5	368.5	369.2	370.7	369.2	368.5	369.2	369.9	370.7	371.4	371.4
180°	368.5	368.5	368.5	368.5	368.5	368.5	368.5	368.5	368.5	368.5	368.5



TEST NUMBER: P832169

CATALOG NUMBER: S123RDIP-S340D805U950-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	1059.8	1059.8	1059.8	1059.8
2.5°	941.6	939.5	938.6	937.7
5°	807.1	800.4	798.9	797.4
7.5°	692.9	690.0	680.7	671.4
10°	600.1	591.4	587.5	583.6
12.5°	522.5	514.5	513.2	511.9
15°	462.3	456.7	454.7	452.8
17.5°	422.8	418.9	416.5	414.1
20°	393.5	390.6	388.9	387.2
22.5°	371.1	368.9	367.6	366.3
25°	349.6	346.3	345.2	344.1
27.5°	329.2	326.3	325.2	324.2
30°	310.0	307.6	306.1	304.6
32.5°	289.2	286.4	285.5	284.6
35°	270.7	269.0	268.1	267.2
37.5°	251.2	249.0	247.7	246.4
40°	234.4	233.3	232.7	232.0
42.5°	217.5	215.5	215.3	215.1
45°	200.5	198.6	198.1	197.7
47.5°	184.7	182.9	182.7	182.5
50°	167.1	164.7	162.9	161.2
52.5°	146.9	144.7	143.2	141.7
55°	128.4	126.0	124.7	123.4
57.5°	114.5	113.4	112.8	112.1
60°	103.2	102.5	102.1	101.7
62.5°	92.8	92.1	92.1	92.1
65°	83.2	82.6	81.9	81.3
67.5°	70.8	69.5	69.3	69.1
70°	55.8	53.9	53.7	53.4
72.5°	43.7	43.5	43.0	42.6
75°	36.1	35.6	35.6	35.6
77.5°	29.1	28.7	28.7	28.7
80°	22.4	22.2	22.4	22.6
82.5°	16.5	16.5	16.3	16.1
85°	10.6	10.4	10.4	10.4
87.5°	5.2	5.2	5.2	5.2
90°	20.9	21.6	22.4	21.6
92.5°	43.3	40.3	41.0	39.5
95°	101.4	94.7	89.5	86.5
97.5°	232.0	203.6	185.7	177.5
100°	550.4	496.0	466.9	467.7
102.5°	825.7	785.4	762.3	740.6
105°	1004.7	976.3	952.5	948.7
107.5°	1115.8	1102.4	1092.7	1084.5
110°	1159.1	1165.0	1163.5	1162.0



TEST NUMBER: P832169

CATALOG NUMBER: S123RDIP-S340D805U950-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
112.5°	1147.9	1169.5	1177.0	1177.7
115°	1102.4	1135.2	1150.1	1153.8
117.5°	1037.5	1074.0	1096.4	1101.6
120°	968.9	1010.6	1028.5	1033.0
122.5°	906.2	942.8	962.9	968.9
125°	853.3	886.1	904.7	909.9
127.5°	809.3	837.6	854.8	859.2
130°	769.0	795.8	811.5	817.5
132.5°	732.4	759.3	772.7	776.4
135°	696.6	719.0	732.4	737.7
137.5°	657.8	681.0	692.2	696.6
140°	621.3	642.2	654.1	653.4
142.5°	585.5	603.4	613.8	613.1
145°	553.4	569.1	575.1	576.5
147.5°	527.3	538.5	544.5	545.2
150°	505.7	513.9	518.4	518.4
152.5°	486.3	493.8	496.0	496.0
155°	469.9	475.9	477.3	478.1
157.5°	455.0	459.4	460.9	460.9
160°	440.8	445.3	445.3	444.5
162.5°	426.6	430.4	430.4	429.6
165°	414.7	417.7	416.9	416.9
167.5°	402.8	405.0	404.3	404.3
170°	392.3	393.8	393.1	393.1
172.5°	383.4	384.9	383.4	382.6
175°	375.9	376.7	375.9	375.2
177.5°	370.7	371.4	369.9	369.9
180°	368.5	368.5	368.5	368.5



TEST NUMBER: P832169

CATALOG NUMBER: S123RDIP-S340D805U950-4F0-1E-UDD-G4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.44	8.14	8.54	9.23	10.72	12.10	12.80	13.20	13.89	15.38
	3H	8.65	9.28	9.75	10.37	11.88	13.60	14.22	14.70	15.31	16.82
	4H	9.03	9.62	10.14	10.72	12.23	14.08	14.67	15.19	15.77	17.28
	6H	9.30	9.85	10.42	10.95	12.47	14.38	14.93	15.51	16.03	17.55
	8H	9.39	9.90	10.51	11.02	12.54	14.46	14.98	15.58	16.09	17.61
	12H	9.44	9.93	10.56	11.03	12.58	14.49	14.98	15.62	16.09	17.63
4H	2H	8.15	8.74	9.27	9.84	11.35	12.08	12.68	13.21	13.77	15.29
	3H	9.51	10.00	10.63	11.12	12.65	13.73	14.22	14.86	15.35	16.87
	4H	9.96	10.41	11.09	11.52	13.07	14.33	14.79	15.46	15.90	17.44
	6H	10.32	10.70	11.45	11.84	13.38	14.76	15.15	15.90	16.29	17.82
	8H	10.44	10.80	11.58	11.93	13.48	14.89	15.25	16.03	16.38	17.93
	12H	10.51	10.84	11.66	11.98	13.54	14.95	15.28	16.10	16.42	17.97
8H	4H	10.26	10.62	11.40	11.75	13.30	14.29	14.65	15.43	15.78	17.33
	6H	10.72	11.02	11.88	12.19	13.74	14.78	15.08	15.94	16.25	17.80
	8H	10.92	11.17	12.08	12.32	13.89	14.97	15.23	16.13	16.38	17.95
	12H	11.05	11.28	12.22	12.43	14.03	15.08	15.31	16.24	16.45	18.06
12H	4H	10.27	10.59	11.42	11.73	13.29	14.24	14.56	15.39	15.70	17.26
	6H	10.78	11.04	11.94	12.19	13.76	14.76	15.02	15.92	16.17	17.74
	8H	10.99	11.22	12.16	12.37	13.97	14.94	15.17	16.11	16.32	17.92