

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: NEO-RAY

Report Number: P332497

Luminaire Tested: **S124DIP-S350D365U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332497  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIP-S350D365U835-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2784.9 lumens  
Efficiency: N/A  
Efficacy: 137.2 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 20.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332497

CATALOG NUMBER: S124DIP-S350D365U835-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332497

CATALOG NUMBER: S124DIP-S350D365U835-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60	54
1	99	94	90	87	91	88	84	81	75	73	70	64	62	60	53	52	51	46
2	90	82	76	71	83	77	71	67	66	62	58	56	53	50	47	45	43	38
3	82	72	65	59	76	67	61	56	58	53	49	49	46	43	41	39	36	32
4	75	64	56	50	69	60	53	47	52	46	42	44	40	36	37	34	31	28
5	69	57	49	43	64	53	46	41	46	40	36	40	35	32	33	30	27	24
6	63	51	43	37	59	48	41	35	42	36	31	36	31	28	30	27	24	21
7	59	46	38	33	54	43	36	31	38	32	28	33	28	25	28	24	21	19
8	55	42	34	29	51	39	32	27	35	29	25	30	25	22	25	22	19	17
9	51	38	31	26	47	36	29	25	32	26	22	27	23	20	23	20	17	15
10	47	35	28	23	44	33	27	22	29	24	20	25	21	18	22	18	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	4769	4769	4769
5°	4783	4725	4760
10°	4753	4687	4710
15°	4695	4621	4633
20°	4619	4538	4542
25°	4532	4444	4431
30°	4426	4333	4294
35°	4315	4217	4161
40°	4200	4086	4011
45°	4080	3956	3881
50°	3947	3841	3721
55°	3804	3690	3571
60°	3660	3523	3416
65°	3500	3364	3228
70°	3319	3151	3028
75°	3041	2895	2820
80°	2706	2599	2529
85°	2371	2279	2232



TEST NUMBER: P332497

CATALOG NUMBER: S124DIP-S350D365U835-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	55.6	2.0
10°-20°	156.7	5.6
20°-30°	230.7	8.3
30°-40°	268.2	9.6
40°-50°	268.2	9.6
50°-60°	234.6	8.4
60°-70°	174.2	6.3
70°-80°	99.0	3.6
80°-90°	29.9	1.1
90°-100°	30.1	1.1
100°-110°	89.3	3.2
110°-120°	151.5	5.4
120°-130°	199.8	7.2
130°-140°	224.4	8.1
140°-150°	220.5	7.9
150°-160°	185.4	6.7
160°-170°	123.4	4.4
170°-180°	43.2	1.6
0°-30°	443.1	15.9
0°-40°	711.3	25.5
0°-60°	1214.1	43.6
0°-90°	1517.2	54.5
90°-120°	270.9	9.7
90°-150°	915.6	32.9
90°-180°	1268.0	45.5
0°-180°	2784.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	591	591	591	591	591	
5°	590	588	583	588	587	56
15°	562	560	553	555	554	158
25°	509	505	499	499	498	234
35°	438	434	428	425	422	274
45°	357	354	346	342	340	275
55°	270	269	262	257	254	242
65°	183	181	176	172	169	181
75°	98	95	93	91	90	104
85°	26	26	25	25	24	28
90°	1	5	8	10	11	3
95°	21	24	27	28	28	24
105°	82	83	84	85	86	87
115°	154	154	153	153	153	152
125°	224	224	224	223	223	200
135°	289	291	292	291	290	224
145°	352	353	353	353	352	220
155°	403	403	402	404	402	185
165°	438	438	437	439	438	124
175°	456	454	454	456	454	43
180°	457	457	457	457	457	



TEST NUMBER: P332497

CATALOG NUMBER: S124DIP-S350D365U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7
2.5°	592.2	592.0	591.7	591.5	591.2	590.6	589.7	588.8	587.9	586.9	587.8
5°	590.2	589.8	589.4	589.0	588.6	587.8	586.6	585.5	584.3	583.1	584.3
7.5°	584.8	584.3	583.9	583.5	583.1	582.2	580.9	579.7	578.4	577.1	578.0
10°	579.8	579.4	579.0	578.6	578.2	577.3	575.9	574.5	573.2	571.8	572.6
12.5°	573.4	573.0	572.6	572.1	571.7	570.8	569.3	567.9	566.4	565.0	565.9
15°	561.8	561.4	561.0	560.6	560.2	559.2	557.6	556.0	554.4	552.9	553.5
17.5°	547.9	547.4	546.9	546.4	545.8	544.8	543.3	541.8	540.3	538.8	539.2
20°	537.7	537.2	536.7	536.1	535.6	534.6	533.0	531.4	529.8	528.2	528.6
22.5°	526.7	526.0	525.3	524.6	523.9	522.8	521.2	519.7	518.1	516.5	517.1
25°	508.8	508.1	507.4	506.6	505.9	504.8	503.3	501.8	500.4	498.9	499.0
27.5°	488.4	487.6	486.9	486.1	485.4	484.3	482.9	481.6	480.2	478.8	478.6
30°	474.8	473.9	473.1	472.2	471.4	470.3	468.9	467.5	466.2	464.8	464.4
32.5°	460.4	459.6	458.8	458.1	457.3	456.2	454.8	453.3	451.9	450.4	449.9
35°	437.8	437.1	436.4	435.6	434.9	433.8	432.3	430.8	429.4	427.9	427.2
37.5°	414.1	413.4	412.7	412.1	411.4	410.3	408.7	407.1	405.5	403.9	403.1
40°	398.5	397.7	396.9	396.0	395.2	394.0	392.4	390.8	389.2	387.7	386.6
42.5°	381.9	381.4	380.9	380.4	379.9	378.7	377.0	375.2	373.5	371.8	370.5
45°	357.4	356.6	355.9	355.2	354.4	353.2	351.5	349.8	348.2	346.5	345.3
47.5°	331.7	331.2	330.7	330.2	329.7	328.7	327.1	325.5	324.0	322.4	321.1
50°	314.3	313.9	313.5	313.0	312.6	311.7	310.2	308.7	307.2	305.8	304.3
52.5°	297.3	296.7	296.2	295.7	295.2	294.2	292.6	291.1	289.5	288.0	286.7
55°	270.3	270.0	269.6	269.3	269.0	268.1	266.6	265.2	263.7	262.2	261.0
57.5°	244.5	244.2	243.8	243.5	243.1	242.2	240.7	239.3	237.8	236.4	235.2
60°	226.7	226.2	225.7	225.1	224.6	223.7	222.3	220.9	219.6	218.2	217.3
62.5°	209.3	208.9	208.4	208.0	207.5	206.6	205.1	203.7	202.2	200.8	199.9
65°	183.2	182.7	182.1	181.6	181.1	180.3	179.2	178.2	177.1	176.1	175.0
67.5°	156.9	156.4	155.9	155.4	154.9	154.2	153.2	152.2	151.2	150.1	149.1
70°	140.6	139.8	139.1	138.4	137.6	136.8	136.0	135.2	134.3	133.5	132.6
72.5°	123.2	122.4	121.7	121.0	120.2	119.5	118.8	118.2	117.5	116.8	116.1
75°	97.5	97.0	96.5	95.9	95.4	94.9	94.4	93.8	93.3	92.8	92.4
77.5°	73.0	72.8	72.5	72.3	72.1	71.7	71.3	70.8	70.3	69.9	69.7
80°	58.2	57.9	57.6	57.3	57.0	56.7	56.5	56.3	56.1	55.9	55.6
82.5°	43.8	43.7	43.5	43.4	43.2	43.1	43.1	43.1	43.0	43.0	42.9
85°	25.6	25.6	25.6	25.6	25.6	25.5	25.2	25.0	24.8	24.6	24.6
87.5°	10.1	10.1	10.2	10.3	10.4	10.5	10.5	10.6	10.6	10.6	10.7
90°	1.1	1.9	2.8	3.7	4.5	5.3	5.9	6.5	7.1	7.8	8.2
92.5°	7.6	8.6	9.5	10.5	11.5	12.2	12.7	13.1	13.6	14.0	14.3
95°	21.2	21.9	22.6	23.3	24.0	24.7	25.2	25.8	26.3	26.9	27.1
97.5°	37.0	37.6	38.2	38.7	39.3	39.9	40.5	41.2	41.8	42.5	42.8
100°	49.5	49.8	50.1	50.4	50.7	51.2	51.9	52.7	53.4	54.1	54.2
102.5°	62.5	62.6	62.7	62.9	63.0	63.4	64.0	64.7	65.3	65.9	66.2
105°	82.3	82.4	82.5	82.6	82.6	82.8	83.2	83.5	83.8	84.1	84.3
107.5°	103.2	103.3	103.4	103.5	103.6	103.6	103.7	103.7	103.8	103.8	104.0
110°	117.3	117.5	117.6	117.8	117.9	118.0	117.9	117.8	117.7	117.7	117.5



TEST NUMBER: P332497

CATALOG NUMBER: S124DIP-S350D365U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	132.0	132.0	132.1	132.1	132.1	132.1	131.9	131.8	131.7	131.5	131.5
115°	154.1	154.1	154.1	154.1	154.1	154.0	153.8	153.7	153.5	153.4	153.3
117.5°	174.8	174.9	175.0	175.0	175.1	175.1	175.0	174.9	174.7	174.6	174.4
120°	188.7	189.0	189.3	189.6	190.0	190.0	189.8	189.5	189.3	189.1	188.7
122.5°	203.1	203.2	203.4	203.5	203.6	203.6	203.5	203.4	203.3	203.2	202.9
125°	224.4	224.4	224.4	224.4	224.4	224.3	224.3	224.2	224.1	224.0	223.9
127.5°	243.7	243.9	244.2	244.4	244.6	244.7	244.6	244.4	244.3	244.2	244.0
130°	257.3	257.5	257.7	258.0	258.2	258.3	258.3	258.3	258.3	258.3	258.2
132.5°	271.1	271.3	271.4	271.6	271.8	271.8	271.8	271.7	271.7	271.6	271.4
135°	289.4	289.9	290.3	290.8	291.3	291.5	291.5	291.5	291.5	291.5	291.4
137.5°	309.3	309.6	309.8	310.0	310.2	310.4	310.5	310.6	310.8	310.9	310.7
140°	322.6	322.8	322.9	323.1	323.3	323.3	323.3	323.3	323.3	323.3	323.3
142.5°	334.8	334.9	335.1	335.2	335.4	335.5	335.4	335.3	335.3	335.2	335.2
145°	351.6	351.9	352.2	352.5	352.9	353.1	353.1	353.2	353.3	353.4	353.3
147.5°	368.3	368.7	369.0	369.4	369.8	369.9	369.9	369.8	369.8	369.7	369.6
150°	378.5	378.8	379.1	379.4	379.7	379.9	379.9	379.9	379.9	379.9	379.9
152.5°	388.1	388.3	388.4	388.6	388.8	388.9	389.0	389.1	389.1	389.2	389.4
155°	402.8	402.8	402.8	402.8	402.8	402.8	402.7	402.6	402.6	402.5	402.8
157.5°	415.3	415.1	415.0	414.9	414.7	414.6	414.6	414.6	414.6	414.6	414.8
160°	422.6	422.5	422.5	422.4	422.3	422.2	422.2	422.1	422.0	421.9	422.2
162.5°	429.4	429.2	429.0	428.8	428.6	428.5	428.4	428.3	428.2	428.1	428.6
165°	438.5	438.3	438.1	437.8	437.6	437.4	437.2	437.1	436.9	436.8	437.2
167.5°	445.5	445.2	444.9	444.5	444.2	444.0	444.1	444.1	444.1	444.1	444.6
170°	449.5	449.1	448.7	448.3	447.9	447.8	447.8	447.9	448.0	448.1	448.5
172.5°	452.3	452.0	451.6	451.3	451.0	450.8	450.8	450.9	450.9	450.9	451.4
175°	456.2	455.8	455.4	455.0	454.6	454.4	454.3	454.2	454.2	454.1	454.6
177.5°	457.5	457.2	456.8	456.5	456.2	456.1	456.1	456.1	456.1	456.1	456.5
180°	456.9	456.9	456.9	456.9	456.9	456.9	456.9	456.9	456.9	456.9	456.9



TEST NUMBER: P332497

CATALOG NUMBER: S124DIP-S350D365U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7
2.5°	588.6	589.5	590.3	590.7	590.6	590.5	590.4	590.3
5°	585.5	586.6	587.8	588.2	588.0	587.8	587.6	587.4
7.5°	578.9	579.9	580.8	581.2	581.1	580.9	580.8	580.7
10°	573.5	574.3	575.2	575.5	575.3	575.0	574.8	574.6
12.5°	566.8	567.7	568.7	569.0	568.7	568.4	568.1	567.8
15°	554.1	554.7	555.4	555.5	555.2	554.9	554.6	554.3
17.5°	539.6	540.0	540.4	540.5	540.3	540.1	539.9	539.7
20°	528.9	529.2	529.5	529.6	529.3	529.1	528.9	528.7
22.5°	517.6	518.2	518.8	518.9	518.5	518.1	517.7	517.4
25°	499.1	499.2	499.3	499.2	498.7	498.3	497.9	497.5
27.5°	478.3	478.1	477.8	477.4	476.9	476.4	475.8	475.3
30°	464.0	463.6	463.1	462.7	462.1	461.6	461.1	460.6
32.5°	449.4	448.9	448.4	447.9	447.4	446.8	446.3	445.8
35°	426.4	425.7	424.9	424.3	423.8	423.3	422.7	422.2
37.5°	402.3	401.5	400.7	400.0	399.3	398.6	397.9	397.2
40°	385.6	384.5	383.5	382.7	382.1	381.6	381.1	380.6
42.5°	369.3	368.1	366.9	366.1	365.7	365.4	365.0	364.7
45°	344.2	343.0	341.9	341.1	340.8	340.5	340.2	339.9
47.5°	319.8	318.5	317.2	316.2	315.4	314.6	313.8	313.0
50°	302.8	301.4	299.9	298.8	298.2	297.6	296.9	296.3
52.5°	285.4	284.1	282.8	281.7	280.9	280.1	279.3	278.5
55°	259.7	258.4	257.2	256.2	255.6	255.0	254.3	253.7
57.5°	234.0	232.8	231.6	230.7	230.1	229.5	228.9	228.2
60°	216.3	215.4	214.4	213.7	213.2	212.6	212.1	211.6
62.5°	199.1	198.2	197.3	196.6	196.1	195.6	195.1	194.5
65°	174.0	172.9	171.9	171.1	170.6	170.0	169.5	169.0
67.5°	148.1	147.1	146.1	145.5	145.4	145.2	145.1	144.9
70°	131.8	131.0	130.1	129.5	129.2	128.9	128.6	128.3
72.5°	115.5	114.8	114.1	113.6	113.3	113.0	112.7	112.4
75°	91.9	91.5	91.1	90.8	90.7	90.6	90.5	90.4
77.5°	69.6	69.5	69.4	69.2	68.9	68.6	68.3	68.1
80°	55.4	55.2	55.0	54.9	54.7	54.6	54.5	54.4
82.5°	42.7	42.6	42.5	42.4	42.3	42.1	42.0	41.9
85°	24.6	24.6	24.6	24.6	24.5	24.4	24.2	24.1
87.5°	10.8	10.9	11.0	11.1	11.1	11.1	11.2	11.2
90°	8.7	9.2	9.7	10.0	10.1	10.3	10.4	10.6
92.5°	14.6	14.8	15.1	15.3	15.4	15.5	15.6	15.7
95°	27.3	27.6	27.8	27.9	27.9	27.9	27.9	27.9
97.5°	43.0	43.3	43.6	43.7	43.7	43.7	43.7	43.7
100°	54.4	54.5	54.7	54.8	54.8	54.8	54.8	54.8
102.5°	66.4	66.6	66.8	67.0	67.0	67.1	67.1	67.2
105°	84.6	84.8	85.0	85.3	85.5	85.8	86.0	86.2
107.5°	104.3	104.5	104.7	104.8	104.8	104.8	104.8	104.7
110°	117.4	117.2	117.0	117.1	117.3	117.6	117.8	118.0





TEST NUMBER: P332497

CATALOG NUMBER: S124DIP-S350D365U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	131.5	131.4	131.4	131.4	131.5	131.5	131.5	131.6
115°	153.2	153.1	153.0	153.0	152.9	152.8	152.7	152.7
117.5°	174.1	173.8	173.6	173.4	173.2	173.0	172.9	172.7
120°	188.3	187.9	187.5	187.4	187.5	187.7	187.8	188.0
122.5°	202.7	202.4	202.1	201.8	201.6	201.3	201.0	200.7
125°	223.7	223.6	223.4	223.2	223.1	222.9	222.8	222.6
127.5°	243.9	243.7	243.5	243.4	243.3	243.2	243.0	242.9
130°	258.0	257.8	257.7	257.4	257.1	256.8	256.5	256.2
132.5°	271.3	271.1	271.0	270.8	270.7	270.6	270.5	270.3
135°	291.2	291.1	290.9	290.7	290.5	290.2	290.0	289.8
137.5°	310.5	310.3	310.1	310.0	310.0	310.1	310.1	310.2
140°	323.2	323.1	323.0	322.9	322.9	322.8	322.7	322.6
142.5°	335.2	335.2	335.1	335.1	335.1	335.1	335.1	335.1
145°	353.2	353.1	353.1	352.9	352.7	352.4	352.2	352.0
147.5°	369.6	369.5	369.4	369.4	369.3	369.2	369.1	369.1
150°	379.9	379.9	379.9	379.8	379.8	379.7	379.6	379.5
152.5°	389.6	389.8	390.0	389.9	389.7	389.5	389.3	389.1
155°	403.1	403.4	403.7	403.7	403.4	403.1	402.8	402.5
157.5°	415.0	415.3	415.5	415.5	415.2	415.0	414.7	414.4
160°	422.4	422.6	422.9	422.8	422.4	422.0	421.6	421.2
162.5°	429.0	429.4	429.8	429.8	429.5	429.1	428.7	428.3
165°	437.7	438.2	438.6	438.7	438.4	438.1	437.8	437.5
167.5°	445.1	445.5	446.0	446.0	445.5	445.0	444.5	444.0
170°	449.0	449.5	450.0	449.9	449.4	448.8	448.3	447.7
172.5°	452.0	452.5	453.0	453.0	452.5	451.9	451.4	450.8
175°	455.2	455.7	456.3	456.3	455.7	455.2	454.6	454.1
177.5°	456.9	457.4	457.8	457.8	457.3	456.8	456.3	455.8
180°	456.9	456.9	456.9	456.9	456.9	456.9	456.9	456.9

(END OF REPORT)